

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333717-935

Luminaire Tested: **S125RDIW-S1090D1560U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333717-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8327.4 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9143	9143	9143	9143
5°	10519	9155	8085	9155
10°	12066	9108	7134	9108
15°	13032	9014	6341	9014
20°	14370	8906	5856	8906
25°	16631	8763	5433	8763
30°	18098	8611	5158	8611
35°	15266	8435	4902	8435
40°	10662	8118	4683	8118
45°	7909	7691	4469	7691
50°	6306	7246	4285	7246
55°	5353	6694	4122	6694
60°	4624	6200	3858	6200
65°	4121	5665	3321	5665
70°	3620	5189	3029	5189
75°	3132	4494	2842	4494
80°	2377	3782	2377	3782
85°	1979	2971	2238	2971



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	1.6
10°-20°	397.8	4.8
20°-30°	630.8	7.6
30°-40°	760.7	9.1
40°-50°	679.3	8.2
50°-60°	520.9	6.3
60°-70°	338.5	4.1
70°-80°	164.6	2.0
80°-90°	42.9	0.5
90°-100°	111.8	1.3
100°-110°	330.0	4.0
110°-120°	559.0	6.7
120°-130°	735.7	8.8
130°-140°	824.3	9.9
140°-150°	807.9	9.7
150°-160°	678.6	8.1
160°-170°	451.1	5.4
170°-180°	157.9	1.9
0°-30°	1164.4	14.0
0°-40°	1925.0	23.1
0°-60°	3125.2	37.5
0°-90°	3671.3	44.1
90°-120°	1000.8	12.0
90°-150°	3368.6	40.5
90°-180°	4656.0	55.9
0°-180°	8327.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1416	1416	1416	1416	1416	
5°	1622	1412	1247	1412	1622	162
15°	1949	1348	948	1348	1949	559
25°	2334	1230	762	1230	2334	1072
35°	1936	1070	622	1070	1936	1170
45°	866	842	489	842	866	691
55°	475	594	366	594	475	431
65°	270	371	217	371	270	268
75°	126	180	114	180	126	134
85°	27	40	30	40	27	32
90°	31	1	31	1	31	19
95°	112	84	112	84	112	114
105°	322	296	322	296	322	341
115°	565	560	565	560	565	559
125°	822	817	822	817	822	734
135°	1066	1062	1066	1062	1066	822
145°	1292	1287	1292	1287	1292	807
155°	1473	1473	1473	1473	1473	678
165°	1597	1601	1597	1601	1597	450
175°	1658	1665	1658	1665	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1489.1	1488.2	1490.0	1484.9	1485.4	1477.5	1477.5	1471.4	1463.5	1457.5	1454.7
5°	1622.5	1623.7	1621.3	1612.7	1606.8	1598.1	1588.2	1570.8	1556.3	1542.3	1531.3
7.5°	1759.9	1760.7	1753.0	1750.3	1735.7	1725.0	1703.1	1679.3	1658.3	1631.6	1611.1
10°	1839.9	1839.3	1831.1	1824.7	1812.0	1795.7	1774.2	1746.3	1720.1	1691.1	1663.2
12.5°	1886.4	1884.8	1882.2	1874.5	1862.6	1848.2	1830.0	1802.5	1770.3	1738.5	1706.0
15°	1949.1	1945.0	1937.5	1927.6	1910.7	1893.9	1873.5	1849.2	1818.3	1782.3	1752.1
17.5°	2026.7	2026.9	2015.3	2001.5	1978.6	1948.9	1917.4	1878.1	1836.3	1796.6	1764.4
20°	2090.9	2089.1	2077.5	2050.8	2024.6	1987.4	1951.5	1903.2	1852.0	1800.4	1760.2
22.5°	2183.0	2178.4	2166.3	2131.2	2090.7	2042.8	1987.7	1928.7	1866.9	1808.2	1755.6
25°	2333.8	2330.3	2306.4	2265.8	2208.9	2135.0	2063.0	1982.2	1893.3	1816.0	1752.1
27.5°	2437.0	2433.2	2415.5	2381.7	2329.2	2251.5	2154.0	2046.0	1935.0	1828.7	1736.6
30°	2426.8	2435.5	2433.2	2417.5	2378.0	2308.3	2218.2	2096.7	1964.8	1839.9	1730.0
32.5°	2280.8	2288.6	2309.0	2339.9	2342.2	2314.3	2247.0	2134.8	1998.3	1856.1	1724.9
35°	1936.3	1946.8	1986.3	2048.5	2129.9	2197.8	2211.7	2151.3	2028.7	1875.9	1717.3
37.5°	1488.6	1545.8	1579.1	1644.5	1767.5	1892.5	2012.8	2057.1	2004.8	1867.8	1704.8
40°	1264.6	1278.5	1337.7	1411.5	1515.0	1645.2	1816.6	1940.3	1944.5	1849.2	1685.2
42.5°	1082.3	1099.9	1140.7	1199.5	1288.1	1418.3	1595.3	1758.6	1834.3	1798.0	1659.7
45°	865.9	879.3	908.9	954.2	1022.2	1129.7	1281.9	1470.8	1620.7	1679.5	1591.1
47.5°	711.3	718.5	744.3	778.9	829.1	907.5	1025.4	1189.3	1369.2	1495.2	1482.8
50°	627.6	635.8	655.5	681.7	724.1	790.3	884.5	1021.1	1206.4	1360.4	1391.2
52.5°	562.5	569.3	581.6	606.3	641.4	692.2	768.3	891.8	1058.6	1222.4	1293.6
55°	475.4	480.0	489.9	503.9	531.8	568.3	634.0	719.5	854.3	1019.3	1123.9
57.5°	403.6	405.9	412.2	425.1	444.4	471.1	518.5	590.9	687.6	836.2	951.7
60°	358.0	360.3	368.4	377.1	392.3	416.6	453.8	504.4	597.4	720.1	836.8
62.5°	321.7	323.1	326.6	335.3	348.5	367.4	396.7	437.9	511.9	619.6	729.9
65°	269.7	270.2	271.4	278.4	286.5	300.4	319.6	348.7	404.5	485.9	583.4
67.5°	219.6	220.5	224.5	227.0	235.5	242.8	254.1	276.3	315.6	370.4	446.3
70°	191.7	191.2	195.3	198.2	201.0	209.8	217.3	235.4	259.8	301.6	365.0
72.5°	165.7	164.2	166.0	167.0	170.8	176.8	184.3	195.4	214.2	243.1	291.5
75°	125.5	126.1	126.1	127.3	130.2	132.5	134.8	140.6	151.1	170.3	196.4
77.5°	88.1	87.1	89.6	90.0	91.7	94.3	96.3	98.6	102.9	110.7	124.2
80°	63.9	63.9	64.5	66.2	65.7	66.8	69.7	72.1	77.3	82.0	86.6
82.5°	49.1	48.6	49.2	49.5	49.4	50.5	51.6	52.1	54.1	56.4	59.6
85°	26.7	26.7	27.3	27.3	27.9	27.9	28.5	28.5	28.5	29.0	29.6
87.5°	16.4	15.8	15.2	15.0	15.3	16.0	15.2	14.5	14.2	13.9	13.9
90°	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7	22.2	20.8	18.8
92.5°	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6	51.7	49.9	47.4
95°	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0	102.0	100.0	97.1
97.5°	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0	161.1	159.2	155.2
100°	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9	201.3	198.6	194.9
102.5°	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9	243.1	240.2	238.3
105°	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8	312.1	310.4	308.6
107.5°	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1	386.2	385.4	384.1
110°	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1	437.1	436.3	435.4



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0	488.6	488.3	487.2
115°	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9	567.1	567.5	566.9
117.5°	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8	644.5	644.4	643.8
120°	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3	697.3	697.3	697.0
122.5°	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8	749.0	749.2	748.5
125°	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8	825.3	825.9	825.6
127.5°	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1	900.3	900.7	900.3
130°	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9	950.2	950.5	949.9
132.5°	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7	998.0	998.3	998.4
135°	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3	1071.3	1071.3	1071.0
137.5°	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9	1142.5	1142.2	1141.5
140°	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0	1187.4	1186.9	1186.0
142.5°	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2	1231.8	1231.5	1230.5
145°	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9	1295.9	1295.9	1295.0
147.5°	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0	1354.3	1353.6	1352.9
150°	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1	1392.1	1392.1	1390.9
152.5°	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7	1426.0	1425.3	1424.8
155°	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1	1475.0	1473.9	1473.5
157.5°	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0	1517.9	1516.7	1516.4
160°	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0	1543.8	1542.7	1542.4
162.5°	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3	1568.0	1566.5	1566.5
165°	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1	1600.9	1599.8	1599.5
167.5°	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3	1624.6	1622.9	1622.9
170°	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9	1639.2	1637.4	1637.4
172.5°	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3	1649.6	1647.9	1647.9
175°	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0	1661.2	1659.5	1659.5
177.5°	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3	1666.9	1665.5	1665.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1454.7	1451.4	1445.4	1439.8	1432.8	1426.8	1422.6	1417.5	1411.0	1403.1	1396.5
5°	1519.1	1506.2	1489.4	1474.9	1456.3	1441.7	1426.7	1412.1	1397.6	1379.0	1362.7
7.5°	1590.4	1564.0	1538.3	1506.1	1476.8	1450.6	1425.5	1400.1	1375.2	1348.8	1323.4
10°	1634.1	1602.1	1566.7	1526.0	1488.8	1453.4	1420.8	1388.9	1355.2	1325.5	1293.6
12.5°	1675.1	1633.7	1593.2	1541.9	1497.2	1453.9	1412.5	1372.6	1336.6	1298.1	1263.9
15°	1712.0	1671.3	1626.0	1563.2	1501.1	1448.7	1399.9	1348.2	1303.5	1260.4	1222.1
17.5°	1726.3	1683.6	1631.0	1570.6	1502.7	1436.9	1374.0	1317.3	1264.6	1214.5	1171.4
20°	1720.7	1679.5	1625.4	1567.9	1495.2	1426.7	1358.7	1295.9	1237.3	1184.3	1138.4
22.5°	1707.2	1664.6	1612.4	1551.6	1482.6	1409.9	1337.3	1270.3	1208.8	1154.1	1104.1
25°	1687.0	1628.9	1575.5	1516.1	1450.5	1378.5	1303.5	1229.7	1164.0	1108.2	1053.6
27.5°	1665.9	1593.5	1525.4	1466.5	1397.1	1332.8	1260.6	1184.9	1115.9	1059.0	1003.0
30°	1646.9	1565.6	1490.6	1423.7	1358.1	1297.1	1228.5	1154.7	1083.8	1025.1	968.2
32.5°	1623.2	1536.7	1454.3	1377.3	1313.9	1253.4	1191.3	1120.8	1051.7	991.2	933.3
35°	1593.5	1483.1	1393.5	1311.6	1241.3	1182.6	1126.8	1069.9	1000.7	938.0	881.6
37.5°	1554.4	1429.1	1325.5	1236.3	1162.1	1103.2	1059.1	1007.1	944.0	883.9	831.6
40°	1530.7	1390.1	1276.7	1188.4	1110.5	1048.4	1007.1	962.9	905.4	849.0	796.7
42.5°	1499.1	1354.3	1227.4	1135.4	1057.0	997.2	955.5	916.9	868.7	815.5	759.5
45°	1437.1	1284.9	1151.8	1053.0	974.0	915.2	876.3	842.1	805.5	756.6	707.8
47.5°	1356.4	1212.5	1073.2	965.4	887.9	833.4	795.7	768.6	742.4	700.9	653.5
50°	1291.8	1153.0	1016.9	912.4	829.8	778.1	742.7	721.2	697.3	659.6	620.1
52.5°	1215.6	1091.6	958.4	851.4	773.6	725.1	691.0	669.6	650.0	619.1	581.4
55°	1095.5	986.8	864.7	767.7	696.2	647.4	614.8	594.5	582.9	556.7	527.1
57.5°	956.7	878.9	771.3	677.7	614.5	566.3	542.4	525.1	512.0	493.5	472.6
60°	860.1	805.5	708.9	620.1	562.0	516.0	494.6	480.0	467.8	452.1	435.8
62.5°	762.0	722.2	638.3	562.0	508.5	470.0	449.9	436.8	422.8	412.2	396.3
65°	630.5	595.0	536.9	477.1	427.7	396.9	382.4	370.7	362.1	350.4	339.4
67.5°	490.5	476.0	435.9	394.7	359.2	331.8	319.3	311.2	300.7	293.7	286.1
70°	404.5	397.5	369.0	341.7	308.6	290.0	278.4	274.8	262.1	255.1	249.9
72.5°	328.2	324.9	308.6	289.6	266.3	250.0	239.3	235.4	227.2	221.6	218.3
75°	224.9	226.1	223.2	210.9	202.2	191.7	182.4	180.1	174.4	169.7	166.8
77.5°	142.2	148.2	148.4	147.8	144.4	137.9	134.1	132.4	126.7	124.9	124.2
80°	97.6	104.0	109.9	109.3	108.1	106.3	103.4	101.7	98.8	97.0	95.9
82.5°	65.1	71.0	75.9	79.0	78.8	77.1	75.1	74.3	73.7	72.4	72.2
85°	30.8	31.9	33.7	37.8	40.6	41.2	40.6	40.1	38.3	38.9	39.5
87.5°	14.0	13.6	13.7	13.3	12.3	14.2	15.2	15.2	14.6	14.2	13.7
90°	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3	3.6	5.9	8.3
92.5°	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4	33.1	34.7	36.2
95°	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4	85.0	85.6	86.1
97.5°	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3	140.4	140.7	140.9
100°	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8
102.5°	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4	227.6	228.8	229.9
105°	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1	297.5	298.9	300.4
107.5°	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9	374.4	375.8	377.3
110°	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9	427.4	428.8	430.2



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9	480.7	481.5	482.2
115°	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6	560.9	562.0	563.1
117.5°	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6	640.2	640.7	641.2
120°	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5	691.0	692.4	693.9
122.5°	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6	744.1	744.6	745.1
125°	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7	818.5	820.3	822.0
127.5°	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7	895.7	896.6	897.6
130°	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4	942.9	944.3	945.7
132.5°	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2	990.6	992.9	995.3
135°	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2	1063.9	1065.7	1067.4
137.5°	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8	1133.5	1135.1	1136.8
140°	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5	1177.9	1179.3	1180.8
142.5°	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2	1222.4	1223.6	1224.8
145°	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9	1288.0	1289.2	1290.3
147.5°	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6	1348.2	1348.8	1349.5
150°	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1	1387.8	1387.6	1387.2
152.5°	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3	1421.8	1422.2	1422.5
155°	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2	1517.6	1517.0	1516.3
160°	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2	1544.4	1543.5	1542.7
162.5°	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2	1568.5	1567.9	1567.3
165°	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1	1600.5	1599.9	1599.4
167.5°	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1	1626.9	1625.8	1624.6
170°	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6	1641.5	1640.3	1639.2
172.5°	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0	1651.9	1650.7	1649.6
175°	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7	1663.5	1662.4	1661.2
177.5°	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7	1669.7	1668.9	1667.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1391.9	1385.4	1380.8	1371.5	1364.9	1362.2	1357.0	1355.6	1360.7	1357.0	1356.6
5°	1350.6	1333.7	1320.3	1306.9	1292.4	1283.1	1269.2	1266.9	1263.3	1258.1	1257.0
7.5°	1300.9	1278.9	1261.7	1239.7	1220.5	1205.1	1187.6	1179.3	1174.8	1168.0	1159.0
10°	1267.4	1241.3	1218.1	1195.9	1172.2	1153.0	1135.5	1122.1	1113.4	1105.3	1101.8
12.5°	1234.4	1207.8	1178.0	1151.3	1124.7	1103.2	1083.9	1075.2	1065.6	1056.0	1047.9
15°	1183.2	1147.7	1115.2	1084.3	1061.7	1038.5	1019.9	1007.1	992.6	988.5	972.8
17.5°	1128.8	1094.0	1055.9	1023.5	997.2	971.6	951.1	936.7	925.7	910.8	903.5
20°	1094.8	1053.6	1016.4	986.8	957.7	927.5	906.5	894.3	883.9	871.7	865.9
22.5°	1058.6	1018.2	980.2	945.4	915.8	886.1	871.2	858.6	846.7	835.4	827.8
25°	1005.3	964.7	924.5	888.6	857.7	836.2	818.8	804.3	797.9	786.9	778.7
27.5°	952.7	909.5	867.9	831.9	807.8	786.5	772.2	760.7	749.2	739.5	732.5
30°	918.8	874.6	829.2	800.8	775.2	754.8	739.2	728.1	719.5	710.8	705.5
32.5°	884.8	839.3	799.0	768.3	744.1	726.5	710.3	699.8	690.6	681.0	674.8
35°	830.4	783.9	751.4	721.2	697.3	681.1	670.0	655.0	647.4	640.4	634.0
37.5°	779.9	736.7	701.5	674.9	654.2	638.1	623.8	615.6	606.3	600.0	594.7
40°	742.7	703.2	671.2	643.3	628.2	610.2	596.8	586.3	579.4	571.3	565.4
42.5°	709.2	672.4	641.4	616.3	597.5	582.3	569.4	559.0	550.1	544.3	539.4
45°	661.9	625.3	595.0	571.8	554.4	539.8	526.5	521.2	509.6	502.7	500.3
47.5°	612.9	580.2	551.0	529.6	511.8	498.0	485.4	474.8	468.4	461.5	457.8
50°	580.0	548.5	521.2	500.3	482.9	467.8	456.2	449.2	440.5	434.1	429.5
52.5°	547.0	517.9	490.6	470.6	455.5	440.4	427.4	420.4	412.2	408.0	404.8
55°	499.8	469.0	445.7	425.9	410.3	396.3	384.1	377.1	372.0	367.8	366.7
57.5°	446.3	421.9	400.3	382.5	366.2	353.1	342.4	335.8	331.1	330.5	327.1
60°	411.5	389.3	369.6	350.4	336.5	324.3	315.0	307.4	302.7	302.2	301.0
62.5°	376.6	355.4	337.1	320.2	307.6	295.9	287.1	278.6	275.8	272.9	270.4
65°	324.9	305.7	290.6	277.2	263.8	253.9	245.2	240.0	233.6	230.1	223.8
67.5°	274.1	259.2	244.7	233.4	222.9	213.5	206.3	198.5	194.2	191.4	186.8
70°	240.6	228.9	214.5	202.2	194.1	186.6	180.7	172.0	169.1	166.8	164.5
72.5°	209.0	198.7	186.6	176.7	168.5	161.4	154.7	150.6	147.7	145.4	144.0
75°	164.5	154.5	144.1	137.2	131.3	125.5	122.0	119.2	118.0	117.4	115.0
77.5°	120.8	115.5	107.2	101.6	97.7	95.4	92.3	90.7	90.7	88.1	87.3
80°	92.4	89.5	82.5	80.2	77.3	75.0	73.2	70.3	67.4	66.2	64.5
82.5°	68.7	65.8	63.0	59.2	56.8	55.4	53.7	52.6	53.0	51.4	50.5
85°	36.6	33.7	32.5	31.9	30.8	31.9	31.3	30.8	30.2	29.6	30.2
87.5°	13.7	14.1	14.1	15.4	14.5	15.3	15.6	15.4	15.8	16.0	15.8
90°	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7	25.1	26.5	27.7
92.5°	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6	55.5	57.5	58.7
95°	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0	106.1	108.1	109.3
97.5°	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0	164.9	166.8	168.0
100°	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9	206.5	209.1	210.7
102.5°	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9	248.7	251.5	253.4
105°	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8	315.6	317.3	318.6
107.5°	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1	388.0	388.8	389.3
110°	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1	438.9	439.8	440.1



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0	489.5	489.8	489.8
115°	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9	566.6	566.3	566.0
117.5°	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8	645.1	645.2	644.8
120°	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3	697.3	697.3	696.7
122.5°	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8	748.6	748.3	747.8
125°	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8	824.1	823.5	823.1
127.5°	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1	899.8	899.5	899.1
130°	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9	949.7	949.3	948.9
132.5°	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7	997.5	997.1	996.6
135°	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3	1071.3	1071.3	1070.7
137.5°	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9	1143.2	1143.6	1143.1
140°	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0	1188.6	1189.1	1188.7
142.5°	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2	1232.5	1233.0	1232.3
145°	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9	1295.9	1295.9	1295.5
147.5°	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0	1355.6	1356.3	1355.7
150°	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1	1392.1	1392.1	1391.7
152.5°	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7	1427.4	1428.1	1427.9
155°	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1	1477.3	1478.4	1478.3
157.5°	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0	1520.2	1521.3	1521.0
160°	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0	1546.1	1547.3	1547.1
162.5°	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3	1570.7	1572.1	1571.9
165°	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1	1603.3	1604.4	1604.1
167.5°	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3	1628.1	1629.8	1629.8
170°	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9	1642.6	1644.3	1644.3
172.5°	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3	1653.0	1654.8	1654.8
175°	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0	1664.7	1666.5	1666.3
177.5°	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3	1669.7	1671.0	1670.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1356.1	1351.0	1349.6	1351.4	1349.6	1351.0	1356.1	1356.6	1357.0	1360.7	1355.6
5°	1251.2	1245.4	1248.3	1247.1	1248.3	1245.4	1251.2	1257.0	1258.1	1263.3	1266.9
7.5°	1158.9	1151.7	1144.0	1146.4	1144.0	1151.7	1158.9	1159.0	1168.0	1174.8	1179.3
10°	1094.2	1088.5	1084.9	1087.9	1084.9	1088.5	1094.2	1101.8	1105.3	1113.4	1122.1
12.5°	1039.8	1036.4	1033.4	1032.1	1033.4	1036.4	1039.8	1047.9	1056.0	1065.6	1075.2
15°	965.9	958.9	956.0	948.4	956.0	958.9	965.9	972.8	988.5	992.6	1007.1
17.5°	897.6	895.3	887.7	884.5	887.7	895.3	897.6	903.5	910.8	925.7	936.7
20°	857.1	854.8	847.3	852.0	847.3	854.8	857.1	865.9	871.7	883.9	894.3
22.5°	823.7	818.6	816.1	814.8	816.1	818.6	823.7	827.8	835.4	846.7	858.6
25°	776.4	768.8	765.9	762.4	765.9	768.8	776.4	778.7	786.9	797.9	804.3
27.5°	729.2	725.1	721.3	720.4	721.3	725.1	729.2	732.5	739.5	749.2	760.7
30°	698.5	694.5	691.6	691.6	691.6	694.5	698.5	705.5	710.8	719.5	728.1
32.5°	671.1	668.0	665.0	664.6	665.0	668.0	671.1	674.8	681.0	690.6	699.8
35°	631.1	626.5	625.3	621.8	625.3	626.5	631.1	634.0	640.4	647.4	655.0
37.5°	589.6	585.7	585.7	585.3	585.7	585.7	589.6	594.7	600.0	606.3	615.6
40°	563.1	560.2	559.6	555.5	559.6	560.2	563.1	565.4	571.3	579.4	586.3
42.5°	534.8	533.2	531.2	529.5	531.2	533.2	534.8	539.4	544.3	550.1	559.0
45°	496.3	492.2	492.2	489.3	492.2	492.2	496.3	500.3	502.7	509.6	521.2
47.5°	456.5	453.4	453.7	450.7	453.7	453.4	456.5	457.8	461.5	468.4	474.8
50°	430.1	428.3	427.7	426.5	427.7	428.3	430.1	429.5	434.1	440.5	449.2
52.5°	403.6	402.7	404.9	402.3	404.9	402.7	403.6	404.8	408.0	412.2	420.4
55°	367.8	366.1	369.6	366.1	369.6	366.1	367.8	366.7	367.8	372.0	377.1
57.5°	326.8	325.2	328.3	326.6	328.3	325.2	326.8	327.1	330.5	331.1	335.8
60°	299.9	296.4	298.1	298.7	298.1	296.4	299.9	301.0	302.2	302.7	307.4
62.5°	267.8	265.7	267.0	264.3	267.0	265.7	267.8	270.4	272.9	275.8	278.6
65°	222.6	220.8	218.5	217.3	218.5	220.8	222.6	223.8	230.1	233.6	240.0
67.5°	187.0	182.8	182.7	183.7	182.7	182.8	187.0	186.8	191.4	194.2	198.5
70°	161.0	161.0	160.4	160.4	160.4	161.0	161.0	164.5	166.8	169.1	172.0
72.5°	142.8	142.4	141.3	140.9	141.3	142.4	142.8	144.0	145.4	147.7	150.6
75°	115.0	115.6	114.5	113.9	114.5	115.6	115.0	115.0	117.4	118.0	119.2
77.5°	85.0	82.5	83.8	82.5	83.8	82.5	85.0	87.3	88.1	90.7	90.7
80°	64.5	63.9	65.7	63.9	65.7	63.9	64.5	64.5	66.2	67.4	70.3
82.5°	51.1	50.5	51.2	49.9	51.2	50.5	51.1	50.5	51.4	53.0	52.6
85°	30.8	30.2	29.6	30.2	29.6	30.2	30.8	30.2	29.6	30.2	30.8
87.5°	16.4	16.1	16.3	16.4	16.3	16.1	16.4	15.8	16.0	15.8	15.4
90°	28.6	29.4	30.3	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7
92.5°	59.4	60.0	60.6	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6
95°	109.9	110.6	111.1	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0
97.5°	168.3	168.7	169.0	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0
100°	211.2	211.8	212.4	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9
102.5°	254.2	254.9	255.8	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9
105°	319.4	320.3	321.2	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8
107.5°	389.2	389.2	389.1	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1
110°	439.8	439.5	439.2	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.3	488.8	488.3	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0
115°	565.8	565.4	565.2	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9
117.5°	643.6	642.5	641.4	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8
120°	695.6	694.4	693.3	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3
122.5°	746.8	745.9	744.9	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8
125°	822.9	822.5	822.3	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8
127.5°	898.5	897.9	897.3	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1
130°	948.4	947.8	947.2	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9
132.5°	995.8	995.0	994.2	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7
135°	1069.5	1068.4	1067.2	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3
137.5°	1141.6	1140.1	1138.7	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9
140°	1187.3	1185.9	1184.4	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0
142.5°	1230.9	1229.5	1228.0	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2
145°	1294.6	1293.7	1292.9	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9
147.5°	1353.8	1351.8	1349.9	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0
150°	1391.1	1390.6	1390.0	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1
152.5°	1426.8	1425.8	1424.8	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7
155°	1476.9	1475.4	1473.9	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1
157.5°	1519.0	1517.1	1515.2	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0
160°	1545.7	1544.2	1542.8	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0
162.5°	1570.3	1568.6	1566.9	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3
165°	1602.4	1600.7	1599.0	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1
167.5°	1628.0	1626.3	1624.4	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3
170°	1642.2	1640.2	1638.1	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9
172.5°	1652.9	1651.1	1649.3	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3
175°	1664.3	1662.2	1660.3	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0
177.5°	1669.3	1667.7	1666.0	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1357.0	1362.2	1364.9	1371.5	1380.8	1385.4	1391.9	1396.5	1403.1	1411.0	1417.5
5°	1269.2	1283.1	1292.4	1306.9	1320.3	1333.7	1350.6	1362.7	1379.0	1397.6	1412.1
7.5°	1187.6	1205.1	1220.5	1239.7	1261.7	1278.9	1300.9	1323.4	1348.8	1375.2	1400.1
10°	1135.5	1153.0	1172.2	1195.9	1218.1	1241.3	1267.4	1293.6	1325.5	1355.2	1388.9
12.5°	1083.9	1103.2	1124.7	1151.3	1178.0	1207.8	1234.4	1263.9	1298.1	1336.6	1372.6
15°	1019.9	1038.5	1061.7	1084.3	1115.2	1147.7	1183.2	1222.1	1260.4	1303.5	1348.2
17.5°	951.1	971.6	997.2	1023.5	1055.9	1094.0	1128.8	1171.4	1214.5	1264.6	1317.3
20°	906.5	927.5	957.7	986.8	1016.4	1053.6	1094.8	1138.4	1184.3	1237.3	1295.9
22.5°	871.2	886.1	915.8	945.4	980.2	1018.2	1058.6	1104.1	1154.1	1208.8	1270.3
25°	818.8	836.2	857.7	888.6	924.5	964.7	1005.3	1053.6	1108.2	1164.0	1229.7
27.5°	772.2	786.5	807.8	831.9	867.9	909.5	952.7	1003.0	1059.0	1115.9	1184.9
30°	739.2	754.8	775.2	800.8	829.2	874.6	918.8	968.2	1025.1	1083.8	1154.7
32.5°	710.3	726.5	744.1	768.3	799.0	839.3	884.8	933.3	991.2	1051.7	1120.8
35°	670.0	681.1	697.3	721.2	751.4	783.9	830.4	881.6	938.0	1000.7	1069.9
37.5°	623.8	638.1	654.2	674.9	701.5	736.7	779.9	831.6	883.9	944.0	1007.1
40°	596.8	610.2	628.2	643.3	671.2	703.2	742.7	796.7	849.0	905.4	962.9
42.5°	569.4	582.3	597.5	616.3	641.4	672.4	709.2	759.5	815.5	868.7	916.9
45°	526.5	539.8	554.4	571.8	595.0	625.3	661.9	707.8	756.6	805.5	842.1
47.5°	485.4	498.0	511.8	529.6	551.0	580.2	612.9	653.5	700.9	742.4	768.6
50°	456.2	467.8	482.9	500.3	521.2	548.5	580.0	620.1	659.6	697.3	721.2
52.5°	427.4	440.4	455.5	470.6	490.6	517.9	547.0	581.4	619.1	650.0	669.6
55°	384.1	396.3	410.3	425.9	445.7	469.0	499.8	527.1	556.7	582.9	594.5
57.5°	342.4	353.1	366.2	382.5	400.3	421.9	446.3	472.6	493.5	512.0	525.1
60°	315.0	324.3	336.5	350.4	369.6	389.3	411.5	435.8	452.1	467.8	480.0
62.5°	287.1	295.9	307.6	320.2	337.1	355.4	376.6	396.3	412.2	422.8	436.8
65°	245.2	253.9	263.8	277.2	290.6	305.7	324.9	339.4	350.4	362.1	370.7
67.5°	206.3	213.5	222.9	233.4	244.7	259.2	274.1	286.1	293.7	300.7	311.2
70°	180.7	186.6	194.1	202.2	214.5	228.9	240.6	249.9	255.1	262.1	274.8
72.5°	154.7	161.4	168.5	176.7	186.6	198.7	209.0	218.3	221.6	227.2	235.4
75°	122.0	125.5	131.3	137.2	144.1	154.5	164.5	166.8	169.7	174.4	180.1
77.5°	92.3	95.4	97.7	101.6	107.2	115.5	120.8	124.2	124.9	126.7	132.4
80°	73.2	75.0	77.3	80.2	82.5	89.5	92.4	95.9	97.0	98.8	101.7
82.5°	53.7	55.4	56.8	59.2	63.0	65.8	68.7	72.2	72.4	73.7	74.3
85°	31.3	31.9	30.8	31.9	32.5	33.7	36.6	39.5	38.9	38.3	40.1
87.5°	15.6	15.3	14.5	15.4	14.1	14.1	13.7	13.7	14.2	14.6	15.2
90°	22.2	20.8	18.8	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3
92.5°	51.7	49.9	47.4	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4
95°	102.0	100.0	97.1	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4
97.5°	161.1	159.2	155.2	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3
100°	201.3	198.6	194.9	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8
102.5°	243.1	240.2	238.3	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4
105°	312.1	310.4	308.6	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1
107.5°	386.2	385.4	384.1	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9
110°	437.1	436.3	435.4	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	488.6	488.3	487.2	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9
115°	567.1	567.5	566.9	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6
117.5°	644.5	644.4	643.8	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6
120°	697.3	697.3	697.0	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5
122.5°	749.0	749.2	748.5	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6
125°	825.3	825.9	825.6	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7
127.5°	900.3	900.7	900.3	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7
130°	950.2	950.5	949.9	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4
132.5°	998.0	998.3	998.4	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2
135°	1071.3	1071.3	1071.0	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2
137.5°	1142.5	1142.2	1141.5	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8
140°	1187.4	1186.9	1186.0	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5
142.5°	1231.8	1231.5	1230.5	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2
145°	1295.9	1295.9	1295.0	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9
147.5°	1354.3	1353.6	1352.9	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6
150°	1392.1	1392.1	1390.9	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1
152.5°	1426.0	1425.3	1424.8	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3
155°	1475.0	1473.9	1473.5	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1517.9	1516.7	1516.4	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2
160°	1543.8	1542.7	1542.4	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2
162.5°	1568.0	1566.5	1566.5	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2
165°	1600.9	1599.8	1599.5	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1
167.5°	1624.6	1622.9	1622.9	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1
170°	1639.2	1637.4	1637.4	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6
172.5°	1649.6	1647.9	1647.9	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0
175°	1661.2	1659.5	1659.5	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7
177.5°	1666.9	1665.5	1665.7	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1422.6	1426.8	1432.8	1439.8	1445.4	1451.4	1454.7	1454.7	1457.5	1463.5	1471.4
5°	1426.7	1441.7	1456.3	1474.9	1489.4	1506.2	1519.1	1531.3	1542.3	1556.3	1570.8
7.5°	1425.5	1450.6	1476.8	1506.1	1538.3	1564.0	1590.4	1611.1	1631.6	1658.3	1679.3
10°	1420.8	1453.4	1488.8	1526.0	1566.7	1602.1	1634.1	1663.2	1691.1	1720.1	1746.3
12.5°	1412.5	1453.9	1497.2	1541.9	1593.2	1633.7	1675.1	1706.0	1738.5	1770.3	1802.5
15°	1399.9	1448.7	1501.1	1563.2	1626.0	1671.3	1712.0	1752.1	1782.3	1818.3	1849.2
17.5°	1374.0	1436.9	1502.7	1570.6	1631.0	1683.6	1726.3	1764.4	1796.6	1836.3	1878.1
20°	1358.7	1426.7	1495.2	1567.9	1625.4	1679.5	1720.7	1760.2	1800.4	1852.0	1903.2
22.5°	1337.3	1409.9	1482.6	1551.6	1612.4	1664.6	1707.2	1755.6	1808.2	1866.9	1928.7
25°	1303.5	1378.5	1450.5	1516.1	1575.5	1628.9	1687.0	1752.1	1816.0	1893.3	1982.2
27.5°	1260.6	1332.8	1397.1	1466.5	1525.4	1593.5	1665.9	1736.6	1828.7	1935.0	2046.0
30°	1228.5	1297.1	1358.1	1423.7	1490.6	1565.6	1646.9	1730.0	1839.9	1964.8	2096.7
32.5°	1191.3	1253.4	1313.9	1377.3	1454.3	1536.7	1623.2	1724.9	1856.1	1998.3	2134.8
35°	1126.8	1182.6	1241.3	1311.6	1393.5	1483.1	1593.5	1717.3	1875.9	2028.7	2151.3
37.5°	1059.1	1103.2	1162.1	1236.3	1325.5	1429.1	1554.4	1704.8	1867.8	2004.8	2057.1
40°	1007.1	1048.4	1110.5	1188.4	1276.7	1390.1	1530.7	1685.2	1849.2	1944.5	1940.3
42.5°	955.5	997.2	1057.0	1135.4	1227.4	1354.3	1499.1	1659.7	1798.0	1834.3	1758.6
45°	876.3	915.2	974.0	1053.0	1151.8	1284.9	1437.1	1591.1	1679.5	1620.7	1470.8
47.5°	795.7	833.4	887.9	965.4	1073.2	1212.5	1356.4	1482.8	1495.2	1369.2	1189.3
50°	742.7	778.1	829.8	912.4	1016.9	1153.0	1291.8	1391.2	1360.4	1206.4	1021.1
52.5°	691.0	725.1	773.6	851.4	958.4	1091.6	1215.6	1293.6	1222.4	1058.6	891.8
55°	614.8	647.4	696.2	767.7	864.7	986.8	1095.5	1123.9	1019.3	854.3	719.5
57.5°	542.4	566.3	614.5	677.7	771.3	878.9	956.7	951.7	836.2	687.6	590.9
60°	494.6	516.0	562.0	620.1	708.9	805.5	860.1	836.8	720.1	597.4	504.4
62.5°	449.9	470.0	508.5	562.0	638.3	722.2	762.0	729.9	619.6	511.9	437.9
65°	382.4	396.9	427.7	477.1	536.9	595.0	630.5	583.4	485.9	404.5	348.7
67.5°	319.3	331.8	359.2	394.7	435.9	476.0	490.5	446.3	370.4	315.6	276.3
70°	278.4	290.0	308.6	341.7	369.0	397.5	404.5	365.0	301.6	259.8	235.4
72.5°	239.3	250.0	266.3	289.6	308.6	324.9	328.2	291.5	243.1	214.2	195.4
75°	182.4	191.7	202.2	210.9	223.2	226.1	224.9	196.4	170.3	151.1	140.6
77.5°	134.1	137.9	144.4	147.8	148.4	148.2	142.2	124.2	110.7	102.9	98.6
80°	103.4	106.3	108.1	109.3	109.9	104.0	97.6	86.6	82.0	77.3	72.1
82.5°	75.1	77.1	78.8	79.0	75.9	71.0	65.1	59.6	56.4	54.1	52.1
85°	40.6	41.2	40.6	37.8	33.7	31.9	30.8	29.6	29.0	28.5	28.5
87.5°	15.2	14.2	12.3	13.3	13.7	13.6	14.0	13.9	13.9	14.2	14.5
90°	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7
92.5°	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6
95°	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0
97.5°	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0
100°	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9
102.5°	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9
105°	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8
107.5°	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1
110°	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0
115°	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9
117.5°	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8
120°	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3
122.5°	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8
125°	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8
127.5°	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1
130°	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9
132.5°	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7
135°	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3
137.5°	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9
140°	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0
142.5°	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2
145°	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9
147.5°	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0
150°	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1
152.5°	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7
155°	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1
157.5°	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0
160°	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0
162.5°	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3
165°	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1
167.5°	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3
170°	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9
172.5°	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3
175°	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0
177.5°	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1477.5	1477.5	1485.4	1484.9	1490.0	1488.2	1489.1
5°	1588.2	1598.1	1606.8	1612.7	1621.3	1623.7	1622.5
7.5°	1703.1	1725.0	1735.7	1750.3	1753.0	1760.7	1759.9
10°	1774.2	1795.7	1812.0	1824.7	1831.1	1839.3	1839.9
12.5°	1830.0	1848.2	1862.6	1874.5	1882.2	1884.8	1886.4
15°	1873.5	1893.9	1910.7	1927.6	1937.5	1945.0	1949.1
17.5°	1917.4	1948.9	1978.6	2001.5	2015.3	2026.9	2026.7
20°	1951.5	1987.4	2024.6	2050.8	2077.5	2089.1	2090.9
22.5°	1987.7	2042.8	2090.7	2131.2	2166.3	2178.4	2183.0
25°	2063.0	2135.0	2208.9	2265.8	2306.4	2330.3	2333.8
27.5°	2154.0	2251.5	2329.2	2381.7	2415.5	2433.2	2437.0
30°	2218.2	2308.3	2378.0	2417.5	2433.2	2435.5	2426.8
32.5°	2247.0	2314.3	2342.2	2339.9	2309.0	2288.6	2280.8
35°	2211.7	2197.8	2129.9	2048.5	1986.3	1946.8	1936.3
37.5°	2012.8	1892.5	1767.5	1644.5	1579.1	1545.8	1488.6
40°	1816.6	1645.2	1515.0	1411.5	1337.7	1278.5	1264.6
42.5°	1595.3	1418.3	1288.1	1199.5	1140.7	1099.9	1082.3
45°	1281.9	1129.7	1022.2	954.2	908.9	879.3	865.9
47.5°	1025.4	907.5	829.1	778.9	744.3	718.5	711.3
50°	884.5	790.3	724.1	681.7	655.5	635.8	627.6
52.5°	768.3	692.2	641.4	606.3	581.6	569.3	562.5
55°	634.0	568.3	531.8	503.9	489.9	480.0	475.4
57.5°	518.5	471.1	444.4	425.1	412.2	405.9	403.6
60°	453.8	416.6	392.3	377.1	368.4	360.3	358.0
62.5°	396.7	367.4	348.5	335.3	326.6	323.1	321.7
65°	319.6	300.4	286.5	278.4	271.4	270.2	269.7
67.5°	254.1	242.8	235.5	227.0	224.5	220.5	219.6
70°	217.3	209.8	201.0	198.2	195.3	191.2	191.7
72.5°	184.3	176.8	170.8	167.0	166.0	164.2	165.7
75°	134.8	132.5	130.2	127.3	126.1	126.1	125.5
77.5°	96.3	94.3	91.7	90.0	89.6	87.1	88.1
80°	69.7	66.8	65.7	66.2	64.5	63.9	63.9
82.5°	51.6	50.5	49.4	49.5	49.2	48.6	49.1
85°	28.5	27.9	27.9	27.3	27.3	26.7	26.7
87.5°	15.2	16.0	15.3	15.0	15.2	15.8	16.4
90°	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.9	439.8	440.1	439.8	439.5	439.2	438.9



TEST NUMBER: P333717-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)