

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333702-935

Luminaire Tested: **S125RDIW-S1090D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333702-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D470U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5250.3 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	54	50
3	86	76	68	63	81	72	65	60	65	60	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	32	54	43	36	31	39	33	29	36	30	27	32	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	31	26	48	36	29	25	33	27	23	30	25	22	28	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9939	9939	9939
5°	9962	9848	9909
10°	9886	9757	9757
15°	9768	9559	9482
20°	9619	9283	9171
25°	9443	9012	8813
30°	9223	8694	8416
35°	8999	8367	7972
40°	8790	8025	7535
45°	8535	7644	7059
50°	8280	7229	6563
55°	7983	6831	6033
60°	7687	6350	5465
65°	7335	5790	4814
70°	6936	5093	4147
75°	6381	4292	3451
80°	5620	3373	2894
85°	4735	2757	2586



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	2.8
10°-20°	404.4	7.7
20°-30°	586.4	11.2
30°-40°	668.3	12.7
40°-50°	651.5	12.4
50°-60°	548.4	10.4
60°-70°	384.4	7.3
70°-80°	197.6	3.8
80°-90°	51.0	1.0
90°-100°	19.1	0.4
100°-110°	117.7	2.2
110°-120°	213.4	4.1
120°-130°	273.9	5.2
130°-140°	294.6	5.6
140°-150°	276.5	5.3
150°-160°	223.7	4.3
160°-170°	144.7	2.8
170°-180°	49.9	1.0
0°-30°	1135.5	21.6
0°-40°	1803.9	34.4
0°-60°	3003.7	57.2
0°-90°	3636.7	69.3
90°-120°	350.2	6.7
90°-150°	1195.3	22.8
90°-180°	1614.0	30.7
0°-180°	5250.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1530	1528	146
15°	1461	1453	1430	1428	1418	412
25°	1325	1306	1265	1250	1237	609
35°	1141	1112	1061	1028	1011	714
45°	934	899	837	792	773	721
55°	709	670	607	556	536	634
65°	480	439	379	334	315	475
75°	256	220	172	147	138	271
85°	64	44	37	36	35	72
90°	0	4	6	8	9	4
95°	22	20	6	8	8	28
105°	114	116	116	116	116	121
115°	215	217	217	216	213	213
125°	306	308	308	307	306	273
135°	381	384	383	382	380	294
145°	442	443	443	443	441	276
155°	487	485	485	486	483	224
165°	514	512	512	514	511	145
175°	526	523	524	526	523	50
180°	526	526	526	526	526	



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1541.7	1541.1	1540.5	1539.8	1539.2	1537.9	1535.9	1533.8	1531.7	1529.7	1531.7
5°	1536.6	1535.6	1534.6	1533.5	1532.5	1530.5	1527.7	1524.8	1522.0	1519.1	1521.7
7.5°	1521.5	1520.5	1519.5	1518.5	1517.5	1515.4	1511.9	1508.6	1505.1	1501.8	1503.6
10°	1507.5	1506.8	1506.0	1505.2	1504.4	1502.3	1498.7	1495.0	1491.4	1487.8	1488.6
12.5°	1491.7	1490.7	1489.8	1488.8	1487.8	1484.9	1480.1	1475.2	1470.3	1465.4	1466.0
15°	1461.0	1459.5	1457.9	1456.4	1454.8	1451.4	1446.0	1440.5	1435.1	1429.7	1429.4
17.5°	1426.4	1424.0	1421.7	1419.3	1416.9	1412.3	1405.5	1398.7	1391.8	1385.0	1383.7
20°	1399.5	1396.9	1394.3	1391.7	1389.1	1383.7	1375.4	1367.2	1358.9	1350.7	1349.4
22.5°	1369.7	1367.1	1364.5	1361.9	1359.3	1353.8	1345.1	1336.4	1327.7	1319.0	1316.5
25°	1325.1	1321.2	1317.3	1313.5	1309.6	1302.9	1293.3	1283.8	1274.2	1264.6	1261.3
27.5°	1273.9	1269.2	1264.5	1259.8	1255.1	1247.7	1237.4	1227.2	1216.9	1206.7	1202.0
30°	1236.7	1231.8	1226.9	1222.0	1217.1	1209.2	1198.3	1187.5	1176.6	1165.8	1159.9
32.5°	1200.4	1194.7	1189.0	1183.3	1177.5	1169.2	1158.0	1147.0	1135.9	1124.9	1118.4
35°	1141.4	1135.2	1129.0	1122.8	1116.6	1107.7	1096.1	1084.4	1072.8	1061.2	1053.7
37.5°	1083.5	1076.0	1068.4	1060.9	1053.3	1043.6	1031.6	1019.6	1007.6	995.7	986.6
40°	1042.6	1034.8	1027.1	1019.3	1011.6	1001.5	989.1	976.7	964.3	951.9	942.1
42.5°	999.8	991.9	984.0	975.9	968.0	957.6	944.8	932.0	919.2	906.4	897.0
45°	934.5	927.0	919.5	912.1	904.6	893.7	879.5	865.3	851.1	836.9	826.6
47.5°	866.9	858.9	851.0	843.2	835.3	824.1	809.9	795.5	781.2	766.9	756.2
50°	824.1	815.5	807.0	798.5	790.0	778.3	763.6	748.9	734.2	719.5	708.6
52.5°	777.6	768.9	760.1	751.4	742.7	731.3	717.5	703.5	689.7	675.8	664.1
55°	709.0	700.8	692.5	684.2	676.0	664.6	650.1	635.7	621.2	606.7	595.1
57.5°	639.7	630.9	622.1	613.2	604.4	593.1	579.1	565.2	551.2	537.3	525.9
60°	595.1	586.1	577.0	568.0	559.0	547.4	533.5	519.5	505.6	491.6	480.3
62.5°	547.7	539.1	530.5	521.8	513.2	501.8	487.7	473.5	459.3	445.1	434.6
65°	480.0	471.2	462.4	453.7	444.9	433.7	420.0	406.3	392.6	378.9	368.6
67.5°	412.8	404.1	395.3	386.5	377.7	366.8	353.6	340.5	327.4	314.3	304.9
70°	367.3	358.5	349.7	341.0	332.2	321.3	308.4	295.5	282.6	269.7	261.7
72.5°	322.7	314.1	305.5	297.0	288.3	278.0	266.0	253.8	241.8	229.7	222.3
75°	255.7	248.0	240.2	232.5	224.7	215.4	204.6	193.7	182.9	172.0	166.3
77.5°	189.2	183.0	176.8	170.7	164.5	157.0	148.4	139.7	131.0	122.3	118.3
80°	151.1	144.9	138.7	132.5	126.3	119.6	112.4	105.1	97.9	90.7	88.3
82.5°	113.9	108.3	102.7	97.2	91.6	86.4	81.4	76.4	71.5	66.5	65.4
85°	63.9	59.2	54.6	49.9	45.3	42.4	41.1	39.8	38.5	37.2	36.9
87.5°	21.4	20.1	18.9	17.6	16.3	15.5	15.4	15.3	15.2	15.2	15.2
90°	0.4	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.2	6.6
92.5°	6.0	5.5	5.0	4.6	4.0	4.0	4.6	5.2	5.7	6.2	6.6
95°	22.2	22.0	21.7	21.4	21.2	19.4	16.1	12.8	9.6	6.2	6.6
97.5°	46.3	46.8	47.3	47.8	48.2	45.2	38.7	32.2	25.7	19.2	16.7
100°	65.0	65.3	65.6	65.9	66.1	66.4	66.7	67.1	67.4	67.8	54.8
102.5°	84.0	84.4	84.7	85.1	85.4	85.7	85.8	86.0	86.3	86.4	84.0
105°	114.5	114.9	115.2	115.5	115.9	116.1	116.1	116.1	116.1	116.1	116.1
107.5°	146.1	146.1	146.1	146.1	146.1	146.2	146.4	146.5	146.7	146.9	147.0
110°	166.7	166.7	166.7	166.7	166.7	166.8	166.9	167.1	167.3	167.5	167.2



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	186.2	186.4	186.7	186.8	187.0	187.1	187.3	187.4	187.4	187.1
115°	215.0	215.4	215.9	216.3	216.7	217.0	217.1	217.1	217.2	217.3	217.0
117.5°	245.0	245.0	245.0	245.0	245.0	245.1	245.4	245.7	246.1	246.4	246.0
120°	263.7	263.6	263.6	263.5	263.4	263.5	263.7	264.0	264.2	264.5	264.3
122.5°	280.3	280.5	280.9	281.2	281.5	281.7	281.9	282.0	282.1	282.2	282.1
125°	305.7	306.3	306.9	307.5	308.2	308.5	308.5	308.5	308.5	308.5	308.2
127.5°	330.1	330.6	331.1	331.5	331.9	332.1	332.0	332.0	331.9	331.8	331.7
130°	345.1	345.5	345.9	346.4	346.8	347.1	347.2	347.2	347.3	347.4	347.2
132.5°	360.1	360.6	361.1	361.5	362.1	362.2	362.1	361.9	361.6	361.4	361.4
135°	381.3	381.9	382.4	382.9	383.4	383.6	383.4	383.2	383.1	382.9	382.7
137.5°	400.9	401.3	401.7	402.3	402.7	402.9	402.7	402.5	402.3	402.2	402.3
140°	413.6	413.8	414.0	414.1	414.3	414.4	414.3	414.2	414.1	414.1	414.2
142.5°	425.2	425.3	425.4	425.5	425.6	425.7	425.9	425.9	426.1	426.2	426.2
145°	442.1	442.3	442.5	442.6	442.8	442.9	442.9	442.9	442.9	442.9	443.0
147.5°	456.9	456.8	456.8	456.8	456.8	456.8	456.9	457.0	457.1	457.2	457.3
150°	466.2	466.1	465.9	465.7	465.5	465.5	465.7	465.9	466.1	466.2	466.4
152.5°	475.3	474.9	474.5	474.2	473.7	473.6	473.8	474.0	474.2	474.3	474.5
155°	486.9	486.4	485.9	485.3	484.8	484.7	484.8	485.0	485.2	485.3	485.6
157.5°	495.8	495.5	495.2	494.9	494.6	494.5	494.5	494.5	494.5	494.6	494.8
160°	502.0	501.5	501.0	500.5	500.0	499.8	499.9	500.0	500.1	500.2	500.5
162.5°	507.0	506.5	506.0	505.5	505.0	504.8	504.9	505.0	505.1	505.1	505.6
165°	513.8	513.2	512.7	512.2	511.7	511.4	511.5	511.6	511.7	511.8	512.3
167.5°	518.8	518.2	517.7	517.1	516.6	516.3	516.4	516.5	516.6	516.7	517.4
170°	521.6	521.0	520.3	519.7	519.1	518.8	518.9	519.0	519.1	519.2	519.9
172.5°	523.4	522.8	522.2	521.6	521.0	520.8	520.9	521.1	521.2	521.4	522.0
175°	525.5	525.0	524.4	523.9	523.4	523.1	523.2	523.3	523.4	523.5	524.2
177.5°	526.4	526.0	525.6	525.1	524.7	524.5	524.6	524.7	524.8	524.9	525.3
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1533.8	1535.9	1537.9	1538.8	1538.6	1538.4	1538.2	1538.0
5°	1524.3	1526.9	1529.5	1530.5	1530.0	1529.5	1529.0	1528.4
7.5°	1505.4	1507.2	1509.0	1509.6	1509.0	1508.5	1507.9	1507.3
10°	1489.4	1490.1	1490.9	1490.9	1490.1	1489.4	1488.6	1487.8
12.5°	1466.6	1467.1	1467.7	1467.4	1466.2	1465.1	1463.9	1462.7
15°	1429.2	1428.9	1428.7	1427.4	1425.0	1422.7	1420.4	1418.1
17.5°	1382.4	1381.1	1379.8	1378.3	1376.3	1374.4	1372.5	1370.6
20°	1348.1	1346.8	1345.5	1343.7	1341.4	1339.0	1336.7	1334.4
22.5°	1314.0	1311.4	1308.9	1306.7	1304.8	1302.9	1300.9	1299.0
25°	1257.9	1254.6	1251.2	1248.1	1245.3	1242.4	1239.6	1236.7
27.5°	1197.3	1192.7	1187.9	1184.2	1181.5	1178.7	1176.0	1173.3
30°	1153.9	1148.0	1142.0	1137.9	1135.6	1133.2	1130.9	1128.6
32.5°	1111.8	1105.2	1098.6	1093.9	1091.0	1088.0	1085.0	1082.1
35°	1046.2	1038.7	1031.2	1025.7	1022.1	1018.5	1014.9	1011.2
37.5°	977.7	968.7	959.7	953.5	949.9	946.4	942.9	939.4
40°	932.3	922.5	912.7	906.2	903.1	900.0	896.9	893.8
42.5°	887.6	878.1	868.7	861.8	857.2	852.7	848.2	843.6
45°	816.2	805.9	795.6	788.4	784.5	780.7	776.8	772.9
47.5°	745.6	734.9	724.4	716.9	712.6	708.3	704.0	699.7
50°	697.8	686.9	676.1	668.7	664.9	661.0	657.1	653.2
52.5°	652.5	640.8	629.0	621.3	617.4	613.5	609.7	605.8
55°	583.5	571.9	560.3	552.3	548.2	544.1	539.9	535.8
57.5°	514.5	503.2	491.8	484.2	480.6	476.9	473.2	469.6
60°	468.9	457.5	446.2	438.6	434.7	430.8	427.0	423.1
62.5°	424.1	413.5	403.0	395.8	391.9	388.1	384.2	380.3
65°	358.3	347.9	337.6	330.5	326.6	322.7	318.8	315.0
67.5°	295.4	285.9	276.5	270.2	267.1	264.0	260.9	257.8
70°	253.7	245.6	237.6	232.0	228.9	225.8	222.7	219.6
72.5°	214.9	207.5	200.1	195.4	193.3	191.2	189.2	187.1
75°	160.7	155.0	149.3	145.5	143.7	141.9	140.1	138.3
77.5°	114.3	110.4	106.3	103.7	102.4	101.0	99.7	98.3
80°	86.0	83.7	81.4	79.9	79.4	78.9	78.4	77.8
82.5°	64.3	63.2	62.2	61.5	61.1	60.8	60.5	60.2
85°	36.7	36.4	36.2	35.9	35.6	35.4	35.1	34.9
87.5°	15.3	15.4	15.5	15.5	15.3	15.2	15.1	14.9
90°	7.1	7.5	7.9	8.4	8.6	8.9	9.1	9.4
92.5°	7.1	7.5	7.9	8.3	8.4	8.5	8.6	8.7
95°	7.1	7.5	7.9	8.2	8.2	8.2	8.2	8.2
97.5°	14.3	11.9	9.4	8.2	8.2	8.2	8.2	8.2
100°	42.0	29.1	16.2	9.6	9.2	8.9	8.5	8.2
102.5°	81.6	79.1	76.7	72.6	66.6	60.8	54.8	49.0
105°	116.1	116.1	116.1	116.1	116.0	115.9	115.8	115.7
107.5°	147.0	147.0	147.0	146.9	146.6	146.4	146.1	145.9
110°	166.9	166.7	166.4	166.3	166.4	166.5	166.6	166.7



TEST NUMBER: P333702-935

CATALOG NUMBER: S125RDIW-S1090D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.4	186.1	185.9	185.8	185.6	185.5	185.4
115°	216.6	216.3	215.9	215.5	215.0	214.5	214.0	213.4
117.5°	245.5	245.0	244.6	244.3	244.0	243.8	243.6	243.4
120°	264.2	264.0	263.8	263.5	263.0	262.6	262.2	261.7
122.5°	281.9	281.7	281.5	281.2	280.7	280.2	279.7	279.2
125°	307.8	307.5	307.1	306.8	306.5	306.3	306.0	305.7
127.5°	331.5	331.3	331.1	330.7	330.0	329.4	328.7	328.1
130°	346.9	346.6	346.4	346.0	345.6	345.2	344.7	344.3
132.5°	361.4	361.3	361.3	361.0	360.6	360.2	359.7	359.3
135°	382.5	382.4	382.2	381.9	381.3	380.8	380.3	379.8
137.5°	402.3	402.3	402.3	402.2	401.7	401.2	400.8	400.4
140°	414.4	414.6	414.7	414.6	414.1	413.5	413.0	412.5
142.5°	426.3	426.3	426.4	426.1	425.6	425.1	424.6	424.0
145°	443.1	443.2	443.2	443.0	442.5	442.0	441.4	440.9
147.5°	457.4	457.5	457.6	457.4	456.8	456.2	455.5	454.9
150°	466.6	466.7	466.9	466.7	466.0	465.3	464.6	463.9
152.5°	474.7	474.8	475.0	474.8	474.2	473.6	472.9	472.3
155°	485.9	486.1	486.4	486.1	485.4	484.7	484.1	483.4
157.5°	495.1	495.3	495.6	495.4	494.7	494.0	493.4	492.7
160°	500.8	501.2	501.5	501.4	500.7	500.0	499.3	498.6
162.5°	506.1	506.6	507.0	507.0	506.2	505.4	504.6	503.9
165°	512.9	513.4	513.9	513.8	513.2	512.4	511.7	511.0
167.5°	518.0	518.6	519.2	519.2	518.3	517.5	516.8	516.0
170°	520.6	521.3	522.0	521.9	521.2	520.4	519.6	518.8
172.5°	522.6	523.2	523.9	523.8	523.1	522.3	521.5	520.7
175°	524.9	525.6	526.2	526.2	525.5	524.7	523.9	523.1
177.5°	525.8	526.2	526.8	526.8	526.2	525.6	525.0	524.5
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5

(END OF REPORT)