

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333665-830

Luminaire Tested: **S125RDIW-S610D770U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333665-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4770.6 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47																				
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41																				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35																				
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30																				
4	75	64	57	51	69	59	53	48	50	45	41	42	38	35	34	32	30	26																				
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23																				
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20																				
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18																				
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16																				
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14																				
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5633	5633	5633	5633
5°	6481	5641	4982	5641
10°	7434	5612	4395	5612
15°	8029	5554	3907	5554
20°	8854	5487	3608	5487
25°	10246	5399	3348	5399
30°	11150	5305	3177	5305
35°	9406	5196	3020	5196
40°	6568	5001	2886	5001
45°	4873	4738	2754	4738
50°	3885	4464	2640	4464
55°	3297	4124	2540	4124
60°	2849	3821	2378	3821
65°	2540	3492	2046	3492
70°	2232	3199	1866	3199
75°	1931	2770	1752	2770
80°	1465	2332	1465	2332
85°	1223	1830	1386	1830



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.8
10°-20°	245.1	5.1
20°-30°	388.6	8.1
30°-40°	468.7	9.8
40°-50°	418.5	8.8
50°-60°	321.0	6.7
60°-70°	208.6	4.4
70°-80°	101.4	2.1
80°-90°	26.2	0.5
90°-100°	60.2	1.3
100°-110°	177.8	3.7
110°-120°	301.2	6.3
120°-130°	396.4	8.3
130°-140°	444.2	9.3
140°-150°	435.3	9.1
150°-160°	365.6	7.7
160°-170°	243.1	5.1
170°-180°	85.1	1.8
0°-30°	717.4	15.0
0°-40°	1186.0	24.9
0°-60°	1925.5	40.4
0°-90°	2261.7	47.4
90°-120°	539.3	11.3
90°-150°	1815.1	38.0
90°-180°	2509.0	52.6
0°-180°	4770.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	872	872	872	872	872	
5°	1000	870	768	870	1000	100
15°	1201	831	584	831	1201	344
25°	1438	758	470	758	1438	660
35°	1193	659	383	659	1193	721
45°	534	519	302	519	534	426
55°	293	366	226	366	293	266
65°	166	228	134	228	166	165
75°	77	111	70	111	77	82
85°	16	25	19	25	16	19
90°	17	1	17	1	17	10
95°	60	46	60	46	60	61
105°	174	160	174	160	174	184
115°	304	302	304	302	304	301
125°	443	440	443	440	443	395
135°	574	572	574	572	574	443
145°	696	693	696	693	696	435
155°	793	793	793	793	793	365
165°	861	863	861	863	861	243
175°	894	897	894	897	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	917.5	916.9	918.0	914.8	915.2	910.3	910.3	906.5	901.7	898.0	896.3
5°	999.7	1000.4	998.9	993.5	990.0	984.6	978.5	967.8	958.8	950.3	943.5
7.5°	1084.3	1084.8	1080.1	1078.5	1069.4	1062.8	1049.3	1034.7	1021.7	1005.2	992.7
10°	1133.6	1133.2	1128.2	1124.3	1116.3	1106.4	1093.1	1075.9	1059.8	1041.9	1024.7
12.5°	1162.2	1161.3	1159.7	1154.9	1147.6	1138.7	1127.5	1110.6	1090.7	1071.1	1051.1
15°	1200.9	1198.3	1193.7	1187.6	1177.2	1166.9	1154.3	1139.3	1120.3	1098.2	1079.5
17.5°	1248.7	1248.8	1241.6	1233.2	1219.1	1200.7	1181.4	1157.2	1131.3	1106.9	1087.1
20°	1288.3	1287.1	1280.0	1263.6	1247.5	1224.6	1202.3	1172.6	1141.1	1109.2	1084.5
22.5°	1344.9	1342.2	1334.7	1313.1	1288.1	1258.6	1224.6	1188.4	1150.3	1114.1	1081.7
25°	1437.9	1435.8	1421.1	1396.0	1360.9	1315.4	1271.0	1221.3	1166.5	1118.9	1079.5
27.5°	1501.5	1499.1	1488.3	1467.4	1435.0	1387.2	1327.1	1260.7	1192.2	1126.7	1069.9
30°	1495.2	1500.5	1499.1	1489.5	1465.1	1422.1	1366.7	1291.8	1210.5	1133.6	1065.9
32.5°	1405.2	1410.0	1422.7	1441.6	1443.0	1425.9	1384.4	1315.3	1231.1	1143.6	1062.7
35°	1193.0	1199.5	1223.8	1262.1	1312.2	1354.2	1362.7	1325.5	1249.9	1155.7	1058.0
37.5°	917.2	952.4	972.9	1013.2	1088.9	1166.0	1240.1	1267.4	1235.3	1150.8	1050.4
40°	779.1	787.7	824.3	869.7	933.4	1013.6	1119.3	1195.5	1198.0	1139.3	1038.3
42.5°	666.8	677.7	702.8	739.0	793.6	873.8	982.9	1083.5	1130.1	1107.8	1022.6
45°	533.5	541.7	560.0	587.9	629.8	696.1	789.9	906.3	998.6	1034.7	980.3
47.5°	438.3	442.7	458.5	479.8	510.9	559.1	631.7	732.7	843.6	921.2	913.6
50°	386.7	391.7	403.9	420.0	446.1	486.9	545.0	629.1	743.3	838.2	857.1
52.5°	346.6	350.7	358.4	373.6	395.1	426.5	473.3	549.5	652.2	753.1	797.0
55°	292.8	295.8	301.8	310.4	327.6	350.2	390.6	443.3	526.3	628.0	692.5
57.5°	248.6	250.1	253.9	261.8	273.7	290.2	319.4	364.1	423.7	515.2	586.4
60°	220.6	222.0	227.0	232.3	241.7	256.7	279.7	310.8	368.1	443.7	515.6
62.5°	198.2	199.1	201.2	206.6	214.7	226.4	244.4	269.8	315.4	381.7	449.7
65°	166.2	166.5	167.2	171.5	176.5	185.1	196.9	214.8	249.2	299.4	359.5
67.5°	135.3	135.8	138.4	139.9	145.1	149.6	156.6	170.2	194.4	228.2	274.9
70°	118.2	117.8	120.3	122.1	123.9	129.2	133.9	145.0	160.0	185.9	224.9
72.5°	102.1	101.2	102.3	102.9	105.3	109.0	113.6	120.4	132.0	149.8	179.6
75°	77.4	77.7	77.7	78.4	80.2	81.6	83.0	86.6	93.1	104.9	121.0
77.5°	54.3	53.7	55.2	55.4	56.5	58.1	59.3	60.7	63.3	68.2	76.5
80°	39.4	39.4	39.8	40.8	40.4	41.2	43.0	44.4	47.6	50.5	53.3
82.5°	30.3	30.0	30.3	30.5	30.4	31.1	31.8	32.0	33.3	34.7	36.8
85°	16.5	16.5	16.9	16.9	17.2	17.2	17.5	17.5	17.5	17.9	18.3
87.5°	9.6	9.2	8.9	8.8	9.0	9.4	9.0	8.6	8.4	8.3	8.3
90°	16.8	16.3	15.8	15.4	14.9	14.3	13.6	12.7	12.0	11.2	10.1
92.5°	33.0	32.7	32.3	32.0	31.7	31.0	30.0	28.9	27.9	26.9	25.5
95°	60.1	59.9	59.6	59.3	58.9	58.2	57.1	56.1	55.0	53.9	52.3
97.5°	91.2	91.0	90.9	90.7	90.5	89.9	88.9	87.8	86.8	85.8	83.6
100°	114.7	114.4	114.1	113.9	113.5	112.6	111.2	109.8	108.5	107.1	105.0
102.5°	138.3	137.8	137.4	137.0	136.5	135.5	134.0	132.5	131.0	129.4	128.4
105°	173.5	173.1	172.6	172.1	171.6	171.0	170.0	169.1	168.1	167.2	166.3
107.5°	209.6	209.6	209.7	209.7	209.7	209.5	209.1	208.6	208.1	207.6	207.0
110°	236.5	236.7	236.8	237.0	237.1	237.0	236.5	236.0	235.5	235.1	234.6



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	262.8	263.1	263.3	263.6	263.9	263.9	263.7	263.5	263.3	263.1	262.5
115°	304.3	304.5	304.7	304.8	305.0	305.1	305.3	305.5	305.6	305.8	305.5
117.5°	345.0	345.5	346.2	346.9	347.4	347.7	347.5	347.4	347.3	347.2	346.9
120°	373.0	373.5	374.2	374.8	375.4	375.7	375.7	375.7	375.7	375.7	375.6
122.5°	401.0	401.4	401.9	402.4	402.9	403.2	403.3	403.5	403.6	403.7	403.3
125°	442.9	443.1	443.2	443.4	443.6	443.7	444.0	444.4	444.7	445.0	444.9
127.5°	483.2	483.5	483.8	484.2	484.5	484.7	484.8	485.0	485.1	485.3	485.1
130°	510.1	510.4	510.7	511.0	511.3	511.5	511.7	511.9	512.0	512.2	511.9
132.5°	535.3	535.7	536.1	536.6	537.0	537.3	537.4	537.6	537.8	537.9	538.0
135°	574.5	575.0	575.7	576.3	576.9	577.2	577.2	577.2	577.2	577.2	577.1
137.5°	612.7	613.6	614.3	615.1	615.9	616.2	616.0	615.9	615.7	615.5	615.1
140°	637.4	638.2	638.9	639.8	640.6	640.7	640.5	640.2	639.8	639.5	639.0
142.5°	660.9	661.7	662.5	663.3	664.0	664.3	664.1	663.9	663.7	663.5	663.0
145°	696.2	696.6	697.1	697.6	698.0	698.3	698.3	698.3	698.3	698.3	697.9
147.5°	726.3	727.4	728.4	729.4	730.5	730.8	730.5	730.1	729.7	729.3	729.0
150°	748.7	748.9	749.3	749.6	749.9	750.1	750.1	750.1	750.1	750.1	749.4
152.5°	767.1	767.7	768.3	768.8	769.4	769.5	769.1	768.7	768.4	768.0	767.7
155°	793.4	794.2	795.0	795.8	796.5	796.6	796.0	795.4	794.8	794.2	794.0
157.5°	815.4	816.4	817.5	818.5	819.5	819.7	819.1	818.5	817.8	817.3	817.1
160°	830.6	831.3	832.1	832.8	833.7	833.7	833.1	832.5	831.9	831.2	831.0
162.5°	843.4	844.3	845.2	846.1	847.1	847.1	846.3	845.6	844.9	844.1	844.0
165°	860.6	861.6	862.5	863.5	864.3	864.5	863.9	863.3	862.6	862.0	861.9
167.5°	874.3	875.3	876.3	877.2	878.2	878.2	877.3	876.4	875.4	874.5	874.5
170°	881.7	882.7	883.8	884.9	886.0	886.1	885.1	884.2	883.3	882.3	882.3
172.5°	887.8	888.7	889.7	890.7	891.6	891.6	890.7	889.8	888.8	887.9	887.9
175°	893.5	894.6	895.7	896.7	897.9	898.0	897.0	896.1	895.1	894.2	894.2
177.5°	896.8	897.8	898.6	899.5	900.3	900.4	899.7	898.9	898.1	897.4	897.6
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	896.3	894.3	890.5	887.1	882.8	879.1	876.5	873.4	869.3	864.5	860.4
5°	935.9	928.0	917.7	908.7	897.3	888.3	879.0	870.1	861.1	849.6	839.6
7.5°	979.9	963.7	947.8	927.9	909.8	893.7	878.3	862.6	847.3	831.0	815.3
10°	1006.8	987.1	965.3	940.2	917.3	895.5	875.4	855.7	835.0	816.7	797.0
12.5°	1032.0	1006.6	981.7	950.0	922.5	895.8	870.2	845.7	823.5	799.8	778.6
15°	1054.8	1029.7	1001.8	963.2	924.8	892.6	862.5	830.7	803.1	776.6	753.0
17.5°	1063.6	1037.4	1004.8	967.7	925.9	885.3	846.6	811.6	779.2	748.3	721.7
20°	1060.2	1034.7	1001.5	966.0	921.2	879.0	837.1	798.4	762.2	729.7	701.4
22.5°	1051.9	1025.6	993.4	956.0	913.5	868.6	824.0	782.7	744.8	711.1	680.2
25°	1039.4	1003.6	970.6	934.2	893.7	849.3	803.1	757.6	717.2	682.8	649.1
27.5°	1026.4	981.8	939.9	903.5	860.8	821.2	776.7	730.1	687.5	652.5	618.0
30°	1014.7	964.6	918.4	877.2	836.8	799.2	756.9	711.4	667.8	631.6	596.5
32.5°	1000.1	946.8	896.1	848.6	809.5	772.2	734.0	690.5	648.0	610.7	575.0
35°	981.8	913.7	858.6	808.1	764.8	728.6	694.3	659.1	616.5	577.9	543.2
37.5°	957.7	880.5	816.7	761.7	716.0	679.7	652.6	620.5	581.6	544.6	512.4
40°	943.1	856.5	786.6	732.2	684.2	645.9	620.5	593.2	557.8	523.1	490.9
42.5°	923.6	834.4	756.3	699.6	651.3	614.4	588.7	565.0	535.2	502.5	468.0
45°	885.4	791.6	709.6	648.8	600.1	563.9	539.9	518.8	496.2	466.2	436.1
47.5°	835.8	747.1	661.2	594.7	547.1	513.5	490.2	473.5	457.4	431.9	402.7
50°	796.0	710.4	626.6	562.1	511.3	479.4	457.6	444.3	429.6	406.4	382.0
52.5°	748.9	672.6	590.5	524.6	476.6	446.8	425.7	412.6	400.4	381.4	358.3
55°	675.0	607.9	532.7	473.0	429.0	398.9	378.8	366.3	359.1	343.0	324.7
57.5°	589.5	541.5	475.2	417.5	378.6	348.8	334.2	323.6	315.5	304.1	291.2
60°	529.9	496.2	436.8	382.0	346.2	317.9	304.7	295.8	288.2	278.5	268.5
62.5°	469.5	445.0	393.3	346.2	313.3	289.5	277.2	269.1	260.4	253.9	244.2
65°	388.5	366.6	330.8	294.0	263.5	244.6	235.6	228.5	223.1	215.9	209.1
67.5°	302.2	293.3	268.6	243.2	221.3	204.4	196.7	191.7	185.2	181.0	176.3
70°	249.2	244.9	227.3	210.6	190.1	178.7	171.5	169.4	161.5	157.2	153.9
72.5°	202.3	200.2	190.1	178.4	164.1	154.0	147.4	145.0	140.0	136.6	134.5
75°	138.6	139.3	137.5	130.0	124.6	118.2	112.4	111.0	107.4	104.5	102.7
77.5°	87.7	91.3	91.4	91.0	89.0	85.0	82.7	81.5	78.0	77.0	76.5
80°	60.1	64.1	67.7	67.3	66.6	65.5	63.7	62.7	60.9	59.8	59.1
82.5°	40.1	43.7	46.8	48.7	48.5	47.5	46.3	45.7	45.4	44.6	44.5
85°	18.9	19.7	20.7	23.3	25.1	25.4	25.1	24.7	23.7	24.0	24.3
87.5°	8.4	8.2	8.2	8.0	7.4	8.7	9.2	9.3	9.0	8.7	8.3
90°	9.0	7.9	6.9	5.7	4.4	3.2	2.0	0.7	2.0	3.2	4.4
92.5°	24.2	22.9	21.5	20.5	19.5	18.7	17.8	17.0	17.8	18.7	19.5
95°	50.8	49.2	47.7	46.8	46.4	46.1	45.8	45.5	45.8	46.1	46.4
97.5°	81.5	79.4	77.2	76.1	76.0	75.8	75.7	75.6	75.7	75.8	76.0
100°	103.0	100.9	99.0	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9
102.5°	127.4	126.4	125.4	124.5	123.9	123.3	122.6	122.1	122.6	123.3	123.9
105°	165.3	164.5	163.5	162.7	161.8	161.1	160.3	159.6	160.3	161.1	161.8
107.5°	206.2	205.6	204.8	204.1	203.3	202.6	201.7	201.0	201.7	202.6	203.3
110°	234.1	233.7	233.2	232.6	231.9	231.0	230.3	229.5	230.3	231.0	231.9



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.9	261.3	260.7	260.2	259.9	259.4	259.0	258.6	259.0	259.4	259.9
115°	305.1	304.8	304.5	304.1	303.4	302.8	302.2	301.6	302.2	302.8	303.4
117.5°	346.7	346.4	346.1	345.8	345.5	345.3	345.0	344.7	345.0	345.3	345.5
120°	375.4	375.2	375.1	374.7	373.9	373.1	372.3	371.6	372.3	373.1	373.9
122.5°	402.9	402.5	402.1	401.8	401.5	401.2	401.0	400.7	401.0	401.2	401.5
125°	444.7	444.5	444.4	443.8	442.9	442.0	441.0	440.1	441.0	442.0	442.9
127.5°	484.9	484.7	484.6	484.2	483.7	483.1	482.6	482.1	482.6	483.1	483.7
130°	511.5	511.2	511.0	510.4	509.6	508.9	508.0	507.3	508.0	508.9	509.6
132.5°	538.0	538.1	538.2	537.5	536.3	535.0	533.8	532.4	533.8	535.0	536.3
135°	576.9	576.7	576.6	576.1	575.1	574.2	573.3	572.3	573.3	574.2	575.1
137.5°	614.7	614.4	614.1	613.5	612.6	611.6	610.8	609.8	610.8	611.6	612.6
140°	638.6	638.1	637.6	637.1	636.2	635.5	634.7	634.0	634.7	635.5	636.2
142.5°	662.4	661.9	661.2	660.6	660.0	659.3	658.6	658.0	658.6	659.3	660.0
145°	697.4	696.9	696.4	695.9	695.2	694.7	694.0	693.4	694.0	694.7	695.2
147.5°	728.6	728.2	727.8	727.5	727.2	726.8	726.5	726.1	726.5	726.8	727.2
150°	748.9	748.2	747.6	747.3	747.5	747.6	747.8	748.0	747.8	747.6	747.5
152.5°	767.5	767.2	766.9	766.8	766.6	766.3	766.1	765.9	766.1	766.3	766.6
155°	793.8	793.7	793.5	793.4	793.4	793.4	793.4	793.4	793.4	793.4	793.4
157.5°	816.9	816.8	816.6	816.7	817.1	817.4	817.7	818.1	817.7	817.4	817.1
160°	830.9	830.8	830.6	830.8	831.2	831.7	832.2	832.6	832.2	831.7	831.2
162.5°	844.0	844.0	844.0	844.1	844.5	844.8	845.2	845.6	845.2	844.8	844.5
165°	861.7	861.6	861.4	861.5	861.8	862.1	862.4	862.7	862.4	862.1	861.8
167.5°	874.5	874.5	874.5	874.8	875.4	876.0	876.7	877.3	876.7	876.0	875.4
170°	882.3	882.3	882.3	882.6	883.3	883.8	884.5	885.1	884.5	883.8	883.3
172.5°	887.9	887.9	887.9	888.3	888.8	889.5	890.0	890.7	890.0	889.5	888.8
175°	894.2	894.2	894.2	894.5	895.1	895.8	896.4	897.0	896.4	895.8	895.1
177.5°	897.7	897.8	898.0	898.2	898.7	899.2	899.8	900.2	899.8	899.2	898.7
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	857.6	853.6	850.7	845.0	840.9	839.2	836.1	835.3	838.4	836.1	835.8
5°	832.1	821.7	813.5	805.2	796.3	790.6	781.9	780.5	778.4	775.1	774.5
7.5°	801.5	788.0	777.4	763.7	752.0	742.4	731.7	726.6	723.8	719.6	714.1
10°	780.9	764.8	750.5	736.9	722.2	710.4	699.6	691.4	686.0	681.0	678.8
12.5°	760.5	744.1	725.9	709.4	693.0	679.7	667.8	662.4	656.5	650.6	645.6
15°	729.0	707.1	687.1	668.1	654.1	639.8	628.4	620.5	611.5	609.1	599.4
17.5°	695.5	674.0	650.5	630.6	614.4	598.6	586.1	577.1	570.3	561.1	556.7
20°	674.6	649.1	626.2	607.9	590.0	571.5	558.6	551.0	544.6	537.1	533.5
22.5°	652.2	627.4	603.9	582.5	564.3	545.9	536.8	529.0	521.7	514.7	510.0
25°	619.4	594.4	569.7	547.4	528.5	515.2	504.4	495.5	491.6	484.7	479.8
27.5°	587.0	560.3	534.7	512.6	497.7	484.6	475.8	468.7	461.6	455.6	451.3
30°	566.1	538.9	511.0	493.4	477.6	465.1	455.4	448.7	443.3	437.9	434.7
32.5°	545.2	517.1	492.3	473.3	458.5	447.6	437.7	431.1	425.5	419.5	415.8
35°	511.6	483.0	463.0	444.3	429.6	419.6	412.8	403.5	398.9	394.5	390.6
37.5°	480.5	453.8	432.2	415.8	403.1	393.1	384.4	379.3	373.6	369.8	366.5
40°	457.6	433.2	413.6	396.3	387.0	376.0	367.7	361.3	356.9	351.9	348.4
42.5°	437.0	414.3	395.2	379.8	368.2	358.7	350.8	344.4	338.9	335.4	332.3
45°	407.8	385.2	366.6	352.3	341.6	332.6	324.4	321.1	314.0	309.7	308.3
47.5°	377.7	357.5	339.5	326.3	315.3	306.8	299.1	292.6	288.6	284.4	282.1
50°	357.3	338.0	321.1	308.3	297.6	288.2	281.1	276.7	271.4	267.5	264.6
52.5°	337.0	319.1	302.3	289.9	280.6	271.4	263.3	259.0	253.9	251.4	249.4
55°	307.9	289.0	274.7	262.4	252.8	244.2	236.7	232.3	229.1	226.7	225.9
57.5°	274.9	260.0	246.7	235.6	225.6	217.5	210.9	206.9	204.1	203.7	201.5
60°	253.4	239.9	227.7	215.9	207.3	199.8	194.1	189.5	186.5	186.2	185.5
62.5°	232.1	219.0	207.6	197.3	189.5	182.3	176.9	171.6	169.9	168.1	166.5
65°	200.1	188.3	179.0	170.8	162.6	156.5	151.1	147.9	143.9	141.8	137.9
67.5°	168.8	159.7	150.7	143.8	137.3	131.6	127.1	122.3	119.7	117.9	115.1
70°	148.3	141.1	132.1	124.6	119.6	114.9	111.3	105.9	104.2	102.7	101.3
72.5°	128.8	122.4	114.9	108.9	103.9	99.4	95.3	92.8	91.0	89.5	88.7
75°	101.3	95.2	88.8	84.5	81.0	77.4	75.2	73.4	72.7	72.3	70.9
77.5°	74.4	71.2	66.0	62.6	60.2	58.8	56.8	55.9	55.9	54.3	53.8
80°	56.9	55.1	50.8	49.4	47.6	46.2	45.1	43.4	41.6	40.8	39.8
82.5°	42.3	40.5	38.8	36.5	35.1	34.1	33.1	32.4	32.6	31.7	31.1
85°	22.5	20.7	20.1	19.7	18.9	19.7	19.3	18.9	18.7	18.3	18.7
87.5°	8.3	8.5	8.5	9.2	8.6	9.1	9.2	9.1	9.3	9.4	9.3
90°	5.7	6.9	7.9	9.0	10.1	11.2	12.0	12.7	13.6	14.3	14.9
92.5°	20.5	21.5	22.9	24.2	25.5	26.9	27.9	28.9	30.0	31.0	31.7
95°	46.8	47.7	49.2	50.8	52.3	53.9	55.0	56.1	57.1	58.2	58.9
97.5°	76.1	77.2	79.4	81.5	83.6	85.8	86.8	87.8	88.9	89.9	90.5
100°	97.9	99.0	100.9	103.0	105.0	107.1	108.5	109.8	111.2	112.6	113.5
102.5°	124.5	125.4	126.4	127.4	128.4	129.4	131.0	132.5	134.0	135.5	136.5
105°	162.7	163.5	164.5	165.3	166.3	167.2	168.1	169.1	170.0	171.0	171.6
107.5°	204.1	204.8	205.6	206.2	207.0	207.6	208.1	208.6	209.1	209.5	209.7
110°	232.6	233.2	233.7	234.1	234.6	235.1	235.5	236.0	236.5	237.0	237.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	260.2	260.7	261.3	261.9	262.5	263.1	263.3	263.5	263.7	263.9	263.9
115°	304.1	304.5	304.8	305.1	305.5	305.8	305.6	305.5	305.3	305.1	305.0
117.5°	345.8	346.1	346.4	346.7	346.9	347.2	347.3	347.4	347.5	347.7	347.4
120°	374.7	375.1	375.2	375.4	375.6	375.7	375.7	375.7	375.7	375.7	375.4
122.5°	401.8	402.1	402.5	402.9	403.3	403.7	403.6	403.5	403.3	403.2	402.9
125°	443.8	444.4	444.5	444.7	444.9	445.0	444.7	444.4	444.0	443.7	443.6
127.5°	484.2	484.6	484.7	484.9	485.1	485.3	485.1	485.0	484.8	484.7	484.5
130°	510.4	511.0	511.2	511.5	511.9	512.2	512.0	511.9	511.7	511.5	511.3
132.5°	537.5	538.2	538.1	538.0	538.0	537.9	537.8	537.6	537.4	537.3	537.0
135°	576.1	576.6	576.7	576.9	577.1	577.2	577.2	577.2	577.2	577.2	576.9
137.5°	613.5	614.1	614.4	614.7	615.1	615.5	615.7	615.9	616.0	616.2	615.9
140°	637.1	637.6	638.1	638.6	639.0	639.5	639.8	640.2	640.5	640.7	640.6
142.5°	660.6	661.2	661.9	662.4	663.0	663.5	663.7	663.9	664.1	664.3	664.0
145°	695.9	696.4	696.9	697.4	697.9	698.3	698.3	698.3	698.3	698.3	698.0
147.5°	727.5	727.8	728.2	728.6	729.0	729.3	729.7	730.1	730.5	730.8	730.5
150°	747.3	747.6	748.2	748.9	749.4	750.1	750.1	750.1	750.1	750.1	749.9
152.5°	766.8	766.9	767.2	767.5	767.7	768.0	768.4	768.7	769.1	769.5	769.4
155°	793.4	793.5	793.7	793.8	794.0	794.2	794.8	795.4	796.0	796.6	796.5
157.5°	816.7	816.6	816.8	816.9	817.1	817.3	817.8	818.5	819.1	819.7	819.5
160°	830.8	830.6	830.8	830.9	831.0	831.2	831.9	832.5	833.1	833.7	833.7
162.5°	844.1	844.0	844.0	844.0	844.0	844.1	844.9	845.6	846.3	847.1	847.1
165°	861.5	861.4	861.6	861.7	861.9	862.0	862.6	863.3	863.9	864.5	864.3
167.5°	874.8	874.5	874.5	874.5	874.5	874.5	875.4	876.4	877.3	878.2	878.2
170°	882.6	882.3	882.3	882.3	882.3	882.3	883.3	884.2	885.1	886.1	886.0
172.5°	888.3	887.9	887.9	887.9	887.9	887.9	888.8	889.8	890.7	891.6	891.6
175°	894.5	894.2	894.2	894.2	894.2	894.2	895.1	896.1	897.0	898.0	897.9
177.5°	898.2	898.0	897.8	897.7	897.6	897.4	898.1	898.9	899.7	900.4	900.3
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	835.6	832.4	831.5	832.6	831.5	832.4	835.6	835.8	836.1	838.4	835.3
5°	770.9	767.3	769.1	768.4	769.1	767.3	770.9	774.5	775.1	778.4	780.5
7.5°	714.0	709.5	704.8	706.3	704.8	709.5	714.0	714.1	719.6	723.8	726.6
10°	674.2	670.6	668.5	670.2	668.5	670.6	674.2	678.8	681.0	686.0	691.4
12.5°	640.6	638.6	636.7	635.9	636.7	638.6	640.6	645.6	650.6	656.5	662.4
15°	595.0	590.8	589.0	584.4	589.0	590.8	595.0	599.4	609.1	611.5	620.5
17.5°	553.0	551.6	547.0	545.0	547.0	551.6	553.0	556.7	561.1	570.3	577.1
20°	528.1	526.7	522.1	524.9	522.1	526.7	528.1	533.5	537.1	544.6	551.0
22.5°	507.5	504.4	502.8	502.0	502.8	504.4	507.5	510.0	514.7	521.7	529.0
25°	478.3	473.7	471.9	469.8	471.9	473.7	478.3	479.8	484.7	491.6	495.5
27.5°	449.3	446.8	444.4	443.8	444.4	446.8	449.3	451.3	455.6	461.6	468.7
30°	430.4	427.8	426.0	426.0	426.0	427.8	430.4	434.7	437.9	443.3	448.7
32.5°	413.5	411.5	409.7	409.4	409.7	411.5	413.5	415.8	419.5	425.5	431.1
35°	388.8	386.0	385.2	383.1	385.2	386.0	388.8	390.6	394.5	398.9	403.5
37.5°	363.3	360.9	360.8	360.6	360.8	360.9	363.3	366.5	369.8	373.6	379.3
40°	346.9	345.2	344.8	342.3	344.8	345.2	346.9	348.4	351.9	356.9	361.3
42.5°	329.5	328.6	327.3	326.2	327.3	328.6	329.5	332.3	335.4	338.9	344.4
45°	305.8	303.3	303.3	301.5	303.3	303.3	305.8	308.3	309.7	314.0	321.1
47.5°	281.3	279.4	279.6	277.7	279.6	279.4	281.3	282.1	284.4	288.6	292.6
50°	264.9	263.9	263.5	262.8	263.5	263.9	264.9	264.6	267.5	271.4	276.7
52.5°	248.6	248.2	249.5	247.9	249.5	248.2	248.6	249.4	251.4	253.9	259.0
55°	226.7	225.6	227.7	225.6	227.7	225.6	226.7	225.9	226.7	229.1	232.3
57.5°	201.3	200.4	202.3	201.2	202.3	200.4	201.3	201.5	203.7	204.1	206.9
60°	184.7	182.6	183.7	184.1	183.7	182.6	184.7	185.5	186.2	186.5	189.5
62.5°	164.9	163.7	164.5	162.9	164.5	163.7	164.9	166.5	168.1	169.9	171.6
65°	137.1	136.1	134.6	133.9	134.6	136.1	137.1	137.9	141.8	143.9	147.9
67.5°	115.2	112.6	112.5	113.1	112.5	112.6	115.2	115.1	117.9	119.7	122.3
70°	99.2	99.2	98.8	98.8	98.8	99.2	99.2	101.3	102.7	104.2	105.9
72.5°	88.0	87.8	87.1	86.8	87.1	87.8	88.0	88.7	89.5	91.0	92.8
75°	70.9	71.3	70.5	70.2	70.5	71.3	70.9	70.9	72.3	72.7	73.4
77.5°	52.3	50.8	51.7	50.8	51.7	50.8	52.3	53.8	54.3	55.9	55.9
80°	39.8	39.4	40.4	39.4	40.4	39.4	39.8	39.8	40.8	41.6	43.4
82.5°	31.5	31.1	31.6	30.8	31.6	31.1	31.5	31.1	31.7	32.6	32.4
85°	18.9	18.7	18.3	18.7	18.3	18.7	18.9	18.7	18.3	18.7	18.9
87.5°	9.7	9.5	9.6	9.6	9.6	9.5	9.7	9.3	9.4	9.3	9.1
90°	15.4	15.8	16.3	16.8	16.3	15.8	15.4	14.9	14.3	13.6	12.7
92.5°	32.0	32.3	32.7	33.0	32.7	32.3	32.0	31.7	31.0	30.0	28.9
95°	59.3	59.6	59.9	60.1	59.9	59.6	59.3	58.9	58.2	57.1	56.1
97.5°	90.7	90.9	91.0	91.2	91.0	90.9	90.7	90.5	89.9	88.9	87.8
100°	113.9	114.1	114.4	114.7	114.4	114.1	113.9	113.5	112.6	111.2	109.8
102.5°	137.0	137.4	137.8	138.3	137.8	137.4	137.0	136.5	135.5	134.0	132.5
105°	172.1	172.6	173.1	173.5	173.1	172.6	172.1	171.6	171.0	170.0	169.1
107.5°	209.7	209.7	209.6	209.6	209.6	209.7	209.7	209.7	209.5	209.1	208.6
110°	237.0	236.8	236.7	236.5	236.7	236.8	237.0	237.1	237.0	236.5	236.0



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	263.6	263.3	263.1	262.8	263.1	263.3	263.6	263.9	263.9	263.7	263.5
115°	304.8	304.7	304.5	304.3	304.5	304.7	304.8	305.0	305.1	305.3	305.5
117.5°	346.9	346.2	345.5	345.0	345.5	346.2	346.9	347.4	347.7	347.5	347.4
120°	374.8	374.2	373.5	373.0	373.5	374.2	374.8	375.4	375.7	375.7	375.7
122.5°	402.4	401.9	401.4	401.0	401.4	401.9	402.4	402.9	403.2	403.3	403.5
125°	443.4	443.2	443.1	442.9	443.1	443.2	443.4	443.6	443.7	444.0	444.4
127.5°	484.2	483.8	483.5	483.2	483.5	483.8	484.2	484.5	484.7	484.8	485.0
130°	511.0	510.7	510.4	510.1	510.4	510.7	511.0	511.3	511.5	511.7	511.9
132.5°	536.6	536.1	535.7	535.3	535.7	536.1	536.6	537.0	537.3	537.4	537.6
135°	576.3	575.7	575.0	574.5	575.0	575.7	576.3	576.9	577.2	577.2	577.2
137.5°	615.1	614.3	613.6	612.7	613.6	614.3	615.1	615.9	616.2	616.0	615.9
140°	639.8	638.9	638.2	637.4	638.2	638.9	639.8	640.6	640.7	640.5	640.2
142.5°	663.3	662.5	661.7	660.9	661.7	662.5	663.3	664.0	664.3	664.1	663.9
145°	697.6	697.1	696.6	696.2	696.6	697.1	697.6	698.0	698.3	698.3	698.3
147.5°	729.4	728.4	727.4	726.3	727.4	728.4	729.4	730.5	730.8	730.5	730.1
150°	749.6	749.3	748.9	748.7	748.9	749.3	749.6	749.9	750.1	750.1	750.1
152.5°	768.8	768.3	767.7	767.1	767.7	768.3	768.8	769.4	769.5	769.1	768.7
155°	795.8	795.0	794.2	793.4	794.2	795.0	795.8	796.5	796.6	796.0	795.4
157.5°	818.5	817.5	816.4	815.4	816.4	817.5	818.5	819.5	819.7	819.1	818.5
160°	832.8	832.1	831.3	830.6	831.3	832.1	832.8	833.7	833.7	833.1	832.5
162.5°	846.1	845.2	844.3	843.4	844.3	845.2	846.1	847.1	847.1	846.3	845.6
165°	863.5	862.5	861.6	860.6	861.6	862.5	863.5	864.3	864.5	863.9	863.3
167.5°	877.2	876.3	875.3	874.3	875.3	876.3	877.2	878.2	878.2	877.3	876.4
170°	884.9	883.8	882.7	881.7	882.7	883.8	884.9	886.0	886.1	885.1	884.2
172.5°	890.7	889.7	888.7	887.8	888.7	889.7	890.7	891.6	891.6	890.7	889.8
175°	896.7	895.7	894.6	893.5	894.6	895.7	896.7	897.9	898.0	897.0	896.1
177.5°	899.5	898.6	897.8	896.8	897.8	898.6	899.5	900.3	900.4	899.7	898.9
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	836.1	839.2	840.9	845.0	850.7	853.6	857.6	860.4	864.5	869.3	873.4
5°	781.9	790.6	796.3	805.2	813.5	821.7	832.1	839.6	849.6	861.1	870.1
7.5°	731.7	742.4	752.0	763.7	777.4	788.0	801.5	815.3	831.0	847.3	862.6
10°	699.6	710.4	722.2	736.9	750.5	764.8	780.9	797.0	816.7	835.0	855.7
12.5°	667.8	679.7	693.0	709.4	725.9	744.1	760.5	778.6	799.8	823.5	845.7
15°	628.4	639.8	654.1	668.1	687.1	707.1	729.0	753.0	776.6	803.1	830.7
17.5°	586.1	598.6	614.4	630.6	650.5	674.0	695.5	721.7	748.3	779.2	811.6
20°	558.6	571.5	590.0	607.9	626.2	649.1	674.6	701.4	729.7	762.2	798.4
22.5°	536.8	545.9	564.3	582.5	603.9	627.4	652.2	680.2	711.1	744.8	782.7
25°	504.4	515.2	528.5	547.4	569.7	594.4	619.4	649.1	682.8	717.2	757.6
27.5°	475.8	484.6	497.7	512.6	534.7	560.3	587.0	618.0	652.5	687.5	730.1
30°	455.4	465.1	477.6	493.4	511.0	538.9	566.1	596.5	631.6	667.8	711.4
32.5°	437.7	447.6	458.5	473.3	492.3	517.1	545.2	575.0	610.7	648.0	690.5
35°	412.8	419.6	429.6	444.3	463.0	483.0	511.6	543.2	577.9	616.5	659.1
37.5°	384.4	393.1	403.1	415.8	432.2	453.8	480.5	512.4	544.6	581.6	620.5
40°	367.7	376.0	387.0	396.3	413.6	433.2	457.6	490.9	523.1	557.8	593.2
42.5°	350.8	358.7	368.2	379.8	395.2	414.3	437.0	468.0	502.5	535.2	565.0
45°	324.4	332.6	341.6	352.3	366.6	385.2	407.8	436.1	466.2	496.2	518.8
47.5°	299.1	306.8	315.3	326.3	339.5	357.5	377.7	402.7	431.9	457.4	473.5
50°	281.1	288.2	297.6	308.3	321.1	338.0	357.3	382.0	406.4	429.6	444.3
52.5°	263.3	271.4	280.6	289.9	302.3	319.1	337.0	358.3	381.4	400.4	412.6
55°	236.7	244.2	252.8	262.4	274.7	289.0	307.9	324.7	343.0	359.1	366.3
57.5°	210.9	217.5	225.6	235.6	246.7	260.0	274.9	291.2	304.1	315.5	323.6
60°	194.1	199.8	207.3	215.9	227.7	239.9	253.4	268.5	278.5	288.2	295.8
62.5°	176.9	182.3	189.5	197.3	207.6	219.0	232.1	244.2	253.9	260.4	269.1
65°	151.1	156.5	162.6	170.8	179.0	188.3	200.1	209.1	215.9	223.1	228.5
67.5°	127.1	131.6	137.3	143.8	150.7	159.7	168.8	176.3	181.0	185.2	191.7
70°	111.3	114.9	119.6	124.6	132.1	141.1	148.3	153.9	157.2	161.5	169.4
72.5°	95.3	99.4	103.9	108.9	114.9	122.4	128.8	134.5	136.6	140.0	145.0
75°	75.2	77.4	81.0	84.5	88.8	95.2	101.3	102.7	104.5	107.4	111.0
77.5°	56.8	58.8	60.2	62.6	66.0	71.2	74.4	76.5	77.0	78.0	81.5
80°	45.1	46.2	47.6	49.4	50.8	55.1	56.9	59.1	59.8	60.9	62.7
82.5°	33.1	34.1	35.1	36.5	38.8	40.5	42.3	44.5	44.6	45.4	45.7
85°	19.3	19.7	18.9	19.7	20.1	20.7	22.5	24.3	24.0	23.7	24.7
87.5°	9.2	9.1	8.6	9.2	8.5	8.5	8.3	8.3	8.7	9.0	9.3
90°	12.0	11.2	10.1	9.0	7.9	6.9	5.7	4.4	3.2	2.0	0.7
92.5°	27.9	26.9	25.5	24.2	22.9	21.5	20.5	19.5	18.7	17.8	17.0
95°	55.0	53.9	52.3	50.8	49.2	47.7	46.8	46.4	46.1	45.8	45.5
97.5°	86.8	85.8	83.6	81.5	79.4	77.2	76.1	76.0	75.8	75.7	75.6
100°	108.5	107.1	105.0	103.0	100.9	99.0	97.9	97.9	97.9	97.9	97.9
102.5°	131.0	129.4	128.4	127.4	126.4	125.4	124.5	123.9	123.3	122.6	122.1
105°	168.1	167.2	166.3	165.3	164.5	163.5	162.7	161.8	161.1	160.3	159.6
107.5°	208.1	207.6	207.0	206.2	205.6	204.8	204.1	203.3	202.6	201.7	201.0
110°	235.5	235.1	234.6	234.1	233.7	233.2	232.6	231.9	231.0	230.3	229.5



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	263.3	263.1	262.5	261.9	261.3	260.7	260.2	259.9	259.4	259.0	258.6
115°	305.6	305.8	305.5	305.1	304.8	304.5	304.1	303.4	302.8	302.2	301.6
117.5°	347.3	347.2	346.9	346.7	346.4	346.1	345.8	345.5	345.3	345.0	344.7
120°	375.7	375.7	375.6	375.4	375.2	375.1	374.7	373.9	373.1	372.3	371.6
122.5°	403.6	403.7	403.3	402.9	402.5	402.1	401.8	401.5	401.2	401.0	400.7
125°	444.7	445.0	444.9	444.7	444.5	444.4	443.8	442.9	442.0	441.0	440.1
127.5°	485.1	485.3	485.1	484.9	484.7	484.6	484.2	483.7	483.1	482.6	482.1
130°	512.0	512.2	511.9	511.5	511.2	511.0	510.4	509.6	508.9	508.0	507.3
132.5°	537.8	537.9	538.0	538.0	538.1	538.2	537.5	536.3	535.0	533.8	532.4
135°	577.2	577.2	577.1	576.9	576.7	576.6	576.1	575.1	574.2	573.3	572.3
137.5°	615.7	615.5	615.1	614.7	614.4	614.1	613.5	612.6	611.6	610.8	609.8
140°	639.8	639.5	639.0	638.6	638.1	637.6	637.1	636.2	635.5	634.7	634.0
142.5°	663.7	663.5	663.0	662.4	661.9	661.2	660.6	660.0	659.3	658.6	658.0
145°	698.3	698.3	697.9	697.4	696.9	696.4	695.9	695.2	694.7	694.0	693.4
147.5°	729.7	729.3	729.0	728.6	728.2	727.8	727.5	727.2	726.8	726.5	726.1
150°	750.1	750.1	749.4	748.9	748.2	747.6	747.3	747.5	747.6	747.8	748.0
152.5°	768.4	768.0	767.7	767.5	767.2	766.9	766.8	766.6	766.3	766.1	765.9
155°	794.8	794.2	794.0	793.8	793.7	793.5	793.4	793.4	793.4	793.4	793.4
157.5°	817.8	817.3	817.1	816.9	816.8	816.6	816.7	817.1	817.4	817.7	818.1
160°	831.9	831.2	831.0	830.9	830.8	830.6	830.8	831.2	831.7	832.2	832.6
162.5°	844.9	844.1	844.0	844.0	844.0	844.0	844.1	844.5	844.8	845.2	845.6
165°	862.6	862.0	861.9	861.7	861.6	861.4	861.5	861.8	862.1	862.4	862.7
167.5°	875.4	874.5	874.5	874.5	874.5	874.5	874.8	875.4	876.0	876.7	877.3
170°	883.3	882.3	882.3	882.3	882.3	882.3	882.6	883.3	883.8	884.5	885.1
172.5°	888.8	887.9	887.9	887.9	887.9	887.9	888.3	888.8	889.5	890.0	890.7
175°	895.1	894.2	894.2	894.2	894.2	894.2	894.5	895.1	895.8	896.4	897.0
177.5°	898.1	897.4	897.6	897.7	897.8	898.0	898.2	898.7	899.2	899.8	900.2
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	876.5	879.1	882.8	887.1	890.5	894.3	896.3	896.3	898.0	901.7	906.5
5°	879.0	888.3	897.3	908.7	917.7	928.0	935.9	943.5	950.3	958.8	967.8
7.5°	878.3	893.7	909.8	927.9	947.8	963.7	979.9	992.7	1005.2	1021.7	1034.7
10°	875.4	895.5	917.3	940.2	965.3	987.1	1006.8	1024.7	1041.9	1059.8	1075.9
12.5°	870.2	895.8	922.5	950.0	981.7	1006.6	1032.0	1051.1	1071.1	1090.7	1110.6
15°	862.5	892.6	924.8	963.2	1001.8	1029.7	1054.8	1079.5	1098.2	1120.3	1139.3
17.5°	846.6	885.3	925.9	967.7	1004.8	1037.4	1063.6	1087.1	1106.9	1131.3	1157.2
20°	837.1	879.0	921.2	966.0	1001.5	1034.7	1060.2	1084.5	1109.2	1141.1	1172.6
22.5°	824.0	868.6	913.5	956.0	993.4	1025.6	1051.9	1081.7	1114.1	1150.3	1188.4
25°	803.1	849.3	893.7	934.2	970.6	1003.6	1039.4	1079.5	1118.9	1166.5	1221.3
27.5°	776.7	821.2	860.8	903.5	939.9	981.8	1026.4	1069.9	1126.7	1192.2	1260.7
30°	756.9	799.2	836.8	877.2	918.4	964.6	1014.7	1065.9	1133.6	1210.5	1291.8
32.5°	734.0	772.2	809.5	848.6	896.1	946.8	1000.1	1062.7	1143.6	1231.1	1315.3
35°	694.3	728.6	764.8	808.1	858.6	913.7	981.8	1058.0	1155.7	1249.9	1325.5
37.5°	652.6	679.7	716.0	761.7	816.7	880.5	957.7	1050.4	1150.8	1235.3	1267.4
40°	620.5	645.9	684.2	732.2	786.6	856.5	943.1	1038.3	1139.3	1198.0	1195.5
42.5°	588.7	614.4	651.3	699.6	756.3	834.4	923.6	1022.6	1107.8	1130.1	1083.5
45°	539.9	563.9	600.1	648.8	709.6	791.6	885.4	980.3	1034.7	998.6	906.3
47.5°	490.2	513.5	547.1	594.7	661.2	747.1	835.8	913.6	921.2	843.6	732.7
50°	457.6	479.4	511.3	562.1	626.6	710.4	796.0	857.1	838.2	743.3	629.1
52.5°	425.7	446.8	476.6	524.6	590.5	672.6	748.9	797.0	753.1	652.2	549.5
55°	378.8	398.9	429.0	473.0	532.7	607.9	675.0	692.5	628.0	526.3	443.3
57.5°	334.2	348.8	378.6	417.5	475.2	541.5	589.5	586.4	515.2	423.7	364.1
60°	304.7	317.9	346.2	382.0	436.8	496.2	529.9	515.6	443.7	368.1	310.8
62.5°	277.2	289.5	313.3	346.2	393.3	445.0	469.5	449.7	381.7	315.4	269.8
65°	235.6	244.6	263.5	294.0	330.8	366.6	388.5	359.5	299.4	249.2	214.8
67.5°	196.7	204.4	221.3	243.2	268.6	293.3	302.2	274.9	228.2	194.4	170.2
70°	171.5	178.7	190.1	210.6	227.3	244.9	249.2	224.9	185.9	160.0	145.0
72.5°	147.4	154.0	164.1	178.4	190.1	200.2	202.3	179.6	149.8	132.0	120.4
75°	112.4	118.2	124.6	130.0	137.5	139.3	138.6	121.0	104.9	93.1	86.6
77.5°	82.7	85.0	89.0	91.0	91.4	91.3	87.7	76.5	68.2	63.3	60.7
80°	63.7	65.5	66.6	67.3	67.7	64.1	60.1	53.3	50.5	47.6	44.4
82.5°	46.3	47.5	48.5	48.7	46.8	43.7	40.1	36.8	34.7	33.3	32.0
85°	25.1	25.4	25.1	23.3	20.7	19.7	18.9	18.3	17.9	17.5	17.5
87.5°	9.2	8.7	7.4	8.0	8.2	8.2	8.4	8.3	8.3	8.4	8.6
90°	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0	12.7
92.5°	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9	28.9
95°	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0	56.1
97.5°	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8	87.8
100°	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5	109.8
102.5°	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0	132.5
105°	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1	169.1
107.5°	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1	208.6
110°	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5	236.0



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3	263.5
115°	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6	305.5
117.5°	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3	347.4
120°	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7	375.7
122.5°	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6	403.5
125°	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7	444.4
127.5°	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1	485.0
130°	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0	511.9
132.5°	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8	537.6
135°	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2	577.2
137.5°	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7	615.9
140°	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8	640.2
142.5°	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7	663.9
145°	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3	698.3
147.5°	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7	730.1
150°	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1	750.1
152.5°	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4	768.7
155°	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8	795.4
157.5°	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8	818.5
160°	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9	832.5
162.5°	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9	845.6
165°	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6	863.3
167.5°	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4	876.4
170°	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3	884.2
172.5°	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8	889.8
175°	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1	896.1
177.5°	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1	898.9
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	910.3	910.3	915.2	914.8	918.0	916.9	917.5
5°	978.5	984.6	990.0	993.5	998.9	1000.4	999.7
7.5°	1049.3	1062.8	1069.4	1078.5	1080.1	1084.8	1084.3
10°	1093.1	1106.4	1116.3	1124.3	1128.2	1133.2	1133.6
12.5°	1127.5	1138.7	1147.6	1154.9	1159.7	1161.3	1162.2
15°	1154.3	1166.9	1177.2	1187.6	1193.7	1198.3	1200.9
17.5°	1181.4	1200.7	1219.1	1233.2	1241.6	1248.8	1248.7
20°	1202.3	1224.6	1247.5	1263.6	1280.0	1287.1	1288.3
22.5°	1224.6	1258.6	1288.1	1313.1	1334.7	1342.2	1344.9
25°	1271.0	1315.4	1360.9	1396.0	1421.1	1435.8	1437.9
27.5°	1327.1	1387.2	1435.0	1467.4	1488.3	1499.1	1501.5
30°	1366.7	1422.1	1465.1	1489.5	1499.1	1500.5	1495.2
32.5°	1384.4	1425.9	1443.0	1441.6	1422.7	1410.0	1405.2
35°	1362.7	1354.2	1312.2	1262.1	1223.8	1199.5	1193.0
37.5°	1240.1	1166.0	1088.9	1013.2	972.9	952.4	917.2
40°	1119.3	1013.6	933.4	869.7	824.3	787.7	779.1
42.5°	982.9	873.8	793.6	739.0	702.8	677.7	666.8
45°	789.9	696.1	629.8	587.9	560.0	541.7	533.5
47.5°	631.7	559.1	510.9	479.8	458.5	442.7	438.3
50°	545.0	486.9	446.1	420.0	403.9	391.7	386.7
52.5°	473.3	426.5	395.1	373.6	358.4	350.7	346.6
55°	390.6	350.2	327.6	310.4	301.8	295.8	292.8
57.5°	319.4	290.2	273.7	261.8	253.9	250.1	248.6
60°	279.7	256.7	241.7	232.3	227.0	222.0	220.6
62.5°	244.4	226.4	214.7	206.6	201.2	199.1	198.2
65°	196.9	185.1	176.5	171.5	167.2	166.5	166.2
67.5°	156.6	149.6	145.1	139.9	138.4	135.8	135.3
70°	133.9	129.2	123.9	122.1	120.3	117.8	118.2
72.5°	113.6	109.0	105.3	102.9	102.3	101.2	102.1
75°	83.0	81.6	80.2	78.4	77.7	77.7	77.4
77.5°	59.3	58.1	56.5	55.4	55.2	53.7	54.3
80°	43.0	41.2	40.4	40.8	39.8	39.4	39.4
82.5°	31.8	31.1	30.4	30.5	30.3	30.0	30.3
85°	17.5	17.2	17.2	16.9	16.9	16.5	16.5
87.5°	9.0	9.4	9.0	8.8	8.9	9.2	9.6
90°	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.5	237.0	237.1	237.0	236.8	236.7	236.5



TEST NUMBER: P333665-830

CATALOG NUMBER: S125RDIW-S610D770U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)