

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333695-830

Luminaire Tested: **S125RDIW-S850D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333695-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1340U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7449.3 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	31	30	25
4	73	63	55	49	66	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.9	1.6
10°-20°	340.6	4.6
20°-30°	493.9	6.6
30°-40°	562.9	7.6
40°-50°	548.6	7.4
50°-60°	461.8	6.2
60°-70°	323.7	4.3
70°-80°	166.4	2.2
80°-90°	45.5	0.6
90°-100°	105.2	1.4
100°-110°	310.7	4.2
110°-120°	526.3	7.1
120°-130°	692.7	9.3
130°-140°	776.1	10.4
140°-150°	760.7	10.2
150°-160°	638.9	8.6
160°-170°	424.7	5.7
170°-180°	148.6	2.0
0°-30°	956.3	12.8
0°-40°	1519.2	20.4
0°-60°	2529.7	34.0
0°-90°	3065.3	41.1
90°-120°	942.3	12.6
90°-150°	3171.8	42.6
90°-180°	4384.0	58.9
0°-180°	7449.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	61
90°	1	11	20	26	29	7
95°	80	82	94	102	105	85
105°	279	285	292	299	303	298
115°	527	532	534	533	532	521
125°	769	776	778	775	774	688
135°	1000	1007	1009	1008	1004	771
145°	1212	1216	1220	1220	1216	757
155°	1386	1387	1388	1392	1386	638
165°	1508	1505	1506	1510	1504	425
175°	1567	1563	1562	1569	1561	149
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.3	17.4	16.7	15.9	15.1	14.8	15.1	15.3	15.5	15.6	15.9
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9
92.5°	29.6	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7
95°	79.5	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0
97.5°	132.1	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7
100°	171.2	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5
102.5°	213.2	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8
105°	278.8	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9
107.5°	351.1	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7
110°	401.1	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.9	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1
115°	527.0	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0
117.5°	602.3	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9
120°	649.2	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6
122.5°	700.1	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2
125°	769.0	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0
127.5°	842.4	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7
130°	886.4	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7
132.5°	930.4	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7
135°	1000.1	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7
137.5°	1065.6	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7
140°	1107.7	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0
142.5°	1149.8	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9
145°	1211.6	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2
147.5°	1268.9	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2
150°	1307.0	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7
152.5°	1338.3	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7
155°	1386.5	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7
157.5°	1429.5	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1
160°	1454.9	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6
162.5°	1477.4	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3
165°	1507.5	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4
167.5°	1533.0	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7
170°	1546.6	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4
172.5°	1556.4	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1
175°	1567.4	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1
177.5°	1573.0	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	16.2	16.5	16.8	16.9	16.9	16.9	16.9	16.9
90°	22.2	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	50.5	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	97.9	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	153.4	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	192.0	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	231.5	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	295.5	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	364.5	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	412.5	413.2	414.1	414.3	414.1	413.8	413.5	413.2



TEST NUMBER: P333695-830

CATALOG NUMBER: S125RDIW-S850D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.4	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.8	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.1	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	705.0	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.5	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.4	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.4	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.4	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.1	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1118.6	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.2	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1275.7	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.2	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1389.9	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1430.2	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1454.6	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1477.6	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1508.4	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1531.3	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1545.0	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1554.8	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1565.8	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1570.7	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)