

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333686-830

Luminaire Tested: **S125RDIW-S850D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333686-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D770U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5956.9 lumens  
Efficiency: N/A  
Efficacy: 132.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49				44	
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42				37	
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36				32	
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31				27	
5	69	57	49	43	64	54	46	41	46	40	36	39	35	32	33	29	27				24	
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24				21	
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21				19	
8	55	42	35	29	50	40	33	28	34	29	25	30	25	22	25	22	19				17	
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17				15	
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16				14	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	2.0
10°-20°	340.6	5.7
20°-30°	493.9	8.3
30°-40°	562.9	9.4
40°-50°	548.6	9.2
50°-60°	461.8	7.8
60°-70°	323.7	5.4
70°-80°	166.4	2.8
80°-90°	44.0	0.7
90°-100°	34.2	0.6
100°-110°	211.0	3.5
110°-120°	382.7	6.4
120°-130°	491.1	8.2
130°-140°	528.2	8.9
140°-150°	495.8	8.3
150°-160°	401.1	6.7
160°-170°	259.4	4.4
170°-180°	89.5	1.5
0°-30°	956.3	16.1
0°-40°	1519.2	25.5
0°-60°	2529.7	42.5
0°-90°	3063.8	51.4
90°-120°	627.9	10.5
90°-150°	2143.1	36.0
90°-180°	2893.0	48.6
0°-180°	5956.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	1	6	11	15	17	4
95°	40	36	11	14	15	51
105°	205	208	208	208	208	218
115°	386	389	390	387	383	382
125°	548	553	553	550	548	489
135°	684	688	686	685	681	527
145°	793	794	794	794	791	496
155°	873	869	870	872	867	402
165°	921	917	918	921	916	260
175°	942	938	939	944	938	90
180°	942	942	942	942	942	



TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.2	17.2	16.2	15.3	14.2	13.9	13.9	13.9	13.9	13.9	14.1
90°	0.7	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0
92.5°	10.7	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0
95°	39.8	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0
97.5°	83.1	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0
100°	116.6	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4
102.5°	150.7	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7
105°	205.3	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4
110°	298.9	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8



TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.6	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5
115°	385.5	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1
117.5°	439.3	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0
120°	472.8	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9
122.5°	502.4	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8
125°	548.3	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5
127.5°	591.9	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7
130°	618.8	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5
132.5°	645.5	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0
135°	683.7	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2
137.5°	718.8	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2
140°	741.7	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7
142.5°	762.3	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2
145°	792.7	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2
147.5°	819.3	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9
150°	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3
152.5°	852.2	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8
155°	873.0	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6
157.5°	889.0	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2
160°	900.2	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4
162.5°	909.2	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5
165°	921.1	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6
167.5°	930.1	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6
170°	935.2	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2
172.5°	938.5	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9
175°	942.2	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9
177.5°	943.8	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	14.3	14.4	14.6	14.6	14.5	14.5	14.4	14.3
90°	12.7	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	12.7	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	12.7	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	25.6	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	75.3	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	146.3	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	299.4	298.9	298.4	298.3	298.4	298.6	298.8	298.9





TEST NUMBER: P333686-830

CATALOG NUMBER: S125RDIW-S850D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.9	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	388.4	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	440.2	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.6	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.4	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.9	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.4	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	622.1	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.9	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.9	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.0	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.3	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.4	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.1	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.6	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.1	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.1	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	887.7	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.0	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	907.4	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	919.5	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	928.7	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	933.4	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	937.1	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	941.1	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	942.7	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)