

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333734-935

Luminaire Tested: **S125RDIW-S1270D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333734-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1340U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8820.0 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	42	41	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11479	11479	11479
5°	11505	11374	11444
10°	11418	11269	11269
15°	11282	11040	10950
20°	11109	10721	10592
25°	10905	10408	10178
30°	10651	10041	9721
35°	10394	9663	9208
40°	10151	9269	8703
45°	9858	8828	8153
50°	9562	8349	7580
55°	9221	7891	6969
60°	8878	7334	6311
65°	8472	6687	5559
70°	8010	5880	4791
75°	7369	4956	3985
80°	6490	3894	3347
85°	5476	3186	2986



TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.1	1.9
10°-20°	467.1	5.3
20°-30°	677.3	7.7
30°-40°	771.9	8.8
40°-50°	752.4	8.5
50°-60°	633.3	7.2
60°-70°	444.0	5.0
70°-80°	228.2	2.6
80°-90°	60.8	0.7
90°-100°	54.6	0.6
100°-110°	336.8	3.8
110°-120°	610.9	6.9
120°-130°	783.9	8.9
130°-140°	843.2	9.6
140°-150°	791.5	9.0
150°-160°	640.2	7.3
160°-170°	414.1	4.7
170°-180°	142.8	1.6
0°-30°	1311.5	14.9
0°-40°	2083.3	23.6
0°-60°	3469.1	39.3
0°-90°	4202.0	47.6
90°-120°	1002.3	11.4
90°-150°	3420.9	38.8
90°-180°	4618.0	52.4
0°-180°	8820.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1775	1769	1754	1767	1765	168
15°	1687	1678	1651	1649	1638	475
25°	1530	1509	1460	1443	1428	704
35°	1318	1284	1226	1188	1168	825
45°	1079	1038	967	915	893	832
55°	819	774	701	642	619	732
65°	554	507	438	386	364	549
75°	295	254	199	170	160	313
85°	74	51	43	42	40	83
90°	1	10	18	23	27	6
95°	64	58	18	23	23	81
105°	328	332	332	332	331	347
115°	615	621	622	617	611	610
125°	875	882	883	878	875	781
135°	1091	1098	1096	1093	1087	841
145°	1265	1267	1268	1268	1262	791
155°	1393	1387	1389	1392	1384	642
165°	1470	1464	1465	1471	1463	415
175°	1504	1498	1498	1506	1497	143
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1780.5	1779.9	1779.1	1778.4	1777.7	1776.2	1773.7	1771.3	1769.0	1766.6	1769.0
5°	1774.7	1773.5	1772.3	1771.1	1769.9	1767.6	1764.4	1761.1	1757.8	1754.5	1757.5
7.5°	1757.2	1756.1	1755.0	1753.8	1752.7	1750.2	1746.2	1742.2	1738.4	1734.4	1736.5
10°	1741.1	1740.2	1739.3	1738.4	1737.5	1735.0	1730.8	1726.6	1722.4	1718.3	1719.2
12.5°	1722.9	1721.7	1720.5	1719.4	1718.3	1714.9	1709.3	1703.7	1698.1	1692.5	1693.2
15°	1687.4	1685.6	1683.9	1682.0	1680.2	1676.2	1669.9	1663.7	1657.4	1651.1	1650.9
17.5°	1647.4	1644.7	1641.9	1639.2	1636.4	1631.1	1623.2	1615.3	1607.5	1599.6	1598.1
20°	1616.3	1613.3	1610.2	1607.3	1604.3	1598.0	1588.5	1579.0	1569.4	1559.9	1558.4
22.5°	1581.9	1578.9	1575.9	1573.0	1569.9	1563.5	1553.4	1543.4	1533.4	1523.4	1520.4
25°	1530.3	1525.9	1521.4	1516.9	1512.4	1504.7	1493.7	1482.6	1471.5	1460.5	1456.6
27.5°	1471.3	1465.9	1460.4	1455.0	1449.6	1441.0	1429.1	1417.3	1405.5	1393.7	1388.3
30°	1428.3	1422.6	1416.9	1411.4	1405.7	1396.5	1384.0	1371.5	1358.9	1346.4	1339.5
32.5°	1386.5	1379.8	1373.2	1366.6	1359.9	1350.2	1337.5	1324.7	1311.9	1299.2	1291.6
35°	1318.3	1311.0	1303.9	1296.8	1289.6	1279.3	1265.8	1252.5	1239.1	1225.6	1216.9
37.5°	1251.4	1242.7	1234.0	1225.3	1216.5	1205.2	1191.5	1177.6	1163.7	1149.9	1139.5
40°	1204.1	1195.2	1186.2	1177.2	1168.4	1156.7	1142.4	1128.1	1113.7	1099.4	1088.1
42.5°	1154.8	1145.6	1136.3	1127.1	1118.0	1106.0	1091.2	1076.4	1061.6	1046.8	1036.0
45°	1079.3	1070.7	1062.0	1053.3	1044.7	1032.2	1015.7	999.4	982.9	966.6	954.6
47.5°	1001.2	992.0	982.9	973.8	964.7	951.8	935.3	918.8	902.2	885.7	873.4
50°	951.7	941.9	932.0	922.2	912.4	899.0	881.9	865.0	847.9	831.0	818.4
52.5°	898.0	887.9	877.9	867.8	857.7	844.6	828.6	812.6	796.5	780.5	767.0
55°	818.9	809.3	799.8	790.2	780.7	767.6	750.9	734.2	717.5	700.8	687.3
57.5°	738.8	728.7	718.4	708.3	698.0	684.9	668.8	652.6	636.5	620.4	607.3
60°	687.3	676.8	666.4	656.0	645.6	632.2	616.1	600.0	583.9	567.8	554.7
62.5°	632.6	622.6	612.6	602.6	592.7	579.5	563.2	546.8	530.5	514.1	502.0
65°	554.4	544.2	534.2	524.0	513.8	500.8	485.1	469.2	453.4	437.6	425.7
67.5°	476.8	466.7	456.5	446.4	436.3	423.6	408.5	393.3	378.2	363.0	352.1
70°	424.2	414.1	403.9	393.7	383.7	371.1	356.2	341.3	326.3	311.4	302.2
72.5°	372.6	362.7	352.8	342.9	333.0	321.1	307.1	293.2	279.2	265.3	256.8
75°	295.3	286.4	277.4	268.5	259.5	248.8	236.3	223.8	211.2	198.6	192.1
77.5°	218.5	211.4	204.2	197.1	189.9	181.3	171.3	161.3	151.3	141.2	136.6
80°	174.5	167.4	160.2	153.0	145.9	138.1	129.8	121.4	113.0	104.7	102.0
82.5°	131.6	125.1	118.6	112.2	105.8	99.7	93.9	88.3	82.5	76.8	75.5
85°	73.9	68.4	63.1	57.7	52.3	48.9	47.4	46.0	44.4	43.0	42.6
87.5°	24.9	23.7	22.4	21.1	19.8	19.3	19.4	19.5	19.5	19.7	19.9
90°	1.1	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1
92.5°	17.1	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1
95°	63.5	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1
97.5°	132.7	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9
100°	186.1	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0
102.5°	240.6	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5
105°	327.8	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5
110°	477.2	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6



TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	532.4	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5
115°	615.4	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0
117.5°	701.2	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0
120°	754.7	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5
122.5°	801.9	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3
125°	875.1	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9
127.5°	944.9	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3
130°	987.7	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7
132.5°	1030.5	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4
135°	1091.4	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4
137.5°	1147.4	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2
140°	1183.9	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5
142.5°	1216.9	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9
145°	1265.2	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7
147.5°	1307.6	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8
150°	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9
152.5°	1360.2	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1
155°	1393.4	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7
157.5°	1419.1	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1
160°	1436.9	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4
162.5°	1451.2	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0
165°	1470.4	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3
167.5°	1484.6	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7
170°	1492.7	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0
172.5°	1498.1	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0
175°	1503.8	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2
177.5°	1506.5	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1771.3	1773.7	1776.2	1777.2	1777.0	1776.8	1776.5	1776.2
5°	1760.5	1763.5	1766.4	1767.6	1767.0	1766.4	1765.8	1765.2
7.5°	1738.5	1740.7	1742.8	1743.4	1742.8	1742.1	1741.5	1740.9
10°	1720.0	1721.0	1721.8	1721.8	1721.0	1720.0	1719.2	1718.3
12.5°	1693.8	1694.4	1695.1	1694.8	1693.4	1692.0	1690.7	1689.3
15°	1650.5	1650.3	1649.9	1648.5	1645.8	1643.1	1640.4	1637.7
17.5°	1596.6	1595.1	1593.6	1591.8	1589.6	1587.3	1585.2	1582.9
20°	1556.9	1555.4	1553.9	1551.8	1549.1	1546.4	1543.8	1541.1
22.5°	1517.5	1514.6	1511.7	1509.1	1506.9	1504.7	1502.4	1500.3
25°	1452.8	1448.9	1445.0	1441.4	1438.1	1434.9	1431.6	1428.3
27.5°	1382.9	1377.4	1372.0	1367.7	1364.5	1361.3	1358.1	1355.0
30°	1332.7	1325.9	1319.0	1314.2	1311.6	1308.8	1306.1	1303.5
32.5°	1284.0	1276.4	1268.9	1263.3	1260.0	1256.5	1253.2	1249.7
35°	1208.3	1199.6	1191.0	1184.6	1180.4	1176.2	1172.1	1167.9
37.5°	1129.1	1118.8	1108.4	1101.1	1097.1	1093.0	1089.0	1084.9
40°	1076.8	1065.4	1054.1	1046.6	1043.0	1039.5	1035.9	1032.3
42.5°	1025.1	1014.3	1003.4	995.3	990.1	984.8	979.6	974.3
45°	942.6	930.7	918.8	910.6	906.1	901.6	897.2	892.7
47.5°	861.2	848.9	836.5	827.9	822.9	818.0	813.0	808.1
50°	805.9	793.3	780.8	772.3	767.8	763.4	758.9	754.4
52.5°	753.5	740.0	726.5	717.6	713.1	708.6	704.1	699.6
55°	673.9	660.5	647.0	637.9	633.2	628.4	623.6	618.9
57.5°	594.2	581.1	567.9	559.3	555.0	550.8	546.6	542.3
60°	541.6	528.5	515.3	506.5	502.0	497.6	493.1	488.6
62.5°	489.8	477.6	465.5	457.1	452.6	448.2	443.7	439.2
65°	413.8	401.8	389.9	381.7	377.2	372.7	368.2	363.8
67.5°	341.1	330.2	319.3	312.0	308.5	304.9	301.4	297.7
70°	292.9	283.7	274.5	268.0	264.4	260.9	257.3	253.7
72.5°	248.2	239.7	231.1	225.7	223.3	220.9	218.5	216.1
75°	185.5	179.0	172.5	168.1	166.0	163.9	161.9	159.7
77.5°	132.0	127.4	122.9	119.8	118.2	116.7	115.1	113.6
80°	99.4	96.7	93.9	92.3	91.7	91.1	90.6	90.0
82.5°	74.3	73.0	71.8	70.9	70.6	70.3	69.9	69.6
85°	42.4	42.1	41.8	41.5	41.2	40.9	40.6	40.3
87.5°	20.1	20.4	20.7	20.8	20.7	20.6	20.5	20.4
90°	20.3	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	20.3	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	20.3	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	40.9	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	120.1	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	233.5	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.6	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.9	477.2	476.4	476.1	476.4	476.6	476.9	477.2





TEST NUMBER: P333734-935

CATALOG NUMBER: S125RDIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	534.5	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	620.1	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	702.7	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	756.0	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.8	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	880.9	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.7	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.9	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.2	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.8	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.3	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.0	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.0	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.0	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.2	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.4	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1358.6	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1390.5	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1416.9	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1433.4	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1448.4	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1467.7	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1482.5	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1490.0	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1495.8	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1502.2	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1504.9	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)