

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333736-935

Luminaire Tested: **S125RDIW-S1270D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333736-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1560U935-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9608.7 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	45	44	44	38
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10559	10559	10559	10559
5°	12149	10573	9337	10573
10°	13935	10519	8239	10519
15°	15051	10411	7324	10411
20°	16597	10287	6763	10287
25°	19207	10120	6274	10120
30°	20901	9945	5956	9945
35°	17631	9742	5662	9742
40°	12312	9377	5409	9377
45°	9134	8882	5161	8882
50°	7283	8368	4950	8368
55°	6182	7731	4761	7731
60°	5341	7161	4456	7161
65°	4759	6544	3836	6544
70°	4181	5995	3497	5995
75°	3618	5190	3284	5190
80°	2745	4366	2745	4366
85°	2290	3431	2586	3431



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.8	1.6
10°-20°	459.5	4.8
20°-30°	728.5	7.6
30°-40°	878.5	9.1
40°-50°	784.5	8.2
50°-60°	601.6	6.3
60°-70°	391.0	4.1
70°-80°	190.1	2.0
80°-90°	49.0	0.5
90°-100°	63.5	0.7
100°-110°	391.6	4.1
110°-120°	710.2	7.4
120°-130°	911.5	9.5
130°-140°	980.4	10.2
140°-150°	920.2	9.6
150°-160°	744.4	7.7
160°-170°	481.4	5.0
170°-180°	166.0	1.7
0°-30°	1344.7	14.0
0°-40°	2223.3	23.1
0°-60°	3609.4	37.6
0°-90°	4239.5	44.1
90°-120°	1165.3	12.1
90°-150°	3977.4	41.4
90°-180°	5369.0	55.9
0°-180°	9608.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1635	1635	1635	1635	1635	
5°	1874	1631	1440	1631	1874	187
15°	2251	1557	1095	1557	2251	645
25°	2695	1420	880	1420	2695	1238
35°	2236	1236	718	1236	2236	1351
45°	1000	972	565	972	1000	798
55°	549	687	423	687	549	498
65°	311	428	251	428	311	310
75°	145	208	132	208	145	154
85°	31	46	35	46	31	36
90°	31	1	31	1	31	15
95°	27	74	27	74	27	22
105°	385	381	385	381	385	348
115°	710	716	710	716	710	705
125°	1017	1017	1017	1017	1017	905
135°	1264	1269	1264	1269	1264	975
145°	1467	1471	1467	1471	1467	916
155°	1608	1620	1608	1620	1608	741
165°	1700	1710	1700	1710	1700	480
175°	1741	1748	1741	1748	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1719.8	1718.7	1720.9	1714.9	1715.5	1706.3	1706.3	1699.4	1690.2	1683.3	1680.1
5°	1873.9	1875.3	1872.5	1862.4	1855.8	1845.7	1834.3	1814.1	1797.3	1781.2	1768.5
7.5°	2032.6	2033.5	2024.6	2021.5	2004.6	1992.3	1966.9	1939.5	1915.2	1884.4	1860.7
10°	2124.9	2124.3	2114.8	2107.5	2092.7	2073.9	2049.1	2016.8	1986.7	1953.1	1920.9
12.5°	2178.6	2176.9	2173.9	2164.9	2151.2	2134.6	2113.5	2081.8	2044.6	2007.9	1970.2
15°	2251.1	2246.3	2237.7	2226.2	2206.7	2187.3	2163.8	2135.6	2100.1	2058.5	2023.5
17.5°	2340.7	2340.9	2327.5	2311.6	2285.2	2250.8	2214.6	2169.0	2120.7	2074.9	2037.8
20°	2414.8	2412.8	2399.4	2368.5	2338.3	2295.3	2253.8	2198.0	2139.0	2079.2	2032.9
22.5°	2521.2	2515.9	2502.0	2461.4	2414.6	2359.2	2295.6	2227.6	2156.2	2088.4	2027.6
25°	2695.4	2691.3	2663.8	2616.8	2551.1	2465.8	2382.6	2289.3	2186.7	2097.4	2023.5
27.5°	2814.6	2810.1	2789.7	2750.7	2690.0	2600.3	2487.7	2363.0	2234.8	2112.0	2005.5
30°	2802.7	2812.8	2810.1	2792.1	2746.4	2665.8	2561.8	2421.6	2269.2	2124.9	1998.0
32.5°	2634.1	2643.2	2666.8	2702.3	2705.0	2672.8	2595.1	2465.6	2307.8	2143.7	1992.1
35°	2236.3	2248.4	2294.0	2365.9	2459.8	2538.3	2554.4	2484.7	2343.0	2166.5	1983.3
37.5°	1719.2	1785.3	1823.7	1899.3	2041.3	2185.7	2324.6	2375.8	2315.5	2157.1	1968.9
40°	1460.4	1476.5	1545.0	1630.2	1749.7	1900.1	2098.1	2241.0	2245.7	2135.6	1946.4
42.5°	1250.0	1270.4	1317.3	1385.4	1487.7	1638.1	1842.5	2031.1	2118.5	2076.6	1916.8
45°	1000.1	1015.5	1049.7	1102.1	1180.6	1304.8	1480.6	1698.7	1871.9	1939.7	1837.6
47.5°	821.5	829.8	859.6	899.5	957.6	1048.1	1184.2	1373.6	1581.2	1726.9	1712.5
50°	724.9	734.3	757.1	787.3	836.3	912.7	1021.5	1179.2	1393.4	1571.2	1606.8
52.5°	649.7	657.5	671.7	700.3	740.7	799.5	887.3	1029.9	1222.6	1411.7	1494.0
55°	549.0	554.4	565.8	581.9	614.2	656.4	732.2	830.9	986.6	1177.2	1298.0
57.5°	466.1	468.7	476.0	490.9	513.2	544.1	598.8	682.4	794.1	965.8	1099.1
60°	413.5	416.1	425.5	435.6	453.1	481.2	524.2	582.6	689.9	831.6	966.5
62.5°	371.5	373.2	377.2	387.3	402.6	424.3	458.1	505.8	591.2	715.6	843.0
65°	311.4	312.1	313.4	321.5	330.9	347.0	369.1	402.7	467.1	561.1	673.8
67.5°	253.7	254.6	259.3	262.2	272.0	280.4	293.4	319.1	364.5	427.8	515.5
70°	221.4	220.8	225.5	228.9	232.2	242.3	251.0	271.8	300.0	348.4	421.5
72.5°	191.4	189.7	191.7	192.9	197.3	204.1	212.9	225.7	247.4	280.7	336.7
75°	145.0	145.7	145.7	147.0	150.3	153.0	155.7	162.4	174.5	196.7	226.9
77.5°	101.8	100.7	103.5	103.9	105.9	108.8	111.2	113.8	118.8	127.9	143.5
80°	73.8	73.8	74.5	76.5	75.9	77.1	80.5	83.3	89.3	94.6	100.0
82.5°	56.7	56.1	56.7	57.2	57.1	58.4	59.6	60.1	62.4	65.1	68.9
85°	30.9	30.9	31.5	31.5	32.2	32.2	32.9	32.9	32.9	33.6	34.3
87.5°	18.0	17.3	16.6	16.4	16.8	17.7	16.8	16.0	15.7	15.4	15.6
90°	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6	22.2	20.8	18.7
92.5°	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6	22.2	20.8	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6	22.2	20.8	31.7
97.5°	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5	55.6	63.8	85.4
100°	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7	182.6	225.5	224.4
102.5°	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5	279.7	287.7	287.1
105°	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0	489.0	488.9	488.4
110°	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6	556.5	557.3	556.7



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5	622.6	623.7	623.4
115°	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9	722.0	723.2	723.0
117.5°	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9	818.4	819.9	818.8
120°	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9	879.5	880.0	879.2
122.5°	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0	938.6	939.2	938.7
125°	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2	1025.4	1026.5	1026.5
127.5°	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0	1103.6	1104.3	1104.5
130°	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4	1155.3	1156.2	1155.8
132.5°	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5	1202.6	1202.8	1203.4
135°	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9	1273.5	1274.1	1274.6
137.5°	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6	1338.5	1338.3	1338.9
140°	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9	1378.4	1377.8	1378.0
142.5°	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4	1418.3	1418.2	1417.8
145°	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3	1473.9	1473.7	1473.7
147.5°	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1	1521.7	1521.4	1521.0
150°	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6	1552.0	1551.4	1550.8
152.5°	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6	1579.0	1578.4	1577.9
155°	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7	1615.8	1615.0	1614.4
157.5°	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4	1646.5	1645.5	1645.5
160°	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5	1665.3	1664.2	1663.9
162.5°	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0	1682.4	1680.8	1680.5
165°	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5	1704.8	1703.1	1702.8
167.5°	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5	1721.5	1719.4	1719.2
170°	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3	1730.0	1727.7	1727.4
172.5°	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1	1737.1	1735.0	1734.5
175°	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5	1744.3	1742.0	1741.7
177.5°	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6	1748.0	1746.4	1746.1
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1680.1	1676.3	1669.3	1662.8	1654.8	1647.9	1643.0	1637.1	1629.6	1620.5	1612.9
5°	1754.4	1739.7	1720.2	1703.4	1682.0	1665.2	1647.7	1630.9	1614.1	1592.7	1573.9
7.5°	1836.9	1806.4	1776.7	1739.4	1705.6	1675.3	1646.3	1617.0	1588.2	1557.7	1528.4
10°	1887.3	1850.4	1809.5	1762.5	1719.5	1678.6	1641.0	1604.0	1565.1	1530.9	1494.0
12.5°	1934.6	1886.9	1840.0	1780.7	1729.1	1679.1	1631.3	1585.3	1543.7	1499.3	1459.7
15°	1977.2	1930.3	1877.9	1805.4	1733.6	1673.2	1616.8	1557.1	1505.4	1455.8	1411.4
17.5°	1993.7	1944.5	1883.7	1814.0	1735.5	1659.5	1586.9	1521.4	1460.6	1402.7	1352.9
20°	1987.3	1939.7	1877.2	1810.8	1726.9	1647.7	1569.2	1496.7	1428.9	1367.8	1314.8
22.5°	1971.8	1922.4	1862.2	1792.0	1712.4	1628.4	1544.5	1467.1	1396.1	1332.9	1275.1
25°	1948.4	1881.3	1819.6	1751.0	1675.2	1592.0	1505.4	1420.1	1344.4	1279.9	1216.9
27.5°	1924.1	1840.3	1761.8	1693.8	1613.6	1539.4	1455.9	1368.5	1288.7	1223.1	1158.4
30°	1902.0	1808.1	1721.5	1644.3	1568.5	1498.1	1418.8	1333.6	1251.7	1184.0	1118.2
32.5°	1874.7	1774.8	1679.6	1590.6	1517.5	1447.6	1375.9	1294.4	1214.7	1144.7	1077.9
35°	1840.3	1712.8	1609.5	1514.8	1433.6	1365.8	1301.4	1235.6	1155.7	1083.2	1018.1
37.5°	1795.2	1650.5	1530.9	1427.8	1342.2	1274.1	1223.2	1163.1	1090.2	1020.8	960.4
40°	1767.8	1605.4	1474.5	1372.5	1282.5	1210.7	1163.1	1112.2	1045.7	980.6	920.2
42.5°	1731.3	1564.1	1417.6	1311.3	1220.8	1151.7	1103.5	1058.9	1003.2	941.9	877.2
45°	1659.7	1483.9	1330.2	1216.2	1124.9	1057.0	1012.1	972.5	930.2	873.8	817.4
47.5°	1566.6	1400.3	1239.5	1114.9	1025.5	962.6	918.9	887.7	857.5	809.5	754.8
50°	1492.0	1331.6	1174.5	1053.7	958.4	898.7	857.7	832.9	805.4	761.7	716.1
52.5°	1403.9	1260.7	1106.9	983.3	893.5	837.5	798.1	773.4	750.6	715.1	671.6
55°	1265.2	1139.6	998.7	886.6	804.1	747.7	710.1	686.6	673.2	643.0	608.7
57.5°	1105.0	1015.0	890.8	782.7	709.7	654.0	626.5	606.5	591.3	570.0	545.8
60°	993.3	930.2	818.8	716.1	649.0	596.0	571.2	554.4	540.3	522.2	503.3
62.5°	880.0	834.1	737.2	649.0	587.3	542.9	519.6	504.5	488.2	476.0	457.7
65°	728.2	687.3	620.2	551.0	494.0	458.4	441.6	428.2	418.1	404.7	391.9
67.5°	566.5	549.8	503.5	455.8	414.9	383.2	368.8	359.4	347.2	339.2	330.5
70°	467.1	459.1	426.2	394.7	356.4	334.9	321.5	317.5	302.7	294.6	288.6
72.5°	379.1	375.3	356.4	334.5	307.5	288.7	276.4	271.8	262.4	256.0	252.1
75°	259.8	261.1	257.7	243.7	233.6	221.4	210.8	208.0	201.4	196.0	192.6
77.5°	164.3	171.2	171.4	170.7	166.7	159.4	154.9	152.9	146.3	144.3	143.5
80°	112.8	120.1	126.8	126.1	124.8	122.9	119.5	117.4	114.1	112.1	110.7
82.5°	75.2	82.1	87.6	91.3	91.0	89.0	86.7	85.8	85.1	83.6	83.3
85°	35.6	36.9	38.9	43.7	47.0	47.6	47.0	46.3	44.3	44.9	45.6
87.5°	15.7	15.3	15.4	15.0	13.9	16.2	17.4	17.5	16.8	16.2	15.6
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0	18.3	16.7	15.2
95°	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9	73.0	72.2	71.3
97.5°	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2	155.8	157.3	158.9
100°	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5	217.3	218.2	219.0
102.5°	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7	280.8	281.9	283.0
105°	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1	382.2	383.4	384.5
107.5°	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3	486.3	486.3	486.3
110°	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7	554.7	554.7	554.7





TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1	619.7	620.4	621.1
115°	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5	716.9	718.3	719.8
117.5°	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3	815.2	815.1	815.1
120°	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4	877.2	876.9	876.6
122.5°	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5	933.5	934.6	935.7
125°	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4	1019.4	1021.5	1023.5
127.5°	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5	1100.0	1101.5	1102.9
130°	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3	1149.8	1151.2	1152.7
132.5°	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1	1199.8	1201.4	1203.2
135°	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9	1270.6	1272.4	1274.1
137.5°	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9	1335.4	1337.0	1338.4
140°	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5	1377.1	1377.6	1378.2
142.5°	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8	1415.1	1415.5	1415.8
145°	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1	1471.6	1472.2	1472.8
147.5°	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4	1520.2	1520.1	1520.0
150°	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1550.8	1550.3	1549.7
152.5°	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5	1580.3	1579.0	1577.7
155°	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1	1618.4	1616.7	1615.0
157.5°	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9	1648.9	1647.9	1646.8
160°	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7	1669.0	1667.2	1665.5
162.5°	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3	1685.6	1683.9	1682.0
165°	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6	1707.9	1706.1	1704.3
167.5°	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1	1724.4	1722.6	1720.8
170°	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5	1733.5	1731.5	1729.4
172.5°	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7	1739.7	1737.7	1735.7
175°	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4	1746.7	1745.0	1743.3
177.5°	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5	1750.2	1748.8	1747.4
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1607.6	1600.1	1594.7	1583.9	1576.4	1573.2	1567.3	1565.6	1571.6	1567.3	1566.8
5°	1559.8	1540.3	1524.9	1509.4	1492.6	1482.0	1465.9	1463.1	1459.1	1453.0	1451.7
7.5°	1502.4	1477.1	1457.2	1431.8	1409.5	1391.7	1371.6	1362.0	1356.8	1349.0	1338.6
10°	1463.8	1433.6	1406.8	1381.2	1353.8	1331.6	1311.5	1296.0	1285.9	1276.5	1272.6
12.5°	1425.6	1394.9	1360.6	1329.7	1299.0	1274.1	1251.8	1241.8	1230.6	1219.6	1210.2
15°	1366.5	1325.5	1288.0	1252.4	1226.2	1199.4	1177.8	1163.1	1146.3	1141.7	1123.5
17.5°	1303.6	1263.5	1219.5	1182.1	1151.7	1122.1	1098.5	1081.8	1069.2	1051.9	1043.5
20°	1264.5	1216.9	1173.9	1139.6	1106.0	1071.2	1047.0	1032.9	1020.8	1006.8	1000.1
22.5°	1222.6	1176.0	1132.0	1091.8	1057.7	1023.4	1006.2	991.6	977.8	964.8	956.0
25°	1161.1	1114.1	1067.8	1026.2	990.7	965.8	945.6	928.8	921.5	908.8	899.3
27.5°	1100.3	1050.3	1002.3	960.8	932.9	908.4	891.8	878.6	865.2	854.1	845.9
30°	1061.1	1010.1	957.8	924.9	895.4	871.8	853.7	840.9	830.9	820.8	814.8
32.5°	1021.9	969.3	922.8	887.3	859.4	839.0	820.4	808.2	797.6	786.4	779.4
35°	959.1	905.4	867.8	832.9	805.4	786.6	773.9	756.4	747.7	739.6	732.2
37.5°	900.7	850.8	810.1	779.5	755.6	736.9	720.4	711.0	700.3	693.0	686.9
40°	857.7	812.1	775.2	743.0	725.6	704.7	689.3	677.2	669.2	659.8	653.1
42.5°	819.1	776.7	740.8	711.9	690.1	672.5	657.6	645.5	635.3	628.6	622.9
45°	764.5	722.2	687.3	660.4	640.3	623.5	608.0	602.0	588.6	580.6	577.9
47.5°	707.9	670.1	636.4	611.7	591.0	575.1	560.7	548.4	541.0	533.0	528.7
50°	669.9	633.6	602.0	577.9	557.8	540.3	526.8	518.8	508.8	501.4	496.0
52.5°	631.7	598.1	566.6	543.5	526.1	508.6	493.6	485.5	476.0	471.3	467.5
55°	577.2	541.7	514.8	492.0	473.8	457.7	443.7	435.6	429.6	424.8	423.5
57.5°	515.5	487.2	462.3	441.8	422.9	407.8	395.5	387.8	382.5	381.8	377.7
60°	475.2	449.7	426.9	404.7	388.6	374.5	363.8	355.1	349.7	349.0	347.7
62.5°	434.9	410.4	389.3	369.8	355.3	341.7	331.6	321.8	318.6	315.2	312.2
65°	375.1	353.0	335.6	320.1	304.7	293.3	283.3	277.2	269.8	265.8	258.4
67.5°	316.5	299.4	282.6	269.6	257.4	246.6	238.2	229.3	224.3	221.1	215.7
70°	277.8	264.4	247.6	233.6	224.2	215.4	208.7	198.6	195.3	192.6	189.9
72.5°	241.3	229.5	215.4	204.1	194.7	186.4	178.7	173.9	170.7	167.9	166.3
75°	189.9	178.6	166.4	158.4	151.7	145.0	140.9	137.6	136.2	135.6	132.9
77.5°	139.5	133.5	123.7	117.4	112.9	110.2	106.6	104.9	104.7	101.8	100.8
80°	106.7	103.3	95.3	92.6	89.3	86.6	84.6	81.2	77.8	76.5	74.5
82.5°	79.3	75.9	72.8	68.4	65.6	64.1	62.0	60.8	61.2	59.3	58.4
85°	42.3	38.9	37.6	36.9	35.6	36.9	36.2	35.6	34.9	34.3	34.9
87.5°	15.5	15.9	15.8	17.3	16.1	17.0	17.3	17.0	17.4	17.7	17.3
90°	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6	25.1	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6	25.1	26.5	27.4
95°	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6	25.1	26.5	27.2
97.5°	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5	39.4	31.3	27.2
100°	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7	96.8	53.9	31.9
102.5°	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5	263.4	255.3	241.4
105°	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.1
107.5°	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0	489.0	489.1	488.7
110°	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6	554.7	553.9	553.6



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5	620.4	619.3	618.5
115°	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9	719.8	718.6	717.2
117.5°	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9	815.5	813.9	812.8
120°	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9	878.3	877.8	876.8
122.5°	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0	937.5	936.9	935.7
125°	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2	1023.0	1021.9	1020.9
127.5°	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0	1102.4	1101.7	1100.4
130°	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4	1153.6	1152.7	1151.5
132.5°	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5	1202.3	1202.1	1201.3
135°	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9	1272.4	1271.8	1270.6
137.5°	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6	1338.7	1338.9	1338.2
140°	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9	1379.5	1380.1	1379.5
142.5°	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4	1418.6	1418.7	1417.9
145°	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3	1474.5	1474.8	1474.1
147.5°	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1	1522.4	1522.8	1521.9
150°	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6	1553.2	1553.8	1552.9
152.5°	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6	1580.1	1580.7	1579.9
155°	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7	1617.6	1618.4	1617.6
157.5°	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4	1648.3	1649.2	1648.6
160°	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5	1667.7	1668.8	1668.3
162.5°	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0	1685.7	1687.2	1686.8
165°	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5	1708.3	1710.0	1709.7
167.5°	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5	1725.6	1727.7	1727.4
170°	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3	1734.7	1736.9	1736.8
172.5°	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1	1741.2	1743.3	1743.0
175°	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5	1748.9	1751.2	1751.0
177.5°	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6	1751.2	1752.8	1752.7
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1566.2	1560.3	1558.7	1560.8	1558.7	1560.3	1566.2	1566.8	1567.3	1571.6	1565.6
5°	1445.0	1438.3	1441.7	1440.3	1441.7	1438.3	1445.0	1451.7	1453.0	1459.1	1463.1
7.5°	1338.4	1330.1	1321.2	1324.0	1321.2	1330.1	1338.4	1338.6	1349.0	1356.8	1362.0
10°	1263.8	1257.1	1253.0	1256.4	1253.0	1257.1	1263.8	1272.6	1276.5	1285.9	1296.0
12.5°	1201.0	1197.0	1193.4	1192.0	1193.4	1197.0	1201.0	1210.2	1219.6	1230.6	1241.8
15°	1115.4	1107.4	1104.1	1095.4	1104.1	1107.4	1115.4	1123.5	1141.7	1146.3	1163.1
17.5°	1036.6	1034.0	1025.3	1021.5	1025.3	1034.0	1036.6	1043.5	1051.9	1069.2	1081.8
20°	990.0	987.3	978.5	984.0	978.5	987.3	990.0	1000.1	1006.8	1020.8	1032.9
22.5°	951.3	945.4	942.5	941.0	942.5	945.4	951.3	956.0	964.8	977.8	991.6
25°	896.6	887.9	884.6	880.5	884.6	887.9	896.6	899.3	908.8	921.5	928.8
27.5°	842.1	837.5	833.0	832.0	833.0	837.5	842.1	845.9	854.1	865.2	878.6
30°	806.8	802.0	798.7	798.7	798.7	802.0	806.8	814.8	820.8	830.9	840.9
32.5°	775.1	771.5	768.1	767.6	768.1	771.5	775.1	779.4	786.4	797.6	808.2
35°	728.9	723.5	722.2	718.2	722.2	723.5	728.9	732.2	739.6	747.7	756.4
37.5°	681.0	676.5	676.4	676.0	676.4	676.5	681.0	686.9	693.0	700.3	711.0
40°	650.3	647.0	646.4	641.6	646.4	647.0	650.3	653.1	659.8	669.2	677.2
42.5°	617.6	615.9	613.5	611.6	613.5	615.9	617.6	622.9	628.6	635.3	645.5
45°	573.2	568.4	568.4	565.1	568.4	568.4	573.2	577.9	580.6	588.6	602.0
47.5°	527.3	523.7	524.0	520.6	524.0	523.7	527.3	528.7	533.0	541.0	548.4
50°	496.6	494.6	494.0	492.7	494.0	494.6	496.6	496.0	501.4	508.8	518.8
52.5°	466.1	465.1	467.7	464.7	467.7	465.1	466.1	467.5	471.3	476.0	485.5
55°	424.8	422.8	426.9	422.8	426.9	422.8	424.8	423.5	424.8	429.6	435.6
57.5°	377.5	375.6	379.2	377.2	379.2	375.6	377.5	377.7	381.8	382.5	387.8
60°	346.3	342.3	344.3	345.0	344.3	342.3	346.3	347.7	349.0	349.7	355.1
62.5°	309.3	306.9	308.3	305.2	308.3	306.9	309.3	312.2	315.2	318.6	321.8
65°	257.1	255.0	252.4	251.0	252.4	255.0	257.1	258.4	265.8	269.8	277.2
67.5°	215.9	211.1	211.0	212.1	211.0	211.1	215.9	215.7	221.1	224.3	229.3
70°	185.9	185.9	185.2	185.2	185.2	185.9	185.9	189.9	192.6	195.3	198.6
72.5°	165.0	164.5	163.2	162.7	163.2	164.5	165.0	166.3	167.9	170.7	173.9
75°	132.9	133.5	132.2	131.6	132.2	133.5	132.9	132.9	135.6	136.2	137.6
77.5°	98.2	95.3	96.8	95.3	96.8	95.3	98.2	100.8	101.8	104.7	104.9
80°	74.5	73.8	75.9	73.8	75.9	73.8	74.5	74.5	76.5	77.8	81.2
82.5°	58.9	58.3	59.2	57.7	59.2	58.3	58.9	58.4	59.3	61.2	60.8
85°	35.6	34.9	34.3	34.9	34.3	34.9	35.6	34.9	34.3	34.9	35.6
87.5°	18.1	17.7	17.8	18.0	17.8	17.7	18.1	17.3	17.7	17.4	17.0
90°	28.5	29.4	30.2	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6
92.5°	27.8	28.2	28.7	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5
100°	30.7	29.5	28.4	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7
102.5°	221.8	202.2	182.6	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5
105°	385.8	385.6	385.2	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2
107.5°	487.8	487.0	486.1	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0
110°	553.9	554.1	554.5	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	618.2	617.8	617.3	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5
115°	715.5	713.7	712.0	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9
117.5°	812.1	811.3	810.5	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9
120°	875.3	873.8	872.5	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9
122.5°	934.1	932.4	930.7	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0
125°	1020.0	1019.2	1018.3	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2
127.5°	1098.2	1096.1	1094.0	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0
130°	1150.1	1148.7	1147.2	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4
132.5°	1199.9	1198.4	1197.0	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5
135°	1268.9	1267.1	1265.4	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9
137.5°	1336.6	1335.2	1333.6	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6
140°	1377.8	1376.1	1374.3	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9
142.5°	1416.1	1414.4	1412.6	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4
145°	1472.4	1470.7	1469.0	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3
147.5°	1519.8	1517.8	1515.7	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1
150°	1550.6	1548.3	1546.0	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6
152.5°	1577.9	1575.8	1573.7	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6
155°	1615.4	1613.1	1610.8	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7
157.5°	1646.2	1643.9	1641.6	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4
160°	1665.9	1663.6	1661.3	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5
162.5°	1684.3	1681.7	1679.2	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0
165°	1707.4	1705.1	1702.8	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5
167.5°	1724.8	1722.3	1719.7	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5
170°	1734.2	1731.6	1729.0	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3
172.5°	1740.4	1737.8	1735.3	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1
175°	1748.4	1745.8	1743.3	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5
177.5°	1750.8	1749.0	1747.1	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1567.3	1573.2	1576.4	1583.9	1594.7	1600.1	1607.6	1612.9	1620.5	1629.6	1637.1
5°	1465.9	1482.0	1492.6	1509.4	1524.9	1540.3	1559.8	1573.9	1592.7	1614.1	1630.9
7.5°	1371.6	1391.7	1409.5	1431.8	1457.2	1477.1	1502.4	1528.4	1557.7	1588.2	1617.0
10°	1311.5	1331.6	1353.8	1381.2	1406.8	1433.6	1463.8	1494.0	1530.9	1565.1	1604.0
12.5°	1251.8	1274.1	1299.0	1329.7	1360.6	1394.9	1425.6	1459.7	1499.3	1543.7	1585.3
15°	1177.8	1199.4	1226.2	1252.4	1288.0	1325.5	1366.5	1411.4	1455.8	1505.4	1557.1
17.5°	1098.5	1122.1	1151.7	1182.1	1219.5	1263.5	1303.6	1352.9	1402.7	1460.6	1521.4
20°	1047.0	1071.2	1106.0	1139.6	1173.9	1216.9	1264.5	1314.8	1367.8	1428.9	1496.7
22.5°	1006.2	1023.4	1057.7	1091.8	1132.0	1176.0	1222.6	1275.1	1332.9	1396.1	1467.1
25°	945.6	965.8	990.7	1026.2	1067.8	1114.1	1161.1	1216.9	1279.9	1344.4	1420.1
27.5°	891.8	908.4	932.9	960.8	1002.3	1050.3	1100.3	1158.4	1223.1	1288.7	1368.5
30°	853.7	871.8	895.4	924.9	957.8	1010.1	1061.1	1118.2	1184.0	1251.7	1333.6
32.5°	820.4	839.0	859.4	887.3	922.8	969.3	1021.9	1077.9	1144.7	1214.7	1294.4
35°	773.9	786.6	805.4	832.9	867.8	905.4	959.1	1018.1	1083.2	1155.7	1235.6
37.5°	720.4	736.9	755.6	779.5	810.1	850.8	900.7	960.4	1020.8	1090.2	1163.1
40°	689.3	704.7	725.6	743.0	775.2	812.1	857.7	920.2	980.6	1045.7	1112.2
42.5°	657.6	672.5	690.1	711.9	740.8	776.7	819.1	877.2	941.9	1003.2	1058.9
45°	608.0	623.5	640.3	660.4	687.3	722.2	764.5	817.4	873.8	930.2	972.5
47.5°	560.7	575.1	591.0	611.7	636.4	670.1	707.9	754.8	809.5	857.5	887.7
50°	526.8	540.3	557.8	577.9	602.0	633.6	669.9	716.1	761.7	805.4	832.9
52.5°	493.6	508.6	526.1	543.5	566.6	598.1	631.7	671.6	715.1	750.6	773.4
55°	443.7	457.7	473.8	492.0	514.8	541.7	577.2	608.7	643.0	673.2	686.6
57.5°	395.5	407.8	422.9	441.8	462.3	487.2	515.5	545.8	570.0	591.3	606.5
60°	363.8	374.5	388.6	404.7	426.9	449.7	475.2	503.3	522.2	540.3	554.4
62.5°	331.6	341.7	355.3	369.8	389.3	410.4	434.9	457.7	476.0	488.2	504.5
65°	283.3	293.3	304.7	320.1	335.6	353.0	375.1	391.9	404.7	418.1	428.2
67.5°	238.2	246.6	257.4	269.6	282.6	299.4	316.5	330.5	339.2	347.2	359.4
70°	208.7	215.4	224.2	233.6	247.6	264.4	277.8	288.6	294.6	302.7	317.5
72.5°	178.7	186.4	194.7	204.1	215.4	229.5	241.3	252.1	256.0	262.4	271.8
75°	140.9	145.0	151.7	158.4	166.4	178.6	189.9	192.6	196.0	201.4	208.0
77.5°	106.6	110.2	112.9	117.4	123.7	133.5	139.5	143.5	144.3	146.3	152.9
80°	84.6	86.6	89.3	92.6	95.3	103.3	106.7	110.7	112.1	114.1	117.4
82.5°	62.0	64.1	65.6	68.4	72.8	75.9	79.3	83.3	83.6	85.1	85.8
85°	36.2	36.9	35.6	36.9	37.6	38.9	42.3	45.6	44.9	44.3	46.3
87.5°	17.3	17.0	16.1	17.3	15.8	15.9	15.5	15.6	16.2	16.8	17.5
90°	22.2	20.8	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.8	18.9	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0
95°	22.2	20.8	31.7	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9
97.5°	55.6	63.8	85.4	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2
100°	182.6	225.5	224.4	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5
102.5°	279.7	287.7	287.1	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7
105°	386.2	386.2	386.2	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1
107.5°	489.0	488.9	488.4	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3
110°	556.5	557.3	556.7	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	622.6	623.7	623.4	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1
115°	722.0	723.2	723.0	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5
117.5°	818.4	819.9	818.8	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3
120°	879.5	880.0	879.2	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4
122.5°	938.6	939.2	938.7	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5
125°	1025.4	1026.5	1026.5	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4
127.5°	1103.6	1104.3	1104.5	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5
130°	1155.3	1156.2	1155.8	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3
132.5°	1202.6	1202.8	1203.4	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1
135°	1273.5	1274.1	1274.6	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9
137.5°	1338.5	1338.3	1338.9	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9
140°	1378.4	1377.8	1378.0	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5
142.5°	1418.3	1418.2	1417.8	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8
145°	1473.9	1473.7	1473.7	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1
147.5°	1521.7	1521.4	1521.0	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4
150°	1552.0	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4
152.5°	1579.0	1578.4	1577.9	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5
155°	1615.8	1615.0	1614.4	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1
157.5°	1646.5	1645.5	1645.5	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9
160°	1665.3	1664.2	1663.9	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7
162.5°	1682.4	1680.8	1680.5	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3
165°	1704.8	1703.1	1702.8	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6
167.5°	1721.5	1719.4	1719.2	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1
170°	1730.0	1727.7	1727.4	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5
172.5°	1737.1	1735.0	1734.5	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7
175°	1744.3	1742.0	1741.7	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4
177.5°	1748.0	1746.4	1746.1	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1643.0	1647.9	1654.8	1662.8	1669.3	1676.3	1680.1	1680.1	1683.3	1690.2	1699.4
5°	1647.7	1665.2	1682.0	1703.4	1720.2	1739.7	1754.4	1768.5	1781.2	1797.3	1814.1
7.5°	1646.3	1675.3	1705.6	1739.4	1776.7	1806.4	1836.9	1860.7	1884.4	1915.2	1939.5
10°	1641.0	1678.6	1719.5	1762.5	1809.5	1850.4	1887.3	1920.9	1953.1	1986.7	2016.8
12.5°	1631.3	1679.1	1729.1	1780.7	1840.0	1886.9	1934.6	1970.2	2007.9	2044.6	2081.8
15°	1616.8	1673.2	1733.6	1805.4	1877.9	1930.3	1977.2	2023.5	2058.5	2100.1	2135.6
17.5°	1586.9	1659.5	1735.5	1814.0	1883.7	1944.5	1993.7	2037.8	2074.9	2120.7	2169.0
20°	1569.2	1647.7	1726.9	1810.8	1877.2	1939.7	1987.3	2032.9	2079.2	2139.0	2198.0
22.5°	1544.5	1628.4	1712.4	1792.0	1862.2	1922.4	1971.8	2027.6	2088.4	2156.2	2227.6
25°	1505.4	1592.0	1675.2	1751.0	1819.6	1881.3	1948.4	2023.5	2097.4	2186.7	2289.3
27.5°	1455.9	1539.4	1613.6	1693.8	1761.8	1840.3	1924.1	2005.5	2112.0	2234.8	2363.0
30°	1418.8	1498.1	1568.5	1644.3	1721.5	1808.1	1902.0	1998.0	2124.9	2269.2	2421.6
32.5°	1375.9	1447.6	1517.5	1590.6	1679.6	1774.8	1874.7	1992.1	2143.7	2307.8	2465.6
35°	1301.4	1365.8	1433.6	1514.8	1609.5	1712.8	1840.3	1983.3	2166.5	2343.0	2484.7
37.5°	1223.2	1274.1	1342.2	1427.8	1530.9	1650.5	1795.2	1968.9	2157.1	2315.5	2375.8
40°	1163.1	1210.7	1282.5	1372.5	1474.5	1605.4	1767.8	1946.4	2135.6	2245.7	2241.0
42.5°	1103.5	1151.7	1220.8	1311.3	1417.6	1564.1	1731.3	1916.8	2076.6	2118.5	2031.1
45°	1012.1	1057.0	1124.9	1216.2	1330.2	1483.9	1659.7	1837.6	1939.7	1871.9	1698.7
47.5°	918.9	962.6	1025.5	1114.9	1239.5	1400.3	1566.6	1712.5	1726.9	1581.2	1373.6
50°	857.7	898.7	958.4	1053.7	1174.5	1331.6	1492.0	1606.8	1571.2	1393.4	1179.2
52.5°	798.1	837.5	893.5	983.3	1106.9	1260.7	1403.9	1494.0	1411.7	1222.6	1029.9
55°	710.1	747.7	804.1	886.6	998.7	1139.6	1265.2	1298.0	1177.2	986.6	830.9
57.5°	626.5	654.0	709.7	782.7	890.8	1015.0	1105.0	1099.1	965.8	794.1	682.4
60°	571.2	596.0	649.0	716.1	818.8	930.2	993.3	966.5	831.6	689.9	582.6
62.5°	519.6	542.9	587.3	649.0	737.2	834.1	880.0	843.0	715.6	591.2	505.8
65°	441.6	458.4	494.0	551.0	620.2	687.3	728.2	673.8	561.1	467.1	402.7
67.5°	368.8	383.2	414.9	455.8	503.5	549.8	566.5	515.5	427.8	364.5	319.1
70°	321.5	334.9	356.4	394.7	426.2	459.1	467.1	421.5	348.4	300.0	271.8
72.5°	276.4	288.7	307.5	334.5	356.4	375.3	379.1	336.7	280.7	247.4	225.7
75°	210.8	221.4	233.6	243.7	257.7	261.1	259.8	226.9	196.7	174.5	162.4
77.5°	154.9	159.4	166.7	170.7	171.4	171.2	164.3	143.5	127.9	118.8	113.8
80°	119.5	122.9	124.8	126.1	126.8	120.1	112.8	100.0	94.6	89.3	83.3
82.5°	86.7	89.0	91.0	91.3	87.6	82.1	75.2	68.9	65.1	62.4	60.1
85°	47.0	47.6	47.0	43.7	38.9	36.9	35.6	34.3	33.6	32.9	32.9
87.5°	17.4	16.2	13.9	15.0	15.4	15.3	15.7	15.6	15.4	15.7	16.0
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6
92.5°	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6
95°	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6
97.5°	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5
100°	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7
102.5°	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5
105°	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0
110°	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6





TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5
115°	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9
117.5°	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9
120°	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9
122.5°	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0
125°	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2
127.5°	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0
130°	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4
132.5°	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5
135°	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9
137.5°	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6
140°	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9
142.5°	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4
145°	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3
147.5°	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1
150°	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6
152.5°	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6
155°	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7
157.5°	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4
160°	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5
162.5°	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0
165°	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5
167.5°	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5
170°	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3
172.5°	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1
175°	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5
177.5°	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1706.3	1706.3	1715.5	1714.9	1720.9	1718.7	1719.8
5°	1834.3	1845.7	1855.8	1862.4	1872.5	1875.3	1873.9
7.5°	1966.9	1992.3	2004.6	2021.5	2024.6	2033.5	2032.6
10°	2049.1	2073.9	2092.7	2107.5	2114.8	2124.3	2124.9
12.5°	2113.5	2134.6	2151.2	2164.9	2173.9	2176.9	2178.6
15°	2163.8	2187.3	2206.7	2226.2	2237.7	2246.3	2251.1
17.5°	2214.6	2250.8	2285.2	2311.6	2327.5	2340.9	2340.7
20°	2253.8	2295.3	2338.3	2368.5	2399.4	2412.8	2414.8
22.5°	2295.6	2359.2	2414.6	2461.4	2502.0	2515.9	2521.2
25°	2382.6	2465.8	2551.1	2616.8	2663.8	2691.3	2695.4
27.5°	2487.7	2600.3	2690.0	2750.7	2789.7	2810.1	2814.6
30°	2561.8	2665.8	2746.4	2792.1	2810.1	2812.8	2802.7
32.5°	2595.1	2672.8	2705.0	2702.3	2666.8	2643.2	2634.1
35°	2554.4	2538.3	2459.8	2365.9	2294.0	2248.4	2236.3
37.5°	2324.6	2185.7	2041.3	1899.3	1823.7	1785.3	1719.2
40°	2098.1	1900.1	1749.7	1630.2	1545.0	1476.5	1460.4
42.5°	1842.5	1638.1	1487.7	1385.4	1317.3	1270.4	1250.0
45°	1480.6	1304.8	1180.6	1102.1	1049.7	1015.5	1000.1
47.5°	1184.2	1048.1	957.6	899.5	859.6	829.8	821.5
50°	1021.5	912.7	836.3	787.3	757.1	734.3	724.9
52.5°	887.3	799.5	740.7	700.3	671.7	657.5	649.7
55°	732.2	656.4	614.2	581.9	565.8	554.4	549.0
57.5°	598.8	544.1	513.2	490.9	476.0	468.7	466.1
60°	524.2	481.2	453.1	435.6	425.5	416.1	413.5
62.5°	458.1	424.3	402.6	387.3	377.2	373.2	371.5
65°	369.1	347.0	330.9	321.5	313.4	312.1	311.4
67.5°	293.4	280.4	272.0	262.2	259.3	254.6	253.7
70°	251.0	242.3	232.2	228.9	225.5	220.8	221.4
72.5°	212.9	204.1	197.3	192.9	191.7	189.7	191.4
75°	155.7	153.0	150.3	147.0	145.7	145.7	145.0
77.5°	111.2	108.8	105.9	103.9	103.5	100.7	101.8
80°	80.5	77.1	75.9	76.5	74.5	73.8	73.8
82.5°	59.6	58.4	57.1	57.2	56.7	56.1	56.7
85°	32.9	32.2	32.2	31.5	31.5	30.9	30.9
87.5°	16.8	17.7	16.8	16.4	16.6	17.3	18.0
90°	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333736-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)