

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333446-930

Luminaire Tested: **S125DIW-S1090D1050U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333446-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1050U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7038.2 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	1.9
10°-20°	370.5	5.3
20°-30°	547.1	7.8
30°-40°	638.4	9.1
40°-50°	641.2	9.1
50°-60°	562.8	8.0
60°-70°	419.4	6.0
70°-80°	239.8	3.4
80°-90°	72.1	1.0
90°-100°	40.4	0.6
100°-110°	249.1	3.5
110°-120°	451.8	6.4
120°-130°	579.9	8.2
130°-140°	623.7	8.9
140°-150°	585.4	8.3
150°-160°	473.6	6.7
160°-170°	306.3	4.4
170°-180°	105.6	1.5
0°-30°	1048.8	14.9
0°-40°	1687.2	24.0
0°-60°	2891.2	41.1
0°-90°	3622.4	51.5
90°-120°	741.4	10.5
90°-150°	2530.3	36.0
90°-180°	3416.0	48.5
0°-180°	7038.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	1	7	13	17	20	5
95°	47	43	13	17	17	60
105°	242	246	246	246	245	257
115°	455	459	460	457	452	451
125°	647	653	653	650	647	578
135°	807	812	811	809	804	622
145°	936	937	938	938	933	585
155°	1031	1026	1027	1029	1023	475
165°	1088	1083	1084	1088	1082	307
175°	1112	1108	1108	1114	1107	106
180°	1112	1112	1112	1112	1112	



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	24.0	24.2	24.5	24.8	25.1	25.3	25.4	25.4	25.4	25.5	25.7
90°	0.8	2.3	3.8	5.2	6.7	8.1	9.4	10.6	11.9	13.2	14.1
92.5°	12.7	11.7	10.7	9.6	8.6	8.6	9.8	10.9	12.1	13.2	14.1
95°	47.0	46.5	45.9	45.3	44.8	41.0	34.1	27.1	20.1	13.2	14.1
97.5°	98.2	99.1	100.1	101.1	102.1	95.7	81.9	68.2	54.4	40.6	35.4
100°	137.7	138.3	138.8	139.3	139.9	140.6	141.3	142.0	142.8	143.5	116.2
102.5°	178.0	178.6	179.4	180.0	180.8	181.3	181.7	182.1	182.6	183.0	177.9
105°	242.4	243.1	243.9	244.6	245.3	245.7	245.7	245.7	245.7	245.7	245.7
107.5°	309.4	309.4	309.4	309.4	309.4	309.6	309.9	310.3	310.6	311.0	311.0
110°	352.9	352.9	352.9	352.9	352.9	353.1	353.4	353.8	354.2	354.6	354.0



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.8	394.3	394.7	395.1	395.6	395.9	396.2	396.3	396.6	396.8	396.1
115°	455.2	456.1	457.0	457.9	458.9	459.3	459.6	459.7	459.9	460.1	459.3
117.5°	518.7	518.6	518.6	518.5	518.5	518.9	519.5	520.2	520.9	521.6	520.7
120°	558.2	558.1	557.8	557.7	557.5	557.7	558.2	558.8	559.3	559.9	559.5
122.5°	593.2	593.9	594.6	595.3	596.0	596.5	596.7	597.0	597.2	597.5	597.1
125°	647.3	648.6	649.9	651.1	652.4	653.1	653.1	653.1	653.1	653.1	652.3
127.5°	698.9	699.9	700.7	701.6	702.5	703.0	702.9	702.8	702.6	702.5	702.1
130°	730.6	731.5	732.4	733.3	734.3	734.7	735.0	735.2	735.3	735.5	735.0
132.5°	762.2	763.3	764.3	765.4	766.5	766.8	766.4	766.0	765.6	765.2	765.1
135°	807.2	808.4	809.4	810.6	811.6	812.0	811.6	811.3	810.9	810.6	810.2
137.5°	848.6	849.6	850.5	851.5	852.5	852.8	852.5	852.2	851.7	851.4	851.5
140°	875.7	876.0	876.4	876.8	877.2	877.3	877.1	876.9	876.7	876.5	876.9
142.5°	900.1	900.3	900.6	900.7	901.0	901.2	901.5	901.7	902.0	902.2	902.3
145°	935.9	936.3	936.6	937.0	937.3	937.5	937.5	937.5	937.5	937.5	937.8
147.5°	967.2	967.2	967.1	967.0	966.9	967.0	967.2	967.4	967.7	967.8	968.1
150°	987.0	986.7	986.3	985.9	985.5	985.5	985.9	986.3	986.7	987.0	987.4
152.5°	1006.2	1005.3	1004.5	1003.7	1002.9	1002.7	1003.1	1003.5	1003.8	1004.1	1004.5
155°	1030.7	1029.6	1028.5	1027.4	1026.3	1026.0	1026.3	1026.7	1027.0	1027.4	1027.9
157.5°	1049.7	1049.0	1048.4	1047.7	1047.0	1046.8	1046.8	1046.8	1046.8	1046.8	1047.5
160°	1062.9	1061.8	1060.7	1059.6	1058.5	1058.0	1058.2	1058.4	1058.6	1058.7	1059.5
162.5°	1073.4	1072.4	1071.2	1070.2	1069.0	1068.5	1068.8	1068.9	1069.1	1069.3	1070.3
165°	1087.6	1086.5	1085.4	1084.3	1083.2	1082.7	1083.0	1083.1	1083.3	1083.5	1084.6
167.5°	1098.1	1097.1	1095.9	1094.8	1093.6	1093.2	1093.3	1093.5	1093.7	1093.9	1095.2
170°	1104.1	1102.9	1101.6	1100.2	1098.9	1098.5	1098.6	1098.8	1098.9	1099.2	1100.7
172.5°	1108.1	1106.8	1105.5	1104.2	1102.9	1102.4	1102.8	1103.1	1103.4	1103.8	1105.1
175°	1112.3	1111.3	1110.1	1109.1	1107.9	1107.5	1107.7	1107.8	1108.1	1108.2	1109.7
177.5°	1114.4	1113.5	1112.6	1111.7	1110.8	1110.4	1110.6	1110.8	1110.8	1111.0	1112.1
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	25.9	26.1	26.3	26.3	25.9	25.7	25.4	25.1
90°	15.0	16.0	16.9	17.6	18.2	18.7	19.2	19.8
92.5°	15.0	16.0	16.9	17.4	17.7	17.9	18.2	18.5
95°	15.0	16.0	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	30.2	25.0	19.9	17.3	17.3	17.3	17.3	17.3
100°	88.9	61.6	34.2	20.2	19.5	18.8	18.0	17.3
102.5°	172.7	167.5	162.4	153.6	141.1	128.7	116.2	103.7
105°	245.7	245.7	245.7	245.6	245.5	245.2	245.1	244.9
107.5°	311.1	311.1	311.2	311.0	310.4	309.8	309.2	308.8
110°	353.4	352.9	352.4	352.2	352.4	352.5	352.7	352.9



TEST NUMBER: P333446-930

CATALOG NUMBER: S125DIW-S1090D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	395.4	394.7	394.0	393.5	393.3	393.0	392.7	392.5
115°	458.6	457.9	457.1	456.2	455.2	454.0	453.0	451.8
117.5°	519.8	518.8	517.8	517.1	516.7	516.2	515.7	515.2
120°	559.1	558.8	558.4	557.7	556.8	556.0	555.1	554.1
122.5°	596.7	596.4	596.0	595.3	594.3	593.2	592.2	591.1
125°	651.6	650.9	650.1	649.5	649.0	648.4	647.8	647.3
127.5°	701.7	701.3	700.9	700.0	698.7	697.3	695.9	694.6
130°	734.4	733.9	733.3	732.5	731.6	730.8	729.9	729.0
132.5°	765.0	764.8	764.8	764.3	763.4	762.4	761.5	760.6
135°	809.8	809.4	809.1	808.4	807.2	806.2	805.0	804.0
137.5°	851.6	851.7	851.7	851.3	850.4	849.4	848.5	847.5
140°	877.3	877.6	878.0	877.6	876.5	875.4	874.3	873.2
142.5°	902.4	902.5	902.5	902.0	900.9	899.8	898.7	897.6
145°	937.9	938.1	938.2	937.8	936.7	935.6	934.5	933.4
147.5°	968.3	968.6	968.7	968.2	966.9	965.6	964.3	963.0
150°	987.7	988.1	988.5	987.9	986.4	985.0	983.5	982.0
152.5°	1004.9	1005.3	1005.6	1005.2	1003.8	1002.5	1001.2	999.9
155°	1028.5	1029.1	1029.6	1029.2	1027.7	1026.2	1024.7	1023.3
157.5°	1048.1	1048.6	1049.2	1048.8	1047.3	1045.9	1044.4	1042.9
160°	1060.2	1060.9	1061.7	1061.3	1059.9	1058.4	1057.0	1055.5
162.5°	1071.4	1072.4	1073.4	1073.1	1071.5	1069.9	1068.3	1066.7
165°	1085.7	1086.8	1087.9	1087.7	1086.2	1084.8	1083.3	1081.8
167.5°	1096.5	1097.8	1099.2	1099.0	1097.3	1095.7	1094.1	1092.4
170°	1102.1	1103.6	1105.1	1104.9	1103.3	1101.6	1100.0	1098.3
172.5°	1106.4	1107.7	1109.1	1108.9	1107.3	1105.5	1103.9	1102.3
175°	1111.2	1112.6	1114.1	1114.0	1112.3	1110.7	1109.1	1107.4
177.5°	1113.0	1114.1	1115.2	1115.1	1113.9	1112.7	1111.6	1110.4
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3

(END OF REPORT)