

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333738-935

Luminaire Tested: **S125RDIW-S1270D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333738-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9571.7 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11479	11479	11479
5°	11505	11374	11444
10°	11418	11269	11269
15°	11282	11040	10950
20°	11109	10721	10592
25°	10905	10408	10178
30°	10651	10041	9721
35°	10394	9663	9208
40°	10151	9269	8703
45°	9858	8828	8153
50°	9562	8349	7580
55°	9221	7891	6969
60°	8878	7334	6311
65°	8472	6687	5559
70°	8010	5880	4791
75°	7369	4956	3985
80°	6490	3894	3347
85°	5476	3186	2986



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.1	1.7
10°-20°	467.1	4.9
20°-30°	677.3	7.1
30°-40°	771.9	8.1
40°-50°	752.4	7.9
50°-60°	633.3	6.6
60°-70°	444.0	4.6
70°-80°	228.2	2.4
80°-90°	61.3	0.6
90°-100°	63.5	0.7
100°-110°	391.6	4.1
110°-120°	710.2	7.4
120°-130°	911.5	9.5
130°-140°	980.4	10.2
140°-150°	920.2	9.6
150°-160°	744.4	7.8
160°-170°	481.4	5.0
170°-180°	166.0	1.7
0°-30°	1311.5	13.7
0°-40°	2083.3	21.8
0°-60°	3469.1	36.2
0°-90°	4202.5	43.9
90°-120°	1165.3	12.2
90°-150°	3977.4	41.6
90°-180°	5369.0	56.1
0°-180°	9571.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1775	1769	1754	1767	1765	168
15°	1687	1678	1651	1649	1638	475
25°	1530	1509	1460	1443	1428	704
35°	1318	1284	1226	1188	1168	825
45°	1079	1038	967	915	893	832
55°	819	774	701	642	619	732
65°	554	507	438	386	364	549
75°	295	254	199	170	160	313
85°	74	51	43	42	40	83
90°	1	12	21	27	31	7
95°	74	67	21	27	27	94
105°	381	386	386	386	385	404
115°	716	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1269	1276	1274	1271	1264	978
145°	1471	1474	1474	1474	1467	920
155°	1620	1613	1615	1618	1608	746
165°	1710	1702	1703	1710	1700	483
175°	1748	1741	1742	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1780.5	1779.9	1779.1	1778.4	1777.7	1776.2	1773.7	1771.3	1769.0	1766.6	1769.0
5°	1774.7	1773.5	1772.3	1771.1	1769.9	1767.6	1764.4	1761.1	1757.8	1754.5	1757.5
7.5°	1757.2	1756.1	1755.0	1753.8	1752.7	1750.2	1746.2	1742.2	1738.4	1734.4	1736.5
10°	1741.1	1740.2	1739.3	1738.4	1737.5	1735.0	1730.8	1726.6	1722.4	1718.3	1719.2
12.5°	1722.9	1721.7	1720.5	1719.4	1718.3	1714.9	1709.3	1703.7	1698.1	1692.5	1693.2
15°	1687.4	1685.6	1683.9	1682.0	1680.2	1676.2	1669.9	1663.7	1657.4	1651.1	1650.9
17.5°	1647.4	1644.7	1641.9	1639.2	1636.4	1631.1	1623.2	1615.3	1607.5	1599.6	1598.1
20°	1616.3	1613.3	1610.2	1607.3	1604.3	1598.0	1588.5	1579.0	1569.4	1559.9	1558.4
22.5°	1581.9	1578.9	1575.9	1573.0	1569.9	1563.5	1553.4	1543.4	1533.4	1523.4	1520.4
25°	1530.3	1525.9	1521.4	1516.9	1512.4	1504.7	1493.7	1482.6	1471.5	1460.5	1456.6
27.5°	1471.3	1465.9	1460.4	1455.0	1449.6	1441.0	1429.1	1417.3	1405.5	1393.7	1388.3
30°	1428.3	1422.6	1416.9	1411.4	1405.7	1396.5	1384.0	1371.5	1358.9	1346.4	1339.5
32.5°	1386.5	1379.8	1373.2	1366.6	1359.9	1350.2	1337.5	1324.7	1311.9	1299.2	1291.6
35°	1318.3	1311.0	1303.9	1296.8	1289.6	1279.3	1265.8	1252.5	1239.1	1225.6	1216.9
37.5°	1251.4	1242.7	1234.0	1225.3	1216.5	1205.2	1191.5	1177.6	1163.7	1149.9	1139.5
40°	1204.1	1195.2	1186.2	1177.2	1168.4	1156.7	1142.4	1128.1	1113.7	1099.4	1088.1
42.5°	1154.8	1145.6	1136.3	1127.1	1118.0	1106.0	1091.2	1076.4	1061.6	1046.8	1036.0
45°	1079.3	1070.7	1062.0	1053.3	1044.7	1032.2	1015.7	999.4	982.9	966.6	954.6
47.5°	1001.2	992.0	982.9	973.8	964.7	951.8	935.3	918.8	902.2	885.7	873.4
50°	951.7	941.9	932.0	922.2	912.4	899.0	881.9	865.0	847.9	831.0	818.4
52.5°	898.0	887.9	877.9	867.8	857.7	844.6	828.6	812.6	796.5	780.5	767.0
55°	818.9	809.3	799.8	790.2	780.7	767.6	750.9	734.2	717.5	700.8	687.3
57.5°	738.8	728.7	718.4	708.3	698.0	684.9	668.8	652.6	636.5	620.4	607.3
60°	687.3	676.8	666.4	656.0	645.6	632.2	616.1	600.0	583.9	567.8	554.7
62.5°	632.6	622.6	612.6	602.6	592.7	579.5	563.2	546.8	530.5	514.1	502.0
65°	554.4	544.2	534.2	524.0	513.8	500.8	485.1	469.2	453.4	437.6	425.7
67.5°	476.8	466.7	456.5	446.4	436.3	423.6	408.5	393.3	378.2	363.0	352.1
70°	424.2	414.1	403.9	393.7	383.7	371.1	356.2	341.3	326.3	311.4	302.2
72.5°	372.6	362.7	352.8	342.9	333.0	321.1	307.1	293.2	279.2	265.3	256.8
75°	295.3	286.4	277.4	268.5	259.5	248.8	236.3	223.8	211.2	198.6	192.1
77.5°	218.5	211.4	204.2	197.1	189.9	181.3	171.3	161.3	151.3	141.2	136.6
80°	174.5	167.4	160.2	153.0	145.9	138.1	129.8	121.4	113.0	104.7	102.0
82.5°	131.6	125.1	118.6	112.2	105.8	99.7	93.9	88.3	82.5	76.8	75.5
85°	73.9	68.4	63.1	57.7	52.3	48.9	47.4	46.0	44.4	43.0	42.6
87.5°	25.0	23.8	22.6	21.4	20.1	19.6	19.8	19.9	20.1	20.2	20.6
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2
92.5°	20.0	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2
95°	73.9	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2
97.5°	154.2	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6
100°	216.5	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6
102.5°	279.7	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7
105°	381.1	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0
110°	554.7	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	619.1	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6
115°	715.5	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0
117.5°	815.3	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4
120°	877.4	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5
122.5°	932.5	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6
125°	1017.4	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4
127.5°	1098.5	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6
130°	1148.3	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3
132.5°	1198.1	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6
135°	1268.9	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5
137.5°	1333.9	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5
140°	1376.5	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4
142.5°	1414.8	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3
145°	1471.1	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9
147.5°	1520.4	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7
150°	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0
152.5°	1581.5	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0
155°	1620.1	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8
157.5°	1649.9	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5
160°	1670.7	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3
162.5°	1687.3	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4
165°	1709.6	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8
167.5°	1726.1	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5
170°	1735.5	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0
172.5°	1741.7	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1
175°	1748.4	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3
177.5°	1751.5	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1771.3	1773.7	1776.2	1777.2	1777.0	1776.8	1776.5	1776.2
5°	1760.5	1763.5	1766.4	1767.6	1767.0	1766.4	1765.8	1765.2
7.5°	1738.5	1740.7	1742.8	1743.4	1742.8	1742.1	1741.5	1740.9
10°	1720.0	1721.0	1721.8	1721.8	1721.0	1720.0	1719.2	1718.3
12.5°	1693.8	1694.4	1695.1	1694.8	1693.4	1692.0	1690.7	1689.3
15°	1650.5	1650.3	1649.9	1648.5	1645.8	1643.1	1640.4	1637.7
17.5°	1596.6	1595.1	1593.6	1591.8	1589.6	1587.3	1585.2	1582.9
20°	1556.9	1555.4	1553.9	1551.8	1549.1	1546.4	1543.8	1541.1
22.5°	1517.5	1514.6	1511.7	1509.1	1506.9	1504.7	1502.4	1500.3
25°	1452.8	1448.9	1445.0	1441.4	1438.1	1434.9	1431.6	1428.3
27.5°	1382.9	1377.4	1372.0	1367.7	1364.5	1361.3	1358.1	1355.0
30°	1332.7	1325.9	1319.0	1314.2	1311.6	1308.8	1306.1	1303.5
32.5°	1284.0	1276.4	1268.9	1263.3	1260.0	1256.5	1253.2	1249.7
35°	1208.3	1199.6	1191.0	1184.6	1180.4	1176.2	1172.1	1167.9
37.5°	1129.1	1118.8	1108.4	1101.1	1097.1	1093.0	1089.0	1084.9
40°	1076.8	1065.4	1054.1	1046.6	1043.0	1039.5	1035.9	1032.3
42.5°	1025.1	1014.3	1003.4	995.3	990.1	984.8	979.6	974.3
45°	942.6	930.7	918.8	910.6	906.1	901.6	897.2	892.7
47.5°	861.2	848.9	836.5	827.9	822.9	818.0	813.0	808.1
50°	805.9	793.3	780.8	772.3	767.8	763.4	758.9	754.4
52.5°	753.5	740.0	726.5	717.6	713.1	708.6	704.1	699.6
55°	673.9	660.5	647.0	637.9	633.2	628.4	623.6	618.9
57.5°	594.2	581.1	567.9	559.3	555.0	550.8	546.6	542.3
60°	541.6	528.5	515.3	506.5	502.0	497.6	493.1	488.6
62.5°	489.8	477.6	465.5	457.1	452.6	448.2	443.7	439.2
65°	413.8	401.8	389.9	381.7	377.2	372.7	368.2	363.8
67.5°	341.1	330.2	319.3	312.0	308.5	304.9	301.4	297.7
70°	292.9	283.7	274.5	268.0	264.4	260.9	257.3	253.7
72.5°	248.2	239.7	231.1	225.7	223.3	220.9	218.5	216.1
75°	185.5	179.0	172.5	168.1	166.0	163.9	161.9	159.7
77.5°	132.0	127.4	122.9	119.8	118.2	116.7	115.1	113.6
80°	99.4	96.7	93.9	92.3	91.7	91.1	90.6	90.0
82.5°	74.3	73.0	71.8	70.9	70.6	70.3	69.9	69.6
85°	42.4	42.1	41.8	41.5	41.2	40.9	40.6	40.3
87.5°	20.8	21.1	21.4	21.5	21.4	21.4	21.4	21.3
90°	23.6	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	23.6	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	23.6	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	139.7	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	271.5	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	555.6	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333738-935

CATALOG NUMBER: S125RDIW-S1270D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	621.5	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	720.9	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	816.9	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.9	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	938.0	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1024.2	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1103.0	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1154.4	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.5	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.9	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.6	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1378.9	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.4	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.3	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.1	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1552.6	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1579.6	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1616.7	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1647.4	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1666.5	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1684.0	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1706.5	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1723.5	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1732.3	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1739.1	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1746.5	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1749.6	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)