

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333458-930

Luminaire Tested: **S125DIW-S1090D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333458-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8707.8 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42																				
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35																				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	44	38	36	34	29																				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25																				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21																				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18																				
6	61	49	41	36	56	45	38	33	38	33	28	31	27	24	24	21	19	16																				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14																				
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13																				
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	1.5
10°-20°	370.5	4.3
20°-30°	547.1	6.3
30°-40°	638.4	7.3
40°-50°	641.2	7.4
50°-60°	562.8	6.5
60°-70°	419.4	4.8
70°-80°	239.8	2.8
80°-90°	73.2	0.8
90°-100°	60.2	0.7
100°-110°	370.8	4.3
110°-120°	672.5	7.7
120°-130°	863.1	9.9
130°-140°	928.3	10.7
140°-150°	871.4	10.0
150°-160°	704.9	8.1
160°-170°	455.9	5.2
170°-180°	157.2	1.8
0°-30°	1048.8	12.0
0°-40°	1687.2	19.4
0°-60°	2891.2	33.2
0°-90°	3623.6	41.6
90°-120°	1103.5	12.7
90°-150°	3766.2	43.3
90°-180°	5084.0	58.4
0°-180°	8707.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	1	11	20	26	29	6
95°	70	64	20	25	26	89
105°	361	365	366	366	364	383
115°	678	683	685	680	672	671
125°	963	972	972	967	963	860
135°	1202	1208	1206	1204	1197	926
145°	1393	1395	1396	1396	1389	871
155°	1534	1527	1529	1532	1523	707
165°	1619	1612	1613	1619	1610	457
175°	1656	1649	1650	1658	1648	158
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	24.1	24.5	24.9	25.4	25.8	26.1	26.3	26.4	26.7	26.8	27.1
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0
92.5°	18.9	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0
95°	70.0	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0
97.5°	146.0	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7
100°	205.0	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9
102.5°	264.9	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8
105°	360.9	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0
110°	525.3	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	586.2	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5
115°	677.5	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7
117.5°	772.0	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9
120°	830.9	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8
122.5°	883.0	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8
125°	963.4	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9
127.5°	1040.2	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1
130°	1087.4	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0
132.5°	1134.5	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8
135°	1201.5	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9
137.5°	1263.1	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5
140°	1303.4	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2
142.5°	1339.7	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0
145°	1393.0	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7
147.5°	1439.7	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0
150°	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7
152.5°	1497.5	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2
155°	1534.1	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1
157.5°	1562.4	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1
160°	1582.0	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0
162.5°	1597.7	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1
165°	1618.9	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3
167.5°	1634.5	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1
170°	1643.4	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2
172.5°	1649.3	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9
175°	1655.6	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7
177.5°	1658.6	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	27.4	27.6	27.9	28.0	27.7	27.5	27.2	27.0
90°	22.3	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	22.3	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	22.3	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	45.0	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	132.2	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	257.1	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	526.1	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333458-930

CATALOG NUMBER: S125DIW-S1090D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	588.5	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	682.7	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	773.6	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	832.3	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	888.2	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	969.9	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1044.5	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1093.2	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.6	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1205.3	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.5	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1305.7	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.1	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.0	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.3	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.1	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1495.7	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1530.9	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1559.9	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1578.0	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1594.6	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1615.9	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1632.1	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1640.4	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1646.8	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1653.8	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1656.8	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)