

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333650-935

Luminaire Tested: **S125RDIW-S375D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333650-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1050U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4854.4 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	71	66	75	69	64	60	54	50	48	40	37	36	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	10
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3402	3402	3402
5°	3411	3371	3392
10°	3385	3341	3341
15°	3344	3273	3245
20°	3293	3178	3140
25°	3233	3085	3017
30°	3157	2976	2882
35°	3080	2864	2730
40°	3010	2748	2580
45°	2922	2617	2417
50°	2834	2475	2247
55°	2733	2339	2066
60°	2631	2174	1870
65°	2512	1984	1647
70°	2374	1743	1420
75°	2186	1470	1183
80°	1923	1153	993
85°	1623	941	889



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	1.0
10°-20°	138.4	2.9
20°-30°	200.8	4.1
30°-40°	228.8	4.7
40°-50°	223.0	4.6
50°-60°	187.7	3.9
60°-70°	131.6	2.7
70°-80°	67.6	1.4
80°-90°	19.5	0.4
90°-100°	42.7	0.9
100°-110°	263.1	5.4
110°-120°	477.1	9.8
120°-130°	612.4	12.6
130°-140°	658.7	13.6
140°-150°	618.2	12.7
150°-160°	500.1	10.3
160°-170°	323.4	6.7
170°-180°	111.6	2.3
0°-30°	388.7	8.0
0°-40°	617.6	12.7
0°-60°	1028.3	21.2
0°-90°	1247.1	25.7
90°-120°	782.9	16.1
90°-150°	2672.2	55.0
90°-180°	3607.0	74.3
0°-180°	4854.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	523	50
15°	500	498	490	489	485	141
25°	454	447	433	428	423	209
35°	391	381	363	352	346	245
45°	320	308	286	271	265	247
55°	243	230	208	190	184	217
65°	164	150	130	114	108	163
75°	88	75	59	50	47	93
85°	22	15	13	12	12	25
90°	1	8	14	18	21	3
95°	50	45	14	18	18	63
105°	256	259	260	259	259	271
115°	481	485	486	482	477	476
125°	684	689	690	686	684	610
135°	852	857	856	854	849	657
145°	988	990	990	991	986	618
155°	1088	1084	1085	1087	1081	501
165°	1149	1144	1144	1149	1142	324
175°	1175	1170	1170	1177	1170	112
180°	1175	1175	1175	1175	1175	



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	527.8	527.6	527.4	527.2	526.9	526.5	525.8	525.0	524.3	523.7	524.3
5°	526.1	525.7	525.4	525.0	524.6	524.0	523.0	522.0	521.1	520.0	521.0
7.5°	520.9	520.6	520.2	519.9	519.5	518.8	517.6	516.4	515.3	514.1	514.7
10°	516.1	515.8	515.6	515.3	515.1	514.3	513.1	511.8	510.6	509.4	509.6
12.5°	510.7	510.3	510.1	509.7	509.4	508.3	506.7	505.1	503.3	501.7	501.9
15°	500.2	499.6	499.1	498.6	498.1	496.9	495.0	493.2	491.3	489.5	489.4
17.5°	488.4	487.5	486.7	485.9	485.1	483.5	481.1	478.8	476.5	474.2	473.7
20°	479.1	478.2	477.3	476.5	475.5	473.7	470.9	468.0	465.2	462.4	461.9
22.5°	468.9	468.0	467.2	466.2	465.4	463.5	460.5	457.5	454.5	451.6	450.7
25°	453.7	452.3	451.0	449.6	448.3	446.0	442.7	439.5	436.2	432.9	431.8
27.5°	436.1	434.5	432.9	431.3	429.6	427.1	423.6	420.1	416.6	413.1	411.5
30°	423.4	421.7	420.0	418.4	416.6	414.0	410.3	406.6	402.9	399.1	397.1
32.5°	411.0	409.0	407.1	405.1	403.1	400.3	396.5	392.7	388.9	385.1	382.9
35°	390.7	388.7	386.5	384.4	382.3	379.2	375.2	371.3	367.3	363.3	360.8
37.5°	370.9	368.3	365.8	363.2	360.6	357.2	353.2	349.0	345.0	340.9	337.8
40°	357.0	354.3	351.6	349.0	346.3	342.9	338.6	334.4	330.1	325.9	322.5
42.5°	342.2	339.6	336.8	334.2	331.4	327.9	323.5	319.1	314.7	310.3	307.1
45°	319.9	317.4	314.8	312.2	309.7	305.9	301.1	296.3	291.4	286.5	282.9
47.5°	296.8	294.0	291.4	288.6	285.9	282.1	277.2	272.3	267.4	262.5	258.9
50°	282.1	279.2	276.3	273.4	270.4	266.5	261.4	256.4	251.3	246.3	242.6
52.5°	266.2	263.2	260.2	257.3	254.3	250.4	245.6	240.8	236.1	231.4	227.4
55°	242.7	239.9	237.0	234.3	231.4	227.6	222.6	217.6	212.7	207.7	203.7
57.5°	219.0	216.0	212.9	209.9	206.9	203.0	198.2	193.5	188.7	183.9	180.0
60°	203.7	200.6	197.5	194.4	191.3	187.4	182.6	177.9	173.1	168.3	164.5
62.5°	187.5	184.5	181.6	178.7	175.6	171.8	166.9	162.1	157.2	152.4	148.8
65°	164.4	161.4	158.3	155.3	152.3	148.4	143.8	139.1	134.4	129.8	126.2
67.5°	141.4	138.4	135.3	132.3	129.3	125.5	121.1	116.6	112.1	107.6	104.4
70°	125.7	122.8	119.8	116.8	113.7	110.0	105.6	101.2	96.8	92.3	89.5
72.5°	110.5	107.5	104.6	101.7	98.8	95.1	91.0	86.9	82.7	78.6	76.1
75°	87.6	84.9	82.2	79.6	77.0	73.8	70.0	66.3	62.6	58.9	56.9
77.5°	64.7	62.7	60.5	58.4	56.3	53.7	50.8	47.8	44.9	41.8	40.5
80°	51.7	49.6	47.5	45.4	43.2	41.0	38.5	36.0	33.5	31.0	30.2
82.5°	39.0	37.1	35.2	33.2	31.3	29.5	27.9	26.2	24.5	22.7	22.4
85°	21.9	20.3	18.7	17.1	15.5	14.5	14.0	13.6	13.2	12.7	12.7
87.5°	7.5	7.3	7.1	7.0	6.7	6.8	7.0	7.1	7.3	7.6	7.7
90°	0.9	2.4	4.0	5.5	7.1	8.5	9.9	11.2	12.6	13.9	14.9
92.5°	13.4	12.3	11.3	10.2	9.0	9.1	10.3	11.5	12.7	13.9	14.9
95°	49.6	49.1	48.5	47.9	47.4	43.3	36.0	28.7	21.3	13.9	14.9
97.5°	103.7	104.7	105.7	106.8	107.8	101.1	86.5	72.0	57.4	42.9	37.4
100°	145.4	146.0	146.5	147.1	147.7	148.4	149.2	150.0	150.8	151.5	122.7
102.5°	188.0	188.6	189.4	190.1	190.9	191.5	191.9	192.3	192.9	193.3	187.9
105°	256.0	256.8	257.5	258.3	259.1	259.5	259.5	259.5	259.5	259.5	259.5
107.5°	326.7	326.7	326.7	326.7	326.7	326.9	327.3	327.7	328.0	328.5	328.5
110°	372.7	372.7	372.7	372.7	372.7	372.9	373.2	373.7	374.0	374.4	373.8



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.9	416.4	416.8	417.2	417.8	418.1	418.4	418.5	418.8	419.0	418.3
115°	480.7	481.6	482.6	483.5	484.6	485.1	485.3	485.5	485.7	485.9	485.1
117.5°	547.8	547.7	547.7	547.6	547.6	547.9	548.6	549.4	550.1	550.9	549.8
120°	589.5	589.4	589.1	588.9	588.8	588.9	589.5	590.1	590.6	591.2	590.9
122.5°	626.5	627.2	627.9	628.6	629.4	629.9	630.2	630.4	630.7	630.9	630.6
125°	683.5	684.9	686.3	687.6	689.0	689.7	689.7	689.7	689.7	689.7	688.9
127.5°	738.0	739.1	740.0	741.0	741.9	742.4	742.3	742.2	742.0	741.9	741.5
130°	771.5	772.5	773.4	774.4	775.4	775.9	776.2	776.4	776.5	776.7	776.2
132.5°	804.9	806.1	807.2	808.3	809.4	809.8	809.3	808.9	808.5	808.1	808.0
135°	852.5	853.7	854.8	856.0	857.1	857.6	857.1	856.8	856.4	856.0	855.6
137.5°	896.2	897.2	898.2	899.2	900.3	900.6	900.3	899.9	899.5	899.1	899.2
140°	924.8	925.1	925.6	925.9	926.3	926.4	926.3	926.0	925.8	925.7	926.0
142.5°	950.5	950.8	951.1	951.2	951.5	951.7	952.0	952.3	952.5	952.8	952.9
145°	988.3	988.8	989.1	989.5	989.9	990.1	990.1	990.1	990.1	990.1	990.3
147.5°	1021.4	1021.4	1021.3	1021.2	1021.1	1021.2	1021.4	1021.7	1021.9	1022.1	1022.4
150°	1042.3	1042.0	1041.6	1041.2	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3	1042.8
152.5°	1062.6	1061.7	1060.8	1060.0	1059.1	1058.9	1059.3	1059.7	1060.1	1060.4	1060.8
155°	1088.5	1087.4	1086.2	1085.0	1083.8	1083.5	1083.8	1084.3	1084.6	1085.0	1085.5
157.5°	1108.5	1107.8	1107.2	1106.5	1105.7	1105.4	1105.4	1105.4	1105.5	1105.5	1106.2
160°	1122.5	1121.3	1120.2	1119.0	1117.8	1117.3	1117.5	1117.8	1117.9	1118.1	1118.9
162.5°	1133.6	1132.5	1131.3	1130.1	1128.9	1128.4	1128.7	1128.9	1129.0	1129.2	1130.3
165°	1148.6	1147.5	1146.2	1145.1	1143.9	1143.4	1143.7	1143.8	1144.0	1144.2	1145.4
167.5°	1159.7	1158.6	1157.4	1156.2	1154.9	1154.4	1154.6	1154.8	1155.0	1155.2	1156.6
170°	1166.0	1164.7	1163.3	1161.9	1160.5	1160.0	1160.2	1160.4	1160.5	1160.8	1162.4
172.5°	1170.2	1168.8	1167.4	1166.1	1164.8	1164.2	1164.6	1164.9	1165.3	1165.6	1167.0
175°	1174.7	1173.5	1172.3	1171.2	1170.0	1169.6	1169.8	1169.9	1170.2	1170.4	1171.9
177.5°	1176.8	1175.9	1174.9	1174.0	1173.1	1172.7	1172.9	1173.0	1173.1	1173.3	1174.4
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.8	526.8	526.8	526.8	526.8	526.8	526.8	526.8
2.5°	525.0	525.8	526.5	526.8	526.8	526.7	526.6	526.5
5°	521.9	522.7	523.6	524.0	523.8	523.6	523.4	523.2
7.5°	515.3	516.0	516.6	516.8	516.6	516.4	516.3	516.0
10°	509.9	510.1	510.4	510.4	510.1	509.9	509.6	509.4
12.5°	502.0	502.3	502.5	502.4	502.0	501.5	501.2	500.8
15°	489.2	489.1	489.0	488.6	487.8	487.1	486.3	485.4
17.5°	473.3	472.9	472.4	471.8	471.2	470.5	469.8	469.2
20°	461.5	461.1	460.6	460.0	459.2	458.4	457.6	456.8
22.5°	449.8	448.9	448.1	447.3	446.7	446.0	445.4	444.7
25°	430.7	429.5	428.3	427.3	426.3	425.3	424.4	423.4
27.5°	409.9	408.3	406.7	405.4	404.5	403.6	402.6	401.7
30°	395.0	393.0	391.0	389.6	388.7	388.0	387.2	386.4
32.5°	380.6	378.4	376.1	374.5	373.5	372.5	371.4	370.5
35°	358.2	355.6	353.0	351.1	349.9	348.7	347.4	346.2
37.5°	334.7	331.7	328.6	326.4	325.2	324.0	322.8	321.6
40°	319.2	315.8	312.5	310.2	309.2	308.2	307.0	306.0
42.5°	303.8	300.7	297.4	295.1	293.5	291.9	290.3	288.8
45°	279.4	275.9	272.3	269.9	268.6	267.3	266.0	264.6
47.5°	255.3	251.6	248.0	245.4	243.9	242.5	241.0	239.5
50°	238.8	235.1	231.4	228.9	227.6	226.3	225.0	223.6
52.5°	223.3	219.4	215.3	212.7	211.4	210.1	208.7	207.4
55°	199.8	195.8	191.8	189.1	187.7	186.2	184.9	183.5
57.5°	176.2	172.3	168.3	165.7	164.5	163.2	162.0	160.7
60°	160.6	156.6	152.7	150.2	148.8	147.5	146.2	144.8
62.5°	145.2	141.5	137.9	135.5	134.1	132.9	131.6	130.2
65°	122.6	119.1	115.5	113.1	111.8	110.5	109.2	107.8
67.5°	101.1	97.9	94.6	92.5	91.4	90.4	89.3	88.3
70°	86.9	84.1	81.4	79.5	78.4	77.3	76.3	75.2
72.5°	73.5	71.0	68.5	66.9	66.2	65.5	64.7	64.1
75°	55.0	53.0	51.1	49.9	49.2	48.6	48.0	47.4
77.5°	39.2	37.8	36.4	35.5	35.0	34.6	34.1	33.7
80°	29.4	28.7	27.9	27.4	27.2	27.0	26.9	26.7
82.5°	22.0	21.6	21.3	21.0	20.9	20.8	20.8	20.6
85°	12.6	12.5	12.4	12.3	12.2	12.1	12.1	12.0
87.5°	7.9	8.2	8.4	8.4	8.5	8.5	8.6	8.6
90°	15.8	16.9	17.8	18.6	19.2	19.7	20.3	20.9
92.5°	15.8	16.9	17.8	18.4	18.7	18.9	19.2	19.5
95°	15.8	16.9	17.8	18.3	18.3	18.3	18.3	18.3
97.5°	31.9	26.4	21.0	18.3	18.3	18.3	18.3	18.3
100°	93.8	65.0	36.2	21.4	20.6	19.8	19.0	18.3
102.5°	182.4	176.9	171.5	162.2	149.0	135.9	122.7	109.5
105°	259.5	259.5	259.5	259.4	259.2	259.0	258.8	258.6
107.5°	328.6	328.6	328.6	328.4	327.8	327.2	326.6	326.1
110°	373.2	372.7	372.1	372.0	372.1	372.3	372.5	372.7



TEST NUMBER: P333650-935

CATALOG NUMBER: S125RDIW-S375D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	417.6	416.8	416.1	415.6	415.3	415.0	414.7	414.5
115°	484.3	483.5	482.8	481.8	480.7	479.5	478.4	477.2
117.5°	548.9	547.9	546.8	546.0	545.6	545.1	544.6	544.1
120°	590.5	590.1	589.7	589.0	588.1	587.1	586.2	585.1
122.5°	630.2	629.8	629.4	628.7	627.6	626.5	625.3	624.2
125°	688.1	687.3	686.6	685.9	685.4	684.8	684.2	683.5
127.5°	741.1	740.6	740.2	739.3	737.9	736.4	734.9	733.6
130°	775.6	775.0	774.4	773.6	772.7	771.7	770.8	769.8
132.5°	807.9	807.7	807.6	807.1	806.2	805.1	804.2	803.2
135°	855.2	854.8	854.5	853.7	852.5	851.4	850.2	849.0
137.5°	899.3	899.4	899.5	899.1	898.0	897.0	896.0	895.0
140°	926.4	926.8	927.2	926.8	925.7	924.5	923.3	922.1
142.5°	953.0	953.0	953.1	952.6	951.4	950.3	949.1	948.0
145°	990.5	990.7	990.8	990.4	989.2	988.1	986.9	985.8
147.5°	1022.6	1022.9	1023.0	1022.5	1021.1	1019.7	1018.3	1016.9
150°	1043.1	1043.5	1043.9	1043.3	1041.7	1040.2	1038.6	1037.1
152.5°	1061.2	1061.6	1062.0	1061.5	1060.1	1058.7	1057.3	1055.9
155°	1086.2	1086.8	1087.4	1086.8	1085.3	1083.7	1082.2	1080.6
157.5°	1106.8	1107.4	1108.0	1107.6	1106.0	1104.5	1102.9	1101.4
160°	1119.6	1120.4	1121.2	1120.8	1119.3	1117.8	1116.2	1114.7
162.5°	1131.4	1132.5	1133.6	1133.2	1131.5	1129.9	1128.2	1126.4
165°	1146.5	1147.7	1148.8	1148.7	1147.1	1145.6	1144.0	1142.5
167.5°	1158.0	1159.3	1160.8	1160.6	1158.8	1157.1	1155.4	1153.7
170°	1163.9	1165.4	1167.0	1166.8	1165.1	1163.4	1161.7	1159.9
172.5°	1168.5	1169.8	1171.2	1171.0	1169.3	1167.5	1165.8	1164.1
175°	1173.5	1175.0	1176.6	1176.5	1174.7	1172.9	1171.2	1169.5
177.5°	1175.4	1176.6	1177.7	1177.6	1176.3	1175.1	1173.9	1172.6
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7

(END OF REPORT)