

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333470-930

Luminaire Tested: **S125DIW-S1270D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333470-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6685.2 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	53	50	48
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	25	22
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10377	10377	10377
5°	10400	10301	10367
10°	10337	10228	10287
15°	10224	10105	10148
20°	10065	9933	9950
25°	9892	9728	9719
30°	9679	9508	9461
35°	9451	9270	9140
40°	9217	9012	8884
45°	8963	8777	8603
50°	8685	8493	8238
55°	8417	8173	7944
60°	8094	7848	7569
65°	7713	7459	7207
70°	7345	7009	6770
75°	6692	6470	6248
80°	5954	5861	5720
85°	5187	5276	4987



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	2.3
10°-20°	427.9	6.4
20°-30°	631.9	9.5
30°-40°	737.3	11.0
40°-50°	740.5	11.1
50°-60°	650.0	9.7
60°-70°	484.3	7.2
70°-80°	276.9	4.1
80°-90°	82.3	1.2
90°-100°	29.6	0.4
100°-110°	182.5	2.7
110°-120°	331.0	5.0
120°-130°	424.8	6.4
130°-140°	456.9	6.8
140°-150°	428.9	6.4
150°-160°	346.9	5.2
160°-170°	224.4	3.4
170°-180°	77.4	1.2
0°-30°	1211.3	18.1
0°-40°	1948.6	29.1
0°-60°	3339.1	49.9
0°-90°	4182.7	62.6
90°-120°	543.2	8.1
90°-150°	1853.8	27.7
90°-180°	2503.0	37.4
0°-180°	6685.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1607	1607	1607	1607	1607	
5°	1604	1601	1589	1600	1599	152
15°	1529	1525	1511	1517	1518	431
25°	1388	1381	1365	1367	1364	638
35°	1199	1193	1176	1169	1159	749
45°	981	976	961	946	942	756
55°	748	743	726	715	706	667
65°	505	501	488	477	472	501
75°	268	266	259	255	250	286
85°	70	71	71	70	67	78
90°	1	5	10	13	14	5
95°	34	32	10	12	13	44
105°	178	180	180	180	179	188
115°	334	336	337	335	331	330
125°	474	478	478	476	474	423
135°	591	595	594	592	589	456
145°	686	687	687	687	684	429
155°	755	752	753	754	750	348
165°	797	793	794	797	793	225
175°	815	812	812	816	811	78
180°	815	815	815	815	815	



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1610.8	1610.1	1609.5	1608.7	1608.1	1606.6	1604.3	1602.1	1599.9	1597.6	1599.9
5°	1604.2	1603.6	1603.0	1602.5	1601.9	1600.3	1597.4	1594.6	1591.8	1588.9	1591.5
7.5°	1589.4	1588.9	1588.3	1587.7	1587.1	1585.3	1582.3	1579.2	1576.1	1573.0	1575.4
10°	1576.2	1575.6	1575.1	1574.5	1573.9	1572.1	1569.0	1565.9	1562.8	1559.7	1562.0
12.5°	1559.9	1558.9	1558.0	1556.9	1555.9	1554.0	1551.0	1548.2	1545.3	1542.4	1544.3
15°	1529.2	1528.4	1527.5	1526.6	1525.8	1523.8	1520.7	1517.6	1514.5	1511.4	1512.8
17.5°	1493.9	1492.6	1491.3	1490.1	1488.9	1486.6	1483.4	1480.2	1477.0	1473.7	1475.5
20°	1464.4	1463.8	1463.2	1462.6	1462.1	1460.0	1456.3	1452.6	1448.9	1445.3	1447.2
22.5°	1434.8	1433.9	1432.8	1431.8	1430.8	1428.6	1425.1	1421.7	1418.2	1414.8	1416.1
25°	1388.1	1386.7	1385.3	1383.9	1382.4	1379.9	1376.2	1372.6	1368.9	1365.2	1365.8
27.5°	1333.4	1332.6	1331.7	1330.9	1330.1	1327.7	1324.0	1320.1	1316.4	1312.6	1312.7
30°	1297.9	1297.0	1296.2	1295.3	1294.5	1291.9	1287.7	1283.4	1279.2	1275.0	1274.4
32.5°	1259.2	1257.9	1256.6	1255.3	1254.0	1251.5	1247.7	1243.9	1240.1	1236.3	1235.3
35°	1198.7	1197.6	1196.5	1195.3	1194.2	1191.6	1187.6	1183.7	1179.7	1175.8	1174.4
37.5°	1135.9	1134.5	1133.1	1131.6	1130.2	1127.6	1124.0	1120.2	1116.5	1112.8	1110.7
40°	1093.2	1091.8	1090.4	1088.9	1087.5	1084.8	1080.9	1076.9	1073.0	1069.0	1066.5
42.5°	1047.4	1046.3	1045.1	1043.8	1042.7	1040.1	1036.2	1032.2	1028.3	1024.3	1022.0
45°	981.3	980.2	979.1	978.0	976.8	974.5	971.2	967.8	964.4	961.0	957.6
47.5°	910.1	910.2	910.3	910.3	910.4	908.3	904.3	900.3	896.2	892.1	888.7
50°	864.4	863.6	862.7	861.9	861.0	858.8	855.5	852.1	848.7	845.3	841.6
52.5°	817.6	817.0	816.4	815.7	815.1	813.0	809.3	805.8	802.2	798.5	795.3
55°	747.5	746.6	745.8	744.9	744.0	741.7	737.7	733.8	729.8	725.9	723.3
57.5°	673.4	673.0	672.5	672.1	671.6	669.8	666.4	663.1	659.7	656.4	653.1
60°	626.6	625.6	624.4	623.3	622.2	620.0	616.9	613.8	610.7	607.6	604.8
62.5°	577.9	577.0	576.1	575.1	574.2	572.5	569.8	567.1	564.5	561.8	558.8
65°	504.7	504.1	503.5	503.0	502.4	500.5	497.4	494.3	491.2	488.1	485.6
67.5°	433.7	432.5	431.4	430.2	429.0	427.2	424.9	422.6	420.3	417.9	415.8
70°	389.0	387.6	386.1	384.7	383.4	381.3	378.8	376.3	373.7	371.2	369.5
72.5°	340.1	339.2	338.3	337.3	336.3	335.0	333.4	331.7	330.1	328.5	326.5
75°	268.2	267.7	267.1	266.5	266.0	265.0	263.6	262.1	260.7	259.3	258.4
77.5°	201.9	201.6	201.4	201.2	201.0	200.5	199.7	198.9	198.0	197.3	196.8
80°	160.1	160.1	160.1	160.1	160.1	159.9	159.3	158.7	158.2	157.6	157.4
82.5°	123.5	123.1	122.6	122.2	121.7	121.5	121.3	121.2	121.2	121.0	120.5
85°	70.0	70.2	70.4	70.8	71.0	71.2	71.2	71.2	71.2	71.2	70.9
87.5°	27.6	27.8	28.0	28.2	28.5	28.5	28.5	28.5	28.4	28.4	28.5
90°	0.6	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4
92.5°	9.3	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4
95°	34.4	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4
97.5°	71.9	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9
100°	100.9	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1
102.5°	130.4	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4
105°	177.6	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9
110°	258.5	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.5	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2
115°	333.5	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6
117.5°	380.0	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5
120°	409.0	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9
122.5°	434.6	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5
125°	474.3	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9
127.5°	512.0	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4
130°	535.2	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4
132.5°	558.4	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5
135°	591.4	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5
137.5°	621.7	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9
140°	641.6	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5
142.5°	659.4	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0
145°	685.7	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0
147.5°	708.7	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2
150°	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4
152.5°	737.1	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0
155°	755.1	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1
157.5°	769.0	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4
160°	778.7	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2
162.5°	786.4	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2
165°	796.8	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6
167.5°	804.5	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3
170°	808.9	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3
172.5°	811.8	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6
175°	815.0	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0
177.5°	816.4	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1602.1	1604.3	1606.6	1607.6	1607.4	1607.2	1607.0	1606.7
5°	1594.0	1596.6	1599.1	1600.3	1599.9	1599.7	1599.4	1599.1
7.5°	1577.8	1580.4	1582.8	1584.0	1583.7	1583.4	1583.1	1582.8
10°	1564.2	1566.5	1568.7	1569.7	1569.5	1569.1	1568.9	1568.6
12.5°	1546.1	1547.8	1549.6	1550.5	1550.5	1550.4	1550.4	1550.3
15°	1514.3	1515.6	1517.0	1517.8	1517.8	1517.8	1517.8	1517.8
17.5°	1477.2	1479.0	1480.7	1480.9	1479.5	1478.1	1476.7	1475.3
20°	1449.3	1451.2	1453.2	1453.5	1452.0	1450.7	1449.3	1447.8
22.5°	1417.4	1418.7	1420.0	1420.2	1419.2	1418.2	1417.2	1416.3
25°	1366.4	1366.9	1367.5	1367.3	1366.5	1365.6	1364.8	1363.9
27.5°	1312.8	1313.0	1313.0	1312.6	1311.8	1311.0	1310.1	1309.3
30°	1273.8	1273.3	1272.7	1272.0	1271.1	1270.3	1269.4	1268.6
32.5°	1234.3	1233.3	1232.2	1230.9	1229.5	1227.9	1226.4	1224.9
35°	1173.0	1171.6	1170.2	1168.3	1166.0	1163.8	1161.6	1159.3
37.5°	1108.6	1106.5	1104.4	1102.7	1101.4	1100.1	1098.8	1097.5
40°	1064.0	1061.4	1058.8	1057.2	1056.3	1055.5	1054.6	1053.8
42.5°	1019.7	1017.3	1015.0	1013.3	1011.9	1010.6	1009.3	1008.0
45°	954.2	950.8	947.5	945.3	944.4	943.6	942.7	941.9
47.5°	885.2	881.7	878.3	875.6	873.6	871.6	869.7	867.7
50°	838.0	834.3	830.6	827.8	825.8	823.9	821.9	819.9
52.5°	792.1	788.9	785.6	782.9	780.7	778.5	776.3	774.1
55°	720.7	718.2	715.7	713.4	711.4	709.5	707.4	705.5
57.5°	649.9	646.6	643.4	641.2	640.1	639.0	637.9	636.8
60°	601.9	599.2	596.3	593.9	591.9	590.0	588.0	586.0
62.5°	555.7	552.7	549.7	547.4	545.8	544.3	542.7	541.3
65°	483.1	480.5	477.9	476.1	475.0	473.9	472.7	471.6
67.5°	413.7	411.5	409.4	408.0	407.2	406.6	405.9	405.2
70°	367.8	366.1	364.4	363.0	361.8	360.7	359.6	358.5
72.5°	324.7	322.7	320.8	319.3	318.1	317.0	315.8	314.7
75°	257.6	256.7	255.9	254.9	253.8	252.7	251.5	250.4
77.5°	196.2	195.8	195.3	194.6	193.8	193.0	192.2	191.4
80°	157.0	156.8	156.5	156.0	155.5	154.9	154.3	153.8
82.5°	120.0	119.5	119.0	118.7	118.5	118.5	118.3	118.2
85°	70.6	70.4	70.0	69.6	69.1	68.5	67.9	67.3
87.5°	28.6	28.8	28.9	28.8	28.5	28.0	27.6	27.3
90°	11.0	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.0	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.0	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	22.2	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	65.1	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	126.5	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.9	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333470-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	289.7	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	336.0	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.7	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.7	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	437.2	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	477.4	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	514.1	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	538.1	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.3	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.7	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.1	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.1	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.4	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.7	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.2	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.5	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	767.8	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	776.7	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	784.9	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	795.4	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	803.3	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	807.4	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	810.6	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	814.1	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	815.5	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)