

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333387-930

Luminaire Tested: **S125DIW-S610D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333387-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1050U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5002.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	43	38	42	37	33	34	30	27	26	24	21	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.5
10°-20°	208.5	4.2
20°-30°	307.9	6.2
30°-40°	359.3	7.2
40°-50°	360.9	7.2
50°-60°	316.8	6.3
60°-70°	236.0	4.7
70°-80°	135.0	2.7
80°-90°	41.6	0.8
90°-100°	71.1	1.4
100°-110°	210.0	4.2
110°-120°	355.6	7.1
120°-130°	468.0	9.4
130°-140°	524.4	10.5
140°-150°	514.0	10.3
150°-160°	431.7	8.6
160°-170°	287.0	5.7
170°-180°	100.4	2.0
0°-30°	590.3	11.8
0°-40°	949.6	19.0
0°-60°	1627.2	32.5
0°-90°	2039.8	40.8
90°-120°	636.7	12.7
90°-150°	2143.1	42.8
90°-180°	2962.0	59.2
0°-180°	5002.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	1	7	13	17	20	5
95°	54	56	64	69	71	57
105°	188	193	198	202	205	201
115°	356	359	361	360	359	352
125°	520	524	525	524	523	465
135°	676	680	682	681	678	521
145°	819	822	824	824	822	512
155°	937	937	938	940	937	431
165°	1019	1017	1018	1021	1016	287
175°	1059	1056	1056	1060	1055	101
180°	1062	1062	1062	1062	1062	



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.5	13.9	14.1	14.4	14.8	14.9	15.1	15.2	15.4	15.5	15.7
90°	0.8	2.3	3.8	5.2	6.7	8.1	9.4	10.7	11.9	13.2	14.1
92.5°	20.0	21.0	22.0	23.1	24.1	25.4	27.0	28.5	30.2	31.7	32.9
95°	53.7	54.1	54.5	54.8	55.2	56.3	58.1	59.9	61.8	63.6	64.9
97.5°	89.2	89.4	89.5	89.7	89.8	91.2	93.7	96.2	98.7	101.3	102.5
100°	115.7	115.7	115.7	115.7	115.7	116.8	119.2	121.6	124.0	126.4	128.1
102.5°	144.1	144.8	145.5	146.3	147.0	148.0	149.2	150.4	151.6	152.9	154.7
105°	188.3	189.2	190.2	191.1	192.0	193.1	194.1	195.3	196.3	197.5	198.5
107.5°	237.3	238.1	239.1	240.0	240.9	241.8	242.6	243.5	244.3	245.2	245.7
110°	270.9	271.9	272.8	273.7	274.7	275.4	275.9	276.5	277.0	277.6	278.1



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	305.3	305.8	306.3	306.8	307.2	307.9	308.5	309.2	309.9	310.6	310.9
115°	356.0	356.8	357.5	358.2	359.0	359.5	359.9	360.3	360.6	361.0	360.9
117.5°	406.9	407.2	407.6	407.9	408.3	408.6	409.0	409.3	409.6	409.9	410.1
120°	438.6	439.6	440.5	441.4	442.3	442.9	443.0	443.3	443.4	443.6	443.6
122.5°	473.0	473.4	473.7	474.0	474.3	474.7	475.2	475.7	476.2	476.7	476.5
125°	519.6	520.7	521.8	522.9	524.0	524.6	524.9	525.1	525.2	525.4	525.1
127.5°	569.2	569.8	570.5	571.0	571.7	572.1	572.3	572.6	572.7	573.0	572.8
130°	598.9	599.8	600.8	601.7	602.6	603.2	603.6	604.0	604.4	604.7	604.5
132.5°	628.7	630.1	631.7	633.2	634.7	635.4	635.4	635.3	635.2	635.1	635.0
135°	675.7	676.9	677.9	679.1	680.2	680.8	681.0	681.2	681.3	681.5	681.5
137.5°	720.1	721.1	722.2	723.3	724.3	725.0	725.5	725.9	726.3	726.7	726.8
140°	748.4	749.3	750.3	751.2	752.1	752.8	753.4	754.0	754.5	755.0	755.5
142.5°	776.9	777.6	778.4	779.2	780.0	780.7	781.4	782.1	782.8	783.5	783.7
145°	818.6	819.4	820.1	820.8	821.6	822.2	822.8	823.4	823.9	824.4	824.4
147.5°	857.4	857.8	858.2	858.5	858.9	859.4	859.8	860.2	860.7	861.1	861.6
150°	883.1	883.0	882.7	882.6	882.4	882.6	883.4	884.1	884.8	885.6	885.6
152.5°	904.2	904.5	904.7	905.1	905.3	905.6	905.9	906.1	906.4	906.8	907.2
155°	936.8	936.8	936.8	936.8	936.8	936.9	937.1	937.3	937.4	937.7	938.4
157.5°	965.9	965.5	965.1	964.7	964.3	964.2	964.3	964.5	964.7	964.9	965.6
160°	983.1	982.5	981.9	981.5	980.9	980.7	980.9	981.0	981.2	981.5	982.2
162.5°	998.3	997.8	997.4	997.0	996.6	996.5	996.5	996.5	996.6	996.6	997.5
165°	1018.6	1018.2	1017.8	1017.5	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5
167.5°	1035.8	1035.0	1034.3	1033.6	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6
170°	1045.1	1044.3	1043.6	1042.8	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8
172.5°	1051.7	1050.9	1050.2	1049.5	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5
175°	1059.1	1058.3	1057.6	1056.9	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9
177.5°	1062.9	1062.3	1061.7	1061.1	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	15.9	16.1	16.2	16.3	16.2	16.1	16.0	15.9
90°	15.1	16.0	16.9	17.6	18.2	18.8	19.2	19.8
92.5°	34.2	35.4	36.6	37.3	37.7	38.2	38.6	39.0
95°	66.2	67.4	68.7	69.5	70.0	70.3	70.7	71.0
97.5°	103.7	104.9	106.2	106.8	107.0	107.3	107.5	107.7
100°	129.7	131.3	133.0	134.0	134.4	134.8	135.1	135.5
102.5°	156.5	158.2	160.0	161.2	161.7	162.2	162.7	163.2
105°	199.7	200.7	201.9	202.7	203.3	203.7	204.3	204.9
107.5°	246.3	246.9	247.4	247.7	247.6	247.6	247.5	247.5
110°	278.7	279.2	279.8	280.0	279.8	279.6	279.4	279.2



TEST NUMBER: P333387-930

CATALOG NUMBER: S125DIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	311.1	311.4	311.6	311.6	311.3	311.0	310.6	310.3
115°	360.6	360.4	360.3	360.1	359.9	359.7	359.5	359.4
117.5°	410.2	410.3	410.5	410.2	409.4	408.7	408.0	407.2
120°	443.6	443.6	443.6	443.3	442.5	441.8	441.1	440.3
122.5°	476.4	476.2	476.1	475.7	475.2	474.5	473.9	473.4
125°	524.6	524.3	523.9	523.7	523.5	523.3	523.1	522.9
127.5°	572.6	572.4	572.3	572.0	571.6	571.3	570.9	570.5
130°	604.4	604.1	604.0	603.7	603.3	603.0	602.6	602.3
132.5°	634.7	634.5	634.4	634.1	633.5	633.0	632.5	631.9
135°	681.5	681.5	681.5	681.2	680.4	679.7	679.0	678.2
137.5°	727.1	727.3	727.5	727.2	726.3	725.4	724.4	723.5
140°	755.8	756.2	756.5	756.3	755.4	754.4	753.5	752.6
142.5°	783.9	784.2	784.4	784.0	783.1	782.2	781.3	780.3
145°	824.4	824.4	824.4	824.2	823.6	823.0	822.6	822.0
147.5°	862.0	862.4	862.9	862.5	861.3	860.0	858.8	857.5
150°	885.6	885.6	885.6	885.4	885.0	884.7	884.3	883.9
152.5°	907.6	908.1	908.5	908.4	907.8	907.1	906.4	905.7
155°	939.1	939.9	940.6	940.4	939.6	938.7	937.8	936.8
157.5°	966.4	967.1	967.8	967.6	966.4	965.2	963.9	962.8
160°	982.9	983.7	984.4	984.2	983.3	982.4	981.5	980.6
162.5°	998.4	999.2	1000.1	1000.0	999.0	997.9	996.9	995.8
165°	1019.2	1019.9	1020.7	1020.5	1019.5	1018.3	1017.2	1016.1
167.5°	1034.7	1035.8	1036.9	1036.9	1035.8	1034.6	1033.5	1032.3
170°	1043.9	1045.1	1046.1	1046.0	1044.7	1043.5	1042.2	1040.9
172.5°	1050.5	1051.7	1052.7	1052.7	1051.6	1050.4	1049.3	1048.1
175°	1057.9	1059.1	1060.2	1060.1	1058.8	1057.5	1056.2	1054.9
177.5°	1061.4	1062.3	1063.1	1063.0	1062.0	1060.9	1060.0	1058.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5

(END OF REPORT)