

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333399-930

Luminaire Tested: **S125DIW-S610D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333399-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6449.9 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19
4	71	60	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.1
10°-20°	208.5	3.2
20°-30°	307.9	4.8
30°-40°	359.3	5.6
40°-50°	360.9	5.6
50°-60°	316.8	4.9
60°-70°	236.0	3.7
70°-80°	135.0	2.1
80°-90°	42.7	0.7
90°-100°	105.8	1.6
100°-110°	312.5	4.8
110°-120°	529.3	8.2
120°-130°	696.6	10.8
130°-140°	780.6	12.1
140°-150°	765.0	11.9
150°-160°	642.6	10.0
160°-170°	427.1	6.6
170°-180°	149.5	2.3
0°-30°	590.3	9.2
0°-40°	949.6	14.7
0°-60°	1627.2	25.2
0°-90°	2040.9	31.6
90°-120°	947.6	14.7
90°-150°	3189.8	49.5
90°-180°	4409.0	68.4
0°-180°	6449.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	1	11	20	26	30	6
95°	80	83	95	103	106	85
105°	280	287	294	301	305	299
115°	530	535	537	536	535	524
125°	773	780	782	780	778	692
135°	1006	1013	1014	1014	1010	775
145°	1218	1223	1227	1227	1223	761
155°	1394	1394	1396	1400	1394	642
165°	1516	1514	1515	1519	1512	428
175°	1576	1572	1571	1578	1570	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.6	14.0	14.5	14.9	15.4	15.7	16.0	16.3	16.6	16.8	17.1
90°	1.2	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0
92.5°	29.8	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0
95°	79.9	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6
97.5°	132.8	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5
100°	172.1	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6
102.5°	214.4	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2
105°	280.4	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5
107.5°	353.1	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7
110°	403.3	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.4	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7
115°	529.9	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0
117.5°	605.7	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3
120°	652.9	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3
122.5°	704.1	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2
125°	773.4	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5
127.5°	847.2	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6
130°	891.4	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8
132.5°	935.7	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0
135°	1005.8	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4
137.5°	1071.7	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9
140°	1114.0	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4
142.5°	1156.3	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4
145°	1218.5	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1
147.5°	1276.1	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4
150°	1314.4	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2
152.5°	1345.9	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3
155°	1394.4	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7
157.5°	1437.6	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3
160°	1463.2	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8
162.5°	1485.9	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7
165°	1516.1	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0
167.5°	1541.6	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4
170°	1555.4	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2
172.5°	1565.3	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0
175°	1576.4	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0
177.5°	1582.0	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	17.4	17.6	17.9	18.0	17.9	17.9	17.9	17.8
90°	22.4	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	50.8	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	98.5	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	154.3	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	193.1	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	232.8	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	297.2	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	366.6	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	414.8	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333399-930

CATALOG NUMBER: S125DIW-S610D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	463.1	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.8	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.6	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	709.1	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	781.0	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.3	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.5	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.8	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.2	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1124.9	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1166.8	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.0	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.0	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1397.7	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1438.4	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1463.0	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1486.0	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1517.0	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1540.0	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1553.8	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1563.7	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1574.8	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1579.7	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)