

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333375-930

Luminaire Tested: **S125DIW-S610D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333375-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3363.6 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	41	48	42	37	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	2.2
10°-20°	208.5	6.2
20°-30°	307.9	9.2
30°-40°	359.3	10.7
40°-50°	360.9	10.7
50°-60°	316.8	9.4
60°-70°	236.0	7.0
70°-80°	135.0	4.0
80°-90°	40.3	1.2
90°-100°	31.8	0.9
100°-110°	93.9	2.8
110°-120°	159.1	4.7
120°-130°	209.4	6.2
130°-140°	234.6	7.0
140°-150°	229.9	6.8
150°-160°	193.1	5.7
160°-170°	128.4	3.8
170°-180°	44.9	1.3
0°-30°	590.3	17.5
0°-40°	949.6	28.2
0°-60°	1627.2	48.4
0°-90°	2038.5	60.6
90°-120°	284.8	8.5
90°-150°	958.7	28.5
90°-180°	1325.0	39.4
0°-180°	3363.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	0	3	6	8	9	3
95°	24	25	28	31	32	26
105°	84	86	88	90	92	90
115°	159	161	162	161	161	157
125°	232	235	235	234	234	208
135°	302	304	305	305	303	233
145°	366	368	369	369	368	229
155°	419	419	419	421	419	193
165°	456	455	455	457	454	128
175°	474	472	472	474	472	45
180°	475	475	475	475	475	



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.5	13.6	13.7	13.9	13.9	14.0	14.0	14.0	14.0	14.1	14.2
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	6.0	6.4
92.5°	9.0	9.4	9.9	10.4	10.8	11.3	12.1	12.8	13.5	14.2	14.8
95°	24.1	24.2	24.4	24.5	24.7	25.2	26.0	26.8	27.6	28.5	29.0
97.5°	39.9	39.9	40.0	40.1	40.2	40.8	41.9	43.0	44.2	45.3	45.8
100°	51.8	51.8	51.8	51.8	51.8	52.3	53.3	54.4	55.4	56.5	57.3
102.5°	64.4	64.7	65.1	65.5	65.8	66.2	66.8	67.3	67.8	68.3	69.1
105°	84.2	84.6	85.0	85.4	85.9	86.3	86.8	87.3	87.8	88.3	88.8
107.5°	106.2	106.6	107.0	107.4	107.8	108.2	108.5	108.9	109.3	109.7	109.9
110°	121.2	121.6	122.1	122.5	122.9	123.2	123.4	123.7	123.9	124.2	124.4



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	136.6	136.8	137.0	137.2	137.5	137.7	138.0	138.4	138.6	138.9	139.1
115°	159.2	159.6	160.0	160.3	160.6	160.9	161.0	161.2	161.3	161.5	161.4
117.5°	182.1	182.1	182.3	182.5	182.6	182.8	183.0	183.0	183.2	183.4	183.4
120°	196.2	196.7	197.1	197.5	197.9	198.1	198.2	198.3	198.4	198.4	198.4
122.5°	211.6	211.7	211.9	212.1	212.1	212.4	212.5	212.8	213.0	213.2	213.1
125°	232.4	232.9	233.4	233.9	234.4	234.7	234.8	234.9	235.0	235.1	234.9
127.5°	254.6	254.9	255.2	255.4	255.8	255.9	256.0	256.1	256.2	256.3	256.2
130°	267.9	268.3	268.7	269.1	269.5	269.9	270.0	270.2	270.4	270.5	270.4
132.5°	281.2	281.8	282.6	283.2	283.9	284.2	284.2	284.1	284.1	284.1	284.0
135°	302.2	302.8	303.3	303.8	304.3	304.5	304.6	304.7	304.8	304.8	304.8
137.5°	322.0	322.5	323.0	323.5	324.0	324.3	324.5	324.7	324.8	325.1	325.1
140°	334.8	335.2	335.6	336.0	336.4	336.8	337.0	337.3	337.5	337.8	337.9
142.5°	347.5	347.8	348.2	348.5	348.9	349.2	349.5	349.8	350.2	350.5	350.6
145°	366.2	366.6	366.9	367.2	367.5	367.8	368.0	368.3	368.5	368.8	368.8
147.5°	383.5	383.7	383.8	384.0	384.3	384.4	384.6	384.8	385.0	385.2	385.4
150°	395.0	394.9	394.8	394.8	394.7	394.8	395.2	395.5	395.8	396.2	396.2
152.5°	404.5	404.6	404.7	404.8	405.0	405.0	405.2	405.4	405.4	405.6	405.8
155°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.2	419.3	419.4	419.7
157.5°	432.0	431.9	431.7	431.5	431.3	431.3	431.4	431.5	431.5	431.6	431.9
160°	439.8	439.5	439.2	439.0	438.7	438.6	438.7	438.8	438.9	439.0	439.4
162.5°	446.5	446.4	446.2	446.0	445.8	445.7	445.7	445.7	445.8	445.8	446.2
165°	455.6	455.4	455.3	455.1	454.9	454.9	455.0	455.1	455.2	455.3	455.6
167.5°	463.3	463.0	462.7	462.4	462.0	461.9	461.9	461.9	461.9	461.9	462.4
170°	467.4	467.1	466.8	466.4	466.1	465.9	465.9	465.9	465.9	465.9	466.4
172.5°	470.4	470.1	469.8	469.4	469.1	469.0	469.0	469.0	469.0	469.0	469.4
175°	473.8	473.4	473.0	472.7	472.4	472.2	472.2	472.2	472.2	472.2	472.7
177.5°	475.4	475.2	474.9	474.7	474.3	474.2	474.2	474.1	474.0	473.9	474.3
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	14.3	14.3	14.4	14.3	14.2	14.0	13.9	13.7
90°	6.8	7.2	7.6	7.9	8.2	8.4	8.6	8.9
92.5°	15.2	15.8	16.4	16.7	16.9	17.0	17.3	17.4
95°	29.6	30.2	30.7	31.1	31.3	31.5	31.6	31.8
97.5°	46.4	47.0	47.5	47.8	47.9	48.0	48.1	48.2
100°	58.0	58.8	59.5	59.9	60.1	60.3	60.4	60.6
102.5°	70.0	70.8	71.6	72.1	72.3	72.6	72.8	73.1
105°	89.3	89.8	90.3	90.7	90.9	91.2	91.4	91.6
107.5°	110.1	110.4	110.6	110.8	110.8	110.7	110.7	110.7
110°	124.7	124.9	125.1	125.2	125.1	125.1	125.0	124.9



TEST NUMBER: P333375-930

CATALOG NUMBER: S125DIW-S610D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	139.2	139.3	139.4	139.4	139.3	139.1	138.9	138.8
115°	161.3	161.3	161.2	161.1	161.0	160.9	160.9	160.8
117.5°	183.5	183.5	183.6	183.5	183.2	182.9	182.5	182.1
120°	198.4	198.4	198.4	198.3	198.0	197.6	197.3	197.0
122.5°	213.1	213.0	213.0	212.8	212.5	212.3	212.0	211.7
125°	234.7	234.6	234.4	234.2	234.2	234.1	234.0	233.9
127.5°	256.2	256.1	256.0	255.8	255.7	255.5	255.4	255.2
130°	270.4	270.3	270.2	270.0	269.9	269.7	269.5	269.4
132.5°	283.9	283.8	283.7	283.6	283.4	283.2	282.9	282.7
135°	304.8	304.8	304.8	304.7	304.4	304.0	303.7	303.4
137.5°	325.2	325.3	325.5	325.3	324.9	324.5	324.0	323.6
140°	338.1	338.3	338.4	338.3	337.9	337.5	337.0	336.6
142.5°	350.7	350.7	350.8	350.7	350.3	349.8	349.4	349.0
145°	368.8	368.8	368.8	368.7	368.4	368.2	367.9	367.7
147.5°	385.6	385.8	386.0	385.8	385.2	384.7	384.1	383.6
150°	396.2	396.2	396.2	396.1	395.9	395.7	395.6	395.4
152.5°	406.0	406.2	406.3	406.3	406.0	405.8	405.4	405.1
155°	420.0	420.4	420.7	420.7	420.3	419.9	419.5	419.1
157.5°	432.3	432.6	432.9	432.8	432.3	431.7	431.2	430.6
160°	439.7	440.0	440.3	440.3	439.9	439.4	439.0	438.6
162.5°	446.6	446.9	447.4	447.4	446.9	446.4	445.9	445.4
165°	455.9	456.2	456.6	456.5	456.0	455.5	455.0	454.5
167.5°	462.8	463.3	463.8	463.8	463.3	462.8	462.3	461.8
170°	466.9	467.4	468.0	467.9	467.3	466.8	466.2	465.6
172.5°	469.9	470.4	470.9	470.9	470.3	469.9	469.4	468.9
175°	473.2	473.8	474.3	474.2	473.6	473.0	472.5	471.9
177.5°	474.7	475.2	475.6	475.5	475.1	474.6	474.1	473.7
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8

(END OF REPORT)