

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333380-930

Luminaire Tested: **S125DIW-S610D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333380-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D770U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4541.7 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	31	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.6
10°-20°	208.5	4.6
20°-30°	307.9	6.8
30°-40°	359.3	7.9
40°-50°	360.9	7.9
50°-60°	316.8	7.0
60°-70°	236.0	5.2
70°-80°	135.0	3.0
80°-90°	41.0	0.9
90°-100°	29.6	0.7
100°-110°	182.5	4.0
110°-120°	331.0	7.3
120°-130°	424.8	9.4
130°-140°	456.9	10.1
140°-150°	428.9	9.4
150°-160°	346.9	7.6
160°-170°	224.4	4.9
170°-180°	77.4	1.7
0°-30°	590.3	13.0
0°-40°	949.6	20.9
0°-60°	1627.2	35.8
0°-90°	2039.2	44.9
90°-120°	543.2	12.0
90°-150°	1853.8	40.8
90°-180°	2503.0	55.1
0°-180°	4541.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	1	5	10	13	14	3
95°	34	32	10	12	13	44
105°	178	180	180	180	179	188
115°	334	336	337	335	331	330
125°	474	478	478	476	474	423
135°	591	595	594	592	589	456
145°	686	687	687	687	684	429
155°	755	752	753	754	750	348
165°	797	793	794	797	793	225
175°	815	812	812	816	811	78
180°	815	815	815	815	815	



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.5	13.7	13.9	14.1	14.3	14.5	14.6	14.7	14.8	14.8	14.9
90°	0.6	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4
92.5°	9.3	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4
95°	34.4	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4
97.5°	71.9	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9
100°	100.9	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1
102.5°	130.4	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4
105°	177.6	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9
110°	258.5	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.5	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2
115°	333.5	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6
117.5°	380.0	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5
120°	409.0	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9
122.5°	434.6	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5
125°	474.3	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9
127.5°	512.0	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4
130°	535.2	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4
132.5°	558.4	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5
135°	591.4	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5
137.5°	621.7	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9
140°	641.6	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5
142.5°	659.4	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0
145°	685.7	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0
147.5°	708.7	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2
150°	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4
152.5°	737.1	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0
155°	755.1	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1
157.5°	769.0	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4
160°	778.7	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2
162.5°	786.4	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2
165°	796.8	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6
167.5°	804.5	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3
170°	808.9	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3
172.5°	811.8	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6
175°	815.0	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0
177.5°	816.4	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	15.1	15.2	15.3	15.3	15.2	15.1	14.9	14.8
90°	11.0	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.0	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.0	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	22.2	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	65.1	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	126.5	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.9	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333380-930

CATALOG NUMBER: S125DIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	289.7	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	336.0	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.7	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.7	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	437.2	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	477.4	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	514.1	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	538.1	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.3	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.7	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.1	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.1	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.4	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.7	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.2	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.5	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	767.8	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	776.7	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	784.9	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	795.4	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	803.3	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	807.4	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	810.6	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	814.1	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	815.5	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)