

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333405-930

Luminaire Tested: **S125DIW-S850D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333405-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4111.1 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20								20		
RC	80					70						30								10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	111	111	111	111		105	105	105	105		93	93	93		82	82	82		72	72	72	68
1	102	97	93	90		96	92	88	85		82	79	77		72	70	69		64	62	61	57
2	93	85	78	73		87	80	75	70		72	67	63		64	60	57		56	54	51	48
3	84	75	67	61		79	71	64	58		63	58	53		56	52	48		50	47	44	40
4	77	66	58	52		73	63	55	50		56	50	45		50	45	41		45	41	38	35
5	71	59	51	44		67	56	48	43		50	44	39		45	40	36		40	36	33	30
6	66	53	45	39		62	50	43	37		45	39	34		41	36	32		36	32	29	26
7	61	48	40	34		57	46	38	33		41	35	30		37	32	28		33	29	26	23
8	56	44	36	30		53	42	34	29		38	31	27		34	29	25		31	26	23	21
9	53	40	32	27		50	38	31	26		35	29	24		31	26	23		28	24	21	19
10	49	37	29	24		46	35	28	24		32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6912	6912	6912
5°	6928	6862	6906
10°	6885	6813	6852
15°	6811	6731	6760
20°	6704	6616	6628
25°	6589	6480	6475
30°	6447	6334	6302
35°	6296	6176	6089
40°	6139	6004	5918
45°	5971	5847	5731
50°	5785	5657	5488
55°	5606	5444	5291
60°	5391	5227	5043
65°	5136	4968	4800
70°	4893	4670	4509
75°	4457	4312	4162
80°	3968	3905	3812
85°	3453	3520	3320



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.5
10°-20°	285.1	6.9
20°-30°	420.9	10.2
30°-40°	491.1	11.9
40°-50°	493.3	12.0
50°-60°	433.0	10.5
60°-70°	322.6	7.8
70°-80°	184.5	4.5
80°-90°	54.7	1.3
90°-100°	31.8	0.8
100°-110°	93.9	2.3
110°-120°	159.1	3.9
120°-130°	209.4	5.1
130°-140°	234.6	5.7
140°-150°	229.9	5.6
150°-160°	193.1	4.7
160°-170°	128.4	3.1
170°-180°	44.9	1.1
0°-30°	806.9	19.6
0°-40°	1298.0	31.6
0°-60°	2224.3	54.1
0°-90°	2786.1	67.8
90°-120°	284.8	6.9
90°-150°	958.7	23.3
90°-180°	1325.0	32.2
0°-180°	4111.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1069	1066	1058	1066	1065	101
15°	1019	1016	1007	1011	1011	287
25°	925	920	909	911	909	425
35°	798	795	783	779	772	499
45°	654	650	640	630	628	504
55°	498	495	484	476	470	444
65°	336	334	325	318	314	333
75°	179	177	173	170	167	190
85°	47	47	48	46	45	52
90°	0	3	6	8	9	4
95°	24	25	28	31	32	26
105°	84	86	88	90	92	90
115°	159	161	162	161	161	157
125°	232	235	235	234	234	208
135°	302	304	305	305	303	233
145°	366	368	369	369	368	229
155°	419	419	419	421	419	193
165°	456	455	455	457	454	128
175°	474	472	472	474	472	45
180°	475	475	475	475	475	



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1073.0	1072.5	1072.1	1071.6	1071.1	1070.2	1068.7	1067.2	1065.7	1064.2	1065.7
5°	1068.6	1068.2	1067.8	1067.5	1067.1	1065.9	1064.0	1062.2	1060.3	1058.4	1060.1
7.5°	1058.7	1058.4	1058.0	1057.6	1057.3	1056.1	1053.9	1051.9	1049.9	1047.7	1049.4
10°	1049.9	1049.6	1049.2	1048.8	1048.5	1047.3	1045.1	1043.1	1041.1	1038.9	1040.5
12.5°	1039.1	1038.4	1037.8	1037.1	1036.4	1035.1	1033.2	1031.3	1029.3	1027.4	1028.7
15°	1018.6	1018.1	1017.5	1016.9	1016.4	1015.0	1013.0	1010.9	1008.9	1006.7	1007.7
17.5°	995.1	994.3	993.4	992.6	991.8	990.3	988.1	986.0	983.8	981.7	982.8
20°	975.4	975.1	974.7	974.3	974.0	972.5	970.0	967.6	965.2	962.7	964.1
22.5°	955.8	955.1	954.5	953.7	953.1	951.6	949.3	947.0	944.7	942.4	943.3
25°	924.6	923.7	922.8	921.8	920.9	919.2	916.7	914.3	911.8	909.4	909.8
27.5°	888.2	887.7	887.1	886.6	886.0	884.4	881.9	879.4	876.9	874.3	874.4
30°	864.5	864.0	863.4	862.8	862.3	860.5	857.8	854.9	852.1	849.3	848.9
32.5°	838.8	837.9	837.1	836.2	835.4	833.6	831.1	828.6	826.1	823.5	822.9
35°	798.5	797.7	797.0	796.2	795.5	793.8	791.2	788.5	785.9	783.3	782.3
37.5°	756.7	755.7	754.7	753.8	752.8	751.1	748.7	746.2	743.7	741.3	739.8
40°	728.2	727.2	726.4	725.4	724.4	722.7	720.0	717.4	714.8	712.1	710.5
42.5°	697.7	696.9	696.1	695.4	694.6	692.8	690.2	687.5	684.9	682.3	680.8
45°	653.7	652.9	652.2	651.4	650.7	649.1	646.9	644.7	642.4	640.2	637.9
47.5°	606.3	606.3	606.3	606.3	606.4	605.1	602.3	599.7	597.0	594.3	591.9
50°	575.8	575.2	574.6	574.1	573.6	572.1	569.9	567.6	565.3	563.0	560.6
52.5°	544.6	544.2	543.8	543.4	543.0	541.5	539.2	536.7	534.3	531.9	529.8
55°	497.9	497.3	496.8	496.2	495.6	494.0	491.4	488.8	486.1	483.5	481.8
57.5°	448.6	448.3	448.0	447.7	447.4	446.1	443.9	441.7	439.4	437.2	435.0
60°	417.4	416.7	416.0	415.2	414.4	413.0	410.9	408.9	406.8	404.7	402.8
62.5°	384.9	384.3	383.8	383.1	382.5	381.3	379.6	377.8	376.0	374.2	372.3
65°	336.1	335.7	335.4	335.0	334.7	333.5	331.3	329.3	327.2	325.1	323.4
67.5°	288.9	288.1	287.3	286.5	285.8	284.5	283.1	281.5	280.0	278.4	277.0
70°	259.1	258.1	257.2	256.2	255.4	254.0	252.3	250.6	248.9	247.3	246.1
72.5°	226.6	225.9	225.3	224.7	224.0	223.1	222.1	220.9	219.9	218.8	217.5
75°	178.6	178.3	177.9	177.6	177.2	176.5	175.5	174.6	173.7	172.8	172.2
77.5°	134.4	134.3	134.2	134.0	133.9	133.5	133.0	132.5	131.9	131.4	131.1
80°	106.7	106.7	106.7	106.7	106.7	106.5	106.2	105.7	105.3	105.0	104.8
82.5°	82.3	82.0	81.7	81.4	81.1	80.9	80.8	80.8	80.7	80.6	80.3
85°	46.6	46.8	47.0	47.1	47.3	47.5	47.5	47.5	47.5	47.5	47.2
87.5°	18.3	18.5	18.6	18.8	18.9	18.9	18.9	18.8	18.8	18.8	18.9
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	6.0	6.4
92.5°	9.0	9.4	9.9	10.4	10.8	11.3	12.1	12.8	13.5	14.2	14.8
95°	24.1	24.2	24.4	24.5	24.7	25.2	26.0	26.8	27.6	28.5	29.0
97.5°	39.9	39.9	40.0	40.1	40.2	40.8	41.9	43.0	44.2	45.3	45.8
100°	51.8	51.8	51.8	51.8	51.8	52.3	53.3	54.4	55.4	56.5	57.3
102.5°	64.4	64.7	65.1	65.5	65.8	66.2	66.8	67.3	67.8	68.3	69.1
105°	84.2	84.6	85.0	85.4	85.9	86.3	86.8	87.3	87.8	88.3	88.8
107.5°	106.2	106.6	107.0	107.4	107.8	108.2	108.5	108.9	109.3	109.7	109.9
110°	121.2	121.6	122.1	122.5	122.9	123.2	123.4	123.7	123.9	124.2	124.4



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	136.6	136.8	137.0	137.2	137.5	137.7	138.0	138.4	138.6	138.9	139.1
115°	159.2	159.6	160.0	160.3	160.6	160.9	161.0	161.2	161.3	161.5	161.4
117.5°	182.1	182.1	182.3	182.5	182.6	182.8	183.0	183.0	183.2	183.4	183.4
120°	196.2	196.7	197.1	197.5	197.9	198.1	198.2	198.3	198.4	198.4	198.4
122.5°	211.6	211.7	211.9	212.1	212.1	212.4	212.5	212.8	213.0	213.2	213.1
125°	232.4	232.9	233.4	233.9	234.4	234.7	234.8	234.9	235.0	235.1	234.9
127.5°	254.6	254.9	255.2	255.4	255.8	255.9	256.0	256.1	256.2	256.3	256.2
130°	267.9	268.3	268.7	269.1	269.5	269.9	270.0	270.2	270.4	270.5	270.4
132.5°	281.2	281.8	282.6	283.2	283.9	284.2	284.2	284.1	284.1	284.1	284.0
135°	302.2	302.8	303.3	303.8	304.3	304.5	304.6	304.7	304.8	304.8	304.8
137.5°	322.0	322.5	323.0	323.5	324.0	324.3	324.5	324.7	324.8	325.1	325.1
140°	334.8	335.2	335.6	336.0	336.4	336.8	337.0	337.3	337.5	337.8	337.9
142.5°	347.5	347.8	348.2	348.5	348.9	349.2	349.5	349.8	350.2	350.5	350.6
145°	366.2	366.6	366.9	367.2	367.5	367.8	368.0	368.3	368.5	368.8	368.8
147.5°	383.5	383.7	383.8	384.0	384.3	384.4	384.6	384.8	385.0	385.2	385.4
150°	395.0	394.9	394.8	394.8	394.7	394.8	395.2	395.5	395.8	396.2	396.2
152.5°	404.5	404.6	404.7	404.8	405.0	405.0	405.2	405.4	405.4	405.6	405.8
155°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.2	419.3	419.4	419.7
157.5°	432.0	431.9	431.7	431.5	431.3	431.3	431.4	431.5	431.5	431.6	431.9
160°	439.8	439.5	439.2	439.0	438.7	438.6	438.7	438.8	438.9	439.0	439.4
162.5°	446.5	446.4	446.2	446.0	445.8	445.7	445.7	445.7	445.8	445.8	446.2
165°	455.6	455.4	455.3	455.1	454.9	454.9	455.0	455.1	455.2	455.3	455.6
167.5°	463.3	463.0	462.7	462.4	462.0	461.9	461.9	461.9	461.9	461.9	462.4
170°	467.4	467.1	466.8	466.4	466.1	465.9	465.9	465.9	465.9	465.9	466.4
172.5°	470.4	470.1	469.8	469.4	469.1	469.0	469.0	469.0	469.0	469.0	469.4
175°	473.8	473.4	473.0	472.7	472.4	472.2	472.2	472.2	472.2	472.2	472.7
177.5°	475.4	475.2	474.9	474.7	474.3	474.2	474.2	474.1	474.0	473.9	474.3
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1067.2	1068.7	1070.2	1070.9	1070.7	1070.6	1070.4	1070.2
5°	1061.8	1063.5	1065.2	1065.9	1065.8	1065.6	1065.4	1065.2
7.5°	1051.1	1052.7	1054.3	1055.1	1054.9	1054.8	1054.5	1054.3
10°	1042.0	1043.5	1045.0	1045.6	1045.5	1045.2	1045.1	1044.9
12.5°	1029.8	1031.0	1032.3	1032.8	1032.8	1032.7	1032.7	1032.7
15°	1008.7	1009.6	1010.6	1011.0	1011.0	1011.0	1011.0	1011.0
17.5°	984.1	985.2	986.3	986.5	985.5	984.6	983.7	982.8
20°	965.4	966.7	968.0	968.2	967.3	966.3	965.4	964.4
22.5°	944.1	945.0	945.9	946.0	945.3	944.7	944.0	943.5
25°	910.1	910.5	910.9	910.8	910.3	909.7	909.1	908.6
27.5°	874.5	874.6	874.7	874.4	873.8	873.3	872.7	872.1
30°	848.6	848.2	847.7	847.3	846.8	846.2	845.6	845.1
32.5°	822.1	821.5	820.8	819.9	819.0	817.9	816.9	816.0
35°	781.4	780.4	779.5	778.3	776.7	775.3	773.7	772.3
37.5°	738.4	737.0	735.6	734.5	733.7	732.8	732.0	731.1
40°	708.7	707.0	705.3	704.2	703.6	703.1	702.5	702.0
42.5°	679.2	677.7	676.1	674.9	674.1	673.2	672.3	671.5
45°	635.6	633.3	631.1	629.7	629.2	628.6	628.0	627.5
47.5°	589.6	587.3	585.1	583.3	582.0	580.7	579.3	578.0
50°	558.2	555.7	553.3	551.4	550.1	548.8	547.5	546.2
52.5°	527.7	525.5	523.3	521.5	520.1	518.6	517.1	515.7
55°	480.1	478.4	476.7	475.2	473.9	472.5	471.2	469.9
57.5°	432.9	430.7	428.5	427.1	426.3	425.7	424.9	424.2
60°	401.0	399.1	397.2	395.6	394.3	393.0	391.7	390.4
62.5°	370.2	368.2	366.2	364.6	363.6	362.6	361.6	360.5
65°	321.8	320.1	318.4	317.2	316.4	315.7	314.9	314.1
67.5°	275.6	274.1	272.7	271.7	271.3	270.8	270.4	269.9
70°	245.0	243.9	242.7	241.8	241.0	240.3	239.5	238.8
72.5°	216.2	215.0	213.7	212.6	211.9	211.2	210.4	209.6
75°	171.6	171.0	170.5	169.8	169.1	168.3	167.5	166.8
77.5°	130.8	130.4	130.0	129.6	129.1	128.6	128.1	127.5
80°	104.6	104.4	104.3	104.0	103.6	103.2	102.8	102.5
82.5°	79.9	79.6	79.2	79.1	79.0	78.9	78.8	78.8
85°	47.0	46.9	46.6	46.4	46.0	45.7	45.2	44.8
87.5°	19.0	19.1	19.2	19.1	18.8	18.5	18.3	18.0
90°	6.8	7.2	7.6	7.9	8.2	8.4	8.6	8.9
92.5°	15.2	15.8	16.4	16.7	16.9	17.0	17.3	17.4
95°	29.6	30.2	30.7	31.1	31.3	31.5	31.6	31.8
97.5°	46.4	47.0	47.5	47.8	47.9	48.0	48.1	48.2
100°	58.0	58.8	59.5	59.9	60.1	60.3	60.4	60.6
102.5°	70.0	70.8	71.6	72.1	72.3	72.6	72.8	73.1
105°	89.3	89.8	90.3	90.7	90.9	91.2	91.4	91.6
107.5°	110.1	110.4	110.6	110.8	110.8	110.7	110.7	110.7
110°	124.7	124.9	125.1	125.2	125.1	125.1	125.0	124.9



TEST NUMBER: P333405-930

CATALOG NUMBER: S125DIW-S850D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	139.2	139.3	139.4	139.4	139.3	139.1	138.9	138.8
115°	161.3	161.3	161.2	161.1	161.0	160.9	160.9	160.8
117.5°	183.5	183.5	183.6	183.5	183.2	182.9	182.5	182.1
120°	198.4	198.4	198.4	198.3	198.0	197.6	197.3	197.0
122.5°	213.1	213.0	213.0	212.8	212.5	212.3	212.0	211.7
125°	234.7	234.6	234.4	234.2	234.2	234.1	234.0	233.9
127.5°	256.2	256.1	256.0	255.8	255.7	255.5	255.4	255.2
130°	270.4	270.3	270.2	270.0	269.9	269.7	269.5	269.4
132.5°	283.9	283.8	283.7	283.6	283.4	283.2	282.9	282.7
135°	304.8	304.8	304.8	304.7	304.4	304.0	303.7	303.4
137.5°	325.2	325.3	325.5	325.3	324.9	324.5	324.0	323.6
140°	338.1	338.3	338.4	338.3	337.9	337.5	337.0	336.6
142.5°	350.7	350.7	350.8	350.7	350.3	349.8	349.4	349.0
145°	368.8	368.8	368.8	368.7	368.4	368.2	367.9	367.7
147.5°	385.6	385.8	386.0	385.8	385.2	384.7	384.1	383.6
150°	396.2	396.2	396.2	396.1	395.9	395.7	395.6	395.4
152.5°	406.0	406.2	406.3	406.3	406.0	405.8	405.4	405.1
155°	420.0	420.4	420.7	420.7	420.3	419.9	419.5	419.1
157.5°	432.3	432.6	432.9	432.8	432.3	431.7	431.2	430.6
160°	439.7	440.0	440.3	440.3	439.9	439.4	439.0	438.6
162.5°	446.6	446.9	447.4	447.4	446.9	446.4	445.9	445.4
165°	455.9	456.2	456.6	456.5	456.0	455.5	455.0	454.5
167.5°	462.8	463.3	463.8	463.8	463.3	462.8	462.3	461.8
170°	466.9	467.4	468.0	467.9	467.3	466.8	466.2	465.6
172.5°	469.9	470.4	470.9	470.9	470.3	469.9	469.4	468.9
175°	473.2	473.8	474.3	474.2	473.6	473.0	472.5	471.9
177.5°	474.7	475.2	475.6	475.5	475.1	474.6	474.1	473.7
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8

(END OF REPORT)