

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333716-930

Luminaire Tested: **S125RDIW-S1090D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333716-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1560U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8560.6 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8657	8657	8657	8657
5°	9961	8669	7656	8669
10°	11425	8625	6755	8625
15°	12341	8536	6005	8536
20°	13608	8434	5544	8434
25°	15748	8298	5144	8298
30°	17137	8154	4883	8154
35°	14456	7987	4642	7987
40°	10095	7687	4435	7687
45°	7489	7283	4232	7283
50°	5971	6861	4058	6861
55°	5068	6339	3904	6339
60°	4379	5871	3653	5871
65°	3903	5365	3145	5365
70°	3429	4913	2868	4913
75°	2967	4257	2692	4257
80°	2250	3582	2250	3582
85°	1875	2816	2119	2816



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.5	1.5
10°-20°	376.7	4.4
20°-30°	597.3	7.0
30°-40°	720.3	8.4
40°-50°	643.2	7.5
50°-60°	493.3	5.8
60°-70°	320.6	3.7
70°-80°	155.9	1.8
80°-90°	40.6	0.5
90°-100°	60.2	0.7
100°-110°	370.8	4.3
110°-120°	672.5	7.9
120°-130°	863.1	10.1
130°-140°	928.3	10.8
140°-150°	871.4	10.2
150°-160°	704.9	8.2
160°-170°	455.9	5.3
170°-180°	157.2	1.8
0°-30°	1102.6	12.9
0°-40°	1822.8	21.3
0°-60°	2959.4	34.6
0°-90°	3476.4	40.6
90°-120°	1103.5	12.9
90°-150°	3766.2	44.0
90°-180°	5084.0	59.4
0°-180°	8560.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1340	1340	1340	1340	1340	
5°	1536	1337	1181	1337	1536	154
15°	1846	1277	898	1277	1846	529
25°	2210	1164	722	1164	2210	1015
35°	1834	1013	589	1013	1834	1108
45°	820	797	463	797	820	654
55°	450	563	347	563	450	408
65°	255	351	206	351	255	254
75°	119	171	108	171	119	127
85°	25	38	29	38	25	30
90°	29	1	29	1	29	14
95°	26	70	26	70	26	21
105°	364	361	364	361	364	330
115°	672	678	672	678	672	668
125°	963	963	963	963	963	857
135°	1197	1202	1197	1202	1197	923
145°	1389	1393	1389	1393	1389	868
155°	1523	1534	1523	1534	1523	702
165°	1610	1619	1610	1619	1610	454
175°	1648	1656	1648	1656	1648	157
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1410.1	1409.2	1411.0	1406.1	1406.6	1399.1	1399.1	1393.3	1385.8	1380.1	1377.4
5°	1536.4	1537.5	1535.3	1527.1	1521.5	1513.3	1503.9	1487.4	1473.7	1460.4	1450.0
7.5°	1666.5	1667.2	1659.9	1657.4	1643.6	1633.5	1612.7	1590.2	1570.3	1545.0	1525.6
10°	1742.2	1741.6	1733.9	1727.9	1715.8	1700.4	1680.0	1653.6	1628.8	1601.3	1574.9
12.5°	1786.2	1784.8	1782.3	1775.0	1763.7	1750.1	1732.8	1706.8	1676.3	1646.3	1615.4
15°	1845.7	1841.8	1834.7	1825.3	1809.3	1793.3	1774.1	1751.0	1721.8	1687.7	1659.1
17.5°	1919.1	1919.3	1908.3	1895.2	1873.6	1845.4	1815.7	1778.4	1738.8	1701.3	1670.8
20°	1979.9	1978.2	1967.2	1942.0	1917.2	1882.0	1847.9	1802.1	1753.7	1704.8	1666.8
22.5°	2067.1	2062.8	2051.3	2018.1	1979.7	1934.4	1882.2	1826.4	1767.8	1712.2	1662.4
25°	2210.0	2206.6	2184.0	2145.5	2091.7	2021.7	1953.5	1877.0	1792.8	1719.6	1659.1
27.5°	2307.6	2304.0	2287.3	2255.3	2205.5	2132.0	2039.6	1937.4	1832.3	1731.6	1644.4
30°	2298.0	2306.2	2304.0	2289.2	2251.8	2185.7	2100.5	1985.4	1860.5	1742.2	1638.2
32.5°	2159.7	2167.1	2186.5	2215.7	2217.9	2191.4	2127.7	2021.5	1892.2	1757.6	1633.4
35°	1833.5	1843.5	1880.9	1939.8	2016.8	2081.1	2094.3	2037.1	1921.0	1776.3	1626.1
37.5°	1409.6	1463.7	1495.3	1557.2	1673.6	1792.0	1905.9	1947.9	1898.4	1768.6	1614.3
40°	1197.4	1210.6	1266.7	1336.6	1434.6	1557.9	1720.2	1837.4	1841.3	1751.0	1595.8
42.5°	1024.8	1041.5	1080.1	1135.9	1219.8	1343.0	1510.7	1665.2	1736.9	1702.6	1571.6
45°	819.9	832.6	860.6	903.6	967.9	1069.8	1213.9	1392.8	1534.7	1590.3	1506.7
47.5°	673.5	680.4	704.8	737.5	785.1	859.3	970.9	1126.2	1296.5	1415.8	1404.1
50°	594.3	602.0	620.7	645.5	685.7	748.4	837.6	966.9	1142.4	1288.2	1317.4
52.5°	532.6	539.1	550.7	574.1	607.3	655.5	727.5	844.5	1002.4	1157.5	1224.9
55°	450.1	454.5	463.9	477.1	503.5	538.2	600.4	681.3	808.9	965.2	1064.2
57.5°	382.1	384.3	390.3	402.5	420.8	446.1	491.0	559.5	651.1	791.8	901.2
60°	339.0	341.2	348.9	357.1	371.5	394.5	429.7	477.6	565.7	681.8	792.4
62.5°	304.6	306.0	309.2	317.5	330.0	347.9	375.6	414.7	484.7	586.7	691.1
65°	255.4	255.8	257.0	263.6	271.3	284.5	302.6	330.2	383.0	460.1	552.4
67.5°	208.0	208.8	212.6	214.9	223.0	229.9	240.6	261.6	298.8	350.7	422.7
70°	181.6	181.1	184.9	187.7	190.4	198.7	205.8	222.9	246.0	285.6	345.6
72.5°	156.9	155.5	157.2	158.2	161.8	167.4	174.6	185.0	202.8	230.2	276.1
75°	118.9	119.4	119.4	120.5	123.3	125.5	127.7	133.1	143.1	161.3	186.0
77.5°	83.4	82.5	84.9	85.2	86.8	89.3	91.2	93.4	97.4	104.8	117.6
80°	60.5	60.5	61.1	62.7	62.2	63.3	66.0	68.2	73.2	77.6	82.0
82.5°	46.5	46.0	46.6	46.9	46.8	47.9	48.8	49.3	51.2	53.4	56.4
85°	25.3	25.3	25.8	25.8	26.4	26.4	27.0	27.0	27.0	27.5	28.0
87.5°	15.6	15.0	14.3	14.2	14.5	15.2	14.4	13.7	13.5	13.2	13.2
90°	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3	21.0	19.6	17.7
92.5°	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3	21.0	19.6	17.9
95°	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3	21.0	19.6	30.0
97.5°	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0	52.7	60.4	80.9
100°	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2	172.9	213.5	212.5
102.5°	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1	264.8	272.5	271.8
105°	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1	463.0	462.9	462.4
110°	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1	526.9	527.7	527.2



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5	589.5	590.6	590.3
115°	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7	683.7	684.9	684.6
117.5°	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6	774.9	776.4	775.3
120°	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3	832.8	833.3	832.5
122.5°	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2	888.8	889.3	888.9
125°	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9	970.9	972.0	972.0
127.5°	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5	1045.1	1045.7	1045.9
130°	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2	1094.0	1094.8	1094.5
132.5°	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6	1138.8	1139.0	1139.5
135°	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3	1205.9	1206.5	1207.0
137.5°	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5	1267.5	1267.3	1267.8
140°	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7	1305.2	1304.6	1304.9
142.5°	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1	1343.0	1343.0	1342.6
145°	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0	1395.7	1395.5	1395.5
147.5°	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3	1441.0	1440.6	1440.3
150°	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1	1469.7	1469.1	1468.5
152.5°	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7	1495.2	1494.6	1494.1
155°	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9	1530.1	1529.3	1528.7
157.5°	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9	1559.1	1558.2	1558.1
160°	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0	1577.0	1575.9	1575.6
162.5°	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6	1593.1	1591.5	1591.3
165°	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9	1614.3	1612.7	1612.4
167.5°	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1	1630.1	1628.2	1627.9
170°	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4	1638.2	1636.0	1635.7
172.5°	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8	1644.9	1642.9	1642.4
175°	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8	1651.7	1649.5	1649.3
177.5°	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8	1655.2	1653.7	1653.4
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1377.4	1374.4	1368.6	1363.3	1356.7	1351.0	1347.1	1342.2	1336.1	1328.6	1322.4
5°	1438.4	1426.3	1410.4	1396.6	1379.0	1365.2	1351.0	1337.2	1323.4	1305.8	1290.4
7.5°	1506.0	1481.0	1456.7	1426.1	1398.4	1373.6	1349.8	1325.8	1302.2	1277.2	1253.1
10°	1547.4	1517.1	1483.5	1445.0	1409.8	1376.2	1345.4	1315.2	1283.3	1255.2	1224.9
12.5°	1586.2	1547.0	1508.6	1460.0	1417.7	1376.7	1337.5	1299.8	1265.7	1229.2	1196.8
15°	1621.1	1582.6	1539.7	1480.3	1421.4	1371.8	1325.6	1276.7	1234.3	1193.5	1157.2
17.5°	1634.7	1594.2	1544.4	1487.3	1422.9	1360.7	1301.1	1247.4	1197.5	1150.1	1109.2
20°	1629.4	1590.3	1539.1	1484.7	1415.8	1351.0	1286.5	1227.1	1171.6	1121.4	1078.0
22.5°	1616.6	1576.2	1526.8	1469.3	1403.9	1335.1	1266.3	1202.9	1144.7	1092.8	1045.5
25°	1597.5	1542.5	1491.8	1435.7	1373.5	1305.3	1234.3	1164.4	1102.2	1049.4	997.7
27.5°	1577.5	1508.9	1444.5	1388.7	1323.0	1262.1	1193.7	1122.0	1056.6	1002.8	949.7
30°	1559.5	1482.5	1411.4	1348.2	1286.0	1228.2	1163.3	1093.4	1026.3	970.7	916.8
32.5°	1537.0	1455.1	1377.1	1304.2	1244.1	1186.8	1128.0	1061.3	995.9	938.6	883.8
35°	1508.9	1404.4	1319.6	1241.9	1175.4	1119.8	1067.0	1013.1	947.6	888.2	834.8
37.5°	1471.9	1353.2	1255.2	1170.7	1100.4	1044.6	1002.9	953.7	893.9	837.0	787.4
40°	1449.4	1316.3	1208.9	1125.4	1051.6	992.7	953.7	911.8	857.4	804.0	754.4
42.5°	1419.5	1282.4	1162.3	1075.1	1000.9	944.3	904.7	868.2	822.6	772.3	719.2
45°	1360.8	1216.7	1090.6	997.1	922.3	866.7	829.8	797.4	762.7	716.5	670.3
47.5°	1284.4	1148.1	1016.3	914.1	840.8	789.2	753.4	727.8	703.0	663.7	618.8
50°	1223.3	1091.8	963.0	864.0	785.8	736.8	703.3	682.9	660.3	624.6	587.2
52.5°	1151.0	1033.6	907.5	806.2	732.5	686.6	654.4	634.1	615.5	586.3	550.6
55°	1037.3	934.4	818.8	726.9	659.3	613.0	582.2	563.0	552.0	527.2	499.1
57.5°	906.0	832.3	730.3	641.7	581.9	536.2	513.6	497.3	484.8	467.3	447.5
60°	814.4	762.7	671.3	587.2	532.1	488.6	468.3	454.5	443.0	428.1	412.7
62.5°	721.5	683.9	604.5	532.1	481.5	445.1	426.0	413.6	400.3	390.3	375.3
65°	597.0	563.5	508.4	451.8	405.0	375.9	362.1	351.1	342.8	331.8	321.4
67.5°	464.5	450.8	412.8	373.7	340.1	314.2	302.3	294.6	284.7	278.1	270.9
70°	383.0	376.4	349.4	323.6	292.2	274.6	263.6	260.2	248.2	241.6	236.6
72.5°	310.8	307.7	292.2	274.3	252.2	236.8	226.6	222.9	215.2	209.9	206.7
75°	213.0	214.1	211.3	199.7	191.5	181.6	172.8	170.6	165.1	160.7	157.9
77.5°	134.7	140.3	140.6	140.0	136.7	130.6	127.0	125.4	119.9	118.3	117.6
80°	92.5	98.5	104.0	103.5	102.3	100.7	97.9	96.3	93.5	91.9	90.8
82.5°	61.6	67.3	71.8	74.8	74.6	73.0	71.1	70.4	69.8	68.6	68.3
85°	29.2	30.2	31.9	35.8	38.5	39.1	38.5	38.0	36.3	36.9	37.4
87.5°	13.3	12.9	13.0	12.6	11.7	13.5	14.3	14.3	13.9	13.5	13.0
90°	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9	17.4	15.8	14.3
95°	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0	69.1	68.3	67.5
97.5°	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0	147.5	149.0	150.5
100°	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0	205.8	206.6	207.4
102.5°	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9	265.9	266.9	268.0
105°	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9	361.9	363.1	364.1
107.5°	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5	460.5	460.5	460.5
110°	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3





TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2	586.9	587.5	588.2
115°	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5	678.8	680.2	681.6
117.5°	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0	771.9	771.8	771.8
120°	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9	830.6	830.4	830.1
122.5°	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0	883.9	885.0	886.1
125°	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4	965.3	967.3	969.1
127.5°	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2	1041.6	1043.0	1044.4
130°	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4	1088.8	1090.1	1091.5
132.5°	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5	1136.1	1137.7	1139.3
135°	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5	1203.1	1204.8	1206.5
137.5°	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1	1264.5	1266.0	1267.4
140°	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4	1304.0	1304.5	1305.0
142.5°	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7	1340.0	1340.4	1340.7
145°	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0	1393.5	1394.1	1394.7
147.5°	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7	1439.5	1439.4	1439.3
150°	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1468.5	1468.0	1467.5
152.5°	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5	1496.4	1495.2	1494.0
155°	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1	1532.5	1530.9	1529.3
157.5°	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4	1561.4	1560.4	1559.4
160°	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0	1580.4	1578.7	1577.1
162.5°	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7	1596.1	1594.5	1592.8
165°	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9	1617.2	1615.5	1613.9
167.5°	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5	1632.9	1631.2	1629.5
170°	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4	1641.4	1639.6	1637.6
172.5°	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3	1647.4	1645.4	1643.6
175°	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6	1654.0	1652.4	1650.7
177.5°	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6	1657.3	1656.0	1654.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1318.0	1311.9	1307.5	1298.7	1292.5	1289.9	1285.0	1283.7	1288.5	1285.0	1284.6
5°	1278.9	1262.9	1250.3	1237.5	1223.8	1215.0	1201.8	1199.6	1196.3	1191.3	1190.3
7.5°	1231.8	1211.0	1194.7	1173.9	1155.7	1141.1	1124.5	1116.7	1112.5	1106.0	1097.5
10°	1200.1	1175.4	1153.4	1132.5	1109.9	1091.8	1075.2	1062.6	1054.3	1046.6	1043.3
12.5°	1168.9	1143.7	1115.5	1090.2	1065.0	1044.6	1026.4	1018.1	1009.0	1000.0	992.3
15°	1120.4	1086.8	1056.0	1026.8	1005.3	983.3	965.7	953.7	939.9	936.0	921.2
17.5°	1068.9	1035.9	999.9	969.1	944.3	920.1	900.7	887.0	876.6	862.4	855.6
20°	1036.7	997.7	962.5	934.4	906.9	878.2	858.4	846.9	837.0	825.4	819.9
22.5°	1002.4	964.2	928.1	895.2	867.2	839.1	825.0	813.0	801.8	791.1	783.8
25°	951.9	913.5	875.5	841.4	812.2	791.8	775.3	761.6	755.5	745.1	737.4
27.5°	902.1	861.2	821.8	787.7	764.9	744.8	731.2	720.3	709.4	700.3	693.6
30°	870.0	828.2	785.2	758.3	734.1	714.8	699.9	689.5	681.3	673.0	668.1
32.5°	837.9	794.8	756.6	727.5	704.6	687.9	672.6	662.7	654.0	644.8	639.0
35°	786.4	742.3	711.5	682.9	660.3	644.9	634.5	620.2	613.0	606.4	600.4
37.5°	738.5	697.6	664.2	639.1	619.5	604.2	590.7	582.9	574.1	568.2	563.1
40°	703.3	665.9	635.6	609.2	594.8	577.8	565.2	555.2	548.6	541.0	535.4
42.5°	671.6	636.7	607.4	583.6	565.8	551.4	539.2	529.3	520.9	515.4	510.8
45°	626.8	592.1	563.5	541.4	525.0	511.2	498.6	493.6	482.6	476.0	473.8
47.5°	580.4	549.4	521.8	501.5	484.6	471.6	459.7	449.6	443.5	437.0	433.5
50°	549.2	519.4	493.6	473.8	457.3	443.0	431.9	425.3	417.1	411.1	406.7
52.5°	518.0	490.4	464.6	445.6	431.3	417.0	404.7	398.1	390.3	386.4	383.4
55°	473.3	444.1	422.1	403.3	388.5	375.3	363.7	357.1	352.2	348.3	347.2
57.5°	422.7	399.5	379.0	362.2	346.7	334.4	324.2	318.0	313.6	313.0	309.7
60°	389.6	368.7	350.0	331.8	318.6	307.0	298.2	291.1	286.7	286.2	285.0
62.5°	356.6	336.6	319.2	303.2	291.3	280.2	271.8	263.8	261.1	258.4	256.0
65°	307.6	289.4	275.2	262.4	249.8	240.4	232.2	227.3	221.2	217.9	211.9
67.5°	259.5	245.4	231.7	221.0	211.1	202.2	195.3	188.0	183.9	181.2	176.8
70°	227.8	216.8	203.1	191.5	183.8	176.7	171.1	162.9	160.1	157.9	155.7
72.5°	197.9	188.2	176.7	167.3	159.6	152.9	146.5	142.6	139.9	137.7	136.4
75°	155.7	146.3	136.5	129.9	124.3	118.9	115.5	112.8	111.7	111.1	108.9
77.5°	114.4	109.4	101.5	96.2	92.5	90.3	87.4	85.9	85.9	83.4	82.7
80°	87.5	84.7	78.1	75.9	73.2	71.0	69.3	66.6	63.8	62.7	61.1
82.5°	65.1	62.3	59.7	56.1	53.8	52.5	50.9	49.8	50.2	48.7	47.9
85°	34.7	31.9	30.8	30.2	29.2	30.2	29.7	29.2	28.6	28.0	28.6
87.5°	13.0	13.4	13.4	14.6	13.7	14.5	14.8	14.6	14.8	15.2	14.9
90°	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3	23.7	25.1	26.2
92.5°	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3	23.7	25.1	25.9
95°	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3	23.7	25.1	25.8
97.5°	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0	37.3	29.6	25.8
100°	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2	91.6	51.0	30.2
102.5°	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1	249.4	241.7	228.6
105°	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.6
107.5°	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1	463.1	463.2	462.8
110°	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1	525.3	524.5	524.2



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5	587.5	586.4	585.7
115°	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7	681.6	680.4	679.1
117.5°	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6	772.2	770.7	769.6
120°	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3	831.7	831.2	830.2
122.5°	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2	887.7	887.1	886.1
125°	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9	968.7	967.7	966.7
127.5°	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5	1043.9	1043.3	1042.0
130°	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2	1092.3	1091.5	1090.4
132.5°	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6	1138.5	1138.3	1137.5
135°	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3	1204.8	1204.3	1203.1
137.5°	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5	1267.6	1267.8	1267.1
140°	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7	1306.3	1306.8	1306.3
142.5°	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1	1343.3	1343.4	1342.6
145°	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0	1396.3	1396.5	1395.9
147.5°	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3	1441.6	1441.9	1441.1
150°	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1	1470.7	1471.3	1470.5
152.5°	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7	1496.2	1496.8	1496.1
155°	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9	1531.7	1532.5	1531.8
157.5°	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9	1560.8	1561.7	1561.1
160°	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0	1579.2	1580.2	1579.7
162.5°	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6	1596.2	1597.7	1597.3
165°	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9	1617.6	1619.3	1618.9
167.5°	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1	1634.0	1636.0	1635.7
170°	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4	1642.6	1644.7	1644.6
172.5°	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8	1648.8	1650.7	1650.5
175°	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8	1656.0	1658.2	1658.1
177.5°	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8	1658.2	1659.8	1659.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1284.1	1279.3	1278.0	1279.7	1278.0	1279.3	1284.1	1284.6	1285.0	1288.5	1283.7
5°	1184.8	1179.2	1182.0	1180.9	1182.0	1179.2	1184.8	1190.3	1191.3	1196.3	1199.6
7.5°	1097.4	1090.5	1083.3	1085.6	1083.3	1090.5	1097.4	1097.5	1106.0	1112.5	1116.7
10°	1036.2	1030.7	1027.4	1030.1	1027.4	1030.7	1036.2	1043.3	1046.6	1054.3	1062.6
12.5°	984.6	981.4	978.5	977.3	978.5	981.4	984.6	992.3	1000.0	1009.0	1018.1
15°	914.6	908.0	905.2	898.1	905.2	908.0	914.6	921.2	936.0	939.9	953.7
17.5°	849.9	847.7	840.6	837.6	840.6	847.7	849.9	855.6	862.4	876.6	887.0
20°	811.6	809.4	802.3	806.7	802.3	809.4	811.6	819.9	825.4	837.0	846.9
22.5°	780.0	775.1	772.8	771.5	772.8	775.1	780.0	783.8	791.1	801.8	813.0
25°	735.2	728.0	725.3	721.9	725.3	728.0	735.2	737.4	745.1	755.5	761.6
27.5°	690.5	686.6	683.0	682.2	683.0	686.6	690.5	693.6	700.3	709.4	720.3
30°	661.5	657.6	654.8	654.8	654.8	657.6	661.5	668.1	673.0	681.3	689.5
32.5°	635.4	632.5	629.7	629.3	629.7	632.5	635.4	639.0	644.8	654.0	662.7
35°	597.6	593.2	592.1	588.8	592.1	593.2	597.6	600.4	606.4	613.0	620.2
37.5°	558.3	554.6	554.6	554.2	554.6	554.6	558.3	563.1	568.2	574.1	582.9
40°	533.2	530.4	529.9	526.0	529.9	530.4	533.2	535.4	541.0	548.6	555.2
42.5°	506.4	504.9	503.0	501.4	503.0	504.9	506.4	510.8	515.4	520.9	529.3
45°	469.9	466.1	466.1	463.3	466.1	466.1	469.9	473.8	476.0	482.6	493.6
47.5°	432.3	429.3	429.7	426.8	429.7	429.3	432.3	433.5	437.0	443.5	449.6
50°	407.2	405.5	405.0	403.9	405.0	405.5	407.2	406.7	411.1	417.1	425.3
52.5°	382.1	381.3	383.4	381.0	383.4	381.3	382.1	383.4	386.4	390.3	398.1
55°	348.3	346.7	350.0	346.7	350.0	346.7	348.3	347.2	348.3	352.2	357.1
57.5°	309.5	307.9	310.9	309.2	310.9	307.9	309.5	309.7	313.0	313.6	318.0
60°	284.0	280.6	282.3	282.8	282.3	280.6	284.0	285.0	286.2	286.7	291.1
62.5°	253.6	251.6	252.8	250.3	252.8	251.6	253.6	256.0	258.4	261.1	263.8
65°	210.8	209.1	206.9	205.8	206.9	209.1	210.8	211.9	217.9	221.2	227.3
67.5°	177.1	173.1	173.0	173.9	173.0	173.1	177.1	176.8	181.2	183.9	188.0
70°	152.5	152.5	151.9	151.9	151.9	152.5	152.5	155.7	157.9	160.1	162.9
72.5°	135.3	134.9	133.8	133.4	133.8	134.9	135.3	136.4	137.7	139.9	142.6
75°	108.9	109.5	108.4	107.9	108.4	109.5	108.9	108.9	111.1	111.7	112.8
77.5°	80.5	78.1	79.3	78.1	79.3	78.1	80.5	82.7	83.4	85.9	85.9
80°	61.1	60.5	62.2	60.5	62.2	60.5	61.1	61.1	62.7	63.8	66.6
82.5°	48.3	47.8	48.5	47.3	48.5	47.8	48.3	47.9	48.7	50.2	49.8
85°	29.2	28.6	28.0	28.6	28.0	28.6	29.2	28.6	28.0	28.6	29.2
87.5°	15.5	15.2	15.4	15.6	15.4	15.2	15.5	14.9	15.2	14.8	14.6
90°	27.0	27.8	28.6	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3
92.5°	26.3	26.7	27.1	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3
95°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3
97.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0
100°	29.0	28.0	26.9	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2
102.5°	210.0	191.5	172.9	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1
105°	365.3	365.1	364.8	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7
107.5°	461.9	461.1	460.3	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1
110°	524.5	524.7	525.1	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	585.4	585.0	584.6	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5
115°	677.5	675.8	674.2	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7
117.5°	769.0	768.3	767.5	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6
120°	828.8	827.4	826.1	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3
122.5°	884.5	882.9	881.3	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2
125°	965.9	965.1	964.3	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9
127.5°	1039.9	1038.0	1035.9	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5
130°	1089.1	1087.7	1086.3	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2
132.5°	1136.2	1134.8	1133.4	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6
135°	1201.5	1199.9	1198.2	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3
137.5°	1265.7	1264.3	1262.8	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5
140°	1304.6	1303.0	1301.4	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7
142.5°	1340.9	1339.3	1337.7	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1
145°	1394.2	1392.6	1391.0	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0
147.5°	1439.2	1437.2	1435.3	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3
150°	1468.3	1466.1	1464.0	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1
152.5°	1494.1	1492.2	1490.2	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7
155°	1529.7	1527.5	1525.3	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9
157.5°	1558.9	1556.7	1554.4	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9
160°	1577.5	1575.3	1573.1	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0
162.5°	1594.9	1592.4	1590.1	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6
165°	1616.8	1614.6	1612.4	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9
167.5°	1633.3	1630.8	1628.4	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1
170°	1642.2	1639.7	1637.2	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4
172.5°	1648.0	1645.6	1643.2	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8
175°	1655.6	1653.2	1650.7	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8
177.5°	1657.9	1656.2	1654.4	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1285.0	1289.9	1292.5	1298.7	1307.5	1311.9	1318.0	1322.4	1328.6	1336.1	1342.2
5°	1201.8	1215.0	1223.8	1237.5	1250.3	1262.9	1278.9	1290.4	1305.8	1323.4	1337.2
7.5°	1124.5	1141.1	1155.7	1173.9	1194.7	1211.0	1231.8	1253.1	1277.2	1302.2	1325.8
10°	1075.2	1091.8	1109.9	1132.5	1153.4	1175.4	1200.1	1224.9	1255.2	1283.3	1315.2
12.5°	1026.4	1044.6	1065.0	1090.2	1115.5	1143.7	1168.9	1196.8	1229.2	1265.7	1299.8
15°	965.7	983.3	1005.3	1026.8	1056.0	1086.8	1120.4	1157.2	1193.5	1234.3	1276.7
17.5°	900.7	920.1	944.3	969.1	999.9	1035.9	1068.9	1109.2	1150.1	1197.5	1247.4
20°	858.4	878.2	906.9	934.4	962.5	997.7	1036.7	1078.0	1121.4	1171.6	1227.1
22.5°	825.0	839.1	867.2	895.2	928.1	964.2	1002.4	1045.5	1092.8	1144.7	1202.9
25°	775.3	791.8	812.2	841.4	875.5	913.5	951.9	997.7	1049.4	1102.2	1164.4
27.5°	731.2	744.8	764.9	787.7	821.8	861.2	902.1	949.7	1002.8	1056.6	1122.0
30°	699.9	714.8	734.1	758.3	785.2	828.2	870.0	916.8	970.7	1026.3	1093.4
32.5°	672.6	687.9	704.6	727.5	756.6	794.8	837.9	883.8	938.6	995.9	1061.3
35°	634.5	644.9	660.3	682.9	711.5	742.3	786.4	834.8	888.2	947.6	1013.1
37.5°	590.7	604.2	619.5	639.1	664.2	697.6	738.5	787.4	837.0	893.9	953.7
40°	565.2	577.8	594.8	609.2	635.6	665.9	703.3	754.4	804.0	857.4	911.8
42.5°	539.2	551.4	565.8	583.6	607.4	636.7	671.6	719.2	772.3	822.6	868.2
45°	498.6	511.2	525.0	541.4	563.5	592.1	626.8	670.3	716.5	762.7	797.4
47.5°	459.7	471.6	484.6	501.5	521.8	549.4	580.4	618.8	663.7	703.0	727.8
50°	431.9	443.0	457.3	473.8	493.6	519.4	549.2	587.2	624.6	660.3	682.9
52.5°	404.7	417.0	431.3	445.6	464.6	490.4	518.0	550.6	586.3	615.5	634.1
55°	363.7	375.3	388.5	403.3	422.1	444.1	473.3	499.1	527.2	552.0	563.0
57.5°	324.2	334.4	346.7	362.2	379.0	399.5	422.7	447.5	467.3	484.8	497.3
60°	298.2	307.0	318.6	331.8	350.0	368.7	389.6	412.7	428.1	443.0	454.5
62.5°	271.8	280.2	291.3	303.2	319.2	336.6	356.6	375.3	390.3	400.3	413.6
65°	232.2	240.4	249.8	262.4	275.2	289.4	307.6	321.4	331.8	342.8	351.1
67.5°	195.3	202.2	211.1	221.0	231.7	245.4	259.5	270.9	278.1	284.7	294.6
70°	171.1	176.7	183.8	191.5	203.1	216.8	227.8	236.6	241.6	248.2	260.2
72.5°	146.5	152.9	159.6	167.3	176.7	188.2	197.9	206.7	209.9	215.2	222.9
75°	115.5	118.9	124.3	129.9	136.5	146.3	155.7	157.9	160.7	165.1	170.6
77.5°	87.4	90.3	92.5	96.2	101.5	109.4	114.4	117.6	118.3	119.9	125.4
80°	69.3	71.0	73.2	75.9	78.1	84.7	87.5	90.8	91.9	93.5	96.3
82.5°	50.9	52.5	53.8	56.1	59.7	62.3	65.1	68.3	68.6	69.8	70.4
85°	29.7	30.2	29.2	30.2	30.8	31.9	34.7	37.4	36.9	36.3	38.0
87.5°	14.8	14.5	13.7	14.6	13.4	13.4	13.0	13.0	13.5	13.9	14.3
90°	21.0	19.6	17.7	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	21.0	19.6	17.9	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9
95°	21.0	19.6	30.0	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0
97.5°	52.7	60.4	80.9	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0
100°	172.9	213.5	212.5	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0
102.5°	264.8	272.5	271.8	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9
105°	365.7	365.7	365.7	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9
107.5°	463.0	462.9	462.4	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5
110°	526.9	527.7	527.2	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	589.5	590.6	590.3	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2
115°	683.7	684.9	684.6	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5
117.5°	774.9	776.4	775.3	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0
120°	832.8	833.3	832.5	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9
122.5°	888.8	889.3	888.9	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0
125°	970.9	972.0	972.0	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4
127.5°	1045.1	1045.7	1045.9	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2
130°	1094.0	1094.8	1094.5	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4
132.5°	1138.8	1139.0	1139.5	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5
135°	1205.9	1206.5	1207.0	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5
137.5°	1267.5	1267.3	1267.8	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1
140°	1305.2	1304.6	1304.9	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4
142.5°	1343.0	1343.0	1342.6	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7
145°	1395.7	1395.5	1395.5	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0
147.5°	1441.0	1440.6	1440.3	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7
150°	1469.7	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1
152.5°	1495.2	1494.6	1494.1	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5
155°	1530.1	1529.3	1528.7	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1
157.5°	1559.1	1558.2	1558.1	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4
160°	1577.0	1575.9	1575.6	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0
162.5°	1593.1	1591.5	1591.3	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7
165°	1614.3	1612.7	1612.4	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9
167.5°	1630.1	1628.2	1627.9	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5
170°	1638.2	1636.0	1635.7	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4
172.5°	1644.9	1642.9	1642.4	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3
175°	1651.7	1649.5	1649.3	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6
177.5°	1655.2	1653.7	1653.4	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1347.1	1351.0	1356.7	1363.3	1368.6	1374.4	1377.4	1377.4	1380.1	1385.8	1393.3
5°	1351.0	1365.2	1379.0	1396.6	1410.4	1426.3	1438.4	1450.0	1460.4	1473.7	1487.4
7.5°	1349.8	1373.6	1398.4	1426.1	1456.7	1481.0	1506.0	1525.6	1545.0	1570.3	1590.2
10°	1345.4	1376.2	1409.8	1445.0	1483.5	1517.1	1547.4	1574.9	1601.3	1628.8	1653.6
12.5°	1337.5	1376.7	1417.7	1460.0	1508.6	1547.0	1586.2	1615.4	1646.3	1676.3	1706.8
15°	1325.6	1371.8	1421.4	1480.3	1539.7	1582.6	1621.1	1659.1	1687.7	1721.8	1751.0
17.5°	1301.1	1360.7	1422.9	1487.3	1544.4	1594.2	1634.7	1670.8	1701.3	1738.8	1778.4
20°	1286.5	1351.0	1415.8	1484.7	1539.1	1590.3	1629.4	1666.8	1704.8	1753.7	1802.1
22.5°	1266.3	1335.1	1403.9	1469.3	1526.8	1576.2	1616.6	1662.4	1712.2	1767.8	1826.4
25°	1234.3	1305.3	1373.5	1435.7	1491.8	1542.5	1597.5	1659.1	1719.6	1792.8	1877.0
27.5°	1193.7	1262.1	1323.0	1388.7	1444.5	1508.9	1577.5	1644.4	1731.6	1832.3	1937.4
30°	1163.3	1228.2	1286.0	1348.2	1411.4	1482.5	1559.5	1638.2	1742.2	1860.5	1985.4
32.5°	1128.0	1186.8	1244.1	1304.2	1377.1	1455.1	1537.0	1633.4	1757.6	1892.2	2021.5
35°	1067.0	1119.8	1175.4	1241.9	1319.6	1404.4	1508.9	1626.1	1776.3	1921.0	2037.1
37.5°	1002.9	1044.6	1100.4	1170.7	1255.2	1353.2	1471.9	1614.3	1768.6	1898.4	1947.9
40°	953.7	992.7	1051.6	1125.4	1208.9	1316.3	1449.4	1595.8	1751.0	1841.3	1837.4
42.5°	904.7	944.3	1000.9	1075.1	1162.3	1282.4	1419.5	1571.6	1702.6	1736.9	1665.2
45°	829.8	866.7	922.3	997.1	1090.6	1216.7	1360.8	1506.7	1590.3	1534.7	1392.8
47.5°	753.4	789.2	840.8	914.1	1016.3	1148.1	1284.4	1404.1	1415.8	1296.5	1126.2
50°	703.3	736.8	785.8	864.0	963.0	1091.8	1223.3	1317.4	1288.2	1142.4	966.9
52.5°	654.4	686.6	732.5	806.2	907.5	1033.6	1151.0	1224.9	1157.5	1002.4	844.5
55°	582.2	613.0	659.3	726.9	818.8	934.4	1037.3	1064.2	965.2	808.9	681.3
57.5°	513.6	536.2	581.9	641.7	730.3	832.3	906.0	901.2	791.8	651.1	559.5
60°	468.3	488.6	532.1	587.2	671.3	762.7	814.4	792.4	681.8	565.7	477.6
62.5°	426.0	445.1	481.5	532.1	604.5	683.9	721.5	691.1	586.7	484.7	414.7
65°	362.1	375.9	405.0	451.8	508.4	563.5	597.0	552.4	460.1	383.0	330.2
67.5°	302.3	314.2	340.1	373.7	412.8	450.8	464.5	422.7	350.7	298.8	261.6
70°	263.6	274.6	292.2	323.6	349.4	376.4	383.0	345.6	285.6	246.0	222.9
72.5°	226.6	236.8	252.2	274.3	292.2	307.7	310.8	276.1	230.2	202.8	185.0
75°	172.8	181.6	191.5	199.7	211.3	214.1	213.0	186.0	161.3	143.1	133.1
77.5°	127.0	130.6	136.7	140.0	140.6	140.3	134.7	117.6	104.8	97.4	93.4
80°	97.9	100.7	102.3	103.5	104.0	98.5	92.5	82.0	77.6	73.2	68.2
82.5°	71.1	73.0	74.6	74.8	71.8	67.3	61.6	56.4	53.4	51.2	49.3
85°	38.5	39.1	38.5	35.8	31.9	30.2	29.2	28.0	27.5	27.0	27.0
87.5°	14.3	13.5	11.7	12.6	13.0	12.9	13.3	13.2	13.2	13.5	13.7
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3
92.5°	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3
95°	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3
97.5°	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0
100°	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2
102.5°	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1
105°	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1
110°	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1





TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5
115°	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7
117.5°	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6
120°	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3
122.5°	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2
125°	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9
127.5°	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5
130°	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2
132.5°	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6
135°	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3
137.5°	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5
140°	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7
142.5°	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1
145°	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0
147.5°	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3
150°	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1
152.5°	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7
155°	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9
157.5°	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9
160°	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0
162.5°	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6
165°	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9
167.5°	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1
170°	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4
172.5°	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8
175°	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8
177.5°	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1399.1	1399.1	1406.6	1406.1	1411.0	1409.2	1410.1
5°	1503.9	1513.3	1521.5	1527.1	1535.3	1537.5	1536.4
7.5°	1612.7	1633.5	1643.6	1657.4	1659.9	1667.2	1666.5
10°	1680.0	1700.4	1715.8	1727.9	1733.9	1741.6	1742.2
12.5°	1732.8	1750.1	1763.7	1775.0	1782.3	1784.8	1786.2
15°	1774.1	1793.3	1809.3	1825.3	1834.7	1841.8	1845.7
17.5°	1815.7	1845.4	1873.6	1895.2	1908.3	1919.3	1919.1
20°	1847.9	1882.0	1917.2	1942.0	1967.2	1978.2	1979.9
22.5°	1882.2	1934.4	1979.7	2018.1	2051.3	2062.8	2067.1
25°	1953.5	2021.7	2091.7	2145.5	2184.0	2206.6	2210.0
27.5°	2039.6	2132.0	2205.5	2255.3	2287.3	2304.0	2307.6
30°	2100.5	2185.7	2251.8	2289.2	2304.0	2306.2	2298.0
32.5°	2127.7	2191.4	2217.9	2215.7	2186.5	2167.1	2159.7
35°	2094.3	2081.1	2016.8	1939.8	1880.9	1843.5	1833.5
37.5°	1905.9	1792.0	1673.6	1557.2	1495.3	1463.7	1409.6
40°	1720.2	1557.9	1434.6	1336.6	1266.7	1210.6	1197.4
42.5°	1510.7	1343.0	1219.8	1135.9	1080.1	1041.5	1024.8
45°	1213.9	1069.8	967.9	903.6	860.6	832.6	819.9
47.5°	970.9	859.3	785.1	737.5	704.8	680.4	673.5
50°	837.6	748.4	685.7	645.5	620.7	602.0	594.3
52.5°	727.5	655.5	607.3	574.1	550.7	539.1	532.6
55°	600.4	538.2	503.5	477.1	463.9	454.5	450.1
57.5°	491.0	446.1	420.8	402.5	390.3	384.3	382.1
60°	429.7	394.5	371.5	357.1	348.9	341.2	339.0
62.5°	375.6	347.9	330.0	317.5	309.2	306.0	304.6
65°	302.6	284.5	271.3	263.6	257.0	255.8	255.4
67.5°	240.6	229.9	223.0	214.9	212.6	208.8	208.0
70°	205.8	198.7	190.4	187.7	184.9	181.1	181.6
72.5°	174.6	167.4	161.8	158.2	157.2	155.5	156.9
75°	127.7	125.5	123.3	120.5	119.4	119.4	118.9
77.5°	91.2	89.3	86.8	85.2	84.9	82.5	83.4
80°	66.0	63.3	62.2	62.7	61.1	60.5	60.5
82.5°	48.8	47.9	46.8	46.9	46.6	46.0	46.5
85°	27.0	26.4	26.4	25.8	25.8	25.3	25.3
87.5°	14.4	15.2	14.5	14.2	14.3	15.0	15.6
90°	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333716-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)