

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333667-935

Luminaire Tested: **S125RDIW-S610D770U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333667-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D770U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4339.8 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5594	5594	5594
5°	5607	5543	5577
10°	5564	5491	5491
15°	5498	5380	5336
20°	5413	5225	5161
25°	5315	5072	4960
30°	5190	4894	4737
35°	5065	4709	4487
40°	4947	4517	4242
45°	4804	4302	3974
50°	4660	4068	3693
55°	4494	3845	3396
60°	4326	3574	3077
65°	4129	3260	2709
70°	3903	2866	2334
75°	3593	2415	1941
80°	3165	1901	1629
85°	2668	1549	1452



TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.4	1.9
10°-20°	227.6	5.2
20°-30°	330.1	7.6
30°-40°	376.2	8.7
40°-50°	366.7	8.4
50°-60°	308.6	7.1
60°-70°	216.4	5.0
70°-80°	111.2	2.6
80°-90°	29.9	0.7
90°-100°	55.0	1.3
100°-110°	162.4	3.7
110°-120°	275.1	6.3
120°-130°	362.1	8.3
130°-140°	405.7	9.3
140°-150°	397.7	9.2
150°-160°	334.0	7.7
160°-170°	222.0	5.1
170°-180°	77.7	1.8
0°-30°	639.1	14.7
0°-40°	1015.3	23.4
0°-60°	1690.5	39.0
0°-90°	2048.0	47.2
90°-120°	492.6	11.4
90°-150°	1658.1	38.2
90°-180°	2292.0	52.8
0°-180°	4339.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	861	860	82
15°	822	818	805	804	798	232
25°	746	735	712	703	696	343
35°	642	626	597	579	569	402
45°	526	506	471	446	435	406
55°	399	377	342	313	302	357
65°	270	247	213	188	177	268
75°	144	124	97	83	78	152
85°	36	25	21	20	20	40
90°	1	6	10	13	15	4
95°	42	43	49	54	55	44
105°	146	149	153	156	158	156
115°	276	278	279	279	278	272
125°	402	406	406	405	405	360
135°	523	526	527	527	525	403
145°	633	636	638	638	636	396
155°	725	725	726	728	725	334
165°	788	787	788	790	786	222
175°	819	817	817	820	816	78
180°	821	821	821	821	821	



TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	867.7	867.4	867.0	866.7	866.3	865.6	864.4	863.2	862.0	860.9	862.0
5°	864.8	864.3	863.7	863.1	862.5	861.4	859.8	858.2	856.6	855.0	856.4
7.5°	856.4	855.7	855.2	854.6	854.1	852.9	850.9	849.0	847.1	845.2	846.2
10°	848.4	848.0	847.6	847.1	846.7	845.5	843.4	841.5	839.4	837.3	837.8
12.5°	839.6	839.0	838.4	837.9	837.3	835.7	833.0	830.3	827.5	824.8	825.1
15°	822.3	821.4	820.5	819.7	818.8	816.8	813.8	810.7	807.7	804.6	804.5
17.5°	802.8	801.5	800.1	798.8	797.5	794.9	791.0	787.2	783.3	779.5	778.8
20°	787.6	786.2	784.7	783.3	781.8	778.8	774.1	769.5	764.8	760.2	759.4
22.5°	770.9	769.4	768.0	766.5	765.1	761.9	757.0	752.2	747.3	742.4	741.0
25°	745.8	743.6	741.4	739.3	737.0	733.2	727.9	722.5	717.1	711.7	709.9
27.5°	717.0	714.4	711.7	709.0	706.4	702.2	696.5	690.7	684.9	679.2	676.5
30°	696.0	693.3	690.5	687.8	685.0	680.5	674.4	668.4	662.3	656.2	652.8
32.5°	675.6	672.4	669.2	666.0	662.7	658.0	651.8	645.6	639.3	633.1	629.4
35°	642.4	638.9	635.4	632.0	628.4	623.5	616.9	610.4	603.8	597.3	593.1
37.5°	609.8	605.5	601.3	597.1	592.9	587.4	580.6	573.9	567.1	560.3	555.3
40°	586.8	582.5	578.1	573.7	569.4	563.7	556.7	549.7	542.8	535.8	530.3
42.5°	562.7	558.3	553.8	549.3	544.8	539.0	531.8	524.5	517.4	510.1	504.8
45°	526.0	521.8	517.5	513.3	509.1	503.0	495.0	487.0	479.0	471.0	465.2
47.5°	487.9	483.5	479.0	474.6	470.1	463.8	455.8	447.7	439.7	431.6	425.7
50°	463.8	459.0	454.2	449.4	444.6	438.1	429.8	421.5	413.2	404.9	398.8
52.5°	437.6	432.7	427.8	422.9	418.0	411.6	403.8	396.0	388.1	380.3	373.8
55°	399.1	394.4	389.8	385.1	380.5	374.0	365.9	357.7	349.7	341.5	334.9
57.5°	360.1	355.1	350.1	345.2	340.2	333.7	325.9	318.1	310.2	302.4	295.9
60°	334.9	329.8	324.8	319.7	314.6	308.2	300.2	292.4	284.6	276.7	270.4
62.5°	308.2	303.4	298.5	293.7	288.9	282.4	274.5	266.5	258.6	250.6	244.6
65°	270.2	265.3	260.3	255.4	250.4	244.1	236.3	228.7	220.9	213.3	207.4
67.5°	232.4	227.4	222.5	217.6	212.6	206.5	199.1	191.7	184.3	176.8	171.6
70°	206.7	201.8	196.8	191.9	186.9	180.8	173.6	166.3	159.0	151.8	147.2
72.5°	181.6	176.8	171.9	167.1	162.3	156.4	149.6	142.8	136.0	129.2	125.1
75°	144.0	139.6	135.2	130.9	126.5	121.2	115.1	109.0	102.9	96.8	93.6
77.5°	106.5	103.0	99.5	96.0	92.6	88.3	83.4	78.6	73.7	68.8	66.6
80°	85.1	81.5	78.1	74.6	71.1	67.3	63.2	59.2	55.1	51.1	49.7
82.5°	64.1	61.0	57.9	54.7	51.6	48.6	45.8	43.0	40.2	37.5	36.9
85°	36.0	33.3	30.7	28.2	25.5	23.8	23.1	22.4	21.7	20.9	20.8
87.5°	12.1	11.5	11.0	10.4	9.8	9.6	9.6	9.7	9.8	9.9	10.1
90°	0.6	1.8	2.9	4.0	5.2	6.3	7.2	8.3	9.2	10.2	10.9
92.5°	15.5	16.3	17.0	17.8	18.7	19.6	20.9	22.1	23.3	24.5	25.5
95°	41.6	41.8	42.1	42.4	42.7	43.6	44.9	46.4	47.8	49.2	50.2
97.5°	69.1	69.1	69.2	69.4	69.5	70.5	72.5	74.5	76.4	78.4	79.3
100°	89.5	89.5	89.5	89.5	89.5	90.4	92.2	94.1	95.9	97.8	99.1
102.5°	111.5	112.0	112.6	113.1	113.7	114.5	115.5	116.4	117.3	118.2	119.7
105°	145.8	146.5	147.1	147.8	148.6	149.4	150.2	151.0	151.9	152.7	153.6
107.5°	183.6	184.3	185.0	185.7	186.4	187.1	187.8	188.4	189.1	189.7	190.1
110°	209.7	210.3	211.0	211.8	212.5	213.0	213.4	213.9	214.3	214.7	215.2



TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	236.3	236.6	236.9	237.4	237.7	238.2	238.7	239.3	239.8	240.3	240.6
115°	275.5	276.0	276.6	277.2	277.8	278.2	278.4	278.7	279.1	279.3	279.1
117.5°	314.9	315.1	315.4	315.6	315.9	316.2	316.4	316.7	316.9	317.2	317.3
120°	339.4	340.1	340.8	341.6	342.2	342.7	342.8	342.9	343.1	343.2	343.2
122.5°	366.0	366.3	366.5	366.8	367.0	367.3	367.6	368.1	368.4	368.8	368.7
125°	402.0	402.9	403.7	404.6	405.4	406.0	406.0	406.2	406.4	406.5	406.2
127.5°	440.4	440.8	441.3	441.9	442.3	442.6	442.8	443.0	443.2	443.3	443.2
130°	463.4	464.1	464.9	465.5	466.2	466.7	467.0	467.3	467.6	467.9	467.7
132.5°	486.4	487.6	488.7	489.9	491.0	491.6	491.5	491.5	491.5	491.4	491.3
135°	522.8	523.7	524.5	525.4	526.2	526.8	526.8	527.0	527.2	527.3	527.3
137.5°	557.1	557.9	558.7	559.6	560.4	560.9	561.3	561.5	561.9	562.2	562.4
140°	579.1	579.8	580.5	581.2	581.9	582.5	582.9	583.3	583.8	584.2	584.4
142.5°	601.1	601.7	602.3	602.9	603.5	604.0	604.6	605.1	605.6	606.1	606.3
145°	633.4	634.0	634.6	635.1	635.7	636.2	636.6	637.1	637.5	637.9	637.9
147.5°	663.3	663.7	663.9	664.3	664.6	664.9	665.2	665.6	665.9	666.2	666.6
150°	683.3	683.1	682.9	682.9	682.7	682.9	683.5	684.1	684.6	685.2	685.2
152.5°	699.6	699.8	700.0	700.3	700.4	700.6	700.9	701.1	701.3	701.5	701.9
155°	724.8	724.8	724.8	724.8	724.8	724.9	725.0	725.1	725.3	725.5	726.0
157.5°	747.3	747.0	746.7	746.4	746.1	746.0	746.1	746.2	746.4	746.6	747.1
160°	760.6	760.2	759.7	759.3	758.9	758.7	758.9	759.1	759.1	759.3	759.9
162.5°	772.4	772.1	771.7	771.5	771.1	770.9	771.0	771.0	771.0	771.1	771.8
165°	788.1	787.8	787.6	787.2	787.0	786.9	787.0	787.1	787.3	787.5	788.0
167.5°	801.4	800.8	800.2	799.7	799.1	798.8	798.8	798.8	798.8	798.8	799.7
170°	808.6	808.0	807.4	806.8	806.2	806.0	806.0	806.0	806.0	806.0	806.8
172.5°	813.6	813.0	812.5	811.9	811.4	811.1	811.1	811.1	811.1	811.1	811.9
175°	819.4	818.8	818.3	817.7	817.1	816.8	816.8	816.8	816.8	816.8	817.7
177.5°	822.3	821.9	821.4	821.0	820.5	820.3	820.1	820.0	819.9	819.8	820.4
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	866.2	866.2	866.2	866.2	866.2	866.2	866.2	866.2
2.5°	863.2	864.4	865.6	866.1	866.0	865.8	865.7	865.6
5°	857.9	859.4	860.8	861.4	861.1	860.8	860.6	860.2
7.5°	847.2	848.3	849.3	849.6	849.3	848.9	848.7	848.3
10°	838.2	838.6	839.1	839.1	838.6	838.2	837.8	837.3
12.5°	825.4	825.8	826.0	825.9	825.2	824.6	823.9	823.2
15°	804.3	804.2	804.1	803.3	802.0	800.7	799.4	798.1
17.5°	778.1	777.3	776.6	775.7	774.6	773.5	772.5	771.4
20°	758.7	757.9	757.2	756.2	754.9	753.6	752.3	751.0
22.5°	739.5	738.0	736.7	735.4	734.3	733.2	732.2	731.1
25°	708.0	706.1	704.2	702.4	700.9	699.2	697.7	696.0
27.5°	673.9	671.2	668.6	666.5	665.0	663.4	661.9	660.3
30°	649.5	646.1	642.7	640.4	639.1	637.8	636.5	635.2
32.5°	625.7	622.1	618.4	615.7	614.0	612.3	610.7	609.1
35°	588.8	584.6	580.4	577.3	575.2	573.2	571.2	569.1
37.5°	550.3	545.2	540.1	536.6	534.6	532.7	530.7	528.7
40°	524.7	519.2	513.7	510.1	508.3	506.5	504.8	503.1
42.5°	499.6	494.2	489.0	485.0	482.5	479.9	477.3	474.8
45°	459.3	453.6	447.7	443.8	441.6	439.4	437.2	435.1
47.5°	419.7	413.6	407.7	403.5	401.1	398.6	396.2	393.8
50°	392.7	386.6	380.5	376.3	374.2	372.0	369.8	367.6
52.5°	367.2	360.6	354.0	349.7	347.5	345.3	343.1	341.0
55°	328.4	321.8	315.3	310.9	308.6	306.3	303.9	301.6
57.5°	289.6	283.2	276.8	272.5	270.4	268.4	266.4	264.3
60°	263.9	257.5	251.2	246.8	244.7	242.5	240.3	238.2
62.5°	238.7	232.7	226.8	222.7	220.6	218.4	216.2	214.0
65°	201.6	195.8	190.0	186.0	183.8	181.7	179.4	177.3
67.5°	166.3	160.9	155.6	152.1	150.3	148.6	146.8	145.1
70°	142.8	138.3	133.7	130.6	128.9	127.2	125.4	123.6
72.5°	121.0	116.8	112.6	109.9	108.8	107.6	106.5	105.3
75°	90.4	87.2	84.0	81.9	80.9	79.9	78.9	77.8
77.5°	64.3	62.1	59.8	58.4	57.6	56.8	56.1	55.4
80°	48.4	47.1	45.8	45.0	44.7	44.4	44.1	43.8
82.5°	36.2	35.6	35.0	34.6	34.4	34.3	34.1	33.9
85°	20.7	20.5	20.3	20.2	20.1	19.9	19.8	19.6
87.5°	10.2	10.3	10.5	10.5	10.5	10.4	10.4	10.4
90°	11.6	12.4	13.1	13.6	14.0	14.5	14.9	15.3
92.5°	26.4	27.4	28.3	28.9	29.3	29.5	29.9	30.1
95°	51.2	52.2	53.2	53.8	54.2	54.4	54.7	54.9
97.5°	80.2	81.2	82.1	82.7	82.8	83.0	83.2	83.3
100°	100.3	101.6	102.9	103.7	104.0	104.3	104.5	104.8
102.5°	121.1	122.4	123.8	124.7	125.1	125.5	125.9	126.3
105°	154.5	155.3	156.2	156.8	157.2	157.6	158.1	158.5
107.5°	190.5	191.0	191.4	191.6	191.6	191.6	191.5	191.5
110°	215.6	216.0	216.5	216.6	216.5	216.3	216.2	216.0





TEST NUMBER: P333667-935

CATALOG NUMBER: S125RDIW-S610D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.7	240.9	241.1	241.1	240.8	240.6	240.3	240.0
115°	279.1	278.9	278.7	278.6	278.4	278.4	278.2	278.0
117.5°	317.4	317.5	317.6	317.4	316.8	316.2	315.6	315.1
120°	343.2	343.2	343.2	342.9	342.4	341.8	341.2	340.7
122.5°	368.6	368.4	368.3	368.1	367.6	367.1	366.7	366.3
125°	406.0	405.6	405.4	405.2	405.0	404.8	404.8	404.6
127.5°	443.1	442.9	442.7	442.6	442.3	442.0	441.7	441.4
130°	467.6	467.4	467.3	467.1	466.8	466.5	466.2	466.0
132.5°	491.1	490.9	490.9	490.5	490.2	489.7	489.4	489.0
135°	527.3	527.3	527.3	527.0	526.4	525.9	525.3	524.8
137.5°	562.6	562.7	562.9	562.6	561.9	561.2	560.5	559.7
140°	584.8	585.0	585.3	585.1	584.4	583.7	583.0	582.3
142.5°	606.5	606.7	606.8	606.6	605.9	605.2	604.4	603.7
145°	637.9	637.9	637.9	637.7	637.2	636.8	636.4	635.9
147.5°	666.9	667.3	667.6	667.3	666.3	665.4	664.4	663.5
150°	685.2	685.2	685.2	685.0	684.8	684.5	684.2	683.9
152.5°	702.2	702.6	702.9	702.8	702.3	701.8	701.3	700.8
155°	726.6	727.1	727.7	727.6	726.9	726.3	725.5	724.8
157.5°	747.7	748.2	748.8	748.6	747.7	746.7	745.8	744.9
160°	760.4	761.0	761.6	761.6	760.8	760.1	759.4	758.7
162.5°	772.5	773.1	773.8	773.8	772.9	772.1	771.3	770.4
165°	788.6	789.2	789.7	789.5	788.8	787.9	787.0	786.2
167.5°	800.6	801.4	802.2	802.2	801.3	800.5	799.6	798.7
170°	807.7	808.6	809.4	809.3	808.3	807.4	806.3	805.4
172.5°	812.8	813.6	814.5	814.5	813.6	812.7	811.8	811.0
175°	818.6	819.4	820.3	820.2	819.2	818.2	817.2	816.2
177.5°	821.1	821.8	822.5	822.4	821.7	820.9	820.1	819.2
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3

(END OF REPORT)