

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333736-930

Luminaire Tested: **S125RDIW-S1270D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333736-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9098.7 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	45	44	44	38
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	1.6
10°-20°	435.1	4.8
20°-30°	689.8	7.6
30°-40°	831.9	9.1
40°-50°	742.9	8.2
50°-60°	569.7	6.3
60°-70°	370.2	4.1
70°-80°	180.0	2.0
80°-90°	46.4	0.5
90°-100°	60.2	0.7
100°-110°	370.8	4.1
110°-120°	672.5	7.4
120°-130°	863.1	9.5
130°-140°	928.3	10.2
140°-150°	871.4	9.6
150°-160°	704.9	7.7
160°-170°	455.9	5.0
170°-180°	157.2	1.7
0°-30°	1273.4	14.0
0°-40°	2105.3	23.1
0°-60°	3417.9	37.6
0°-90°	4014.5	44.1
90°-120°	1103.5	12.1
90°-150°	3766.2	41.4
90°-180°	5084.0	55.9
0°-180°	9098.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	29	1	29	1	29	14
95°	26	70	26	70	26	21
105°	364	361	364	361	364	330
115°	672	678	672	678	672	668
125°	963	963	963	963	963	857
135°	1197	1202	1197	1202	1197	923
145°	1389	1393	1389	1393	1389	868
155°	1523	1534	1523	1534	1523	702
165°	1610	1619	1610	1619	1610	454
175°	1648	1656	1648	1656	1648	157
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	17.0	16.4	15.7	15.6	15.9	16.7	15.9	15.2	14.8	14.6	14.8
90°	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3	21.0	19.6	17.7
92.5°	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3	21.0	19.6	17.9
95°	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3	21.0	19.6	30.0
97.5°	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0	52.7	60.4	80.9
100°	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2	172.9	213.5	212.5
102.5°	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1	264.8	272.5	271.8
105°	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1	463.0	462.9	462.4
110°	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1	526.9	527.7	527.2



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5	589.5	590.6	590.3
115°	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7	683.7	684.9	684.6
117.5°	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6	774.9	776.4	775.3
120°	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3	832.8	833.3	832.5
122.5°	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2	888.8	889.3	888.9
125°	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9	970.9	972.0	972.0
127.5°	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5	1045.1	1045.7	1045.9
130°	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2	1094.0	1094.8	1094.5
132.5°	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6	1138.8	1139.0	1139.5
135°	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3	1205.9	1206.5	1207.0
137.5°	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5	1267.5	1267.3	1267.8
140°	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7	1305.2	1304.6	1304.9
142.5°	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1	1343.0	1343.0	1342.6
145°	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0	1395.7	1395.5	1395.5
147.5°	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3	1441.0	1440.6	1440.3
150°	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1	1469.7	1469.1	1468.5
152.5°	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7	1495.2	1494.6	1494.1
155°	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9	1530.1	1529.3	1528.7
157.5°	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9	1559.1	1558.2	1558.1
160°	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0	1577.0	1575.9	1575.6
162.5°	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6	1593.1	1591.5	1591.3
165°	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9	1614.3	1612.7	1612.4
167.5°	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1	1630.1	1628.2	1627.9
170°	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4	1638.2	1636.0	1635.7
172.5°	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8	1644.9	1642.9	1642.4
175°	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8	1651.7	1649.5	1649.3
177.5°	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8	1655.2	1653.7	1653.4
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	14.8	14.5	14.6	14.2	13.2	15.3	16.5	16.6	15.9	15.3	14.8
90°	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9	17.4	15.8	14.3
95°	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0	69.1	68.3	67.5
97.5°	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0	147.5	149.0	150.5
100°	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0	205.8	206.6	207.4
102.5°	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9	265.9	266.9	268.0
105°	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9	361.9	363.1	364.1
107.5°	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5	460.5	460.5	460.5
110°	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2	586.9	587.5	588.2
115°	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5	678.8	680.2	681.6
117.5°	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0	771.9	771.8	771.8
120°	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9	830.6	830.4	830.1
122.5°	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0	883.9	885.0	886.1
125°	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4	965.3	967.3	969.1
127.5°	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2	1041.6	1043.0	1044.4
130°	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4	1088.8	1090.1	1091.5
132.5°	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5	1136.1	1137.7	1139.3
135°	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5	1203.1	1204.8	1206.5
137.5°	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1	1264.5	1266.0	1267.4
140°	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4	1304.0	1304.5	1305.0
142.5°	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7	1340.0	1340.4	1340.7
145°	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0	1393.5	1394.1	1394.7
147.5°	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7	1439.5	1439.4	1439.3
150°	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1468.5	1468.0	1467.5
152.5°	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5	1496.4	1495.2	1494.0
155°	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1	1532.5	1530.9	1529.3
157.5°	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4	1561.4	1560.4	1559.4
160°	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0	1580.4	1578.7	1577.1
162.5°	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7	1596.1	1594.5	1592.8
165°	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9	1617.2	1615.5	1613.9
167.5°	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5	1632.9	1631.2	1629.5
170°	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4	1641.4	1639.6	1637.6
172.5°	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3	1647.4	1645.4	1643.6
175°	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6	1654.0	1652.4	1650.7
177.5°	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6	1657.3	1656.0	1654.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.7	15.1	15.0	16.4	15.2	16.1	16.4	16.1	16.5	16.7	16.4
90°	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3	23.7	25.1	26.2
92.5°	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3	23.7	25.1	25.9
95°	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3	23.7	25.1	25.8
97.5°	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0	37.3	29.6	25.8
100°	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2	91.6	51.0	30.2
102.5°	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1	249.4	241.7	228.6
105°	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.6
107.5°	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1	463.1	463.2	462.8
110°	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1	525.3	524.5	524.2



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5	587.5	586.4	585.7
115°	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7	681.6	680.4	679.1
117.5°	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6	772.2	770.7	769.6
120°	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3	831.7	831.2	830.2
122.5°	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2	887.7	887.1	886.1
125°	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9	968.7	967.7	966.7
127.5°	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5	1043.9	1043.3	1042.0
130°	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2	1092.3	1091.5	1090.4
132.5°	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6	1138.5	1138.3	1137.5
135°	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3	1204.8	1204.3	1203.1
137.5°	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5	1267.6	1267.8	1267.1
140°	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7	1306.3	1306.8	1306.3
142.5°	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1	1343.3	1343.4	1342.6
145°	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0	1396.3	1396.5	1395.9
147.5°	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3	1441.6	1441.9	1441.1
150°	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1	1470.7	1471.3	1470.5
152.5°	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7	1496.2	1496.8	1496.1
155°	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9	1531.7	1532.5	1531.8
157.5°	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9	1560.8	1561.7	1561.1
160°	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0	1579.2	1580.2	1579.7
162.5°	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6	1596.2	1597.7	1597.3
165°	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9	1617.6	1619.3	1618.9
167.5°	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1	1634.0	1636.0	1635.7
170°	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4	1642.6	1644.7	1644.6
172.5°	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8	1648.8	1650.7	1650.5
175°	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8	1656.0	1658.2	1658.1
177.5°	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8	1658.2	1659.8	1659.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	17.1	16.7	16.9	17.0	16.9	16.7	17.1	16.4	16.7	16.5	16.1
90°	27.0	27.8	28.6	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3
92.5°	26.3	26.7	27.1	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3
95°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3
97.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0
100°	29.0	28.0	26.9	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2
102.5°	210.0	191.5	172.9	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1
105°	365.3	365.1	364.8	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7
107.5°	461.9	461.1	460.3	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1
110°	524.5	524.7	525.1	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	585.4	585.0	584.6	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5
115°	677.5	675.8	674.2	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7
117.5°	769.0	768.3	767.5	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6
120°	828.8	827.4	826.1	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3
122.5°	884.5	882.9	881.3	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2
125°	965.9	965.1	964.3	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9
127.5°	1039.9	1038.0	1035.9	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5
130°	1089.1	1087.7	1086.3	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2
132.5°	1136.2	1134.8	1133.4	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6
135°	1201.5	1199.9	1198.2	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3
137.5°	1265.7	1264.3	1262.8	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5
140°	1304.6	1303.0	1301.4	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7
142.5°	1340.9	1339.3	1337.7	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1
145°	1394.2	1392.6	1391.0	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0
147.5°	1439.2	1437.2	1435.3	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3
150°	1468.3	1466.1	1464.0	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1
152.5°	1494.1	1492.2	1490.2	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7
155°	1529.7	1527.5	1525.3	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9
157.5°	1558.9	1556.7	1554.4	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9
160°	1577.5	1575.3	1573.1	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0
162.5°	1594.9	1592.4	1590.1	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6
165°	1616.8	1614.6	1612.4	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9
167.5°	1633.3	1630.8	1628.4	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1
170°	1642.2	1639.7	1637.2	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4
172.5°	1648.0	1645.6	1643.2	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8
175°	1655.6	1653.2	1650.7	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8
177.5°	1657.9	1656.2	1654.4	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	16.4	16.1	15.2	16.4	15.0	15.1	14.7	14.8	15.3	15.9	16.6
90°	21.0	19.6	17.7	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	21.0	19.6	17.9	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9
95°	21.0	19.6	30.0	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0
97.5°	52.7	60.4	80.9	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0
100°	172.9	213.5	212.5	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0
102.5°	264.8	272.5	271.8	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9
105°	365.7	365.7	365.7	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9
107.5°	463.0	462.9	462.4	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5
110°	526.9	527.7	527.2	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	589.5	590.6	590.3	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2
115°	683.7	684.9	684.6	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5
117.5°	774.9	776.4	775.3	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0
120°	832.8	833.3	832.5	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9
122.5°	888.8	889.3	888.9	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0
125°	970.9	972.0	972.0	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4
127.5°	1045.1	1045.7	1045.9	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2
130°	1094.0	1094.8	1094.5	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4
132.5°	1138.8	1139.0	1139.5	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5
135°	1205.9	1206.5	1207.0	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5
137.5°	1267.5	1267.3	1267.8	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1
140°	1305.2	1304.6	1304.9	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4
142.5°	1343.0	1343.0	1342.6	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7
145°	1395.7	1395.5	1395.5	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0
147.5°	1441.0	1440.6	1440.3	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7
150°	1469.7	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1
152.5°	1495.2	1494.6	1494.1	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5
155°	1530.1	1529.3	1528.7	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1
157.5°	1559.1	1558.2	1558.1	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4
160°	1577.0	1575.9	1575.6	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0
162.5°	1593.1	1591.5	1591.3	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7
165°	1614.3	1612.7	1612.4	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9
167.5°	1630.1	1628.2	1627.9	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5
170°	1638.2	1636.0	1635.7	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4
172.5°	1644.9	1642.9	1642.4	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3
175°	1651.7	1649.5	1649.3	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6
177.5°	1655.2	1653.7	1653.4	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.5	15.3	13.2	14.2	14.6	14.5	14.8	14.8	14.6	14.8	15.2
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3
92.5°	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3
95°	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3
97.5°	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0
100°	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2
102.5°	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1
105°	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1
110°	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5
115°	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7
117.5°	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6
120°	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3
122.5°	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2
125°	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9
127.5°	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5
130°	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2
132.5°	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6
135°	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3
137.5°	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5
140°	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7
142.5°	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1
145°	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0
147.5°	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3
150°	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1
152.5°	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7
155°	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9
157.5°	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9
160°	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0
162.5°	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6
165°	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9
167.5°	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1
170°	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4
172.5°	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8
175°	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8
177.5°	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	15.9	16.7	15.9	15.6	15.7	16.4	17.0
90°	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333736-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)