

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333739-930

Luminaire Tested: **S125RDIW-S1270D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333739-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8388.4 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10869	10869	10869
5°	10895	10771	10836
10°	10812	10670	10670
15°	10683	10454	10369
20°	10519	10152	10030
25°	10326	9855	9638
30°	10086	9508	9205
35°	9842	9150	8719
40°	9613	8777	8241
45°	9334	8360	7721
50°	9055	7905	7178
55°	8731	7472	6598
60°	8407	6945	5977
65°	8023	6333	5265
70°	7585	5569	4538
75°	6977	4694	3773
80°	6148	3686	3169
85°	5187	3016	2831



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.3	1.9
10°-20°	442.3	5.3
20°-30°	641.3	7.6
30°-40°	730.9	8.7
40°-50°	712.5	8.5
50°-60°	599.7	7.1
60°-70°	420.4	5.0
70°-80°	216.1	2.6
80°-90°	58.0	0.7
90°-100°	105.8	1.3
100°-110°	312.5	3.7
110°-120°	529.3	6.3
120°-130°	696.6	8.3
130°-140°	780.6	9.3
140°-150°	765.0	9.1
150°-160°	642.6	7.7
160°-170°	427.1	5.1
170°-180°	149.5	1.8
0°-30°	1241.9	14.8
0°-40°	1972.8	23.5
0°-60°	3284.9	39.2
0°-90°	3979.5	47.4
90°-120°	947.6	11.3
90°-150°	3189.8	38.0
90°-180°	4409.0	52.6
0°-180°	8388.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1680	1675	1661	1673	1672	159
15°	1598	1589	1564	1562	1551	450
25°	1449	1428	1383	1367	1352	666
35°	1248	1216	1161	1125	1106	781
45°	1022	983	915	866	845	788
55°	775	733	664	608	586	693
65°	525	480	414	365	344	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	11	20	26	30	8
95°	80	83	95	103	106	85
105°	280	287	294	301	305	299
115°	530	535	537	536	535	524
125°	773	780	782	780	778	692
135°	1006	1013	1014	1014	1010	775
145°	1218	1223	1227	1227	1223	761
155°	1394	1394	1396	1400	1394	642
165°	1516	1514	1515	1519	1512	428
175°	1576	1572	1571	1578	1570	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1686.0	1685.4	1684.7	1684.0	1683.3	1681.9	1679.6	1677.3	1675.1	1672.8	1675.1
5°	1680.5	1679.4	1678.2	1677.1	1675.9	1673.8	1670.7	1667.6	1664.5	1661.4	1664.2
7.5°	1663.9	1662.9	1661.8	1660.7	1659.6	1657.3	1653.5	1649.8	1646.1	1642.3	1644.3
10°	1648.7	1647.8	1647.0	1646.2	1645.3	1642.9	1638.9	1635.0	1631.0	1627.1	1627.9
12.5°	1631.4	1630.4	1629.2	1628.2	1627.1	1623.9	1618.6	1613.3	1607.9	1602.6	1603.3
15°	1597.8	1596.1	1594.5	1592.8	1591.1	1587.2	1581.3	1575.4	1569.5	1563.5	1563.3
17.5°	1559.9	1557.4	1554.8	1552.2	1549.6	1544.5	1537.1	1529.6	1522.2	1514.7	1513.3
20°	1530.5	1527.6	1524.8	1522.0	1519.1	1513.2	1504.2	1495.2	1486.1	1477.1	1475.7
22.5°	1497.9	1495.1	1492.2	1489.5	1486.6	1480.5	1471.0	1461.5	1452.0	1442.5	1439.7
25°	1449.1	1444.9	1440.6	1436.4	1432.2	1424.8	1414.4	1403.9	1393.4	1383.0	1379.3
27.5°	1393.2	1388.0	1382.9	1377.8	1372.6	1364.5	1353.2	1342.1	1330.9	1319.7	1314.6
30°	1352.5	1347.1	1341.7	1336.4	1331.1	1322.4	1310.5	1298.7	1286.8	1275.0	1268.4
32.5°	1312.9	1306.6	1300.3	1294.0	1287.8	1278.6	1266.5	1254.4	1242.3	1230.2	1223.0
35°	1248.3	1241.5	1234.7	1227.9	1221.2	1211.4	1198.7	1186.0	1173.3	1160.6	1152.3
37.5°	1185.0	1176.7	1168.5	1160.3	1151.9	1141.3	1128.2	1115.1	1102.0	1088.8	1079.0
40°	1140.2	1131.7	1123.2	1114.8	1106.4	1095.3	1081.7	1068.2	1054.6	1041.1	1030.4
42.5°	1093.5	1084.8	1076.0	1067.3	1058.7	1047.3	1033.3	1019.3	1005.3	991.2	981.0
45°	1022.0	1013.8	1005.6	997.4	989.2	977.4	961.8	946.3	930.7	915.3	903.9
47.5°	948.0	939.4	930.7	922.1	913.5	901.3	885.7	870.0	854.4	838.7	827.0
50°	901.2	891.9	882.6	873.3	864.0	851.3	835.1	819.0	802.9	786.8	774.9
52.5°	850.4	840.8	831.3	821.7	812.2	799.8	784.6	769.5	754.2	739.1	726.3
55°	775.4	766.4	757.3	748.3	739.2	726.8	711.0	695.2	679.4	663.6	650.9
57.5°	699.6	690.0	680.3	670.7	661.0	648.6	633.3	618.0	602.8	587.5	575.1
60°	650.9	640.9	631.0	621.2	611.3	598.7	583.4	568.2	552.9	537.7	525.3
62.5°	599.0	589.5	580.1	570.6	561.3	548.8	533.3	517.8	502.3	486.8	475.3
65°	525.0	515.4	505.8	496.2	486.6	474.3	459.3	444.3	429.3	414.4	403.1
67.5°	451.5	441.9	432.3	422.7	413.1	401.1	386.8	372.4	358.1	343.7	333.4
70°	401.7	392.1	382.5	372.8	363.3	351.4	337.3	323.2	309.0	294.9	286.2
72.5°	352.9	343.5	334.1	324.7	315.4	304.0	290.8	277.6	264.4	251.2	243.1
75°	279.6	271.2	262.7	254.2	245.7	235.6	223.7	211.9	200.0	188.1	181.9
77.5°	206.9	200.2	193.4	186.6	179.9	171.7	162.2	152.7	143.2	133.7	129.4
80°	165.3	158.5	151.7	144.9	138.1	130.8	122.9	115.0	107.0	99.1	96.6
82.5°	124.6	118.5	112.3	106.2	100.2	94.4	88.9	83.6	78.1	72.7	71.5
85°	70.0	64.8	59.8	54.6	49.6	46.3	44.9	43.5	42.1	40.7	40.4
87.5°	23.6	22.5	21.4	20.2	19.1	18.6	18.8	18.9	19.0	19.2	19.5
90°	1.2	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0
92.5°	29.8	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0
95°	79.9	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6
97.5°	132.8	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5
100°	172.1	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6
102.5°	214.4	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2
105°	280.4	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5
107.5°	353.1	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7
110°	403.3	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.4	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7
115°	529.9	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0
117.5°	605.7	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3
120°	652.9	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3
122.5°	704.1	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2
125°	773.4	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5
127.5°	847.2	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6
130°	891.4	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8
132.5°	935.7	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0
135°	1005.8	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4
137.5°	1071.7	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9
140°	1114.0	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4
142.5°	1156.3	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4
145°	1218.5	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1
147.5°	1276.1	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4
150°	1314.4	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2
152.5°	1345.9	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3
155°	1394.4	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7
157.5°	1437.6	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3
160°	1463.2	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8
162.5°	1485.9	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7
165°	1516.1	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0
167.5°	1541.6	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4
170°	1555.4	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2
172.5°	1565.3	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0
175°	1576.4	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0
177.5°	1582.0	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1677.3	1679.6	1681.9	1682.9	1682.7	1682.5	1682.2	1682.0
5°	1667.0	1669.9	1672.7	1673.8	1673.2	1672.7	1672.1	1671.5
7.5°	1646.3	1648.3	1650.2	1650.9	1650.2	1649.7	1649.0	1648.5
10°	1628.7	1629.6	1630.4	1630.4	1629.6	1628.7	1627.9	1627.1
12.5°	1603.9	1604.5	1605.2	1604.8	1603.5	1602.2	1600.9	1599.6
15°	1562.9	1562.7	1562.4	1561.0	1558.4	1555.9	1553.3	1550.8
17.5°	1511.9	1510.4	1509.0	1507.3	1505.2	1503.1	1501.0	1498.9
20°	1474.2	1472.8	1471.5	1469.4	1466.9	1464.4	1461.8	1459.3
22.5°	1437.0	1434.2	1431.4	1429.0	1426.9	1424.8	1422.7	1420.7
25°	1375.7	1372.0	1368.3	1364.9	1361.8	1358.7	1355.6	1352.5
27.5°	1309.5	1304.3	1299.2	1295.1	1292.1	1289.1	1286.1	1283.1
30°	1262.0	1255.5	1249.0	1244.5	1241.9	1239.3	1236.8	1234.3
32.5°	1215.9	1208.7	1201.5	1196.3	1193.1	1189.8	1186.7	1183.4
35°	1144.2	1136.0	1127.8	1121.7	1117.8	1113.8	1109.9	1105.9
37.5°	1069.2	1059.4	1049.5	1042.7	1038.9	1035.0	1031.2	1027.4
40°	1019.6	1008.9	998.2	991.1	987.7	984.3	980.9	977.5
42.5°	970.7	960.4	950.1	942.5	937.5	932.5	927.6	922.6
45°	892.6	881.3	870.0	862.3	858.0	853.8	849.5	845.3
47.5°	815.5	803.8	792.1	784.0	779.3	774.6	769.9	765.2
50°	763.1	751.2	739.4	731.3	727.1	722.8	718.6	714.4
52.5°	713.5	700.7	687.9	679.5	675.2	671.0	666.8	662.5
55°	638.1	625.4	612.7	604.1	599.6	595.0	590.5	586.0
57.5°	562.6	550.2	537.8	529.6	525.5	521.5	517.6	513.6
60°	512.8	500.4	488.0	479.6	475.4	471.2	466.9	462.7
62.5°	463.8	452.2	440.8	432.8	428.6	424.4	420.1	415.9
65°	391.8	380.5	369.2	361.4	357.2	352.9	348.7	344.5
67.5°	323.0	312.7	302.4	295.5	292.1	288.7	285.4	281.9
70°	277.4	268.6	259.9	253.8	250.4	247.0	243.6	240.3
72.5°	235.1	227.0	218.8	213.7	211.4	209.2	206.9	204.6
75°	175.7	169.5	163.3	159.1	157.2	155.2	153.3	151.2
77.5°	125.0	120.7	116.3	113.4	111.9	110.5	109.0	107.5
80°	94.1	91.6	88.9	87.4	86.8	86.3	85.8	85.2
82.5°	70.4	69.1	68.0	67.2	66.9	66.5	66.2	65.9
85°	40.1	39.9	39.5	39.3	39.0	38.7	38.4	38.2
87.5°	19.7	20.0	20.3	20.4	20.3	20.3	20.2	20.1
90°	22.4	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	50.8	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	98.5	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	154.3	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	193.1	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	232.8	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	297.2	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	366.6	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	414.8	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333739-930

CATALOG NUMBER: S125RDIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	463.1	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.8	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.6	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	709.1	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	781.0	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.3	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.5	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.8	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.2	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1124.9	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1166.8	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.0	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.0	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1397.7	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1438.4	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1463.0	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1486.0	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1517.0	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1540.0	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1553.8	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1563.7	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1574.8	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1579.7	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)