

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333643-930

Luminaire Tested: **S125RDIW-S375D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333643-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2504.7 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	59	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	26	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3222	3222	3222
5°	3229	3192	3212
10°	3205	3163	3163
15°	3167	3099	3074
20°	3118	3009	2973
25°	3061	2921	2857
30°	2990	2818	2729
35°	2917	2713	2584
40°	2850	2602	2443
45°	2767	2478	2288
50°	2685	2344	2127
55°	2587	2215	1956
60°	2492	2059	1771
65°	2378	1878	1560
70°	2247	1650	1344
75°	2069	1392	1118
80°	1822	1093	941
85°	1534	897	837



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	1.9
10°-20°	131.1	5.2
20°-30°	190.1	7.6
30°-40°	216.7	8.7
40°-50°	211.2	8.4
50°-60°	177.8	7.1
60°-70°	124.6	5.0
70°-80°	64.1	2.6
80°-90°	17.2	0.7
90°-100°	31.8	1.3
100°-110°	93.9	3.7
110°-120°	159.1	6.4
120°-130°	209.4	8.4
130°-140°	234.6	9.4
140°-150°	229.9	9.2
150°-160°	193.1	7.7
160°-170°	128.4	5.1
170°-180°	44.9	1.8
0°-30°	368.1	14.7
0°-40°	584.8	23.3
0°-60°	973.7	38.9
0°-90°	1179.6	47.1
90°-120°	284.8	11.4
90°-150°	958.7	38.3
90°-180°	1325.0	52.9
0°-180°	2504.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	499	499	499	499	499	
5°	498	496	492	496	496	47
15°	474	471	464	463	460	133
25°	430	423	410	405	401	198
35°	370	361	344	333	328	232
45°	303	292	271	257	250	234
55°	230	217	197	180	174	206
65°	156	142	123	108	102	154
75°	83	71	56	48	45	88
85°	21	14	12	12	11	23
90°	0	3	6	8	9	2
95°	24	25	28	31	32	26
105°	84	86	88	90	92	90
115°	159	161	162	161	161	157
125°	232	235	235	234	234	208
135°	302	304	305	305	303	233
145°	366	368	369	369	368	229
155°	419	419	419	421	419	193
165°	456	455	455	457	454	128
175°	474	472	472	474	472	45
180°	475	475	475	475	475	



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9
2.5°	499.8	499.6	499.4	499.2	499.0	498.6	497.9	497.2	496.5	495.9	496.5
5°	498.1	497.8	497.5	497.1	496.8	496.2	495.2	494.3	493.4	492.4	493.3
7.5°	493.3	492.9	492.6	492.3	492.0	491.2	490.2	489.0	488.0	486.8	487.4
10°	488.7	488.4	488.2	488.0	487.7	487.0	485.8	484.6	483.5	482.3	482.6
12.5°	483.6	483.2	483.0	482.7	482.3	481.4	479.8	478.3	476.6	475.1	475.2
15°	473.6	473.1	472.6	472.1	471.7	470.5	468.7	467.0	465.2	463.5	463.4
17.5°	462.4	461.6	460.9	460.1	459.3	457.9	455.6	453.4	451.2	449.0	448.6
20°	453.6	452.8	452.0	451.2	450.3	448.6	445.9	443.2	440.5	437.8	437.4
22.5°	444.0	443.2	442.4	441.5	440.7	438.9	436.0	433.3	430.4	427.6	426.8
25°	429.6	428.3	427.1	425.7	424.5	422.3	419.2	416.1	413.0	409.9	408.9
27.5°	412.9	411.5	409.9	408.4	406.8	404.5	401.1	397.8	394.5	391.2	389.6
30°	400.9	399.3	397.7	396.2	394.5	392.0	388.5	385.0	381.5	377.9	376.0
32.5°	389.1	387.3	385.5	383.6	381.7	379.0	375.4	371.9	368.3	364.7	362.6
35°	370.0	368.0	366.0	363.9	362.0	359.1	355.3	351.6	347.8	344.1	341.6
37.5°	351.2	348.8	346.3	343.9	341.4	338.3	334.4	330.5	326.7	322.8	319.8
40°	338.0	335.5	333.0	330.4	327.9	324.7	320.7	316.7	312.6	308.6	305.4
42.5°	324.1	321.6	318.9	316.4	313.8	310.5	306.3	302.1	298.0	293.8	290.8
45°	303.0	300.5	298.1	295.6	293.3	289.7	285.1	280.5	275.9	271.3	267.9
47.5°	281.0	278.4	275.9	273.3	270.8	267.2	262.5	257.9	253.2	248.6	245.2
50°	267.2	264.4	261.6	258.9	256.1	252.3	247.5	242.8	238.0	233.3	229.8
52.5°	252.1	249.2	246.4	243.6	240.8	237.1	232.6	228.0	223.6	219.1	215.3
55°	229.8	227.1	224.5	221.8	219.2	215.5	210.8	206.0	201.4	196.7	192.9
57.5°	207.4	204.6	201.6	198.8	195.9	192.2	187.7	183.2	178.7	174.1	170.5
60°	192.9	190.0	187.0	184.1	181.2	177.5	172.9	168.4	163.9	159.4	155.7
62.5°	177.6	174.7	171.9	169.2	166.3	162.7	158.1	153.5	148.9	144.3	140.9
65°	155.6	152.8	149.9	147.1	144.2	140.6	136.2	131.8	127.3	122.9	119.5
67.5°	133.9	131.0	128.2	125.3	122.5	118.9	114.6	110.4	106.2	101.9	98.8
70°	119.0	116.3	113.4	110.6	107.7	104.2	100.0	95.8	91.6	87.4	84.8
72.5°	104.6	101.8	99.1	96.3	93.5	90.1	86.2	82.3	78.4	74.4	72.1
75°	82.9	80.4	77.9	75.3	72.9	69.9	66.3	62.8	59.3	55.8	53.9
77.5°	61.3	59.4	57.3	55.3	53.3	50.9	48.1	45.2	42.5	39.6	38.3
80°	49.0	47.0	45.0	43.0	40.9	38.8	36.4	34.1	31.7	29.4	28.6
82.5°	36.9	35.1	33.3	31.5	29.7	28.0	26.4	24.8	23.2	21.5	21.2
85°	20.7	19.2	17.7	16.2	14.7	13.7	13.3	12.9	12.5	12.1	12.0
87.5°	7.0	6.7	6.4	6.0	5.6	5.5	5.5	5.6	5.6	5.7	5.8
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	6.0	6.4
92.5°	9.0	9.4	9.9	10.4	10.8	11.3	12.1	12.8	13.5	14.2	14.8
95°	24.1	24.2	24.4	24.5	24.7	25.2	26.0	26.8	27.6	28.5	29.0
97.5°	39.9	39.9	40.0	40.1	40.2	40.8	41.9	43.0	44.2	45.3	45.8
100°	51.8	51.8	51.8	51.8	51.8	52.3	53.3	54.4	55.4	56.5	57.3
102.5°	64.4	64.7	65.1	65.5	65.8	66.2	66.8	67.3	67.8	68.3	69.1
105°	84.2	84.6	85.0	85.4	85.9	86.3	86.8	87.3	87.8	88.3	88.8
107.5°	106.2	106.6	107.0	107.4	107.8	108.2	108.5	108.9	109.3	109.7	109.9
110°	121.2	121.6	122.1	122.5	122.9	123.2	123.4	123.7	123.9	124.2	124.4



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	136.6	136.8	137.0	137.2	137.5	137.7	138.0	138.4	138.6	138.9	139.1
115°	159.2	159.6	160.0	160.3	160.6	160.9	161.0	161.2	161.3	161.5	161.4
117.5°	182.1	182.1	182.3	182.5	182.6	182.8	183.0	183.0	183.2	183.4	183.4
120°	196.2	196.7	197.1	197.5	197.9	198.1	198.2	198.3	198.4	198.4	198.4
122.5°	211.6	211.7	211.9	212.1	212.1	212.4	212.5	212.8	213.0	213.2	213.1
125°	232.4	232.9	233.4	233.9	234.4	234.7	234.8	234.9	235.0	235.1	234.9
127.5°	254.6	254.9	255.2	255.4	255.8	255.9	256.0	256.1	256.2	256.3	256.2
130°	267.9	268.3	268.7	269.1	269.5	269.9	270.0	270.2	270.4	270.5	270.4
132.5°	281.2	281.8	282.6	283.2	283.9	284.2	284.2	284.1	284.1	284.1	284.0
135°	302.2	302.8	303.3	303.8	304.3	304.5	304.6	304.7	304.8	304.8	304.8
137.5°	322.0	322.5	323.0	323.5	324.0	324.3	324.5	324.7	324.8	325.1	325.1
140°	334.8	335.2	335.6	336.0	336.4	336.8	337.0	337.3	337.5	337.8	337.9
142.5°	347.5	347.8	348.2	348.5	348.9	349.2	349.5	349.8	350.2	350.5	350.6
145°	366.2	366.6	366.9	367.2	367.5	367.8	368.0	368.3	368.5	368.8	368.8
147.5°	383.5	383.7	383.8	384.0	384.3	384.4	384.6	384.8	385.0	385.2	385.4
150°	395.0	394.9	394.8	394.8	394.7	394.8	395.2	395.5	395.8	396.2	396.2
152.5°	404.5	404.6	404.7	404.8	405.0	405.0	405.2	405.4	405.4	405.6	405.8
155°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.2	419.3	419.4	419.7
157.5°	432.0	431.9	431.7	431.5	431.3	431.3	431.4	431.5	431.5	431.6	431.9
160°	439.8	439.5	439.2	439.0	438.7	438.6	438.7	438.8	438.9	439.0	439.4
162.5°	446.5	446.4	446.2	446.0	445.8	445.7	445.7	445.7	445.8	445.8	446.2
165°	455.6	455.4	455.3	455.1	454.9	454.9	455.0	455.1	455.2	455.3	455.6
167.5°	463.3	463.0	462.7	462.4	462.0	461.9	461.9	461.9	461.9	461.9	462.4
170°	467.4	467.1	466.8	466.4	466.1	465.9	465.9	465.9	465.9	465.9	466.4
172.5°	470.4	470.1	469.8	469.4	469.1	469.0	469.0	469.0	469.0	469.0	469.4
175°	473.8	473.4	473.0	472.7	472.4	472.2	472.2	472.2	472.2	472.2	472.7
177.5°	475.4	475.2	474.9	474.7	474.3	474.2	474.2	474.1	474.0	473.9	474.3
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9
2.5°	497.2	497.9	498.6	498.9	498.8	498.7	498.6	498.6
5°	494.2	495.0	495.8	496.2	496.0	495.8	495.6	495.5
7.5°	488.0	488.6	489.2	489.3	489.2	489.0	488.9	488.6
10°	482.8	483.1	483.3	483.3	483.1	482.8	482.6	482.3
12.5°	475.4	475.6	475.8	475.7	475.3	474.9	474.6	474.2
15°	463.3	463.2	463.1	462.7	461.9	461.2	460.5	459.7
17.5°	448.2	447.8	447.4	446.8	446.2	445.6	444.9	444.3
20°	437.0	436.6	436.2	435.6	434.8	434.1	433.3	432.6
22.5°	425.9	425.1	424.3	423.5	423.0	422.3	421.8	421.1
25°	407.8	406.7	405.6	404.6	403.7	402.8	401.9	400.9
27.5°	388.2	386.6	385.1	383.9	383.0	382.1	381.2	380.3
30°	374.1	372.2	370.2	368.9	368.1	367.4	366.6	365.9
32.5°	360.4	358.3	356.1	354.7	353.7	352.7	351.7	350.8
35°	339.2	336.7	334.3	332.5	331.3	330.2	329.0	327.8
37.5°	316.9	314.1	311.1	309.1	307.9	306.8	305.7	304.5
40°	302.2	299.1	295.9	293.8	292.8	291.8	290.7	289.8
42.5°	287.7	284.7	281.6	279.4	277.9	276.4	274.9	273.5
45°	264.6	261.2	257.9	255.6	254.4	253.1	251.8	250.5
47.5°	241.7	238.2	234.8	232.4	231.0	229.6	228.2	226.8
50°	226.2	222.7	219.2	216.8	215.6	214.3	213.0	211.7
52.5°	211.5	207.7	203.9	201.4	200.2	198.9	197.6	196.4
55°	189.1	185.4	181.6	179.0	177.7	176.3	175.0	173.7
57.5°	166.8	163.1	159.4	156.9	155.8	154.6	153.4	152.2
60°	152.1	148.3	144.6	142.2	140.9	139.7	138.4	137.1
62.5°	137.5	134.0	130.6	128.3	127.0	125.8	124.6	123.3
65°	116.1	112.8	109.4	107.1	105.9	104.6	103.4	102.1
67.5°	95.7	92.7	89.6	87.6	86.6	85.6	84.5	83.6
70°	82.3	79.7	77.0	75.3	74.2	73.2	72.2	71.2
72.5°	69.6	67.3	64.9	63.3	62.7	62.0	61.3	60.7
75°	52.1	50.2	48.4	47.2	46.6	46.0	45.4	44.8
77.5°	37.1	35.8	34.5	33.6	33.2	32.8	32.3	31.9
80°	27.9	27.1	26.4	25.9	25.8	25.6	25.4	25.3
82.5°	20.9	20.5	20.1	19.9	19.8	19.7	19.6	19.5
85°	11.9	11.8	11.7	11.7	11.6	11.5	11.4	11.3
87.5°	5.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0
90°	6.8	7.2	7.6	7.9	8.2	8.4	8.6	8.9
92.5°	15.2	15.8	16.4	16.7	16.9	17.0	17.3	17.4
95°	29.6	30.2	30.7	31.1	31.3	31.5	31.6	31.8
97.5°	46.4	47.0	47.5	47.8	47.9	48.0	48.1	48.2
100°	58.0	58.8	59.5	59.9	60.1	60.3	60.4	60.6
102.5°	70.0	70.8	71.6	72.1	72.3	72.6	72.8	73.1
105°	89.3	89.8	90.3	90.7	90.9	91.2	91.4	91.6
107.5°	110.1	110.4	110.6	110.8	110.8	110.7	110.7	110.7
110°	124.7	124.9	125.1	125.2	125.1	125.1	125.0	124.9



TEST NUMBER: P333643-930

CATALOG NUMBER: S125RDIW-S375D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	139.2	139.3	139.4	139.4	139.3	139.1	138.9	138.8
115°	161.3	161.3	161.2	161.1	161.0	160.9	160.9	160.8
117.5°	183.5	183.5	183.6	183.5	183.2	182.9	182.5	182.1
120°	198.4	198.4	198.4	198.3	198.0	197.6	197.3	197.0
122.5°	213.1	213.0	213.0	212.8	212.5	212.3	212.0	211.7
125°	234.7	234.6	234.4	234.2	234.2	234.1	234.0	233.9
127.5°	256.2	256.1	256.0	255.8	255.7	255.5	255.4	255.2
130°	270.4	270.3	270.2	270.0	269.9	269.7	269.5	269.4
132.5°	283.9	283.8	283.7	283.6	283.4	283.2	282.9	282.7
135°	304.8	304.8	304.8	304.7	304.4	304.0	303.7	303.4
137.5°	325.2	325.3	325.5	325.3	324.9	324.5	324.0	323.6
140°	338.1	338.3	338.4	338.3	337.9	337.5	337.0	336.6
142.5°	350.7	350.7	350.8	350.7	350.3	349.8	349.4	349.0
145°	368.8	368.8	368.8	368.7	368.4	368.2	367.9	367.7
147.5°	385.6	385.8	386.0	385.8	385.2	384.7	384.1	383.6
150°	396.2	396.2	396.2	396.1	395.9	395.7	395.6	395.4
152.5°	406.0	406.2	406.3	406.3	406.0	405.8	405.4	405.1
155°	420.0	420.4	420.7	420.7	420.3	419.9	419.5	419.1
157.5°	432.3	432.6	432.9	432.8	432.3	431.7	431.2	430.6
160°	439.7	440.0	440.3	440.3	439.9	439.4	439.0	438.6
162.5°	446.6	446.9	447.4	447.4	446.9	446.4	445.9	445.4
165°	455.9	456.2	456.6	456.5	456.0	455.5	455.0	454.5
167.5°	462.8	463.3	463.8	463.8	463.3	462.8	462.3	461.8
170°	466.9	467.4	468.0	467.9	467.3	466.8	466.2	465.6
172.5°	469.9	470.4	470.9	470.9	470.3	469.9	469.4	468.9
175°	473.2	473.8	474.3	474.2	473.6	473.0	472.5	471.9
177.5°	474.7	475.2	475.6	475.5	475.1	474.6	474.1	473.7
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8

(END OF REPORT)