

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333436-840

Luminaire Tested: **S125DIW-S1090D770U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333436-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D770U840-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7633.4 lumens  
Efficiency: N/A  
Efficacy: 142.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12010	10407	9111	10407
10°	13973	10352	7984	10352
15°	15468	10277	7365	10277
20°	17314	10156	6868	10156
25°	20283	10020	6625	10020
30°	21908	9887	6415	9887
35°	18013	9635	6277	9635
40°	12803	9286	6126	9286
45°	9836	8815	6039	8815
50°	8397	8232	6027	8232
55°	7475	7659	6079	7659
60°	6744	7034	6234	7034
65°	6229	6406	6395	6406
70°	5663	5754	6488	5754
75°	5001	5068	6428	5068
80°	4206	4132	5880	4132
85°	3327	2979	4742	2979



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.6	2.0
10°-20°	460.3	6.0
20°-30°	747.4	9.8
30°-40°	911.7	11.9
40°-50°	829.4	10.9
50°-60°	660.6	8.7
60°-70°	460.1	6.0
70°-80°	245.4	3.2
80°-90°	64.0	0.8
90°-100°	36.7	0.5
100°-110°	226.1	3.0
110°-120°	410.0	5.4
120°-130°	526.2	6.9
130°-140°	566.0	7.4
140°-150°	531.3	7.0
150°-160°	429.7	5.6
160°-170°	277.9	3.6
170°-180°	95.9	1.3
0°-30°	1362.3	17.8
0°-40°	2274.0	29.8
0°-60°	3764.0	49.3
0°-90°	4533.6	59.4
90°-120°	672.8	8.8
90°-150°	2296.2	30.1
90°-180°	3100.0	40.6
0°-180°	7633.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1606	1606	1606	1606	1606	
5°	1853	1605	1405	1605	1853	187
15°	2313	1537	1102	1537	2313	662
25°	2846	1406	930	1406	2846	1300
35°	2285	1222	796	1222	2285	1398
45°	1077	965	661	965	1077	862
55°	664	680	540	680	664	598
65°	408	419	418	419	408	405
75°	200	203	258	203	200	216
85°	45	40	64	40	45	52
90°	18	1	18	1	18	10
95°	16	43	16	43	16	13
105°	222	220	222	220	222	201
115°	410	413	410	413	410	407
125°	587	587	587	587	587	523
135°	730	733	730	733	730	563
145°	847	849	847	849	847	529
155°	929	935	929	935	929	428
165°	982	987	982	987	982	277
175°	1005	1010	1005	1010	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1698.6	1696.4	1694.3	1689.8	1693.1	1683.8	1679.5	1671.8	1662.5	1659.3	1655.5
5°	1852.6	1856.0	1859.5	1845.1	1846.4	1836.9	1815.1	1797.4	1783.1	1764.6	1751.7
7.5°	2038.0	2029.9	2029.3	2020.0	2004.1	1991.3	1968.3	1939.1	1911.0	1878.8	1852.2
10°	2130.7	2131.4	2125.3	2114.4	2097.3	2085.1	2055.1	2026.4	1991.7	1950.8	1921.5
12.5°	2200.5	2203.3	2195.6	2180.9	2172.5	2145.1	2121.6	2087.5	2046.2	2013.5	1968.9
15°	2313.4	2305.9	2300.5	2282.0	2267.8	2239.1	2201.6	2166.2	2121.1	2079.6	2038.0
17.5°	2422.2	2428.1	2417.9	2401.2	2356.7	2323.3	2273.0	2224.5	2168.5	2112.7	2063.1
20°	2519.2	2524.7	2509.0	2479.7	2426.5	2393.2	2327.0	2264.3	2199.6	2128.0	2073.5
22.5°	2640.3	2635.9	2614.7	2570.2	2524.2	2462.4	2390.9	2314.5	2233.3	2152.5	2080.0
25°	2846.4	2817.7	2804.8	2749.7	2689.0	2598.3	2500.1	2388.3	2287.4	2180.5	2087.8
27.5°	2960.6	2951.6	2937.2	2898.7	2835.0	2738.0	2622.3	2486.1	2343.8	2208.7	2087.4
30°	2937.7	2939.1	2940.4	2928.2	2887.3	2814.4	2699.2	2552.6	2383.6	2231.6	2091.1
32.5°	2734.9	2759.7	2783.4	2811.5	2823.0	2808.9	2736.8	2604.4	2430.4	2257.8	2089.0
35°	2284.7	2292.3	2369.2	2445.6	2549.2	2629.7	2683.5	2624.8	2478.3	2280.0	2086.4
37.5°	1781.5	1818.3	1871.6	1957.8	2107.4	2241.3	2413.5	2492.6	2445.4	2287.2	2081.6
40°	1518.6	1552.7	1587.5	1675.4	1801.5	1963.7	2159.3	2326.3	2365.2	2264.3	2065.3
42.5°	1315.8	1342.8	1381.4	1447.4	1552.9	1696.6	1883.4	2101.6	2235.9	2197.8	2030.9
45°	1076.9	1094.0	1124.0	1176.5	1252.8	1365.2	1530.2	1768.8	1976.7	2045.5	1949.4
47.5°	921.8	921.7	945.0	981.3	1036.3	1131.9	1253.8	1440.8	1662.8	1827.1	1819.5
50°	835.7	832.2	850.6	882.0	925.6	989.1	1105.6	1254.9	1468.1	1654.3	1706.1
52.5°	761.5	761.9	773.3	796.4	832.9	887.1	974.1	1108.7	1291.0	1482.0	1579.5
55°	663.9	661.2	674.1	689.8	716.4	751.8	814.6	917.5	1065.3	1253.4	1380.3
57.5°	574.4	582.0	587.1	598.0	620.2	643.9	696.7	772.2	889.6	1051.1	1185.1
60°	522.1	529.6	533.7	544.6	562.3	582.8	623.7	685.0	783.9	922.9	1055.8
62.5°	475.2	481.1	482.4	492.2	506.8	526.6	558.8	610.4	688.4	810.0	940.2
65°	407.6	407.6	410.3	420.5	427.4	445.0	469.6	507.2	569.9	664.6	775.7
67.5°	342.4	345.7	345.1	349.5	355.8	369.6	387.2	418.1	464.5	533.7	622.6
70°	299.9	302.7	301.9	305.4	312.1	321.0	335.4	364.7	398.1	457.4	533.7
72.5°	261.8	262.9	261.1	265.6	269.6	277.4	293.4	309.0	340.2	390.3	453.0
75°	200.4	201.8	203.1	205.8	210.0	214.0	222.2	237.9	258.3	295.8	336.1
77.5°	150.3	147.6	150.9	150.5	152.8	155.9	163.2	171.5	188.2	212.0	243.1
80°	113.1	113.8	113.8	114.5	118.0	120.0	126.1	132.2	145.2	162.9	184.7
82.5°	82.6	84.4	83.3	84.5	87.4	88.9	92.3	97.4	104.8	118.8	134.5
85°	44.9	41.6	42.9	44.3	44.3	44.9	47.7	49.8	53.8	59.3	65.4
87.5°	16.7	17.7	18.1	18.0	18.5	18.3	20.3	20.2	21.6	23.1	25.0
90°	18.0	17.5	17.0	16.5	16.0	15.2	14.4	13.6	12.8	12.0	10.8
92.5°	16.8	16.6	16.3	16.1	15.9	15.2	14.4	13.6	12.8	12.0	10.9
95°	15.8	15.8	15.8	15.8	15.8	15.2	14.4	13.6	12.8	12.0	18.3
97.5°	15.8	15.8	15.8	15.8	15.8	18.1	22.7	27.5	32.1	36.9	49.3
100°	15.8	16.4	17.1	17.7	18.4	31.1	55.8	80.7	105.4	130.2	129.6
102.5°	94.1	105.4	116.7	128.1	139.4	147.3	152.1	156.7	161.5	166.1	165.7
105°	222.3	222.4	222.6	222.8	222.9	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.1	280.6	281.1	281.7	282.2	282.4	282.4	282.4	282.3	282.3	282.0
110°	320.2	320.1	319.9	319.7	319.6	319.7	320.2	320.7	321.2	321.7	321.4



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.2	356.4	356.7	356.9	357.1	357.5	358.2	358.8	359.4	360.1	359.9
115°	410.0	411.0	412.0	413.0	414.0	414.9	415.6	416.2	416.9	417.6	417.4
117.5°	467.6	468.0	468.4	468.8	469.3	469.9	470.8	471.6	472.5	473.3	472.7
120°	502.8	503.7	504.5	505.3	506.1	506.8	507.1	507.5	507.8	508.1	507.6
122.5°	536.3	537.3	538.3	539.3	540.2	540.9	541.2	541.5	541.9	542.2	542.0
125°	587.4	587.9	588.3	588.9	589.4	590.0	590.7	591.3	592.0	592.6	592.6
127.5°	630.4	631.6	632.8	634.0	635.3	636.1	636.4	636.8	637.1	637.5	637.6
130°	661.5	662.3	663.2	664.0	664.8	665.5	666.0	666.5	666.9	667.4	667.3
132.5°	690.2	691.1	691.9	692.7	693.6	694.0	694.1	694.2	694.3	694.4	694.8
135°	729.5	730.5	731.5	732.6	733.6	734.3	734.6	734.9	735.2	735.6	735.9
137.5°	769.1	769.9	770.8	771.6	772.5	773.0	772.8	772.8	772.7	772.6	773.0
140°	792.4	793.5	794.5	795.4	796.4	796.8	796.4	796.1	795.8	795.4	795.6
142.5°	814.6	815.6	816.6	817.6	818.6	819.0	819.0	818.9	818.8	818.8	818.5
145°	847.1	848.1	849.0	850.0	851.0	851.4	851.3	851.1	850.9	850.8	850.8
147.5°	873.8	875.0	876.3	877.5	878.6	879.1	878.9	878.7	878.5	878.3	878.1
150°	891.2	892.5	893.8	895.1	896.6	897.1	896.7	896.4	896.1	895.6	895.3
152.5°	907.4	908.6	909.8	910.9	912.1	912.6	912.2	911.9	911.6	911.2	910.9
155°	928.6	930.0	931.3	932.6	933.9	934.3	933.8	933.3	932.8	932.3	932.0
157.5°	946.4	947.8	949.1	950.4	951.7	952.1	951.6	951.1	950.6	950.0	950.0
160°	957.8	959.2	960.5	961.8	963.1	963.4	962.8	962.1	961.5	960.8	960.6
162.5°	968.0	969.5	970.9	972.4	973.8	974.1	973.1	972.2	971.3	970.4	970.2
165°	981.7	983.1	984.4	985.7	987.0	987.2	986.2	985.2	984.2	983.2	983.1
167.5°	991.3	992.8	994.3	995.8	997.3	997.4	996.2	995.0	993.8	992.7	992.5
170°	996.7	998.2	999.7	1001.2	1002.7	1002.8	1001.5	1000.1	998.8	997.4	997.2
172.5°	1000.3	1001.8	1003.3	1004.8	1006.2	1006.4	1005.2	1004.0	1002.8	1001.7	1001.4
175°	1004.9	1006.4	1007.9	1009.5	1010.9	1011.0	1009.7	1008.4	1007.0	1005.7	1005.5
177.5°	1007.6	1008.7	1009.8	1010.8	1011.9	1012.0	1011.0	1010.1	1009.2	1008.2	1008.0
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1652.2	1648.4	1644.1	1636.4	1627.1	1622.2	1614.6	1609.7	1599.8	1591.6	1583.0
5°	1736.1	1718.4	1702.0	1680.8	1657.7	1642.6	1625.0	1605.2	1584.8	1563.6	1540.4
7.5°	1822.9	1791.5	1757.5	1720.8	1685.0	1651.9	1620.4	1589.5	1560.6	1525.7	1496.1
10°	1881.3	1841.7	1799.5	1749.7	1701.3	1659.0	1616.1	1578.6	1540.4	1499.5	1463.4
12.5°	1939.5	1886.9	1827.2	1772.6	1714.3	1663.3	1612.9	1565.0	1517.0	1471.8	1429.6
15°	1980.7	1934.4	1879.2	1801.5	1736.1	1665.9	1599.0	1537.0	1479.0	1428.7	1375.5
17.5°	2007.9	1948.1	1888.9	1814.3	1728.6	1650.0	1574.4	1503.4	1438.0	1374.1	1322.8
20°	2012.8	1951.5	1889.5	1816.4	1728.6	1638.6	1563.0	1477.7	1407.5	1341.4	1278.7
22.5°	2011.1	1941.7	1874.1	1799.1	1713.3	1630.4	1538.9	1452.1	1375.9	1310.9	1245.5
25°	1995.8	1921.5	1836.9	1761.3	1676.8	1588.8	1496.1	1406.1	1328.5	1254.2	1189.4
27.5°	1983.0	1886.5	1790.9	1702.6	1621.0	1540.4	1451.7	1359.6	1273.3	1198.1	1137.1
30°	1967.1	1861.5	1753.7	1661.7	1577.9	1499.5	1415.7	1325.8	1235.8	1162.2	1096.7
32.5°	1953.0	1829.9	1716.2	1616.0	1527.2	1451.0	1373.7	1288.1	1199.7	1125.1	1059.7
35°	1925.5	1783.1	1652.9	1539.7	1445.0	1366.7	1301.9	1222.1	1141.0	1068.7	1006.0
37.5°	1890.8	1721.7	1582.1	1463.4	1359.6	1277.0	1216.7	1155.5	1077.6	1007.9	951.3
40°	1863.5	1678.1	1530.2	1408.9	1301.2	1215.3	1159.4	1101.5	1036.7	972.0	912.0
42.5°	1829.2	1638.9	1477.8	1347.3	1240.6	1157.0	1098.3	1049.1	992.0	931.6	876.0
45°	1766.1	1567.7	1393.2	1252.8	1145.1	1062.6	1002.0	965.1	922.2	864.9	817.9
47.5°	1673.2	1482.2	1301.7	1156.8	1045.7	969.3	912.4	877.1	846.9	804.3	761.6
50°	1590.8	1418.5	1235.8	1092.0	980.9	903.8	851.3	819.3	793.3	760.6	724.6
52.5°	1498.7	1338.3	1170.8	1028.6	918.7	842.7	791.3	763.2	741.5	718.1	682.6
55°	1352.3	1216.0	1060.6	925.6	824.0	749.7	704.8	680.2	662.6	644.8	623.0
57.5°	1191.0	1084.4	946.7	823.3	729.8	662.3	620.3	596.4	582.6	573.5	560.7
60°	1077.6	986.3	867.7	755.2	663.9	603.9	563.0	544.6	533.0	525.5	515.9
62.5°	972.4	897.4	787.5	684.9	605.0	548.3	511.8	493.9	482.8	479.2	471.3
65°	817.3	759.3	668.6	583.5	515.3	466.9	436.3	419.2	412.3	408.3	409.0
67.5°	664.4	629.1	556.3	483.6	429.3	388.7	364.2	351.0	347.6	342.1	342.0
70°	571.2	544.6	483.2	419.9	371.4	340.1	318.3	304.7	301.2	298.5	297.9
72.5°	488.9	465.5	412.3	361.5	318.0	290.5	272.5	264.3	258.7	257.1	257.0
75°	367.4	354.5	312.1	272.0	242.0	222.9	210.7	203.1	199.0	198.3	199.0
77.5°	261.2	249.8	223.0	194.5	175.6	161.2	150.8	148.1	143.5	143.7	143.0
80°	196.3	188.8	171.8	149.3	133.6	121.3	115.8	111.1	109.8	107.7	109.8
82.5°	142.3	134.3	122.7	108.4	95.4	88.1	82.6	81.1	80.3	79.4	79.8
85°	70.2	70.9	64.0	53.1	47.7	43.6	40.2	40.2	39.5	38.9	39.5
87.5°	26.0	24.6	22.2	20.3	17.3	15.5	14.6	14.8	13.5	13.2	14.0
90°	9.7	8.5	7.3	6.1	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	9.9	8.9	7.9	7.8	8.7	9.7	10.6	11.5	10.6	9.7	8.7
95°	24.6	30.9	37.3	40.7	41.2	41.6	42.1	42.6	42.1	41.6	41.2
97.5°	61.8	74.3	86.8	92.6	91.7	90.9	90.0	89.1	90.0	90.9	91.7
100°	128.9	128.3	127.5	126.9	126.4	125.9	125.4	124.9	125.4	125.9	126.4
102.5°	165.3	164.9	164.5	164.0	163.4	162.8	162.1	161.5	162.1	162.8	163.4
105°	223.0	223.0	223.0	222.7	222.0	221.4	220.7	219.9	220.7	221.4	222.0
107.5°	281.6	281.2	280.9	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7
110°	321.1	320.7	320.4	320.2	320.2	320.2	320.2	320.2	320.2	320.2	320.2





TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	359.7	359.5	359.3	359.0	358.6	358.2	357.8	357.4	357.8	358.2	358.6
115°	417.2	417.1	416.9	416.4	415.6	414.8	413.8	413.0	413.8	414.8	415.6
117.5°	472.1	471.5	470.8	470.5	470.6	470.6	470.6	470.7	470.6	470.6	470.6
120°	507.1	506.5	506.0	505.9	506.0	506.2	506.4	506.5	506.4	506.2	506.0
122.5°	541.7	541.5	541.3	540.9	540.2	539.6	539.0	538.3	539.0	539.6	540.2
125°	592.6	592.6	592.6	592.1	590.9	589.8	588.5	587.4	588.5	589.8	590.9
127.5°	637.7	637.8	637.9	637.5	636.7	635.9	635.1	634.2	635.1	635.9	636.7
130°	667.1	666.9	666.8	666.3	665.5	664.6	663.8	663.0	663.8	664.6	665.5
132.5°	695.1	695.5	695.9	695.6	694.6	693.7	692.7	691.7	692.7	693.7	694.6
135°	736.2	736.6	736.9	736.6	735.6	734.6	733.6	732.6	733.6	734.6	735.6
137.5°	773.3	773.6	773.9	773.6	772.7	771.8	771.0	770.1	771.0	771.8	772.7
140°	795.8	795.9	796.1	796.0	795.7	795.4	795.0	794.7	795.0	795.4	795.7
142.5°	818.3	818.1	817.8	817.6	817.4	817.2	817.0	816.8	817.0	817.2	817.4
145°	850.8	850.8	850.8	850.6	850.3	850.0	849.6	849.3	849.6	850.0	850.3
147.5°	877.9	877.8	877.6	877.5	877.6	877.6	877.7	877.8	877.7	877.6	877.6
150°	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	895.3	895.0	894.6
152.5°	910.6	910.3	909.9	910.1	910.9	911.6	912.3	913.0	912.3	911.6	910.9
155°	931.7	931.4	931.0	931.4	932.3	933.3	934.3	935.3	934.3	933.3	932.3
157.5°	950.0	949.9	949.9	950.2	950.8	951.4	952.0	952.5	952.0	951.4	950.8
160°	960.5	960.3	960.1	960.6	961.5	962.5	963.5	964.5	963.5	962.5	961.5
162.5°	970.1	969.9	969.7	970.1	971.1	972.1	973.1	974.1	973.1	972.1	971.1
165°	982.9	982.7	982.6	983.0	984.0	985.0	985.9	986.9	985.9	985.0	984.0
167.5°	992.3	992.2	992.0	992.4	993.5	994.5	995.5	996.5	995.5	994.5	993.5
170°	997.1	996.9	996.7	997.2	998.5	999.6	1000.8	1002.0	1000.8	999.6	998.5
172.5°	1001.1	1000.8	1000.5	1000.9	1002.0	1003.2	1004.4	1005.5	1004.4	1003.2	1002.0
175°	1005.3	1005.2	1005.0	1005.4	1006.4	1007.4	1008.5	1009.5	1008.5	1007.4	1006.4
177.5°	1007.9	1007.8	1007.6	1008.0	1008.9	1009.7	1010.4	1011.2	1010.4	1009.7	1008.9
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1578.0	1572.1	1567.1	1556.2	1550.2	1542.1	1535.5	1542.6	1535.0	1538.2	1533.4
5°	1528.8	1509.7	1496.1	1476.3	1459.4	1443.6	1432.1	1430.0	1424.5	1421.8	1413.6
7.5°	1469.7	1445.8	1422.4	1396.4	1374.6	1352.4	1338.3	1326.6	1318.8	1308.6	1301.6
10°	1434.8	1402.7	1375.5	1344.1	1316.9	1293.0	1273.9	1264.4	1255.6	1242.5	1237.8
12.5°	1391.7	1358.6	1325.3	1291.8	1265.6	1239.0	1222.6	1208.2	1202.0	1187.5	1186.0
15°	1340.1	1290.3	1257.6	1223.5	1187.4	1165.6	1152.0	1136.2	1129.4	1119.2	1111.7
17.5°	1278.4	1234.0	1193.1	1157.8	1126.8	1108.4	1091.6	1080.8	1069.0	1062.4	1050.1
20°	1233.8	1191.4	1150.5	1113.1	1089.2	1068.0	1054.4	1044.2	1032.0	1028.5	1016.3
22.5°	1196.1	1149.4	1110.2	1078.7	1052.7	1028.9	1014.1	1007.1	998.7	988.2	985.7
25°	1134.9	1086.5	1053.1	1021.8	998.6	976.7	966.5	957.7	949.5	942.0	939.3
27.5°	1082.0	1038.7	999.1	970.8	950.6	930.7	921.7	910.9	904.9	898.9	891.5
30°	1044.9	1000.6	965.8	938.6	916.8	899.1	889.5	882.0	876.6	871.1	867.0
32.5°	1006.7	965.7	932.0	905.3	883.5	870.1	861.7	856.4	850.4	843.8	838.7
35°	956.3	911.3	878.6	855.5	838.4	828.2	818.6	813.9	807.0	807.0	801.5
37.5°	899.5	860.6	831.7	810.6	795.3	786.2	775.8	772.5	768.2	765.3	763.4
40°	865.7	829.5	802.2	781.1	764.8	757.3	749.1	743.7	740.9	737.5	736.1
42.5°	830.7	796.3	770.1	750.6	736.4	730.0	722.4	718.5	713.1	708.6	707.8
45°	777.7	744.3	720.4	704.8	692.5	685.0	680.2	672.1	669.3	663.9	663.2
47.5°	727.4	695.4	672.0	659.1	648.3	642.2	634.7	626.5	623.4	620.7	620.4
50°	689.8	660.5	638.6	626.4	616.2	607.3	599.9	594.4	592.3	592.3	593.7
52.5°	651.7	626.6	608.1	593.1	583.5	574.0	567.1	563.8	560.7	564.0	566.4
55°	595.7	570.5	556.8	542.6	533.0	522.1	518.7	517.4	515.3	520.8	523.5
57.5°	536.5	518.9	502.9	488.7	480.1	473.8	469.2	468.4	472.2	474.8	483.6
60°	499.0	478.5	464.1	453.2	443.0	439.0	437.6	436.3	439.0	446.5	458.1
62.5°	457.5	440.9	425.5	417.3	409.8	402.9	402.7	403.5	409.0	417.6	429.1
65°	396.7	382.3	372.1	362.6	356.5	352.3	353.8	356.5	362.6	374.2	387.2
67.5°	335.0	325.2	316.0	308.2	302.4	302.4	303.8	307.8	315.1	328.4	340.2
70°	295.2	284.3	276.7	273.4	268.5	265.8	269.9	276.7	282.9	295.2	305.4
72.5°	255.3	246.1	240.2	237.9	235.8	233.7	235.0	242.4	250.6	263.0	274.8
75°	196.3	192.9	188.8	186.1	184.0	185.4	186.7	193.6	200.4	213.4	227.0
77.5°	143.3	139.8	137.2	136.6	135.5	136.2	140.0	145.0	151.7	161.2	171.5
80°	108.4	107.0	105.6	104.9	104.9	105.6	111.1	114.5	120.7	129.5	137.6
82.5°	79.0	78.1	77.9	77.7	78.3	78.4	81.7	86.1	91.2	97.9	104.9
85°	41.6	40.2	42.2	42.9	41.6	43.6	44.9	47.7	49.8	53.1	56.6
87.5°	14.8	16.2	15.9	16.7	16.9	18.2	17.9	20.2	21.4	22.7	22.3
90°	6.1	7.3	8.5	9.7	10.8	12.0	12.8	13.6	14.4	15.2	16.0
92.5°	7.8	7.9	8.9	9.9	10.9	12.0	12.8	13.6	14.4	15.2	15.9
95°	40.7	37.3	30.9	24.6	18.3	12.0	12.8	13.6	14.4	15.2	15.8
97.5°	92.6	86.8	74.3	61.8	49.3	36.9	32.1	27.5	22.7	18.1	15.8
100°	126.9	127.5	128.3	128.9	129.6	130.2	105.4	80.7	55.8	31.1	18.4
102.5°	164.0	164.5	164.9	165.3	165.7	166.1	161.5	156.7	152.1	147.3	139.4
105°	222.7	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	223.0	222.9
107.5°	280.7	280.9	281.2	281.6	282.0	282.3	282.3	282.4	282.4	282.4	282.2
110°	320.2	320.4	320.7	321.1	321.4	321.7	321.2	320.7	320.2	319.7	319.6



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	359.0	359.3	359.5	359.7	359.9	360.1	359.4	358.8	358.2	357.5	357.1
115°	416.4	416.9	417.1	417.2	417.4	417.6	416.9	416.2	415.6	414.9	414.0
117.5°	470.5	470.8	471.5	472.1	472.7	473.3	472.5	471.6	470.8	469.9	469.3
120°	505.9	506.0	506.5	507.1	507.6	508.1	507.8	507.5	507.1	506.8	506.1
122.5°	540.9	541.3	541.5	541.7	542.0	542.2	541.9	541.5	541.2	540.9	540.2
125°	592.1	592.6	592.6	592.6	592.6	592.6	592.0	591.3	590.7	590.0	589.4
127.5°	637.5	637.9	637.8	637.7	637.6	637.5	637.1	636.8	636.4	636.1	635.3
130°	666.3	666.8	666.9	667.1	667.3	667.4	666.9	666.5	666.0	665.5	664.8
132.5°	695.6	695.9	695.5	695.1	694.8	694.4	694.3	694.2	694.1	694.0	693.6
135°	736.6	736.9	736.6	736.2	735.9	735.6	735.2	734.9	734.6	734.3	733.6
137.5°	773.6	773.9	773.6	773.3	773.0	772.6	772.7	772.8	772.8	773.0	772.5
140°	796.0	796.1	795.9	795.8	795.6	795.4	795.8	796.1	796.4	796.8	796.4
142.5°	817.6	817.8	818.1	818.3	818.5	818.8	818.8	818.9	819.0	819.0	818.6
145°	850.6	850.8	850.8	850.8	850.8	850.8	850.9	851.1	851.3	851.4	851.0
147.5°	877.5	877.6	877.8	877.9	878.1	878.3	878.5	878.7	878.9	879.1	878.6
150°	894.3	894.3	894.6	895.0	895.3	895.6	896.1	896.4	896.7	897.1	896.6
152.5°	910.1	909.9	910.3	910.6	910.9	911.2	911.6	911.9	912.2	912.6	912.1
155°	931.4	931.0	931.4	931.7	932.0	932.3	932.8	933.3	933.8	934.3	933.9
157.5°	950.2	949.9	949.9	950.0	950.0	950.0	950.6	951.1	951.6	952.1	951.7
160°	960.6	960.1	960.3	960.5	960.6	960.8	961.5	962.1	962.8	963.4	963.1
162.5°	970.1	969.7	969.9	970.1	970.2	970.4	971.3	972.2	973.1	974.1	973.8
165°	983.0	982.6	982.7	982.9	983.1	983.2	984.2	985.2	986.2	987.2	987.0
167.5°	992.4	992.0	992.2	992.3	992.5	992.7	993.8	995.0	996.2	997.4	997.3
170°	997.2	996.7	996.9	997.1	997.2	997.4	998.8	1000.1	1001.5	1002.8	1002.7
172.5°	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8	1004.0	1005.2	1006.4	1006.2
175°	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0	1008.4	1009.7	1011.0	1010.9
177.5°	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2	1010.1	1011.0	1012.0	1011.9
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1530.0	1533.9	1530.7	1535.0	1530.7	1533.9	1530.0	1533.4	1538.2	1535.0	1542.6
5°	1410.3	1404.1	1408.2	1405.4	1408.2	1404.1	1410.3	1413.6	1421.8	1424.5	1430.0
7.5°	1299.6	1293.7	1287.0	1283.8	1287.0	1293.7	1299.6	1301.6	1308.6	1318.8	1326.6
10°	1230.3	1222.8	1222.1	1217.4	1222.1	1222.8	1230.3	1237.8	1242.5	1255.6	1264.4
12.5°	1179.6	1172.7	1164.9	1162.9	1164.9	1172.7	1179.6	1186.0	1187.5	1202.0	1208.2
15°	1107.6	1102.2	1097.4	1101.5	1097.4	1102.2	1107.6	1111.7	1119.2	1129.4	1136.2
17.5°	1047.7	1043.3	1042.5	1037.4	1042.5	1043.3	1047.7	1050.1	1062.4	1069.0	1080.8
20°	1010.2	1006.7	1008.1	999.3	1008.1	1006.7	1010.2	1016.3	1028.5	1032.0	1044.2
22.5°	980.2	973.5	972.7	970.9	972.7	973.5	980.2	985.7	988.2	998.7	1007.1
25°	933.1	929.7	926.3	929.7	926.3	929.7	933.1	939.3	942.0	949.5	957.7
27.5°	892.1	888.0	887.1	887.5	887.1	888.0	892.1	891.5	898.9	904.9	910.9
30°	867.0	860.2	860.9	860.2	860.9	860.2	867.0	867.0	871.1	876.6	882.0
32.5°	839.7	835.1	834.1	832.9	834.1	835.1	839.7	838.7	843.8	850.4	856.4
35°	799.5	799.5	796.1	796.1	796.1	799.5	799.5	801.5	807.0	807.0	813.9
37.5°	761.7	761.0	759.0	759.3	759.0	761.0	761.7	763.4	765.3	768.2	772.5
40°	733.4	732.8	730.6	726.6	730.6	732.8	733.4	736.1	737.5	740.9	743.7
42.5°	706.1	703.9	702.9	701.6	702.9	703.9	706.1	707.8	708.6	713.1	718.5
45°	663.2	663.2	661.9	661.2	661.9	663.2	663.2	663.2	663.9	669.3	672.1
47.5°	621.5	622.7	625.3	624.9	625.3	622.7	621.5	620.4	620.7	623.4	626.5
50°	596.4	597.1	599.2	599.9	599.2	597.1	596.4	593.7	592.3	592.3	594.4
52.5°	568.6	572.6	575.1	574.7	575.1	572.6	568.6	566.4	564.0	560.7	563.8
55°	529.6	534.4	539.2	539.9	539.2	534.4	529.6	523.5	520.8	515.3	517.4
57.5°	491.0	497.7	502.7	504.4	502.7	497.7	491.0	483.6	474.8	472.2	468.4
60°	464.8	473.7	479.9	482.6	479.9	473.7	464.8	458.1	446.5	439.0	436.3
62.5°	439.8	449.7	455.9	456.4	455.9	449.7	439.8	429.1	417.6	409.0	403.5
65°	398.7	409.0	414.4	418.5	414.4	409.0	398.7	387.2	374.2	362.6	356.5
67.5°	354.6	364.8	370.8	374.1	370.8	364.8	354.6	340.2	328.4	315.1	307.8
70°	322.4	332.6	340.8	343.6	340.8	332.6	322.4	305.4	295.2	282.9	276.7
72.5°	290.7	299.9	306.5	309.7	306.5	299.9	290.7	274.8	263.0	250.6	242.4
75°	235.8	248.1	254.3	257.6	254.3	248.1	235.8	227.0	213.4	200.4	193.6
77.5°	181.9	193.0	196.7	198.4	196.7	193.0	181.9	171.5	161.2	151.7	145.0
80°	145.8	152.7	157.4	158.1	157.4	152.7	145.8	137.6	129.5	120.7	114.5
82.5°	112.1	117.8	119.3	121.1	119.3	117.8	112.1	104.9	97.9	91.2	86.1
85°	61.3	64.0	64.7	64.0	64.7	64.0	61.3	56.6	53.1	49.8	47.7
87.5°	23.4	23.0	23.1	24.3	23.1	23.0	23.4	22.3	22.7	21.4	20.2
90°	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.2	14.4	13.6
92.5°	16.1	16.3	16.6	16.8	16.6	16.3	16.1	15.9	15.2	14.4	13.6
95°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.2	14.4	13.6
97.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	18.1	22.7	27.5
100°	17.7	17.1	16.4	15.8	16.4	17.1	17.7	18.4	31.1	55.8	80.7
102.5°	128.1	116.7	105.4	94.1	105.4	116.7	128.1	139.4	147.3	152.1	156.7
105°	222.8	222.6	222.4	222.3	222.4	222.6	222.8	222.9	223.0	223.0	223.0
107.5°	281.7	281.1	280.6	280.1	280.6	281.1	281.7	282.2	282.4	282.4	282.4
110°	319.7	319.9	320.1	320.2	320.1	319.9	319.7	319.6	319.7	320.2	320.7



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	356.9	356.7	356.4	356.2	356.4	356.7	356.9	357.1	357.5	358.2	358.8
115°	413.0	412.0	411.0	410.0	411.0	412.0	413.0	414.0	414.9	415.6	416.2
117.5°	468.8	468.4	468.0	467.6	468.0	468.4	468.8	469.3	469.9	470.8	471.6
120°	505.3	504.5	503.7	502.8	503.7	504.5	505.3	506.1	506.8	507.1	507.5
122.5°	539.3	538.3	537.3	536.3	537.3	538.3	539.3	540.2	540.9	541.2	541.5
125°	588.9	588.3	587.9	587.4	587.9	588.3	588.9	589.4	590.0	590.7	591.3
127.5°	634.0	632.8	631.6	630.4	631.6	632.8	634.0	635.3	636.1	636.4	636.8
130°	664.0	663.2	662.3	661.5	662.3	663.2	664.0	664.8	665.5	666.0	666.5
132.5°	692.7	691.9	691.1	690.2	691.1	691.9	692.7	693.6	694.0	694.1	694.2
135°	732.6	731.5	730.5	729.5	730.5	731.5	732.6	733.6	734.3	734.6	734.9
137.5°	771.6	770.8	769.9	769.1	769.9	770.8	771.6	772.5	773.0	772.8	772.8
140°	795.4	794.5	793.5	792.4	793.5	794.5	795.4	796.4	796.8	796.4	796.1
142.5°	817.6	816.6	815.6	814.6	815.6	816.6	817.6	818.6	819.0	819.0	818.9
145°	850.0	849.0	848.1	847.1	848.1	849.0	850.0	851.0	851.4	851.3	851.1
147.5°	877.5	876.3	875.0	873.8	875.0	876.3	877.5	878.6	879.1	878.9	878.7
150°	895.1	893.8	892.5	891.2	892.5	893.8	895.1	896.6	897.1	896.7	896.4
152.5°	910.9	909.8	908.6	907.4	908.6	909.8	910.9	912.1	912.6	912.2	911.9
155°	932.6	931.3	930.0	928.6	930.0	931.3	932.6	933.9	934.3	933.8	933.3
157.5°	950.4	949.1	947.8	946.4	947.8	949.1	950.4	951.7	952.1	951.6	951.1
160°	961.8	960.5	959.2	957.8	959.2	960.5	961.8	963.1	963.4	962.8	962.1
162.5°	972.4	970.9	969.5	968.0	969.5	970.9	972.4	973.8	974.1	973.1	972.2
165°	985.7	984.4	983.1	981.7	983.1	984.4	985.7	987.0	987.2	986.2	985.2
167.5°	995.8	994.3	992.8	991.3	992.8	994.3	995.8	997.3	997.4	996.2	995.0
170°	1001.2	999.7	998.2	996.7	998.2	999.7	1001.2	1002.7	1002.8	1001.5	1000.1
172.5°	1004.8	1003.3	1001.8	1000.3	1001.8	1003.3	1004.8	1006.2	1006.4	1005.2	1004.0
175°	1009.5	1007.9	1006.4	1004.9	1006.4	1007.9	1009.5	1010.9	1011.0	1009.7	1008.4
177.5°	1010.8	1009.8	1008.7	1007.6	1008.7	1009.8	1010.8	1011.9	1012.0	1011.0	1010.1
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1535.5	1542.1	1550.2	1556.2	1567.1	1572.1	1578.0	1583.0	1591.6	1599.8	1609.7
5°	1432.1	1443.6	1459.4	1476.3	1496.1	1509.7	1528.8	1540.4	1563.6	1584.8	1605.2
7.5°	1338.3	1352.4	1374.6	1396.4	1422.4	1445.8	1469.7	1496.1	1525.7	1560.6	1589.5
10°	1273.9	1293.0	1316.9	1344.1	1375.5	1402.7	1434.8	1463.4	1499.5	1540.4	1578.6
12.5°	1222.6	1239.0	1265.6	1291.8	1325.3	1358.6	1391.7	1429.6	1471.8	1517.0	1565.0
15°	1152.0	1165.6	1187.4	1223.5	1257.6	1290.3	1340.1	1375.5	1428.7	1479.0	1537.0
17.5°	1091.6	1108.4	1126.8	1157.8	1193.1	1234.0	1278.4	1322.8	1374.1	1438.0	1503.4
20°	1054.4	1068.0	1089.2	1113.1	1150.5	1191.4	1233.8	1278.7	1341.4	1407.5	1477.7
22.5°	1014.1	1028.9	1052.7	1078.7	1110.2	1149.4	1196.1	1245.5	1310.9	1375.9	1452.1
25°	966.5	976.7	998.6	1021.8	1053.1	1086.5	1134.9	1189.4	1254.2	1328.5	1406.1
27.5°	921.7	930.7	950.6	970.8	999.1	1038.7	1082.0	1137.1	1198.1	1273.3	1359.6
30°	889.5	899.1	916.8	938.6	965.8	1000.6	1044.9	1096.7	1162.2	1235.8	1325.8
32.5°	861.7	870.1	883.5	905.3	932.0	965.7	1006.7	1059.7	1125.1	1199.7	1288.1
35°	818.6	828.2	838.4	855.5	878.6	911.3	956.3	1006.0	1068.7	1141.0	1222.1
37.5°	775.8	786.2	795.3	810.6	831.7	860.6	899.5	951.3	1007.9	1077.6	1155.5
40°	749.1	757.3	764.8	781.1	802.2	829.5	865.7	912.0	972.0	1036.7	1101.5
42.5°	722.4	730.0	736.4	750.6	770.1	796.3	830.7	876.0	931.6	992.0	1049.1
45°	680.2	685.0	692.5	704.8	720.4	744.3	777.7	817.9	864.9	922.2	965.1
47.5°	634.7	642.2	648.3	659.1	672.0	695.4	727.4	761.6	804.3	846.9	877.1
50°	599.9	607.3	616.2	626.4	638.6	660.5	689.8	724.6	760.6	793.3	819.3
52.5°	567.1	574.0	583.5	593.1	608.1	626.6	651.7	682.6	718.1	741.5	763.2
55°	518.7	522.1	533.0	542.6	556.8	570.5	595.7	623.0	644.8	662.6	680.2
57.5°	469.2	473.8	480.1	488.7	502.9	518.9	536.5	560.7	573.5	582.6	596.4
60°	437.6	439.0	443.0	453.2	464.1	478.5	499.0	515.9	525.5	533.0	544.6
62.5°	402.7	402.9	409.8	417.3	425.5	440.9	457.5	471.3	479.2	482.8	493.9
65°	353.8	352.3	356.5	362.6	372.1	382.3	396.7	409.0	408.3	412.3	419.2
67.5°	303.8	302.4	302.4	308.2	316.0	325.2	335.0	342.0	342.1	347.6	351.0
70°	269.9	265.8	268.5	273.4	276.7	284.3	295.2	297.9	298.5	301.2	304.7
72.5°	235.0	233.7	235.8	237.9	240.2	246.1	255.3	257.0	257.1	258.7	264.3
75°	186.7	185.4	184.0	186.1	188.8	192.9	196.3	199.0	198.3	199.0	203.1
77.5°	140.0	136.2	135.5	136.6	137.2	139.8	143.3	143.0	143.7	143.5	148.1
80°	111.1	105.6	104.9	104.9	105.6	107.0	108.4	109.8	107.7	109.8	111.1
82.5°	81.7	78.4	78.3	77.7	77.9	78.1	79.0	79.8	79.4	80.3	81.1
85°	44.9	43.6	41.6	42.9	42.2	40.2	41.6	39.5	38.9	39.5	40.2
87.5°	17.9	18.2	16.9	16.7	15.9	16.2	14.8	14.0	13.2	13.5	14.8
90°	12.8	12.0	10.8	9.7	8.5	7.3	6.1	4.7	3.4	2.1	0.7
92.5°	12.8	12.0	10.9	9.9	8.9	7.9	7.8	8.7	9.7	10.6	11.5
95°	12.8	12.0	18.3	24.6	30.9	37.3	40.7	41.2	41.6	42.1	42.6
97.5°	32.1	36.9	49.3	61.8	74.3	86.8	92.6	91.7	90.9	90.0	89.1
100°	105.4	130.2	129.6	128.9	128.3	127.5	126.9	126.4	125.9	125.4	124.9
102.5°	161.5	166.1	165.7	165.3	164.9	164.5	164.0	163.4	162.8	162.1	161.5
105°	223.0	223.0	223.0	223.0	223.0	223.0	222.7	222.0	221.4	220.7	219.9
107.5°	282.3	282.3	282.0	281.6	281.2	280.9	280.7	280.7	280.7	280.7	280.7
110°	321.2	321.7	321.4	321.1	320.7	320.4	320.2	320.2	320.2	320.2	320.2



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	360.1	359.9	359.7	359.5	359.3	359.0	358.6	358.2	357.8	357.4
115°	416.9	417.6	417.4	417.2	417.1	416.9	416.4	415.6	414.8	413.8	413.0
117.5°	472.5	473.3	472.7	472.1	471.5	470.8	470.5	470.6	470.6	470.6	470.7
120°	507.8	508.1	507.6	507.1	506.5	506.0	505.9	506.0	506.2	506.4	506.5
122.5°	541.9	542.2	542.0	541.7	541.5	541.3	540.9	540.2	539.6	539.0	538.3
125°	592.0	592.6	592.6	592.6	592.6	592.6	592.1	590.9	589.8	588.5	587.4
127.5°	637.1	637.5	637.6	637.7	637.8	637.9	637.5	636.7	635.9	635.1	634.2
130°	666.9	667.4	667.3	667.1	666.9	666.8	666.3	665.5	664.6	663.8	663.0
132.5°	694.3	694.4	694.8	695.1	695.5	695.9	695.6	694.6	693.7	692.7	691.7
135°	735.2	735.6	735.9	736.2	736.6	736.9	736.6	735.6	734.6	733.6	732.6
137.5°	772.7	772.6	773.0	773.3	773.6	773.9	773.6	772.7	771.8	771.0	770.1
140°	795.8	795.4	795.6	795.8	795.9	796.1	796.0	795.7	795.4	795.0	794.7
142.5°	818.8	818.8	818.5	818.3	818.1	817.8	817.6	817.4	817.2	817.0	816.8
145°	850.9	850.8	850.8	850.8	850.8	850.8	850.6	850.3	850.0	849.6	849.3
147.5°	878.5	878.3	878.1	877.9	877.8	877.6	877.5	877.6	877.6	877.7	877.8
150°	896.1	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6
152.5°	911.6	911.2	910.9	910.6	910.3	909.9	910.1	910.9	911.6	912.3	913.0
155°	932.8	932.3	932.0	931.7	931.4	931.0	931.4	932.3	933.3	934.3	935.3
157.5°	950.6	950.0	950.0	950.0	949.9	949.9	950.2	950.8	951.4	952.0	952.5
160°	961.5	960.8	960.6	960.5	960.3	960.1	960.6	961.5	962.5	963.5	964.5
162.5°	971.3	970.4	970.2	970.1	969.9	969.7	970.1	971.1	972.1	973.1	974.1
165°	984.2	983.2	983.1	982.9	982.7	982.6	983.0	984.0	985.0	985.9	986.9
167.5°	993.8	992.7	992.5	992.3	992.2	992.0	992.4	993.5	994.5	995.5	996.5
170°	998.8	997.4	997.2	997.1	996.9	996.7	997.2	998.5	999.6	1000.8	1002.0
172.5°	1002.8	1001.7	1001.4	1001.1	1000.8	1000.5	1000.9	1002.0	1003.2	1004.4	1005.5
175°	1007.0	1005.7	1005.5	1005.3	1005.2	1005.0	1005.4	1006.4	1007.4	1008.5	1009.5
177.5°	1009.2	1008.2	1008.0	1007.9	1007.8	1007.6	1008.0	1008.9	1009.7	1010.4	1011.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1614.6	1622.2	1627.1	1636.4	1644.1	1648.4	1652.2	1655.5	1659.3	1662.5	1671.8
5°	1625.0	1642.6	1657.7	1680.8	1702.0	1718.4	1736.1	1751.7	1764.6	1783.1	1797.4
7.5°	1620.4	1651.9	1685.0	1720.8	1757.5	1791.5	1822.9	1852.2	1878.8	1911.0	1939.1
10°	1616.1	1659.0	1701.3	1749.7	1799.5	1841.7	1881.3	1921.5	1950.8	1991.7	2026.4
12.5°	1612.9	1663.3	1714.3	1772.6	1827.2	1886.9	1939.5	1968.9	2013.5	2046.2	2087.5
15°	1599.0	1665.9	1736.1	1801.5	1879.2	1934.4	1980.7	2038.0	2079.6	2121.1	2166.2
17.5°	1574.4	1650.0	1728.6	1814.3	1888.9	1948.1	2007.9	2063.1	2112.7	2168.5	2224.5
20°	1563.0	1638.6	1728.6	1816.4	1889.5	1951.5	2012.8	2073.5	2128.0	2199.6	2264.3
22.5°	1538.9	1630.4	1713.3	1799.1	1874.1	1941.7	2011.1	2080.0	2152.5	2233.3	2314.5
25°	1496.1	1588.8	1676.8	1761.3	1836.9	1921.5	1995.8	2087.8	2180.5	2287.4	2388.3
27.5°	1451.7	1540.4	1621.0	1702.6	1790.9	1886.5	1983.0	2087.4	2208.7	2343.8	2486.1
30°	1415.7	1499.5	1577.9	1661.7	1753.7	1861.5	1967.1	2091.1	2231.6	2383.6	2552.6
32.5°	1373.7	1451.0	1527.2	1616.0	1716.2	1829.9	1953.0	2089.0	2257.8	2430.4	2604.4
35°	1301.9	1366.7	1445.0	1539.7	1652.9	1783.1	1925.5	2086.4	2280.0	2478.3	2624.8
37.5°	1216.7	1277.0	1359.6	1463.4	1582.1	1721.7	1890.8	2081.6	2287.2	2445.4	2492.6
40°	1159.4	1215.3	1301.2	1408.9	1530.2	1678.1	1863.5	2065.3	2264.3	2365.2	2326.3
42.5°	1098.3	1157.0	1240.6	1347.3	1477.8	1638.9	1829.2	2030.9	2197.8	2235.9	2101.6
45°	1002.0	1062.6	1145.1	1252.8	1393.2	1567.7	1766.1	1949.4	2045.5	1976.7	1768.8
47.5°	912.4	969.3	1045.7	1156.8	1301.7	1482.2	1673.2	1819.5	1827.1	1662.8	1440.8
50°	851.3	903.8	980.9	1092.0	1235.8	1418.5	1590.8	1706.1	1654.3	1468.1	1254.9
52.5°	791.3	842.7	918.7	1028.6	1170.8	1338.3	1498.7	1579.5	1482.0	1291.0	1108.7
55°	704.8	749.7	824.0	925.6	1060.6	1216.0	1352.3	1380.3	1253.4	1065.3	917.5
57.5°	620.3	662.3	729.8	823.3	946.7	1084.4	1191.0	1185.1	1051.1	889.6	772.2
60°	563.0	603.9	663.9	755.2	867.7	986.3	1077.6	1055.8	922.9	783.9	685.0
62.5°	511.8	548.3	605.0	684.9	787.5	897.4	972.4	940.2	810.0	688.4	610.4
65°	436.3	466.9	515.3	583.5	668.6	759.3	817.3	775.7	664.6	569.9	507.2
67.5°	364.2	388.7	429.3	483.6	556.3	629.1	664.4	622.6	533.7	464.5	418.1
70°	318.3	340.1	371.4	419.9	483.2	544.6	571.2	533.7	457.4	398.1	364.7
72.5°	272.5	290.5	318.0	361.5	412.3	465.5	488.9	453.0	390.3	340.2	309.0
75°	210.7	222.9	242.0	272.0	312.1	354.5	367.4	336.1	295.8	258.3	237.9
77.5°	150.8	161.2	175.6	194.5	223.0	249.8	261.2	243.1	212.0	188.2	171.5
80°	115.8	121.3	133.6	149.3	171.8	188.8	196.3	184.7	162.9	145.2	132.2
82.5°	82.6	88.1	95.4	108.4	122.7	134.3	142.3	134.5	118.8	104.8	97.4
85°	40.2	43.6	47.7	53.1	64.0	70.9	70.2	65.4	59.3	53.8	49.8
87.5°	14.6	15.5	17.3	20.3	22.2	24.6	26.0	25.0	23.1	21.6	20.2
90°	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8	13.6
92.5°	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8	13.6
95°	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8	13.6
97.5°	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1	27.5
100°	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4	80.7
102.5°	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5	156.7
105°	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3	282.4
110°	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2	320.7





TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4	358.8
115°	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9	416.2
117.5°	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5	471.6
120°	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8	507.5
122.5°	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9	541.5
125°	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0	591.3
127.5°	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1	636.8
130°	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9	666.5
132.5°	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3	694.2
135°	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2	734.9
137.5°	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7	772.8
140°	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8	796.1
142.5°	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8	818.9
145°	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9	851.1
147.5°	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5	878.7
150°	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1	896.4
152.5°	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6	911.9
155°	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8	933.3
157.5°	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6	951.1
160°	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5	962.1
162.5°	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3	972.2
165°	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2	985.2
167.5°	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8	995.0
170°	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8	1000.1
172.5°	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8	1004.0
175°	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0	1008.4
177.5°	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2	1010.1
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9	1605.9
2.5°	1679.5	1683.8	1693.1	1689.8	1694.3	1696.4	1698.6
5°	1815.1	1836.9	1846.4	1845.1	1859.5	1856.0	1852.6
7.5°	1968.3	1991.3	2004.1	2020.0	2029.3	2029.9	2038.0
10°	2055.1	2085.1	2097.3	2114.4	2125.3	2131.4	2130.7
12.5°	2121.6	2145.1	2172.5	2180.9	2195.6	2203.3	2200.5
15°	2201.6	2239.1	2267.8	2282.0	2300.5	2305.9	2313.4
17.5°	2273.0	2323.3	2356.7	2401.2	2417.9	2428.1	2422.2
20°	2327.0	2393.2	2426.5	2479.7	2509.0	2524.7	2519.2
22.5°	2390.9	2462.4	2524.2	2570.2	2614.7	2635.9	2640.3
25°	2500.1	2598.3	2689.0	2749.7	2804.8	2817.7	2846.4
27.5°	2622.3	2738.0	2835.0	2898.7	2937.2	2951.6	2960.6
30°	2699.2	2814.4	2887.3	2928.2	2940.4	2939.1	2937.7
32.5°	2736.8	2808.9	2823.0	2811.5	2783.4	2759.7	2734.9
35°	2683.5	2629.7	2549.2	2445.6	2369.2	2292.3	2284.7
37.5°	2413.5	2241.3	2107.4	1957.8	1871.6	1818.3	1781.5
40°	2159.3	1963.7	1801.5	1675.4	1587.5	1552.7	1518.6
42.5°	1883.4	1696.6	1552.9	1447.4	1381.4	1342.8	1315.8
45°	1530.2	1365.2	1252.8	1176.5	1124.0	1094.0	1076.9
47.5°	1253.8	1131.9	1036.3	981.3	945.0	921.7	921.8
50°	1105.6	989.1	925.6	882.0	850.6	832.2	835.7
52.5°	974.1	887.1	832.9	796.4	773.3	761.9	761.5
55°	814.6	751.8	716.4	689.8	674.1	661.2	663.9
57.5°	696.7	643.9	620.2	598.0	587.1	582.0	574.4
60°	623.7	582.8	562.3	544.6	533.7	529.6	522.1
62.5°	558.8	526.6	506.8	492.2	482.4	481.1	475.2
65°	469.6	445.0	427.4	420.5	410.3	407.6	407.6
67.5°	387.2	369.6	355.8	349.5	345.1	345.7	342.4
70°	335.4	321.0	312.1	305.4	301.9	302.7	299.9
72.5°	293.4	277.4	269.6	265.6	261.1	262.9	261.8
75°	222.2	214.0	210.0	205.8	203.1	201.8	200.4
77.5°	163.2	155.9	152.8	150.5	150.9	147.6	150.3
80°	126.1	120.0	118.0	114.5	113.8	113.8	113.1
82.5°	92.3	88.9	87.4	84.5	83.3	84.4	82.6
85°	47.7	44.9	44.3	44.3	42.9	41.6	44.9
87.5°	20.3	18.3	18.5	18.0	18.1	17.7	16.7
90°	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.2	319.7	319.6	319.7	319.9	320.1	320.2



TEST NUMBER: P333436-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)