

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333440-840

Luminaire Tested: **S125DIW-S1090D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333440-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7585.9 lumens
Efficiency: N/A
Efficacy: 141.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59								
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50								
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42								
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35								
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	33	30								
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26								
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23								
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20								
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18								
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16								
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11129	11129	11129
5°	11154	11048	11119
10°	11086	10970	11032
15°	10965	10838	10884
20°	10794	10653	10672
25°	10608	10434	10424
30°	10380	10197	10147
35°	10136	9942	9802
40°	9885	9666	9528
45°	9613	9414	9227
50°	9315	9109	8835
55°	9026	8765	8519
60°	8681	8418	8117
65°	8270	8000	7728
70°	7878	7517	7260
75°	7177	6939	6700
80°	6390	6289	6133
85°	5550	5654	5350



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.1
10°-20°	459.0	6.1
20°-30°	677.7	8.9
30°-40°	790.7	10.4
40°-50°	794.2	10.5
50°-60°	697.1	9.2
60°-70°	519.5	6.8
70°-80°	297.0	3.9
80°-90°	88.5	1.2
90°-100°	36.7	0.5
100°-110°	226.1	3.0
110°-120°	410.0	5.4
120°-130°	526.2	6.9
130°-140°	566.0	7.5
140°-150°	531.3	7.0
150°-160°	429.7	5.7
160°-170°	277.9	3.7
170°-180°	95.9	1.3
0°-30°	1299.1	17.1
0°-40°	2089.8	27.5
0°-60°	3581.2	47.2
0°-90°	4486.1	59.1
90°-120°	672.8	8.9
90°-150°	2296.2	30.3
90°-180°	3100.0	40.9
0°-180°	7585.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1720	1717	1704	1716	1715	163
15°	1640	1635	1621	1627	1628	462
25°	1489	1481	1464	1466	1463	685
35°	1286	1279	1261	1254	1243	804
45°	1052	1046	1031	1015	1010	811
55°	802	797	778	766	757	715
65°	541	538	524	512	506	537
75°	288	285	278	274	268	307
85°	75	76	76	75	72	84
90°	1	7	12	16	18	6
95°	43	39	12	16	16	54
105°	220	223	223	223	222	233
115°	413	417	418	414	410	409
125°	587	592	593	590	587	524
135°	733	737	736	734	730	564
145°	849	851	851	851	847	531
155°	935	931	932	934	929	431
165°	987	983	983	987	982	279
175°	1010	1005	1006	1011	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1727.6	1726.9	1726.1	1725.4	1724.6	1723.0	1720.6	1718.2	1715.8	1713.3	1715.8
5°	1720.5	1719.9	1719.3	1718.7	1718.1	1716.3	1713.2	1710.2	1707.2	1704.1	1706.9
7.5°	1704.7	1704.0	1703.4	1702.8	1702.2	1700.2	1696.9	1693.5	1690.2	1686.9	1689.6
10°	1690.5	1689.9	1689.3	1688.7	1688.1	1686.1	1682.7	1679.4	1676.1	1672.7	1675.2
12.5°	1673.0	1671.9	1670.8	1669.7	1668.7	1666.6	1663.4	1660.4	1657.3	1654.2	1656.2
15°	1640.0	1639.1	1638.2	1637.3	1636.4	1634.3	1630.9	1627.6	1624.3	1620.9	1622.4
17.5°	1602.2	1600.8	1599.4	1598.1	1596.8	1594.4	1590.9	1587.5	1584.1	1580.5	1582.5
20°	1570.5	1569.9	1569.3	1568.7	1568.1	1565.8	1561.9	1557.9	1554.0	1550.0	1552.2
22.5°	1538.8	1537.8	1536.7	1535.6	1534.5	1532.1	1528.4	1524.7	1521.1	1517.3	1518.7
25°	1488.7	1487.2	1485.7	1484.2	1482.7	1480.0	1476.0	1472.1	1468.1	1464.2	1464.8
27.5°	1430.1	1429.2	1428.3	1427.3	1426.4	1424.0	1419.9	1415.8	1411.8	1407.8	1407.9
30°	1391.9	1391.0	1390.1	1389.2	1388.3	1385.5	1381.0	1376.4	1371.9	1367.4	1366.8
32.5°	1350.5	1349.1	1347.7	1346.3	1344.9	1342.2	1338.1	1334.0	1330.0	1326.0	1324.8
35°	1285.6	1284.3	1283.1	1281.9	1280.7	1278.0	1273.7	1269.5	1265.3	1261.0	1259.5
37.5°	1218.2	1216.7	1215.2	1213.7	1212.1	1209.4	1205.4	1201.4	1197.4	1193.5	1191.1
40°	1172.5	1170.9	1169.4	1167.9	1166.4	1163.5	1159.2	1155.0	1150.7	1146.5	1143.8
42.5°	1123.4	1122.1	1120.8	1119.5	1118.2	1115.5	1111.3	1107.0	1102.8	1098.5	1096.0
45°	1052.5	1051.3	1050.1	1048.8	1047.6	1045.2	1041.6	1037.9	1034.3	1030.7	1027.0
47.5°	976.1	976.1	976.2	976.3	976.3	974.2	969.9	965.4	961.1	956.7	953.0
50°	927.1	926.1	925.2	924.3	923.4	921.1	917.5	913.8	910.2	906.6	902.6
52.5°	876.9	876.2	875.6	874.8	874.2	871.9	868.1	864.1	860.3	856.4	852.9
55°	801.6	800.7	799.8	798.9	798.0	795.4	791.1	786.9	782.6	778.4	775.7
57.5°	722.3	721.8	721.3	720.8	720.3	718.3	714.7	711.1	707.6	704.0	700.4
60°	672.1	670.9	669.6	668.4	667.2	665.0	661.7	658.3	655.0	651.7	648.6
62.5°	619.8	618.7	617.8	616.8	615.9	614.0	611.1	608.2	605.4	602.6	599.3
65°	541.2	540.6	540.0	539.4	538.8	536.8	533.5	530.2	526.8	523.5	520.8
67.5°	465.1	463.8	462.6	461.3	460.1	458.2	455.7	453.2	450.7	448.3	446.0
70°	417.2	415.7	414.1	412.6	411.1	409.0	406.3	403.5	400.8	398.1	396.3
72.5°	364.9	363.8	362.7	361.7	360.7	359.3	357.6	355.8	354.1	352.2	350.2
75°	287.6	287.0	286.4	285.8	285.2	284.2	282.7	281.1	279.6	278.1	277.2
77.5°	216.5	216.2	216.0	215.8	215.5	215.0	214.1	213.3	212.5	211.6	211.1
80°	171.8	171.8	171.8	171.8	171.8	171.5	170.9	170.3	169.7	169.1	168.7
82.5°	132.5	132.0	131.6	131.1	130.6	130.3	130.2	130.1	129.9	129.8	129.3
85°	74.9	75.2	75.5	75.8	76.1	76.3	76.3	76.3	76.3	76.3	76.0
87.5°	29.6	29.9	30.1	30.4	30.7	30.8	30.8	30.8	30.8	30.8	30.9
90°	0.7	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8
92.5°	11.5	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8
95°	42.6	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8
97.5°	89.1	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1
100°	124.9	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4
102.5°	161.5	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5
105°	219.9	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3
110°	320.2	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.4	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4
115°	413.0	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9
117.5°	470.7	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5
120°	506.5	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8
122.5°	538.3	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9
125°	587.4	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0
127.5°	634.2	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1
130°	663.0	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9
132.5°	691.7	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3
135°	732.6	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2
137.5°	770.1	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7
140°	794.7	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8
142.5°	816.8	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8
145°	849.3	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9
147.5°	877.8	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5
150°	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1
152.5°	913.0	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6
155°	935.3	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8
157.5°	952.5	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6
160°	964.5	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5
162.5°	974.1	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3
165°	986.9	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2
167.5°	996.5	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8
170°	1002.0	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8
172.5°	1005.5	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8
175°	1009.5	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0
177.5°	1011.2	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1718.2	1720.6	1723.0	1724.1	1723.9	1723.6	1723.4	1723.2
5°	1709.6	1712.3	1715.1	1716.3	1716.0	1715.7	1715.4	1715.1
7.5°	1692.2	1695.0	1697.6	1698.8	1698.5	1698.2	1697.9	1697.6
10°	1677.6	1680.0	1682.4	1683.5	1683.2	1682.9	1682.6	1682.3
12.5°	1658.1	1660.0	1661.9	1662.9	1662.8	1662.7	1662.7	1662.6
15°	1624.0	1625.5	1627.0	1627.8	1627.8	1627.8	1627.8	1627.8
17.5°	1584.4	1586.2	1588.1	1588.3	1586.8	1585.3	1583.8	1582.3
20°	1554.3	1556.4	1558.5	1558.8	1557.3	1555.8	1554.3	1552.8
22.5°	1520.1	1521.6	1522.9	1523.1	1522.1	1521.1	1520.0	1518.9
25°	1465.4	1466.0	1466.6	1466.4	1465.5	1464.6	1463.7	1462.8
27.5°	1408.0	1408.1	1408.3	1407.9	1406.9	1406.0	1405.1	1404.2
30°	1366.1	1365.5	1364.9	1364.2	1363.3	1362.4	1361.5	1360.6
32.5°	1323.7	1322.6	1321.6	1320.2	1318.6	1317.0	1315.2	1313.6
35°	1258.0	1256.5	1255.0	1253.0	1250.6	1248.2	1245.8	1243.3
37.5°	1188.9	1186.7	1184.5	1182.7	1181.2	1179.8	1178.4	1177.1
40°	1141.0	1138.3	1135.6	1133.8	1132.9	1132.0	1131.0	1130.1
42.5°	1093.6	1091.1	1088.6	1086.6	1085.3	1083.9	1082.5	1081.1
45°	1023.4	1019.8	1016.1	1013.8	1012.9	1012.0	1011.1	1010.2
47.5°	949.4	945.6	942.0	939.1	937.0	934.8	932.7	930.6
50°	898.7	894.7	890.8	887.8	885.7	883.5	881.4	879.3
52.5°	849.5	846.1	842.6	839.7	837.3	835.0	832.6	830.2
55°	773.0	770.2	767.5	765.1	763.0	760.8	758.7	756.6
57.5°	697.0	693.5	689.9	687.6	686.5	685.3	684.2	683.0
60°	645.6	642.6	639.5	636.9	634.8	632.7	630.6	628.4
62.5°	596.0	592.8	589.5	587.0	585.4	583.8	582.1	580.5
65°	518.1	515.3	512.6	510.6	509.4	508.2	507.0	505.7
67.5°	443.6	441.3	439.0	437.5	436.8	436.1	435.4	434.6
70°	394.5	392.6	390.8	389.3	388.1	386.9	385.7	384.5
72.5°	348.2	346.1	344.1	342.4	341.2	340.0	338.8	337.6
75°	276.3	275.4	274.5	273.4	272.2	270.9	269.7	268.5
77.5°	210.5	210.0	209.4	208.7	207.8	207.0	206.1	205.3
80°	168.4	168.1	167.8	167.3	166.7	166.1	165.5	164.9
82.5°	128.7	128.2	127.6	127.2	127.1	127.0	126.9	126.7
85°	75.7	75.4	75.1	74.6	74.0	73.4	72.8	72.2
87.5°	31.1	31.2	31.4	31.3	30.9	30.5	30.2	29.8
90°	13.6	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	13.6	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	13.6	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	27.5	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	80.7	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	156.7	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.7	320.2	319.7	319.6	319.7	319.9	320.1	320.2



TEST NUMBER: P333440-840

CATALOG NUMBER: S125DIW-S1090D770U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.8	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	416.2	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	471.6	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.5	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.5	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	591.3	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.8	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.5	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.2	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.9	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.1	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	818.9	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.1	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.7	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.4	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	911.9	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.3	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.1	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.1	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	972.2	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	985.2	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	995.0	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1000.1	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1004.0	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1008.4	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1010.1	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)