

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333690-930

Luminaire Tested: **S125RDIW-S850D1050U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333690-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1050U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6066.6 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7257	7175	7219
10°	7202	7108	7108
15°	7117	6964	6907
20°	7007	6762	6681
25°	6879	6565	6420
30°	6718	6334	6131
35°	6556	6095	5807
40°	6403	5847	5490
45°	6218	5569	5142
50°	6031	5267	4782
55°	5816	4977	4396
60°	5599	4627	3981
65°	5344	4219	3506
70°	5053	3709	3021
75°	4649	3127	2515
80°	4095	2455	2109
85°	3453	2008	1882



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	1.7
10°-20°	294.6	4.9
20°-30°	427.2	7.0
30°-40°	486.9	8.0
40°-50°	474.6	7.8
50°-60°	399.5	6.6
60°-70°	280.0	4.6
70°-80°	143.9	2.4
80°-90°	38.7	0.6
90°-100°	40.4	0.7
100°-110°	249.1	4.1
110°-120°	451.8	7.4
120°-130°	579.9	9.6
130°-140°	623.7	10.3
140°-150°	585.4	9.6
150°-160°	473.6	7.8
160°-170°	306.3	5.0
170°-180°	105.6	1.7
0°-30°	827.2	13.6
0°-40°	1314.1	21.7
0°-60°	2188.2	36.1
0°-90°	2650.8	43.7
90°-120°	741.4	12.2
90°-150°	2530.3	41.7
90°-180°	3416.0	56.3
0°-180°	6066.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1121	1121	1121	1121	1121	
5°	1119	1116	1107	1115	1114	106
15°	1064	1059	1042	1040	1033	300
25°	965	952	921	910	901	444
35°	832	810	773	749	737	520
45°	681	655	610	577	563	525
55°	516	488	442	405	390	462
65°	350	320	276	243	229	346
75°	186	160	125	107	101	197
85°	47	32	27	26	25	52
90°	1	7	13	17	20	4
95°	47	43	13	17	17	60
105°	242	246	246	246	245	257
115°	455	459	460	457	452	451
125°	647	653	653	650	647	578
135°	807	812	811	809	804	622
145°	936	937	938	938	933	585
155°	1031	1026	1027	1029	1023	475
165°	1088	1083	1084	1088	1082	307
175°	1112	1108	1108	1114	1107	106
180°	1112	1112	1112	1112	1112	



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1123.1	1122.7	1122.2	1121.8	1121.3	1120.3	1118.8	1117.3	1115.8	1114.3	1115.8
5°	1119.4	1118.7	1117.9	1117.1	1116.4	1115.0	1112.9	1110.8	1108.7	1106.7	1108.6
7.5°	1108.4	1107.7	1106.9	1106.2	1105.5	1103.9	1101.5	1098.9	1096.5	1094.0	1095.3
10°	1098.2	1097.6	1097.1	1096.5	1095.9	1094.4	1091.8	1089.1	1086.5	1083.9	1084.3
12.5°	1086.7	1086.0	1085.2	1084.6	1083.9	1081.7	1078.2	1074.6	1071.1	1067.6	1068.0
15°	1064.4	1063.2	1062.1	1060.9	1059.8	1057.3	1053.4	1049.4	1045.5	1041.5	1041.3
17.5°	1039.1	1037.4	1035.7	1034.0	1032.2	1028.8	1023.9	1018.9	1013.9	1008.9	1008.0
20°	1019.5	1017.6	1015.7	1013.8	1011.9	1008.0	1002.0	996.0	989.9	983.9	983.0
22.5°	997.8	995.9	994.0	992.1	990.3	986.2	979.8	973.5	967.2	960.9	959.0
25°	965.3	962.5	959.6	956.8	954.0	949.1	942.2	935.1	928.2	921.3	918.8
27.5°	928.1	924.6	921.2	917.8	914.4	908.9	901.5	894.0	886.6	879.1	875.6
30°	900.9	897.3	893.8	890.2	886.6	880.8	873.0	865.1	857.2	849.3	845.0
32.5°	874.5	870.3	866.2	862.0	857.8	851.7	843.7	835.6	827.5	819.5	814.7
35°	831.5	827.0	822.5	817.9	813.4	806.9	798.5	790.0	781.5	773.1	767.6
37.5°	789.3	783.8	778.4	772.8	767.4	760.3	751.5	742.7	734.0	725.3	718.8
40°	759.5	753.9	748.2	742.6	736.9	729.6	720.6	711.5	702.5	693.5	686.3
42.5°	728.4	722.6	716.8	710.9	705.2	697.7	688.3	679.0	669.6	660.3	653.5
45°	680.8	675.3	669.8	664.4	658.9	651.0	640.7	630.4	620.0	609.7	602.1
47.5°	631.5	625.7	620.0	614.2	608.5	600.4	590.0	579.5	569.1	558.6	550.9
50°	600.3	594.1	587.9	581.7	575.5	567.0	556.3	545.6	534.8	524.2	516.2
52.5°	566.5	560.1	553.8	547.4	541.0	532.8	522.7	512.6	502.4	492.3	483.8
55°	516.5	510.5	504.5	498.5	492.4	484.1	473.6	463.1	452.6	442.0	433.5
57.5°	466.0	459.6	453.1	446.7	440.3	432.0	421.8	411.6	401.5	391.3	383.1
60°	433.5	427.0	420.4	413.8	407.2	398.8	388.7	378.5	368.4	358.2	349.9
62.5°	399.0	392.7	386.5	380.1	373.8	365.6	355.2	345.0	334.6	324.3	316.7
65°	349.7	343.3	336.9	330.5	324.1	315.9	306.0	296.0	286.0	276.1	268.5
67.5°	300.8	294.3	288.0	281.6	275.2	267.2	257.6	248.1	238.6	228.9	222.1
70°	267.6	261.1	254.8	248.3	242.0	234.1	224.7	215.2	205.9	196.4	190.6
72.5°	235.1	228.8	222.6	216.3	210.1	202.5	193.7	184.9	176.1	167.3	161.9
75°	186.3	180.7	175.0	169.3	163.7	156.9	149.0	141.1	133.2	125.3	121.2
77.5°	137.9	133.3	128.8	124.3	119.8	114.4	108.0	101.7	95.4	89.1	86.2
80°	110.1	105.6	101.0	96.5	92.0	87.2	81.9	76.6	71.3	66.0	64.3
82.5°	83.0	78.9	74.8	70.8	66.7	62.9	59.3	55.7	52.0	48.4	47.6
85°	46.6	43.2	39.8	36.4	33.0	30.8	29.9	28.9	28.0	27.1	26.9
87.5°	15.7	15.0	14.2	13.5	12.7	12.4	12.5	12.6	12.7	12.8	13.0
90°	0.8	2.3	3.8	5.2	6.7	8.1	9.4	10.6	11.9	13.2	14.1
92.5°	12.7	11.7	10.7	9.6	8.6	8.6	9.8	10.9	12.1	13.2	14.1
95°	47.0	46.5	45.9	45.3	44.8	41.0	34.1	27.1	20.1	13.2	14.1
97.5°	98.2	99.1	100.1	101.1	102.1	95.7	81.9	68.2	54.4	40.6	35.4
100°	137.7	138.3	138.8	139.3	139.9	140.6	141.3	142.0	142.8	143.5	116.2
102.5°	178.0	178.6	179.4	180.0	180.8	181.3	181.7	182.1	182.6	183.0	177.9
105°	242.4	243.1	243.9	244.6	245.3	245.7	245.7	245.7	245.7	245.7	245.7
107.5°	309.4	309.4	309.4	309.4	309.4	309.6	309.9	310.3	310.6	311.0	311.0
110°	352.9	352.9	352.9	352.9	352.9	353.1	353.4	353.8	354.2	354.6	354.0



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.8	394.3	394.7	395.1	395.6	395.9	396.2	396.3	396.6	396.8	396.1
115°	455.2	456.1	457.0	457.9	458.9	459.3	459.6	459.7	459.9	460.1	459.3
117.5°	518.7	518.6	518.6	518.5	518.5	518.9	519.5	520.2	520.9	521.6	520.7
120°	558.2	558.1	557.8	557.7	557.5	557.7	558.2	558.8	559.3	559.9	559.5
122.5°	593.2	593.9	594.6	595.3	596.0	596.5	596.7	597.0	597.2	597.5	597.1
125°	647.3	648.6	649.9	651.1	652.4	653.1	653.1	653.1	653.1	653.1	652.3
127.5°	698.9	699.9	700.7	701.6	702.5	703.0	702.9	702.8	702.6	702.5	702.1
130°	730.6	731.5	732.4	733.3	734.3	734.7	735.0	735.2	735.3	735.5	735.0
132.5°	762.2	763.3	764.3	765.4	766.5	766.8	766.4	766.0	765.6	765.2	765.1
135°	807.2	808.4	809.4	810.6	811.6	812.0	811.6	811.3	810.9	810.6	810.2
137.5°	848.6	849.6	850.5	851.5	852.5	852.8	852.5	852.2	851.7	851.4	851.5
140°	875.7	876.0	876.4	876.8	877.2	877.3	877.1	876.9	876.7	876.5	876.9
142.5°	900.1	900.3	900.6	900.7	901.0	901.2	901.5	901.7	902.0	902.2	902.3
145°	935.9	936.3	936.6	937.0	937.3	937.5	937.5	937.5	937.5	937.5	937.8
147.5°	967.2	967.2	967.1	967.0	966.9	967.0	967.2	967.4	967.7	967.8	968.1
150°	987.0	986.7	986.3	985.9	985.5	985.5	985.9	986.3	986.7	987.0	987.4
152.5°	1006.2	1005.3	1004.5	1003.7	1002.9	1002.7	1003.1	1003.5	1003.8	1004.1	1004.5
155°	1030.7	1029.6	1028.5	1027.4	1026.3	1026.0	1026.3	1026.7	1027.0	1027.4	1027.9
157.5°	1049.7	1049.0	1048.4	1047.7	1047.0	1046.8	1046.8	1046.8	1046.8	1046.8	1047.5
160°	1062.9	1061.8	1060.7	1059.6	1058.5	1058.0	1058.2	1058.4	1058.6	1058.7	1059.5
162.5°	1073.4	1072.4	1071.2	1070.2	1069.0	1068.5	1068.8	1068.9	1069.1	1069.3	1070.3
165°	1087.6	1086.5	1085.4	1084.3	1083.2	1082.7	1083.0	1083.1	1083.3	1083.5	1084.6
167.5°	1098.1	1097.1	1095.9	1094.8	1093.6	1093.2	1093.3	1093.5	1093.7	1093.9	1095.2
170°	1104.1	1102.9	1101.6	1100.2	1098.9	1098.5	1098.6	1098.8	1098.9	1099.2	1100.7
172.5°	1108.1	1106.8	1105.5	1104.2	1102.9	1102.4	1102.8	1103.1	1103.4	1103.8	1105.1
175°	1112.3	1111.3	1110.1	1109.1	1107.9	1107.5	1107.7	1107.8	1108.1	1108.2	1109.7
177.5°	1114.4	1113.5	1112.6	1111.7	1110.8	1110.4	1110.6	1110.8	1110.8	1111.0	1112.1
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1117.3	1118.8	1120.3	1121.0	1120.9	1120.7	1120.5	1120.4
5°	1110.4	1112.3	1114.2	1115.0	1114.6	1114.2	1113.9	1113.5
7.5°	1096.7	1098.0	1099.3	1099.7	1099.3	1098.9	1098.5	1098.0
10°	1084.9	1085.5	1086.1	1086.1	1085.5	1084.9	1084.3	1083.9
12.5°	1068.4	1068.8	1069.2	1069.0	1068.1	1067.2	1066.4	1065.5
15°	1041.1	1040.9	1040.7	1039.8	1038.1	1036.4	1034.7	1033.0
17.5°	1007.1	1006.2	1005.2	1004.0	1002.7	1001.3	999.9	998.5
20°	982.0	981.0	980.2	978.8	977.1	975.4	973.7	972.1
22.5°	957.2	955.4	953.5	951.9	950.5	949.1	947.7	946.3
25°	916.4	914.0	911.5	909.2	907.1	905.1	903.0	900.9
27.5°	872.2	868.8	865.4	862.7	860.7	858.7	856.7	854.7
30°	840.7	836.3	831.9	829.0	827.3	825.6	823.9	822.1
32.5°	809.9	805.1	800.4	796.9	794.8	792.6	790.4	788.3
35°	762.1	756.7	751.2	747.2	744.5	741.9	739.3	736.6
37.5°	712.2	705.6	699.1	694.6	692.0	689.4	686.9	684.4
40°	679.1	672.1	664.9	660.1	657.9	655.7	653.4	651.2
42.5°	646.6	639.8	632.9	627.8	624.5	621.2	617.8	614.6
45°	594.6	587.1	579.5	574.4	571.5	568.8	565.9	563.0
47.5°	543.2	535.4	527.7	522.2	519.1	516.0	512.8	509.7
50°	508.3	500.4	492.5	487.1	484.4	481.5	478.7	475.9
52.5°	475.3	466.8	458.3	452.6	449.8	446.9	444.2	441.3
55°	425.1	416.6	408.1	402.4	399.4	396.4	393.4	390.4
57.5°	374.8	366.6	358.2	352.8	350.1	347.4	344.8	342.1
60°	341.6	333.3	325.1	319.5	316.7	313.9	311.0	308.2
62.5°	308.9	301.3	293.6	288.4	285.5	282.7	279.9	277.0
65°	261.0	253.5	245.9	240.8	237.9	235.1	232.3	229.4
67.5°	215.2	208.3	201.4	196.8	194.6	192.3	190.0	187.8
70°	184.7	179.0	173.1	169.1	166.8	164.5	162.3	160.0
72.5°	156.5	151.2	145.8	142.4	140.8	139.3	137.9	136.3
75°	117.1	112.9	108.8	106.1	104.7	103.4	102.1	100.8
77.5°	83.2	80.4	77.5	75.6	74.6	73.6	72.6	71.7
80°	62.7	61.0	59.3	58.2	57.9	57.5	57.1	56.7
82.5°	46.9	46.1	45.2	44.8	44.5	44.4	44.1	43.9
85°	26.7	26.5	26.3	26.2	25.9	25.8	25.6	25.4
87.5°	13.1	13.4	13.5	13.6	13.5	13.5	13.5	13.5
90°	15.0	16.0	16.9	17.6	18.2	18.7	19.2	19.8
92.5°	15.0	16.0	16.9	17.4	17.7	17.9	18.2	18.5
95°	15.0	16.0	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	30.2	25.0	19.9	17.3	17.3	17.3	17.3	17.3
100°	88.9	61.6	34.2	20.2	19.5	18.8	18.0	17.3
102.5°	172.7	167.5	162.4	153.6	141.1	128.7	116.2	103.7
105°	245.7	245.7	245.7	245.6	245.5	245.2	245.1	244.9
107.5°	311.1	311.1	311.2	311.0	310.4	309.8	309.2	308.8
110°	353.4	352.9	352.4	352.2	352.4	352.5	352.7	352.9



TEST NUMBER: P333690-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	395.4	394.7	394.0	393.5	393.3	393.0	392.7	392.5
115°	458.6	457.9	457.1	456.2	455.2	454.0	453.0	451.8
117.5°	519.8	518.8	517.8	517.1	516.7	516.2	515.7	515.2
120°	559.1	558.8	558.4	557.7	556.8	556.0	555.1	554.1
122.5°	596.7	596.4	596.0	595.3	594.3	593.2	592.2	591.1
125°	651.6	650.9	650.1	649.5	649.0	648.4	647.8	647.3
127.5°	701.7	701.3	700.9	700.0	698.7	697.3	695.9	694.6
130°	734.4	733.9	733.3	732.5	731.6	730.8	729.9	729.0
132.5°	765.0	764.8	764.8	764.3	763.4	762.4	761.5	760.6
135°	809.8	809.4	809.1	808.4	807.2	806.2	805.0	804.0
137.5°	851.6	851.7	851.7	851.3	850.4	849.4	848.5	847.5
140°	877.3	877.6	878.0	877.6	876.5	875.4	874.3	873.2
142.5°	902.4	902.5	902.5	902.0	900.9	899.8	898.7	897.6
145°	937.9	938.1	938.2	937.8	936.7	935.6	934.5	933.4
147.5°	968.3	968.6	968.7	968.2	966.9	965.6	964.3	963.0
150°	987.7	988.1	988.5	987.9	986.4	985.0	983.5	982.0
152.5°	1004.9	1005.3	1005.6	1005.2	1003.8	1002.5	1001.2	999.9
155°	1028.5	1029.1	1029.6	1029.2	1027.7	1026.2	1024.7	1023.3
157.5°	1048.1	1048.6	1049.2	1048.8	1047.3	1045.9	1044.4	1042.9
160°	1060.2	1060.9	1061.7	1061.3	1059.9	1058.4	1057.0	1055.5
162.5°	1071.4	1072.4	1073.4	1073.1	1071.5	1069.9	1068.3	1066.7
165°	1085.7	1086.8	1087.9	1087.7	1086.2	1084.8	1083.3	1081.8
167.5°	1096.5	1097.8	1099.2	1099.0	1097.3	1095.7	1094.1	1092.4
170°	1102.1	1103.6	1105.1	1104.9	1103.3	1101.6	1100.0	1098.3
172.5°	1106.4	1107.7	1109.1	1108.9	1107.3	1105.5	1103.9	1102.3
175°	1111.2	1112.6	1114.1	1114.0	1112.3	1110.7	1109.1	1107.4
177.5°	1113.0	1114.1	1115.2	1115.1	1113.9	1112.7	1111.6	1110.4
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3

(END OF REPORT)