

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333489-840

Luminaire Tested: **S125DIW-S1270D1560U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333489-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10644.2 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12882	12759	12841
10°	12804	12669	12742
15°	12664	12517	12570
20°	12466	12304	12325
25°	12252	12050	12039
30°	11989	11777	11718
35°	11706	11483	11321
40°	11415	11163	11005
45°	11102	10872	10656
50°	10758	10520	10203
55°	10424	10124	9839
60°	10026	9722	9376
65°	9553	9239	8926
70°	9098	8682	8384
75°	8289	8015	7738
80°	7375	7260	7089
85°	6417	6536	6180



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.6	1.8
10°-20°	530.1	5.0
20°-30°	782.7	7.4
30°-40°	913.3	8.6
40°-50°	917.2	8.6
50°-60°	805.1	7.6
60°-70°	599.9	5.6
70°-80°	343.0	3.2
80°-90°	104.1	1.0
90°-100°	131.1	1.2
100°-110°	387.1	3.6
110°-120°	655.6	6.2
120°-130°	862.9	8.1
130°-140°	966.8	9.1
140°-150°	947.6	8.9
150°-160°	795.9	7.5
160°-170°	529.1	5.0
170°-180°	185.2	1.7
0°-30°	1500.4	14.1
0°-40°	2413.6	22.7
0°-60°	4136.0	38.9
0°-90°	5183.0	48.7
90°-120°	1173.8	11.0
90°-150°	3951.1	37.1
90°-180°	5461.0	51.3
0°-180°	10644.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1990	1990	1990	1990	1990	
5°	1987	1983	1968	1981	1981	188
15°	1894	1889	1872	1880	1880	534
25°	1719	1711	1691	1694	1689	791
35°	1485	1478	1456	1448	1436	928
45°	1216	1208	1190	1172	1167	936
55°	926	920	899	885	874	826
65°	625	621	605	591	584	620
75°	332	329	321	316	310	354
85°	87	88	88	86	83	97
90°	2	14	24	32	37	10
95°	99	103	117	128	131	106
105°	347	355	364	373	378	371
115°	656	662	666	664	663	649
125°	958	967	969	966	964	858
135°	1246	1255	1256	1256	1250	960
145°	1509	1515	1520	1520	1515	943
155°	1727	1727	1729	1734	1727	795
165°	1878	1875	1876	1882	1873	530
175°	1953	1947	1946	1954	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1995.2	1994.4	1993.6	1992.7	1991.9	1990.0	1987.2	1984.4	1981.7	1978.8	1981.7
5°	1987.0	1986.3	1985.6	1984.9	1984.2	1982.2	1978.6	1975.1	1971.7	1968.1	1971.3
7.5°	1968.7	1968.0	1967.3	1966.6	1965.9	1963.7	1959.8	1956.0	1952.2	1948.3	1951.4
10°	1952.4	1951.7	1951.0	1950.3	1949.5	1947.3	1943.5	1939.6	1935.7	1931.9	1934.7
12.5°	1932.2	1931.0	1929.8	1928.4	1927.2	1924.8	1921.2	1917.6	1914.1	1910.5	1912.8
15°	1894.1	1893.1	1892.0	1891.0	1890.0	1887.4	1883.6	1879.8	1875.9	1872.1	1873.8
17.5°	1850.4	1848.9	1847.2	1845.7	1844.2	1841.4	1837.4	1833.4	1829.5	1825.4	1827.7
20°	1813.8	1813.1	1812.4	1811.7	1811.0	1808.4	1803.8	1799.3	1794.7	1790.2	1792.6
22.5°	1777.3	1776.0	1774.7	1773.5	1772.2	1769.5	1765.2	1761.0	1756.7	1752.4	1754.0
25°	1719.4	1717.6	1715.9	1714.1	1712.3	1709.2	1704.7	1700.1	1695.6	1691.0	1691.7
27.5°	1651.6	1650.6	1649.5	1648.5	1647.5	1644.6	1639.9	1635.2	1630.5	1625.8	1626.0
30°	1607.6	1606.5	1605.5	1604.4	1603.4	1600.2	1595.0	1589.7	1584.5	1579.2	1578.5
32.5°	1559.7	1558.1	1556.5	1554.9	1553.3	1550.1	1545.4	1540.8	1536.0	1531.4	1530.1
35°	1484.7	1483.4	1482.0	1480.6	1479.1	1476.0	1471.1	1466.2	1461.3	1456.4	1454.7
37.5°	1406.9	1405.2	1403.5	1401.7	1400.0	1396.7	1392.2	1387.6	1382.9	1378.4	1375.7
40°	1354.0	1352.3	1350.6	1348.8	1347.1	1343.7	1338.9	1333.9	1329.1	1324.1	1321.0
42.5°	1297.4	1296.0	1294.4	1292.9	1291.5	1288.3	1283.4	1278.5	1273.6	1268.7	1265.9
45°	1215.5	1214.2	1212.7	1211.3	1209.9	1207.1	1203.0	1198.7	1194.6	1190.3	1186.1
47.5°	1127.3	1127.4	1127.5	1127.5	1127.6	1125.1	1120.1	1115.1	1110.0	1105.0	1100.8
50°	1070.7	1069.6	1068.5	1067.5	1066.4	1063.8	1059.7	1055.4	1051.3	1047.0	1042.5
52.5°	1012.7	1012.0	1011.2	1010.4	1009.7	1007.0	1002.5	998.0	993.6	989.1	985.1
55°	925.8	924.7	923.7	922.6	921.6	918.7	913.7	908.9	903.9	899.1	895.9
57.5°	834.1	833.6	833.0	832.5	831.9	829.6	825.5	821.3	817.2	813.0	809.0
60°	776.2	774.9	773.5	772.0	770.6	768.0	764.2	760.3	756.5	752.7	749.1
62.5°	715.8	714.7	713.6	712.4	711.2	709.1	705.8	702.5	699.2	695.9	692.2
65°	625.1	624.4	623.7	623.0	622.3	620.0	616.1	612.3	608.4	604.6	601.5
67.5°	537.2	535.7	534.3	532.8	531.4	529.2	526.3	523.4	520.6	517.7	515.0
70°	481.8	480.1	478.3	476.6	474.8	472.3	469.2	466.1	462.9	459.8	457.7
72.5°	421.3	420.1	419.0	417.8	416.6	415.0	412.9	410.9	408.9	406.9	404.5
75°	332.2	331.5	330.8	330.1	329.4	328.2	326.5	324.7	323.0	321.2	320.1
77.5°	250.0	249.7	249.4	249.2	248.9	248.3	247.3	246.3	245.3	244.4	243.8
80°	198.3	198.3	198.3	198.3	198.3	198.0	197.3	196.6	195.9	195.2	194.9
82.5°	153.0	152.5	151.9	151.4	150.8	150.5	150.3	150.2	150.1	149.9	149.3
85°	86.6	86.9	87.3	87.7	88.0	88.2	88.2	88.2	88.2	88.2	87.9
87.5°	34.3	34.8	35.4	36.0	36.5	36.9	37.1	37.3	37.5	37.7	38.0
90°	1.5	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1
92.5°	36.9	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7
95°	99.0	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7
97.5°	164.5	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9
100°	213.2	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1
102.5°	265.6	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1
105°	347.3	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1
107.5°	437.4	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0
110°	499.6	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	562.9	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1
115°	656.4	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2
117.5°	750.2	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0
120°	808.7	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9
122.5°	872.1	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5
125°	958.0	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0
127.5°	1049.4	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0
130°	1104.2	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5
132.5°	1159.0	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5
135°	1245.9	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5
137.5°	1327.5	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1
140°	1379.9	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7
142.5°	1432.3	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8
145°	1509.3	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9
147.5°	1580.6	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4
150°	1628.1	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7
152.5°	1667.1	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5
155°	1727.2	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0
157.5°	1780.7	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3
160°	1812.4	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7
162.5°	1840.5	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1
165°	1877.9	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7
167.5°	1909.6	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5
170°	1926.6	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6
172.5°	1938.8	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8
175°	1952.6	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4
177.5°	1959.5	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1	1990.1
2.5°	1984.4	1987.2	1990.0	1991.3	1991.0	1990.7	1990.4	1990.1
5°	1974.4	1977.6	1980.7	1982.2	1981.8	1981.5	1981.1	1980.7
7.5°	1954.4	1957.5	1960.6	1962.0	1961.7	1961.3	1961.0	1960.6
10°	1937.5	1940.4	1943.1	1944.3	1944.0	1943.6	1943.3	1943.0
12.5°	1915.0	1917.2	1919.5	1920.6	1920.5	1920.4	1920.4	1920.3
15°	1875.6	1877.3	1879.1	1880.0	1880.0	1880.0	1880.0	1880.0
17.5°	1829.8	1832.0	1834.1	1834.3	1832.6	1830.9	1829.1	1827.4
20°	1795.1	1797.6	1800.0	1800.4	1798.6	1796.9	1795.1	1793.3
22.5°	1755.7	1757.3	1758.9	1759.1	1757.9	1756.7	1755.4	1754.3
25°	1692.4	1693.1	1693.8	1693.6	1692.6	1691.5	1690.5	1689.4
27.5°	1626.1	1626.3	1626.4	1625.9	1624.9	1623.9	1622.8	1621.7
30°	1577.8	1577.1	1576.4	1575.6	1574.5	1573.5	1572.4	1571.3
32.5°	1528.8	1527.6	1526.3	1524.7	1522.9	1521.0	1519.0	1517.2
35°	1452.9	1451.2	1449.5	1447.1	1444.3	1441.6	1438.8	1435.9
37.5°	1373.1	1370.6	1368.0	1365.8	1364.2	1362.6	1361.0	1359.4
40°	1317.9	1314.7	1311.5	1309.5	1308.4	1307.4	1306.3	1305.3
42.5°	1263.0	1260.1	1257.3	1255.1	1253.4	1251.8	1250.2	1248.6
45°	1181.9	1177.7	1173.6	1170.9	1169.8	1168.8	1167.7	1166.7
47.5°	1096.4	1092.2	1087.9	1084.6	1082.1	1079.6	1077.2	1074.8
50°	1037.9	1033.4	1028.9	1025.3	1022.9	1020.5	1018.0	1015.5
52.5°	981.1	977.1	973.1	969.8	967.0	964.3	961.6	958.9
55°	892.7	889.6	886.5	883.6	881.2	878.8	876.3	873.8
57.5°	805.0	800.9	796.9	794.2	792.8	791.5	790.1	788.8
60°	745.6	742.1	738.6	735.7	733.2	730.7	728.3	725.9
62.5°	688.3	684.6	680.9	678.0	676.1	674.2	672.3	670.4
65°	598.3	595.1	592.0	589.8	588.3	586.9	585.5	584.1
67.5°	512.4	509.7	507.1	505.3	504.4	503.6	502.8	501.9
70°	455.6	453.4	451.3	449.6	448.2	446.8	445.5	444.0
72.5°	402.1	399.7	397.4	395.5	394.0	392.6	391.2	389.8
75°	319.1	318.0	317.0	315.8	314.4	313.0	311.5	310.1
77.5°	243.1	242.5	241.9	241.1	240.0	239.0	238.1	237.1
80°	194.5	194.2	193.8	193.3	192.6	191.9	191.2	190.6
82.5°	148.7	148.0	147.3	147.0	146.8	146.7	146.5	146.4
85°	87.5	87.2	86.7	86.2	85.5	84.8	84.1	83.4
87.5°	38.3	38.7	39.0	39.0	38.6	38.3	37.9	37.6
90°	27.8	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	62.9	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	122.0	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	191.2	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	239.1	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	288.4	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	368.1	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	454.0	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	513.8	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333489-840

CATALOG NUMBER: S125DIW-S1270D1560U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	573.6	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.9	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.3	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.3	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	967.3	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.7	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1114.2	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1170.2	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.5	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1393.4	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.2	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1589.2	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1673.3	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1731.3	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1781.6	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1812.1	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1840.7	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1879.1	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1907.5	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1924.6	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1936.8	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1950.6	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1956.7	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)