

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333698-930

Luminaire Tested: **S125RDIW-S850D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333698-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7736.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	58	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7257	7175	7219
10°	7202	7108	7108
15°	7117	6964	6907
20°	7007	6762	6681
25°	6879	6565	6420
30°	6718	6334	6131
35°	6556	6095	5807
40°	6403	5847	5490
45°	6218	5569	5142
50°	6031	5267	4782
55°	5816	4977	4396
60°	5599	4627	3981
65°	5344	4219	3506
70°	5053	3709	3021
75°	4649	3127	2515
80°	4095	2455	2109
85°	3453	2008	1882



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	1.4
10°-20°	294.6	3.8
20°-30°	427.2	5.5
30°-40°	486.9	6.3
40°-50°	474.6	6.1
50°-60°	399.5	5.2
60°-70°	280.0	3.6
70°-80°	143.9	1.9
80°-90°	39.8	0.5
90°-100°	60.2	0.8
100°-110°	370.8	4.8
110°-120°	672.5	8.7
120°-130°	863.1	11.2
130°-140°	928.3	12.0
140°-150°	871.4	11.3
150°-160°	704.9	9.1
160°-170°	455.9	5.9
170°-180°	157.2	2.0
0°-30°	827.2	10.7
0°-40°	1314.1	17.0
0°-60°	2188.2	28.3
0°-90°	2651.9	34.3
90°-120°	1103.5	14.3
90°-150°	3766.2	48.7
90°-180°	5084.0	65.7
0°-180°	7736.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1121	1121	1121	1121	1121	
5°	1119	1116	1107	1115	1114	106
15°	1064	1059	1042	1040	1033	300
25°	965	952	921	910	901	444
35°	832	810	773	749	737	520
45°	681	655	610	577	563	525
55°	516	488	442	405	390	462
65°	350	320	276	243	229	346
75°	186	160	125	107	101	197
85°	47	32	27	26	25	52
90°	1	11	20	26	29	5
95°	70	64	20	25	26	89
105°	361	365	366	366	364	383
115°	678	683	685	680	672	671
125°	963	972	972	967	963	860
135°	1202	1208	1206	1204	1197	926
145°	1393	1395	1396	1396	1389	871
155°	1534	1527	1529	1532	1523	707
165°	1619	1612	1613	1619	1610	457
175°	1656	1649	1650	1658	1648	158
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1123.1	1122.7	1122.2	1121.8	1121.3	1120.3	1118.8	1117.3	1115.8	1114.3	1115.8
5°	1119.4	1118.7	1117.9	1117.1	1116.4	1115.0	1112.9	1110.8	1108.7	1106.7	1108.6
7.5°	1108.4	1107.7	1106.9	1106.2	1105.5	1103.9	1101.5	1098.9	1096.5	1094.0	1095.3
10°	1098.2	1097.6	1097.1	1096.5	1095.9	1094.4	1091.8	1089.1	1086.5	1083.9	1084.3
12.5°	1086.7	1086.0	1085.2	1084.6	1083.9	1081.7	1078.2	1074.6	1071.1	1067.6	1068.0
15°	1064.4	1063.2	1062.1	1060.9	1059.8	1057.3	1053.4	1049.4	1045.5	1041.5	1041.3
17.5°	1039.1	1037.4	1035.7	1034.0	1032.2	1028.8	1023.9	1018.9	1013.9	1008.9	1008.0
20°	1019.5	1017.6	1015.7	1013.8	1011.9	1008.0	1002.0	996.0	989.9	983.9	983.0
22.5°	997.8	995.9	994.0	992.1	990.3	986.2	979.8	973.5	967.2	960.9	959.0
25°	965.3	962.5	959.6	956.8	954.0	949.1	942.2	935.1	928.2	921.3	918.8
27.5°	928.1	924.6	921.2	917.8	914.4	908.9	901.5	894.0	886.6	879.1	875.6
30°	900.9	897.3	893.8	890.2	886.6	880.8	873.0	865.1	857.2	849.3	845.0
32.5°	874.5	870.3	866.2	862.0	857.8	851.7	843.7	835.6	827.5	819.5	814.7
35°	831.5	827.0	822.5	817.9	813.4	806.9	798.5	790.0	781.5	773.1	767.6
37.5°	789.3	783.8	778.4	772.8	767.4	760.3	751.5	742.7	734.0	725.3	718.8
40°	759.5	753.9	748.2	742.6	736.9	729.6	720.6	711.5	702.5	693.5	686.3
42.5°	728.4	722.6	716.8	710.9	705.2	697.7	688.3	679.0	669.6	660.3	653.5
45°	680.8	675.3	669.8	664.4	658.9	651.0	640.7	630.4	620.0	609.7	602.1
47.5°	631.5	625.7	620.0	614.2	608.5	600.4	590.0	579.5	569.1	558.6	550.9
50°	600.3	594.1	587.9	581.7	575.5	567.0	556.3	545.6	534.8	524.2	516.2
52.5°	566.5	560.1	553.8	547.4	541.0	532.8	522.7	512.6	502.4	492.3	483.8
55°	516.5	510.5	504.5	498.5	492.4	484.1	473.6	463.1	452.6	442.0	433.5
57.5°	466.0	459.6	453.1	446.7	440.3	432.0	421.8	411.6	401.5	391.3	383.1
60°	433.5	427.0	420.4	413.8	407.2	398.8	388.7	378.5	368.4	358.2	349.9
62.5°	399.0	392.7	386.5	380.1	373.8	365.6	355.2	345.0	334.6	324.3	316.7
65°	349.7	343.3	336.9	330.5	324.1	315.9	306.0	296.0	286.0	276.1	268.5
67.5°	300.8	294.3	288.0	281.6	275.2	267.2	257.6	248.1	238.6	228.9	222.1
70°	267.6	261.1	254.8	248.3	242.0	234.1	224.7	215.2	205.9	196.4	190.6
72.5°	235.1	228.8	222.6	216.3	210.1	202.5	193.7	184.9	176.1	167.3	161.9
75°	186.3	180.7	175.0	169.3	163.7	156.9	149.0	141.1	133.2	125.3	121.2
77.5°	137.9	133.3	128.8	124.3	119.8	114.4	108.0	101.7	95.4	89.1	86.2
80°	110.1	105.6	101.0	96.5	92.0	87.2	81.9	76.6	71.3	66.0	64.3
82.5°	83.0	78.9	74.8	70.8	66.7	62.9	59.3	55.7	52.0	48.4	47.6
85°	46.6	43.2	39.8	36.4	33.0	30.8	29.9	28.9	28.0	27.1	26.9
87.5°	15.8	15.2	14.6	13.9	13.4	13.1	13.4	13.6	13.9	14.1	14.3
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0
92.5°	18.9	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0
95°	70.0	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0
97.5°	146.0	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7
100°	205.0	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9
102.5°	264.9	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8
105°	360.9	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0
110°	525.3	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	586.2	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5
115°	677.5	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7
117.5°	772.0	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9
120°	830.9	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8
122.5°	883.0	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8
125°	963.4	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9
127.5°	1040.2	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1
130°	1087.4	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0
132.5°	1134.5	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8
135°	1201.5	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9
137.5°	1263.1	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5
140°	1303.4	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2
142.5°	1339.7	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0
145°	1393.0	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7
147.5°	1439.7	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0
150°	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7
152.5°	1497.5	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2
155°	1534.1	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1
157.5°	1562.4	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1
160°	1582.0	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0
162.5°	1597.7	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1
165°	1618.9	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3
167.5°	1634.5	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1
170°	1643.4	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2
172.5°	1649.3	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9
175°	1655.6	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7
177.5°	1658.6	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1117.3	1118.8	1120.3	1121.0	1120.9	1120.7	1120.5	1120.4
5°	1110.4	1112.3	1114.2	1115.0	1114.6	1114.2	1113.9	1113.5
7.5°	1096.7	1098.0	1099.3	1099.7	1099.3	1098.9	1098.5	1098.0
10°	1084.9	1085.5	1086.1	1086.1	1085.5	1084.9	1084.3	1083.9
12.5°	1068.4	1068.8	1069.2	1069.0	1068.1	1067.2	1066.4	1065.5
15°	1041.1	1040.9	1040.7	1039.8	1038.1	1036.4	1034.7	1033.0
17.5°	1007.1	1006.2	1005.2	1004.0	1002.7	1001.3	999.9	998.5
20°	982.0	981.0	980.2	978.8	977.1	975.4	973.7	972.1
22.5°	957.2	955.4	953.5	951.9	950.5	949.1	947.7	946.3
25°	916.4	914.0	911.5	909.2	907.1	905.1	903.0	900.9
27.5°	872.2	868.8	865.4	862.7	860.7	858.7	856.7	854.7
30°	840.7	836.3	831.9	829.0	827.3	825.6	823.9	822.1
32.5°	809.9	805.1	800.4	796.9	794.8	792.6	790.4	788.3
35°	762.1	756.7	751.2	747.2	744.5	741.9	739.3	736.6
37.5°	712.2	705.6	699.1	694.6	692.0	689.4	686.9	684.4
40°	679.1	672.1	664.9	660.1	657.9	655.7	653.4	651.2
42.5°	646.6	639.8	632.9	627.8	624.5	621.2	617.8	614.6
45°	594.6	587.1	579.5	574.4	571.5	568.8	565.9	563.0
47.5°	543.2	535.4	527.7	522.2	519.1	516.0	512.8	509.7
50°	508.3	500.4	492.5	487.1	484.4	481.5	478.7	475.9
52.5°	475.3	466.8	458.3	452.6	449.8	446.9	444.2	441.3
55°	425.1	416.6	408.1	402.4	399.4	396.4	393.4	390.4
57.5°	374.8	366.6	358.2	352.8	350.1	347.4	344.8	342.1
60°	341.6	333.3	325.1	319.5	316.7	313.9	311.0	308.2
62.5°	308.9	301.3	293.6	288.4	285.5	282.7	279.9	277.0
65°	261.0	253.5	245.9	240.8	237.9	235.1	232.3	229.4
67.5°	215.2	208.3	201.4	196.8	194.6	192.3	190.0	187.8
70°	184.7	179.0	173.1	169.1	166.8	164.5	162.3	160.0
72.5°	156.5	151.2	145.8	142.4	140.8	139.3	137.9	136.3
75°	117.1	112.9	108.8	106.1	104.7	103.4	102.1	100.8
77.5°	83.2	80.4	77.5	75.6	74.6	73.6	72.6	71.7
80°	62.7	61.0	59.3	58.2	57.9	57.5	57.1	56.7
82.5°	46.9	46.1	45.2	44.8	44.5	44.4	44.1	43.9
85°	26.7	26.5	26.3	26.2	25.9	25.8	25.6	25.4
87.5°	14.6	14.9	15.2	15.3	15.3	15.3	15.3	15.4
90°	22.3	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	22.3	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	22.3	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	45.0	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	132.2	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	257.1	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	526.1	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333698-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	588.5	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	682.7	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	773.6	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	832.3	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	888.2	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	969.9	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1044.5	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1093.2	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.6	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1205.3	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.5	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1305.7	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.1	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.0	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.3	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.1	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1495.7	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1530.9	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1559.9	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1578.0	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1594.6	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1615.9	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1632.1	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1640.4	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1646.8	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1653.8	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1656.8	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)