

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333362-840

Luminaire Tested: **S125DIW-S375D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333362-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D1340U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6955.2 lumens  
Efficiency: N/A  
Efficacy: 149.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22				
1	92	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	26	19				
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	23	22	16				
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	19	18	13				
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11				
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10				
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9				
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7				
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	8	6				
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	0.8
10°-20°	157.1	2.3
20°-30°	232.0	3.3
30°-40°	270.7	3.9
40°-50°	271.9	3.9
50°-60°	238.7	3.4
60°-70°	177.8	2.6
70°-80°	101.7	1.5
80°-90°	33.2	0.5
90°-100°	64.1	0.9
100°-110°	395.0	5.7
110°-120°	716.5	10.3
120°-130°	919.5	13.2
130°-140°	989.0	14.2
140°-150°	928.3	13.3
150°-160°	750.9	10.8
160°-170°	485.7	7.0
170°-180°	167.5	2.4
0°-30°	444.7	6.4
0°-40°	715.5	10.3
0°-60°	1226.0	17.6
0°-90°	1538.8	22.1
90°-120°	1175.6	16.9
90°-150°	4012.4	57.7
90°-180°	5416.0	77.9
0°-180°	6955.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	1	12	21	27	31	5
95°	74	68	21	27	28	95
105°	384	389	390	390	388	408
115°	722	728	730	724	716	715
125°	1026	1035	1036	1030	1026	916
135°	1280	1287	1285	1282	1275	986
145°	1484	1486	1487	1487	1480	928
155°	1634	1627	1629	1632	1623	753
165°	1725	1717	1718	1725	1716	487
175°	1764	1757	1757	1767	1756	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.3	10.8	11.3	11.7	12.2	12.6	12.9	13.2	13.5	13.9	14.1
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4
92.5°	20.1	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4
95°	74.5	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4
97.5°	155.6	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1
100°	218.3	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2
102.5°	282.2	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1
105°	384.5	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2
110°	559.7	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4



TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	624.5	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0
115°	721.8	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4
117.5°	822.4	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7
120°	885.1	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3
122.5°	940.6	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8
125°	1026.4	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4
127.5°	1108.2	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4
130°	1158.4	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5
132.5°	1208.7	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3
135°	1280.1	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8
137.5°	1345.7	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3
140°	1388.6	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5
142.5°	1427.2	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8
145°	1484.0	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9
147.5°	1533.7	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1
150°	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7
152.5°	1595.4	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9
155°	1634.4	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0
157.5°	1664.5	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9
160°	1685.4	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0
162.5°	1702.1	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2
165°	1724.6	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8
167.5°	1741.3	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7
170°	1750.8	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2
172.5°	1757.1	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3
175°	1763.8	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6
177.5°	1767.0	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	14.4	14.7	15.0	15.2	15.2	15.2	15.2	15.2
90°	23.8	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	23.8	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	23.8	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	48.0	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	140.9	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	273.9	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.3	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	560.5	559.7	558.8	558.5	558.8	559.1	559.4	559.7





TEST NUMBER: P333362-840

CATALOG NUMBER: S125DIW-S375D1340U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	626.9	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	727.3	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	824.2	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.7	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	946.2	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1033.2	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.8	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1164.6	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1213.0	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1284.1	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.4	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.1	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1430.9	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.2	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.5	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.3	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1593.5	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1630.9	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1661.9	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1681.2	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1698.8	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1721.5	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1738.8	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1747.6	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1754.4	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1761.9	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1765.0	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)