

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333365-840

Luminaire Tested: **S125DIW-S375D1560U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333365-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7016.8 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	57	56	43	41	40	27	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19	14
4	70	59	52	46	61	53	47	42	41	36	33	30	27	24	19	17	16	12
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	39	34	52	42	36	31	33	28	24	24	21	18	15	14	12	9
7	54	42	35	30	48	38	31	27	29	25	21	22	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3551	3551	3551	3551
5°	4112	3563	3120	3563
10°	4783	3545	2733	3545
15°	5295	3518	2521	3518
20°	5927	3477	2351	3477
25°	6944	3430	2268	3430
30°	7500	3384	2196	3384
35°	6166	3299	2149	3299
40°	4383	3179	2097	3179
45°	3368	3018	2067	3018
50°	2875	2817	2063	2817
55°	2559	2622	2081	2622
60°	2308	2408	2134	2408
65°	2133	2193	2190	2193
70°	1939	1969	2221	1969
75°	1712	1737	2201	1737
80°	1443	1417	2012	1417
85°	1149	1015	1623	1015



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	0.8
10°-20°	157.6	2.2
20°-30°	255.9	3.6
30°-40°	312.1	4.4
40°-50°	283.9	4.0
50°-60°	226.2	3.2
60°-70°	157.5	2.2
70°-80°	84.0	1.2
80°-90°	25.5	0.4
90°-100°	131.1	1.9
100°-110°	387.1	5.5
110°-120°	655.6	9.3
120°-130°	862.9	12.3
130°-140°	966.8	13.8
140°-150°	947.6	13.5
150°-160°	795.9	11.3
160°-170°	529.1	7.5
170°-180°	185.2	2.6
0°-30°	466.4	6.6
0°-40°	778.5	11.1
0°-60°	1288.6	18.4
0°-90°	1555.6	22.2
90°-120°	1173.8	16.7
90°-150°	3951.1	56.3
90°-180°	5461.0	77.8
0°-180°	7016.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	634	550	481	550	634	64
15°	792	526	377	526	792	227
25°	974	481	318	481	974	445
35°	782	418	273	418	782	479
45°	369	330	226	330	369	295
55°	227	233	185	233	227	205
65°	140	144	143	144	140	138
75°	69	70	88	70	69	74
85°	16	14	22	14	16	19
90°	37	2	37	2	37	22
95°	131	99	131	99	131	133
105°	378	347	378	347	378	400
115°	663	656	663	656	663	655
125°	964	958	964	958	964	861
135°	1250	1246	1250	1246	1250	965
145°	1515	1509	1515	1509	1515	946
155°	1727	1727	1727	1727	1727	795
165°	1873	1878	1873	1878	1873	528
175°	1945	1953	1945	1953	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	581.5	580.8	580.0	578.6	579.7	576.4	575.0	572.4	569.2	568.0	566.7
5°	634.2	635.4	636.6	631.7	632.2	628.8	621.4	615.3	610.5	604.1	599.7
7.5°	697.7	695.0	694.7	691.6	686.1	681.7	673.9	663.9	654.2	643.2	634.1
10°	729.4	729.7	727.6	723.9	718.0	713.8	703.6	693.8	681.9	667.8	657.8
12.5°	753.4	754.4	751.6	746.6	743.8	734.4	726.3	714.7	700.5	689.3	674.1
15°	791.9	789.4	787.6	781.2	776.4	766.6	753.8	741.5	726.2	712.0	697.7
17.5°	829.2	831.3	827.8	822.0	806.8	795.4	778.2	761.5	742.4	723.3	706.3
20°	862.4	864.3	859.0	848.9	830.7	819.3	796.7	775.2	753.1	728.5	709.8
22.5°	903.9	902.4	895.1	879.9	864.1	843.0	818.5	792.3	764.6	736.9	712.1
25°	974.4	964.6	960.2	941.3	920.6	889.5	856.0	817.7	783.2	746.5	714.8
27.5°	1013.6	1010.5	1005.5	992.4	970.6	937.4	897.8	851.1	802.4	756.2	714.6
30°	1005.7	1006.2	1006.6	1002.5	988.5	963.5	924.0	873.9	816.0	764.0	715.9
32.5°	936.2	944.7	952.9	962.5	966.4	961.6	937.0	891.6	832.0	773.0	715.2
35°	782.1	784.8	811.1	837.3	872.7	900.3	918.7	898.6	848.5	780.5	714.3
37.5°	609.9	622.5	640.8	670.2	721.4	767.3	826.3	853.3	837.2	783.0	712.7
40°	519.9	531.6	543.5	573.6	616.7	672.3	739.2	796.4	809.7	775.2	707.0
42.5°	450.5	459.7	472.9	495.5	531.6	580.8	644.8	719.5	765.5	752.5	695.3
45°	368.7	374.6	384.8	402.7	428.9	467.4	523.8	605.5	676.7	700.2	667.4
47.5°	315.6	315.6	323.6	335.9	354.8	387.5	429.3	493.2	569.3	625.5	622.9
50°	286.1	284.9	291.2	301.9	316.9	338.6	378.5	429.6	502.6	566.3	584.1
52.5°	260.6	260.8	264.7	272.7	285.2	303.7	333.5	379.6	441.9	507.4	540.8
55°	227.3	226.3	230.8	236.1	245.3	257.4	278.8	314.1	364.8	429.1	472.5
57.5°	196.6	199.2	201.0	204.7	212.3	220.5	238.5	264.4	304.6	359.8	405.7
60°	178.7	181.3	182.7	186.4	192.5	199.5	213.5	234.5	268.3	316.0	361.4
62.5°	162.7	164.7	165.2	168.5	173.5	180.3	191.3	208.9	235.7	277.3	321.8
65°	139.6	139.6	140.5	144.0	146.3	152.4	160.8	173.6	195.1	227.5	265.6
67.5°	117.2	118.4	118.2	119.7	121.8	126.5	132.5	143.1	159.1	182.7	213.2
70°	102.7	103.6	103.4	104.5	106.8	109.9	114.8	124.8	136.2	156.5	182.7
72.5°	89.6	90.0	89.4	90.9	92.3	94.9	100.5	105.8	116.4	133.6	155.1
75°	68.6	69.1	69.6	70.5	71.9	73.3	76.0	81.4	88.5	101.3	115.0
77.5°	51.4	50.5	51.7	51.5	52.3	53.4	55.8	58.7	64.4	72.6	83.2
80°	38.8	39.0	39.0	39.2	40.4	41.1	43.1	45.2	49.7	55.7	63.2
82.5°	28.3	28.9	28.5	29.0	29.9	30.4	31.6	33.3	35.9	40.7	46.0
85°	15.5	14.2	14.7	15.1	15.1	15.5	16.4	17.1	18.5	20.3	22.4
87.5°	11.8	11.9	11.9	11.7	11.7	11.4	11.8	11.5	11.7	12.0	12.2
90°	36.6	35.5	34.5	33.5	32.5	31.1	29.5	27.8	26.1	24.3	22.0
92.5°	71.9	71.1	70.4	69.7	68.9	67.5	65.1	62.9	60.7	58.5	55.5
95°	131.0	130.3	129.7	129.0	128.3	126.7	124.4	122.0	119.7	117.2	113.9
97.5°	198.6	198.2	197.8	197.4	197.0	195.6	193.4	191.2	188.9	186.7	182.1
100°	249.7	249.1	248.4	247.7	247.1	245.2	242.2	239.1	236.1	233.0	228.6
102.5°	300.9	300.0	299.0	298.1	297.2	295.0	291.8	288.4	285.1	281.8	279.5
105°	377.7	376.7	375.7	374.7	373.7	372.1	370.1	368.1	366.1	364.1	361.9
107.5°	456.3	456.4	456.5	456.5	456.6	456.1	455.0	454.0	453.0	452.0	450.5
110°	514.8	515.1	515.4	515.8	516.1	515.8	514.8	513.8	512.7	511.7	510.7



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.1	572.7	573.3	573.9	574.5	574.5	574.1	573.6	573.1	572.7	571.4
115°	662.6	662.9	663.2	663.6	663.9	664.2	664.6	664.9	665.2	665.6	664.9
117.5°	750.8	752.2	753.6	754.9	756.3	756.8	756.6	756.3	756.0	755.8	755.1
120°	811.8	813.1	814.5	815.9	817.2	817.9	817.9	817.9	817.9	817.9	817.5
122.5°	872.7	873.7	874.8	876.0	877.1	877.7	878.0	878.3	878.5	878.8	877.9
125°	964.1	964.4	964.7	965.1	965.4	965.9	966.6	967.3	968.0	968.7	968.4
127.5°	1051.8	1052.5	1053.2	1053.8	1054.5	1055.0	1055.4	1055.7	1056.0	1056.4	1056.0
130°	1110.3	1111.0	1111.7	1112.4	1113.0	1113.5	1113.9	1114.2	1114.5	1114.9	1114.2
132.5°	1165.1	1166.1	1167.0	1168.0	1168.9	1169.5	1169.9	1170.2	1170.5	1170.9	1171.0
135°	1250.4	1251.7	1253.1	1254.5	1255.9	1256.5	1256.5	1256.5	1256.5	1256.5	1256.2
137.5°	1333.8	1335.5	1337.3	1339.0	1340.7	1341.3	1340.9	1340.5	1340.1	1339.7	1338.9
140°	1387.5	1389.2	1390.9	1392.6	1394.2	1394.7	1394.1	1393.4	1392.7	1392.1	1391.1
142.5°	1438.7	1440.4	1442.1	1443.7	1445.4	1446.1	1445.6	1445.2	1444.8	1444.4	1443.2
145°	1515.4	1516.4	1517.4	1518.4	1519.4	1519.9	1519.9	1519.9	1519.9	1519.9	1518.9
147.5°	1580.9	1583.3	1585.5	1587.8	1590.1	1590.8	1590.0	1589.2	1588.4	1587.6	1586.8
150°	1629.6	1630.3	1631.0	1631.6	1632.3	1632.7	1632.7	1632.7	1632.7	1632.7	1631.3
152.5°	1669.9	1671.1	1672.3	1673.5	1674.8	1675.0	1674.2	1673.3	1672.5	1671.7	1671.1
155°	1727.2	1728.8	1730.5	1732.2	1733.9	1734.0	1732.7	1731.3	1730.0	1728.7	1728.3
157.5°	1774.9	1777.2	1779.4	1781.6	1783.9	1784.3	1783.0	1781.6	1780.3	1778.9	1778.6
160°	1807.9	1809.6	1811.2	1812.9	1814.6	1814.8	1813.4	1812.1	1810.7	1809.4	1809.1
162.5°	1835.8	1837.9	1839.8	1841.8	1843.7	1843.9	1842.3	1840.7	1839.1	1837.3	1837.3
165°	1873.3	1875.4	1877.4	1879.5	1881.5	1881.8	1880.5	1879.1	1877.7	1876.4	1876.0
167.5°	1903.2	1905.3	1907.4	1909.5	1911.6	1911.6	1909.6	1907.5	1905.5	1903.5	1903.5
170°	1919.0	1921.4	1923.8	1926.1	1928.5	1928.6	1926.6	1924.6	1922.6	1920.6	1920.6
172.5°	1932.5	1934.5	1936.6	1938.7	1940.9	1940.9	1938.8	1936.8	1934.8	1932.8	1932.8
175°	1944.9	1947.3	1949.6	1952.1	1954.4	1954.6	1952.6	1950.6	1948.4	1946.4	1946.4
177.5°	1952.3	1954.1	1956.0	1957.9	1959.8	1959.9	1958.3	1956.7	1955.1	1953.5	1953.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	565.6	564.3	562.8	560.2	557.0	555.3	552.8	551.1	547.8	544.9	541.9
5°	594.3	588.2	582.7	575.4	567.5	562.4	556.3	549.6	542.5	535.3	527.4
7.5°	624.1	613.3	601.7	589.2	576.8	565.5	554.7	544.2	534.3	522.3	512.2
10°	644.0	630.5	616.0	599.1	582.4	567.9	553.3	540.5	527.4	513.4	501.0
12.5°	664.0	646.0	625.5	606.8	586.9	569.5	552.2	535.7	519.4	503.8	489.4
15°	678.1	662.3	643.4	616.7	594.3	570.3	547.4	526.2	506.3	489.1	470.9
17.5°	687.4	666.9	646.6	621.2	591.8	564.9	539.0	514.6	492.3	470.4	452.9
20°	689.0	668.0	646.8	621.9	591.8	561.0	535.0	505.9	481.9	459.2	437.8
22.5°	688.5	664.7	641.6	615.9	586.5	558.2	526.8	497.2	471.0	448.8	426.4
25°	683.3	657.8	628.8	603.0	574.0	543.9	512.2	481.4	454.8	429.4	407.2
27.5°	678.8	645.9	613.1	582.9	554.9	527.4	497.0	465.4	436.0	410.2	389.3
30°	673.5	637.2	600.4	568.9	540.2	513.4	484.6	453.8	423.0	397.9	375.5
32.5°	668.6	626.4	587.5	553.2	522.8	496.8	470.3	441.0	410.7	385.2	362.7
35°	659.2	610.5	565.8	527.1	494.7	467.9	445.7	418.4	390.6	365.9	344.5
37.5°	647.3	589.5	541.6	501.0	465.4	437.2	416.6	395.6	368.9	345.1	325.7
40°	637.9	574.5	523.8	482.3	445.5	416.1	396.9	377.1	355.0	332.8	312.3
42.5°	626.2	561.1	505.9	461.2	424.7	396.1	376.0	359.2	339.6	318.9	299.9
45°	604.6	536.7	477.0	428.9	392.0	363.8	343.1	330.4	315.7	296.1	280.0
47.5°	572.8	507.5	445.7	396.1	358.0	331.8	312.4	300.2	289.9	275.4	260.7
50°	544.6	485.6	423.0	373.9	335.8	309.4	291.4	280.4	271.7	260.4	248.0
52.5°	513.1	458.2	400.8	352.1	314.5	288.5	270.9	261.3	253.9	245.9	233.7
55°	462.9	416.3	363.0	316.9	282.2	256.7	241.3	232.9	226.8	220.8	213.3
57.5°	407.8	371.2	324.2	281.9	249.8	226.7	212.4	204.2	199.4	196.3	192.0
60°	368.9	337.7	297.1	258.5	227.3	206.7	192.8	186.4	182.5	180.0	176.6
62.5°	332.9	307.2	269.6	234.5	207.1	187.7	175.2	169.1	165.3	164.0	161.4
65°	279.8	259.9	228.9	199.8	176.4	159.9	149.4	143.5	141.2	139.8	140.0
67.5°	227.4	215.4	190.5	165.6	146.9	133.1	124.6	120.2	119.0	117.1	117.1
70°	195.5	186.4	165.4	143.7	127.1	116.4	109.0	104.3	103.1	102.2	102.0
72.5°	167.3	159.4	141.2	123.8	108.9	99.5	93.3	90.5	88.6	88.1	88.0
75°	125.7	121.4	106.8	93.1	82.8	76.3	72.1	69.6	68.2	67.9	68.2
77.5°	89.4	85.5	76.3	66.6	60.1	55.1	51.6	50.7	49.2	49.2	49.0
80°	67.2	64.6	58.8	51.1	45.7	41.5	39.7	38.1	37.6	36.9	37.6
82.5°	48.7	45.9	42.0	37.1	32.6	30.2	28.3	27.8	27.5	27.2	27.3
85°	24.0	24.2	21.9	18.2	16.4	14.9	13.7	13.7	13.5	13.3	13.5
87.5°	12.1	11.3	10.1	9.0	7.6	6.5	5.7	5.4	5.4	5.7	6.4
90°	19.6	17.3	14.8	12.3	9.7	7.0	4.2	1.5	4.2	7.0	9.7
92.5°	52.6	49.8	46.9	44.4	42.5	40.7	38.8	36.9	38.8	40.7	42.5
95°	110.5	107.1	103.7	101.7	101.0	100.4	99.7	99.0	99.7	100.4	101.0
97.5°	177.4	172.7	168.0	165.6	165.3	165.0	164.7	164.5	164.7	165.0	165.3
100°	224.2	219.8	215.4	213.2	213.2	213.2	213.2	213.2	213.2	213.2	213.2
102.5°	277.3	275.1	272.9	271.0	269.6	268.3	267.0	265.6	267.0	268.3	269.6
105°	359.9	357.9	355.9	354.1	352.3	350.6	348.9	347.3	348.9	350.6	352.3
107.5°	448.9	447.4	445.9	444.1	442.5	440.8	439.1	437.4	439.1	440.8	442.5
110°	509.7	508.7	507.7	506.3	504.6	502.9	501.3	499.6	501.3	502.9	504.6



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	570.1	568.8	567.5	566.4	565.5	564.7	563.8	562.9	563.8	564.7	565.5
115°	664.2	663.6	662.9	661.9	660.5	659.1	657.8	656.4	657.8	659.1	660.5
117.5°	754.5	753.9	753.3	752.7	752.0	751.4	750.8	750.2	750.8	751.4	752.0
120°	817.2	816.9	816.5	815.5	813.9	812.1	810.4	808.7	810.4	812.1	813.9
122.5°	877.1	876.2	875.3	874.5	873.9	873.3	872.7	872.1	872.7	873.3	873.9
125°	968.0	967.7	967.3	966.1	964.1	962.1	960.0	958.0	960.0	962.1	964.1
127.5°	1055.6	1055.2	1054.8	1054.0	1052.8	1051.7	1050.6	1049.4	1050.6	1051.7	1052.8
130°	1113.5	1112.9	1112.2	1111.0	1109.2	1107.6	1105.9	1104.2	1105.9	1107.6	1109.2
132.5°	1171.1	1171.3	1171.4	1170.1	1167.4	1164.6	1161.8	1159.0	1161.8	1164.6	1167.4
135°	1255.9	1255.5	1255.2	1253.9	1251.9	1249.9	1247.9	1245.9	1247.9	1249.9	1251.9
137.5°	1338.2	1337.5	1336.7	1335.3	1333.3	1331.4	1329.5	1327.5	1329.5	1331.4	1333.3
140°	1390.1	1389.0	1388.0	1386.6	1384.9	1383.2	1381.6	1379.9	1381.6	1383.2	1384.9
142.5°	1441.9	1440.6	1439.3	1437.9	1436.5	1435.1	1433.7	1432.3	1433.7	1435.1	1436.5
145°	1517.9	1516.9	1515.9	1514.8	1513.4	1512.1	1510.7	1509.3	1510.7	1512.1	1513.4
147.5°	1586.0	1585.2	1584.4	1583.6	1582.9	1582.1	1581.3	1580.6	1581.3	1582.1	1582.9
150°	1630.0	1628.6	1627.3	1626.8	1627.1	1627.5	1627.8	1628.1	1627.8	1627.5	1627.1
152.5°	1670.6	1670.1	1669.5	1669.0	1668.5	1668.1	1667.6	1667.1	1667.6	1668.1	1668.5
155°	1728.0	1727.7	1727.3	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2
157.5°	1778.3	1777.9	1777.6	1777.8	1778.5	1779.3	1780.0	1780.7	1780.0	1779.3	1778.5
160°	1808.7	1808.4	1808.1	1808.4	1809.4	1810.4	1811.4	1812.4	1811.4	1810.4	1809.4
162.5°	1837.2	1837.1	1837.1	1837.4	1838.3	1839.0	1839.7	1840.5	1839.7	1839.0	1838.3
165°	1875.7	1875.4	1875.0	1875.2	1875.9	1876.5	1877.2	1877.9	1877.2	1876.5	1875.9
167.5°	1903.5	1903.5	1903.5	1904.2	1905.5	1906.9	1908.2	1909.6	1908.2	1906.9	1905.5
170°	1920.6	1920.6	1920.6	1921.3	1922.6	1923.9	1925.3	1926.6	1925.3	1923.9	1922.6
172.5°	1932.8	1932.8	1932.8	1933.4	1934.8	1936.1	1937.5	1938.8	1937.5	1936.1	1934.8
175°	1946.4	1946.4	1946.4	1947.1	1948.4	1949.8	1951.2	1952.6	1951.2	1949.8	1948.4
177.5°	1954.0	1954.3	1954.5	1955.2	1956.3	1957.4	1958.4	1959.5	1958.4	1957.4	1956.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	540.3	538.2	536.5	532.8	530.7	528.0	525.7	528.2	525.5	526.6	524.9
5°	523.4	516.8	512.2	505.4	499.6	494.2	490.3	489.6	487.7	486.8	483.9
7.5°	503.1	494.9	487.0	478.1	470.6	463.0	458.2	454.1	451.5	448.0	445.6
10°	491.2	480.2	470.9	460.2	450.8	442.6	436.2	432.8	429.8	425.4	423.7
12.5°	476.5	465.1	453.7	442.2	433.2	424.1	418.6	413.6	411.5	406.6	406.1
15°	458.8	441.7	430.5	418.9	406.5	399.0	394.4	389.0	386.7	383.1	380.6
17.5°	437.7	422.4	408.5	396.4	385.8	379.5	373.7	370.0	366.0	363.7	359.5
20°	422.3	407.9	393.8	381.0	372.8	365.7	361.0	357.5	353.3	352.1	347.9
22.5°	409.5	393.5	380.1	369.3	360.4	352.2	347.2	344.8	341.9	338.3	337.5
25°	388.5	371.9	360.5	349.8	341.8	334.4	330.9	327.9	325.1	322.4	321.5
27.5°	370.4	355.6	342.0	332.3	325.4	318.6	315.6	311.8	309.8	307.7	305.2
30°	357.7	342.5	330.6	321.3	313.9	307.8	304.5	301.9	300.1	298.2	296.8
32.5°	344.7	330.6	319.1	309.9	302.5	297.9	295.0	293.2	291.1	288.9	287.1
35°	327.4	311.9	300.7	292.9	287.0	283.5	280.2	278.6	276.3	276.3	274.4
37.5°	307.9	294.6	284.7	277.5	272.3	269.1	265.6	264.5	263.0	262.0	261.4
40°	296.4	284.0	274.7	267.4	261.9	259.2	256.4	254.6	253.7	252.5	252.1
42.5°	284.4	272.6	263.7	257.0	252.1	249.9	247.3	246.0	244.1	242.6	242.3
45°	266.2	254.8	246.6	241.3	237.1	234.5	232.9	230.0	229.1	227.3	227.0
47.5°	249.0	238.0	230.0	225.6	222.0	219.8	217.3	214.5	213.4	212.5	212.4
50°	236.1	226.1	218.6	214.5	211.0	207.9	205.3	203.5	202.8	202.8	203.3
52.5°	223.1	214.5	208.2	203.1	199.8	196.5	194.1	193.0	192.0	193.1	193.9
55°	204.0	195.3	190.7	185.7	182.5	178.7	177.5	177.1	176.4	178.2	179.3
57.5°	183.7	177.6	172.2	167.3	164.4	162.2	160.7	160.4	161.7	162.6	165.6
60°	170.8	163.8	159.0	155.2	151.7	150.3	149.8	149.4	150.3	152.8	156.8
62.5°	156.6	151.0	145.6	142.9	140.3	137.9	137.8	138.1	140.0	143.0	146.9
65°	135.8	130.9	127.4	124.1	122.0	120.7	121.1	122.0	124.1	128.2	132.5
67.5°	114.6	111.3	108.2	105.5	103.5	103.5	104.0	105.4	107.9	112.4	116.4
70°	101.1	97.4	94.7	93.6	91.9	91.0	92.4	94.7	96.8	101.1	104.5
72.5°	87.5	84.2	82.2	81.4	80.7	80.0	80.5	83.0	85.8	90.0	94.1
75°	67.2	66.0	64.6	63.7	63.0	63.5	63.9	66.2	68.6	73.0	77.7
77.5°	49.1	47.9	47.0	46.8	46.4	46.7	48.0	49.7	51.9	55.1	58.7
80°	37.1	36.7	36.2	36.0	36.0	36.2	38.1	39.2	41.3	44.3	47.2
82.5°	27.1	26.8	26.7	26.6	26.8	26.9	28.0	29.5	31.2	33.5	36.0
85°	14.2	13.7	14.4	14.7	14.2	14.9	15.5	16.4	17.1	18.2	19.4
87.5°	7.2	8.0	8.3	9.0	9.4	10.3	10.4	11.5	12.2	12.9	13.0
90°	12.3	14.8	17.3	19.6	22.0	24.3	26.1	27.8	29.5	31.1	32.5
92.5°	44.4	46.9	49.8	52.6	55.5	58.5	60.7	62.9	65.1	67.5	68.9
95°	101.7	103.7	107.1	110.5	113.9	117.2	119.7	122.0	124.4	126.7	128.3
97.5°	165.6	168.0	172.7	177.4	182.1	186.7	188.9	191.2	193.4	195.6	197.0
100°	213.2	215.4	219.8	224.2	228.6	233.0	236.1	239.1	242.2	245.2	247.1
102.5°	271.0	272.9	275.1	277.3	279.5	281.8	285.1	288.4	291.8	295.0	297.2
105°	354.1	355.9	357.9	359.9	361.9	364.1	366.1	368.1	370.1	372.1	373.7
107.5°	444.1	445.9	447.4	448.9	450.5	452.0	453.0	454.0	455.0	456.1	456.6
110°	506.3	507.7	508.7	509.7	510.7	511.7	512.7	513.8	514.8	515.8	516.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	566.4	567.5	568.8	570.1	571.4	572.7	573.1	573.6	574.1	574.5	574.5
115°	661.9	662.9	663.6	664.2	664.9	665.6	665.2	664.9	664.6	664.2	663.9
117.5°	752.7	753.3	753.9	754.5	755.1	755.8	756.0	756.3	756.6	756.8	756.3
120°	815.5	816.5	816.9	817.2	817.5	817.9	817.9	817.9	817.9	817.9	817.2
122.5°	874.5	875.3	876.2	877.1	877.9	878.8	878.5	878.3	878.0	877.7	877.1
125°	966.1	967.3	967.7	968.0	968.4	968.7	968.0	967.3	966.6	965.9	965.4
127.5°	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0	1055.7	1055.4	1055.0	1054.5
130°	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5	1114.2	1113.9	1113.5	1113.0
132.5°	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5	1170.2	1169.9	1169.5	1168.9
135°	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5	1256.5	1256.5	1256.5	1255.9
137.5°	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1	1340.5	1340.9	1341.3	1340.7
140°	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7	1393.4	1394.1	1394.7	1394.2
142.5°	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8	1445.2	1445.6	1446.1	1445.4
145°	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.4
147.5°	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4	1589.2	1590.0	1590.8	1590.1
150°	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7	1632.7	1632.7	1632.7	1632.3
152.5°	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5	1673.3	1674.2	1675.0	1674.8
155°	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0	1731.3	1732.7	1734.0	1733.9
157.5°	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3	1781.6	1783.0	1784.3	1783.9
160°	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7	1812.1	1813.4	1814.8	1814.6
162.5°	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1	1840.7	1842.3	1843.9	1843.7
165°	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7	1879.1	1880.5	1881.8	1881.5
167.5°	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5	1907.5	1909.6	1911.6	1911.6
170°	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6	1924.6	1926.6	1928.6	1928.5
172.5°	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8	1936.8	1938.8	1940.9	1940.9
175°	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4	1950.6	1952.6	1954.6	1954.4
177.5°	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1	1956.7	1958.3	1959.9	1959.8
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	523.8	525.1	524.0	525.5	524.0	525.1	523.8	524.9	526.6	525.5	528.2
5°	482.8	480.7	482.1	481.2	482.1	480.7	482.8	483.9	486.8	487.7	489.6
7.5°	444.9	442.9	440.6	439.5	440.6	442.9	444.9	445.6	448.0	451.5	454.1
10°	421.2	418.6	418.4	416.8	418.4	418.6	421.2	423.7	425.4	429.8	432.8
12.5°	403.8	401.4	398.8	398.1	398.8	401.4	403.8	406.1	406.6	411.5	413.6
15°	379.2	377.3	375.7	377.1	375.7	377.3	379.2	380.6	383.1	386.7	389.0
17.5°	358.7	357.2	356.9	355.2	356.9	357.2	358.7	359.5	363.7	366.0	370.0
20°	345.8	344.7	345.2	342.0	345.2	344.7	345.8	347.9	352.1	353.3	357.5
22.5°	335.6	333.3	333.0	332.3	333.0	333.3	335.6	337.5	338.3	341.9	344.8
25°	319.4	318.3	317.1	318.3	317.1	318.3	319.4	321.5	322.4	325.1	327.9
27.5°	305.4	304.0	303.7	303.9	303.7	304.0	305.4	305.2	307.7	309.8	311.8
30°	296.8	294.5	294.7	294.5	294.7	294.5	296.8	296.8	298.2	300.1	301.9
32.5°	287.5	285.9	285.6	285.2	285.6	285.9	287.5	287.1	288.9	291.1	293.2
35°	273.7	273.7	272.6	272.6	272.6	273.7	273.7	274.4	276.3	276.3	278.6
37.5°	260.7	260.5	259.8	259.9	259.8	260.5	260.7	261.4	262.0	263.0	264.5
40°	251.1	250.9	250.1	248.7	250.1	250.9	251.1	252.1	252.5	253.7	254.6
42.5°	241.8	241.0	240.7	240.1	240.7	241.0	241.8	242.3	242.6	244.1	246.0
45°	227.0	227.0	226.6	226.3	226.6	227.0	227.0	227.0	227.3	229.1	230.0
47.5°	212.8	213.2	214.1	213.9	214.1	213.2	212.8	212.4	212.5	213.4	214.5
50°	204.2	204.4	205.1	205.3	205.1	204.4	204.2	203.3	202.8	202.8	203.5
52.5°	194.7	196.0	196.9	196.7	196.9	196.0	194.7	193.9	193.1	192.0	193.0
55°	181.3	183.0	184.6	184.8	184.6	183.0	181.3	179.3	178.2	176.4	177.1
57.5°	168.1	170.4	172.1	172.7	172.1	170.4	168.1	165.6	162.6	161.7	160.4
60°	159.2	162.2	164.3	165.2	164.3	162.2	159.2	156.8	152.8	150.3	149.4
62.5°	150.6	154.0	156.0	156.2	156.0	154.0	150.6	146.9	143.0	140.0	138.1
65°	136.5	140.0	141.9	143.3	141.9	140.0	136.5	132.5	128.2	124.1	122.0
67.5°	121.4	124.9	126.9	128.1	126.9	124.9	121.4	116.4	112.4	107.9	105.4
70°	110.4	113.9	116.6	117.6	116.6	113.9	110.4	104.5	101.1	96.8	94.7
72.5°	99.6	102.7	104.9	106.0	104.9	102.7	99.6	94.1	90.0	85.8	83.0
75°	80.7	84.9	87.1	88.2	87.1	84.9	80.7	77.7	73.0	68.6	66.2
77.5°	62.2	66.0	67.4	68.0	67.4	66.0	62.2	58.7	55.1	51.9	49.7
80°	49.9	52.3	53.9	54.1	53.9	52.3	49.9	47.2	44.3	41.3	39.2
82.5°	38.4	40.3	40.8	41.4	40.8	40.3	38.4	36.0	33.5	31.2	29.5
85°	21.0	21.9	22.2	21.9	22.2	21.9	21.0	19.4	18.2	17.1	16.4
87.5°	13.6	13.6	13.8	14.4	13.8	13.6	13.6	13.0	12.9	12.2	11.5
90°	33.5	34.5	35.5	36.6	35.5	34.5	33.5	32.5	31.1	29.5	27.8
92.5°	69.7	70.4	71.1	71.9	71.1	70.4	69.7	68.9	67.5	65.1	62.9
95°	129.0	129.7	130.3	131.0	130.3	129.7	129.0	128.3	126.7	124.4	122.0
97.5°	197.4	197.8	198.2	198.6	198.2	197.8	197.4	197.0	195.6	193.4	191.2
100°	247.7	248.4	249.1	249.7	249.1	248.4	247.7	247.1	245.2	242.2	239.1
102.5°	298.1	299.0	300.0	300.9	300.0	299.0	298.1	297.2	295.0	291.8	288.4
105°	374.7	375.7	376.7	377.7	376.7	375.7	374.7	373.7	372.1	370.1	368.1
107.5°	456.5	456.5	456.4	456.3	456.4	456.5	456.5	456.6	456.1	455.0	454.0
110°	515.8	515.4	515.1	514.8	515.1	515.4	515.8	516.1	515.8	514.8	513.8



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	573.9	573.3	572.7	572.1	572.7	573.3	573.9	574.5	574.5	574.1	573.6
115°	663.6	663.2	662.9	662.6	662.9	663.2	663.6	663.9	664.2	664.6	664.9
117.5°	754.9	753.6	752.2	750.8	752.2	753.6	754.9	756.3	756.8	756.6	756.3
120°	815.9	814.5	813.1	811.8	813.1	814.5	815.9	817.2	817.9	817.9	817.9
122.5°	876.0	874.8	873.7	872.7	873.7	874.8	876.0	877.1	877.7	878.0	878.3
125°	965.1	964.7	964.4	964.1	964.4	964.7	965.1	965.4	965.9	966.6	967.3
127.5°	1053.8	1053.2	1052.5	1051.8	1052.5	1053.2	1053.8	1054.5	1055.0	1055.4	1055.7
130°	1112.4	1111.7	1111.0	1110.3	1111.0	1111.7	1112.4	1113.0	1113.5	1113.9	1114.2
132.5°	1168.0	1167.0	1166.1	1165.1	1166.1	1167.0	1168.0	1168.9	1169.5	1169.9	1170.2
135°	1254.5	1253.1	1251.7	1250.4	1251.7	1253.1	1254.5	1255.9	1256.5	1256.5	1256.5
137.5°	1339.0	1337.3	1335.5	1333.8	1335.5	1337.3	1339.0	1340.7	1341.3	1340.9	1340.5
140°	1392.6	1390.9	1389.2	1387.5	1389.2	1390.9	1392.6	1394.2	1394.7	1394.1	1393.4
142.5°	1443.7	1442.1	1440.4	1438.7	1440.4	1442.1	1443.7	1445.4	1446.1	1445.6	1445.2
145°	1518.4	1517.4	1516.4	1515.4	1516.4	1517.4	1518.4	1519.4	1519.9	1519.9	1519.9
147.5°	1587.8	1585.5	1583.3	1580.9	1583.3	1585.5	1587.8	1590.1	1590.8	1590.0	1589.2
150°	1631.6	1631.0	1630.3	1629.6	1630.3	1631.0	1631.6	1632.3	1632.7	1632.7	1632.7
152.5°	1673.5	1672.3	1671.1	1669.9	1671.1	1672.3	1673.5	1674.8	1675.0	1674.2	1673.3
155°	1732.2	1730.5	1728.8	1727.2	1728.8	1730.5	1732.2	1733.9	1734.0	1732.7	1731.3
157.5°	1781.6	1779.4	1777.2	1774.9	1777.2	1779.4	1781.6	1783.9	1784.3	1783.0	1781.6
160°	1812.9	1811.2	1809.6	1807.9	1809.6	1811.2	1812.9	1814.6	1814.8	1813.4	1812.1
162.5°	1841.8	1839.8	1837.9	1835.8	1837.9	1839.8	1841.8	1843.7	1843.9	1842.3	1840.7
165°	1879.5	1877.4	1875.4	1873.3	1875.4	1877.4	1879.5	1881.5	1881.8	1880.5	1879.1
167.5°	1909.5	1907.4	1905.3	1903.2	1905.3	1907.4	1909.5	1911.6	1911.6	1909.6	1907.5
170°	1926.1	1923.8	1921.4	1919.0	1921.4	1923.8	1926.1	1928.5	1928.6	1926.6	1924.6
172.5°	1938.7	1936.6	1934.5	1932.5	1934.5	1936.6	1938.7	1940.9	1940.9	1938.8	1936.8
175°	1952.1	1949.6	1947.3	1944.9	1947.3	1949.6	1952.1	1954.4	1954.6	1952.6	1950.6
177.5°	1957.9	1956.0	1954.1	1952.3	1954.1	1956.0	1957.9	1959.8	1959.9	1958.3	1956.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	525.7	528.0	530.7	532.8	536.5	538.2	540.3	541.9	544.9	547.8	551.1
5°	490.3	494.2	499.6	505.4	512.2	516.8	523.4	527.4	535.3	542.5	549.6
7.5°	458.2	463.0	470.6	478.1	487.0	494.9	503.1	512.2	522.3	534.3	544.2
10°	436.2	442.6	450.8	460.2	470.9	480.2	491.2	501.0	513.4	527.4	540.5
12.5°	418.6	424.1	433.2	442.2	453.7	465.1	476.5	489.4	503.8	519.4	535.7
15°	394.4	399.0	406.5	418.9	430.5	441.7	458.8	470.9	489.1	506.3	526.2
17.5°	373.7	379.5	385.8	396.4	408.5	422.4	437.7	452.9	470.4	492.3	514.6
20°	361.0	365.7	372.8	381.0	393.8	407.9	422.3	437.8	459.2	481.9	505.9
22.5°	347.2	352.2	360.4	369.3	380.1	393.5	409.5	426.4	448.8	471.0	497.2
25°	330.9	334.4	341.8	349.8	360.5	371.9	388.5	407.2	429.4	454.8	481.4
27.5°	315.6	318.6	325.4	332.3	342.0	355.6	370.4	389.3	410.2	436.0	465.4
30°	304.5	307.8	313.9	321.3	330.6	342.5	357.7	375.5	397.9	423.0	453.8
32.5°	295.0	297.9	302.5	309.9	319.1	330.6	344.7	362.7	385.2	410.7	441.0
35°	280.2	283.5	287.0	292.9	300.7	311.9	327.4	344.5	365.9	390.6	418.4
37.5°	265.6	269.1	272.3	277.5	284.7	294.6	307.9	325.7	345.1	368.9	395.6
40°	256.4	259.2	261.9	267.4	274.7	284.0	296.4	312.3	332.8	355.0	377.1
42.5°	247.3	249.9	252.1	257.0	263.7	272.6	284.4	299.9	318.9	339.6	359.2
45°	232.9	234.5	237.1	241.3	246.6	254.8	266.2	280.0	296.1	315.7	330.4
47.5°	217.3	219.8	222.0	225.6	230.0	238.0	249.0	260.7	275.4	289.9	300.2
50°	205.3	207.9	211.0	214.5	218.6	226.1	236.1	248.0	260.4	271.7	280.4
52.5°	194.1	196.5	199.8	203.1	208.2	214.5	223.1	233.7	245.9	253.9	261.3
55°	177.5	178.7	182.5	185.7	190.7	195.3	204.0	213.3	220.8	226.8	232.9
57.5°	160.7	162.2	164.4	167.3	172.2	177.6	183.7	192.0	196.3	199.4	204.2
60°	149.8	150.3	151.7	155.2	159.0	163.8	170.8	176.6	180.0	182.5	186.4
62.5°	137.8	137.9	140.3	142.9	145.6	151.0	156.6	161.4	164.0	165.3	169.1
65°	121.1	120.7	122.0	124.1	127.4	130.9	135.8	140.0	139.8	141.2	143.5
67.5°	104.0	103.5	103.5	105.5	108.2	111.3	114.6	117.1	117.1	119.0	120.2
70°	92.4	91.0	91.9	93.6	94.7	97.4	101.1	102.0	102.2	103.1	104.3
72.5°	80.5	80.0	80.7	81.4	82.2	84.2	87.5	88.0	88.1	88.6	90.5
75°	63.9	63.5	63.0	63.7	64.6	66.0	67.2	68.2	67.9	68.2	69.6
77.5°	48.0	46.7	46.4	46.8	47.0	47.9	49.1	49.0	49.2	49.2	50.7
80°	38.1	36.2	36.0	36.0	36.2	36.7	37.1	37.6	36.9	37.6	38.1
82.5°	28.0	26.9	26.8	26.6	26.7	26.8	27.1	27.3	27.2	27.5	27.8
85°	15.5	14.9	14.2	14.7	14.4	13.7	14.2	13.5	13.3	13.5	13.7
87.5°	10.4	10.3	9.4	9.0	8.3	8.0	7.2	6.4	5.7	5.4	5.4
90°	26.1	24.3	22.0	19.6	17.3	14.8	12.3	9.7	7.0	4.2	1.5
92.5°	60.7	58.5	55.5	52.6	49.8	46.9	44.4	42.5	40.7	38.8	36.9
95°	119.7	117.2	113.9	110.5	107.1	103.7	101.7	101.0	100.4	99.7	99.0
97.5°	188.9	186.7	182.1	177.4	172.7	168.0	165.6	165.3	165.0	164.7	164.5
100°	236.1	233.0	228.6	224.2	219.8	215.4	213.2	213.2	213.2	213.2	213.2
102.5°	285.1	281.8	279.5	277.3	275.1	272.9	271.0	269.6	268.3	267.0	265.6
105°	366.1	364.1	361.9	359.9	357.9	355.9	354.1	352.3	350.6	348.9	347.3
107.5°	453.0	452.0	450.5	448.9	447.4	445.9	444.1	442.5	440.8	439.1	437.4
110°	512.7	511.7	510.7	509.7	508.7	507.7	506.3	504.6	502.9	501.3	499.6



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	573.1	572.7	571.4	570.1	568.8	567.5	566.4	565.5	564.7	563.8	562.9
115°	665.2	665.6	664.9	664.2	663.6	662.9	661.9	660.5	659.1	657.8	656.4
117.5°	756.0	755.8	755.1	754.5	753.9	753.3	752.7	752.0	751.4	750.8	750.2
120°	817.9	817.9	817.5	817.2	816.9	816.5	815.5	813.9	812.1	810.4	808.7
122.5°	878.5	878.8	877.9	877.1	876.2	875.3	874.5	873.9	873.3	872.7	872.1
125°	968.0	968.7	968.4	968.0	967.7	967.3	966.1	964.1	962.1	960.0	958.0
127.5°	1056.0	1056.4	1056.0	1055.6	1055.2	1054.8	1054.0	1052.8	1051.7	1050.6	1049.4
130°	1114.5	1114.9	1114.2	1113.5	1112.9	1112.2	1111.0	1109.2	1107.6	1105.9	1104.2
132.5°	1170.5	1170.9	1171.0	1171.1	1171.3	1171.4	1170.1	1167.4	1164.6	1161.8	1159.0
135°	1256.5	1256.5	1256.2	1255.9	1255.5	1255.2	1253.9	1251.9	1249.9	1247.9	1245.9
137.5°	1340.1	1339.7	1338.9	1338.2	1337.5	1336.7	1335.3	1333.3	1331.4	1329.5	1327.5
140°	1392.7	1392.1	1391.1	1390.1	1389.0	1388.0	1386.6	1384.9	1383.2	1381.6	1379.9
142.5°	1444.8	1444.4	1443.2	1441.9	1440.6	1439.3	1437.9	1436.5	1435.1	1433.7	1432.3
145°	1519.9	1519.9	1518.9	1517.9	1516.9	1515.9	1514.8	1513.4	1512.1	1510.7	1509.3
147.5°	1588.4	1587.6	1586.8	1586.0	1585.2	1584.4	1583.6	1582.9	1582.1	1581.3	1580.6
150°	1632.7	1632.7	1631.3	1630.0	1628.6	1627.3	1626.8	1627.1	1627.5	1627.8	1628.1
152.5°	1672.5	1671.7	1671.1	1670.6	1670.1	1669.5	1669.0	1668.5	1668.1	1667.6	1667.1
155°	1730.0	1728.7	1728.3	1728.0	1727.7	1727.3	1727.2	1727.2	1727.2	1727.2	1727.2
157.5°	1780.3	1778.9	1778.6	1778.3	1777.9	1777.6	1777.8	1778.5	1779.3	1780.0	1780.7
160°	1810.7	1809.4	1809.1	1808.7	1808.4	1808.1	1808.4	1809.4	1810.4	1811.4	1812.4
162.5°	1839.1	1837.3	1837.3	1837.2	1837.1	1837.1	1837.4	1838.3	1839.0	1839.7	1840.5
165°	1877.7	1876.4	1876.0	1875.7	1875.4	1875.0	1875.2	1875.9	1876.5	1877.2	1877.9
167.5°	1905.5	1903.5	1903.5	1903.5	1903.5	1903.5	1904.2	1905.5	1906.9	1908.2	1909.6
170°	1922.6	1920.6	1920.6	1920.6	1920.6	1920.6	1921.3	1922.6	1923.9	1925.3	1926.6
172.5°	1934.8	1932.8	1932.8	1932.8	1932.8	1932.8	1933.4	1934.8	1936.1	1937.5	1938.8
175°	1948.4	1946.4	1946.4	1946.4	1946.4	1946.4	1947.1	1948.4	1949.8	1951.2	1952.6
177.5°	1955.1	1953.5	1953.7	1954.0	1954.3	1954.5	1955.2	1956.3	1957.4	1958.4	1959.5
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	552.8	555.3	557.0	560.2	562.8	564.3	565.6	566.7	568.0	569.2	572.4
5°	556.3	562.4	567.5	575.4	582.7	588.2	594.3	599.7	604.1	610.5	615.3
7.5°	554.7	565.5	576.8	589.2	601.7	613.3	624.1	634.1	643.2	654.2	663.9
10°	553.3	567.9	582.4	599.1	616.0	630.5	644.0	657.8	667.8	681.9	693.8
12.5°	552.2	569.5	586.9	606.8	625.5	646.0	664.0	674.1	689.3	700.5	714.7
15°	547.4	570.3	594.3	616.7	643.4	662.3	678.1	697.7	712.0	726.2	741.5
17.5°	539.0	564.9	591.8	621.2	646.6	666.9	687.4	706.3	723.3	742.4	761.5
20°	535.0	561.0	591.8	621.9	646.8	668.0	689.0	709.8	728.5	753.1	775.2
22.5°	526.8	558.2	586.5	615.9	641.6	664.7	688.5	712.1	736.9	764.6	792.3
25°	512.2	543.9	574.0	603.0	628.8	657.8	683.3	714.8	746.5	783.2	817.7
27.5°	497.0	527.4	554.9	582.9	613.1	645.9	678.8	714.6	756.2	802.4	851.1
30°	484.6	513.4	540.2	568.9	600.4	637.2	673.5	715.9	764.0	816.0	873.9
32.5°	470.3	496.8	522.8	553.2	587.5	626.4	668.6	715.2	773.0	832.0	891.6
35°	445.7	467.9	494.7	527.1	565.8	610.5	659.2	714.3	780.5	848.5	898.6
37.5°	416.6	437.2	465.4	501.0	541.6	589.5	647.3	712.7	783.0	837.2	853.3
40°	396.9	416.1	445.5	482.3	523.8	574.5	637.9	707.0	775.2	809.7	796.4
42.5°	376.0	396.1	424.7	461.2	505.9	561.1	626.2	695.3	752.5	765.5	719.5
45°	343.1	363.8	392.0	428.9	477.0	536.7	604.6	667.4	700.2	676.7	605.5
47.5°	312.4	331.8	358.0	396.1	445.7	507.5	572.8	622.9	625.5	569.3	493.2
50°	291.4	309.4	335.8	373.9	423.0	485.6	544.6	584.1	566.3	502.6	429.6
52.5°	270.9	288.5	314.5	352.1	400.8	458.2	513.1	540.8	507.4	441.9	379.6
55°	241.3	256.7	282.2	316.9	363.0	416.3	462.9	472.5	429.1	364.8	314.1
57.5°	212.4	226.7	249.8	281.9	324.2	371.2	407.8	405.7	359.8	304.6	264.4
60°	192.8	206.7	227.3	258.5	297.1	337.7	368.9	361.4	316.0	268.3	234.5
62.5°	175.2	187.7	207.1	234.5	269.6	307.2	332.9	321.8	277.3	235.7	208.9
65°	149.4	159.9	176.4	199.8	228.9	259.9	279.8	265.6	227.5	195.1	173.6
67.5°	124.6	133.1	146.9	165.6	190.5	215.4	227.4	213.2	182.7	159.1	143.1
70°	109.0	116.4	127.1	143.7	165.4	186.4	195.5	182.7	156.5	136.2	124.8
72.5°	93.3	99.5	108.9	123.8	141.2	159.4	167.3	155.1	133.6	116.4	105.8
75°	72.1	76.3	82.8	93.1	106.8	121.4	125.7	115.0	101.3	88.5	81.4
77.5°	51.6	55.1	60.1	66.6	76.3	85.5	89.4	83.2	72.6	64.4	58.7
80°	39.7	41.5	45.7	51.1	58.8	64.6	67.2	63.2	55.7	49.7	45.2
82.5°	28.3	30.2	32.6	37.1	42.0	45.9	48.7	46.0	40.7	35.9	33.3
85°	13.7	14.9	16.4	18.2	21.9	24.2	24.0	22.4	20.3	18.5	17.1
87.5°	5.7	6.5	7.6	9.0	10.1	11.3	12.1	12.2	12.0	11.7	11.5
90°	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1	27.8
92.5°	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7	62.9
95°	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7	122.0
97.5°	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9	191.2
100°	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1	239.1
102.5°	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1	288.4
105°	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1	368.1
107.5°	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0	454.0
110°	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7	513.8



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1	573.6
115°	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2	664.9
117.5°	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0	756.3
120°	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9	817.9
122.5°	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5	878.3
125°	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0	967.3
127.5°	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0	1055.7
130°	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5	1114.2
132.5°	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5	1170.2
135°	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5	1256.5
137.5°	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1	1340.5
140°	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7	1393.4
142.5°	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8	1445.2
145°	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9	1519.9
147.5°	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4	1589.2
150°	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7	1632.7
152.5°	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5	1673.3
155°	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0	1731.3
157.5°	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3	1781.6
160°	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7	1812.1
162.5°	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1	1840.7
165°	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7	1879.1
167.5°	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5	1907.5
170°	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6	1924.6
172.5°	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8	1936.8
175°	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4	1950.6
177.5°	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1	1956.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	575.0	576.4	579.7	578.6	580.0	580.8	581.5
5°	621.4	628.8	632.2	631.7	636.6	635.4	634.2
7.5°	673.9	681.7	686.1	691.6	694.7	695.0	697.7
10°	703.6	713.8	718.0	723.9	727.6	729.7	729.4
12.5°	726.3	734.4	743.8	746.6	751.6	754.4	753.4
15°	753.8	766.6	776.4	781.2	787.6	789.4	791.9
17.5°	778.2	795.4	806.8	822.0	827.8	831.3	829.2
20°	796.7	819.3	830.7	848.9	859.0	864.3	862.4
22.5°	818.5	843.0	864.1	879.9	895.1	902.4	903.9
25°	856.0	889.5	920.6	941.3	960.2	964.6	974.4
27.5°	897.8	937.4	970.6	992.4	1005.5	1010.5	1013.6
30°	924.0	963.5	988.5	1002.5	1006.6	1006.2	1005.7
32.5°	937.0	961.6	966.4	962.5	952.9	944.7	936.2
35°	918.7	900.3	872.7	837.3	811.1	784.8	782.1
37.5°	826.3	767.3	721.4	670.2	640.8	622.5	609.9
40°	739.2	672.3	616.7	573.6	543.5	531.6	519.9
42.5°	644.8	580.8	531.6	495.5	472.9	459.7	450.5
45°	523.8	467.4	428.9	402.7	384.8	374.6	368.7
47.5°	429.3	387.5	354.8	335.9	323.6	315.6	315.6
50°	378.5	338.6	316.9	301.9	291.2	284.9	286.1
52.5°	333.5	303.7	285.2	272.7	264.7	260.8	260.6
55°	278.8	257.4	245.3	236.1	230.8	226.3	227.3
57.5°	238.5	220.5	212.3	204.7	201.0	199.2	196.6
60°	213.5	199.5	192.5	186.4	182.7	181.3	178.7
62.5°	191.3	180.3	173.5	168.5	165.2	164.7	162.7
65°	160.8	152.4	146.3	144.0	140.5	139.6	139.6
67.5°	132.5	126.5	121.8	119.7	118.2	118.4	117.2
70°	114.8	109.9	106.8	104.5	103.4	103.6	102.7
72.5°	100.5	94.9	92.3	90.9	89.4	90.0	89.6
75°	76.0	73.3	71.9	70.5	69.6	69.1	68.6
77.5°	55.8	53.4	52.3	51.5	51.7	50.5	51.4
80°	43.1	41.1	40.4	39.2	39.0	39.0	38.8
82.5°	31.6	30.4	29.9	29.0	28.5	28.9	28.3
85°	16.4	15.5	15.1	15.1	14.7	14.2	15.5
87.5°	11.8	11.4	11.7	11.7	11.9	11.9	11.8
90°	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333365-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)