

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333368-840

Luminaire Tested: **S125DIW-S375D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333368-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7836.9 lumens
Efficiency: N/A
Efficacy: 146.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12				
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10				
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	46	39	33	51	41	35	30	32	27	24	22	20	17	14	12	11	8				
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10	7				
8	49	38	30	25	43	34	27	23	26	21	18	19	16	13	12	10	9	6				
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5				
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3810	3810	3810
5°	3818	3782	3806
10°	3796	3756	3777
15°	3754	3710	3726
20°	3696	3647	3654
25°	3632	3572	3569
30°	3554	3491	3473
35°	3470	3404	3356
40°	3384	3309	3262
45°	3291	3222	3159
50°	3189	3118	3024
55°	3090	3001	2916
60°	2971	2882	2780
65°	2832	2740	2647
70°	2696	2574	2485
75°	2458	2376	2293
80°	2187	2153	2101
85°	1904	1941	1830



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	0.7
10°-20°	157.1	2.0
20°-30°	232.0	3.0
30°-40°	270.7	3.5
40°-50°	271.9	3.5
50°-60°	238.7	3.0
60°-70°	177.8	2.3
70°-80°	101.7	1.3
80°-90°	33.8	0.4
90°-100°	74.5	1.0
100°-110°	459.3	5.9
110°-120°	833.0	10.6
120°-130°	1069.1	13.6
130°-140°	1149.9	14.7
140°-150°	1079.3	13.8
150°-160°	873.1	11.1
160°-170°	564.7	7.2
170°-180°	194.8	2.5
0°-30°	444.7	5.7
0°-40°	715.5	9.1
0°-60°	1226.0	15.6
0°-90°	1539.4	19.6
90°-120°	1366.8	17.4
90°-150°	4665.0	59.5
90°-180°	6298.0	80.4
0°-180°	7836.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	589	588	583	587	587	56
15°	562	560	555	557	557	158
25°	510	507	501	502	501	234
35°	440	438	432	429	426	275
45°	360	358	353	348	346	278
55°	274	273	266	262	259	245
65°	185	184	179	175	173	184
75°	98	98	95	94	92	105
85°	26	26	26	26	25	29
90°	2	14	24	32	36	5
95°	87	79	24	32	32	110
105°	447	453	453	453	452	474
115°	839	846	848	842	833	832
125°	1193	1203	1204	1198	1193	1065
135°	1488	1497	1494	1491	1482	1147
145°	1726	1728	1728	1729	1721	1079
155°	1900	1892	1894	1898	1886	875
165°	2005	1997	1998	2006	1994	566
175°	2051	2042	2043	2054	2042	195
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	591.4	591.2	591.0	590.7	590.5	589.9	589.1	588.2	587.4	586.5	587.4
5°	589.0	588.8	588.5	588.3	588.1	587.5	586.5	585.5	584.4	583.4	584.3
7.5°	583.6	583.4	583.2	583.0	582.8	582.1	581.0	579.8	578.7	577.5	578.5
10°	578.8	578.6	578.3	578.1	577.9	577.2	576.1	574.9	573.8	572.7	573.5
12.5°	572.8	572.4	572.0	571.7	571.3	570.6	569.5	568.5	567.3	566.3	566.9
15°	561.5	561.2	560.9	560.6	560.2	559.5	558.4	557.2	556.0	554.9	555.4
17.5°	548.5	548.1	547.5	547.1	546.6	545.8	544.6	543.5	542.3	541.1	541.8
20°	537.7	537.5	537.2	537.0	536.8	536.0	534.7	533.3	532.0	530.7	531.4
22.5°	526.8	526.4	526.0	525.7	525.3	524.5	523.2	522.0	520.7	519.5	520.0
25°	509.7	509.2	508.6	508.1	507.6	506.6	505.3	503.9	502.6	501.3	501.5
27.5°	489.6	489.3	489.0	488.7	488.4	487.5	486.1	484.7	483.3	481.9	482.0
30°	476.6	476.3	475.8	475.5	475.2	474.3	472.8	471.2	469.7	468.1	467.9
32.5°	462.3	461.8	461.4	460.9	460.4	459.5	458.1	456.7	455.3	453.9	453.5
35°	440.1	439.7	439.3	438.9	438.5	437.5	436.1	434.6	433.1	431.7	431.2
37.5°	417.1	416.6	416.1	415.5	415.0	414.0	412.6	411.3	409.9	408.6	407.8
40°	401.4	400.8	400.3	399.8	399.3	398.3	396.9	395.5	393.9	392.5	391.6
42.5°	384.6	384.2	383.7	383.2	382.8	381.9	380.4	379.0	377.5	376.1	375.3
45°	360.3	359.9	359.5	359.1	358.6	357.8	356.6	355.4	354.1	352.8	351.6
47.5°	334.2	334.2	334.2	334.3	334.3	333.6	332.0	330.5	329.0	327.5	326.3
50°	317.4	317.1	316.8	316.4	316.1	315.4	314.1	312.9	311.6	310.3	309.0
52.5°	300.2	299.9	299.7	299.5	299.3	298.5	297.2	295.9	294.5	293.2	292.1
55°	274.4	274.1	273.8	273.5	273.2	272.3	270.8	269.4	267.9	266.5	265.6
57.5°	247.3	247.1	246.9	246.8	246.6	245.9	244.7	243.5	242.3	241.1	239.8
60°	230.0	229.6	229.2	228.8	228.4	227.6	226.5	225.4	224.2	223.1	222.1
62.5°	212.2	211.9	211.5	211.2	210.9	210.2	209.2	208.2	207.2	206.3	205.2
65°	185.3	185.1	184.9	184.7	184.5	183.8	182.7	181.5	180.4	179.3	178.2
67.5°	159.3	158.9	158.3	157.9	157.5	156.8	156.0	155.1	154.3	153.5	152.7
70°	142.8	142.3	141.8	141.3	140.8	140.0	139.1	138.1	137.2	136.3	135.6
72.5°	124.9	124.5	124.2	123.8	123.5	123.0	122.4	121.8	121.2	120.6	119.9
75°	98.5	98.3	98.1	97.9	97.7	97.3	96.7	96.2	95.7	95.2	94.9
77.5°	74.1	74.0	73.9	73.8	73.8	73.6	73.3	73.0	72.7	72.4	72.2
80°	58.8	58.8	58.8	58.8	58.8	58.7	58.5	58.3	58.1	57.9	57.8
82.5°	45.3	45.2	45.0	44.8	44.7	44.6	44.5	44.5	44.4	44.4	44.2
85°	25.7	25.8	25.9	26.0	26.1	26.2	26.2	26.2	26.2	26.2	26.1
87.5°	10.4	10.9	11.5	12.0	12.5	13.0	13.4	13.8	14.1	14.5	14.9
90°	1.5	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1
92.5°	23.4	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1
95°	86.6	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1
97.5°	180.9	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2
100°	253.9	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2
102.5°	328.1	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0
105°	447.0	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5
110°	650.7	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	726.1	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2
115°	839.2	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9
117.5°	956.2	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9
120°	1029.2	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6
122.5°	1093.7	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9
125°	1193.4	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6
127.5°	1288.5	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4
130°	1346.9	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0
132.5°	1405.2	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6
135°	1488.2	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7
137.5°	1564.6	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9
140°	1614.5	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7
142.5°	1659.4	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6
145°	1725.5	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8
147.5°	1783.2	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8
150°	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4
152.5°	1854.9	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0
155°	1900.3	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2
157.5°	1935.2	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2
160°	1959.5	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3
162.5°	1979.0	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3
165°	2005.2	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5
167.5°	2024.6	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1
170°	2035.6	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1
172.5°	2042.9	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4
175°	2050.7	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9
177.5°	2054.4	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.0	590.0	590.0	590.0	590.0	590.0	590.0	590.0
2.5°	588.2	589.1	589.9	590.3	590.2	590.1	590.1	590.0
5°	585.2	586.2	587.1	587.5	587.4	587.3	587.2	587.1
7.5°	579.4	580.3	581.2	581.6	581.5	581.4	581.3	581.2
10°	574.3	575.1	576.0	576.3	576.2	576.1	576.0	575.9
12.5°	567.6	568.4	569.0	569.3	569.3	569.3	569.3	569.2
15°	555.9	556.4	557.0	557.2	557.2	557.2	557.2	557.2
17.5°	542.4	543.0	543.7	543.7	543.2	542.7	542.2	541.7
20°	532.1	532.8	533.5	533.7	533.1	532.6	532.1	531.6
22.5°	520.4	520.9	521.4	521.4	521.1	520.7	520.4	520.0
25°	501.7	501.9	502.1	502.0	501.7	501.4	501.1	500.8
27.5°	482.0	482.0	482.1	482.0	481.6	481.3	481.0	480.7
30°	467.7	467.5	467.3	467.1	466.8	466.5	466.1	465.7
32.5°	453.2	452.8	452.4	452.0	451.4	450.8	450.3	449.7
35°	430.7	430.2	429.6	429.0	428.2	427.3	426.5	425.7
37.5°	407.1	406.3	405.5	404.9	404.3	403.9	403.4	402.9
40°	390.6	389.7	388.8	388.2	387.9	387.5	387.2	386.9
42.5°	374.4	373.5	372.6	372.0	371.5	371.0	370.6	370.1
45°	350.3	349.1	347.9	347.1	346.8	346.5	346.2	345.9
47.5°	325.0	323.8	322.4	321.4	320.7	320.0	319.3	318.6
50°	307.7	306.3	305.0	304.0	303.2	302.5	301.7	301.0
52.5°	290.8	289.6	288.4	287.5	286.7	285.9	285.1	284.3
55°	264.6	263.7	262.8	262.0	261.3	260.4	259.7	259.0
57.5°	238.6	237.4	236.2	235.4	235.0	234.6	234.2	233.8
60°	221.1	219.9	218.9	218.0	217.3	216.6	215.9	215.2
62.5°	204.1	202.9	201.8	201.0	200.5	199.9	199.2	198.7
65°	177.3	176.4	175.5	174.8	174.4	174.0	173.6	173.2
67.5°	151.9	151.1	150.3	149.8	149.6	149.3	149.1	148.8
70°	135.0	134.4	133.8	133.3	132.9	132.5	132.0	131.6
72.5°	119.2	118.5	117.8	117.2	116.8	116.4	115.9	115.5
75°	94.6	94.3	93.9	93.6	93.2	92.8	92.4	91.9
77.5°	72.1	71.9	71.7	71.5	71.2	70.9	70.6	70.3
80°	57.7	57.6	57.5	57.3	57.1	56.9	56.7	56.5
82.5°	44.0	43.8	43.7	43.5	43.5	43.5	43.4	43.4
85°	26.0	25.9	25.8	25.5	25.3	25.1	24.9	24.7
87.5°	15.2	15.6	16.0	16.2	16.2	16.2	16.3	16.3
90°	27.7	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	27.7	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	55.7	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	163.8	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	318.4	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	651.7	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333368-840

CATALOG NUMBER: S125DIW-S375D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	728.9	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	845.6	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	958.2	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.9	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1100.1	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1201.3	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.7	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1354.0	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.4	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1493.0	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.0	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1617.3	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.7	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.2	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.2	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.0	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1852.7	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1896.2	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1932.2	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1954.6	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1975.2	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2001.6	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2021.5	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2031.8	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2039.8	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2048.5	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2052.1	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)