

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333455

Luminaire Tested: **S125DIW-S1090D1560U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333455
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9899.3 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45					45			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39					39			
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33					33			
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28					28			
4	74	63	56	50	68	58	52	46	49	44	40	41	37	34	33	30	28	24					24			
5	68	56	48	43	62	52	45	40	44	39	35	36	32	29	29	27	24	21					21			
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18					18			
7	58	46	38	32	53	42	35	30	36	30	27	30	26	23	24	21	19	16					16			
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15					15			
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13					13			
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10270	10270	10270	10270
5°	11893	10305	9022	10305
10°	13837	10251	7906	10251
15°	15317	10176	7293	10176
20°	17145	10057	6801	10057
25°	20085	9922	6560	9922
30°	21694	9790	6352	9790
35°	17837	9541	6215	9541
40°	12678	9195	6066	9195
45°	9740	8729	5980	8729
50°	8314	8151	5968	8151
55°	7402	7585	6019	7585
60°	6678	6966	6173	6966
65°	6168	6343	6333	6343
70°	5608	5697	6424	5697
75°	4951	5018	6366	5018
80°	4166	4091	5824	4091
85°	3298	2949	4698	2949



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	1.5
10°-20°	455.8	4.6
20°-30°	740.1	7.5
30°-40°	902.8	9.1
40°-50°	821.3	8.3
50°-60°	654.2	6.6
60°-70°	455.6	4.6
70°-80°	243.0	2.5
80°-90°	65.6	0.7
90°-100°	129.8	1.3
100°-110°	383.3	3.9
110°-120°	649.2	6.6
120°-130°	854.4	8.6
130°-140°	957.4	9.7
140°-150°	938.3	9.5
150°-160°	788.1	8.0
160°-170°	523.9	5.3
170°-180°	183.3	1.9
0°-30°	1349.0	13.6
0°-40°	2251.8	22.7
0°-60°	3727.3	37.7
0°-90°	4491.4	45.4
90°-120°	1162.3	11.7
90°-150°	3912.5	39.5
90°-180°	5408.0	54.6
0°-180°	9899.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1834	1590	1392	1590	1834	185
15°	2291	1522	1091	1522	2291	656
25°	2819	1392	921	1392	2819	1287
35°	2262	1210	788	1210	2262	1385
45°	1066	956	655	956	1066	854
55°	657	674	535	674	657	592
65°	404	415	414	415	404	401
75°	198	201	255	201	198	214
85°	44	40	63	40	44	52
90°	36	2	36	2	36	22
95°	130	98	130	98	130	132
105°	374	344	374	344	374	396
115°	656	650	656	650	656	649
125°	955	949	955	949	955	852
135°	1238	1234	1238	1234	1238	955
145°	1501	1495	1501	1495	1501	937
155°	1710	1710	1710	1710	1710	787
165°	1855	1860	1855	1860	1855	523
175°	1926	1934	1926	1934	1926	183
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1682.0	1679.8	1677.7	1673.3	1676.6	1667.4	1663.1	1655.5	1646.3	1643.1	1639.3
5°	1834.5	1837.9	1841.3	1827.1	1828.4	1819.0	1797.4	1779.8	1765.7	1747.4	1734.6
7.5°	2018.1	2010.1	2009.5	2000.3	1984.5	1971.8	1949.1	1920.2	1892.3	1860.4	1834.1
10°	2109.9	2110.6	2104.5	2093.7	2076.8	2064.7	2035.0	2006.6	1972.2	1931.7	1902.7
12.5°	2179.0	2181.8	2174.2	2159.6	2151.3	2124.1	2100.9	2067.1	2026.2	1993.8	1949.7
15°	2290.8	2283.4	2278.0	2259.7	2245.6	2217.2	2180.1	2145.0	2100.4	2059.3	2018.1
17.5°	2398.5	2404.4	2394.3	2377.7	2333.7	2300.6	2250.8	2202.8	2147.3	2092.1	2042.9
20°	2494.6	2500.0	2484.5	2455.5	2402.8	2369.8	2304.3	2242.2	2178.1	2107.2	2053.2
22.5°	2614.5	2610.2	2589.2	2545.1	2499.5	2438.3	2367.5	2291.9	2211.5	2131.5	2059.7
25°	2818.6	2790.2	2777.4	2722.8	2662.7	2572.9	2475.7	2365.0	2265.1	2159.2	2067.4
27.5°	2931.7	2922.8	2908.5	2870.4	2807.3	2711.3	2596.7	2461.8	2320.9	2187.1	2067.0
30°	2909.0	2910.4	2911.7	2899.6	2859.1	2786.9	2672.8	2527.7	2360.3	2209.8	2070.7
32.5°	2708.2	2732.7	2756.2	2784.0	2795.4	2781.5	2710.1	2579.0	2406.7	2235.7	2068.6
35°	2262.4	2269.9	2346.1	2421.7	2524.3	2604.0	2657.3	2599.2	2454.1	2257.7	2066.0
37.5°	1764.1	1800.5	1853.3	1938.7	2086.8	2219.4	2389.9	2468.3	2421.5	2264.9	2061.3
40°	1503.8	1537.5	1572.0	1659.0	1783.9	1944.5	2138.2	2303.6	2342.1	2242.2	2045.1
42.5°	1302.9	1329.7	1367.9	1433.3	1537.7	1680.0	1865.0	2081.1	2214.1	2176.3	2011.1
45°	1066.4	1083.3	1113.0	1165.0	1240.6	1351.9	1515.3	1751.5	1957.4	2025.5	1930.4
47.5°	912.8	912.7	935.8	971.7	1026.2	1120.8	1241.6	1426.7	1646.6	1809.3	1801.7
50°	827.5	824.1	842.3	873.4	916.6	979.4	1094.8	1242.6	1453.8	1638.1	1689.4
52.5°	754.1	754.5	765.7	788.6	824.8	878.4	964.6	1097.9	1278.4	1467.5	1564.1
55°	657.4	654.7	667.5	683.1	709.4	744.5	806.6	908.5	1054.9	1241.2	1366.8
57.5°	568.8	576.3	581.4	592.2	614.1	637.6	689.9	764.7	880.9	1040.8	1173.5
60°	517.0	524.4	528.5	539.3	556.8	577.1	617.6	678.3	776.2	913.9	1045.5
62.5°	470.6	476.4	477.7	487.4	501.8	521.5	553.3	604.4	681.7	802.1	931.0
65°	403.6	403.6	406.3	416.4	423.2	440.7	465.0	502.2	564.3	658.1	768.1
67.5°	339.1	342.3	341.7	346.1	352.3	366.0	383.4	414.0	460.0	528.5	616.5
70°	297.0	299.7	299.0	302.4	309.1	317.9	332.1	361.1	394.2	452.9	528.5
72.5°	259.2	260.3	258.5	263.0	267.0	274.7	290.5	306.0	336.9	386.5	448.6
75°	198.4	199.8	201.1	203.8	207.9	211.9	220.0	235.6	255.8	292.9	332.8
77.5°	148.8	146.2	149.4	149.0	151.3	154.4	161.6	169.8	186.4	209.9	240.7
80°	112.0	112.7	112.7	113.4	116.8	118.8	124.9	130.9	143.8	161.3	182.9
82.5°	81.8	83.6	82.5	83.7	86.5	88.0	91.4	96.4	103.8	117.6	133.2
85°	44.5	41.2	42.5	43.9	43.9	44.5	47.2	49.3	53.3	58.7	64.8
87.5°	20.2	21.1	21.4	21.2	21.6	21.3	23.1	22.8	24.1	25.3	27.0
90°	36.2	35.2	34.2	33.2	32.2	30.8	29.2	27.5	25.8	24.1	21.8
92.5°	71.2	70.4	69.7	69.0	68.2	66.8	64.5	62.3	60.1	57.9	55.0
95°	129.7	129.0	128.4	127.7	127.0	125.5	123.2	120.8	118.5	116.1	112.8
97.5°	196.7	196.3	195.9	195.5	195.1	193.7	191.5	189.3	187.1	184.9	180.3
100°	247.3	246.7	246.0	245.3	244.7	242.8	239.8	236.8	233.8	230.7	226.4
102.5°	298.0	297.1	296.1	295.2	294.3	292.1	288.9	285.6	282.3	279.0	276.8
105°	374.0	373.0	372.0	371.0	370.0	368.5	366.5	364.5	362.5	360.5	358.4
107.5°	451.8	451.9	452.0	452.0	452.1	451.6	450.6	449.6	448.6	447.6	446.1
110°	509.8	510.1	510.4	510.8	511.1	510.8	509.8	508.8	507.7	506.7	505.7



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	566.5	567.1	567.7	568.3	568.9	568.9	568.5	568.0	567.5	567.1	565.8
115°	656.1	656.4	656.7	657.1	657.4	657.7	658.1	658.4	658.7	659.1	658.4
117.5°	743.5	744.9	746.2	747.5	748.9	749.4	749.2	748.9	748.6	748.4	747.7
120°	803.9	805.2	806.5	807.9	809.2	809.9	809.9	809.9	809.9	809.9	809.5
122.5°	864.2	865.2	866.3	867.4	868.5	869.1	869.4	869.7	869.9	870.2	869.3
125°	954.7	955.0	955.3	955.7	956.0	956.5	957.2	957.9	958.5	959.2	958.9
127.5°	1041.5	1042.2	1042.9	1043.5	1044.2	1044.7	1045.1	1045.4	1045.7	1046.1	1045.7
130°	1099.5	1100.1	1100.8	1101.5	1102.1	1102.6	1103.0	1103.3	1103.6	1104.0	1103.3
132.5°	1153.7	1154.7	1155.6	1156.6	1157.5	1158.1	1158.5	1158.8	1159.1	1159.5	1159.6
135°	1238.2	1239.5	1240.9	1242.2	1243.6	1244.2	1244.2	1244.2	1244.2	1244.2	1243.9
137.5°	1320.8	1322.5	1324.2	1325.9	1327.6	1328.2	1327.8	1327.4	1327.0	1326.6	1325.8
140°	1373.9	1375.6	1377.3	1379.0	1380.6	1381.1	1380.5	1379.8	1379.1	1378.5	1377.5
142.5°	1424.6	1426.3	1428.0	1429.6	1431.3	1432.0	1431.5	1431.1	1430.7	1430.3	1429.1
145°	1500.6	1501.6	1502.6	1503.6	1504.6	1505.1	1505.1	1505.1	1505.1	1505.1	1504.1
147.5°	1565.5	1567.8	1570.0	1572.3	1574.6	1575.3	1574.5	1573.7	1572.9	1572.1	1571.3
150°	1613.7	1614.4	1615.1	1615.7	1616.4	1616.8	1616.8	1616.8	1616.8	1616.8	1615.4
152.5°	1653.6	1654.8	1656.0	1657.2	1658.4	1658.6	1657.8	1657.0	1656.2	1655.4	1654.8
155°	1710.3	1711.9	1713.6	1715.3	1717.0	1717.1	1715.8	1714.4	1713.1	1711.8	1711.4
157.5°	1757.6	1759.8	1762.0	1764.2	1766.5	1766.9	1765.6	1764.2	1762.9	1761.5	1761.2
160°	1790.2	1791.9	1793.5	1795.2	1796.9	1797.1	1795.7	1794.4	1793.0	1791.7	1791.4
162.5°	1817.9	1819.9	1821.8	1823.8	1825.7	1825.9	1824.3	1822.7	1821.1	1819.4	1819.4
165°	1855.0	1857.1	1859.1	1861.1	1863.1	1863.4	1862.1	1860.7	1859.4	1858.1	1857.7
167.5°	1884.6	1886.7	1888.8	1890.8	1892.9	1892.9	1890.9	1888.9	1886.9	1884.9	1884.9
170°	1900.3	1902.6	1905.0	1907.3	1909.7	1909.8	1907.8	1905.8	1903.8	1901.8	1901.8
172.5°	1913.6	1915.6	1917.7	1919.8	1921.9	1921.9	1919.9	1917.9	1915.9	1913.9	1913.9
175°	1925.9	1928.3	1930.6	1933.0	1935.3	1935.5	1933.5	1931.5	1929.4	1927.4	1927.4
177.5°	1933.2	1935.0	1936.9	1938.8	1940.7	1940.8	1939.2	1937.6	1936.0	1934.4	1934.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1636.1	1632.3	1628.0	1620.4	1611.2	1606.4	1598.8	1594.0	1584.2	1576.1	1567.5
5°	1719.1	1701.6	1685.4	1664.4	1641.5	1626.6	1609.1	1589.5	1569.3	1548.3	1525.4
7.5°	1805.1	1774.0	1740.3	1704.0	1668.5	1635.8	1604.6	1574.0	1545.4	1510.8	1481.5
10°	1862.9	1823.7	1781.9	1732.6	1684.7	1642.8	1600.3	1563.2	1525.4	1484.9	1449.1
12.5°	1920.6	1868.5	1809.4	1755.3	1697.6	1647.1	1597.1	1549.7	1502.2	1457.4	1415.6
15°	1961.4	1915.5	1860.8	1783.9	1719.1	1649.6	1583.4	1522.0	1464.6	1414.7	1362.1
17.5°	1988.3	1929.1	1870.4	1796.6	1711.7	1633.9	1559.0	1488.7	1424.0	1360.7	1309.9
20°	1993.1	1932.4	1871.0	1798.7	1711.7	1622.6	1547.7	1463.3	1393.8	1328.3	1266.2
22.5°	1991.5	1922.7	1855.8	1781.5	1696.6	1614.5	1523.9	1437.9	1362.5	1298.1	1233.3
25°	1976.3	1902.7	1819.0	1744.1	1660.4	1573.3	1481.5	1392.4	1315.5	1241.9	1177.8
27.5°	1963.6	1868.1	1773.4	1686.0	1605.2	1525.4	1437.5	1346.3	1260.9	1186.4	1126.0
30°	1947.9	1843.3	1736.6	1645.5	1562.5	1484.9	1401.9	1312.8	1223.7	1150.8	1086.0
32.5°	1933.9	1812.0	1699.4	1600.2	1512.3	1436.8	1360.3	1275.5	1188.0	1114.1	1049.3
35°	1906.7	1765.7	1636.8	1524.7	1430.9	1353.3	1289.2	1210.2	1129.9	1058.3	996.2
37.5°	1872.3	1704.9	1566.6	1449.1	1346.3	1264.5	1204.8	1144.2	1067.1	998.1	942.0
40°	1845.3	1661.7	1515.3	1395.1	1288.5	1203.4	1148.1	1090.7	1026.6	962.5	903.1
42.5°	1811.3	1622.9	1463.4	1334.1	1228.5	1145.7	1087.6	1038.9	982.3	922.5	867.4
45°	1748.8	1552.4	1379.6	1240.6	1133.9	1052.2	992.2	955.7	913.2	856.5	809.9
47.5°	1656.9	1467.7	1289.0	1145.5	1035.5	959.8	903.5	868.5	838.6	796.4	754.2
50°	1575.3	1404.6	1223.7	1081.3	971.3	895.0	843.0	811.3	785.6	753.2	717.5
52.5°	1484.1	1325.2	1159.4	1018.6	909.7	834.5	783.6	755.7	734.3	711.1	675.9
55°	1339.1	1204.1	1050.2	916.6	816.0	742.4	697.9	673.6	656.1	638.5	616.9
57.5°	1179.4	1073.8	937.5	815.3	722.7	655.8	614.2	590.6	576.9	567.9	555.2
60°	1067.1	976.7	859.2	747.8	657.4	598.0	557.5	539.3	527.8	520.4	510.9
62.5°	962.9	888.6	779.8	678.2	599.1	542.9	506.8	489.1	478.1	474.5	466.7
65°	809.3	751.9	662.1	577.8	510.3	462.3	432.0	415.1	408.3	404.3	405.0
67.5°	657.9	623.0	550.9	478.9	425.1	384.9	360.6	347.6	344.2	338.8	338.7
70°	565.6	539.3	478.5	415.8	367.8	336.8	315.2	301.7	298.3	295.6	295.0
72.5°	484.1	461.0	408.3	358.0	314.9	287.7	269.8	261.7	256.2	254.6	254.5
75°	363.8	351.0	309.1	269.3	239.6	220.7	208.6	201.1	197.1	196.4	197.1
77.5°	258.6	247.4	220.8	192.6	173.9	159.6	149.3	146.7	142.1	142.3	141.6
80°	194.4	187.0	170.1	147.8	132.3	120.1	114.7	110.0	108.7	106.6	108.7
82.5°	140.9	133.0	121.5	107.3	94.5	87.2	81.8	80.3	79.5	78.6	79.0
85°	69.5	70.2	63.4	52.6	47.2	43.2	39.8	39.8	39.1	38.5	39.1
87.5°	27.6	26.1	23.5	21.3	18.1	16.0	14.9	14.9	13.8	13.8	14.9
90°	19.4	17.1	14.7	12.2	9.6	6.9	4.2	1.5	4.2	6.9	9.6
92.5°	52.1	49.3	46.4	44.0	42.1	40.3	38.4	36.5	38.4	40.3	42.1
95°	109.4	106.1	102.7	100.7	100.0	99.4	98.7	98.0	98.7	99.4	100.0
97.5°	175.7	171.0	166.4	164.0	163.7	163.4	163.1	162.9	163.1	163.4	163.7
100°	222.0	217.7	213.3	211.1	211.1	211.1	211.1	211.1	211.1	211.1	211.1
102.5°	274.6	272.4	270.2	268.4	267.0	265.7	264.4	263.0	264.4	265.7	267.0
105°	356.4	354.4	352.4	350.6	348.9	347.2	345.5	343.9	345.5	347.2	348.9
107.5°	444.5	443.0	441.5	439.8	438.2	436.5	434.8	433.1	434.8	436.5	438.2
110°	504.7	503.7	502.7	501.4	499.7	498.0	496.4	494.7	496.4	498.0	499.7



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.5	563.2	562.0	560.9	560.0	559.2	558.3	557.4	558.3	559.2	560.0
115°	657.7	657.1	656.4	655.4	654.0	652.7	651.4	650.0	651.4	652.7	654.0
117.5°	747.1	746.5	745.9	745.3	744.7	744.1	743.5	742.9	743.5	744.1	744.7
120°	809.2	808.9	808.5	807.5	805.9	804.2	802.5	800.8	802.5	804.2	805.9
122.5°	868.5	867.6	866.7	866.0	865.4	864.8	864.2	863.6	864.2	864.8	865.4
125°	958.5	958.2	957.9	956.7	954.7	952.7	950.6	948.6	950.6	952.7	954.7
127.5°	1045.3	1044.9	1044.5	1043.7	1042.5	1041.4	1040.3	1039.1	1040.3	1041.4	1042.5
130°	1102.6	1102.0	1101.3	1100.1	1098.4	1096.8	1095.1	1093.4	1095.1	1096.8	1098.4
132.5°	1159.7	1159.9	1160.0	1158.7	1156.0	1153.2	1150.5	1147.7	1150.5	1153.2	1156.0
135°	1243.6	1243.2	1242.9	1241.7	1239.7	1237.7	1235.7	1233.7	1235.7	1237.7	1239.7
137.5°	1325.1	1324.4	1323.6	1322.3	1320.3	1318.4	1316.5	1314.5	1316.5	1318.4	1320.3
140°	1376.5	1375.4	1374.4	1373.1	1371.4	1369.7	1368.1	1366.4	1368.1	1369.7	1371.4
142.5°	1427.8	1426.5	1425.2	1423.9	1422.5	1421.1	1419.7	1418.3	1419.7	1421.1	1422.5
145°	1503.1	1502.1	1501.1	1500.0	1498.6	1497.3	1495.9	1494.6	1495.9	1497.3	1498.6
147.5°	1570.5	1569.7	1568.9	1568.1	1567.4	1566.6	1565.9	1565.2	1565.9	1566.6	1567.4
150°	1614.1	1612.7	1611.4	1610.9	1611.2	1611.6	1611.9	1612.2	1611.9	1611.6	1611.2
152.5°	1654.3	1653.8	1653.2	1652.7	1652.2	1651.8	1651.3	1650.8	1651.3	1651.8	1652.2
155°	1711.1	1710.8	1710.4	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3
157.5°	1760.9	1760.5	1760.2	1760.4	1761.1	1761.9	1762.6	1763.3	1762.6	1761.9	1761.1
160°	1791.0	1790.7	1790.4	1790.7	1791.7	1792.7	1793.7	1794.7	1793.7	1792.7	1791.7
162.5°	1819.3	1819.2	1819.2	1819.5	1820.3	1821.0	1821.7	1822.5	1821.7	1821.0	1820.3
165°	1857.4	1857.1	1856.7	1856.9	1857.6	1858.2	1858.9	1859.6	1858.9	1858.2	1857.6
167.5°	1884.9	1884.9	1884.9	1885.6	1886.9	1888.3	1889.6	1890.9	1889.6	1888.3	1886.9
170°	1901.8	1901.8	1901.8	1902.5	1903.8	1905.1	1906.5	1907.8	1906.5	1905.1	1903.8
172.5°	1913.9	1913.9	1913.9	1914.5	1915.9	1917.2	1918.6	1919.9	1918.6	1917.2	1915.9
175°	1927.4	1927.4	1927.4	1928.1	1929.4	1930.8	1932.1	1933.5	1932.1	1930.8	1929.4
177.5°	1934.9	1935.2	1935.4	1936.1	1937.2	1938.3	1939.3	1940.4	1939.3	1938.3	1937.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1562.6	1556.7	1551.8	1541.0	1535.1	1527.0	1520.5	1527.5	1520.0	1523.2	1518.4
5°	1513.9	1495.0	1481.5	1461.9	1445.1	1429.5	1418.1	1416.0	1410.6	1407.9	1399.8
7.5°	1455.3	1431.7	1408.5	1382.8	1361.2	1339.2	1325.2	1313.6	1305.9	1295.8	1288.9
10°	1420.8	1389.0	1362.1	1331.0	1304.0	1280.4	1261.5	1252.0	1243.3	1230.4	1225.7
12.5°	1378.1	1345.3	1312.4	1279.2	1253.2	1226.9	1210.7	1196.4	1190.3	1175.9	1174.4
15°	1327.0	1277.7	1245.3	1211.5	1175.8	1154.2	1140.7	1125.1	1118.4	1108.3	1100.8
17.5°	1265.9	1221.9	1181.4	1146.5	1115.8	1097.6	1080.9	1070.2	1058.6	1052.0	1039.8
20°	1221.7	1179.8	1139.3	1102.2	1078.6	1057.6	1044.1	1034.0	1021.9	1018.5	1006.4
22.5°	1184.4	1138.2	1099.4	1068.2	1042.4	1018.8	1004.2	997.3	988.9	978.5	976.1
25°	1123.8	1075.9	1042.8	1011.8	988.8	967.2	957.1	948.3	940.2	932.8	930.1
27.5°	1071.4	1028.6	989.3	961.3	941.3	921.6	912.7	902.0	896.1	890.1	882.8
30°	1034.7	990.8	956.4	929.4	907.8	890.3	880.8	873.4	868.0	862.6	858.5
32.5°	996.9	956.3	922.9	896.5	874.9	861.6	853.3	848.0	842.1	835.6	830.5
35°	947.0	902.4	870.0	847.1	830.2	820.1	810.6	805.9	799.1	799.1	793.7
37.5°	890.7	852.2	823.6	802.7	787.5	778.5	768.2	765.0	760.7	757.8	755.9
40°	857.2	821.4	794.4	773.5	757.3	749.9	741.8	736.4	733.7	730.3	728.9
42.5°	822.6	788.5	762.6	743.3	729.2	722.9	715.3	711.5	706.1	701.7	700.9
45°	770.1	737.0	713.4	697.9	685.7	678.3	673.6	665.5	662.8	657.4	656.7
47.5°	720.3	688.6	665.4	652.7	642.0	635.9	628.5	620.4	617.3	614.6	614.3
50°	683.1	654.0	632.4	620.3	610.2	601.4	594.0	588.6	586.5	586.5	587.9
52.5°	645.3	620.5	602.2	587.3	577.8	568.4	561.6	558.3	555.2	558.5	560.9
55°	589.9	564.9	551.4	537.3	527.8	517.0	513.6	512.3	510.3	515.7	518.4
57.5°	531.3	513.8	498.0	483.9	475.4	469.2	464.6	463.8	467.6	470.2	478.9
60°	494.1	473.8	459.6	448.8	438.7	434.7	433.3	432.0	434.7	442.1	453.6
62.5°	453.0	436.6	421.3	413.2	405.8	399.0	398.8	399.6	405.0	413.5	424.9
65°	392.8	378.6	368.5	359.1	353.0	348.9	350.3	353.0	359.1	370.5	383.4
67.5°	331.7	322.0	312.9	305.2	299.4	299.4	300.8	304.8	312.0	325.2	336.9
70°	292.3	281.5	274.0	270.7	265.9	263.2	267.3	274.0	280.1	292.3	302.4
72.5°	252.8	243.7	237.9	235.6	233.5	231.4	232.7	240.0	248.2	260.4	272.1
75°	194.4	191.0	187.0	184.3	182.2	183.6	184.9	191.7	198.4	211.3	224.8
77.5°	141.9	138.4	135.9	135.3	134.2	134.9	138.6	143.6	150.2	159.6	169.8
80°	107.3	106.0	104.6	103.9	103.9	104.6	110.0	113.4	119.5	128.2	136.3
82.5°	78.2	77.3	77.1	76.9	77.5	77.6	80.9	85.3	90.3	96.9	103.9
85°	41.2	39.8	41.8	42.5	41.2	43.2	44.5	47.2	49.3	52.6	56.0
87.5°	15.9	17.5	17.5	18.5	18.9	20.5	20.3	22.8	24.2	25.6	25.3
90°	12.2	14.7	17.1	19.4	21.8	24.1	25.8	27.5	29.2	30.8	32.2
92.5°	44.0	46.4	49.3	52.1	55.0	57.9	60.1	62.3	64.5	66.8	68.2
95°	100.7	102.7	106.1	109.4	112.8	116.1	118.5	120.8	123.2	125.5	127.0
97.5°	164.0	166.4	171.0	175.7	180.3	184.9	187.1	189.3	191.5	193.7	195.1
100°	211.1	213.3	217.7	222.0	226.4	230.7	233.8	236.8	239.8	242.8	244.7
102.5°	268.4	270.2	272.4	274.6	276.8	279.0	282.3	285.6	288.9	292.1	294.3
105°	350.6	352.4	354.4	356.4	358.4	360.5	362.5	364.5	366.5	368.5	370.0
107.5°	439.8	441.5	443.0	444.5	446.1	447.6	448.6	449.6	450.6	451.6	452.1
110°	501.4	502.7	503.7	504.7	505.7	506.7	507.7	508.8	509.8	510.8	511.1



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	560.9	562.0	563.2	564.5	565.8	567.1	567.5	568.0	568.5	568.9	568.9
115°	655.4	656.4	657.1	657.7	658.4	659.1	658.7	658.4	658.1	657.7	657.4
117.5°	745.3	745.9	746.5	747.1	747.7	748.4	748.6	748.9	749.2	749.4	748.9
120°	807.5	808.5	808.9	809.2	809.5	809.9	809.9	809.9	809.9	809.9	809.2
122.5°	866.0	866.7	867.6	868.5	869.3	870.2	869.9	869.7	869.4	869.1	868.5
125°	956.7	957.9	958.2	958.5	958.9	959.2	958.5	957.9	957.2	956.5	956.0
127.5°	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7	1045.4	1045.1	1044.7	1044.2
130°	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6	1103.3	1103.0	1102.6	1102.1
132.5°	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1	1158.8	1158.5	1158.1	1157.5
135°	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2	1244.2	1244.2	1244.2	1243.6
137.5°	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0	1327.4	1327.8	1328.2	1327.6
140°	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1	1379.8	1380.5	1381.1	1380.6
142.5°	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7	1431.1	1431.5	1432.0	1431.3
145°	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1	1505.1	1505.1	1505.1	1504.6
147.5°	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9	1573.7	1574.5	1575.3	1574.6
150°	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8	1616.8	1616.8	1616.8	1616.4
152.5°	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2	1657.0	1657.8	1658.6	1658.4
155°	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1	1714.4	1715.8	1717.1	1717.0
157.5°	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9	1764.2	1765.6	1766.9	1766.5
160°	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0	1794.4	1795.7	1797.1	1796.9
162.5°	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1	1822.7	1824.3	1825.9	1825.7
165°	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4	1860.7	1862.1	1863.4	1863.1
167.5°	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9	1888.9	1890.9	1892.9	1892.9
170°	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8	1905.8	1907.8	1909.8	1909.7
172.5°	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9	1917.9	1919.9	1921.9	1921.9
175°	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4	1931.5	1933.5	1935.5	1935.3
177.5°	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0	1937.6	1939.2	1940.8	1940.7
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1515.1	1518.9	1515.7	1520.0	1515.7	1518.9	1515.1	1518.4	1523.2	1520.0	1527.5
5°	1396.5	1390.4	1394.4	1391.7	1394.4	1390.4	1396.5	1399.8	1407.9	1410.6	1416.0
7.5°	1286.9	1281.1	1274.4	1271.3	1274.4	1281.1	1286.9	1288.9	1295.8	1305.9	1313.6
10°	1218.3	1210.9	1210.2	1205.5	1210.2	1210.9	1218.3	1225.7	1230.4	1243.3	1252.0
12.5°	1168.1	1161.2	1153.5	1151.5	1153.5	1161.2	1168.1	1174.4	1175.9	1190.3	1196.4
15°	1096.8	1091.4	1086.7	1090.7	1086.7	1091.4	1096.8	1100.8	1108.3	1118.4	1125.1
17.5°	1037.5	1033.1	1032.3	1027.3	1032.3	1033.1	1037.5	1039.8	1052.0	1058.6	1070.2
20°	1000.3	996.9	998.3	989.5	998.3	996.9	1000.3	1006.4	1018.5	1021.9	1034.0
22.5°	970.6	964.0	963.2	961.4	963.2	964.0	970.6	976.1	978.5	988.9	997.3
25°	924.0	920.6	917.3	920.6	917.3	920.6	924.0	930.1	932.8	940.2	948.3
27.5°	883.4	879.3	878.4	878.8	878.4	879.3	883.4	882.8	890.1	896.1	902.0
30°	858.5	851.8	852.5	851.8	852.5	851.8	858.5	858.5	862.6	868.0	873.4
32.5°	831.5	826.9	826.0	824.8	826.0	826.9	831.5	830.5	835.6	842.1	848.0
35°	791.7	791.7	788.3	788.3	788.3	791.7	791.7	793.7	799.1	799.1	805.9
37.5°	754.3	753.6	751.6	751.9	751.6	753.6	754.3	755.9	757.8	760.7	765.0
40°	726.2	725.6	723.5	719.5	723.5	725.6	726.2	728.9	730.3	733.7	736.4
42.5°	699.2	697.0	696.0	694.7	696.0	697.0	699.2	700.9	701.7	706.1	711.5
45°	656.7	656.7	655.4	654.7	655.4	656.7	656.7	656.7	657.4	662.8	665.5
47.5°	615.4	616.6	619.2	618.8	619.2	616.6	615.4	614.3	614.6	617.3	620.4
50°	590.6	591.3	593.3	594.0	593.3	591.3	590.6	587.9	586.5	586.5	588.6
52.5°	563.0	567.0	569.5	569.1	569.5	567.0	563.0	560.9	558.5	555.2	558.3
55°	524.4	529.2	533.9	534.6	533.9	529.2	524.4	518.4	515.7	510.3	512.3
57.5°	486.2	492.8	497.8	499.5	497.8	492.8	486.2	478.9	470.2	467.6	463.8
60°	460.3	469.1	475.2	477.9	475.2	469.1	460.3	453.6	442.1	434.7	432.0
62.5°	435.5	445.3	451.4	451.9	451.4	445.3	435.5	424.9	413.5	405.0	399.6
65°	394.8	405.0	410.4	414.4	410.4	405.0	394.8	383.4	370.5	359.1	353.0
67.5°	351.1	361.2	367.2	370.4	367.2	361.2	351.1	336.9	325.2	312.0	304.8
70°	319.3	329.4	337.5	340.2	337.5	329.4	319.3	302.4	292.3	280.1	274.0
72.5°	287.9	297.0	303.5	306.7	303.5	297.0	287.9	272.1	260.4	248.2	240.0
75°	233.5	245.7	251.8	255.1	251.8	245.7	233.5	224.8	211.3	198.4	191.7
77.5°	180.1	191.1	194.8	196.5	194.8	191.1	180.1	169.8	159.6	150.2	143.6
80°	144.4	151.2	155.9	156.6	155.9	151.2	144.4	136.3	128.2	119.5	113.4
82.5°	111.0	116.6	118.1	119.9	118.1	116.6	111.0	103.9	96.9	90.3	85.3
85°	60.7	63.4	64.1	63.4	64.1	63.4	60.7	56.0	52.6	49.3	47.2
87.5°	26.6	26.3	26.5	27.8	26.5	26.3	26.6	25.3	25.6	24.2	22.8
90°	33.2	34.2	35.2	36.2	35.2	34.2	33.2	32.2	30.8	29.2	27.5
92.5°	69.0	69.7	70.4	71.2	70.4	69.7	69.0	68.2	66.8	64.5	62.3
95°	127.7	128.4	129.0	129.7	129.0	128.4	127.7	127.0	125.5	123.2	120.8
97.5°	195.5	195.9	196.3	196.7	196.3	195.9	195.5	195.1	193.7	191.5	189.3
100°	245.3	246.0	246.7	247.3	246.7	246.0	245.3	244.7	242.8	239.8	236.8
102.5°	295.2	296.1	297.1	298.0	297.1	296.1	295.2	294.3	292.1	288.9	285.6
105°	371.0	372.0	373.0	374.0	373.0	372.0	371.0	370.0	368.5	366.5	364.5
107.5°	452.0	452.0	451.9	451.8	451.9	452.0	452.0	452.1	451.6	450.6	449.6
110°	510.8	510.4	510.1	509.8	510.1	510.4	510.8	511.1	510.8	509.8	508.8



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	568.3	567.7	567.1	566.5	567.1	567.7	568.3	568.9	568.9	568.5	568.0
115°	657.1	656.7	656.4	656.1	656.4	656.7	657.1	657.4	657.7	658.1	658.4
117.5°	747.5	746.2	744.9	743.5	744.9	746.2	747.5	748.9	749.4	749.2	748.9
120°	807.9	806.5	805.2	803.9	805.2	806.5	807.9	809.2	809.9	809.9	809.9
122.5°	867.4	866.3	865.2	864.2	865.2	866.3	867.4	868.5	869.1	869.4	869.7
125°	955.7	955.3	955.0	954.7	955.0	955.3	955.7	956.0	956.5	957.2	957.9
127.5°	1043.5	1042.9	1042.2	1041.5	1042.2	1042.9	1043.5	1044.2	1044.7	1045.1	1045.4
130°	1101.5	1100.8	1100.1	1099.5	1100.1	1100.8	1101.5	1102.1	1102.6	1103.0	1103.3
132.5°	1156.6	1155.6	1154.7	1153.7	1154.7	1155.6	1156.6	1157.5	1158.1	1158.5	1158.8
135°	1242.2	1240.9	1239.5	1238.2	1239.5	1240.9	1242.2	1243.6	1244.2	1244.2	1244.2
137.5°	1325.9	1324.2	1322.5	1320.8	1322.5	1324.2	1325.9	1327.6	1328.2	1327.8	1327.4
140°	1379.0	1377.3	1375.6	1373.9	1375.6	1377.3	1379.0	1380.6	1381.1	1380.5	1379.8
142.5°	1429.6	1428.0	1426.3	1424.6	1426.3	1428.0	1429.6	1431.3	1432.0	1431.5	1431.1
145°	1503.6	1502.6	1501.6	1500.6	1501.6	1502.6	1503.6	1504.6	1505.1	1505.1	1505.1
147.5°	1572.3	1570.0	1567.8	1565.5	1567.8	1570.0	1572.3	1574.6	1575.3	1574.5	1573.7
150°	1615.7	1615.1	1614.4	1613.7	1614.4	1615.1	1615.7	1616.4	1616.8	1616.8	1616.8
152.5°	1657.2	1656.0	1654.8	1653.6	1654.8	1656.0	1657.2	1658.4	1658.6	1657.8	1657.0
155°	1715.3	1713.6	1711.9	1710.3	1711.9	1713.6	1715.3	1717.0	1717.1	1715.8	1714.4
157.5°	1764.2	1762.0	1759.8	1757.6	1759.8	1762.0	1764.2	1766.5	1766.9	1765.6	1764.2
160°	1795.2	1793.5	1791.9	1790.2	1791.9	1793.5	1795.2	1796.9	1797.1	1795.7	1794.4
162.5°	1823.8	1821.8	1819.9	1817.9	1819.9	1821.8	1823.8	1825.7	1825.9	1824.3	1822.7
165°	1861.1	1859.1	1857.1	1855.0	1857.1	1859.1	1861.1	1863.1	1863.4	1862.1	1860.7
167.5°	1890.8	1888.8	1886.7	1884.6	1886.7	1888.8	1890.8	1892.9	1892.9	1890.9	1888.9
170°	1907.3	1905.0	1902.6	1900.3	1902.6	1905.0	1907.3	1909.7	1909.8	1907.8	1905.8
172.5°	1919.8	1917.7	1915.6	1913.6	1915.6	1917.7	1919.8	1921.9	1921.9	1919.9	1917.9
175°	1933.0	1930.6	1928.3	1925.9	1928.3	1930.6	1933.0	1935.3	1935.5	1933.5	1931.5
177.5°	1938.8	1936.9	1935.0	1933.2	1935.0	1936.9	1938.8	1940.7	1940.8	1939.2	1937.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1520.5	1527.0	1535.1	1541.0	1551.8	1556.7	1562.6	1567.5	1576.1	1584.2	1594.0
5°	1418.1	1429.5	1445.1	1461.9	1481.5	1495.0	1513.9	1525.4	1548.3	1569.3	1589.5
7.5°	1325.2	1339.2	1361.2	1382.8	1408.5	1431.7	1455.3	1481.5	1510.8	1545.4	1574.0
10°	1261.5	1280.4	1304.0	1331.0	1362.1	1389.0	1420.8	1449.1	1484.9	1525.4	1563.2
12.5°	1210.7	1226.9	1253.2	1279.2	1312.4	1345.3	1378.1	1415.6	1457.4	1502.2	1549.7
15°	1140.7	1154.2	1175.8	1211.5	1245.3	1277.7	1327.0	1362.1	1414.7	1464.6	1522.0
17.5°	1080.9	1097.6	1115.8	1146.5	1181.4	1221.9	1265.9	1309.9	1360.7	1424.0	1488.7
20°	1044.1	1057.6	1078.6	1102.2	1139.3	1179.8	1221.7	1266.2	1328.3	1393.8	1463.3
22.5°	1004.2	1018.8	1042.4	1068.2	1099.4	1138.2	1184.4	1233.3	1298.1	1362.5	1437.9
25°	957.1	967.2	988.8	1011.8	1042.8	1075.9	1123.8	1177.8	1241.9	1315.5	1392.4
27.5°	912.7	921.6	941.3	961.3	989.3	1028.6	1071.4	1126.0	1186.4	1260.9	1346.3
30°	880.8	890.3	907.8	929.4	956.4	990.8	1034.7	1086.0	1150.8	1223.7	1312.8
32.5°	853.3	861.6	874.9	896.5	922.9	956.3	996.9	1049.3	1114.1	1188.0	1275.5
35°	810.6	820.1	830.2	847.1	870.0	902.4	947.0	996.2	1058.3	1129.9	1210.2
37.5°	768.2	778.5	787.5	802.7	823.6	852.2	890.7	942.0	998.1	1067.1	1144.2
40°	741.8	749.9	757.3	773.5	794.4	821.4	857.2	903.1	962.5	1026.6	1090.7
42.5°	715.3	722.9	729.2	743.3	762.6	788.5	822.6	867.4	922.5	982.3	1038.9
45°	673.6	678.3	685.7	697.9	713.4	737.0	770.1	809.9	856.5	913.2	955.7
47.5°	628.5	635.9	642.0	652.7	665.4	688.6	720.3	754.2	796.4	838.6	868.5
50°	594.0	601.4	610.2	620.3	632.4	654.0	683.1	717.5	753.2	785.6	811.3
52.5°	561.6	568.4	577.8	587.3	602.2	620.5	645.3	675.9	711.1	734.3	755.7
55°	513.6	517.0	527.8	537.3	551.4	564.9	589.9	616.9	638.5	656.1	673.6
57.5°	464.6	469.2	475.4	483.9	498.0	513.8	531.3	555.2	567.9	576.9	590.6
60°	433.3	434.7	438.7	448.8	459.6	473.8	494.1	510.9	520.4	527.8	539.3
62.5°	398.8	399.0	405.8	413.2	421.3	436.6	453.0	466.7	474.5	478.1	489.1
65°	350.3	348.9	353.0	359.1	368.5	378.6	392.8	405.0	404.3	408.3	415.1
67.5°	300.8	299.4	299.4	305.2	312.9	322.0	331.7	338.7	338.8	344.2	347.6
70°	267.3	263.2	265.9	270.7	274.0	281.5	292.3	295.0	295.6	298.3	301.7
72.5°	232.7	231.4	233.5	235.6	237.9	243.7	252.8	254.5	254.6	256.2	261.7
75°	184.9	183.6	182.2	184.3	187.0	191.0	194.4	197.1	196.4	197.1	201.1
77.5°	138.6	134.9	134.2	135.3	135.9	138.4	141.9	141.6	142.3	142.1	146.7
80°	110.0	104.6	103.9	103.9	104.6	106.0	107.3	108.7	106.6	108.7	110.0
82.5°	80.9	77.6	77.5	76.9	77.1	77.3	78.2	79.0	78.6	79.5	80.3
85°	44.5	43.2	41.2	42.5	41.8	39.8	41.2	39.1	38.5	39.1	39.8
87.5°	20.3	20.5	18.9	18.5	17.5	17.5	15.9	14.9	13.8	13.8	14.9
90°	25.8	24.1	21.8	19.4	17.1	14.7	12.2	9.6	6.9	4.2	1.5
92.5°	60.1	57.9	55.0	52.1	49.3	46.4	44.0	42.1	40.3	38.4	36.5
95°	118.5	116.1	112.8	109.4	106.1	102.7	100.7	100.0	99.4	98.7	98.0
97.5°	187.1	184.9	180.3	175.7	171.0	166.4	164.0	163.7	163.4	163.1	162.9
100°	233.8	230.7	226.4	222.0	217.7	213.3	211.1	211.1	211.1	211.1	211.1
102.5°	282.3	279.0	276.8	274.6	272.4	270.2	268.4	267.0	265.7	264.4	263.0
105°	362.5	360.5	358.4	356.4	354.4	352.4	350.6	348.9	347.2	345.5	343.9
107.5°	448.6	447.6	446.1	444.5	443.0	441.5	439.8	438.2	436.5	434.8	433.1
110°	507.7	506.7	505.7	504.7	503.7	502.7	501.4	499.7	498.0	496.4	494.7



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	567.5	567.1	565.8	564.5	563.2	562.0	560.9	560.0	559.2	558.3	557.4
115°	658.7	659.1	658.4	657.7	657.1	656.4	655.4	654.0	652.7	651.4	650.0
117.5°	748.6	748.4	747.7	747.1	746.5	745.9	745.3	744.7	744.1	743.5	742.9
120°	809.9	809.9	809.5	809.2	808.9	808.5	807.5	805.9	804.2	802.5	800.8
122.5°	869.9	870.2	869.3	868.5	867.6	866.7	866.0	865.4	864.8	864.2	863.6
125°	958.5	959.2	958.9	958.5	958.2	957.9	956.7	954.7	952.7	950.6	948.6
127.5°	1045.7	1046.1	1045.7	1045.3	1044.9	1044.5	1043.7	1042.5	1041.4	1040.3	1039.1
130°	1103.6	1104.0	1103.3	1102.6	1102.0	1101.3	1100.1	1098.4	1096.8	1095.1	1093.4
132.5°	1159.1	1159.5	1159.6	1159.7	1159.9	1160.0	1158.7	1156.0	1153.2	1150.5	1147.7
135°	1244.2	1244.2	1243.9	1243.6	1243.2	1242.9	1241.7	1239.7	1237.7	1235.7	1233.7
137.5°	1327.0	1326.6	1325.8	1325.1	1324.4	1323.6	1322.3	1320.3	1318.4	1316.5	1314.5
140°	1379.1	1378.5	1377.5	1376.5	1375.4	1374.4	1373.1	1371.4	1369.7	1368.1	1366.4
142.5°	1430.7	1430.3	1429.1	1427.8	1426.5	1425.2	1423.9	1422.5	1421.1	1419.7	1418.3
145°	1505.1	1505.1	1504.1	1503.1	1502.1	1501.1	1500.0	1498.6	1497.3	1495.9	1494.6
147.5°	1572.9	1572.1	1571.3	1570.5	1569.7	1568.9	1568.1	1567.4	1566.6	1565.9	1565.2
150°	1616.8	1616.8	1615.4	1614.1	1612.7	1611.4	1610.9	1611.2	1611.6	1611.9	1612.2
152.5°	1656.2	1655.4	1654.8	1654.3	1653.8	1653.2	1652.7	1652.2	1651.8	1651.3	1650.8
155°	1713.1	1711.8	1711.4	1711.1	1710.8	1710.4	1710.3	1710.3	1710.3	1710.3	1710.3
157.5°	1762.9	1761.5	1761.2	1760.9	1760.5	1760.2	1760.4	1761.1	1761.9	1762.6	1763.3
160°	1793.0	1791.7	1791.4	1791.0	1790.7	1790.4	1790.7	1791.7	1792.7	1793.7	1794.7
162.5°	1821.1	1819.4	1819.4	1819.3	1819.2	1819.2	1819.5	1820.3	1821.0	1821.7	1822.5
165°	1859.4	1858.1	1857.7	1857.4	1857.1	1856.7	1856.9	1857.6	1858.2	1858.9	1859.6
167.5°	1886.9	1884.9	1884.9	1884.9	1884.9	1884.9	1885.6	1886.9	1888.3	1889.6	1890.9
170°	1903.8	1901.8	1901.8	1901.8	1901.8	1901.8	1902.5	1903.8	1905.1	1906.5	1907.8
172.5°	1915.9	1913.9	1913.9	1913.9	1913.9	1913.9	1914.5	1915.9	1917.2	1918.6	1919.9
175°	1929.4	1927.4	1927.4	1927.4	1927.4	1927.4	1928.1	1929.4	1930.8	1932.1	1933.5
177.5°	1936.0	1934.4	1934.6	1934.9	1935.2	1935.4	1936.1	1937.2	1938.3	1939.3	1940.4
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1598.8	1606.4	1611.2	1620.4	1628.0	1632.3	1636.1	1639.3	1643.1	1646.3	1655.5
5°	1609.1	1626.6	1641.5	1664.4	1685.4	1701.6	1719.1	1734.6	1747.4	1765.7	1779.8
7.5°	1604.6	1635.8	1668.5	1704.0	1740.3	1774.0	1805.1	1834.1	1860.4	1892.3	1920.2
10°	1600.3	1642.8	1684.7	1732.6	1781.9	1823.7	1862.9	1902.7	1931.7	1972.2	2006.6
12.5°	1597.1	1647.1	1697.6	1755.3	1809.4	1868.5	1920.6	1949.7	1993.8	2026.2	2067.1
15°	1583.4	1649.6	1719.1	1783.9	1860.8	1915.5	1961.4	2018.1	2059.3	2100.4	2145.0
17.5°	1559.0	1633.9	1711.7	1796.6	1870.4	1929.1	1988.3	2042.9	2092.1	2147.3	2202.8
20°	1547.7	1622.6	1711.7	1798.7	1871.0	1932.4	1993.1	2053.2	2107.2	2178.1	2242.2
22.5°	1523.9	1614.5	1696.6	1781.5	1855.8	1922.7	1991.5	2059.7	2131.5	2211.5	2291.9
25°	1481.5	1573.3	1660.4	1744.1	1819.0	1902.7	1976.3	2067.4	2159.2	2265.1	2365.0
27.5°	1437.5	1525.4	1605.2	1686.0	1773.4	1868.1	1963.6	2067.0	2187.1	2320.9	2461.8
30°	1401.9	1484.9	1562.5	1645.5	1736.6	1843.3	1947.9	2070.7	2209.8	2360.3	2527.7
32.5°	1360.3	1436.8	1512.3	1600.2	1699.4	1812.0	1933.9	2068.6	2235.7	2406.7	2579.0
35°	1289.2	1353.3	1430.9	1524.7	1636.8	1765.7	1906.7	2066.0	2257.7	2454.1	2599.2
37.5°	1204.8	1264.5	1346.3	1449.1	1566.6	1704.9	1872.3	2061.3	2264.9	2421.5	2468.3
40°	1148.1	1203.4	1288.5	1395.1	1515.3	1661.7	1845.3	2045.1	2242.2	2342.1	2303.6
42.5°	1087.6	1145.7	1228.5	1334.1	1463.4	1622.9	1811.3	2011.1	2176.3	2214.1	2081.1
45°	992.2	1052.2	1133.9	1240.6	1379.6	1552.4	1748.8	1930.4	2025.5	1957.4	1751.5
47.5°	903.5	959.8	1035.5	1145.5	1289.0	1467.7	1656.9	1801.7	1809.3	1646.6	1426.7
50°	843.0	895.0	971.3	1081.3	1223.7	1404.6	1575.3	1689.4	1638.1	1453.8	1242.6
52.5°	783.6	834.5	909.7	1018.6	1159.4	1325.2	1484.1	1564.1	1467.5	1278.4	1097.9
55°	697.9	742.4	816.0	916.6	1050.2	1204.1	1339.1	1366.8	1241.2	1054.9	908.5
57.5°	614.2	655.8	722.7	815.3	937.5	1073.8	1179.4	1173.5	1040.8	880.9	764.7
60°	557.5	598.0	657.4	747.8	859.2	976.7	1067.1	1045.5	913.9	776.2	678.3
62.5°	506.8	542.9	599.1	678.2	779.8	888.6	962.9	931.0	802.1	681.7	604.4
65°	432.0	462.3	510.3	577.8	662.1	751.9	809.3	768.1	658.1	564.3	502.2
67.5°	360.6	384.9	425.1	478.9	550.9	623.0	657.9	616.5	528.5	460.0	414.0
70°	315.2	336.8	367.8	415.8	478.5	539.3	565.6	528.5	452.9	394.2	361.1
72.5°	269.8	287.7	314.9	358.0	408.3	461.0	484.1	448.6	386.5	336.9	306.0
75°	208.6	220.7	239.6	269.3	309.1	351.0	363.8	332.8	292.9	255.8	235.6
77.5°	149.3	159.6	173.9	192.6	220.8	247.4	258.6	240.7	209.9	186.4	169.8
80°	114.7	120.1	132.3	147.8	170.1	187.0	194.4	182.9	161.3	143.8	130.9
82.5°	81.8	87.2	94.5	107.3	121.5	133.0	140.9	133.2	117.6	103.8	96.4
85°	39.8	43.2	47.2	52.6	63.4	70.2	69.5	64.8	58.7	53.3	49.3
87.5°	14.9	16.0	18.1	21.3	23.5	26.1	27.6	27.0	25.3	24.1	22.8
90°	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8	27.5
92.5°	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1	62.3
95°	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5	120.8
97.5°	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1	189.3
100°	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8	236.8
102.5°	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3	285.6
105°	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5	364.5
107.5°	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6	449.6
110°	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7	508.8



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5	568.0
115°	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7	658.4
117.5°	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6	748.9
120°	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9	809.9
122.5°	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9	869.7
125°	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5	957.9
127.5°	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7	1045.4
130°	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6	1103.3
132.5°	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1	1158.8
135°	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2	1244.2
137.5°	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0	1327.4
140°	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1	1379.8
142.5°	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7	1431.1
145°	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1	1505.1
147.5°	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9	1573.7
150°	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8	1616.8
152.5°	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2	1657.0
155°	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1	1714.4
157.5°	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9	1764.2
160°	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0	1794.4
162.5°	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1	1822.7
165°	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4	1860.7
167.5°	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9	1888.9
170°	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8	1905.8
172.5°	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9	1917.9
175°	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4	1931.5
177.5°	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0	1937.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1663.1	1667.4	1676.6	1673.3	1677.7	1679.8	1682.0
5°	1797.4	1819.0	1828.4	1827.1	1841.3	1837.9	1834.5
7.5°	1949.1	1971.8	1984.5	2000.3	2009.5	2010.1	2018.1
10°	2035.0	2064.7	2076.8	2093.7	2104.5	2110.6	2109.9
12.5°	2100.9	2124.1	2151.3	2159.6	2174.2	2181.8	2179.0
15°	2180.1	2217.2	2245.6	2259.7	2278.0	2283.4	2290.8
17.5°	2250.8	2300.6	2333.7	2377.7	2394.3	2404.4	2398.5
20°	2304.3	2369.8	2402.8	2455.5	2484.5	2500.0	2494.6
22.5°	2367.5	2438.3	2499.5	2545.1	2589.2	2610.2	2614.5
25°	2475.7	2572.9	2662.7	2722.8	2777.4	2790.2	2818.6
27.5°	2596.7	2711.3	2807.3	2870.4	2908.5	2922.8	2931.7
30°	2672.8	2786.9	2859.1	2899.6	2911.7	2910.4	2909.0
32.5°	2710.1	2781.5	2795.4	2784.0	2756.2	2732.7	2708.2
35°	2657.3	2604.0	2524.3	2421.7	2346.1	2269.9	2262.4
37.5°	2389.9	2219.4	2086.8	1938.7	1853.3	1800.5	1764.1
40°	2138.2	1944.5	1783.9	1659.0	1572.0	1537.5	1503.8
42.5°	1865.0	1680.0	1537.7	1433.3	1367.9	1329.7	1302.9
45°	1515.3	1351.9	1240.6	1165.0	1113.0	1083.3	1066.4
47.5°	1241.6	1120.8	1026.2	971.7	935.8	912.7	912.8
50°	1094.8	979.4	916.6	873.4	842.3	824.1	827.5
52.5°	964.6	878.4	824.8	788.6	765.7	754.5	754.1
55°	806.6	744.5	709.4	683.1	667.5	654.7	657.4
57.5°	689.9	637.6	614.1	592.2	581.4	576.3	568.8
60°	617.6	577.1	556.8	539.3	528.5	524.4	517.0
62.5°	553.3	521.5	501.8	487.4	477.7	476.4	470.6
65°	465.0	440.7	423.2	416.4	406.3	403.6	403.6
67.5°	383.4	366.0	352.3	346.1	341.7	342.3	339.1
70°	332.1	317.9	309.1	302.4	299.0	299.7	297.0
72.5°	290.5	274.7	267.0	263.0	258.5	260.3	259.2
75°	220.0	211.9	207.9	203.8	201.1	199.8	198.4
77.5°	161.6	154.4	151.3	149.0	149.4	146.2	148.8
80°	124.9	118.8	116.8	113.4	112.7	112.7	112.0
82.5°	91.4	88.0	86.5	83.7	82.5	83.6	81.8
85°	47.2	44.5	43.9	43.9	42.5	41.2	44.5
87.5°	23.1	21.3	21.6	21.2	21.4	21.1	20.2
90°	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	509.8	510.8	511.1	510.8	510.4	510.1	509.8



TEST NUMBER: P333455

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)