

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333459

Luminaire Tested: **S125DIW-S1090D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333459  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1560U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9852.3 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45								
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38								
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32								
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27								
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23								
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20								
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17								
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16								
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14								
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13								
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.9	1.6
10°-20°	454.5	4.6
20°-30°	671.0	6.8
30°-40°	783.0	7.9
40°-50°	786.4	8.0
50°-60°	690.3	7.0
60°-70°	514.4	5.2
70°-80°	294.1	3.0
80°-90°	89.8	0.9
90°-100°	129.8	1.3
100°-110°	383.3	3.9
110°-120°	649.2	6.6
120°-130°	854.4	8.7
130°-140°	957.4	9.7
140°-150°	938.3	9.5
150°-160°	788.1	8.0
160°-170°	523.9	5.3
170°-180°	183.3	1.9
0°-30°	1286.4	13.1
0°-40°	2069.4	21.0
0°-60°	3546.2	36.0
0°-90°	4444.5	45.1
90°-120°	1162.3	11.8
90°-150°	3912.5	39.7
90°-180°	5408.0	54.9
0°-180°	9852.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	2	13	24	32	36	9
95°	98	102	116	126	130	105
105°	344	352	360	369	374	367
115°	650	656	659	658	656	643
125°	949	957	959	956	955	849
135°	1234	1242	1244	1244	1238	951
145°	1495	1501	1505	1505	1501	934
155°	1710	1710	1712	1717	1710	787
165°	1860	1857	1858	1863	1855	524
175°	1934	1928	1927	1935	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.5	30.0	30.5	31.1	31.6	32.0	32.2	32.4	32.7	32.9	33.2
90°	1.5	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8
92.5°	36.5	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1
95°	98.0	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5
97.5°	162.9	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1
100°	211.1	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8
102.5°	263.0	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3
105°	343.9	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5
107.5°	433.1	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6
110°	494.7	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7



TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	557.4	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5
115°	650.0	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7
117.5°	742.9	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6
120°	800.8	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9
122.5°	863.6	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9
125°	948.6	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5
127.5°	1039.1	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7
130°	1093.4	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6
132.5°	1147.7	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1
135°	1233.7	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2
137.5°	1314.5	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0
140°	1366.4	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1
142.5°	1418.3	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7
145°	1494.6	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1
147.5°	1565.2	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9
150°	1612.2	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8
152.5°	1650.8	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2
155°	1710.3	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1
157.5°	1763.3	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9
160°	1794.7	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0
162.5°	1822.5	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1
165°	1859.6	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4
167.5°	1890.9	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9
170°	1907.8	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8
172.5°	1919.9	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9
175°	1933.5	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4
177.5°	1940.4	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	33.6	33.9	34.2	34.3	34.0	33.7	33.4	33.2
90°	27.5	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	62.3	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	120.8	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	189.3	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	236.8	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	285.6	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	364.5	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	449.6	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	508.8	509.8	510.8	511.1	510.8	510.4	510.1	509.8





TEST NUMBER: P333459

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.0	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.4	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	748.9	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.7	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.9	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.4	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.3	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.8	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.4	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1379.8	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.1	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1573.7	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.0	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1714.4	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1764.2	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1794.4	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1822.7	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1860.7	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1888.9	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1905.8	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1917.9	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1931.5	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1937.6	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)