

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333383-840

Luminaire Tested: **S125DIW-S610D1050U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333383-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1050U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6222.4 lumens
Efficiency: N/A
Efficacy: 137.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35																				
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	31	30	25																				
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19																				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17																				
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	20	17	15																				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.4
10°-20°	259.1	4.2
20°-30°	420.7	6.8
30°-40°	513.1	8.2
40°-50°	466.8	7.5
50°-60°	371.8	6.0
60°-70°	259.0	4.2
70°-80°	138.1	2.2
80°-90°	37.7	0.6
90°-100°	88.1	1.4
100°-110°	260.1	4.2
110°-120°	440.5	7.1
120°-130°	579.7	9.3
130°-140°	649.6	10.4
140°-150°	636.6	10.2
150°-160°	534.7	8.6
160°-170°	355.4	5.7
170°-180°	124.4	2.0
0°-30°	766.7	12.3
0°-40°	1279.9	20.6
0°-60°	2118.5	34.0
0°-90°	2553.3	41.0
90°-120°	788.6	12.7
90°-150°	2654.6	42.7
90°-180°	3669.0	59.0
0°-180°	6222.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	24	1	24	1	24	15
95°	88	67	88	67	88	90
105°	254	233	254	233	254	269
115°	445	441	445	441	445	440
125°	648	644	648	644	648	578
135°	840	837	840	837	840	648
145°	1018	1014	1018	1014	1018	636
155°	1160	1160	1160	1160	1160	534
165°	1259	1262	1259	1262	1259	355
175°	1307	1312	1307	1312	1307	124
180°	1315	1315	1315	1315	1315	



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	12.3	12.7	12.9	12.8	12.9	12.8	13.7	13.5	14.2	14.9	15.9
90°	24.5	23.8	23.2	22.5	21.8	20.9	19.8	18.7	17.5	16.4	14.7
92.5°	48.3	47.8	47.3	46.8	46.3	45.3	43.8	42.3	40.8	39.3	37.4
95°	88.0	87.6	87.1	86.6	86.1	85.1	83.5	82.0	80.4	78.8	76.5
97.5°	133.4	133.2	132.9	132.6	132.3	131.5	130.0	128.5	126.9	125.4	122.3
100°	167.8	167.3	166.9	166.4	166.0	164.7	162.7	160.7	158.6	156.5	153.6
102.5°	202.2	201.6	201.0	200.3	199.7	198.2	196.0	193.8	191.6	189.3	187.8
105°	253.8	253.1	252.4	251.8	251.1	250.0	248.6	247.3	245.9	244.6	243.2
107.5°	306.6	306.6	306.7	306.7	306.8	306.4	305.8	305.1	304.4	303.7	302.7
110°	345.9	346.1	346.3	346.6	346.8	346.6	345.9	345.2	344.5	343.9	343.2



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.4	384.8	385.2	385.6	386.0	386.0	385.7	385.4	385.1	384.8	383.8
115°	445.1	445.4	445.6	445.8	446.1	446.3	446.5	446.7	447.0	447.2	446.7
117.5°	504.4	505.3	506.2	507.2	508.1	508.5	508.3	508.1	508.0	507.8	507.4
120°	545.4	546.3	547.2	548.2	549.1	549.5	549.5	549.5	549.5	549.5	549.3
122.5°	586.3	587.0	587.7	588.5	589.3	589.7	589.9	590.1	590.3	590.5	589.9
125°	647.7	647.9	648.1	648.4	648.6	648.9	649.4	649.8	650.4	650.8	650.6
127.5°	706.7	707.1	707.6	708.0	708.5	708.8	709.0	709.2	709.5	709.7	709.4
130°	746.0	746.4	746.9	747.3	747.8	748.1	748.3	748.6	748.8	749.0	748.6
132.5°	782.7	783.5	784.1	784.7	785.4	785.8	786.0	786.2	786.5	786.7	786.8
135°	840.1	841.0	841.9	842.8	843.7	844.1	844.1	844.1	844.1	844.1	843.9
137.5°	896.2	897.3	898.5	899.6	900.7	901.1	900.9	900.6	900.3	900.1	899.6
140°	932.2	933.3	934.4	935.6	936.8	937.1	936.6	936.1	935.7	935.2	934.5
142.5°	966.5	967.8	968.9	970.0	971.1	971.6	971.3	971.0	970.7	970.5	969.6
145°	1018.1	1018.9	1019.5	1020.2	1020.9	1021.2	1021.2	1021.2	1021.2	1021.2	1020.6
147.5°	1062.2	1063.7	1065.2	1066.8	1068.3	1068.8	1068.2	1067.7	1067.2	1066.6	1066.1
150°	1094.9	1095.3	1095.8	1096.2	1096.7	1096.9	1096.9	1096.9	1096.9	1096.9	1096.0
152.5°	1121.9	1122.7	1123.6	1124.4	1125.2	1125.3	1124.8	1124.2	1123.7	1123.2	1122.8
155°	1160.3	1161.5	1162.7	1163.8	1164.9	1165.1	1164.2	1163.3	1162.4	1161.4	1161.1
157.5°	1192.5	1194.0	1195.5	1197.0	1198.5	1198.8	1197.9	1197.0	1196.1	1195.2	1195.0
160°	1214.6	1215.8	1216.9	1218.0	1219.1	1219.3	1218.4	1217.5	1216.6	1215.7	1215.4
162.5°	1233.4	1234.8	1236.1	1237.4	1238.7	1238.8	1237.7	1236.7	1235.6	1234.5	1234.5
165°	1258.6	1260.0	1261.3	1262.7	1264.0	1264.3	1263.3	1262.4	1261.5	1260.6	1260.4
167.5°	1278.7	1280.1	1281.5	1282.9	1284.3	1284.3	1282.9	1281.6	1280.2	1278.9	1278.9
170°	1289.3	1290.9	1292.5	1294.0	1295.7	1295.8	1294.4	1293.0	1291.7	1290.3	1290.3
172.5°	1298.3	1299.7	1301.1	1302.5	1303.9	1303.9	1302.6	1301.2	1299.9	1298.5	1298.5
175°	1306.7	1308.3	1309.9	1311.5	1313.0	1313.2	1311.8	1310.4	1309.1	1307.7	1307.7
177.5°	1311.6	1312.9	1314.1	1315.5	1316.7	1316.8	1315.8	1314.6	1313.5	1312.4	1312.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	16.2	15.2	13.6	12.4	10.5	9.2	8.6	8.5	8.0	8.0	8.7
90°	13.2	11.6	10.0	8.3	6.5	4.6	2.8	1.0	2.8	4.6	6.5
92.5°	35.3	33.4	31.5	29.9	28.6	27.3	26.1	24.7	26.1	27.3	28.6
95°	74.2	72.0	69.7	68.4	67.9	67.5	67.0	66.6	67.0	67.5	67.9
97.5°	119.2	116.0	112.9	111.3	111.1	110.9	110.7	110.5	110.7	110.9	111.1
100°	150.7	147.6	144.7	143.3	143.3	143.3	143.3	143.3	143.3	143.3	143.3
102.5°	186.3	184.8	183.3	182.1	181.2	180.3	179.4	178.4	179.4	180.3	181.2
105°	241.9	240.4	239.1	237.8	236.7	235.6	234.4	233.3	234.4	235.6	236.7
107.5°	301.6	300.5	299.5	298.4	297.3	296.2	295.0	293.9	295.0	296.2	297.3
110°	342.4	341.7	341.1	340.2	339.0	337.9	336.8	335.6	336.8	337.9	339.0



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	383.0	382.1	381.3	380.5	380.0	379.4	378.8	378.2	378.8	379.4	380.0
115°	446.3	445.8	445.4	444.6	443.7	442.8	441.9	441.0	441.9	442.8	443.7
117.5°	507.0	506.5	506.1	505.7	505.2	504.8	504.4	504.0	504.4	504.8	505.2
120°	549.1	548.8	548.6	547.9	546.7	545.6	544.5	543.3	544.5	545.6	546.7
122.5°	589.3	588.7	588.0	587.5	587.1	586.7	586.3	585.9	586.3	586.7	587.1
125°	650.4	650.2	649.8	649.0	647.7	646.3	645.0	643.6	645.0	646.3	647.7
127.5°	709.2	708.9	708.6	708.1	707.3	706.6	705.8	705.0	705.8	706.6	707.3
130°	748.1	747.7	747.2	746.4	745.3	744.2	743.0	741.8	743.0	744.2	745.3
132.5°	786.9	787.0	787.1	786.2	784.3	782.4	780.5	778.7	780.5	782.4	784.3
135°	843.7	843.5	843.2	842.5	841.1	839.7	838.4	837.0	838.4	839.7	841.1
137.5°	899.1	898.6	898.1	897.2	895.9	894.5	893.2	891.9	893.2	894.5	895.9
140°	933.9	933.2	932.5	931.6	930.5	929.4	928.2	927.1	928.2	929.4	930.5
142.5°	968.8	967.9	967.0	966.1	965.1	964.2	963.2	962.3	963.2	964.2	965.1
145°	1019.9	1019.2	1018.4	1017.6	1016.7	1015.8	1014.9	1014.0	1014.9	1015.8	1016.7
147.5°	1065.5	1065.0	1064.5	1063.9	1063.4	1063.0	1062.5	1062.0	1062.5	1063.0	1063.4
150°	1095.1	1094.2	1093.3	1093.0	1093.2	1093.4	1093.7	1093.9	1093.7	1093.4	1093.2
152.5°	1122.4	1122.1	1121.7	1121.4	1121.1	1120.6	1120.3	1120.0	1120.3	1120.6	1121.1
155°	1160.9	1160.7	1160.4	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3	1160.3
157.5°	1194.7	1194.5	1194.3	1194.4	1194.9	1195.4	1195.9	1196.4	1195.9	1195.4	1194.9
160°	1215.2	1215.0	1214.8	1215.0	1215.7	1216.3	1217.0	1217.7	1217.0	1216.3	1215.7
162.5°	1234.4	1234.4	1234.3	1234.5	1235.0	1235.5	1236.0	1236.5	1236.0	1235.5	1235.0
165°	1260.2	1260.0	1259.7	1259.8	1260.3	1260.7	1261.2	1261.7	1261.2	1260.7	1260.3
167.5°	1278.9	1278.9	1278.9	1279.3	1280.2	1281.1	1282.0	1282.9	1282.0	1281.1	1280.2
170°	1290.3	1290.3	1290.3	1290.8	1291.7	1292.6	1293.5	1294.4	1293.5	1292.6	1291.7
172.5°	1298.5	1298.5	1298.5	1299.0	1299.9	1300.8	1301.7	1302.6	1301.7	1300.8	1299.9
175°	1307.7	1307.7	1307.7	1308.2	1309.1	1310.0	1310.9	1311.8	1310.9	1310.0	1309.1
177.5°	1312.8	1312.9	1313.1	1313.6	1314.3	1315.0	1315.8	1316.6	1315.8	1315.0	1314.3
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	9.3	10.3	10.3	10.9	11.2	12.2	12.1	13.5	14.4	15.2	15.1
90°	8.3	10.0	11.6	13.2	14.7	16.4	17.5	18.7	19.8	20.9	21.8
92.5°	29.9	31.5	33.4	35.3	37.4	39.3	40.8	42.3	43.8	45.3	46.3
95°	68.4	69.7	72.0	74.2	76.5	78.8	80.4	82.0	83.5	85.1	86.1
97.5°	111.3	112.9	116.0	119.2	122.3	125.4	126.9	128.5	130.0	131.5	132.3
100°	143.3	144.7	147.6	150.7	153.6	156.5	158.6	160.7	162.7	164.7	166.0
102.5°	182.1	183.3	184.8	186.3	187.8	189.3	191.6	193.8	196.0	198.2	199.7
105°	237.8	239.1	240.4	241.9	243.2	244.6	245.9	247.3	248.6	250.0	251.1
107.5°	298.4	299.5	300.5	301.6	302.7	303.7	304.4	305.1	305.8	306.4	306.8
110°	340.2	341.1	341.7	342.4	343.2	343.9	344.5	345.2	345.9	346.6	346.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	380.5	381.3	382.1	383.0	383.8	384.8	385.1	385.4	385.7	386.0	386.0
115°	444.6	445.4	445.8	446.3	446.7	447.2	447.0	446.7	446.5	446.3	446.1
117.5°	505.7	506.1	506.5	507.0	507.4	507.8	508.0	508.1	508.3	508.5	508.1
120°	547.9	548.6	548.8	549.1	549.3	549.5	549.5	549.5	549.5	549.5	549.1
122.5°	587.5	588.0	588.7	589.3	589.9	590.5	590.3	590.1	589.9	589.7	589.3
125°	649.0	649.8	650.2	650.4	650.6	650.8	650.4	649.8	649.4	648.9	648.6
127.5°	708.1	708.6	708.9	709.2	709.4	709.7	709.5	709.2	709.0	708.8	708.5
130°	746.4	747.2	747.7	748.1	748.6	749.0	748.8	748.6	748.3	748.1	747.8
132.5°	786.2	787.1	787.0	786.9	786.8	786.7	786.5	786.2	786.0	785.8	785.4
135°	842.5	843.2	843.5	843.7	843.9	844.1	844.1	844.1	844.1	844.1	843.7
137.5°	897.2	898.1	898.6	899.1	899.6	900.1	900.3	900.6	900.9	901.1	900.7
140°	931.6	932.5	933.2	933.9	934.5	935.2	935.7	936.1	936.6	937.1	936.8
142.5°	966.1	967.0	967.9	968.8	969.6	970.5	970.7	971.0	971.3	971.6	971.1
145°	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2	1021.2	1021.2	1021.2	1020.9
147.5°	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2	1067.7	1068.2	1068.8	1068.3
150°	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9	1096.9	1096.9	1096.9	1096.7
152.5°	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7	1124.2	1124.8	1125.3	1125.2
155°	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4	1163.3	1164.2	1165.1	1164.9
157.5°	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1	1197.0	1197.9	1198.8	1198.5
160°	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6	1217.5	1218.4	1219.3	1219.1
162.5°	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6	1236.7	1237.7	1238.8	1238.7
165°	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5	1262.4	1263.3	1264.3	1264.0
167.5°	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2	1281.6	1282.9	1284.3	1284.3
170°	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7	1293.0	1294.4	1295.8	1295.7
172.5°	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9	1301.2	1302.6	1303.9	1303.9
175°	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1	1310.4	1311.8	1313.2	1313.0
177.5°	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5	1314.6	1315.8	1316.8	1316.7
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	15.9	15.7	15.9	16.6	15.9	15.7	15.9	15.1	15.2	14.4	13.5
90°	22.5	23.2	23.8	24.5	23.8	23.2	22.5	21.8	20.9	19.8	18.7
92.5°	46.8	47.3	47.8	48.3	47.8	47.3	46.8	46.3	45.3	43.8	42.3
95°	86.6	87.1	87.6	88.0	87.6	87.1	86.6	86.1	85.1	83.5	82.0
97.5°	132.6	132.9	133.2	133.4	133.2	132.9	132.6	132.3	131.5	130.0	128.5
100°	166.4	166.9	167.3	167.8	167.3	166.9	166.4	166.0	164.7	162.7	160.7
102.5°	200.3	201.0	201.6	202.2	201.6	201.0	200.3	199.7	198.2	196.0	193.8
105°	251.8	252.4	253.1	253.8	253.1	252.4	251.8	251.1	250.0	248.6	247.3
107.5°	306.7	306.7	306.6	306.6	306.6	306.7	306.7	306.8	306.4	305.8	305.1
110°	346.6	346.3	346.1	345.9	346.1	346.3	346.6	346.8	346.6	345.9	345.2



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	385.6	385.2	384.8	384.4	384.8	385.2	385.6	386.0	386.0	385.7	385.4
115°	445.8	445.6	445.4	445.1	445.4	445.6	445.8	446.1	446.3	446.5	446.7
117.5°	507.2	506.2	505.3	504.4	505.3	506.2	507.2	508.1	508.5	508.3	508.1
120°	548.2	547.2	546.3	545.4	546.3	547.2	548.2	549.1	549.5	549.5	549.5
122.5°	588.5	587.7	587.0	586.3	587.0	587.7	588.5	589.3	589.7	589.9	590.1
125°	648.4	648.1	647.9	647.7	647.9	648.1	648.4	648.6	648.9	649.4	649.8
127.5°	708.0	707.6	707.1	706.7	707.1	707.6	708.0	708.5	708.8	709.0	709.2
130°	747.3	746.9	746.4	746.0	746.4	746.9	747.3	747.8	748.1	748.3	748.6
132.5°	784.7	784.1	783.5	782.7	783.5	784.1	784.7	785.4	785.8	786.0	786.2
135°	842.8	841.9	841.0	840.1	841.0	841.9	842.8	843.7	844.1	844.1	844.1
137.5°	899.6	898.5	897.3	896.2	897.3	898.5	899.6	900.7	901.1	900.9	900.6
140°	935.6	934.4	933.3	932.2	933.3	934.4	935.6	936.8	937.1	936.6	936.1
142.5°	970.0	968.9	967.8	966.5	967.8	968.9	970.0	971.1	971.6	971.3	971.0
145°	1020.2	1019.5	1018.9	1018.1	1018.9	1019.5	1020.2	1020.9	1021.2	1021.2	1021.2
147.5°	1066.8	1065.2	1063.7	1062.2	1063.7	1065.2	1066.8	1068.3	1068.8	1068.2	1067.7
150°	1096.2	1095.8	1095.3	1094.9	1095.3	1095.8	1096.2	1096.7	1096.9	1096.9	1096.9
152.5°	1124.4	1123.6	1122.7	1121.9	1122.7	1123.6	1124.4	1125.2	1125.3	1124.8	1124.2
155°	1163.8	1162.7	1161.5	1160.3	1161.5	1162.7	1163.8	1164.9	1165.1	1164.2	1163.3
157.5°	1197.0	1195.5	1194.0	1192.5	1194.0	1195.5	1197.0	1198.5	1198.8	1197.9	1197.0
160°	1218.0	1216.9	1215.8	1214.6	1215.8	1216.9	1218.0	1219.1	1219.3	1218.4	1217.5
162.5°	1237.4	1236.1	1234.8	1233.4	1234.8	1236.1	1237.4	1238.7	1238.8	1237.7	1236.7
165°	1262.7	1261.3	1260.0	1258.6	1260.0	1261.3	1262.7	1264.0	1264.3	1263.3	1262.4
167.5°	1282.9	1281.5	1280.1	1278.7	1280.1	1281.5	1282.9	1284.3	1284.3	1282.9	1281.6
170°	1294.0	1292.5	1290.9	1289.3	1290.9	1292.5	1294.0	1295.7	1295.8	1294.4	1293.0
172.5°	1302.5	1301.1	1299.7	1298.3	1299.7	1301.1	1302.5	1303.9	1303.9	1302.6	1301.2
175°	1311.5	1309.9	1308.3	1306.7	1308.3	1309.9	1311.5	1313.0	1313.2	1311.8	1310.4
177.5°	1315.5	1314.1	1312.9	1311.6	1312.9	1314.1	1315.5	1316.7	1316.8	1315.8	1314.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	12.1	12.2	11.2	10.9	10.3	10.3	9.3	8.7	8.0	8.0	8.5
90°	17.5	16.4	14.7	13.2	11.6	10.0	8.3	6.5	4.6	2.8	1.0
92.5°	40.8	39.3	37.4	35.3	33.4	31.5	29.9	28.6	27.3	26.1	24.7
95°	80.4	78.8	76.5	74.2	72.0	69.7	68.4	67.9	67.5	67.0	66.6
97.5°	126.9	125.4	122.3	119.2	116.0	112.9	111.3	111.1	110.9	110.7	110.5
100°	158.6	156.5	153.6	150.7	147.6	144.7	143.3	143.3	143.3	143.3	143.3
102.5°	191.6	189.3	187.8	186.3	184.8	183.3	182.1	181.2	180.3	179.4	178.4
105°	245.9	244.6	243.2	241.9	240.4	239.1	237.8	236.7	235.6	234.4	233.3
107.5°	304.4	303.7	302.7	301.6	300.5	299.5	298.4	297.3	296.2	295.0	293.9
110°	344.5	343.9	343.2	342.4	341.7	341.1	340.2	339.0	337.9	336.8	335.6



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	385.1	384.8	383.8	383.0	382.1	381.3	380.5	380.0	379.4	378.8	378.2
115°	447.0	447.2	446.7	446.3	445.8	445.4	444.6	443.7	442.8	441.9	441.0
117.5°	508.0	507.8	507.4	507.0	506.5	506.1	505.7	505.2	504.8	504.4	504.0
120°	549.5	549.5	549.3	549.1	548.8	548.6	547.9	546.7	545.6	544.5	543.3
122.5°	590.3	590.5	589.9	589.3	588.7	588.0	587.5	587.1	586.7	586.3	585.9
125°	650.4	650.8	650.6	650.4	650.2	649.8	649.0	647.7	646.3	645.0	643.6
127.5°	709.5	709.7	709.4	709.2	708.9	708.6	708.1	707.3	706.6	705.8	705.0
130°	748.8	749.0	748.6	748.1	747.7	747.2	746.4	745.3	744.2	743.0	741.8
132.5°	786.5	786.7	786.8	786.9	787.0	787.1	786.2	784.3	782.4	780.5	778.7
135°	844.1	844.1	843.9	843.7	843.5	843.2	842.5	841.1	839.7	838.4	837.0
137.5°	900.3	900.1	899.6	899.1	898.6	898.1	897.2	895.9	894.5	893.2	891.9
140°	935.7	935.2	934.5	933.9	933.2	932.5	931.6	930.5	929.4	928.2	927.1
142.5°	970.7	970.5	969.6	968.8	967.9	967.0	966.1	965.1	964.2	963.2	962.3
145°	1021.2	1021.2	1020.6	1019.9	1019.2	1018.4	1017.6	1016.7	1015.8	1014.9	1014.0
147.5°	1067.2	1066.6	1066.1	1065.5	1065.0	1064.5	1063.9	1063.4	1063.0	1062.5	1062.0
150°	1096.9	1096.9	1096.0	1095.1	1094.2	1093.3	1093.0	1093.2	1093.4	1093.7	1093.9
152.5°	1123.7	1123.2	1122.8	1122.4	1122.1	1121.7	1121.4	1121.1	1120.6	1120.3	1120.0
155°	1162.4	1161.4	1161.1	1160.9	1160.7	1160.4	1160.3	1160.3	1160.3	1160.3	1160.3
157.5°	1196.1	1195.2	1195.0	1194.7	1194.5	1194.3	1194.4	1194.9	1195.4	1195.9	1196.4
160°	1216.6	1215.7	1215.4	1215.2	1215.0	1214.8	1215.0	1215.7	1216.3	1217.0	1217.7
162.5°	1235.6	1234.5	1234.5	1234.4	1234.4	1234.3	1234.5	1235.0	1235.5	1236.0	1236.5
165°	1261.5	1260.6	1260.4	1260.2	1260.0	1259.7	1259.8	1260.3	1260.7	1261.2	1261.7
167.5°	1280.2	1278.9	1278.9	1278.9	1278.9	1278.9	1279.3	1280.2	1281.1	1282.0	1282.9
170°	1291.7	1290.3	1290.3	1290.3	1290.3	1290.3	1290.8	1291.7	1292.6	1293.5	1294.4
172.5°	1299.9	1298.5	1298.5	1298.5	1298.5	1298.5	1299.0	1299.9	1300.8	1301.7	1302.6
175°	1309.1	1307.7	1307.7	1307.7	1307.7	1307.7	1308.2	1309.1	1310.0	1310.9	1311.8
177.5°	1313.5	1312.4	1312.6	1312.8	1312.9	1313.1	1313.6	1314.3	1315.0	1315.8	1316.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.6	9.2	10.5	12.4	13.6	15.2	16.2	15.9	14.9	14.2	13.5
90°	2.8	4.6	6.5	8.3	10.0	11.6	13.2	14.7	16.4	17.5	18.7
92.5°	26.1	27.3	28.6	29.9	31.5	33.4	35.3	37.4	39.3	40.8	42.3
95°	67.0	67.5	67.9	68.4	69.7	72.0	74.2	76.5	78.8	80.4	82.0
97.5°	110.7	110.9	111.1	111.3	112.9	116.0	119.2	122.3	125.4	126.9	128.5
100°	143.3	143.3	143.3	143.3	144.7	147.6	150.7	153.6	156.5	158.6	160.7
102.5°	179.4	180.3	181.2	182.1	183.3	184.8	186.3	187.8	189.3	191.6	193.8
105°	234.4	235.6	236.7	237.8	239.1	240.4	241.9	243.2	244.6	245.9	247.3
107.5°	295.0	296.2	297.3	298.4	299.5	300.5	301.6	302.7	303.7	304.4	305.1
110°	336.8	337.9	339.0	340.2	341.1	341.7	342.4	343.2	343.9	344.5	345.2



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	378.8	379.4	380.0	380.5	381.3	382.1	383.0	383.8	384.8	385.1	385.4
115°	441.9	442.8	443.7	444.6	445.4	445.8	446.3	446.7	447.2	447.0	446.7
117.5°	504.4	504.8	505.2	505.7	506.1	506.5	507.0	507.4	507.8	508.0	508.1
120°	544.5	545.6	546.7	547.9	548.6	548.8	549.1	549.3	549.5	549.5	549.5
122.5°	586.3	586.7	587.1	587.5	588.0	588.7	589.3	589.9	590.5	590.3	590.1
125°	645.0	646.3	647.7	649.0	649.8	650.2	650.4	650.6	650.8	650.4	649.8
127.5°	705.8	706.6	707.3	708.1	708.6	708.9	709.2	709.4	709.7	709.5	709.2
130°	743.0	744.2	745.3	746.4	747.2	747.7	748.1	748.6	749.0	748.8	748.6
132.5°	780.5	782.4	784.3	786.2	787.1	787.0	786.9	786.8	786.7	786.5	786.2
135°	838.4	839.7	841.1	842.5	843.2	843.5	843.7	843.9	844.1	844.1	844.1
137.5°	893.2	894.5	895.9	897.2	898.1	898.6	899.1	899.6	900.1	900.3	900.6
140°	928.2	929.4	930.5	931.6	932.5	933.2	933.9	934.5	935.2	935.7	936.1
142.5°	963.2	964.2	965.1	966.1	967.0	967.9	968.8	969.6	970.5	970.7	971.0
145°	1014.9	1015.8	1016.7	1017.6	1018.4	1019.2	1019.9	1020.6	1021.2	1021.2	1021.2
147.5°	1062.5	1063.0	1063.4	1063.9	1064.5	1065.0	1065.5	1066.1	1066.6	1067.2	1067.7
150°	1093.7	1093.4	1093.2	1093.0	1093.3	1094.2	1095.1	1096.0	1096.9	1096.9	1096.9
152.5°	1120.3	1120.6	1121.1	1121.4	1121.7	1122.1	1122.4	1122.8	1123.2	1123.7	1124.2
155°	1160.3	1160.3	1160.3	1160.3	1160.4	1160.7	1160.9	1161.1	1161.4	1162.4	1163.3
157.5°	1195.9	1195.4	1194.9	1194.4	1194.3	1194.5	1194.7	1195.0	1195.2	1196.1	1197.0
160°	1217.0	1216.3	1215.7	1215.0	1214.8	1215.0	1215.2	1215.4	1215.7	1216.6	1217.5
162.5°	1236.0	1235.5	1235.0	1234.5	1234.3	1234.4	1234.4	1234.5	1234.5	1235.6	1236.7
165°	1261.2	1260.7	1260.3	1259.8	1259.7	1260.0	1260.2	1260.4	1260.6	1261.5	1262.4
167.5°	1282.0	1281.1	1280.2	1279.3	1278.9	1278.9	1278.9	1278.9	1278.9	1280.2	1281.6
170°	1293.5	1292.6	1291.7	1290.8	1290.3	1290.3	1290.3	1290.3	1290.3	1291.7	1293.0
172.5°	1301.7	1300.8	1299.9	1299.0	1298.5	1298.5	1298.5	1298.5	1298.5	1299.9	1301.2
175°	1310.9	1310.0	1309.1	1308.2	1307.7	1307.7	1307.7	1307.7	1307.7	1309.1	1310.4
177.5°	1315.8	1315.0	1314.3	1313.6	1313.1	1312.9	1312.8	1312.6	1312.4	1313.5	1314.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	13.7	12.8	12.9	12.8	12.9	12.7	12.3
90°	19.8	20.9	21.8	22.5	23.2	23.8	24.5
92.5°	43.8	45.3	46.3	46.8	47.3	47.8	48.3
95°	83.5	85.1	86.1	86.6	87.1	87.6	88.0
97.5°	130.0	131.5	132.3	132.6	132.9	133.2	133.4
100°	162.7	164.7	166.0	166.4	166.9	167.3	167.8
102.5°	196.0	198.2	199.7	200.3	201.0	201.6	202.2
105°	248.6	250.0	251.1	251.8	252.4	253.1	253.8
107.5°	305.8	306.4	306.8	306.7	306.7	306.6	306.6
110°	345.9	346.6	346.8	346.6	346.3	346.1	345.9



TEST NUMBER: P333383-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	385.7	386.0	386.0	385.6	385.2	384.8	384.4
115°	446.5	446.3	446.1	445.8	445.6	445.4	445.1
117.5°	508.3	508.5	508.1	507.2	506.2	505.3	504.4
120°	549.5	549.5	549.1	548.2	547.2	546.3	545.4
122.5°	589.9	589.7	589.3	588.5	587.7	587.0	586.3
125°	649.4	648.9	648.6	648.4	648.1	647.9	647.7
127.5°	709.0	708.8	708.5	708.0	707.6	707.1	706.7
130°	748.3	748.1	747.8	747.3	746.9	746.4	746.0
132.5°	786.0	785.8	785.4	784.7	784.1	783.5	782.7
135°	844.1	844.1	843.7	842.8	841.9	841.0	840.1
137.5°	900.9	901.1	900.7	899.6	898.5	897.3	896.2
140°	936.6	937.1	936.8	935.6	934.4	933.3	932.2
142.5°	971.3	971.6	971.1	970.0	968.9	967.8	966.5
145°	1021.2	1021.2	1020.9	1020.2	1019.5	1018.9	1018.1
147.5°	1068.2	1068.8	1068.3	1066.8	1065.2	1063.7	1062.2
150°	1096.9	1096.9	1096.7	1096.2	1095.8	1095.3	1094.9
152.5°	1124.8	1125.3	1125.2	1124.4	1123.6	1122.7	1121.9
155°	1164.2	1165.1	1164.9	1163.8	1162.7	1161.5	1160.3
157.5°	1197.9	1198.8	1198.5	1197.0	1195.5	1194.0	1192.5
160°	1218.4	1219.3	1219.1	1218.0	1216.9	1215.8	1214.6
162.5°	1237.7	1238.8	1238.7	1237.4	1236.1	1234.8	1233.4
165°	1263.3	1264.3	1264.0	1262.7	1261.3	1260.0	1258.6
167.5°	1282.9	1284.3	1284.3	1282.9	1281.5	1280.1	1278.7
170°	1294.4	1295.8	1295.7	1294.0	1292.5	1290.9	1289.3
172.5°	1302.6	1303.9	1303.9	1302.5	1301.1	1299.7	1298.3
175°	1311.8	1313.2	1313.0	1311.5	1309.9	1308.3	1306.7
177.5°	1315.8	1316.8	1316.7	1315.5	1314.1	1312.9	1311.6
180°	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8	1314.8

(END OF REPORT)