

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333386-840

Luminaire Tested: **S125DIW-S610D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333386-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1050U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6757.6 lumens
Efficiency: N/A
Efficacy: 149.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	51	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.4
10°-20°	258.3	3.8
20°-30°	381.4	5.6
30°-40°	445.0	6.6
40°-50°	447.0	6.6
50°-60°	392.4	5.8
60°-70°	292.4	4.3
70°-80°	167.2	2.5
80°-90°	51.5	0.8
90°-100°	50.1	0.7
100°-110°	308.6	4.6
110°-120°	559.7	8.3
120°-130°	718.2	10.6
130°-140°	772.5	11.4
140°-150°	725.1	10.7
150°-160°	586.6	8.7
160°-170°	379.4	5.6
170°-180°	130.8	1.9
0°-30°	731.2	10.8
0°-40°	1176.2	17.4
0°-60°	2015.6	29.8
0°-90°	2526.6	37.4
90°-120°	918.3	13.6
90°-150°	3134.2	46.4
90°-180°	4231.0	62.6
0°-180°	6757.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	1	9	16	21	24	5
95°	58	53	16	21	21	74
105°	300	304	304	304	303	318
115°	564	569	570	566	560	559
125°	802	808	809	805	802	716
135°	1000	1006	1004	1002	996	770
145°	1159	1161	1161	1162	1156	725
155°	1277	1271	1273	1275	1268	588
165°	1347	1341	1342	1347	1340	380
175°	1378	1372	1373	1380	1372	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.8	17.2	17.5	17.9	18.3	18.5	18.7	18.9	19.1	19.2	19.5
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.1	14.7	16.4	17.5
92.5°	15.8	14.4	13.2	11.9	10.6	10.7	12.1	13.5	14.9	16.4	17.5
95°	58.2	57.6	56.9	56.1	55.5	50.8	42.2	33.6	24.9	16.4	17.5
97.5°	121.6	122.8	124.0	125.2	126.4	118.6	101.5	84.4	67.4	50.3	43.8
100°	170.6	171.3	171.9	172.6	173.3	174.1	175.0	175.9	176.8	177.7	143.9
102.5°	220.5	221.3	222.2	223.0	223.9	224.6	225.1	225.6	226.2	226.7	220.4
105°	300.2	301.1	302.1	303.0	303.9	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	383.2	383.2	383.2	383.2	383.2	383.4	383.8	384.4	384.8	385.3	385.3
110°	437.2	437.2	437.2	437.2	437.2	437.4	437.8	438.3	438.7	439.2	438.5



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.4	488.9	489.4	490.0	490.4	490.7	490.9	491.2	491.5	490.6
115°	563.8	564.9	566.0	567.1	568.4	569.0	569.3	569.5	569.7	569.9	569.0
117.5°	642.5	642.4	642.4	642.3	642.3	642.7	643.5	644.4	645.2	646.1	644.9
120°	691.5	691.3	690.9	690.7	690.5	690.7	691.5	692.2	692.8	693.5	693.1
122.5°	734.8	735.6	736.5	737.3	738.2	738.8	739.1	739.4	739.7	740.0	739.6
125°	801.7	803.3	805.0	806.5	808.1	808.9	808.9	808.9	808.9	808.9	808.0
127.5°	865.7	866.9	868.0	869.1	870.2	870.7	870.6	870.5	870.3	870.2	869.7
130°	904.9	906.1	907.2	908.3	909.5	910.1	910.4	910.6	910.8	911.0	910.4
132.5°	944.1	945.4	946.7	948.1	949.4	949.8	949.3	948.8	948.3	947.9	947.7
135°	999.9	1001.3	1002.6	1004.0	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5
137.5°	1051.2	1052.4	1053.5	1054.7	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7
140°	1084.7	1085.1	1085.6	1086.0	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1
142.5°	1114.9	1115.2	1115.5	1115.7	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6
145°	1159.2	1159.7	1160.1	1160.6	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5
147.5°	1198.0	1198.0	1197.9	1197.8	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1
150°	1222.5	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0
152.5°	1246.3	1245.3	1244.3	1243.2	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3
155°	1276.7	1275.4	1273.9	1272.6	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2
157.5°	1300.2	1299.4	1298.6	1297.8	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5
160°	1316.6	1315.1	1313.8	1312.4	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3
162.5°	1329.6	1328.3	1326.9	1325.5	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8
165°	1347.2	1345.8	1344.4	1343.1	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4
167.5°	1360.2	1358.9	1357.5	1356.0	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6
170°	1367.6	1366.0	1364.4	1362.8	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3
172.5°	1372.5	1370.9	1369.3	1367.8	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8
175°	1377.8	1376.4	1375.0	1373.7	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5
177.5°	1380.3	1379.2	1378.1	1377.0	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	19.7	19.9	20.1	20.2	20.0	19.9	19.8	19.6
90°	18.6	19.8	20.9	21.8	22.5	23.1	23.8	24.5
92.5°	18.6	19.8	20.9	21.6	21.9	22.2	22.5	22.9
95°	18.6	19.8	20.9	21.4	21.4	21.4	21.4	21.4
97.5°	37.5	31.0	24.6	21.4	21.4	21.4	21.4	21.4
100°	110.1	76.2	42.4	25.0	24.1	23.2	22.3	21.4
102.5°	213.9	207.5	201.2	190.3	174.8	159.4	143.9	128.5
105°	304.4	304.4	304.4	304.3	304.1	303.8	303.6	303.4
107.5°	385.4	385.4	385.5	385.2	384.5	383.7	383.0	382.4
110°	437.8	437.2	436.5	436.3	436.5	436.7	436.9	437.2



TEST NUMBER: P333386-840

CATALOG NUMBER: S125DIW-S610D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.8	488.9	488.1	487.5	487.2	486.8	486.5	486.1
115°	568.0	567.1	566.2	565.1	563.8	562.4	561.1	559.7
117.5°	643.8	642.6	641.4	640.5	640.0	639.3	638.7	638.1
120°	692.6	692.2	691.7	690.8	689.7	688.6	687.5	686.3
122.5°	739.1	738.7	738.2	737.4	736.1	734.8	733.5	732.2
125°	807.1	806.2	805.3	804.5	803.9	803.1	802.4	801.7
127.5°	869.2	868.7	868.2	867.1	865.5	863.7	862.0	860.4
130°	909.7	909.0	908.3	907.4	906.3	905.1	904.0	902.9
132.5°	947.6	947.4	947.3	946.6	945.5	944.3	943.2	942.1
135°	1003.1	1002.6	1002.2	1001.3	999.9	998.6	997.1	995.8
137.5°	1054.8	1054.9	1055.0	1054.5	1053.3	1052.1	1051.0	1049.8
140°	1086.6	1087.0	1087.5	1087.0	1085.7	1084.3	1083.0	1081.6
142.5°	1117.7	1117.8	1117.9	1117.3	1115.9	1114.6	1113.2	1111.9
145°	1161.7	1162.0	1162.2	1161.6	1160.2	1158.9	1157.5	1156.2
147.5°	1199.4	1199.7	1199.9	1199.3	1197.6	1196.0	1194.4	1192.8
150°	1223.5	1224.0	1224.4	1223.7	1221.8	1220.0	1218.2	1216.4
152.5°	1244.7	1245.2	1245.6	1245.1	1243.3	1241.7	1240.1	1238.5
155°	1273.9	1274.7	1275.4	1274.8	1272.9	1271.1	1269.3	1267.5
157.5°	1298.2	1298.9	1299.6	1299.1	1297.3	1295.5	1293.6	1291.8
160°	1313.2	1314.1	1315.0	1314.5	1312.8	1311.0	1309.2	1307.4
162.5°	1327.1	1328.3	1329.6	1329.2	1327.2	1325.2	1323.2	1321.2
165°	1344.7	1346.2	1347.5	1347.3	1345.4	1343.6	1341.8	1340.0
167.5°	1358.2	1359.8	1361.5	1361.3	1359.2	1357.2	1355.1	1353.1
170°	1365.1	1367.0	1368.8	1368.6	1366.5	1364.5	1362.5	1360.4
172.5°	1370.5	1372.1	1373.7	1373.5	1371.5	1369.4	1367.4	1365.3
175°	1376.3	1378.2	1380.0	1379.9	1377.8	1375.7	1373.7	1371.7
177.5°	1378.7	1380.0	1381.3	1381.2	1379.7	1378.3	1376.8	1375.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8

(END OF REPORT)