

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333489

Luminaire Tested: **S125DIW-S1270D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333489  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D1560U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10540.2 lumens  
Efficiency: N/A  
Efficacy: 127.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.8	1.8
10°-20°	524.9	5.0
20°-30°	775.0	7.4
30°-40°	904.3	8.6
40°-50°	908.3	8.6
50°-60°	797.3	7.6
60°-70°	594.1	5.6
70°-80°	339.7	3.2
80°-90°	103.1	1.0
90°-100°	129.8	1.2
100°-110°	383.3	3.6
110°-120°	649.2	6.2
120°-130°	854.4	8.1
130°-140°	957.4	9.1
140°-150°	938.3	8.9
150°-160°	788.1	7.5
160°-170°	523.9	5.0
170°-180°	183.3	1.7
0°-30°	1485.7	14.1
0°-40°	2390.0	22.7
0°-60°	4095.6	38.9
0°-90°	5132.4	48.7
90°-120°	1162.3	11.0
90°-150°	3912.5	37.1
90°-180°	5408.0	51.3
0°-180°	10540.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	2	13	24	32	36	10
95°	98	102	116	126	130	105
105°	344	352	360	369	374	367
115°	650	656	659	658	656	643
125°	949	957	959	956	955	849
135°	1234	1242	1244	1244	1238	951
145°	1495	1501	1505	1505	1501	934
155°	1710	1710	1712	1717	1710	787
165°	1860	1857	1858	1863	1855	524
175°	1934	1928	1927	1935	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	34.0	34.5	35.1	35.6	36.1	36.5	36.7	36.9	37.1	37.3	37.6
90°	1.5	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8
92.5°	36.5	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1
95°	98.0	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5
97.5°	162.9	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1
100°	211.1	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8
102.5°	263.0	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3
105°	343.9	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5
107.5°	433.1	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6
110°	494.7	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7



TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	557.4	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5
115°	650.0	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7
117.5°	742.9	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6
120°	800.8	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9
122.5°	863.6	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9
125°	948.6	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5
127.5°	1039.1	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7
130°	1093.4	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6
132.5°	1147.7	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1
135°	1233.7	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2
137.5°	1314.5	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0
140°	1366.4	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1
142.5°	1418.3	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7
145°	1494.6	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1
147.5°	1565.2	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9
150°	1612.2	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8
152.5°	1650.8	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2
155°	1710.3	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1
157.5°	1763.3	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9
160°	1794.7	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0
162.5°	1822.5	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1
165°	1859.6	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4
167.5°	1890.9	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9
170°	1907.8	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8
172.5°	1919.9	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9
175°	1933.5	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4
177.5°	1940.4	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	37.9	38.3	38.6	38.6	38.2	37.9	37.5	37.2
90°	27.5	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	62.3	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	120.8	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	189.3	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	236.8	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	285.6	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	364.5	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	449.6	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	508.8	509.8	510.8	511.1	510.8	510.4	510.1	509.8





TEST NUMBER: P333489

CATALOG NUMBER: S125DIW-S1270D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.0	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.4	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	748.9	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.7	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.9	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.4	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.3	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.8	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.4	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1379.8	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.1	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1573.7	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.0	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1714.4	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1764.2	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1794.4	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1822.7	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1860.7	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1888.9	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1905.8	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1917.9	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1931.5	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1937.6	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)