

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333470

Luminaire Tested: **S125DIW-S1270D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333470
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8199.7 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	53	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	25	22	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.3
10°-20°	524.9	6.4
20°-30°	775.0	9.5
30°-40°	904.3	11.0
40°-50°	908.3	11.1
50°-60°	797.3	9.7
60°-70°	594.1	7.2
70°-80°	339.7	4.1
80°-90°	100.9	1.2
90°-100°	36.3	0.4
100°-110°	223.9	2.7
110°-120°	406.0	5.0
120°-130°	521.1	6.4
130°-140°	560.5	6.8
140°-150°	526.1	6.4
150°-160°	425.5	5.2
160°-170°	275.2	3.4
170°-180°	94.9	1.2
0°-30°	1485.7	18.1
0°-40°	2390.0	29.1
0°-60°	4095.6	49.9
0°-90°	5130.3	62.6
90°-120°	666.2	8.1
90°-150°	2273.8	27.7
90°-180°	3069.0	37.4
0°-180°	8199.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	7	12	15	18	6
95°	42	39	12	15	16	54
105°	218	221	221	221	220	231
115°	409	413	414	410	406	405
125°	582	587	587	584	582	519
135°	725	730	728	727	722	559
145°	841	842	842	843	839	526
155°	926	922	923	925	920	427
165°	977	973	974	978	972	276
175°	1000	995	996	1001	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	34.1	34.4	34.6	34.9	35.0	34.9	34.9	34.8	34.8	35.0
90°	0.7	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7
92.5°	11.4	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7
95°	42.2	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7
97.5°	88.2	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8
100°	123.7	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4
102.5°	159.9	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9
105°	217.8	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5
110°	317.1	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.9	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9
115°	409.0	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8
117.5°	466.1	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9
120°	501.6	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8
122.5°	533.0	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6
125°	581.7	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2
127.5°	628.0	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9
130°	656.5	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4
132.5°	684.9	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5
135°	725.4	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0
137.5°	762.6	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2
140°	786.9	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0
142.5°	808.8	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8
145°	841.0	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6
147.5°	869.2	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9
150°	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3
152.5°	904.1	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7
155°	926.2	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7
157.5°	943.2	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3
160°	955.1	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1
162.5°	964.6	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8
165°	977.3	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6
167.5°	986.8	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1
170°	992.2	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0
172.5°	995.7	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0
175°	999.6	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2
177.5°	1001.3	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	35.1	35.3	35.5	35.3	34.9	34.4	33.9	33.5
90°	13.5	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	13.5	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	13.5	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	27.2	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	79.9	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	155.2	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.6	317.1	316.6	316.5	316.6	316.8	317.0	317.1



TEST NUMBER: P333470

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.3	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	412.1	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	467.0	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.5	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	536.2	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	585.5	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.6	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	660.0	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.4	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.7	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.3	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	810.9	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	842.8	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.1	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.6	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.0	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.2	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	941.8	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	952.7	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	962.7	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	975.6	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	985.3	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	990.3	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	994.2	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	998.5	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1000.2	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)