

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333398-840

Luminaire Tested: **S125DIW-S610D1560U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333398-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1560U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8825.5 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	71	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	42	43	38	34	32	29	26	22	20	19	15
5	65	53	46	40	58	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.0
10°-20°	258.3	2.9
20°-30°	381.4	4.3
30°-40°	445.0	5.0
40°-50°	447.0	5.1
50°-60°	392.4	4.4
60°-70°	292.4	3.3
70°-80°	167.2	1.9
80°-90°	52.9	0.6
90°-100°	74.5	0.8
100°-110°	459.3	5.2
110°-120°	833.0	9.4
120°-130°	1069.1	12.1
130°-140°	1149.9	13.0
140°-150°	1079.3	12.2
150°-160°	873.1	9.9
160°-170°	564.7	6.4
170°-180°	194.8	2.2
0°-30°	731.2	8.3
0°-40°	1176.2	13.3
0°-60°	2015.6	22.8
0°-90°	2528.0	28.6
90°-120°	1366.8	15.5
90°-150°	4665.0	52.9
90°-180°	6298.0	71.4
0°-180°	8825.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	2	14	24	32	36	6
95°	87	79	24	32	32	110
105°	447	453	453	453	452	474
115°	839	846	848	842	833	832
125°	1193	1203	1204	1198	1193	1065
135°	1488	1497	1494	1491	1482	1147
145°	1726	1728	1728	1729	1721	1079
155°	1900	1892	1894	1898	1886	875
165°	2005	1997	1998	2006	1994	566
175°	2051	2042	2043	2054	2042	195
180°	2051	2051	2051	2051	2051	



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.9	17.4	18.0	18.5	19.1	19.5	19.8	20.2	20.5	20.8	21.2
90°	1.5	4.2	7.0	9.6	12.3	14.8	17.3	19.6	21.9	24.3	26.1
92.5°	23.4	21.5	19.6	17.8	15.9	16.0	18.1	20.1	22.2	24.3	26.1
95°	86.6	85.6	84.6	83.6	82.6	75.6	62.8	50.0	37.2	24.3	26.1
97.5°	180.9	182.7	184.5	186.4	188.2	176.4	151.0	125.6	100.2	74.8	65.2
100°	253.9	254.9	255.9	256.9	257.9	259.1	260.4	261.9	263.2	264.5	214.2
102.5°	328.1	329.3	330.6	331.9	333.2	334.3	335.1	335.9	336.7	337.5	328.0
105°	447.0	448.3	449.7	451.0	452.3	453.0	453.0	453.0	453.0	453.0	453.0
107.5°	570.4	570.4	570.4	570.4	570.4	570.7	571.4	572.1	572.8	573.4	573.5
110°	650.7	650.7	650.7	650.7	650.7	651.0	651.7	652.4	653.0	653.7	652.7



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	726.1	726.9	727.7	728.5	729.3	729.9	730.3	730.7	731.1	731.5	730.2
115°	839.2	840.8	842.5	844.2	845.9	846.9	847.3	847.6	848.0	848.3	846.9
117.5°	956.2	956.1	956.0	956.0	955.9	956.5	957.9	959.1	960.4	961.7	959.9
120°	1029.2	1028.9	1028.5	1028.1	1027.8	1028.1	1029.2	1030.2	1031.2	1032.2	1031.6
122.5°	1093.7	1094.9	1096.2	1097.5	1098.7	1099.6	1100.1	1100.6	1101.1	1101.6	1100.9
125°	1193.4	1195.7	1198.1	1200.4	1202.9	1204.0	1204.0	1204.0	1204.0	1204.0	1202.6
127.5°	1288.5	1290.2	1291.9	1293.6	1295.3	1296.1	1295.9	1295.7	1295.5	1295.3	1294.4
130°	1346.9	1348.6	1350.3	1352.0	1353.6	1354.6	1355.0	1355.3	1355.6	1356.0	1355.0
132.5°	1405.2	1407.2	1409.2	1411.2	1413.1	1413.7	1413.0	1412.2	1411.5	1410.8	1410.6
135°	1488.2	1490.3	1492.4	1494.4	1496.4	1497.0	1496.4	1495.7	1495.0	1494.4	1493.7
137.5°	1564.6	1566.3	1568.1	1569.8	1571.7	1572.2	1571.6	1570.9	1570.3	1569.7	1569.9
140°	1614.5	1615.2	1615.8	1616.5	1617.2	1617.3	1617.0	1616.7	1616.3	1616.0	1616.7
142.5°	1659.4	1659.8	1660.2	1660.6	1661.0	1661.5	1662.0	1662.4	1662.9	1663.4	1663.6
145°	1725.5	1726.1	1726.8	1727.5	1728.2	1728.5	1728.5	1728.5	1728.5	1728.5	1728.8
147.5°	1783.2	1783.0	1782.9	1782.8	1782.6	1782.8	1783.2	1783.6	1784.0	1784.4	1784.8
150°	1819.7	1819.0	1818.4	1817.7	1816.9	1816.9	1817.7	1818.4	1819.0	1819.7	1820.4
152.5°	1854.9	1853.5	1852.0	1850.5	1849.0	1848.6	1849.3	1850.0	1850.7	1851.3	1852.0
155°	1900.3	1898.2	1896.2	1894.2	1892.2	1891.5	1892.2	1892.8	1893.5	1894.2	1895.2
157.5°	1935.2	1934.0	1932.8	1931.6	1930.4	1929.8	1929.9	1930.0	1930.0	1930.1	1931.2
160°	1959.5	1957.5	1955.5	1953.5	1951.5	1950.6	1951.0	1951.3	1951.6	1952.0	1953.3
162.5°	1979.0	1977.0	1975.0	1972.9	1970.9	1970.0	1970.3	1970.8	1971.1	1971.4	1973.3
165°	2005.2	2003.2	2001.0	1999.0	1997.0	1996.2	1996.5	1996.9	1997.2	1997.5	1999.5
167.5°	2024.6	2022.6	2020.4	2018.3	2016.2	2015.4	2015.7	2016.0	2016.4	2016.7	2019.1
170°	2035.6	2033.2	2030.8	2028.4	2026.1	2025.1	2025.4	2025.8	2026.1	2026.4	2029.1
172.5°	2042.9	2040.5	2038.1	2035.8	2033.4	2032.6	2033.2	2033.8	2034.4	2035.0	2037.4
175°	2050.7	2048.7	2046.7	2044.7	2042.7	2041.8	2042.1	2042.5	2042.9	2043.2	2045.9
177.5°	2054.4	2052.8	2051.1	2049.5	2047.9	2047.2	2047.5	2047.8	2048.0	2048.3	2050.2
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	21.5	21.8	22.2	22.3	22.2	22.2	22.1	22.0
90°	27.7	29.4	31.1	32.4	33.4	34.4	35.4	36.5
92.5°	27.7	29.4	31.1	32.1	32.6	33.1	33.6	34.0
95°	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9
97.5°	55.7	46.3	36.7	31.9	31.9	31.9	31.9	31.9
100°	163.8	113.5	63.2	37.4	36.0	34.6	33.3	31.9
102.5°	318.4	308.9	299.4	283.2	260.1	237.2	214.2	191.3
105°	453.0	453.0	453.0	452.8	452.5	452.2	451.8	451.5
107.5°	573.6	573.6	573.7	573.2	572.2	571.2	570.2	569.2
110°	651.7	650.7	649.6	649.3	649.6	649.9	650.4	650.7



TEST NUMBER: P333398-840

CATALOG NUMBER: S125DIW-S610D1560U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	728.9	727.7	726.4	725.5	725.1	724.6	724.1	723.6
115°	845.6	844.2	842.8	841.2	839.2	837.1	835.1	833.0
117.5°	958.2	956.4	954.6	953.3	952.5	951.6	950.7	949.8
120°	1030.9	1030.2	1029.6	1028.3	1026.6	1024.9	1023.3	1021.6
122.5°	1100.1	1099.5	1098.8	1097.5	1095.6	1093.6	1091.7	1089.6
125°	1201.3	1199.9	1198.6	1197.4	1196.4	1195.4	1194.4	1193.4
127.5°	1293.7	1293.0	1292.2	1290.6	1288.1	1285.7	1283.1	1280.6
130°	1354.0	1353.0	1352.0	1350.6	1349.0	1347.3	1345.5	1343.8
132.5°	1410.4	1410.2	1410.0	1409.0	1407.3	1405.6	1403.9	1402.2
135°	1493.0	1492.4	1491.7	1490.3	1488.2	1486.2	1484.2	1482.2
137.5°	1570.0	1570.1	1570.3	1569.5	1567.7	1566.0	1564.2	1562.5
140°	1617.3	1618.0	1618.7	1618.0	1616.0	1614.0	1611.9	1609.9
142.5°	1663.7	1663.9	1664.0	1663.0	1660.9	1658.9	1656.9	1654.9
145°	1729.2	1729.5	1729.8	1729.0	1727.0	1725.0	1722.9	1720.9
147.5°	1785.2	1785.6	1786.0	1785.0	1782.6	1780.2	1777.8	1775.3
150°	1821.0	1821.7	1822.4	1821.4	1818.7	1815.9	1813.3	1810.6
152.5°	1852.7	1853.3	1854.0	1853.1	1850.7	1848.3	1845.8	1843.4
155°	1896.2	1897.2	1898.2	1897.3	1894.7	1892.0	1889.3	1886.5
157.5°	1932.2	1933.3	1934.4	1933.6	1930.9	1928.1	1925.4	1922.8
160°	1954.6	1956.0	1957.3	1956.7	1954.0	1951.3	1948.5	1945.9
162.5°	1975.2	1977.1	1978.9	1978.4	1975.5	1972.5	1969.5	1966.5
165°	2001.6	2003.7	2005.7	2005.3	2002.7	1999.9	1997.2	1994.5
167.5°	2021.5	2024.0	2026.4	2026.1	2023.1	2020.0	2017.0	2014.0
170°	2031.8	2034.6	2037.2	2037.1	2034.1	2031.0	2027.9	2024.9
172.5°	2039.8	2042.3	2044.7	2044.4	2041.3	2038.3	2035.3	2032.3
175°	2048.5	2051.2	2054.0	2053.8	2050.7	2047.7	2044.7	2041.6
177.5°	2052.1	2054.0	2055.9	2055.8	2053.6	2051.4	2049.2	2047.1
180°	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7	2050.7

(END OF REPORT)