

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333380-840

Luminaire Tested: **S125DIW-S610D770U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333380-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D770U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5625.6 lumens  
Efficiency: N/A  
Efficacy: 149.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	31	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6264	6264	6264
5°	6278	6218	6257
10°	6239	6174	6209
15°	6171	6100	6125
20°	6075	5996	6006
25°	5971	5872	5867
30°	5842	5739	5711
35°	5705	5595	5517
40°	5563	5440	5363
45°	5411	5298	5193
50°	5243	5127	4972
55°	5080	4933	4796
60°	4886	4738	4570
65°	4655	4504	4351
70°	4434	4232	4086
75°	4040	3905	3773
80°	3593	3537	3451
85°	3127	3179	3016



TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.4	1.6
10°-20°	258.3	4.6
20°-30°	381.4	6.8
30°-40°	445.0	7.9
40°-50°	447.0	7.9
50°-60°	392.4	7.0
60°-70°	292.4	5.2
70°-80°	167.2	3.0
80°-90°	50.7	0.9
90°-100°	36.7	0.7
100°-110°	226.1	4.0
110°-120°	410.0	7.3
120°-130°	526.2	9.4
130°-140°	566.0	10.1
140°-150°	531.3	9.4
150°-160°	429.7	7.6
160°-170°	277.9	4.9
170°-180°	95.9	1.7
0°-30°	731.2	13.0
0°-40°	1176.2	20.9
0°-60°	2015.6	35.8
0°-90°	2525.8	44.9
90°-120°	672.8	12.0
90°-150°	2296.2	40.8
90°-180°	3100.0	55.1
0°-180°	5625.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	968	966	959	966	965	92
15°	923	920	912	916	916	260
25°	838	834	824	825	823	385
35°	724	720	710	706	700	452
45°	592	589	580	571	569	456
55°	451	448	438	431	426	403
65°	305	303	295	288	285	302
75°	162	160	156	154	151	173
85°	42	43	43	42	41	47
90°	1	7	12	16	18	4
95°	43	39	12	16	16	54
105°	220	223	223	223	222	233
115°	413	417	418	414	410	409
125°	587	592	593	590	587	524
135°	733	737	736	734	730	564
145°	849	851	851	851	847	531
155°	935	931	932	934	929	431
165°	987	983	983	987	982	279
175°	1010	1005	1006	1011	1005	96
180°	1010	1010	1010	1010	1010	



TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	972.3	971.9	971.5	971.1	970.7	969.8	968.5	967.0	965.7	964.3	965.7
5°	968.4	968.0	967.7	967.2	966.9	965.9	964.2	962.5	960.8	959.1	960.7
7.5°	959.4	959.1	958.8	958.4	958.1	956.9	955.0	953.2	951.3	949.5	950.9
10°	951.4	951.1	950.8	950.4	950.1	949.0	947.1	945.2	943.3	941.5	942.8
12.5°	941.6	941.0	940.4	939.8	939.2	938.0	936.2	934.5	932.7	931.0	932.1
15°	923.0	922.5	922.0	921.5	921.0	919.8	918.0	916.0	914.1	912.3	913.1
17.5°	901.7	901.0	900.2	899.5	898.7	897.4	895.4	893.4	891.5	889.6	890.6
20°	883.9	883.5	883.2	882.9	882.5	881.3	879.1	876.9	874.6	872.4	873.6
22.5°	866.1	865.5	864.8	864.2	863.6	862.3	860.2	858.2	856.1	853.9	854.7
25°	837.9	837.0	836.2	835.4	834.5	832.9	830.7	828.5	826.3	824.0	824.5
27.5°	804.9	804.4	803.9	803.3	802.8	801.4	799.1	796.9	794.6	792.3	792.3
30°	783.4	782.8	782.3	781.8	781.3	779.8	777.3	774.7	772.1	769.6	769.2
32.5°	760.0	759.3	758.5	757.7	756.9	755.4	753.2	750.8	748.5	746.3	745.7
35°	723.6	722.9	722.2	721.5	720.8	719.3	716.9	714.5	712.2	709.7	708.9
37.5°	685.6	684.8	684.0	683.1	682.3	680.6	678.4	676.2	673.9	671.7	670.4
40°	659.8	659.0	658.1	657.3	656.4	654.8	652.5	650.1	647.6	645.3	643.8
42.5°	632.3	631.6	630.8	630.1	629.3	627.8	625.4	623.1	620.7	618.2	616.9
45°	592.4	591.7	591.0	590.3	589.7	588.2	586.2	584.2	582.1	580.1	578.0
47.5°	549.4	549.4	549.5	549.5	549.5	548.3	545.8	543.4	541.0	538.5	536.4
50°	521.8	521.2	520.7	520.2	519.7	518.5	516.3	514.3	512.3	510.3	508.1
52.5°	493.5	493.1	492.8	492.4	492.0	490.7	488.6	486.4	484.2	482.0	480.1
55°	451.2	450.6	450.1	449.6	449.1	447.7	445.2	442.9	440.5	438.1	436.6
57.5°	406.5	406.3	406.0	405.7	405.5	404.2	402.2	400.2	398.2	396.3	394.3
60°	378.3	377.6	376.9	376.2	375.6	374.3	372.4	370.5	368.6	366.8	365.1
62.5°	348.8	348.3	347.7	347.2	346.6	345.6	344.0	342.3	340.7	339.1	337.3
65°	304.6	304.3	304.0	303.6	303.3	302.2	300.2	298.4	296.5	294.7	293.1
67.5°	261.8	261.1	260.3	259.6	258.9	257.9	256.5	255.1	253.7	252.3	251.0
70°	234.8	234.0	233.1	232.3	231.4	230.1	228.6	227.1	225.6	224.1	223.0
72.5°	205.3	204.7	204.2	203.6	203.0	202.2	201.3	200.3	199.2	198.2	197.1
75°	161.9	161.6	161.2	160.9	160.6	160.0	159.1	158.2	157.3	156.5	156.0
77.5°	121.9	121.7	121.6	121.4	121.3	121.0	120.5	120.1	119.6	119.1	118.8
80°	96.6	96.6	96.6	96.6	96.6	96.5	96.1	95.8	95.5	95.1	94.9
82.5°	74.6	74.3	74.0	73.7	73.5	73.3	73.2	73.2	73.1	73.0	72.7
85°	42.2	42.4	42.5	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.8
87.5°	16.8	17.0	17.3	17.5	17.8	18.0	18.1	18.2	18.3	18.4	18.5
90°	0.7	2.1	3.4	4.7	6.1	7.3	8.5	9.7	10.8	12.0	12.8
92.5°	11.5	10.6	9.7	8.7	7.8	7.9	8.9	9.9	10.9	12.0	12.8
95°	42.6	42.1	41.6	41.2	40.7	37.3	30.9	24.6	18.3	12.0	12.8
97.5°	89.1	90.0	90.9	91.7	92.6	86.8	74.3	61.8	49.3	36.9	32.1
100°	124.9	125.4	125.9	126.4	126.9	127.5	128.3	128.9	129.6	130.2	105.4
102.5°	161.5	162.1	162.8	163.4	164.0	164.5	164.9	165.3	165.7	166.1	161.5
105°	219.9	220.7	221.4	222.0	222.7	223.0	223.0	223.0	223.0	223.0	223.0
107.5°	280.7	280.7	280.7	280.7	280.7	280.9	281.2	281.6	282.0	282.3	282.3
110°	320.2	320.2	320.2	320.2	320.2	320.4	320.7	321.1	321.4	321.7	321.2



TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.4	357.8	358.2	358.6	359.0	359.3	359.5	359.7	359.9	360.1	359.4
115°	413.0	413.8	414.8	415.6	416.4	416.9	417.1	417.2	417.4	417.6	416.9
117.5°	470.7	470.6	470.6	470.6	470.5	470.8	471.5	472.1	472.7	473.3	472.5
120°	506.5	506.4	506.2	506.0	505.9	506.0	506.5	507.1	507.6	508.1	507.8
122.5°	538.3	539.0	539.6	540.2	540.9	541.3	541.5	541.7	542.0	542.2	541.9
125°	587.4	588.5	589.8	590.9	592.1	592.6	592.6	592.6	592.6	592.6	592.0
127.5°	634.2	635.1	635.9	636.7	637.5	637.9	637.8	637.7	637.6	637.5	637.1
130°	663.0	663.8	664.6	665.5	666.3	666.8	666.9	667.1	667.3	667.4	666.9
132.5°	691.7	692.7	693.7	694.6	695.6	695.9	695.5	695.1	694.8	694.4	694.3
135°	732.6	733.6	734.6	735.6	736.6	736.9	736.6	736.2	735.9	735.6	735.2
137.5°	770.1	771.0	771.8	772.7	773.6	773.9	773.6	773.3	773.0	772.6	772.7
140°	794.7	795.0	795.4	795.7	796.0	796.1	795.9	795.8	795.6	795.4	795.8
142.5°	816.8	817.0	817.2	817.4	817.6	817.8	818.1	818.3	818.5	818.8	818.8
145°	849.3	849.6	850.0	850.3	850.6	850.8	850.8	850.8	850.8	850.8	850.9
147.5°	877.8	877.7	877.6	877.6	877.5	877.6	877.8	877.9	878.1	878.3	878.5
150°	895.6	895.3	895.0	894.6	894.3	894.3	894.6	895.0	895.3	895.6	896.1
152.5°	913.0	912.3	911.6	910.9	910.1	909.9	910.3	910.6	910.9	911.2	911.6
155°	935.3	934.3	933.3	932.3	931.4	931.0	931.4	931.7	932.0	932.3	932.8
157.5°	952.5	952.0	951.4	950.8	950.2	949.9	949.9	950.0	950.0	950.0	950.6
160°	964.5	963.5	962.5	961.5	960.6	960.1	960.3	960.5	960.6	960.8	961.5
162.5°	974.1	973.1	972.1	971.1	970.1	969.7	969.9	970.1	970.2	970.4	971.3
165°	986.9	985.9	985.0	984.0	983.0	982.6	982.7	982.9	983.1	983.2	984.2
167.5°	996.5	995.5	994.5	993.5	992.4	992.0	992.2	992.3	992.5	992.7	993.8
170°	1002.0	1000.8	999.6	998.5	997.2	996.7	996.9	997.1	997.2	997.4	998.8
172.5°	1005.5	1004.4	1003.2	1002.0	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1002.8
175°	1009.5	1008.5	1007.4	1006.4	1005.4	1005.0	1005.2	1005.3	1005.5	1005.7	1007.0
177.5°	1011.2	1010.4	1009.7	1008.9	1008.0	1007.6	1007.8	1007.9	1008.0	1008.2	1009.2
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5



TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	969.9	969.9	969.9	969.9	969.9	969.9	969.9	969.9
2.5°	967.0	968.5	969.8	970.4	970.3	970.1	970.0	969.9
5°	962.2	963.7	965.2	965.9	965.7	965.6	965.4	965.2
7.5°	952.4	953.9	955.4	956.1	955.9	955.7	955.6	955.4
10°	944.2	945.5	947.0	947.6	947.4	947.2	947.0	946.8
12.5°	933.2	934.3	935.3	935.9	935.8	935.8	935.8	935.7
15°	914.0	914.8	915.7	916.1	916.1	916.1	916.1	916.1
17.5°	891.7	892.7	893.8	893.9	893.0	892.2	891.4	890.5
20°	874.7	876.0	877.2	877.4	876.5	875.7	874.7	873.9
22.5°	855.6	856.4	857.2	857.3	856.7	856.1	855.5	855.0
25°	824.8	825.1	825.5	825.4	824.9	824.4	823.8	823.3
27.5°	792.4	792.5	792.5	792.3	791.8	791.3	790.8	790.3
30°	768.9	768.6	768.2	767.8	767.3	766.8	766.3	765.8
32.5°	745.1	744.4	743.8	743.1	742.1	741.2	740.2	739.3
35°	708.0	707.2	706.3	705.2	703.9	702.5	701.1	699.7
37.5°	669.1	667.9	666.6	665.6	664.8	664.1	663.3	662.5
40°	642.2	640.7	639.1	638.1	637.6	637.1	636.6	636.1
42.5°	615.5	614.1	612.7	611.6	610.8	610.1	609.3	608.4
45°	575.9	573.9	571.9	570.6	570.1	569.6	569.1	568.6
47.5°	534.3	532.2	530.2	528.6	527.4	526.1	524.9	523.7
50°	505.8	503.6	501.4	499.7	498.5	497.3	496.0	494.9
52.5°	478.1	476.2	474.2	472.6	471.3	469.9	468.6	467.3
55°	435.0	433.5	432.0	430.6	429.4	428.2	427.1	425.9
57.5°	392.2	390.3	388.3	387.0	386.4	385.7	385.1	384.5
60°	363.3	361.6	359.9	358.5	357.3	356.1	354.9	353.8
62.5°	335.5	333.7	331.7	330.4	329.5	328.5	327.6	326.7
65°	291.5	290.0	288.5	287.4	286.7	286.0	285.4	284.7
67.5°	249.7	248.4	247.1	246.2	245.8	245.4	245.0	244.6
70°	222.0	221.0	219.9	219.1	218.4	217.7	217.0	216.4
72.5°	195.9	194.8	193.6	192.7	192.0	191.4	190.7	190.0
75°	155.5	155.0	154.5	153.9	153.2	152.5	151.9	151.2
77.5°	118.5	118.2	117.9	117.4	116.9	116.5	116.0	115.5
80°	94.8	94.6	94.4	94.2	93.8	93.5	93.2	92.8
82.5°	72.4	72.1	71.8	71.6	71.6	71.5	71.4	71.4
85°	42.6	42.4	42.3	42.0	41.7	41.3	41.0	40.7
87.5°	18.7	18.9	19.0	19.0	18.9	18.7	18.5	18.3
90°	13.6	14.4	15.2	16.0	16.5	17.0	17.5	18.0
92.5°	13.6	14.4	15.2	15.9	16.1	16.3	16.6	16.8
95°	13.6	14.4	15.2	15.8	15.8	15.8	15.8	15.8
97.5°	27.5	22.7	18.1	15.8	15.8	15.8	15.8	15.8
100°	80.7	55.8	31.1	18.4	17.7	17.1	16.4	15.8
102.5°	156.7	152.1	147.3	139.4	128.1	116.7	105.4	94.1
105°	223.0	223.0	223.0	222.9	222.8	222.6	222.4	222.3
107.5°	282.4	282.4	282.4	282.2	281.7	281.1	280.6	280.1
110°	320.7	320.2	319.7	319.6	319.7	319.9	320.1	320.2





TEST NUMBER: P333380-840

CATALOG NUMBER: S125DIW-S610D770U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.8	358.2	357.5	357.1	356.9	356.7	356.4	356.2
115°	416.2	415.6	414.9	414.0	413.0	412.0	411.0	410.0
117.5°	471.6	470.8	469.9	469.3	468.8	468.4	468.0	467.6
120°	507.5	507.1	506.8	506.1	505.3	504.5	503.7	502.8
122.5°	541.5	541.2	540.9	540.2	539.3	538.3	537.3	536.3
125°	591.3	590.7	590.0	589.4	588.9	588.3	587.9	587.4
127.5°	636.8	636.4	636.1	635.3	634.0	632.8	631.6	630.4
130°	666.5	666.0	665.5	664.8	664.0	663.2	662.3	661.5
132.5°	694.2	694.1	694.0	693.6	692.7	691.9	691.1	690.2
135°	734.9	734.6	734.3	733.6	732.6	731.5	730.5	729.5
137.5°	772.8	772.8	773.0	772.5	771.6	770.8	769.9	769.1
140°	796.1	796.4	796.8	796.4	795.4	794.5	793.5	792.4
142.5°	818.9	819.0	819.0	818.6	817.6	816.6	815.6	814.6
145°	851.1	851.3	851.4	851.0	850.0	849.0	848.1	847.1
147.5°	878.7	878.9	879.1	878.6	877.5	876.3	875.0	873.8
150°	896.4	896.7	897.1	896.6	895.1	893.8	892.5	891.2
152.5°	911.9	912.2	912.6	912.1	910.9	909.8	908.6	907.4
155°	933.3	933.8	934.3	933.9	932.6	931.3	930.0	928.6
157.5°	951.1	951.6	952.1	951.7	950.4	949.1	947.8	946.4
160°	962.1	962.8	963.4	963.1	961.8	960.5	959.2	957.8
162.5°	972.2	973.1	974.1	973.8	972.4	970.9	969.5	968.0
165°	985.2	986.2	987.2	987.0	985.7	984.4	983.1	981.7
167.5°	995.0	996.2	997.4	997.3	995.8	994.3	992.8	991.3
170°	1000.1	1001.5	1002.8	1002.7	1001.2	999.7	998.2	996.7
172.5°	1004.0	1005.2	1006.4	1006.2	1004.8	1003.3	1001.8	1000.3
175°	1008.4	1009.7	1011.0	1010.9	1009.5	1007.9	1006.4	1004.9
177.5°	1010.1	1011.0	1012.0	1011.9	1010.8	1009.8	1008.7	1007.6
180°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5

(END OF REPORT)