

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333368

Luminaire Tested: **S125DIW-S375D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333368
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7760.4 lumens
Efficiency: N/A
Efficacy: 145.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20				
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12				
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10				
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	46	39	33	51	41	35	30	32	27	24	22	20	17	14	12	11	8				
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	13	11	10	7				
8	49	38	30	25	43	34	27	23	26	21	18	19	16	13	12	10	9	6				
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5				
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3773	3773	3773
5°	3781	3745	3769
10°	3758	3719	3740
15°	3718	3674	3689
20°	3659	3612	3618
25°	3596	3537	3534
30°	3519	3457	3439
35°	3436	3370	3323
40°	3351	3277	3230
45°	3259	3191	3128
50°	3158	3088	2995
55°	3059	2971	2888
60°	2942	2853	2753
65°	2804	2713	2621
70°	2670	2549	2460
75°	2433	2353	2271
80°	2165	2131	2079
85°	1882	1919	1815



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	0.7
10°-20°	155.6	2.0
20°-30°	229.7	3.0
30°-40°	268.1	3.5
40°-50°	269.2	3.5
50°-60°	236.3	3.0
60°-70°	176.1	2.3
70°-80°	100.7	1.3
80°-90°	33.5	0.4
90°-100°	73.8	1.0
100°-110°	454.8	5.9
110°-120°	824.9	10.6
120°-130°	1058.6	13.6
130°-140°	1138.6	14.7
140°-150°	1068.8	13.8
150°-160°	864.5	11.1
160°-170°	559.1	7.2
170°-180°	192.9	2.5
0°-30°	440.4	5.7
0°-40°	708.5	9.1
0°-60°	1214.0	15.6
0°-90°	1524.3	19.6
90°-120°	1353.5	17.4
90°-150°	4619.5	59.5
90°-180°	6236.0	80.4
0°-180°	7760.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	583	582	578	582	581	55
15°	556	554	550	552	552	157
25°	505	502	496	497	496	232
35°	436	434	428	425	422	272
45°	357	355	349	344	342	275
55°	272	270	264	260	256	243
65°	184	182	178	173	172	182
75°	98	96	94	93	91	104
85°	25	26	26	25	24	28
90°	2	13	24	31	36	5
95°	86	78	24	31	32	109
105°	443	448	449	448	447	469
115°	831	838	840	834	825	823
125°	1182	1192	1192	1186	1182	1055
135°	1474	1482	1480	1476	1468	1136
145°	1709	1711	1712	1712	1704	1068
155°	1882	1873	1876	1879	1868	867
165°	1986	1977	1978	1986	1975	561
175°	2031	2022	2023	2034	2022	193
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	585.6	585.4	585.2	584.9	584.7	584.1	583.3	582.5	581.7	580.8	581.7
5°	583.2	583.0	582.8	582.6	582.4	581.8	580.8	579.8	578.7	577.7	578.6
7.5°	577.9	577.7	577.5	577.3	577.1	576.4	575.3	574.1	573.0	571.9	572.8
10°	573.1	572.9	572.7	572.5	572.3	571.6	570.5	569.3	568.2	567.1	567.9
12.5°	567.2	566.8	566.4	566.1	565.7	565.0	563.9	562.9	561.8	560.8	561.4
15°	556.0	555.7	555.4	555.1	554.7	554.0	552.9	551.8	550.6	549.5	550.0
17.5°	543.1	542.7	542.2	541.8	541.3	540.5	539.3	538.2	537.0	535.8	536.5
20°	532.4	532.2	532.0	531.8	531.6	530.8	529.5	528.1	526.8	525.5	526.2
22.5°	521.7	521.3	520.9	520.6	520.2	519.4	518.1	516.9	515.6	514.4	514.9
25°	504.7	504.2	503.6	503.1	502.6	501.7	500.4	499.0	497.7	496.4	496.6
27.5°	484.8	484.5	484.2	483.9	483.6	482.7	481.4	480.0	478.6	477.2	477.3
30°	471.9	471.6	471.2	470.9	470.6	469.7	468.2	466.6	465.1	463.5	463.3
32.5°	457.8	457.3	456.9	456.4	455.9	455.0	453.6	452.2	450.9	449.5	449.1
35°	435.8	435.4	435.0	434.6	434.2	433.2	431.8	430.4	428.9	427.5	427.0
37.5°	413.0	412.5	412.0	411.4	410.9	410.0	408.6	407.3	405.9	404.6	403.8
40°	397.5	396.9	396.4	395.9	395.4	394.4	393.0	391.6	390.1	388.7	387.8
42.5°	380.8	380.4	380.0	379.5	379.1	378.2	376.7	375.3	373.8	372.4	371.6
45°	356.8	356.4	356.0	355.6	355.1	354.3	353.1	351.9	350.6	349.4	348.2
47.5°	330.9	330.9	330.9	331.0	331.0	330.3	328.8	327.3	325.8	324.3	323.1
50°	314.3	314.0	313.7	313.3	313.0	312.3	311.0	309.8	308.6	307.3	306.0
52.5°	297.3	297.0	296.8	296.6	296.4	295.6	294.3	293.0	291.6	290.3	289.2
55°	271.7	271.4	271.1	270.8	270.5	269.6	268.2	266.8	265.3	263.9	263.0
57.5°	244.9	244.7	244.5	244.4	244.2	243.5	242.3	241.1	239.9	238.7	237.5
60°	227.8	227.4	227.0	226.6	226.2	225.4	224.3	223.2	222.0	220.9	219.9
62.5°	210.1	209.8	209.4	209.1	208.8	208.1	207.2	206.2	205.2	204.3	203.2
65°	183.5	183.3	183.1	182.9	182.7	182.0	180.9	179.7	178.6	177.5	176.5
67.5°	157.7	157.3	156.8	156.4	156.0	155.3	154.5	153.6	152.8	152.0	151.2
70°	141.4	140.9	140.4	139.9	139.4	138.6	137.7	136.8	135.9	135.0	134.3
72.5°	123.7	123.3	123.0	122.6	122.3	121.8	121.2	120.6	120.0	119.4	118.7
75°	97.5	97.3	97.1	96.9	96.7	96.3	95.8	95.3	94.8	94.3	94.0
77.5°	73.4	73.3	73.2	73.1	73.1	72.9	72.6	72.3	72.0	71.7	71.5
80°	58.2	58.2	58.2	58.2	58.2	58.1	57.9	57.7	57.5	57.3	57.2
82.5°	44.9	44.8	44.6	44.4	44.3	44.2	44.1	44.1	44.0	44.0	43.8
85°	25.4	25.5	25.6	25.7	25.8	25.9	25.9	25.9	25.9	25.9	25.8
87.5°	10.3	10.8	11.4	11.9	12.4	12.9	13.3	13.7	14.0	14.4	14.8
90°	1.5	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8
92.5°	23.2	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8
95°	85.8	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8
97.5°	179.1	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6
100°	251.4	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1
102.5°	324.9	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8
105°	442.6	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9
110°	644.3	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	719.0	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1
115°	831.0	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6
117.5°	946.9	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5
120°	1019.1	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5
122.5°	1083.0	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1
125°	1181.7	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9
127.5°	1275.9	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8
130°	1333.7	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8
132.5°	1391.5	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8
135°	1473.7	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1
137.5°	1549.3	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6
140°	1598.7	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9
142.5°	1643.2	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3
145°	1708.6	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9
147.5°	1765.8	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4
150°	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6
152.5°	1836.8	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9
155°	1881.7	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7
157.5°	1916.3	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3
160°	1940.4	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2
162.5°	1959.7	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0
165°	1985.6	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0
167.5°	2004.8	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4
170°	2015.7	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3
172.5°	2022.9	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5
175°	2030.7	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9
177.5°	2034.3	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	582.5	583.3	584.1	584.5	584.4	584.3	584.3	584.2
5°	579.5	580.5	581.4	581.8	581.7	581.6	581.5	581.4
7.5°	573.7	574.6	575.5	575.9	575.8	575.7	575.6	575.5
10°	568.7	569.5	570.4	570.7	570.6	570.5	570.4	570.3
12.5°	562.1	562.8	563.4	563.7	563.7	563.7	563.7	563.6
15°	550.5	551.0	551.6	551.8	551.8	551.8	551.8	551.8
17.5°	537.1	537.7	538.4	538.4	537.9	537.4	536.9	536.4
20°	526.9	527.6	528.3	528.5	527.9	527.4	526.9	526.4
22.5°	515.3	515.8	516.3	516.3	516.0	515.6	515.3	514.9
25°	496.8	497.0	497.2	497.1	496.8	496.5	496.2	495.9
27.5°	477.3	477.3	477.4	477.3	476.9	476.6	476.3	476.0
30°	463.1	462.9	462.7	462.5	462.2	461.9	461.5	461.2
32.5°	448.8	448.4	448.0	447.6	447.0	446.4	445.9	445.3
35°	426.5	426.0	425.4	424.8	424.0	423.1	422.3	421.5
37.5°	403.1	402.3	401.5	400.9	400.4	400.0	399.5	399.0
40°	386.8	385.9	385.0	384.4	384.1	383.7	383.4	383.1
42.5°	370.7	369.9	369.0	368.4	367.9	367.4	367.0	366.5
45°	346.9	345.7	344.5	343.7	343.4	343.1	342.8	342.5
47.5°	321.8	320.6	319.3	318.3	317.6	316.9	316.2	315.5
50°	304.7	303.3	302.0	301.0	300.2	299.5	298.8	298.1
52.5°	288.0	286.8	285.6	284.7	283.9	283.1	282.3	281.5
55°	262.0	261.1	260.2	259.4	258.7	257.9	257.2	256.5
57.5°	236.3	235.1	233.9	233.1	232.7	232.3	231.9	231.5
60°	218.9	217.8	216.8	215.9	215.2	214.5	213.8	213.1
62.5°	202.1	200.9	199.8	199.0	198.5	197.9	197.3	196.8
65°	175.6	174.7	173.8	173.1	172.7	172.3	171.9	171.5
67.5°	150.4	149.6	148.8	148.3	148.1	147.8	147.6	147.3
70°	133.7	133.1	132.5	132.0	131.6	131.2	130.7	130.3
72.5°	118.0	117.3	116.6	116.1	115.7	115.3	114.8	114.4
75°	93.7	93.4	93.0	92.7	92.3	91.9	91.5	91.0
77.5°	71.4	71.2	71.0	70.8	70.5	70.2	69.9	69.6
80°	57.1	57.0	56.9	56.7	56.5	56.3	56.1	55.9
82.5°	43.6	43.4	43.3	43.1	43.1	43.1	43.0	43.0
85°	25.7	25.6	25.5	25.3	25.1	24.9	24.7	24.5
87.5°	15.1	15.4	15.8	16.0	16.0	16.0	16.1	16.1
90°	27.4	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	27.4	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	27.4	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	55.2	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	162.2	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	315.3	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	645.3	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333368

CATALOG NUMBER: S125DIW-S375D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.8	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	837.3	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	948.8	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.8	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1089.4	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1189.6	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1281.1	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1340.8	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.6	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1478.4	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.7	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1601.5	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.4	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.3	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1767.8	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.2	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1834.6	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1877.7	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1913.3	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1935.5	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1955.9	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1982.0	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2001.8	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2012.0	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2019.9	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2028.5	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2032.1	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)