

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333422-840

Luminaire Tested: **S125DIW-S850D1340U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333422-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8869.9 lumens
Efficiency: N/A
Efficacy: 144.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.4
10°-20°	353.1	4.0
20°-30°	521.3	5.9
30°-40°	608.3	6.9
40°-50°	611.0	6.9
50°-60°	536.3	6.0
60°-70°	399.6	4.5
70°-80°	228.5	2.6
80°-90°	70.2	0.8
90°-100°	64.1	0.7
100°-110°	395.0	4.5
110°-120°	716.5	8.1
120°-130°	919.5	10.4
130°-140°	989.0	11.2
140°-150°	928.3	10.5
150°-160°	750.9	8.5
160°-170°	485.7	5.5
170°-180°	167.5	1.9
0°-30°	999.4	11.3
0°-40°	1607.8	18.1
0°-60°	2755.1	31.1
0°-90°	3453.4	38.9
90°-120°	1175.6	13.3
90°-150°	4012.4	45.2
90°-180°	5416.0	61.1
0°-180°	8869.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	12	21	27	31	6
95°	74	68	21	27	28	95
105°	384	389	390	390	388	408
115°	722	728	730	724	716	715
125°	1026	1035	1036	1030	1026	916
135°	1280	1287	1285	1282	1275	986
145°	1484	1486	1487	1487	1480	928
155°	1634	1627	1629	1632	1623	753
165°	1725	1717	1718	1725	1716	487
175°	1764	1757	1757	1767	1756	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.9	23.4	23.8	24.3	24.7	25.1	25.3	25.5	25.8	26.0	26.3
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4
92.5°	20.1	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4
95°	74.5	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4
97.5°	155.6	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1
100°	218.3	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2
102.5°	282.2	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1
105°	384.5	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2
110°	559.7	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	624.5	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0
115°	721.8	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4
117.5°	822.4	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7
120°	885.1	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3
122.5°	940.6	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8
125°	1026.4	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4
127.5°	1108.2	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4
130°	1158.4	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5
132.5°	1208.7	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3
135°	1280.1	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8
137.5°	1345.7	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3
140°	1388.6	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5
142.5°	1427.2	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8
145°	1484.0	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9
147.5°	1533.7	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1
150°	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7
152.5°	1595.4	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9
155°	1634.4	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0
157.5°	1664.5	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9
160°	1685.4	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0
162.5°	1702.1	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2
165°	1724.6	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8
167.5°	1741.3	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7
170°	1750.8	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2
172.5°	1757.1	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3
175°	1763.8	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6
177.5°	1767.0	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	26.6	26.9	27.2	27.2	27.0	26.8	26.7	26.5
90°	23.8	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	23.8	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	23.8	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	48.0	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	140.9	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	273.9	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.3	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	560.5	559.7	558.8	558.5	558.8	559.1	559.4	559.7



TEST NUMBER: P333422-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	626.9	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	727.3	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	824.2	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.7	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	946.2	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1033.2	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.8	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1164.6	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1213.0	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1284.1	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.4	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.1	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1430.9	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.2	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.5	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.3	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1593.5	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1630.9	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1661.9	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1681.2	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1698.8	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1721.5	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1738.8	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1747.6	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1754.4	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1761.9	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1765.0	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)