

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333346

Luminaire Tested: **S125DIW-S375D770U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333346
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D770U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4607.7 lumens
Efficiency: N/A
Efficacy: 151.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	29	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3516	3516	3516	3516
5°	4071	3528	3089	3528
10°	4737	3510	2706	3510
15°	5243	3484	2497	3484
20°	5869	3443	2328	3443
25°	6876	3397	2246	3397
30°	7427	3351	2175	3351
35°	6106	3266	2128	3266
40°	4340	3148	2076	3148
45°	3335	2988	2047	2988
50°	2846	2790	2043	2790
55°	2535	2597	2061	2597
60°	2286	2384	2113	2384
65°	2112	2172	2168	2172
70°	1920	1951	2200	1951
75°	1694	1719	2178	1719
80°	1428	1402	1993	1402
85°	1134	1008	1608	1008



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.1
10°-20°	156.0	3.4
20°-30°	253.4	5.5
30°-40°	309.1	6.7
40°-50°	281.2	6.1
50°-60°	224.0	4.9
60°-70°	156.0	3.4
70°-80°	83.2	1.8
80°-90°	23.1	0.5
90°-100°	36.3	0.8
100°-110°	223.9	4.9
110°-120°	406.0	8.8
120°-130°	521.1	11.3
130°-140°	560.5	12.2
140°-150°	526.1	11.4
150°-160°	425.5	9.2
160°-170°	275.2	6.0
170°-180°	94.9	2.1
0°-30°	461.8	10.0
0°-40°	770.9	16.7
0°-60°	1276.0	27.7
0°-90°	1538.3	33.4
90°-120°	666.2	14.5
90°-150°	2273.8	49.3
90°-180°	3069.0	66.6
0°-180°	4607.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	628	544	476	544	628	63
15°	784	521	373	521	784	224
25°	965	477	315	477	965	441
35°	774	414	270	414	774	474
45°	365	327	224	327	365	292
55°	225	231	183	231	225	203
65°	138	142	142	142	138	137
75°	68	69	87	69	68	73
85°	15	14	22	14	15	18
90°	18	1	18	1	18	8
95°	16	42	16	42	16	13
105°	220	218	220	218	220	199
115°	406	409	406	409	406	403
125°	582	582	582	582	582	517
135°	722	725	722	725	722	558
145°	839	841	839	841	839	524
155°	920	926	920	926	920	424
165°	972	977	972	977	972	274
175°	995	1000	995	1000	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	575.8	575.1	574.3	572.9	574.0	570.8	569.4	566.8	563.6	562.5	561.2
5°	628.0	629.2	630.4	625.5	626.0	622.7	615.3	609.3	604.5	598.2	593.8
7.5°	690.9	688.2	687.9	684.8	679.4	675.0	667.3	657.4	647.8	636.9	627.9
10°	722.3	722.6	720.5	716.8	711.0	706.8	696.7	687.0	675.2	661.3	651.4
12.5°	746.0	747.0	744.3	739.3	736.5	727.2	719.2	707.7	693.7	682.6	667.5
15°	784.2	781.7	779.9	773.6	768.8	759.1	746.4	734.3	719.1	705.0	690.9
17.5°	821.1	823.2	819.7	814.0	798.9	787.6	770.6	754.1	735.1	716.2	699.4
20°	854.0	855.9	850.6	840.6	822.6	811.3	788.9	767.6	745.7	721.4	702.9
22.5°	895.1	893.6	886.4	871.3	855.7	834.8	810.5	784.6	757.1	729.7	705.1
25°	964.9	955.2	950.8	932.1	911.6	880.8	847.6	809.7	775.5	739.2	707.8
27.5°	1003.7	1000.6	995.7	982.7	961.1	928.2	889.0	842.8	794.6	748.8	707.6
30°	995.9	996.4	996.8	992.7	978.8	954.1	915.0	865.4	808.0	756.5	708.9
32.5°	927.1	935.5	943.6	953.1	957.0	952.2	927.8	882.9	823.9	765.4	708.2
35°	774.5	777.1	803.2	829.1	864.2	891.5	909.7	889.8	840.2	772.9	707.3
37.5°	603.9	616.4	634.5	663.7	714.4	759.8	818.2	845.0	829.0	775.4	705.7
40°	514.8	526.4	538.2	568.0	610.7	665.7	732.0	788.6	801.8	767.6	700.1
42.5°	446.1	455.2	468.3	490.7	526.4	575.1	638.5	712.5	758.0	745.1	688.5
45°	365.1	370.9	381.0	398.8	424.7	462.8	518.7	599.6	670.1	693.4	660.9
47.5°	312.5	312.5	320.4	332.6	351.3	383.7	425.1	488.4	563.7	619.4	616.8
50°	283.3	282.1	288.4	299.0	313.8	335.3	374.8	425.4	497.7	560.8	578.4
52.5°	258.1	258.3	262.1	270.0	282.4	300.7	330.2	375.9	437.6	502.4	535.5
55°	225.1	224.1	228.5	233.8	242.9	254.9	276.1	311.0	361.2	424.9	467.9
57.5°	194.7	197.3	199.0	202.7	210.2	218.3	236.2	261.8	301.6	356.3	401.7
60°	177.0	179.5	180.9	184.6	190.6	197.6	211.4	232.2	265.7	312.9	357.9
62.5°	161.1	163.1	163.6	166.9	171.8	178.5	189.4	206.9	233.4	274.6	318.7
65°	138.2	138.2	139.1	142.6	144.9	150.9	159.2	171.9	193.2	225.3	263.0
67.5°	116.1	117.2	117.0	118.5	120.6	125.3	131.2	141.7	157.5	180.9	211.1
70°	101.7	102.6	102.4	103.5	105.8	108.8	113.7	123.6	134.9	155.0	180.9
72.5°	88.7	89.1	88.5	90.0	91.4	94.0	99.5	104.8	115.3	132.3	153.6
75°	67.9	68.4	68.9	69.8	71.2	72.6	75.3	80.6	87.6	100.3	113.9
77.5°	50.9	50.0	51.2	51.0	51.8	52.9	55.3	58.1	63.8	71.9	82.4
80°	38.4	38.6	38.6	38.8	40.0	40.7	42.7	44.8	49.2	55.2	62.6
82.5°	28.0	28.6	28.2	28.7	29.6	30.1	31.3	33.0	35.5	40.3	45.6
85°	15.3	14.1	14.6	15.0	15.0	15.3	16.2	16.9	18.3	20.1	22.2
87.5°	8.0	8.3	8.4	8.3	8.3	8.2	8.8	8.6	9.0	9.4	9.9
90°	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5	12.7	11.9	10.7
92.5°	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5	12.7	11.9	10.8
95°	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5	12.7	11.9	18.1
97.5°	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2	31.8	36.5	48.8
100°	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9	104.4	128.9	128.3
102.5°	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2	159.9	164.5	164.1
105°	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6	279.5	279.5	279.2
110°	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6	318.1	318.6	318.3



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3	355.9	356.6	356.4
115°	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1	412.8	413.5	413.3
117.5°	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0	467.9	468.7	468.1
120°	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5	502.8	503.1	502.6
122.5°	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2	536.6	536.9	536.7
125°	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5	586.2	586.8	586.8
127.5°	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6	630.9	631.3	631.4
130°	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0	660.4	660.9	660.8
132.5°	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4	687.5	687.6	688.0
135°	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7	728.0	728.4	728.7
137.5°	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3	765.2	765.1	765.4
140°	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3	788.0	787.6	787.8
142.5°	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9	810.8	810.8	810.5
145°	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8	842.6	842.5	842.5
147.5°	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1	869.9	869.7	869.5
150°	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6	887.3	886.9	886.6
152.5°	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0	902.7	902.3	902.0
155°	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2	923.7	923.2	922.9
157.5°	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8	941.3	940.7	940.7
160°	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7	952.1	951.4	951.2
162.5°	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7	961.8	960.9	960.7
165°	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6	974.6	973.6	973.5
167.5°	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3	984.1	983.0	982.8
170°	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3	989.0	987.7	987.5
172.5°	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2	993.0	991.9	991.6
175°	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5	997.2	995.9	995.7
177.5°	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2	999.3	998.4	998.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	560.1	558.8	557.3	554.7	551.6	549.9	547.4	545.7	542.4	539.6	536.6
5°	588.5	582.5	577.0	569.8	562.0	556.9	550.9	544.2	537.2	530.1	522.2
7.5°	618.0	607.3	595.8	583.4	571.2	560.0	549.3	538.9	529.1	517.2	507.2
10°	637.7	624.3	610.0	593.2	576.7	562.4	547.9	535.2	522.2	508.4	496.1
12.5°	657.5	639.7	619.4	600.9	581.2	563.9	546.8	530.5	514.3	498.9	484.6
15°	671.5	655.8	637.1	610.7	588.5	564.7	542.1	521.1	501.4	484.3	466.3
17.5°	680.7	660.4	640.3	615.1	586.0	559.4	533.7	509.6	487.5	465.8	448.5
20°	682.3	661.5	640.5	615.8	586.0	555.5	529.8	501.0	477.2	454.7	433.5
22.5°	681.8	658.2	635.3	609.9	580.8	552.7	521.7	492.3	466.4	444.4	422.2
25°	676.6	651.4	622.7	597.1	568.4	538.6	507.2	476.7	450.4	425.2	403.2
27.5°	672.2	639.6	607.1	577.2	549.5	522.2	492.1	460.9	431.7	406.2	385.5
30°	666.9	631.0	594.5	563.3	534.9	508.4	479.9	449.4	418.9	394.0	371.8
32.5°	662.1	620.3	581.8	547.8	517.7	491.9	465.7	436.7	406.7	381.4	359.2
35°	652.8	604.5	560.3	522.0	489.9	463.3	441.3	414.3	386.8	362.3	341.1
37.5°	641.0	583.7	536.3	496.1	460.9	432.9	412.5	391.7	365.3	341.7	322.5
40°	631.7	568.9	518.7	477.6	441.1	412.0	393.0	373.4	351.5	329.5	309.2
42.5°	620.1	555.6	501.0	456.7	420.6	392.2	372.3	355.7	336.3	315.8	297.0
45°	598.7	531.5	472.3	424.7	388.2	360.2	339.7	327.2	312.6	293.2	277.3
47.5°	567.2	502.5	441.3	392.2	354.5	328.6	309.3	297.3	287.1	272.7	258.2
50°	539.3	480.9	418.9	370.2	332.5	306.4	288.6	277.7	269.0	257.9	245.6
52.5°	508.1	453.7	396.9	348.7	311.4	285.7	268.3	258.7	251.4	243.5	231.4
55°	458.4	412.2	359.5	313.8	279.4	254.2	238.9	230.6	224.6	218.6	211.2
57.5°	403.8	367.6	321.0	279.1	247.4	224.5	210.3	202.2	197.5	194.4	190.1
60°	365.3	334.4	294.2	256.0	225.1	204.7	190.9	184.6	180.7	178.2	174.9
62.5°	329.6	304.2	267.0	232.2	205.1	185.9	173.5	167.4	163.7	162.4	159.8
65°	277.1	257.4	226.7	197.8	174.7	158.3	147.9	142.1	139.8	138.4	138.6
67.5°	225.2	213.3	188.6	164.0	145.5	131.8	123.4	119.0	117.8	116.0	116.0
70°	193.6	184.6	163.8	142.3	125.9	115.3	107.9	103.3	102.1	101.2	101.0
72.5°	165.7	157.8	139.8	122.6	107.8	98.5	92.4	89.6	87.7	87.2	87.1
75°	124.5	120.2	105.8	92.2	82.0	75.6	71.4	68.9	67.5	67.2	67.5
77.5°	88.5	84.7	75.6	65.9	59.5	54.6	51.1	50.2	48.7	48.7	48.5
80°	66.5	64.0	58.2	50.6	45.3	41.1	39.3	37.7	37.2	36.5	37.2
82.5°	48.2	45.5	41.6	36.7	32.3	29.9	28.0	27.5	27.2	26.9	27.0
85°	23.8	24.0	21.7	18.0	16.2	14.8	13.6	13.6	13.4	13.2	13.4
87.5°	10.0	9.4	8.5	7.7	6.5	5.7	5.2	5.1	4.8	4.9	5.4
90°	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4	10.5	9.6	8.6
95°	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2	41.7	41.2	40.8
97.5°	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2	89.1	90.0	90.8
100°	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7	124.2	124.7	125.2
102.5°	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9	160.5	161.2	161.8
105°	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8	218.5	219.2	219.8
107.5°	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0
110°	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9	354.3	354.7	355.1
115°	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0	409.8	410.7	411.5
117.5°	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1	466.0	466.0	466.0
120°	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6	501.5	501.3	501.1
122.5°	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0	533.7	534.3	534.9
125°	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7	582.8	584.0	585.1
127.5°	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0	628.9	629.7	630.5
130°	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5	657.3	658.1	659.0
132.5°	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9	685.9	686.9	687.8
135°	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4	726.4	727.4	728.4
137.5°	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6	763.5	764.3	765.2
140°	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9	787.2	787.6	787.9
142.5°	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8	809.0	809.2	809.4
145°	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0	841.3	841.7	842.0
147.5°	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2	869.1	869.0	869.0
150°	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	886.6	886.3	885.9
152.5°	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1	903.4	902.7	902.0
155°	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2	925.2	924.2	923.2
157.5°	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2	942.7	942.1	941.5
160°	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1	954.1	953.1	952.1
162.5°	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6	963.6	962.6	961.6
165°	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3	976.3	975.4	974.4
167.5°	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8	985.8	984.8	983.8
170°	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2	991.0	989.8	988.7
172.5°	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7	994.6	993.4	992.2
175°	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6	998.6	997.6	996.6
177.5°	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3	1000.5	999.8	999.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	535.0	532.9	531.3	527.6	525.5	522.8	520.6	523.0	520.4	521.5	519.8
5°	518.3	511.8	507.2	500.5	494.7	489.4	485.5	484.8	482.9	482.0	479.2
7.5°	498.2	490.1	482.2	473.4	466.0	458.5	453.7	449.7	447.1	443.6	441.2
10°	486.4	475.5	466.3	455.7	446.4	438.3	431.9	428.6	425.6	421.2	419.6
12.5°	471.8	460.6	449.3	437.9	429.0	420.0	414.5	409.6	407.5	402.6	402.1
15°	454.3	437.4	426.3	414.8	402.5	395.1	390.5	385.2	382.9	379.4	376.9
17.5°	433.4	418.3	404.5	392.5	382.0	375.8	370.0	366.4	362.4	360.1	356.0
20°	418.2	403.9	390.0	377.3	369.2	362.1	357.5	354.0	349.8	348.7	344.5
22.5°	405.5	389.7	376.4	365.7	356.9	348.8	343.8	341.4	338.6	335.0	334.2
25°	384.7	368.3	357.0	346.4	338.5	331.1	327.7	324.7	321.9	319.3	318.4
27.5°	366.8	352.1	338.7	329.1	322.2	315.5	312.5	308.8	306.8	304.7	302.2
30°	354.2	339.2	327.4	318.2	310.8	304.8	301.5	299.0	297.2	295.3	293.9
32.5°	341.3	327.4	316.0	306.9	299.5	295.0	292.1	290.3	288.3	286.1	284.3
35°	324.2	308.9	297.8	290.0	284.2	280.7	277.5	275.9	273.6	273.6	271.7
37.5°	304.9	291.7	281.9	274.8	269.6	266.5	263.0	261.9	260.4	259.4	258.8
40°	293.5	281.2	272.0	264.8	259.3	256.7	253.9	252.1	251.2	250.0	249.6
42.5°	281.6	269.9	261.1	254.5	249.6	247.5	244.9	243.6	241.7	240.2	239.9
45°	263.6	252.3	244.2	238.9	234.8	232.2	230.6	227.8	226.9	225.1	224.8
47.5°	246.6	235.7	227.8	223.4	219.8	217.7	215.2	212.4	211.3	210.4	210.3
50°	233.8	223.9	216.5	212.4	208.9	205.9	203.3	201.5	200.8	200.8	201.3
52.5°	220.9	212.4	206.2	201.1	197.8	194.6	192.2	191.1	190.1	191.2	192.0
55°	202.0	193.4	188.8	183.9	180.7	177.0	175.8	175.4	174.7	176.5	177.5
57.5°	181.9	175.9	170.5	165.7	162.8	160.6	159.1	158.8	160.1	161.0	164.0
60°	169.1	162.2	157.4	153.7	150.2	148.8	148.3	147.9	148.8	151.3	155.3
62.5°	155.1	149.5	144.2	141.5	138.9	136.6	136.5	136.8	138.6	141.6	145.5
65°	134.5	129.6	126.2	122.9	120.8	119.5	119.9	120.8	122.9	126.9	131.2
67.5°	113.5	110.2	107.1	104.5	102.5	102.5	103.0	104.4	106.8	111.3	115.3
70°	100.1	96.4	93.8	92.7	91.0	90.1	91.5	93.8	95.9	100.1	103.5
72.5°	86.6	83.4	81.4	80.6	79.9	79.2	79.7	82.2	85.0	89.1	93.2
75°	66.5	65.4	64.0	63.1	62.4	62.9	63.3	65.6	67.9	72.3	76.9
77.5°	48.6	47.4	46.5	46.3	45.9	46.2	47.5	49.2	51.4	54.6	58.1
80°	36.7	36.3	35.8	35.6	35.6	35.8	37.7	38.8	40.9	43.9	46.7
82.5°	26.8	26.5	26.4	26.3	26.5	26.6	27.7	29.2	30.9	33.2	35.6
85°	14.1	13.6	14.3	14.6	14.1	14.8	15.3	16.2	16.9	18.0	19.2
87.5°	5.8	6.4	6.5	6.9	7.1	7.7	7.7	8.6	9.2	9.7	9.6
90°	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5	14.3	15.1	15.8
92.5°	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5	14.3	15.1	15.7
95°	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5	14.3	15.1	15.6
97.5°	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2	22.5	17.9	15.6
100°	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9	55.3	30.8	18.2
102.5°	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2	150.6	145.9	138.0
105°	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.7
107.5°	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6	279.6	279.6	279.4
110°	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6	317.1	316.6	316.5



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3	354.7	354.0	353.6
115°	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1	411.5	410.8	410.0
117.5°	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0	466.2	465.3	464.7
120°	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5	502.1	501.8	501.2
122.5°	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2	535.9	535.6	534.9
125°	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5	584.9	584.2	583.6
127.5°	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6	630.2	629.9	629.1
130°	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0	659.5	659.0	658.3
132.5°	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4	687.3	687.2	686.8
135°	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7	727.4	727.1	726.4
137.5°	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3	765.3	765.4	765.0
140°	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3	788.6	789.0	788.6
142.5°	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9	811.0	811.0	810.6
145°	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8	843.0	843.1	842.7
147.5°	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1	870.3	870.5	870.0
150°	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6	887.9	888.3	887.8
152.5°	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0	903.3	903.7	903.2
155°	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2	924.7	925.2	924.8
157.5°	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8	942.3	942.8	942.4
160°	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7	953.4	954.0	953.7
162.5°	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7	963.6	964.6	964.3
165°	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6	976.6	977.6	977.4
167.5°	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3	986.5	987.7	987.6
170°	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3	991.7	993.0	992.9
172.5°	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2	995.4	996.6	996.4
175°	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5	999.8	1001.1	1001.0
177.5°	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2	1001.1	1002.1	1002.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	518.7	520.0	518.9	520.4	518.9	520.0	518.7	519.8	521.5	520.4	523.0
5°	478.1	476.0	477.4	476.5	477.4	476.0	478.1	479.2	482.0	482.9	484.8
7.5°	440.6	438.6	436.3	435.2	436.3	438.6	440.6	441.2	443.6	447.1	449.7
10°	417.1	414.5	414.3	412.7	414.3	414.5	417.1	419.6	421.2	425.6	428.6
12.5°	399.9	397.5	394.9	394.2	394.9	397.5	399.9	402.1	402.6	407.5	409.6
15°	375.5	373.6	372.0	373.4	372.0	373.6	375.5	376.9	379.4	382.9	385.2
17.5°	355.2	353.7	353.4	351.7	353.4	353.7	355.2	356.0	360.1	362.4	366.4
20°	342.4	341.3	341.8	338.7	341.8	341.3	342.4	344.5	348.7	349.8	354.0
22.5°	332.3	330.0	329.7	329.1	329.7	330.0	332.3	334.2	335.0	338.6	341.4
25°	316.3	315.2	314.0	315.2	314.0	315.2	316.3	318.4	319.3	321.9	324.7
27.5°	302.4	301.0	300.7	300.9	300.7	301.0	302.4	302.2	304.7	306.8	308.8
30°	293.9	291.6	291.8	291.6	291.8	291.6	293.9	293.9	295.3	297.2	299.0
32.5°	284.7	283.1	282.8	282.4	282.8	283.1	284.7	284.3	286.1	288.3	290.3
35°	271.0	271.0	269.9	269.9	269.9	271.0	271.0	271.7	273.6	273.6	275.9
37.5°	258.2	258.0	257.3	257.4	257.3	258.0	258.2	258.8	259.4	260.4	261.9
40°	248.6	248.4	247.7	246.3	247.7	248.4	248.6	249.6	250.0	251.2	252.1
42.5°	239.4	238.6	238.3	237.8	238.3	238.6	239.4	239.9	240.2	241.7	243.6
45°	224.8	224.8	224.4	224.1	224.4	224.8	224.8	224.8	225.1	226.9	227.8
47.5°	210.7	211.1	212.0	211.8	212.0	211.1	210.7	210.3	210.4	211.3	212.4
50°	202.2	202.4	203.1	203.3	203.1	202.4	202.2	201.3	200.8	200.8	201.5
52.5°	192.8	194.1	195.0	194.8	195.0	194.1	192.8	192.0	191.2	190.1	191.1
55°	179.5	181.2	182.8	183.0	182.8	181.2	179.5	177.5	176.5	174.7	175.4
57.5°	166.5	168.7	170.4	171.0	170.4	168.7	166.5	164.0	161.0	160.1	158.8
60°	157.6	160.6	162.7	163.6	162.7	160.6	157.6	155.3	151.3	148.8	147.9
62.5°	149.1	152.5	154.5	154.7	154.5	152.5	149.1	145.5	141.6	138.6	136.8
65°	135.2	138.6	140.5	141.9	140.5	138.6	135.2	131.2	126.9	122.9	120.8
67.5°	120.2	123.7	125.7	126.8	125.7	123.7	120.2	115.3	111.3	106.8	104.4
70°	109.3	112.8	115.5	116.5	115.5	112.8	109.3	103.5	100.1	95.9	93.8
72.5°	98.6	101.7	103.9	105.0	103.9	101.7	98.6	93.2	89.1	85.0	82.2
75°	79.9	84.1	86.2	87.3	86.2	84.1	79.9	76.9	72.3	67.9	65.6
77.5°	61.6	65.4	66.7	67.3	66.7	65.4	61.6	58.1	54.6	51.4	49.2
80°	49.4	51.8	53.4	53.6	53.4	51.8	49.4	46.7	43.9	40.9	38.8
82.5°	38.0	39.9	40.4	41.0	40.4	39.9	38.0	35.6	33.2	30.9	29.2
85°	20.8	21.7	22.0	21.7	22.0	21.7	20.8	19.2	18.0	16.9	16.2
87.5°	10.1	10.0	10.1	10.6	10.1	10.0	10.1	9.6	9.7	9.2	8.6
90°	16.3	16.8	17.3	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5
92.5°	15.9	16.1	16.4	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5
95°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5
97.5°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2
100°	17.5	16.9	16.2	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9
102.5°	126.8	115.6	104.4	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2
105°	220.6	220.4	220.2	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8
107.5°	278.9	278.4	277.9	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6
110°	316.6	316.8	317.0	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	353.4	353.2	352.9	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3
115°	409.0	408.0	407.0	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1
117.5°	464.2	463.8	463.4	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0
120°	500.4	499.6	498.8	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5
122.5°	534.0	533.0	532.1	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2
125°	583.1	582.6	582.2	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5
127.5°	627.8	626.6	625.4	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6
130°	657.5	656.7	655.8	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0
132.5°	685.9	685.1	684.3	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4
135°	725.4	724.4	723.4	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7
137.5°	764.1	763.3	762.4	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3
140°	787.6	786.7	785.7	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3
142.5°	809.6	808.6	807.6	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9
145°	841.7	840.7	839.8	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8
147.5°	868.9	867.7	866.5	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1
150°	886.4	885.1	883.8	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6
152.5°	902.0	900.9	899.7	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0
155°	923.5	922.2	920.9	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2
157.5°	941.1	939.8	938.5	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8
160°	952.4	951.1	949.8	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7
162.5°	962.9	961.4	960.0	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7
165°	976.1	974.8	973.5	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6
167.5°	986.1	984.6	983.1	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3
170°	991.4	989.9	988.4	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3
172.5°	995.0	993.5	992.0	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2
175°	999.6	998.1	996.6	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5
177.5°	1000.9	999.9	998.8	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	520.6	522.8	525.5	527.6	531.3	532.9	535.0	536.6	539.6	542.4	545.7
5°	485.5	489.4	494.7	500.5	507.2	511.8	518.3	522.2	530.1	537.2	544.2
7.5°	453.7	458.5	466.0	473.4	482.2	490.1	498.2	507.2	517.2	529.1	538.9
10°	431.9	438.3	446.4	455.7	466.3	475.5	486.4	496.1	508.4	522.2	535.2
12.5°	414.5	420.0	429.0	437.9	449.3	460.6	471.8	484.6	498.9	514.3	530.5
15°	390.5	395.1	402.5	414.8	426.3	437.4	454.3	466.3	484.3	501.4	521.1
17.5°	370.0	375.8	382.0	392.5	404.5	418.3	433.4	448.5	465.8	487.5	509.6
20°	357.5	362.1	369.2	377.3	390.0	403.9	418.2	433.5	454.7	477.2	501.0
22.5°	343.8	348.8	356.9	365.7	376.4	389.7	405.5	422.2	444.4	466.4	492.3
25°	327.7	331.1	338.5	346.4	357.0	368.3	384.7	403.2	425.2	450.4	476.7
27.5°	312.5	315.5	322.2	329.1	338.7	352.1	366.8	385.5	406.2	431.7	460.9
30°	301.5	304.8	310.8	318.2	327.4	339.2	354.2	371.8	394.0	418.9	449.4
32.5°	292.1	295.0	299.5	306.9	316.0	327.4	341.3	359.2	381.4	406.7	436.7
35°	277.5	280.7	284.2	290.0	297.8	308.9	324.2	341.1	362.3	386.8	414.3
37.5°	263.0	266.5	269.6	274.8	281.9	291.7	304.9	322.5	341.7	365.3	391.7
40°	253.9	256.7	259.3	264.8	272.0	281.2	293.5	309.2	329.5	351.5	373.4
42.5°	244.9	247.5	249.6	254.5	261.1	269.9	281.6	297.0	315.8	336.3	355.7
45°	230.6	232.2	234.8	238.9	244.2	252.3	263.6	277.3	293.2	312.6	327.2
47.5°	215.2	217.7	219.8	223.4	227.8	235.7	246.6	258.2	272.7	287.1	297.3
50°	203.3	205.9	208.9	212.4	216.5	223.9	233.8	245.6	257.9	269.0	277.7
52.5°	192.2	194.6	197.8	201.1	206.2	212.4	220.9	231.4	243.5	251.4	258.7
55°	175.8	177.0	180.7	183.9	188.8	193.4	202.0	211.2	218.6	224.6	230.6
57.5°	159.1	160.6	162.8	165.7	170.5	175.9	181.9	190.1	194.4	197.5	202.2
60°	148.3	148.8	150.2	153.7	157.4	162.2	169.1	174.9	178.2	180.7	184.6
62.5°	136.5	136.6	138.9	141.5	144.2	149.5	155.1	159.8	162.4	163.7	167.4
65°	119.9	119.5	120.8	122.9	126.2	129.6	134.5	138.6	138.4	139.8	142.1
67.5°	103.0	102.5	102.5	104.5	107.1	110.2	113.5	116.0	116.0	117.8	119.0
70°	91.5	90.1	91.0	92.7	93.8	96.4	100.1	101.0	101.2	102.1	103.3
72.5°	79.7	79.2	79.9	80.6	81.4	83.4	86.6	87.1	87.2	87.7	89.6
75°	63.3	62.9	62.4	63.1	64.0	65.4	66.5	67.5	67.2	67.5	68.9
77.5°	47.5	46.2	45.9	46.3	46.5	47.4	48.6	48.5	48.7	48.7	50.2
80°	37.7	35.8	35.6	35.6	35.8	36.3	36.7	37.2	36.5	37.2	37.7
82.5°	27.7	26.6	26.5	26.3	26.4	26.5	26.8	27.0	26.9	27.2	27.5
85°	15.3	14.8	14.1	14.6	14.3	13.6	14.1	13.4	13.2	13.4	13.6
87.5°	7.7	7.7	7.1	6.9	6.5	6.4	5.8	5.4	4.9	4.8	5.1
90°	12.7	11.9	10.7	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7
92.5°	12.7	11.9	10.8	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4
95°	12.7	11.9	18.1	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2
97.5°	31.8	36.5	48.8	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2
100°	104.4	128.9	128.3	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7
102.5°	159.9	164.5	164.1	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9
105°	220.8	220.8	220.8	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8
107.5°	279.5	279.5	279.2	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0
110°	318.1	318.6	318.3	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	355.9	356.6	356.4	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9
115°	412.8	413.5	413.3	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0
117.5°	467.9	468.7	468.1	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1
120°	502.8	503.1	502.6	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6
122.5°	536.6	536.9	536.7	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0
125°	586.2	586.8	586.8	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7
127.5°	630.9	631.3	631.4	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0
130°	660.4	660.9	660.8	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5
132.5°	687.5	687.6	688.0	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9
135°	728.0	728.4	728.7	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4
137.5°	765.2	765.1	765.4	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6
140°	788.0	787.6	787.8	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9
142.5°	810.8	810.8	810.5	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8
145°	842.6	842.5	842.5	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0
147.5°	869.9	869.7	869.5	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2
150°	887.3	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9
152.5°	902.7	902.3	902.0	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1
155°	923.7	923.2	922.9	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2
157.5°	941.3	940.7	940.7	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2
160°	952.1	951.4	951.2	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1
162.5°	961.8	960.9	960.7	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6
165°	974.6	973.6	973.5	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3
167.5°	984.1	983.0	982.8	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8
170°	989.0	987.7	987.5	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2
172.5°	993.0	991.9	991.6	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7
175°	997.2	995.9	995.7	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6
177.5°	999.3	998.4	998.2	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	547.4	549.9	551.6	554.7	557.3	558.8	560.1	561.2	562.5	563.6	566.8
5°	550.9	556.9	562.0	569.8	577.0	582.5	588.5	593.8	598.2	604.5	609.3
7.5°	549.3	560.0	571.2	583.4	595.8	607.3	618.0	627.9	636.9	647.8	657.4
10°	547.9	562.4	576.7	593.2	610.0	624.3	637.7	651.4	661.3	675.2	687.0
12.5°	546.8	563.9	581.2	600.9	619.4	639.7	657.5	667.5	682.6	693.7	707.7
15°	542.1	564.7	588.5	610.7	637.1	655.8	671.5	690.9	705.0	719.1	734.3
17.5°	533.7	559.4	586.0	615.1	640.3	660.4	680.7	699.4	716.2	735.1	754.1
20°	529.8	555.5	586.0	615.8	640.5	661.5	682.3	702.9	721.4	745.7	767.6
22.5°	521.7	552.7	580.8	609.9	635.3	658.2	681.8	705.1	729.7	757.1	784.6
25°	507.2	538.6	568.4	597.1	622.7	651.4	676.6	707.8	739.2	775.5	809.7
27.5°	492.1	522.2	549.5	577.2	607.1	639.6	672.2	707.6	748.8	794.6	842.8
30°	479.9	508.4	534.9	563.3	594.5	631.0	666.9	708.9	756.5	808.0	865.4
32.5°	465.7	491.9	517.7	547.8	581.8	620.3	662.1	708.2	765.4	823.9	882.9
35°	441.3	463.3	489.9	522.0	560.3	604.5	652.8	707.3	772.9	840.2	889.8
37.5°	412.5	432.9	460.9	496.1	536.3	583.7	641.0	705.7	775.4	829.0	845.0
40°	393.0	412.0	441.1	477.6	518.7	568.9	631.7	700.1	767.6	801.8	788.6
42.5°	372.3	392.2	420.6	456.7	501.0	555.6	620.1	688.5	745.1	758.0	712.5
45°	339.7	360.2	388.2	424.7	472.3	531.5	598.7	660.9	693.4	670.1	599.6
47.5°	309.3	328.6	354.5	392.2	441.3	502.5	567.2	616.8	619.4	563.7	488.4
50°	288.6	306.4	332.5	370.2	418.9	480.9	539.3	578.4	560.8	497.7	425.4
52.5°	268.3	285.7	311.4	348.7	396.9	453.7	508.1	535.5	502.4	437.6	375.9
55°	238.9	254.2	279.4	313.8	359.5	412.2	458.4	467.9	424.9	361.2	311.0
57.5°	210.3	224.5	247.4	279.1	321.0	367.6	403.8	401.7	356.3	301.6	261.8
60°	190.9	204.7	225.1	256.0	294.2	334.4	365.3	357.9	312.9	265.7	232.2
62.5°	173.5	185.9	205.1	232.2	267.0	304.2	329.6	318.7	274.6	233.4	206.9
65°	147.9	158.3	174.7	197.8	226.7	257.4	277.1	263.0	225.3	193.2	171.9
67.5°	123.4	131.8	145.5	164.0	188.6	213.3	225.2	211.1	180.9	157.5	141.7
70°	107.9	115.3	125.9	142.3	163.8	184.6	193.6	180.9	155.0	134.9	123.6
72.5°	92.4	98.5	107.8	122.6	139.8	157.8	165.7	153.6	132.3	115.3	104.8
75°	71.4	75.6	82.0	92.2	105.8	120.2	124.5	113.9	100.3	87.6	80.6
77.5°	51.1	54.6	59.5	65.9	75.6	84.7	88.5	82.4	71.9	63.8	58.1
80°	39.3	41.1	45.3	50.6	58.2	64.0	66.5	62.6	55.2	49.2	44.8
82.5°	28.0	29.9	32.3	36.7	41.6	45.5	48.2	45.6	40.3	35.5	33.0
85°	13.6	14.8	16.2	18.0	21.7	24.0	23.8	22.2	20.1	18.3	16.9
87.5°	5.2	5.7	6.5	7.7	8.5	9.4	10.0	9.9	9.4	9.0	8.6
90°	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5
92.5°	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5
95°	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5
97.5°	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2
100°	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9
102.5°	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2
105°	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6
110°	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3
115°	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1
117.5°	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0
120°	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5
122.5°	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2
125°	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5
127.5°	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6
130°	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0
132.5°	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4
135°	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7
137.5°	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3
140°	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3
142.5°	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9
145°	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8
147.5°	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1
150°	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6
152.5°	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0
155°	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2
157.5°	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8
160°	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7
162.5°	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7
165°	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6
167.5°	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3
170°	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3
172.5°	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2
175°	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5
177.5°	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.4	544.4	544.4	544.4	544.4	544.4	544.4
2.5°	569.4	570.8	574.0	572.9	574.3	575.1	575.8
5°	615.3	622.7	626.0	625.5	630.4	629.2	628.0
7.5°	667.3	675.0	679.4	684.8	687.9	688.2	690.9
10°	696.7	706.8	711.0	716.8	720.5	722.6	722.3
12.5°	719.2	727.2	736.5	739.3	744.3	747.0	746.0
15°	746.4	759.1	768.8	773.6	779.9	781.7	784.2
17.5°	770.6	787.6	798.9	814.0	819.7	823.2	821.1
20°	788.9	811.3	822.6	840.6	850.6	855.9	854.0
22.5°	810.5	834.8	855.7	871.3	886.4	893.6	895.1
25°	847.6	880.8	911.6	932.1	950.8	955.2	964.9
27.5°	889.0	928.2	961.1	982.7	995.7	1000.6	1003.7
30°	915.0	954.1	978.8	992.7	996.8	996.4	995.9
32.5°	927.8	952.2	957.0	953.1	943.6	935.5	927.1
35°	909.7	891.5	864.2	829.1	803.2	777.1	774.5
37.5°	818.2	759.8	714.4	663.7	634.5	616.4	603.9
40°	732.0	665.7	610.7	568.0	538.2	526.4	514.8
42.5°	638.5	575.1	526.4	490.7	468.3	455.2	446.1
45°	518.7	462.8	424.7	398.8	381.0	370.9	365.1
47.5°	425.1	383.7	351.3	332.6	320.4	312.5	312.5
50°	374.8	335.3	313.8	299.0	288.4	282.1	283.3
52.5°	330.2	300.7	282.4	270.0	262.1	258.3	258.1
55°	276.1	254.9	242.9	233.8	228.5	224.1	225.1
57.5°	236.2	218.3	210.2	202.7	199.0	197.3	194.7
60°	211.4	197.6	190.6	184.6	180.9	179.5	177.0
62.5°	189.4	178.5	171.8	166.9	163.6	163.1	161.1
65°	159.2	150.9	144.9	142.6	139.1	138.2	138.2
67.5°	131.2	125.3	120.6	118.5	117.0	117.2	116.1
70°	113.7	108.8	105.8	103.5	102.4	102.6	101.7
72.5°	99.5	94.0	91.4	90.0	88.5	89.1	88.7
75°	75.3	72.6	71.2	69.8	68.9	68.4	67.9
77.5°	55.3	52.9	51.8	51.0	51.2	50.0	50.9
80°	42.7	40.7	40.0	38.8	38.6	38.6	38.4
82.5°	31.3	30.1	29.6	28.7	28.2	28.6	28.0
85°	16.2	15.3	15.0	15.0	14.6	14.1	15.3
87.5°	8.8	8.2	8.3	8.3	8.4	8.3	8.0
90°	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.1	316.6	316.5	316.6	316.8	317.0	317.1



TEST NUMBER: P333346

CATALOG NUMBER: S125DIW-S375D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)