

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333423-840

Luminaire Tested: **S125DIW-S850D1340U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333423-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1340U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8150.5 lumens  
Efficiency: N/A  
Efficacy: 132.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	31	27	27	24	22	19
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	19	16
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8561	8561	8561
5°	8581	8499	8554
10°	8529	8439	8487
15°	8436	8338	8372
20°	8304	8195	8210
25°	8161	8027	8020
30°	7986	7845	7806
35°	7798	7649	7541
40°	7605	7436	7331
45°	7395	7242	7099
50°	7166	7007	6797
55°	6944	6742	6554
60°	6679	6475	6245
65°	6363	6154	5946
70°	6060	5784	5586
75°	5522	5340	5155
80°	4917	4839	4720
85°	4276	4357	4113



TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	1.5
10°-20°	353.1	4.3
20°-30°	521.3	6.4
30°-40°	608.3	7.5
40°-50°	611.0	7.5
50°-60°	536.3	6.6
60°-70°	399.6	4.9
70°-80°	228.5	2.8
80°-90°	70.2	0.9
90°-100°	112.7	1.4
100°-110°	332.9	4.1
110°-120°	563.9	6.9
120°-130°	742.1	9.1
130°-140°	831.6	10.2
140°-150°	815.0	10.0
150°-160°	684.5	8.4
160°-170°	455.0	5.6
170°-180°	159.2	2.0
0°-30°	999.4	12.3
0°-40°	1607.8	19.7
0°-60°	2755.1	33.8
0°-90°	3453.4	42.4
90°-120°	1009.6	12.4
90°-150°	3398.3	41.7
90°-180°	4697.0	57.6
0°-180°	8150.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1324	1321	1311	1320	1319	125
15°	1262	1258	1247	1252	1252	355
25°	1145	1140	1126	1128	1125	527
35°	989	984	970	965	956	618
45°	810	805	793	781	777	624
55°	617	613	599	590	582	550
65°	416	414	403	394	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	64
90°	1	12	21	27	31	8
95°	85	88	101	110	113	91
105°	299	305	313	321	325	319
115°	565	570	572	571	570	558
125°	824	831	833	831	829	738
135°	1072	1079	1081	1080	1076	826
145°	1298	1303	1307	1307	1303	811
155°	1486	1486	1487	1491	1486	684
165°	1615	1613	1614	1618	1611	455
175°	1679	1674	1674	1681	1673	160
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1329.1	1328.5	1328.0	1327.4	1326.8	1325.5	1323.7	1321.9	1320.0	1318.2	1320.0
5°	1323.6	1323.1	1322.6	1322.2	1321.7	1320.3	1318.0	1315.7	1313.3	1311.0	1313.1
7.5°	1311.4	1311.0	1310.5	1310.0	1309.6	1308.1	1305.5	1302.9	1300.4	1297.8	1299.8
10°	1300.5	1300.1	1299.6	1299.1	1298.7	1297.2	1294.5	1292.0	1289.5	1286.9	1288.8
12.5°	1287.1	1286.3	1285.5	1284.5	1283.7	1282.1	1279.8	1277.4	1275.0	1272.6	1274.1
15°	1261.7	1261.0	1260.3	1259.6	1258.9	1257.3	1254.8	1252.1	1249.6	1247.0	1248.2
17.5°	1232.5	1231.5	1230.5	1229.5	1228.5	1226.6	1224.0	1221.3	1218.6	1216.0	1217.4
20°	1208.2	1207.8	1207.3	1206.8	1206.4	1204.6	1201.5	1198.5	1195.5	1192.4	1194.2
22.5°	1183.9	1183.1	1182.2	1181.3	1180.5	1178.7	1175.9	1173.0	1170.1	1167.3	1168.4
25°	1145.3	1144.2	1143.0	1141.8	1140.6	1138.5	1135.5	1132.5	1129.4	1126.4	1126.9
27.5°	1100.1	1099.5	1098.8	1098.1	1097.4	1095.5	1092.4	1089.2	1086.1	1083.0	1083.1
30°	1070.9	1070.2	1069.4	1068.7	1068.0	1065.9	1062.5	1058.9	1055.4	1052.0	1051.5
32.5°	1038.9	1037.8	1036.8	1035.7	1034.7	1032.6	1029.5	1026.3	1023.2	1020.1	1019.3
35°	989.1	988.1	987.1	986.2	985.3	983.2	980.0	976.6	973.4	970.2	969.0
37.5°	937.3	936.0	934.8	933.7	932.5	930.4	927.4	924.2	921.2	918.2	916.4
40°	902.0	900.8	899.7	898.5	897.3	895.1	891.8	888.6	885.3	882.0	880.0
42.5°	864.2	863.2	862.2	861.3	860.3	858.2	855.0	851.6	848.4	845.2	843.2
45°	809.7	808.7	807.8	806.9	806.0	804.1	801.3	798.5	795.7	792.9	790.1
47.5°	750.9	751.0	751.0	751.0	751.1	749.5	746.1	742.8	739.4	736.1	733.2
50°	713.2	712.5	711.8	711.0	710.4	708.6	705.9	703.1	700.2	697.4	694.4
52.5°	674.6	674.1	673.6	673.1	672.6	670.8	667.8	664.8	661.9	658.8	656.2
55°	616.7	616.0	615.3	614.6	613.9	611.9	608.6	605.4	602.1	598.8	596.7
57.5°	555.6	555.3	554.9	554.5	554.2	552.6	549.9	547.1	544.3	541.6	538.9
60°	517.1	516.1	515.2	514.2	513.3	511.6	509.0	506.4	503.9	501.3	499.0
62.5°	476.8	476.1	475.3	474.5	473.8	472.3	470.2	468.0	465.7	463.5	461.1
65°	416.4	415.9	415.5	415.0	414.5	413.0	410.4	407.9	405.3	402.7	400.6
67.5°	357.9	356.9	355.9	354.9	354.0	352.4	350.6	348.7	346.8	344.9	343.1
70°	320.9	319.7	318.6	317.4	316.3	314.7	312.6	310.4	308.3	306.3	304.9
72.5°	280.6	279.8	279.0	278.3	277.5	276.4	275.1	273.7	272.4	271.0	269.4
75°	221.3	220.9	220.4	219.9	219.4	218.6	217.4	216.3	215.1	214.0	213.3
77.5°	166.5	166.3	166.2	166.0	165.8	165.4	164.7	164.1	163.4	162.8	162.4
80°	132.2	132.2	132.2	132.2	132.2	131.9	131.5	131.0	130.5	130.1	129.9
82.5°	101.9	101.6	101.2	100.8	100.5	100.2	100.1	100.1	100.0	99.9	99.5
85°	57.7	58.0	58.2	58.4	58.6	58.8	58.8	58.8	58.8	58.8	58.5
87.5°	22.9	23.4	23.8	24.3	24.7	25.1	25.3	25.5	25.8	26.1	26.3
90°	1.3	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4
92.5°	31.7	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2
95°	85.1	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9
97.5°	141.5	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5
100°	183.4	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1
102.5°	228.4	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2
105°	298.7	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9
107.5°	376.2	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7
110°	429.7	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0



TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.1	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9
115°	564.6	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2
117.5°	645.3	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3
120°	695.6	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5
122.5°	750.1	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6
125°	823.9	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5
127.5°	902.5	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3
130°	949.7	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6
132.5°	996.8	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8
135°	1071.6	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8
137.5°	1141.8	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6
140°	1186.8	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9
142.5°	1231.9	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7
145°	1298.2	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4
147.5°	1359.5	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2
150°	1400.4	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3
152.5°	1433.9	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6
155°	1485.5	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9
157.5°	1531.6	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2
160°	1558.8	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4
162.5°	1583.0	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8
165°	1615.2	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1
167.5°	1642.4	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9
170°	1657.1	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7
172.5°	1667.6	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1
175°	1679.4	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9
177.5°	1685.4	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6	1325.6
2.5°	1321.9	1323.7	1325.5	1326.5	1326.3	1326.1	1325.9	1325.6
5°	1315.2	1317.3	1319.4	1320.3	1320.1	1319.9	1319.6	1319.4
7.5°	1301.9	1303.9	1306.0	1306.9	1306.7	1306.5	1306.2	1306.0
10°	1290.6	1292.5	1294.3	1295.2	1294.9	1294.6	1294.4	1294.2
12.5°	1275.6	1277.1	1278.6	1279.3	1279.3	1279.2	1279.2	1279.1
15°	1249.4	1250.5	1251.7	1252.2	1252.2	1252.2	1252.2	1252.2
17.5°	1218.9	1220.3	1221.7	1221.9	1220.7	1219.6	1218.4	1217.3
20°	1195.8	1197.4	1199.0	1199.2	1198.1	1196.9	1195.8	1194.6
22.5°	1169.4	1170.5	1171.6	1171.7	1170.9	1170.1	1169.3	1168.6
25°	1127.3	1127.8	1128.3	1128.1	1127.5	1126.8	1126.1	1125.4
27.5°	1083.2	1083.3	1083.4	1083.1	1082.4	1081.7	1081.0	1080.3
30°	1051.1	1050.6	1050.1	1049.6	1048.8	1048.1	1047.4	1046.7
32.5°	1018.3	1017.5	1016.7	1015.6	1014.4	1013.1	1011.9	1010.7
35°	967.9	966.6	965.5	964.0	962.1	960.3	958.4	956.5
37.5°	914.6	912.9	911.2	909.8	908.8	907.7	906.7	905.5
40°	877.9	875.8	873.6	872.2	871.5	870.9	870.2	869.5
42.5°	841.3	839.4	837.5	836.0	835.0	833.8	832.7	831.7
45°	787.3	784.5	781.7	779.9	779.3	778.6	777.9	777.2
47.5°	730.3	727.5	724.7	722.5	720.8	719.2	717.5	715.9
50°	691.4	688.3	685.3	683.0	681.4	679.7	678.1	676.5
52.5°	653.6	650.9	648.2	646.0	644.2	642.4	640.6	638.7
55°	594.7	592.6	590.5	588.7	586.9	585.3	583.7	582.1
57.5°	536.2	533.5	530.8	529.0	528.1	527.3	526.3	525.4
60°	496.7	494.3	492.0	490.0	488.4	486.8	485.1	483.5
62.5°	458.6	456.1	453.5	451.6	450.4	449.1	447.9	446.6
65°	398.6	396.5	394.4	392.8	391.9	391.0	390.0	389.1
67.5°	341.3	339.5	337.8	336.6	336.1	335.5	334.9	334.4
70°	303.5	302.1	300.6	299.5	298.5	297.6	296.7	295.8
72.5°	267.8	266.3	264.7	263.4	262.5	261.6	260.6	259.6
75°	212.6	211.9	211.2	210.4	209.4	208.4	207.5	206.6
77.5°	162.0	161.5	161.1	160.6	159.9	159.3	158.6	157.9
80°	129.6	129.4	129.2	128.8	128.4	127.8	127.3	126.9
82.5°	99.0	98.6	98.2	98.0	97.9	97.8	97.7	97.6
85°	58.3	58.1	57.8	57.5	57.0	56.6	56.0	55.5
87.5°	26.6	26.9	27.2	27.3	27.1	26.9	26.7	26.5
90°	23.8	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	54.1	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	104.9	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	164.4	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	205.7	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	248.0	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	316.6	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	390.5	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	441.9	442.7	443.6	443.9	443.6	443.3	443.0	442.7





TEST NUMBER: P333423-840

CATALOG NUMBER: S125DIW-S850D1340U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	493.3	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.9	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.5	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.4	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.9	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	908.0	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.3	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.5	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.0	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1198.5	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.0	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1366.9	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.2	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1489.1	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1532.4	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1558.5	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1583.2	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1616.2	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1640.7	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1655.4	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1665.9	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1677.6	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1682.9	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)