

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333425-840

Luminaire Tested: **S125DIW-S850D1560U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333425-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1560U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8951.6 lumens  
Efficiency: N/A  
Efficacy: 131.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	26	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7979	7979	7979	7979
5°	9240	8006	7010	8006
10°	10750	7965	6142	7965
15°	11900	7906	5666	7906
20°	13320	7813	5283	7813
25°	15605	7709	5097	7709
30°	16855	7607	4935	7607
35°	13858	7413	4829	7413
40°	9850	7144	4713	7144
45°	7567	6783	4646	6783
50°	6459	6333	4636	6333
55°	5751	5892	4677	5892
60°	5187	5412	4795	5412
65°	4792	4927	4919	4927
70°	4358	4426	4991	4426
75°	3848	3898	4946	3898
80°	3239	3176	4526	3176
85°	2564	2290	3653	2290



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	1.3
10°-20°	354.1	4.0
20°-30°	575.0	6.4
30°-40°	701.4	7.8
40°-50°	638.1	7.1
50°-60°	508.2	5.7
60°-70°	354.0	4.0
70°-80°	188.8	2.1
80°-90°	51.9	0.6
90°-100°	131.1	1.5
100°-110°	387.1	4.3
110°-120°	655.6	7.3
120°-130°	862.9	9.6
130°-140°	966.8	10.8
140°-150°	947.6	10.6
150°-160°	795.9	8.9
160°-170°	529.1	5.9
170°-180°	185.2	2.1
0°-30°	1048.1	11.7
0°-40°	1749.5	19.5
0°-60°	2895.8	32.3
0°-90°	3490.4	39.0
90°-120°	1173.8	13.1
90°-150°	3951.1	44.1
90°-180°	5461.0	61.0
0°-180°	8951.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1236	1236	1236	1236	1236	
5°	1425	1235	1081	1235	1425	144
15°	1780	1182	847	1182	1780	509
25°	2190	1082	715	1082	2190	1000
35°	1758	940	612	940	1758	1076
45°	828	743	509	743	828	663
55°	511	523	415	523	511	460
65°	314	322	322	322	314	311
75°	154	156	198	156	154	166
85°	35	31	49	31	35	41
90°	37	2	37	2	37	22
95°	131	99	131	99	131	133
105°	378	347	378	347	378	400
115°	663	656	663	656	663	655
125°	964	958	964	958	964	861
135°	1250	1246	1250	1246	1250	965
145°	1515	1509	1515	1509	1515	946
155°	1727	1727	1727	1727	1727	795
165°	1873	1878	1873	1878	1873	528
175°	1945	1953	1945	1953	1945	185
180°	1957	1957	1957	1957	1957	



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1306.8	1305.0	1303.4	1300.0	1302.5	1295.5	1292.0	1286.2	1279.1	1276.6	1273.6
5°	1425.2	1427.8	1430.5	1419.5	1420.6	1413.2	1396.4	1382.8	1371.8	1357.7	1347.7
7.5°	1567.9	1561.7	1561.2	1554.1	1541.8	1532.0	1514.3	1491.9	1470.2	1445.4	1424.9
10°	1639.2	1639.7	1635.0	1626.6	1613.6	1604.1	1581.0	1558.9	1532.3	1500.8	1478.2
12.5°	1692.9	1695.1	1689.1	1677.8	1671.4	1650.2	1632.1	1606.0	1574.2	1549.0	1514.7
15°	1779.8	1773.9	1769.8	1755.7	1744.6	1722.6	1693.7	1666.5	1631.8	1599.8	1567.9
17.5°	1863.4	1868.0	1860.2	1847.2	1813.1	1787.4	1748.7	1711.3	1668.3	1625.4	1587.2
20°	1938.1	1942.3	1930.3	1907.7	1866.8	1841.1	1790.2	1742.0	1692.1	1637.1	1595.2
22.5°	2031.2	2027.9	2011.7	1977.3	1941.9	1894.4	1839.3	1780.6	1718.2	1656.0	1600.2
25°	2189.8	2167.8	2157.8	2115.4	2068.7	1998.9	1923.4	1837.4	1759.8	1677.5	1606.2
27.5°	2277.6	2270.8	2259.7	2230.1	2181.0	2106.5	2017.4	1912.6	1803.1	1699.2	1605.9
30°	2260.1	2261.1	2262.2	2252.7	2221.3	2165.2	2076.6	1963.8	1833.7	1716.8	1608.8
32.5°	2104.1	2123.1	2141.3	2162.9	2171.7	2161.0	2105.5	2003.7	1869.9	1737.0	1607.1
35°	1757.7	1763.5	1822.7	1881.5	1961.2	2023.1	2064.5	2019.4	1906.6	1754.0	1605.1
37.5°	1370.5	1398.9	1439.9	1506.2	1621.2	1724.2	1856.7	1917.6	1881.3	1759.6	1601.4
40°	1168.3	1194.6	1221.2	1288.9	1385.9	1510.8	1661.2	1789.7	1819.6	1742.0	1588.8
42.5°	1012.3	1033.0	1062.7	1113.6	1194.7	1305.1	1449.0	1616.9	1720.2	1690.8	1562.5
45°	828.5	841.6	864.7	905.0	963.8	1050.4	1177.2	1360.8	1520.7	1573.7	1499.8
47.5°	709.1	709.0	727.0	754.9	797.3	870.8	964.6	1108.4	1279.3	1405.6	1399.8
50°	642.9	640.3	654.4	678.5	712.1	760.8	850.5	965.3	1129.5	1272.6	1312.5
52.5°	585.8	586.1	594.8	612.7	640.8	682.5	749.4	852.9	993.2	1140.1	1215.2
55°	510.8	508.7	518.6	530.7	551.1	578.3	626.6	705.8	819.6	964.3	1061.9
57.5°	441.9	447.7	451.7	460.1	477.1	495.3	536.0	594.1	684.4	808.6	911.7
60°	401.6	407.5	410.6	419.0	432.6	448.4	479.8	527.0	603.0	710.0	812.2
62.5°	365.6	370.1	371.1	378.7	389.8	405.2	429.9	469.5	529.6	623.2	723.4
65°	313.6	313.6	315.7	323.6	328.8	342.4	361.3	390.1	438.4	511.3	596.7
67.5°	263.5	266.0	265.4	268.9	273.8	284.3	297.8	321.6	357.4	410.6	479.0
70°	230.8	232.8	232.3	234.9	240.1	247.0	258.0	280.5	306.2	351.8	410.6
72.5°	201.4	202.2	200.9	204.3	207.4	213.4	225.7	237.7	261.8	300.2	348.5
75°	154.2	155.2	156.2	158.3	161.5	164.6	171.0	183.0	198.7	227.6	258.5
77.5°	115.5	113.6	116.1	115.8	117.5	120.0	125.5	131.9	144.8	163.1	187.0
80°	87.1	87.6	87.6	88.1	90.7	92.3	97.0	101.7	111.7	125.3	142.1
82.5°	63.5	64.9	64.1	65.0	67.3	68.4	71.0	74.8	80.7	91.4	103.5
85°	34.6	32.0	33.0	34.1	34.1	34.6	36.7	38.3	41.4	45.6	50.3
87.5°	17.4	18.0	18.3	18.1	18.3	18.0	19.3	19.0	19.9	20.8	22.0
90°	36.6	35.5	34.5	33.5	32.5	31.1	29.5	27.8	26.1	24.3	22.0
92.5°	71.9	71.1	70.4	69.7	68.9	67.5	65.1	62.9	60.7	58.5	55.5
95°	131.0	130.3	129.7	129.0	128.3	126.7	124.4	122.0	119.7	117.2	113.9
97.5°	198.6	198.2	197.8	197.4	197.0	195.6	193.4	191.2	188.9	186.7	182.1
100°	249.7	249.1	248.4	247.7	247.1	245.2	242.2	239.1	236.1	233.0	228.6
102.5°	300.9	300.0	299.0	298.1	297.2	295.0	291.8	288.4	285.1	281.8	279.5
105°	377.7	376.7	375.7	374.7	373.7	372.1	370.1	368.1	366.1	364.1	361.9
107.5°	456.3	456.4	456.5	456.5	456.6	456.1	455.0	454.0	453.0	452.0	450.5
110°	514.8	515.1	515.4	515.8	516.1	515.8	514.8	513.8	512.7	511.7	510.7



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.1	572.7	573.3	573.9	574.5	574.5	574.1	573.6	573.1	572.7	571.4
115°	662.6	662.9	663.2	663.6	663.9	664.2	664.6	664.9	665.2	665.6	664.9
117.5°	750.8	752.2	753.6	754.9	756.3	756.8	756.6	756.3	756.0	755.8	755.1
120°	811.8	813.1	814.5	815.9	817.2	817.9	817.9	817.9	817.9	817.9	817.5
122.5°	872.7	873.7	874.8	876.0	877.1	877.7	878.0	878.3	878.5	878.8	877.9
125°	964.1	964.4	964.7	965.1	965.4	965.9	966.6	967.3	968.0	968.7	968.4
127.5°	1051.8	1052.5	1053.2	1053.8	1054.5	1055.0	1055.4	1055.7	1056.0	1056.4	1056.0
130°	1110.3	1111.0	1111.7	1112.4	1113.0	1113.5	1113.9	1114.2	1114.5	1114.9	1114.2
132.5°	1165.1	1166.1	1167.0	1168.0	1168.9	1169.5	1169.9	1170.2	1170.5	1170.9	1171.0
135°	1250.4	1251.7	1253.1	1254.5	1255.9	1256.5	1256.5	1256.5	1256.5	1256.5	1256.2
137.5°	1333.8	1335.5	1337.3	1339.0	1340.7	1341.3	1340.9	1340.5	1340.1	1339.7	1338.9
140°	1387.5	1389.2	1390.9	1392.6	1394.2	1394.7	1394.1	1393.4	1392.7	1392.1	1391.1
142.5°	1438.7	1440.4	1442.1	1443.7	1445.4	1446.1	1445.6	1445.2	1444.8	1444.4	1443.2
145°	1515.4	1516.4	1517.4	1518.4	1519.4	1519.9	1519.9	1519.9	1519.9	1519.9	1518.9
147.5°	1580.9	1583.3	1585.5	1587.8	1590.1	1590.8	1590.0	1589.2	1588.4	1587.6	1586.8
150°	1629.6	1630.3	1631.0	1631.6	1632.3	1632.7	1632.7	1632.7	1632.7	1632.7	1631.3
152.5°	1669.9	1671.1	1672.3	1673.5	1674.8	1675.0	1674.2	1673.3	1672.5	1671.7	1671.1
155°	1727.2	1728.8	1730.5	1732.2	1733.9	1734.0	1732.7	1731.3	1730.0	1728.7	1728.3
157.5°	1774.9	1777.2	1779.4	1781.6	1783.9	1784.3	1783.0	1781.6	1780.3	1778.9	1778.6
160°	1807.9	1809.6	1811.2	1812.9	1814.6	1814.8	1813.4	1812.1	1810.7	1809.4	1809.1
162.5°	1835.8	1837.9	1839.8	1841.8	1843.7	1843.9	1842.3	1840.7	1839.1	1837.3	1837.3
165°	1873.3	1875.4	1877.4	1879.5	1881.5	1881.8	1880.5	1879.1	1877.7	1876.4	1876.0
167.5°	1903.2	1905.3	1907.4	1909.5	1911.6	1911.6	1909.6	1907.5	1905.5	1903.5	1903.5
170°	1919.0	1921.4	1923.8	1926.1	1928.5	1928.6	1926.6	1924.6	1922.6	1920.6	1920.6
172.5°	1932.5	1934.5	1936.6	1938.7	1940.9	1940.9	1938.8	1936.8	1934.8	1932.8	1932.8
175°	1944.9	1947.3	1949.6	1952.1	1954.4	1954.6	1952.6	1950.6	1948.4	1946.4	1946.4
177.5°	1952.3	1954.1	1956.0	1957.9	1959.8	1959.9	1958.3	1956.7	1955.1	1953.5	1953.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1271.1	1268.2	1264.8	1258.9	1251.8	1248.0	1242.1	1238.4	1230.8	1224.6	1217.8
5°	1335.5	1321.9	1309.4	1293.1	1275.3	1263.7	1250.1	1234.9	1219.2	1203.0	1185.1
7.5°	1402.4	1378.3	1352.0	1323.8	1296.3	1270.9	1246.7	1222.8	1200.6	1173.8	1151.0
10°	1447.2	1416.8	1384.3	1346.0	1308.9	1276.4	1243.3	1214.5	1185.1	1153.7	1125.8
12.5°	1492.2	1451.7	1405.7	1363.7	1318.9	1279.7	1240.8	1204.0	1167.1	1132.3	1099.8
15°	1523.9	1488.1	1445.7	1385.9	1335.5	1281.6	1230.2	1182.5	1137.9	1099.1	1058.2
17.5°	1544.7	1498.7	1453.2	1395.8	1329.8	1269.4	1211.2	1156.6	1106.3	1057.1	1017.7
20°	1548.5	1501.3	1453.6	1397.5	1329.8	1260.6	1202.4	1136.8	1082.9	1032.0	983.7
22.5°	1547.2	1493.8	1441.8	1384.0	1318.1	1254.4	1184.0	1117.1	1058.5	1008.5	958.2
25°	1535.4	1478.2	1413.2	1355.0	1290.0	1222.3	1151.0	1081.8	1022.0	964.8	915.0
27.5°	1525.5	1451.4	1377.8	1309.9	1247.1	1185.1	1116.8	1045.9	979.7	921.7	874.7
30°	1513.4	1432.1	1349.2	1278.4	1214.0	1153.7	1089.1	1020.0	950.7	894.0	843.7
32.5°	1502.5	1407.8	1320.3	1243.2	1174.9	1116.3	1056.8	991.0	923.0	865.6	815.2
35°	1481.4	1371.8	1271.6	1184.6	1111.7	1051.4	1001.6	940.2	877.8	822.2	774.0
37.5°	1454.6	1324.5	1217.1	1125.8	1045.9	982.4	936.0	888.9	829.0	775.5	731.8
40°	1433.6	1291.0	1177.2	1083.9	1001.1	934.9	892.0	847.4	797.6	747.8	701.7
42.5°	1407.2	1260.8	1137.0	1036.5	954.4	890.1	845.0	807.1	763.2	716.7	673.9
45°	1358.7	1206.1	1071.9	963.8	880.9	817.5	770.8	742.6	709.5	665.4	629.2
47.5°	1287.3	1140.3	1001.5	890.0	804.5	745.7	702.0	674.8	651.5	618.7	585.9
50°	1223.9	1091.3	950.7	840.0	754.6	695.3	655.0	630.3	610.4	585.2	557.4
52.5°	1153.0	1029.6	900.8	791.4	706.8	648.3	608.8	587.1	570.6	552.5	525.1
55°	1040.4	935.5	816.0	712.1	634.0	576.8	542.2	523.3	509.7	496.0	479.3
57.5°	916.3	834.2	728.3	633.5	561.5	509.5	477.2	458.8	448.3	441.2	431.3
60°	829.0	758.8	667.5	581.0	510.8	464.6	433.1	419.0	410.1	404.2	397.0
62.5°	748.1	690.4	605.8	526.8	465.4	421.8	393.7	380.0	371.4	368.6	362.5
65°	628.7	584.2	514.4	448.9	396.5	359.2	335.6	322.4	317.2	314.1	314.7
67.5°	511.2	484.0	428.0	372.1	330.2	299.0	280.1	270.0	267.4	263.3	263.2
70°	439.4	419.0	371.8	323.1	285.8	261.7	244.9	234.4	231.8	229.6	229.1
72.5°	376.1	358.2	317.2	278.1	244.7	223.5	209.6	203.4	199.0	197.8	197.7
75°	282.7	272.7	240.1	209.2	186.1	171.5	162.1	156.2	153.1	152.6	153.1
77.5°	201.0	192.3	171.6	149.7	135.1	124.0	116.0	114.0	110.5	110.6	110.0
80°	151.0	145.2	132.2	114.8	102.8	93.3	89.2	85.4	84.4	82.8	84.4
82.5°	109.5	103.3	94.4	83.4	73.4	67.8	63.5	62.4	61.8	61.0	61.4
85°	54.0	54.5	49.3	40.9	36.7	33.5	30.9	30.9	30.4	29.9	30.4
87.5°	22.4	21.1	18.9	17.2	14.5	12.7	11.7	11.6	10.9	11.0	12.0
90°	19.6	17.3	14.8	12.3	9.7	7.0	4.2	1.5	4.2	7.0	9.7
92.5°	52.6	49.8	46.9	44.4	42.5	40.7	38.8	36.9	38.8	40.7	42.5
95°	110.5	107.1	103.7	101.7	101.0	100.4	99.7	99.0	99.7	100.4	101.0
97.5°	177.4	172.7	168.0	165.6	165.3	165.0	164.7	164.5	164.7	165.0	165.3
100°	224.2	219.8	215.4	213.2	213.2	213.2	213.2	213.2	213.2	213.2	213.2
102.5°	277.3	275.1	272.9	271.0	269.6	268.3	267.0	265.6	267.0	268.3	269.6
105°	359.9	357.9	355.9	354.1	352.3	350.6	348.9	347.3	348.9	350.6	352.3
107.5°	448.9	447.4	445.9	444.1	442.5	440.8	439.1	437.4	439.1	440.8	442.5
110°	509.7	508.7	507.7	506.3	504.6	502.9	501.3	499.6	501.3	502.9	504.6





TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	570.1	568.8	567.5	566.4	565.5	564.7	563.8	562.9	563.8	564.7	565.5
115°	664.2	663.6	662.9	661.9	660.5	659.1	657.8	656.4	657.8	659.1	660.5
117.5°	754.5	753.9	753.3	752.7	752.0	751.4	750.8	750.2	750.8	751.4	752.0
120°	817.2	816.9	816.5	815.5	813.9	812.1	810.4	808.7	810.4	812.1	813.9
122.5°	877.1	876.2	875.3	874.5	873.9	873.3	872.7	872.1	872.7	873.3	873.9
125°	968.0	967.7	967.3	966.1	964.1	962.1	960.0	958.0	960.0	962.1	964.1
127.5°	1055.6	1055.2	1054.8	1054.0	1052.8	1051.7	1050.6	1049.4	1050.6	1051.7	1052.8
130°	1113.5	1112.9	1112.2	1111.0	1109.2	1107.6	1105.9	1104.2	1105.9	1107.6	1109.2
132.5°	1171.1	1171.3	1171.4	1170.1	1167.4	1164.6	1161.8	1159.0	1161.8	1164.6	1167.4
135°	1255.9	1255.5	1255.2	1253.9	1251.9	1249.9	1247.9	1245.9	1247.9	1249.9	1251.9
137.5°	1338.2	1337.5	1336.7	1335.3	1333.3	1331.4	1329.5	1327.5	1329.5	1331.4	1333.3
140°	1390.1	1389.0	1388.0	1386.6	1384.9	1383.2	1381.6	1379.9	1381.6	1383.2	1384.9
142.5°	1441.9	1440.6	1439.3	1437.9	1436.5	1435.1	1433.7	1432.3	1433.7	1435.1	1436.5
145°	1517.9	1516.9	1515.9	1514.8	1513.4	1512.1	1510.7	1509.3	1510.7	1512.1	1513.4
147.5°	1586.0	1585.2	1584.4	1583.6	1582.9	1582.1	1581.3	1580.6	1581.3	1582.1	1582.9
150°	1630.0	1628.6	1627.3	1626.8	1627.1	1627.5	1627.8	1628.1	1627.8	1627.5	1627.1
152.5°	1670.6	1670.1	1669.5	1669.0	1668.5	1668.1	1667.6	1667.1	1667.6	1668.1	1668.5
155°	1728.0	1727.7	1727.3	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2	1727.2
157.5°	1778.3	1777.9	1777.6	1777.8	1778.5	1779.3	1780.0	1780.7	1780.0	1779.3	1778.5
160°	1808.7	1808.4	1808.1	1808.4	1809.4	1810.4	1811.4	1812.4	1811.4	1810.4	1809.4
162.5°	1837.2	1837.1	1837.1	1837.4	1838.3	1839.0	1839.7	1840.5	1839.7	1839.0	1838.3
165°	1875.7	1875.4	1875.0	1875.2	1875.9	1876.5	1877.2	1877.9	1877.2	1876.5	1875.9
167.5°	1903.5	1903.5	1903.5	1904.2	1905.5	1906.9	1908.2	1909.6	1908.2	1906.9	1905.5
170°	1920.6	1920.6	1920.6	1921.3	1922.6	1923.9	1925.3	1926.6	1925.3	1923.9	1922.6
172.5°	1932.8	1932.8	1932.8	1933.4	1934.8	1936.1	1937.5	1938.8	1937.5	1936.1	1934.8
175°	1946.4	1946.4	1946.4	1947.1	1948.4	1949.8	1951.2	1952.6	1951.2	1949.8	1948.4
177.5°	1954.0	1954.3	1954.5	1955.2	1956.3	1957.4	1958.4	1959.5	1958.4	1957.4	1956.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1214.1	1209.4	1205.7	1197.3	1192.7	1186.4	1181.3	1186.8	1180.9	1183.5	1179.6
5°	1176.2	1161.5	1151.0	1135.8	1122.7	1110.6	1101.8	1100.1	1095.9	1093.9	1087.5
7.5°	1130.6	1112.3	1094.3	1074.4	1057.5	1040.5	1029.6	1020.6	1014.6	1006.7	1001.4
10°	1103.8	1079.1	1058.2	1034.1	1013.1	994.7	980.1	972.7	965.9	955.9	952.3
12.5°	1070.7	1045.2	1019.6	993.8	973.7	953.2	940.6	929.5	924.8	913.5	912.4
15°	1031.0	992.7	967.5	941.3	913.4	896.7	886.2	874.1	868.9	861.0	855.3
17.5°	983.5	949.4	917.9	890.7	866.9	852.7	839.7	831.4	822.4	817.3	807.9
20°	949.2	916.7	885.1	856.3	838.0	821.7	811.2	803.3	794.0	791.3	781.8
22.5°	920.2	884.3	854.1	829.9	809.8	791.5	780.1	774.9	768.3	760.2	758.3
25°	873.1	835.9	810.2	786.1	768.2	751.4	743.6	736.8	730.4	724.7	722.6
27.5°	832.4	799.1	768.6	746.8	731.3	716.0	709.0	700.7	696.2	691.6	685.9
30°	803.9	769.8	743.1	722.1	705.3	691.7	684.3	678.5	674.4	670.1	667.0
32.5°	774.5	743.0	717.0	696.5	679.7	669.4	662.9	658.8	654.2	649.1	645.2
35°	735.7	701.0	675.9	658.1	645.0	637.1	629.8	626.1	620.9	620.9	616.6
37.5°	692.0	662.1	639.9	623.6	611.9	604.8	596.8	594.3	591.0	588.8	587.3
40°	666.0	638.1	617.2	601.0	588.3	582.6	576.3	572.1	570.0	567.3	566.3
42.5°	639.1	612.6	592.5	577.4	566.5	561.6	555.7	552.8	548.6	545.1	544.5
45°	598.3	572.6	554.3	542.2	532.8	527.0	523.3	517.1	514.9	510.8	510.2
47.5°	559.6	534.9	516.9	507.1	498.8	494.0	488.3	482.0	479.6	477.5	477.3
50°	530.7	508.2	491.3	481.9	474.0	467.3	461.4	457.3	455.7	455.7	456.8
52.5°	501.3	482.1	467.9	456.4	448.9	441.6	436.3	433.7	431.3	433.8	435.8
55°	458.3	438.9	428.4	417.4	410.1	401.6	399.1	398.0	396.5	400.6	402.7
57.5°	412.8	399.2	386.9	376.0	369.4	364.6	361.0	360.3	363.2	365.3	372.1
60°	383.8	368.1	357.1	348.7	340.8	337.7	336.7	335.6	337.7	343.5	352.3
62.5°	351.9	339.2	327.3	321.0	315.3	310.0	309.8	310.4	314.7	321.2	330.1
65°	305.2	294.2	286.3	278.9	274.3	271.1	272.2	274.3	278.9	287.9	297.8
67.5°	257.7	250.1	243.1	237.1	232.6	232.6	233.7	236.8	242.4	252.7	261.8
70°	227.0	218.6	212.9	210.3	206.6	204.5	207.6	212.9	217.6	227.0	234.9
72.5°	196.4	189.3	184.8	183.0	181.5	179.8	180.8	186.4	192.9	202.3	211.5
75°	151.0	148.3	145.2	143.2	141.6	142.6	143.7	149.0	154.2	164.1	174.6
77.5°	110.2	107.4	105.6	105.1	104.2	104.7	107.8	111.6	116.7	124.0	131.9
80°	83.4	82.3	81.3	80.8	80.8	81.3	85.4	88.1	92.8	99.7	105.9
82.5°	60.7	60.1	59.9	59.8	60.2	60.3	62.8	66.2	70.2	75.3	80.8
85°	32.0	30.9	32.5	33.0	32.0	33.5	34.6	36.7	38.3	40.9	43.5
87.5°	12.9	14.3	14.3	15.2	15.8	17.1	17.0	19.0	20.2	21.3	21.2
90°	12.3	14.8	17.3	19.6	22.0	24.3	26.1	27.8	29.5	31.1	32.5
92.5°	44.4	46.9	49.8	52.6	55.5	58.5	60.7	62.9	65.1	67.5	68.9
95°	101.7	103.7	107.1	110.5	113.9	117.2	119.7	122.0	124.4	126.7	128.3
97.5°	165.6	168.0	172.7	177.4	182.1	186.7	188.9	191.2	193.4	195.6	197.0
100°	213.2	215.4	219.8	224.2	228.6	233.0	236.1	239.1	242.2	245.2	247.1
102.5°	271.0	272.9	275.1	277.3	279.5	281.8	285.1	288.4	291.8	295.0	297.2
105°	354.1	355.9	357.9	359.9	361.9	364.1	366.1	368.1	370.1	372.1	373.7
107.5°	444.1	445.9	447.4	448.9	450.5	452.0	453.0	454.0	455.0	456.1	456.6
110°	506.3	507.7	508.7	509.7	510.7	511.7	512.7	513.8	514.8	515.8	516.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	566.4	567.5	568.8	570.1	571.4	572.7	573.1	573.6	574.1	574.5	574.5
115°	661.9	662.9	663.6	664.2	664.9	665.6	665.2	664.9	664.6	664.2	663.9
117.5°	752.7	753.3	753.9	754.5	755.1	755.8	756.0	756.3	756.6	756.8	756.3
120°	815.5	816.5	816.9	817.2	817.5	817.9	817.9	817.9	817.9	817.9	817.2
122.5°	874.5	875.3	876.2	877.1	877.9	878.8	878.5	878.3	878.0	877.7	877.1
125°	966.1	967.3	967.7	968.0	968.4	968.7	968.0	967.3	966.6	965.9	965.4
127.5°	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0	1055.7	1055.4	1055.0	1054.5
130°	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5	1114.2	1113.9	1113.5	1113.0
132.5°	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5	1170.2	1169.9	1169.5	1168.9
135°	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5	1256.5	1256.5	1256.5	1255.9
137.5°	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1	1340.5	1340.9	1341.3	1340.7
140°	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7	1393.4	1394.1	1394.7	1394.2
142.5°	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8	1445.2	1445.6	1446.1	1445.4
145°	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.4
147.5°	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4	1589.2	1590.0	1590.8	1590.1
150°	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7	1632.7	1632.7	1632.7	1632.3
152.5°	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5	1673.3	1674.2	1675.0	1674.8
155°	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0	1731.3	1732.7	1734.0	1733.9
157.5°	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3	1781.6	1783.0	1784.3	1783.9
160°	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7	1812.1	1813.4	1814.8	1814.6
162.5°	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1	1840.7	1842.3	1843.9	1843.7
165°	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7	1879.1	1880.5	1881.8	1881.5
167.5°	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5	1907.5	1909.6	1911.6	1911.6
170°	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6	1924.6	1926.6	1928.6	1928.5
172.5°	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8	1936.8	1938.8	1940.9	1940.9
175°	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4	1950.6	1952.6	1954.6	1954.4
177.5°	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1	1956.7	1958.3	1959.9	1959.8
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1177.1	1180.0	1177.5	1180.9	1177.5	1180.0	1177.1	1179.6	1183.5	1180.9	1186.8
5°	1084.9	1080.3	1083.4	1081.3	1083.4	1080.3	1084.9	1087.5	1093.9	1095.9	1100.1
7.5°	999.8	995.2	990.2	987.7	990.2	995.2	999.8	1001.4	1006.7	1014.6	1020.6
10°	946.5	940.7	940.2	936.5	940.2	940.7	946.5	952.3	955.9	965.9	972.7
12.5°	907.5	902.1	896.2	894.6	896.2	902.1	907.5	912.4	913.5	924.8	929.5
15°	852.1	847.9	844.2	847.4	844.2	847.9	852.1	855.3	861.0	868.9	874.1
17.5°	806.1	802.6	801.9	798.1	801.9	802.6	806.1	807.9	817.3	822.4	831.4
20°	777.1	774.5	775.6	768.7	775.6	774.5	777.1	781.8	791.3	794.0	803.3
22.5°	754.1	748.9	748.3	746.9	748.3	748.9	754.1	758.3	760.2	768.3	774.9
25°	717.9	715.3	712.7	715.3	712.7	715.3	717.9	722.6	724.7	730.4	736.8
27.5°	686.3	683.2	682.5	682.8	682.5	683.2	686.3	685.9	691.6	696.2	700.7
30°	667.0	661.8	662.3	661.8	662.3	661.8	667.0	667.0	670.1	674.4	678.5
32.5°	646.0	642.5	641.8	640.8	641.8	642.5	646.0	645.2	649.1	654.2	658.8
35°	615.1	615.1	612.5	612.5	612.5	615.1	615.1	616.6	620.9	620.9	626.1
37.5°	586.0	585.5	583.9	584.2	583.9	585.5	586.0	587.3	588.8	591.0	594.3
40°	564.2	563.7	562.1	559.0	562.1	563.7	564.2	566.3	567.3	570.0	572.1
42.5°	543.2	541.5	540.8	539.7	540.8	541.5	543.2	544.5	545.1	548.6	552.8
45°	510.2	510.2	509.2	508.7	509.2	510.2	510.2	510.2	510.8	514.9	517.1
47.5°	478.2	479.1	481.1	480.8	481.1	479.1	478.2	477.3	477.5	479.6	482.0
50°	458.8	459.4	460.9	461.4	460.9	459.4	458.8	456.8	455.7	455.7	457.3
52.5°	437.5	440.5	442.4	442.1	442.4	440.5	437.5	435.8	433.8	431.3	433.7
55°	407.5	411.1	414.8	415.4	414.8	411.1	407.5	402.7	400.6	396.5	398.0
57.5°	377.8	382.9	386.8	388.0	386.8	382.9	377.8	372.1	365.3	363.2	360.3
60°	357.6	364.5	369.2	371.2	369.2	364.5	357.6	352.3	343.5	337.7	335.6
62.5°	338.3	346.0	350.7	351.1	350.7	346.0	338.3	330.1	321.2	314.7	310.4
65°	306.8	314.7	318.8	321.9	318.8	314.7	306.8	297.8	287.9	278.9	274.3
67.5°	272.8	280.6	285.3	287.8	285.3	280.6	272.8	261.8	252.7	242.4	236.8
70°	248.0	255.9	262.2	264.3	262.2	255.9	248.0	234.9	227.0	217.6	212.9
72.5°	223.7	230.8	235.8	238.2	235.8	230.8	223.7	211.5	202.3	192.9	186.4
75°	181.5	190.9	195.6	198.2	195.6	190.9	181.5	174.6	164.1	154.2	149.0
77.5°	139.9	148.6	151.4	152.7	151.4	148.6	139.9	131.9	124.0	116.7	111.6
80°	112.2	117.4	121.1	121.7	121.1	117.4	112.2	105.9	99.7	92.8	88.1
82.5°	86.2	90.6	91.8	93.1	91.8	90.6	86.2	80.8	75.3	70.2	66.2
85°	47.2	49.3	49.8	49.3	49.8	49.3	47.2	43.5	40.9	38.3	36.7
87.5°	22.2	22.0	22.2	23.2	22.2	22.0	22.2	21.2	21.3	20.2	19.0
90°	33.5	34.5	35.5	36.6	35.5	34.5	33.5	32.5	31.1	29.5	27.8
92.5°	69.7	70.4	71.1	71.9	71.1	70.4	69.7	68.9	67.5	65.1	62.9
95°	129.0	129.7	130.3	131.0	130.3	129.7	129.0	128.3	126.7	124.4	122.0
97.5°	197.4	197.8	198.2	198.6	198.2	197.8	197.4	197.0	195.6	193.4	191.2
100°	247.7	248.4	249.1	249.7	249.1	248.4	247.7	247.1	245.2	242.2	239.1
102.5°	298.1	299.0	300.0	300.9	300.0	299.0	298.1	297.2	295.0	291.8	288.4
105°	374.7	375.7	376.7	377.7	376.7	375.7	374.7	373.7	372.1	370.1	368.1
107.5°	456.5	456.5	456.4	456.3	456.4	456.5	456.5	456.6	456.1	455.0	454.0
110°	515.8	515.4	515.1	514.8	515.1	515.4	515.8	516.1	515.8	514.8	513.8



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	573.9	573.3	572.7	572.1	572.7	573.3	573.9	574.5	574.5	574.1	573.6
115°	663.6	663.2	662.9	662.6	662.9	663.2	663.6	663.9	664.2	664.6	664.9
117.5°	754.9	753.6	752.2	750.8	752.2	753.6	754.9	756.3	756.8	756.6	756.3
120°	815.9	814.5	813.1	811.8	813.1	814.5	815.9	817.2	817.9	817.9	817.9
122.5°	876.0	874.8	873.7	872.7	873.7	874.8	876.0	877.1	877.7	878.0	878.3
125°	965.1	964.7	964.4	964.1	964.4	964.7	965.1	965.4	965.9	966.6	967.3
127.5°	1053.8	1053.2	1052.5	1051.8	1052.5	1053.2	1053.8	1054.5	1055.0	1055.4	1055.7
130°	1112.4	1111.7	1111.0	1110.3	1111.0	1111.7	1112.4	1113.0	1113.5	1113.9	1114.2
132.5°	1168.0	1167.0	1166.1	1165.1	1166.1	1167.0	1168.0	1168.9	1169.5	1169.9	1170.2
135°	1254.5	1253.1	1251.7	1250.4	1251.7	1253.1	1254.5	1255.9	1256.5	1256.5	1256.5
137.5°	1339.0	1337.3	1335.5	1333.8	1335.5	1337.3	1339.0	1340.7	1341.3	1340.9	1340.5
140°	1392.6	1390.9	1389.2	1387.5	1389.2	1390.9	1392.6	1394.2	1394.7	1394.1	1393.4
142.5°	1443.7	1442.1	1440.4	1438.7	1440.4	1442.1	1443.7	1445.4	1446.1	1445.6	1445.2
145°	1518.4	1517.4	1516.4	1515.4	1516.4	1517.4	1518.4	1519.4	1519.9	1519.9	1519.9
147.5°	1587.8	1585.5	1583.3	1580.9	1583.3	1585.5	1587.8	1590.1	1590.8	1590.0	1589.2
150°	1631.6	1631.0	1630.3	1629.6	1630.3	1631.0	1631.6	1632.3	1632.7	1632.7	1632.7
152.5°	1673.5	1672.3	1671.1	1669.9	1671.1	1672.3	1673.5	1674.8	1675.0	1674.2	1673.3
155°	1732.2	1730.5	1728.8	1727.2	1728.8	1730.5	1732.2	1733.9	1734.0	1732.7	1731.3
157.5°	1781.6	1779.4	1777.2	1774.9	1777.2	1779.4	1781.6	1783.9	1784.3	1783.0	1781.6
160°	1812.9	1811.2	1809.6	1807.9	1809.6	1811.2	1812.9	1814.6	1814.8	1813.4	1812.1
162.5°	1841.8	1839.8	1837.9	1835.8	1837.9	1839.8	1841.8	1843.7	1843.9	1842.3	1840.7
165°	1879.5	1877.4	1875.4	1873.3	1875.4	1877.4	1879.5	1881.5	1881.8	1880.5	1879.1
167.5°	1909.5	1907.4	1905.3	1903.2	1905.3	1907.4	1909.5	1911.6	1911.6	1909.6	1907.5
170°	1926.1	1923.8	1921.4	1919.0	1921.4	1923.8	1926.1	1928.5	1928.6	1926.6	1924.6
172.5°	1938.7	1936.6	1934.5	1932.5	1934.5	1936.6	1938.7	1940.9	1940.9	1938.8	1936.8
175°	1952.1	1949.6	1947.3	1944.9	1947.3	1949.6	1952.1	1954.4	1954.6	1952.6	1950.6
177.5°	1957.9	1956.0	1954.1	1952.3	1954.1	1956.0	1957.9	1959.8	1959.9	1958.3	1956.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1181.3	1186.4	1192.7	1197.3	1205.7	1209.4	1214.1	1217.8	1224.6	1230.8	1238.4
5°	1101.8	1110.6	1122.7	1135.8	1151.0	1161.5	1176.2	1185.1	1203.0	1219.2	1234.9
7.5°	1029.6	1040.5	1057.5	1074.4	1094.3	1112.3	1130.6	1151.0	1173.8	1200.6	1222.8
10°	980.1	994.7	1013.1	1034.1	1058.2	1079.1	1103.8	1125.8	1153.7	1185.1	1214.5
12.5°	940.6	953.2	973.7	993.8	1019.6	1045.2	1070.7	1099.8	1132.3	1167.1	1204.0
15°	886.2	896.7	913.4	941.3	967.5	992.7	1031.0	1058.2	1099.1	1137.9	1182.5
17.5°	839.7	852.7	866.9	890.7	917.9	949.4	983.5	1017.7	1057.1	1106.3	1156.6
20°	811.2	821.7	838.0	856.3	885.1	916.7	949.2	983.7	1032.0	1082.9	1136.8
22.5°	780.1	791.5	809.8	829.9	854.1	884.3	920.2	958.2	1008.5	1058.5	1117.1
25°	743.6	751.4	768.2	786.1	810.2	835.9	873.1	915.0	964.8	1022.0	1081.8
27.5°	709.0	716.0	731.3	746.8	768.6	799.1	832.4	874.7	921.7	979.7	1045.9
30°	684.3	691.7	705.3	722.1	743.1	769.8	803.9	843.7	894.0	950.7	1020.0
32.5°	662.9	669.4	679.7	696.5	717.0	743.0	774.5	815.2	865.6	923.0	991.0
35°	629.8	637.1	645.0	658.1	675.9	701.0	735.7	774.0	822.2	877.8	940.2
37.5°	596.8	604.8	611.9	623.6	639.9	662.1	692.0	731.8	775.5	829.0	888.9
40°	576.3	582.6	588.3	601.0	617.2	638.1	666.0	701.7	747.8	797.6	847.4
42.5°	555.7	561.6	566.5	577.4	592.5	612.6	639.1	673.9	716.7	763.2	807.1
45°	523.3	527.0	532.8	542.2	554.3	572.6	598.3	629.2	665.4	709.5	742.6
47.5°	488.3	494.0	498.8	507.1	516.9	534.9	559.6	585.9	618.7	651.5	674.8
50°	461.4	467.3	474.0	481.9	491.3	508.2	530.7	557.4	585.2	610.4	630.3
52.5°	436.3	441.6	448.9	456.4	467.9	482.1	501.3	525.1	552.5	570.6	587.1
55°	399.1	401.6	410.1	417.4	428.4	438.9	458.3	479.3	496.0	509.7	523.3
57.5°	361.0	364.6	369.4	376.0	386.9	399.2	412.8	431.3	441.2	448.3	458.8
60°	336.7	337.7	340.8	348.7	357.1	368.1	383.8	397.0	404.2	410.1	419.0
62.5°	309.8	310.0	315.3	321.0	327.3	339.2	351.9	362.5	368.6	371.4	380.0
65°	272.2	271.1	274.3	278.9	286.3	294.2	305.2	314.7	314.1	317.2	322.4
67.5°	233.7	232.6	232.6	237.1	243.1	250.1	257.7	263.2	263.3	267.4	270.0
70°	207.6	204.5	206.6	210.3	212.9	218.6	227.0	229.1	229.6	231.8	234.4
72.5°	180.8	179.8	181.5	183.0	184.8	189.3	196.4	197.7	197.8	199.0	203.4
75°	143.7	142.6	141.6	143.2	145.2	148.3	151.0	153.1	152.6	153.1	156.2
77.5°	107.8	104.7	104.2	105.1	105.6	107.4	110.2	110.0	110.6	110.5	114.0
80°	85.4	81.3	80.8	80.8	81.3	82.3	83.4	84.4	82.8	84.4	85.4
82.5°	62.8	60.3	60.2	59.8	59.9	60.1	60.7	61.4	61.0	61.8	62.4
85°	34.6	33.5	32.0	33.0	32.5	30.9	32.0	30.4	29.9	30.4	30.9
87.5°	17.0	17.1	15.8	15.2	14.3	14.3	12.9	12.0	11.0	10.9	11.6
90°	26.1	24.3	22.0	19.6	17.3	14.8	12.3	9.7	7.0	4.2	1.5
92.5°	60.7	58.5	55.5	52.6	49.8	46.9	44.4	42.5	40.7	38.8	36.9
95°	119.7	117.2	113.9	110.5	107.1	103.7	101.7	101.0	100.4	99.7	99.0
97.5°	188.9	186.7	182.1	177.4	172.7	168.0	165.6	165.3	165.0	164.7	164.5
100°	236.1	233.0	228.6	224.2	219.8	215.4	213.2	213.2	213.2	213.2	213.2
102.5°	285.1	281.8	279.5	277.3	275.1	272.9	271.0	269.6	268.3	267.0	265.6
105°	366.1	364.1	361.9	359.9	357.9	355.9	354.1	352.3	350.6	348.9	347.3
107.5°	453.0	452.0	450.5	448.9	447.4	445.9	444.1	442.5	440.8	439.1	437.4
110°	512.7	511.7	510.7	509.7	508.7	507.7	506.3	504.6	502.9	501.3	499.6



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	573.1	572.7	571.4	570.1	568.8	567.5	566.4	565.5	564.7	563.8	562.9
115°	665.2	665.6	664.9	664.2	663.6	662.9	661.9	660.5	659.1	657.8	656.4
117.5°	756.0	755.8	755.1	754.5	753.9	753.3	752.7	752.0	751.4	750.8	750.2
120°	817.9	817.9	817.5	817.2	816.9	816.5	815.5	813.9	812.1	810.4	808.7
122.5°	878.5	878.8	877.9	877.1	876.2	875.3	874.5	873.9	873.3	872.7	872.1
125°	968.0	968.7	968.4	968.0	967.7	967.3	966.1	964.1	962.1	960.0	958.0
127.5°	1056.0	1056.4	1056.0	1055.6	1055.2	1054.8	1054.0	1052.8	1051.7	1050.6	1049.4
130°	1114.5	1114.9	1114.2	1113.5	1112.9	1112.2	1111.0	1109.2	1107.6	1105.9	1104.2
132.5°	1170.5	1170.9	1171.0	1171.1	1171.3	1171.4	1170.1	1167.4	1164.6	1161.8	1159.0
135°	1256.5	1256.5	1256.2	1255.9	1255.5	1255.2	1253.9	1251.9	1249.9	1247.9	1245.9
137.5°	1340.1	1339.7	1338.9	1338.2	1337.5	1336.7	1335.3	1333.3	1331.4	1329.5	1327.5
140°	1392.7	1392.1	1391.1	1390.1	1389.0	1388.0	1386.6	1384.9	1383.2	1381.6	1379.9
142.5°	1444.8	1444.4	1443.2	1441.9	1440.6	1439.3	1437.9	1436.5	1435.1	1433.7	1432.3
145°	1519.9	1519.9	1518.9	1517.9	1516.9	1515.9	1514.8	1513.4	1512.1	1510.7	1509.3
147.5°	1588.4	1587.6	1586.8	1586.0	1585.2	1584.4	1583.6	1582.9	1582.1	1581.3	1580.6
150°	1632.7	1632.7	1631.3	1630.0	1628.6	1627.3	1626.8	1627.1	1627.5	1627.8	1628.1
152.5°	1672.5	1671.7	1671.1	1670.6	1670.1	1669.5	1669.0	1668.5	1668.1	1667.6	1667.1
155°	1730.0	1728.7	1728.3	1728.0	1727.7	1727.3	1727.2	1727.2	1727.2	1727.2	1727.2
157.5°	1780.3	1778.9	1778.6	1778.3	1777.9	1777.6	1777.8	1778.5	1779.3	1780.0	1780.7
160°	1810.7	1809.4	1809.1	1808.7	1808.4	1808.1	1808.4	1809.4	1810.4	1811.4	1812.4
162.5°	1839.1	1837.3	1837.3	1837.2	1837.1	1837.1	1837.4	1838.3	1839.0	1839.7	1840.5
165°	1877.7	1876.4	1876.0	1875.7	1875.4	1875.0	1875.2	1875.9	1876.5	1877.2	1877.9
167.5°	1905.5	1903.5	1903.5	1903.5	1903.5	1903.5	1904.2	1905.5	1906.9	1908.2	1909.6
170°	1922.6	1920.6	1920.6	1920.6	1920.6	1920.6	1921.3	1922.6	1923.9	1925.3	1926.6
172.5°	1934.8	1932.8	1932.8	1932.8	1932.8	1932.8	1933.4	1934.8	1936.1	1937.5	1938.8
175°	1948.4	1946.4	1946.4	1946.4	1946.4	1946.4	1947.1	1948.4	1949.8	1951.2	1952.6
177.5°	1955.1	1953.5	1953.7	1954.0	1954.3	1954.5	1955.2	1956.3	1957.4	1958.4	1959.5
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1242.1	1248.0	1251.8	1258.9	1264.8	1268.2	1271.1	1273.6	1276.6	1279.1	1286.2
5°	1250.1	1263.7	1275.3	1293.1	1309.4	1321.9	1335.5	1347.7	1357.7	1371.8	1382.8
7.5°	1246.7	1270.9	1296.3	1323.8	1352.0	1378.3	1402.4	1424.9	1445.4	1470.2	1491.9
10°	1243.3	1276.4	1308.9	1346.0	1384.3	1416.8	1447.2	1478.2	1500.8	1532.3	1558.9
12.5°	1240.8	1279.7	1318.9	1363.7	1405.7	1451.7	1492.2	1514.7	1549.0	1574.2	1606.0
15°	1230.2	1281.6	1335.5	1385.9	1445.7	1488.1	1523.9	1567.9	1599.8	1631.8	1666.5
17.5°	1211.2	1269.4	1329.8	1395.8	1453.2	1498.7	1544.7	1587.2	1625.4	1668.3	1711.3
20°	1202.4	1260.6	1329.8	1397.5	1453.6	1501.3	1548.5	1595.2	1637.1	1692.1	1742.0
22.5°	1184.0	1254.4	1318.1	1384.0	1441.8	1493.8	1547.2	1600.2	1656.0	1718.2	1780.6
25°	1151.0	1222.3	1290.0	1355.0	1413.2	1478.2	1535.4	1606.2	1677.5	1759.8	1837.4
27.5°	1116.8	1185.1	1247.1	1309.9	1377.8	1451.4	1525.5	1605.9	1699.2	1803.1	1912.6
30°	1089.1	1153.7	1214.0	1278.4	1349.2	1432.1	1513.4	1608.8	1716.8	1833.7	1963.8
32.5°	1056.8	1116.3	1174.9	1243.2	1320.3	1407.8	1502.5	1607.1	1737.0	1869.9	2003.7
35°	1001.6	1051.4	1111.7	1184.6	1271.6	1371.8	1481.4	1605.1	1754.0	1906.6	2019.4
37.5°	936.0	982.4	1045.9	1125.8	1217.1	1324.5	1454.6	1601.4	1759.6	1881.3	1917.6
40°	892.0	934.9	1001.1	1083.9	1177.2	1291.0	1433.6	1588.8	1742.0	1819.6	1789.7
42.5°	845.0	890.1	954.4	1036.5	1137.0	1260.8	1407.2	1562.5	1690.8	1720.2	1616.9
45°	770.8	817.5	880.9	963.8	1071.9	1206.1	1358.7	1499.8	1573.7	1520.7	1360.8
47.5°	702.0	745.7	804.5	890.0	1001.5	1140.3	1287.3	1399.8	1405.6	1279.3	1108.4
50°	655.0	695.3	754.6	840.0	950.7	1091.3	1223.9	1312.5	1272.6	1129.5	965.3
52.5°	608.8	648.3	706.8	791.4	900.8	1029.6	1153.0	1215.2	1140.1	993.2	852.9
55°	542.2	576.8	634.0	712.1	816.0	935.5	1040.4	1061.9	964.3	819.6	705.8
57.5°	477.2	509.5	561.5	633.5	728.3	834.2	916.3	911.7	808.6	684.4	594.1
60°	433.1	464.6	510.8	581.0	667.5	758.8	829.0	812.2	710.0	603.0	527.0
62.5°	393.7	421.8	465.4	526.8	605.8	690.4	748.1	723.4	623.2	529.6	469.5
65°	335.6	359.2	396.5	448.9	514.4	584.2	628.7	596.7	511.3	438.4	390.1
67.5°	280.1	299.0	330.2	372.1	428.0	484.0	511.2	479.0	410.6	357.4	321.6
70°	244.9	261.7	285.8	323.1	371.8	419.0	439.4	410.6	351.8	306.2	280.5
72.5°	209.6	223.5	244.7	278.1	317.2	358.2	376.1	348.5	300.2	261.8	237.7
75°	162.1	171.5	186.1	209.2	240.1	272.7	282.7	258.5	227.6	198.7	183.0
77.5°	116.0	124.0	135.1	149.7	171.6	192.3	201.0	187.0	163.1	144.8	131.9
80°	89.2	93.3	102.8	114.8	132.2	145.2	151.0	142.1	125.3	111.7	101.7
82.5°	63.5	67.8	73.4	83.4	94.4	103.3	109.5	103.5	91.4	80.7	74.8
85°	30.9	33.5	36.7	40.9	49.3	54.5	54.0	50.3	45.6	41.4	38.3
87.5°	11.7	12.7	14.5	17.2	18.9	21.1	22.4	22.0	20.8	19.9	19.0
90°	4.2	7.0	9.7	12.3	14.8	17.3	19.6	22.0	24.3	26.1	27.8
92.5°	38.8	40.7	42.5	44.4	46.9	49.8	52.6	55.5	58.5	60.7	62.9
95°	99.7	100.4	101.0	101.7	103.7	107.1	110.5	113.9	117.2	119.7	122.0
97.5°	164.7	165.0	165.3	165.6	168.0	172.7	177.4	182.1	186.7	188.9	191.2
100°	213.2	213.2	213.2	213.2	215.4	219.8	224.2	228.6	233.0	236.1	239.1
102.5°	267.0	268.3	269.6	271.0	272.9	275.1	277.3	279.5	281.8	285.1	288.4
105°	348.9	350.6	352.3	354.1	355.9	357.9	359.9	361.9	364.1	366.1	368.1
107.5°	439.1	440.8	442.5	444.1	445.9	447.4	448.9	450.5	452.0	453.0	454.0
110°	501.3	502.9	504.6	506.3	507.7	508.7	509.7	510.7	511.7	512.7	513.8





TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.8	564.7	565.5	566.4	567.5	568.8	570.1	571.4	572.7	573.1	573.6
115°	657.8	659.1	660.5	661.9	662.9	663.6	664.2	664.9	665.6	665.2	664.9
117.5°	750.8	751.4	752.0	752.7	753.3	753.9	754.5	755.1	755.8	756.0	756.3
120°	810.4	812.1	813.9	815.5	816.5	816.9	817.2	817.5	817.9	817.9	817.9
122.5°	872.7	873.3	873.9	874.5	875.3	876.2	877.1	877.9	878.8	878.5	878.3
125°	960.0	962.1	964.1	966.1	967.3	967.7	968.0	968.4	968.7	968.0	967.3
127.5°	1050.6	1051.7	1052.8	1054.0	1054.8	1055.2	1055.6	1056.0	1056.4	1056.0	1055.7
130°	1105.9	1107.6	1109.2	1111.0	1112.2	1112.9	1113.5	1114.2	1114.9	1114.5	1114.2
132.5°	1161.8	1164.6	1167.4	1170.1	1171.4	1171.3	1171.1	1171.0	1170.9	1170.5	1170.2
135°	1247.9	1249.9	1251.9	1253.9	1255.2	1255.5	1255.9	1256.2	1256.5	1256.5	1256.5
137.5°	1329.5	1331.4	1333.3	1335.3	1336.7	1337.5	1338.2	1338.9	1339.7	1340.1	1340.5
140°	1381.6	1383.2	1384.9	1386.6	1388.0	1389.0	1390.1	1391.1	1392.1	1392.7	1393.4
142.5°	1433.7	1435.1	1436.5	1437.9	1439.3	1440.6	1441.9	1443.2	1444.4	1444.8	1445.2
145°	1510.7	1512.1	1513.4	1514.8	1515.9	1516.9	1517.9	1518.9	1519.9	1519.9	1519.9
147.5°	1581.3	1582.1	1582.9	1583.6	1584.4	1585.2	1586.0	1586.8	1587.6	1588.4	1589.2
150°	1627.8	1627.5	1627.1	1626.8	1627.3	1628.6	1630.0	1631.3	1632.7	1632.7	1632.7
152.5°	1667.6	1668.1	1668.5	1669.0	1669.5	1670.1	1670.6	1671.1	1671.7	1672.5	1673.3
155°	1727.2	1727.2	1727.2	1727.2	1727.3	1727.7	1728.0	1728.3	1728.7	1730.0	1731.3
157.5°	1780.0	1779.3	1778.5	1777.8	1777.6	1777.9	1778.3	1778.6	1778.9	1780.3	1781.6
160°	1811.4	1810.4	1809.4	1808.4	1808.1	1808.4	1808.7	1809.1	1809.4	1810.7	1812.1
162.5°	1839.7	1839.0	1838.3	1837.4	1837.1	1837.1	1837.2	1837.3	1837.3	1839.1	1840.7
165°	1877.2	1876.5	1875.9	1875.2	1875.0	1875.4	1875.7	1876.0	1876.4	1877.7	1879.1
167.5°	1908.2	1906.9	1905.5	1904.2	1903.5	1903.5	1903.5	1903.5	1903.5	1905.5	1907.5
170°	1925.3	1923.9	1922.6	1921.3	1920.6	1920.6	1920.6	1920.6	1920.6	1922.6	1924.6
172.5°	1937.5	1936.1	1934.8	1933.4	1932.8	1932.8	1932.8	1932.8	1932.8	1934.8	1936.8
175°	1951.2	1949.8	1948.4	1947.1	1946.4	1946.4	1946.4	1946.4	1946.4	1948.4	1950.6
177.5°	1958.4	1957.4	1956.3	1955.2	1954.5	1954.3	1954.0	1953.7	1953.5	1955.1	1956.7
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5	1235.5
2.5°	1292.0	1295.5	1302.5	1300.0	1303.4	1305.0	1306.8
5°	1396.4	1413.2	1420.6	1419.5	1430.5	1427.8	1425.2
7.5°	1514.3	1532.0	1541.8	1554.1	1561.2	1561.7	1567.9
10°	1581.0	1604.1	1613.6	1626.6	1635.0	1639.7	1639.2
12.5°	1632.1	1650.2	1671.4	1677.8	1689.1	1695.1	1692.9
15°	1693.7	1722.6	1744.6	1755.7	1769.8	1773.9	1779.8
17.5°	1748.7	1787.4	1813.1	1847.2	1860.2	1868.0	1863.4
20°	1790.2	1841.1	1866.8	1907.7	1930.3	1942.3	1938.1
22.5°	1839.3	1894.4	1941.9	1977.3	2011.7	2027.9	2031.2
25°	1923.4	1998.9	2068.7	2115.4	2157.8	2167.8	2189.8
27.5°	2017.4	2106.5	2181.0	2230.1	2259.7	2270.8	2277.6
30°	2076.6	2165.2	2221.3	2252.7	2262.2	2261.1	2260.1
32.5°	2105.5	2161.0	2171.7	2162.9	2141.3	2123.1	2104.1
35°	2064.5	2023.1	1961.2	1881.5	1822.7	1763.5	1757.7
37.5°	1856.7	1724.2	1621.2	1506.2	1439.9	1398.9	1370.5
40°	1661.2	1510.8	1385.9	1288.9	1221.2	1194.6	1168.3
42.5°	1449.0	1305.1	1194.7	1113.6	1062.7	1033.0	1012.3
45°	1177.2	1050.4	963.8	905.0	864.7	841.6	828.5
47.5°	964.6	870.8	797.3	754.9	727.0	709.0	709.1
50°	850.5	760.8	712.1	678.5	654.4	640.3	642.9
52.5°	749.4	682.5	640.8	612.7	594.8	586.1	585.8
55°	626.6	578.3	551.1	530.7	518.6	508.7	510.8
57.5°	536.0	495.3	477.1	460.1	451.7	447.7	441.9
60°	479.8	448.4	432.6	419.0	410.6	407.5	401.6
62.5°	429.9	405.2	389.8	378.7	371.1	370.1	365.6
65°	361.3	342.4	328.8	323.6	315.7	313.6	313.6
67.5°	297.8	284.3	273.8	268.9	265.4	266.0	263.5
70°	258.0	247.0	240.1	234.9	232.3	232.8	230.8
72.5°	225.7	213.4	207.4	204.3	200.9	202.2	201.4
75°	171.0	164.6	161.5	158.3	156.2	155.2	154.2
77.5°	125.5	120.0	117.5	115.8	116.1	113.6	115.5
80°	97.0	92.3	90.7	88.1	87.6	87.6	87.1
82.5°	71.0	68.4	67.3	65.0	64.1	64.9	63.5
85°	36.7	34.6	34.1	34.1	33.0	32.0	34.6
87.5°	19.3	18.0	18.3	18.1	18.3	18.0	17.4
90°	29.5	31.1	32.5	33.5	34.5	35.5	36.6
92.5°	65.1	67.5	68.9	69.7	70.4	71.1	71.9
95°	124.4	126.7	128.3	129.0	129.7	130.3	131.0
97.5°	193.4	195.6	197.0	197.4	197.8	198.2	198.6
100°	242.2	245.2	247.1	247.7	248.4	249.1	249.7
102.5°	291.8	295.0	297.2	298.1	299.0	300.0	300.9
105°	370.1	372.1	373.7	374.7	375.7	376.7	377.7
107.5°	455.0	456.1	456.6	456.5	456.5	456.4	456.3
110°	514.8	515.8	516.1	515.8	515.4	515.1	514.8



TEST NUMBER: P333425-840

CATALOG NUMBER: S125DIW-S850D1560U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	574.1	574.5	574.5	573.9	573.3	572.7	572.1
115°	664.6	664.2	663.9	663.6	663.2	662.9	662.6
117.5°	756.6	756.8	756.3	754.9	753.6	752.2	750.8
120°	817.9	817.9	817.2	815.9	814.5	813.1	811.8
122.5°	878.0	877.7	877.1	876.0	874.8	873.7	872.7
125°	966.6	965.9	965.4	965.1	964.7	964.4	964.1
127.5°	1055.4	1055.0	1054.5	1053.8	1053.2	1052.5	1051.8
130°	1113.9	1113.5	1113.0	1112.4	1111.7	1111.0	1110.3
132.5°	1169.9	1169.5	1168.9	1168.0	1167.0	1166.1	1165.1
135°	1256.5	1256.5	1255.9	1254.5	1253.1	1251.7	1250.4
137.5°	1340.9	1341.3	1340.7	1339.0	1337.3	1335.5	1333.8
140°	1394.1	1394.7	1394.2	1392.6	1390.9	1389.2	1387.5
142.5°	1445.6	1446.1	1445.4	1443.7	1442.1	1440.4	1438.7
145°	1519.9	1519.9	1519.4	1518.4	1517.4	1516.4	1515.4
147.5°	1590.0	1590.8	1590.1	1587.8	1585.5	1583.3	1580.9
150°	1632.7	1632.7	1632.3	1631.6	1631.0	1630.3	1629.6
152.5°	1674.2	1675.0	1674.8	1673.5	1672.3	1671.1	1669.9
155°	1732.7	1734.0	1733.9	1732.2	1730.5	1728.8	1727.2
157.5°	1783.0	1784.3	1783.9	1781.6	1779.4	1777.2	1774.9
160°	1813.4	1814.8	1814.6	1812.9	1811.2	1809.6	1807.9
162.5°	1842.3	1843.9	1843.7	1841.8	1839.8	1837.9	1835.8
165°	1880.5	1881.8	1881.5	1879.5	1877.4	1875.4	1873.3
167.5°	1909.6	1911.6	1911.6	1909.5	1907.4	1905.3	1903.2
170°	1926.6	1928.6	1928.5	1926.1	1923.8	1921.4	1919.0
172.5°	1938.8	1940.9	1940.9	1938.7	1936.6	1934.5	1932.5
175°	1952.6	1954.6	1954.4	1952.1	1949.6	1947.3	1944.9
177.5°	1958.3	1959.9	1959.8	1957.9	1956.0	1954.1	1952.3
180°	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1	1957.1

(END OF REPORT)