

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333393

Luminaire Tested: **S125DIW-S610D1340U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333393
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7153.9 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.3
10°-20°	255.8	3.6
20°-30°	377.7	5.3
30°-40°	440.7	6.2
40°-50°	442.6	6.2
50°-60°	388.5	5.4
60°-70°	289.5	4.0
70°-80°	165.5	2.3
80°-90°	51.8	0.7
90°-100°	111.6	1.6
100°-110°	329.7	4.6
110°-120°	558.4	7.8
120°-130°	734.9	10.3
130°-140°	823.5	11.5
140°-150°	807.1	11.3
150°-160°	677.9	9.5
160°-170°	450.6	6.3
170°-180°	157.7	2.2
0°-30°	724.0	10.1
0°-40°	1164.7	16.3
0°-60°	1995.9	27.9
0°-90°	2502.7	35.0
90°-120°	999.7	14.0
90°-150°	3365.1	47.0
90°-180°	4651.0	65.0
0°-180°	7153.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	1	12	21	27	31	7
95°	84	88	100	109	112	90
105°	296	302	310	318	322	316
115°	559	564	567	566	564	553
125°	816	823	825	822	821	730
135°	1061	1068	1070	1070	1065	818
145°	1286	1291	1295	1294	1291	803
155°	1471	1471	1472	1477	1471	677
165°	1599	1597	1598	1603	1596	451
175°	1663	1658	1658	1665	1656	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.7	17.1	17.6	18.1	18.5	18.9	19.1	19.4	19.7	20.0	20.2
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2
92.5°	31.4	33.0	34.6	36.2	37.8	39.9	42.4	44.9	47.3	49.8	51.7
95°	84.3	84.9	85.5	86.0	86.6	88.4	91.2	94.1	97.0	99.9	101.9
97.5°	140.1	140.3	140.6	140.8	141.0	143.1	147.1	151.1	155.1	159.0	160.9
100°	181.6	181.6	181.6	181.6	181.6	183.5	187.2	191.0	194.7	198.5	201.1
102.5°	226.2	227.4	228.5	229.7	230.8	232.4	234.3	236.2	238.1	240.0	242.8
105°	295.8	297.2	298.6	300.1	301.5	303.1	304.8	306.6	308.3	310.0	311.8
107.5°	372.5	374.0	375.4	376.9	378.3	379.7	381.0	382.3	383.7	385.0	385.9
110°	425.5	426.9	428.4	429.8	431.2	432.4	433.3	434.1	435.0	435.8	436.7



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.4	480.2	480.9	481.7	482.4	483.4	484.4	485.5	486.6	487.7	488.1
115°	559.1	560.2	561.4	562.5	563.7	564.6	565.1	565.7	566.3	566.9	566.6
117.5°	639.0	639.5	640.0	640.5	641.1	641.6	642.1	642.6	643.1	643.7	643.9
120°	688.8	690.2	691.7	693.1	694.6	695.4	695.7	696.0	696.3	696.6	696.6
122.5°	742.8	743.3	743.8	744.3	744.8	745.5	746.2	747.0	747.7	748.5	748.2
125°	815.9	817.6	819.4	821.1	822.8	823.8	824.1	824.4	824.7	825.0	824.4
127.5°	893.7	894.7	895.7	896.7	897.7	898.3	898.7	899.0	899.4	899.7	899.4
130°	940.4	941.9	943.3	944.8	946.2	947.2	947.8	948.4	948.9	949.5	949.2
132.5°	987.1	989.5	991.9	994.2	996.6	997.7	997.6	997.5	997.4	997.3	997.0
135°	1061.1	1062.8	1064.5	1066.3	1068.0	1069.0	1069.3	1069.6	1069.9	1070.2	1070.2
137.5°	1130.6	1132.3	1134.0	1135.6	1137.3	1138.4	1139.1	1139.7	1140.4	1141.0	1141.3
140°	1175.2	1176.7	1178.1	1179.6	1181.0	1182.1	1183.0	1183.9	1184.7	1185.6	1186.2
142.5°	1219.9	1221.1	1222.3	1223.5	1224.7	1225.8	1226.9	1228.0	1229.1	1230.2	1230.6
145°	1285.5	1286.6	1287.8	1288.9	1290.1	1291.1	1292.0	1292.8	1293.7	1294.6	1294.6
147.5°	1346.2	1346.8	1347.5	1348.1	1348.7	1349.4	1350.1	1350.8	1351.5	1352.2	1352.9
150°	1386.7	1386.4	1386.1	1385.8	1385.5	1385.9	1387.1	1388.3	1389.4	1390.6	1390.6
152.5°	1419.9	1420.3	1420.7	1421.1	1421.5	1421.9	1422.4	1422.8	1423.3	1423.8	1424.5
155°	1471.0	1471.0	1471.0	1471.0	1471.0	1471.1	1471.4	1471.7	1472.0	1472.3	1473.4
157.5°	1516.6	1516.0	1515.4	1514.7	1514.1	1513.9	1514.2	1514.5	1514.8	1515.1	1516.2
160°	1543.6	1542.8	1541.9	1541.0	1540.2	1539.9	1540.2	1540.5	1540.7	1541.0	1542.2
162.5°	1567.5	1566.9	1566.2	1565.6	1565.0	1564.7	1564.7	1564.8	1564.8	1564.9	1566.3
165°	1599.4	1598.8	1598.2	1597.7	1597.1	1597.0	1597.2	1597.5	1597.8	1598.1	1599.3
167.5°	1626.4	1625.2	1624.1	1622.9	1621.8	1621.2	1621.2	1621.2	1621.2	1621.2	1622.9
170°	1640.9	1639.8	1638.6	1637.5	1636.3	1635.7	1635.7	1635.7	1635.7	1635.7	1637.5
172.5°	1651.3	1650.1	1649.0	1647.8	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.8
175°	1663.0	1661.8	1660.7	1659.5	1658.4	1657.8	1657.8	1657.8	1657.8	1657.8	1659.5
177.5°	1668.9	1668.0	1667.1	1666.2	1665.2	1664.7	1664.4	1664.2	1664.0	1663.7	1665.1
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	20.5	20.8	21.1	21.2	21.1	21.0	20.9	20.8
90°	23.6	25.1	26.5	27.7	28.5	29.4	30.3	31.1
92.5°	53.6	55.5	57.4	58.7	59.3	60.0	60.6	61.2
95°	103.9	105.9	108.0	109.2	109.8	110.4	111.0	111.6
97.5°	162.8	164.7	166.6	167.8	168.1	168.5	168.8	169.2
100°	203.7	206.2	208.8	210.4	211.0	211.6	212.2	212.7
102.5°	245.6	248.4	251.3	253.1	253.9	254.7	255.5	256.3
105°	313.5	315.2	316.9	318.2	319.1	320.0	320.8	321.7
107.5°	386.7	387.6	388.5	388.9	388.8	388.7	388.7	388.6
110°	437.6	438.4	439.3	439.6	439.3	439.0	438.7	438.4



TEST NUMBER: P333393

CATALOG NUMBER: S125DIW-S610D1340U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	488.5	488.9	489.3	489.3	488.8	488.3	487.7	487.2
115°	566.3	566.0	565.7	565.4	565.1	564.8	564.6	564.3
117.5°	644.1	644.3	644.6	644.1	643.0	641.8	640.7	639.5
120°	696.6	696.6	696.6	696.0	694.8	693.7	692.5	691.4
122.5°	748.0	747.8	747.5	747.0	746.0	745.1	744.2	743.3
125°	823.8	823.3	822.7	822.3	822.0	821.7	821.4	821.1
127.5°	899.1	898.8	898.6	898.1	897.6	897.0	896.4	895.8
130°	948.9	948.7	948.4	947.9	947.4	946.8	946.2	945.6
132.5°	996.7	996.4	996.1	995.6	994.8	993.9	993.1	992.3
135°	1070.2	1070.2	1070.2	1069.6	1068.4	1067.3	1066.1	1065.0
137.5°	1141.7	1142.0	1142.4	1141.8	1140.4	1138.9	1137.5	1136.1
140°	1186.8	1187.3	1187.9	1187.5	1186.0	1184.6	1183.2	1181.7
142.5°	1230.9	1231.3	1231.6	1231.1	1229.6	1228.2	1226.7	1225.3
145°	1294.6	1294.6	1294.6	1294.1	1293.3	1292.4	1291.5	1290.7
147.5°	1353.5	1354.2	1354.9	1354.3	1352.3	1350.4	1348.4	1346.5
150°	1390.6	1390.6	1390.6	1390.3	1389.7	1389.1	1388.5	1388.0
152.5°	1425.1	1425.8	1426.5	1426.4	1425.3	1424.3	1423.2	1422.2
155°	1474.6	1475.7	1476.9	1476.7	1475.3	1473.9	1472.4	1471.0
157.5°	1517.4	1518.5	1519.7	1519.3	1517.4	1515.5	1513.6	1511.7
160°	1543.3	1544.5	1545.6	1545.5	1544.1	1542.6	1541.2	1539.7
162.5°	1567.7	1569.0	1570.4	1570.3	1568.6	1566.9	1565.3	1563.6
165°	1600.4	1601.6	1602.7	1602.4	1600.7	1599.0	1597.2	1595.5
167.5°	1624.7	1626.4	1628.1	1628.1	1626.3	1624.5	1622.7	1620.9
170°	1639.2	1640.9	1642.6	1642.5	1640.5	1638.5	1636.4	1634.4
172.5°	1649.6	1651.3	1653.0	1653.0	1651.2	1649.4	1647.6	1645.8
175°	1661.2	1663.0	1664.7	1664.5	1662.5	1660.5	1658.5	1656.5
177.5°	1666.5	1667.9	1669.3	1669.2	1667.5	1665.9	1664.3	1662.7
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9

(END OF REPORT)