

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333416

Luminaire Tested: **S125DIW-S850D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333416  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7608.5 lumens  
Efficiency: N/A  
Efficacy: 144.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45				
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38				
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32				
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27				
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20				
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.8	1.6
10°-20°	349.6	4.6
20°-30°	516.2	6.8
30°-40°	602.4	7.9
40°-50°	605.0	8.0
50°-60°	531.1	7.0
60°-70°	395.7	5.2
70°-80°	226.3	3.0
80°-90°	68.7	0.9
90°-100°	49.6	0.7
100°-110°	305.6	4.0
110°-120°	554.2	7.3
120°-130°	711.2	9.3
130°-140°	765.0	10.1
140°-150°	718.0	9.4
150°-160°	580.8	7.6
160°-170°	375.7	4.9
170°-180°	129.6	1.7
0°-30°	989.7	13.0
0°-40°	1592.1	20.9
0°-60°	2728.2	35.9
0°-90°	3418.8	44.9
90°-120°	909.3	12.0
90°-150°	3103.6	40.8
90°-180°	4190.0	55.1
0°-180°	7608.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	9	16	21	24	6
95°	58	53	16	21	21	73
105°	297	301	301	301	300	315
115°	558	563	564	560	554	553
125°	794	801	801	797	794	709
135°	990	996	994	992	986	763
145°	1148	1150	1150	1151	1145	718
155°	1264	1259	1260	1263	1255	582
165°	1334	1328	1329	1334	1327	377
175°	1364	1359	1359	1366	1358	130
180°	1364	1364	1364	1364	1364	



TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.6	23.0	23.4	23.7	24.1	24.3	24.4	24.6	24.7	24.8	25.1
90°	1.0	2.8	4.6	6.4	8.2	9.9	11.5	13.0	14.6	16.2	17.3
92.5°	15.6	14.3	13.1	11.8	10.5	10.6	12.0	13.4	14.8	16.2	17.3
95°	57.6	57.0	56.3	55.6	55.0	50.3	41.8	33.3	24.7	16.2	17.3
97.5°	120.4	121.6	122.8	124.0	125.2	117.4	100.5	83.6	66.7	49.8	43.4
100°	168.9	169.6	170.2	170.9	171.6	172.4	173.3	174.2	175.1	176.0	142.5
102.5°	218.3	219.1	220.0	220.8	221.7	222.4	222.9	223.4	224.0	224.5	218.2
105°	297.3	298.2	299.1	300.0	300.9	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	379.5	379.5	379.5	379.5	379.5	379.7	380.1	380.6	381.0	381.5	381.5
110°	432.9	432.9	432.9	432.9	432.9	433.1	433.5	434.0	434.4	434.9	434.2



TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	483.6	484.1	484.6	485.2	485.6	485.9	486.1	486.4	486.7	485.8
115°	558.3	559.4	560.5	561.6	562.8	563.4	563.7	563.9	564.1	564.3	563.4
117.5°	636.2	636.1	636.1	636.0	636.0	636.4	637.2	638.1	638.9	639.8	638.6
120°	684.7	684.5	684.2	684.0	683.8	684.0	684.7	685.4	686.0	686.7	686.3
122.5°	727.6	728.4	729.3	730.1	731.0	731.6	731.9	732.2	732.5	732.8	732.4
125°	793.9	795.5	797.1	798.6	800.2	801.0	801.0	801.0	801.0	801.0	800.1
127.5°	857.2	858.4	859.5	860.6	861.7	862.2	862.1	862.0	861.8	861.7	861.2
130°	896.1	897.2	898.3	899.4	900.6	901.2	901.5	901.7	901.9	902.1	901.5
132.5°	934.9	936.2	937.5	938.8	940.1	940.5	940.0	939.5	939.0	938.6	938.4
135°	990.1	991.5	992.8	994.2	995.5	996.0	995.5	995.1	994.6	994.2	993.7
137.5°	1040.9	1042.1	1043.2	1044.4	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4
140°	1074.1	1074.5	1075.0	1075.4	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5
142.5°	1104.0	1104.3	1104.6	1104.8	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7
145°	1147.9	1148.4	1148.8	1149.3	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2
147.5°	1186.3	1186.3	1186.2	1186.1	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4
150°	1210.6	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1
152.5°	1234.1	1233.1	1232.1	1231.1	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1
155°	1264.2	1262.9	1261.5	1260.2	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8
157.5°	1287.5	1286.7	1285.9	1285.1	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8
160°	1303.7	1302.3	1301.0	1299.6	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5
162.5°	1316.6	1315.3	1313.9	1312.6	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8
165°	1334.0	1332.7	1331.3	1330.0	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3
167.5°	1346.9	1345.6	1344.2	1342.8	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3
170°	1354.2	1352.7	1351.1	1349.5	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0
172.5°	1359.1	1357.5	1355.9	1354.4	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4
175°	1364.3	1363.0	1361.6	1360.3	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1
177.5°	1366.8	1365.7	1364.6	1363.5	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	25.3	25.5	25.7	25.7	25.5	25.3	25.0	24.8
90°	18.4	19.6	20.7	21.6	22.3	22.9	23.6	24.3
92.5°	18.4	19.6	20.7	21.4	21.7	22.0	22.3	22.7
95°	18.4	19.6	20.7	21.2	21.2	21.2	21.2	21.2
97.5°	37.1	30.7	24.4	21.2	21.2	21.2	21.2	21.2
100°	109.0	75.5	42.0	24.8	23.9	23.0	22.1	21.2
102.5°	211.8	205.5	199.2	188.4	173.1	157.8	142.5	127.2
105°	301.4	301.4	301.4	301.3	301.1	300.8	300.6	300.4
107.5°	381.6	381.6	381.7	381.4	380.7	380.0	379.3	378.7
110°	433.5	432.9	432.2	432.0	432.2	432.4	432.6	432.9





TEST NUMBER: P333416

CATALOG NUMBER: S125DIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	485.0	484.1	483.3	482.7	482.4	482.0	481.7	481.4
115°	562.5	561.6	560.7	559.6	558.3	556.9	555.6	554.2
117.5°	637.5	636.3	635.1	634.2	633.7	633.1	632.5	631.9
120°	685.8	685.4	684.9	684.1	683.0	681.9	680.8	679.6
122.5°	731.9	731.5	731.0	730.2	728.9	727.6	726.3	725.0
125°	799.2	798.3	797.4	796.6	796.0	795.3	794.6	793.9
127.5°	860.7	860.2	859.7	858.6	857.0	855.3	853.6	852.0
130°	900.8	900.1	899.4	898.5	897.4	896.3	895.2	894.1
132.5°	938.3	938.1	938.0	937.4	936.3	935.1	934.0	932.9
135°	993.3	992.8	992.4	991.5	990.1	988.8	987.4	986.1
137.5°	1044.5	1044.6	1044.7	1044.2	1043.0	1041.8	1040.7	1039.5
140°	1076.0	1076.4	1076.9	1076.4	1075.1	1073.7	1072.4	1071.0
142.5°	1106.8	1106.9	1107.0	1106.4	1105.0	1103.7	1102.3	1101.0
145°	1150.4	1150.6	1150.8	1150.3	1148.9	1147.6	1146.2	1144.9
147.5°	1187.7	1188.0	1188.2	1187.6	1185.9	1184.3	1182.7	1181.1
150°	1211.5	1212.0	1212.4	1211.7	1209.9	1208.1	1206.3	1204.5
152.5°	1232.5	1233.0	1233.4	1232.9	1231.2	1229.6	1228.0	1226.4
155°	1261.5	1262.2	1262.9	1262.3	1260.5	1258.7	1256.9	1255.1
157.5°	1285.5	1286.2	1286.9	1286.4	1284.6	1282.8	1281.0	1279.2
160°	1300.4	1301.3	1302.2	1301.7	1300.0	1298.2	1296.4	1294.6
162.5°	1314.1	1315.3	1316.6	1316.2	1314.2	1312.3	1310.3	1308.3
165°	1331.6	1333.0	1334.3	1334.1	1332.3	1330.5	1328.7	1326.9
167.5°	1344.9	1346.5	1348.2	1348.0	1345.9	1343.9	1341.9	1339.9
170°	1351.8	1353.6	1355.4	1355.2	1353.2	1351.2	1349.2	1347.1
172.5°	1357.1	1358.7	1360.3	1360.1	1358.1	1356.0	1354.0	1352.0
175°	1362.9	1364.7	1366.5	1366.4	1364.3	1362.3	1360.3	1358.3
177.5°	1365.2	1366.5	1367.8	1367.7	1366.2	1364.8	1363.4	1361.9
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3

(END OF REPORT)