

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333410

Luminaire Tested: **S125DIW-S850D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333410  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D770U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6487.6 lumens  
Efficiency: N/A  
Efficacy: 144.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.8	1.9
10°-20°	349.6	5.4
20°-30°	516.2	8.0
30°-40°	602.4	9.3
40°-50°	605.0	9.3
50°-60°	531.1	8.2
60°-70°	395.7	6.1
70°-80°	226.3	3.5
80°-90°	67.9	1.0
90°-100°	36.3	0.6
100°-110°	223.9	3.5
110°-120°	406.0	6.3
120°-130°	521.1	8.0
130°-140°	560.5	8.6
140°-150°	526.1	8.1
150°-160°	425.5	6.6
160°-170°	275.2	4.2
170°-180°	94.9	1.5
0°-30°	989.7	15.3
0°-40°	1592.1	24.5
0°-60°	2728.2	42.1
0°-90°	3418.1	52.7
90°-120°	666.2	10.3
90°-150°	2273.8	35.0
90°-180°	3069.0	47.3
0°-180°	6487.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	7	12	15	18	5
95°	42	39	12	15	16	54
105°	218	221	221	221	220	231
115°	409	413	414	410	406	405
125°	582	587	587	584	582	519
135°	725	730	728	727	722	559
145°	841	842	842	843	839	526
155°	926	922	923	925	920	427
165°	977	973	974	978	972	276
175°	1000	995	996	1001	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.6	22.8	23.1	23.4	23.6	23.8	23.8	23.9	23.9	24.0	24.1
90°	0.7	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7
92.5°	11.4	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7
95°	42.2	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7
97.5°	88.2	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8
100°	123.7	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4
102.5°	159.9	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9
105°	217.8	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5
110°	317.1	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1



TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.9	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9
115°	409.0	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8
117.5°	466.1	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9
120°	501.6	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8
122.5°	533.0	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6
125°	581.7	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2
127.5°	628.0	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9
130°	656.5	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4
132.5°	684.9	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5
135°	725.4	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0
137.5°	762.6	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2
140°	786.9	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0
142.5°	808.8	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8
145°	841.0	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6
147.5°	869.2	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9
150°	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3
152.5°	904.1	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7
155°	926.2	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7
157.5°	943.2	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3
160°	955.1	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1
162.5°	964.6	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8
165°	977.3	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6
167.5°	986.8	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1
170°	992.2	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0
172.5°	995.7	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0
175°	999.6	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2
177.5°	1001.3	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	24.3	24.5	24.6	24.6	24.3	24.0	23.8	23.5
90°	13.5	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	13.5	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	13.5	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	27.2	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	79.9	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	155.2	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.6	317.1	316.6	316.5	316.6	316.8	317.0	317.1





TEST NUMBER: P333410

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.3	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	412.1	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	467.0	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.5	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	536.2	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	585.5	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.6	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	660.0	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.4	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.7	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.3	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	810.9	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	842.8	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.1	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.6	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.0	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.2	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	941.8	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	952.7	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	962.7	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	975.6	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	985.3	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	990.3	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	994.2	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	998.5	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1000.2	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)