

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333710-840

Luminaire Tested: **S125RDIW-S1090D1050U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333710-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1050U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8498.1 lumens
Efficiency: N/A
Efficacy: 138.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	74	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	45	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	2.0
10°-20°	474.3	5.6
20°-30°	687.8	8.1
30°-40°	783.9	9.2
40°-50°	764.1	9.0
50°-60°	643.2	7.6
60°-70°	450.9	5.3
70°-80°	231.8	2.7
80°-90°	61.4	0.7
90°-100°	50.1	0.6
100°-110°	308.6	3.6
110°-120°	559.7	6.6
120°-130°	718.2	8.5
130°-140°	772.5	9.1
140°-150°	725.1	8.5
150°-160°	586.6	6.9
160°-170°	379.4	4.5
170°-180°	130.8	1.5
0°-30°	1331.9	15.7
0°-40°	2115.8	24.9
0°-60°	3523.1	41.5
0°-90°	4267.1	50.2
90°-120°	918.3	10.8
90°-150°	3134.2	36.9
90°-180°	4231.0	49.8
0°-180°	8498.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	9	16	21	24	6
95°	58	53	16	21	21	74
105°	300	304	304	304	303	318
115°	564	569	570	566	560	559
125°	802	808	809	805	802	716
135°	1000	1006	1004	1002	996	770
145°	1159	1161	1161	1162	1156	725
155°	1277	1271	1273	1275	1268	588
165°	1347	1341	1342	1347	1340	380
175°	1378	1372	1373	1380	1372	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.2	23.9	22.6	21.3	20.0	19.3	19.4	19.5	19.6	19.6	19.9
90°	1.0	2.8	4.6	6.5	8.3	10.0	11.6	13.1	14.7	16.4	17.5
92.5°	15.8	14.4	13.2	11.9	10.6	10.7	12.1	13.5	14.9	16.4	17.5
95°	58.2	57.6	56.9	56.1	55.5	50.8	42.2	33.6	24.9	16.4	17.5
97.5°	121.6	122.8	124.0	125.2	126.4	118.6	101.5	84.4	67.4	50.3	43.8
100°	170.6	171.3	171.9	172.6	173.3	174.1	175.0	175.9	176.8	177.7	143.9
102.5°	220.5	221.3	222.2	223.0	223.9	224.6	225.1	225.6	226.2	226.7	220.4
105°	300.2	301.1	302.1	303.0	303.9	304.4	304.4	304.4	304.4	304.4	304.4
107.5°	383.2	383.2	383.2	383.2	383.2	383.4	383.8	384.4	384.8	385.3	385.3
110°	437.2	437.2	437.2	437.2	437.2	437.4	437.8	438.3	438.7	439.2	438.5



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.4	488.9	489.4	490.0	490.4	490.7	490.9	491.2	491.5	490.6
115°	563.8	564.9	566.0	567.1	568.4	569.0	569.3	569.5	569.7	569.9	569.0
117.5°	642.5	642.4	642.4	642.3	642.3	642.7	643.5	644.4	645.2	646.1	644.9
120°	691.5	691.3	690.9	690.7	690.5	690.7	691.5	692.2	692.8	693.5	693.1
122.5°	734.8	735.6	736.5	737.3	738.2	738.8	739.1	739.4	739.7	740.0	739.6
125°	801.7	803.3	805.0	806.5	808.1	808.9	808.9	808.9	808.9	808.9	808.0
127.5°	865.7	866.9	868.0	869.1	870.2	870.7	870.6	870.5	870.3	870.2	869.7
130°	904.9	906.1	907.2	908.3	909.5	910.1	910.4	910.6	910.8	911.0	910.4
132.5°	944.1	945.4	946.7	948.1	949.4	949.8	949.3	948.8	948.3	947.9	947.7
135°	999.9	1001.3	1002.6	1004.0	1005.3	1005.8	1005.3	1004.9	1004.4	1004.0	1003.5
137.5°	1051.2	1052.4	1053.5	1054.7	1055.9	1056.3	1055.9	1055.5	1055.0	1054.6	1054.7
140°	1084.7	1085.1	1085.6	1086.0	1086.5	1086.6	1086.4	1086.1	1085.9	1085.7	1086.1
142.5°	1114.9	1115.2	1115.5	1115.7	1116.0	1116.3	1116.6	1116.9	1117.2	1117.5	1117.6
145°	1159.2	1159.7	1160.1	1160.6	1161.0	1161.2	1161.2	1161.2	1161.2	1161.2	1161.5
147.5°	1198.0	1198.0	1197.9	1197.8	1197.7	1197.8	1198.0	1198.3	1198.6	1198.8	1199.1
150°	1222.5	1222.1	1221.6	1221.2	1220.7	1220.7	1221.2	1221.6	1222.1	1222.5	1223.0
152.5°	1246.3	1245.3	1244.3	1243.2	1242.2	1242.0	1242.4	1242.9	1243.3	1243.7	1244.3
155°	1276.7	1275.4	1273.9	1272.6	1271.2	1270.8	1271.2	1271.7	1272.1	1272.6	1273.2
157.5°	1300.2	1299.4	1298.6	1297.8	1296.9	1296.6	1296.6	1296.6	1296.7	1296.7	1297.5
160°	1316.6	1315.1	1313.8	1312.4	1311.1	1310.5	1310.7	1311.0	1311.2	1311.4	1312.3
162.5°	1329.6	1328.3	1326.9	1325.5	1324.1	1323.5	1323.8	1324.0	1324.2	1324.4	1325.8
165°	1347.2	1345.8	1344.4	1343.1	1341.7	1341.1	1341.4	1341.6	1341.8	1342.0	1343.4
167.5°	1360.2	1358.9	1357.5	1356.0	1354.6	1354.0	1354.2	1354.4	1354.7	1354.9	1356.6
170°	1367.6	1366.0	1364.4	1362.8	1361.2	1360.6	1360.8	1361.0	1361.2	1361.5	1363.3
172.5°	1372.5	1370.9	1369.3	1367.8	1366.1	1365.5	1365.9	1366.3	1366.8	1367.2	1368.8
175°	1377.8	1376.4	1375.0	1373.7	1372.3	1371.8	1372.0	1372.2	1372.5	1372.7	1374.5
177.5°	1380.3	1379.2	1378.1	1377.0	1375.9	1375.4	1375.6	1375.8	1375.9	1376.1	1377.5
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	20.1	20.3	20.5	20.6	20.5	20.4	20.3	20.2
90°	18.6	19.8	20.9	21.8	22.5	23.1	23.8	24.5
92.5°	18.6	19.8	20.9	21.6	21.9	22.2	22.5	22.9
95°	18.6	19.8	20.9	21.4	21.4	21.4	21.4	21.4
97.5°	37.5	31.0	24.6	21.4	21.4	21.4	21.4	21.4
100°	110.1	76.2	42.4	25.0	24.1	23.2	22.3	21.4
102.5°	213.9	207.5	201.2	190.3	174.8	159.4	143.9	128.5
105°	304.4	304.4	304.4	304.3	304.1	303.8	303.6	303.4
107.5°	385.4	385.4	385.5	385.2	384.5	383.7	383.0	382.4
110°	437.8	437.2	436.5	436.3	436.5	436.7	436.9	437.2



TEST NUMBER: P333710-840

CATALOG NUMBER: S125RDIW-S1090D1050U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	489.8	488.9	488.1	487.5	487.2	486.8	486.5	486.1
115°	568.0	567.1	566.2	565.1	563.8	562.4	561.1	559.7
117.5°	643.8	642.6	641.4	640.5	640.0	639.3	638.7	638.1
120°	692.6	692.2	691.7	690.8	689.7	688.6	687.5	686.3
122.5°	739.1	738.7	738.2	737.4	736.1	734.8	733.5	732.2
125°	807.1	806.2	805.3	804.5	803.9	803.1	802.4	801.7
127.5°	869.2	868.7	868.2	867.1	865.5	863.7	862.0	860.4
130°	909.7	909.0	908.3	907.4	906.3	905.1	904.0	902.9
132.5°	947.6	947.4	947.3	946.6	945.5	944.3	943.2	942.1
135°	1003.1	1002.6	1002.2	1001.3	999.9	998.6	997.1	995.8
137.5°	1054.8	1054.9	1055.0	1054.5	1053.3	1052.1	1051.0	1049.8
140°	1086.6	1087.0	1087.5	1087.0	1085.7	1084.3	1083.0	1081.6
142.5°	1117.7	1117.8	1117.9	1117.3	1115.9	1114.6	1113.2	1111.9
145°	1161.7	1162.0	1162.2	1161.6	1160.2	1158.9	1157.5	1156.2
147.5°	1199.4	1199.7	1199.9	1199.3	1197.6	1196.0	1194.4	1192.8
150°	1223.5	1224.0	1224.4	1223.7	1221.8	1220.0	1218.2	1216.4
152.5°	1244.7	1245.2	1245.6	1245.1	1243.3	1241.7	1240.1	1238.5
155°	1273.9	1274.7	1275.4	1274.8	1272.9	1271.1	1269.3	1267.5
157.5°	1298.2	1298.9	1299.6	1299.1	1297.3	1295.5	1293.6	1291.8
160°	1313.2	1314.1	1315.0	1314.5	1312.8	1311.0	1309.2	1307.4
162.5°	1327.1	1328.3	1329.6	1329.2	1327.2	1325.2	1323.2	1321.2
165°	1344.7	1346.2	1347.5	1347.3	1345.4	1343.6	1341.8	1340.0
167.5°	1358.2	1359.8	1361.5	1361.3	1359.2	1357.2	1355.1	1353.1
170°	1365.1	1367.0	1368.8	1368.6	1366.5	1364.5	1362.5	1360.4
172.5°	1370.5	1372.1	1373.7	1373.5	1371.5	1369.4	1367.4	1365.3
175°	1376.3	1378.2	1380.0	1379.9	1377.8	1375.7	1373.7	1371.7
177.5°	1378.7	1380.0	1381.3	1381.2	1379.7	1378.3	1376.8	1375.3
180°	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8	1377.8

(END OF REPORT)