

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333710

Luminaire Tested: **S125RDIW-S1090D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333710  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1050U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8415.0 lumens  
Efficiency: N/A  
Efficacy: 137.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	74	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	45	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.1	2.0
10°-20°	469.7	5.6
20°-30°	681.1	8.1
30°-40°	776.2	9.2
40°-50°	756.6	9.0
50°-60°	636.9	7.6
60°-70°	446.5	5.3
70°-80°	229.5	2.7
80°-90°	60.8	0.7
90°-100°	49.6	0.6
100°-110°	305.6	3.6
110°-120°	554.2	6.6
120°-130°	711.2	8.5
130°-140°	765.0	9.1
140°-150°	718.0	8.5
150°-160°	580.8	6.9
160°-170°	375.7	4.5
170°-180°	129.6	1.5
0°-30°	1318.9	15.7
0°-40°	2095.1	24.9
0°-60°	3488.6	41.5
0°-90°	4225.4	50.2
90°-120°	909.3	10.8
90°-150°	3103.6	36.9
90°-180°	4190.0	49.8
0°-180°	8415.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	9	16	21	24	6
95°	58	53	16	21	21	73
105°	297	301	301	301	300	315
115°	558	563	564	560	554	553
125°	794	801	801	797	794	709
135°	990	996	994	992	986	763
145°	1148	1150	1150	1151	1145	718
155°	1264	1259	1260	1263	1255	582
165°	1334	1328	1329	1334	1327	377
175°	1364	1359	1359	1366	1358	130
180°	1364	1364	1364	1364	1364	



TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.7	22.4	21.1	19.8	19.1	19.2	19.3	19.4	19.4	19.7
90°	1.0	2.8	4.6	6.4	8.2	9.9	11.5	13.0	14.6	16.2	17.3
92.5°	15.6	14.3	13.1	11.8	10.5	10.6	12.0	13.4	14.8	16.2	17.3
95°	57.6	57.0	56.3	55.6	55.0	50.3	41.8	33.3	24.7	16.2	17.3
97.5°	120.4	121.6	122.8	124.0	125.2	117.4	100.5	83.6	66.7	49.8	43.4
100°	168.9	169.6	170.2	170.9	171.6	172.4	173.3	174.2	175.1	176.0	142.5
102.5°	218.3	219.1	220.0	220.8	221.7	222.4	222.9	223.4	224.0	224.5	218.2
105°	297.3	298.2	299.1	300.0	300.9	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	379.5	379.5	379.5	379.5	379.5	379.7	380.1	380.6	381.0	381.5	381.5
110°	432.9	432.9	432.9	432.9	432.9	433.1	433.5	434.0	434.4	434.9	434.2



TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	483.6	484.1	484.6	485.2	485.6	485.9	486.1	486.4	486.7	485.8
115°	558.3	559.4	560.5	561.6	562.8	563.4	563.7	563.9	564.1	564.3	563.4
117.5°	636.2	636.1	636.1	636.0	636.0	636.4	637.2	638.1	638.9	639.8	638.6
120°	684.7	684.5	684.2	684.0	683.8	684.0	684.7	685.4	686.0	686.7	686.3
122.5°	727.6	728.4	729.3	730.1	731.0	731.6	731.9	732.2	732.5	732.8	732.4
125°	793.9	795.5	797.1	798.6	800.2	801.0	801.0	801.0	801.0	801.0	800.1
127.5°	857.2	858.4	859.5	860.6	861.7	862.2	862.1	862.0	861.8	861.7	861.2
130°	896.1	897.2	898.3	899.4	900.6	901.2	901.5	901.7	901.9	902.1	901.5
132.5°	934.9	936.2	937.5	938.8	940.1	940.5	940.0	939.5	939.0	938.6	938.4
135°	990.1	991.5	992.8	994.2	995.5	996.0	995.5	995.1	994.6	994.2	993.7
137.5°	1040.9	1042.1	1043.2	1044.4	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4
140°	1074.1	1074.5	1075.0	1075.4	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5
142.5°	1104.0	1104.3	1104.6	1104.8	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7
145°	1147.9	1148.4	1148.8	1149.3	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2
147.5°	1186.3	1186.3	1186.2	1186.1	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4
150°	1210.6	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1
152.5°	1234.1	1233.1	1232.1	1231.1	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1
155°	1264.2	1262.9	1261.5	1260.2	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8
157.5°	1287.5	1286.7	1285.9	1285.1	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8
160°	1303.7	1302.3	1301.0	1299.6	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5
162.5°	1316.6	1315.3	1313.9	1312.6	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8
165°	1334.0	1332.7	1331.3	1330.0	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3
167.5°	1346.9	1345.6	1344.2	1342.8	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3
170°	1354.2	1352.7	1351.1	1349.5	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0
172.5°	1359.1	1357.5	1355.9	1354.4	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4
175°	1364.3	1363.0	1361.6	1360.3	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1
177.5°	1366.8	1365.7	1364.6	1363.5	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	19.9	20.1	20.3	20.4	20.3	20.2	20.1	20.0
90°	18.4	19.6	20.7	21.6	22.3	22.9	23.6	24.3
92.5°	18.4	19.6	20.7	21.4	21.7	22.0	22.3	22.7
95°	18.4	19.6	20.7	21.2	21.2	21.2	21.2	21.2
97.5°	37.1	30.7	24.4	21.2	21.2	21.2	21.2	21.2
100°	109.0	75.5	42.0	24.8	23.9	23.0	22.1	21.2
102.5°	211.8	205.5	199.2	188.4	173.1	157.8	142.5	127.2
105°	301.4	301.4	301.4	301.3	301.1	300.8	300.6	300.4
107.5°	381.6	381.6	381.7	381.4	380.7	380.0	379.3	378.7
110°	433.5	432.9	432.2	432.0	432.2	432.4	432.6	432.9





TEST NUMBER: P333710

CATALOG NUMBER: S125RDIW-S1090D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	485.0	484.1	483.3	482.7	482.4	482.0	481.7	481.4
115°	562.5	561.6	560.7	559.6	558.3	556.9	555.6	554.2
117.5°	637.5	636.3	635.1	634.2	633.7	633.1	632.5	631.9
120°	685.8	685.4	684.9	684.1	683.0	681.9	680.8	679.6
122.5°	731.9	731.5	731.0	730.2	728.9	727.6	726.3	725.0
125°	799.2	798.3	797.4	796.6	796.0	795.3	794.6	793.9
127.5°	860.7	860.2	859.7	858.6	857.0	855.3	853.6	852.0
130°	900.8	900.1	899.4	898.5	897.4	896.3	895.2	894.1
132.5°	938.3	938.1	938.0	937.4	936.3	935.1	934.0	932.9
135°	993.3	992.8	992.4	991.5	990.1	988.8	987.4	986.1
137.5°	1044.5	1044.6	1044.7	1044.2	1043.0	1041.8	1040.7	1039.5
140°	1076.0	1076.4	1076.9	1076.4	1075.1	1073.7	1072.4	1071.0
142.5°	1106.8	1106.9	1107.0	1106.4	1105.0	1103.7	1102.3	1101.0
145°	1150.4	1150.6	1150.8	1150.3	1148.9	1147.6	1146.2	1144.9
147.5°	1187.7	1188.0	1188.2	1187.6	1185.9	1184.3	1182.7	1181.1
150°	1211.5	1212.0	1212.4	1211.7	1209.9	1208.1	1206.3	1204.5
152.5°	1232.5	1233.0	1233.4	1232.9	1231.2	1229.6	1228.0	1226.4
155°	1261.5	1262.2	1262.9	1262.3	1260.5	1258.7	1256.9	1255.1
157.5°	1285.5	1286.2	1286.9	1286.4	1284.6	1282.8	1281.0	1279.2
160°	1300.4	1301.3	1302.2	1301.7	1300.0	1298.2	1296.4	1294.6
162.5°	1314.1	1315.3	1316.6	1316.2	1314.2	1312.3	1310.3	1308.3
165°	1331.6	1333.0	1334.3	1334.1	1332.3	1330.5	1328.7	1326.9
167.5°	1344.9	1346.5	1348.2	1348.0	1345.9	1343.9	1341.9	1339.9
170°	1351.8	1353.6	1355.4	1355.2	1353.2	1351.2	1349.2	1347.1
172.5°	1357.1	1358.7	1360.3	1360.1	1358.1	1356.0	1354.0	1352.0
175°	1362.9	1364.7	1366.5	1366.4	1364.3	1362.3	1360.3	1358.3
177.5°	1365.2	1366.5	1367.8	1367.7	1366.2	1364.8	1363.4	1361.9
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3

(END OF REPORT)