

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333712-840

Luminaire Tested: **S125RDIW-S1090D1340U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333712-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1340U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9721.9 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	71	81	75	70	65	62	59	56	51	49	46	41	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24				
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	29	27	24	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10723	10723	10723	10723
5°	12337	10738	9483	10738
10°	14152	10683	8368	10683
15°	15285	10573	7438	10573
20°	16855	10446	6868	10446
25°	19506	10278	6372	10278
30°	21227	10100	6049	10100
35°	17906	9894	5750	9894
40°	12505	9522	5493	9522
45°	9276	9020	5242	9020
50°	7396	8499	5027	8499
55°	6277	7851	4835	7851
60°	5424	7272	4525	7272
65°	4834	6645	3895	6645
70°	4247	6086	3552	6086
75°	3673	5273	3334	5273
80°	2786	4437	2786	4437
85°	2319	3490	2623	3490



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	1.6
10°-20°	466.6	4.8
20°-30°	739.8	7.6
30°-40°	892.2	9.2
40°-50°	796.7	8.2
50°-60°	611.0	6.3
60°-70°	397.1	4.1
70°-80°	193.0	2.0
80°-90°	49.8	0.5
90°-100°	64.1	0.7
100°-110°	395.0	4.1
110°-120°	716.5	7.4
120°-130°	919.5	9.5
130°-140°	989.0	10.2
140°-150°	928.3	9.5
150°-160°	750.9	7.7
160°-170°	485.7	5.0
170°-180°	167.5	1.7
0°-30°	1365.7	14.0
0°-40°	2257.9	23.2
0°-60°	3665.6	37.7
0°-90°	4305.5	44.3
90°-120°	1175.6	12.1
90°-150°	4012.4	41.3
90°-180°	5416.0	55.7
0°-180°	9721.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1903	1656	1463	1656	1903	190
15°	2286	1581	1112	1581	2286	655
25°	2737	1442	894	1442	2737	1257
35°	2271	1255	729	1255	2271	1372
45°	1016	988	574	988	1016	810
55°	558	697	429	697	558	506
65°	316	435	255	435	316	315
75°	147	211	134	211	147	157
85°	31	47	35	47	31	37
90°	31	1	31	1	31	15
95°	28	74	28	74	28	23
105°	388	384	388	384	388	351
115°	716	722	716	722	716	711
125°	1026	1026	1026	1026	1026	913
135°	1275	1280	1275	1280	1275	984
145°	1480	1484	1480	1484	1480	925
155°	1623	1634	1623	1634	1623	748
165°	1716	1725	1716	1725	1716	484
175°	1756	1764	1756	1764	1756	167
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1746.6	1745.5	1747.7	1741.6	1742.2	1732.9	1732.9	1725.9	1716.6	1709.5	1706.2
5°	1903.0	1904.4	1901.7	1891.5	1884.6	1874.4	1862.8	1842.4	1825.3	1809.0	1796.0
7.5°	2064.2	2065.1	2056.1	2053.0	2035.8	2023.3	1997.5	1969.6	1945.0	1913.7	1889.7
10°	2158.0	2157.3	2147.7	2140.2	2125.3	2106.2	2080.9	2048.2	2017.5	1983.5	1950.8
12.5°	2212.5	2210.7	2207.7	2198.6	2184.6	2167.8	2146.4	2114.2	2076.4	2039.1	2000.9
15°	2286.1	2281.3	2272.5	2260.9	2241.1	2221.3	2197.5	2168.9	2132.7	2090.4	2055.1
17.5°	2377.1	2377.3	2363.7	2347.5	2320.7	2285.8	2249.0	2202.8	2153.7	2107.3	2069.5
20°	2452.4	2450.3	2436.7	2405.4	2374.7	2331.1	2288.9	2232.2	2172.2	2111.6	2064.6
22.5°	2560.4	2555.1	2540.8	2499.7	2452.2	2396.0	2331.4	2262.2	2189.7	2120.8	2059.1
25°	2737.3	2733.2	2705.2	2657.6	2590.8	2504.2	2419.6	2324.9	2220.7	2130.0	2055.1
27.5°	2858.3	2853.9	2833.2	2793.5	2731.9	2640.8	2526.4	2399.7	2269.6	2144.9	2036.8
30°	2846.4	2856.6	2853.9	2835.5	2789.1	2707.3	2601.7	2459.2	2304.5	2158.0	2029.1
32.5°	2675.1	2684.3	2708.3	2744.4	2747.1	2714.4	2635.4	2504.0	2343.8	2177.1	2023.2
35°	2271.1	2283.4	2329.8	2402.7	2498.1	2577.8	2594.1	2523.2	2379.4	2200.2	2014.2
37.5°	1746.0	1813.0	1852.1	1928.8	2073.1	2219.7	2360.8	2412.8	2351.5	2190.7	1999.5
40°	1483.2	1499.5	1569.0	1655.6	1777.0	1929.7	2130.7	2275.8	2280.7	2168.9	1976.6
42.5°	1269.4	1290.1	1337.9	1406.9	1510.9	1663.6	1871.2	2062.6	2151.4	2108.9	1946.6
45°	1015.6	1031.3	1066.0	1119.2	1198.9	1325.0	1503.6	1725.2	1901.0	1969.8	1866.2
47.5°	834.2	842.7	873.0	913.5	972.5	1064.4	1202.6	1394.9	1605.9	1753.7	1739.2
50°	736.1	745.7	768.8	799.5	849.3	927.0	1037.4	1197.6	1415.0	1595.6	1631.7
52.5°	659.7	667.7	682.2	711.1	752.2	811.9	901.1	1046.0	1241.6	1433.7	1517.2
55°	557.5	563.0	574.6	591.0	623.7	666.6	743.7	843.8	1002.0	1195.5	1318.2
57.5°	473.3	476.1	483.4	498.6	521.2	552.5	608.1	693.1	806.5	980.8	1116.2
60°	419.9	422.6	432.1	442.3	460.1	488.7	532.3	591.6	700.6	844.6	981.5
62.5°	377.3	379.0	383.0	393.2	408.8	430.9	465.2	513.6	600.4	726.7	856.1
65°	316.3	316.9	318.3	326.5	336.0	352.3	374.9	409.0	474.4	569.9	684.3
67.5°	257.6	258.6	263.4	266.2	276.2	284.8	298.0	324.1	370.1	434.4	523.5
70°	224.9	224.3	229.0	232.5	235.8	246.1	254.9	276.1	304.7	353.8	428.1
72.5°	194.4	192.6	194.7	195.9	200.4	207.3	216.2	229.1	251.3	285.1	341.9
75°	147.2	147.9	147.9	149.3	152.7	155.4	158.1	164.9	177.2	199.8	230.4
77.5°	103.3	102.2	105.1	105.5	107.6	110.6	112.9	115.6	120.7	129.9	145.7
80°	74.9	74.9	75.6	77.7	77.1	78.4	81.8	84.5	90.7	96.1	101.6
82.5°	57.6	57.0	57.7	58.1	58.0	59.3	60.5	61.1	63.4	66.1	69.9
85°	31.3	31.3	32.0	32.0	32.7	32.7	33.4	33.4	33.4	34.0	34.7
87.5°	18.3	17.6	16.9	16.7	17.1	17.9	17.1	16.3	16.0	15.7	15.8
90°	31.4	30.5	29.6	28.8	27.9	26.8	25.2	23.8	22.4	20.9	18.9
92.5°	29.3	28.9	28.5	28.1	27.7	26.8	25.2	23.8	22.4	20.9	19.1
95°	27.5	27.5	27.5	27.5	27.5	26.8	25.2	23.8	22.4	20.9	31.9
97.5°	27.5	27.5	27.5	27.5	27.5	31.5	39.8	48.0	56.1	64.3	86.1
100°	27.5	28.6	29.8	30.9	32.1	54.3	97.7	140.9	184.2	227.5	226.3
102.5°	164.5	184.2	204.0	223.8	243.5	257.5	265.7	273.9	282.1	290.2	289.5
105°	388.3	388.6	388.9	389.2	389.5	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	489.6	490.4	491.3	492.1	493.0	493.4	493.4	493.3	493.2	493.2	492.6
110°	559.7	559.4	559.1	558.8	558.5	558.8	559.7	560.5	561.4	562.2	561.7



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.4	622.8	623.2	623.6	624.0	624.8	625.9	626.9	628.0	629.1	628.8
115°	716.5	718.2	720.0	721.8	723.5	725.0	726.1	727.3	728.4	729.6	729.3
117.5°	817.0	817.7	818.5	819.2	819.9	821.1	822.6	824.2	825.7	827.2	826.1
120°	878.7	880.1	881.5	883.0	884.4	885.4	886.1	886.7	887.3	887.8	887.0
122.5°	937.3	938.9	940.6	942.3	943.9	945.1	945.6	946.2	946.8	947.5	947.1
125°	1026.4	1027.2	1028.1	1029.1	1029.9	1030.9	1032.1	1033.2	1034.4	1035.5	1035.5
127.5°	1101.5	1103.6	1105.8	1107.9	1110.0	1111.5	1112.1	1112.8	1113.4	1114.0	1114.2
130°	1155.9	1157.3	1158.7	1160.2	1161.6	1162.9	1163.7	1164.6	1165.5	1166.3	1166.0
132.5°	1206.1	1207.5	1209.0	1210.4	1211.8	1212.6	1212.8	1213.0	1213.3	1213.4	1214.1
135°	1274.9	1276.6	1278.3	1280.1	1281.8	1282.9	1283.5	1284.1	1284.8	1285.3	1285.9
137.5°	1343.8	1345.3	1346.9	1348.4	1349.9	1350.6	1350.5	1350.4	1350.3	1350.2	1350.7
140°	1384.6	1386.4	1388.2	1389.9	1391.6	1392.2	1391.6	1391.1	1390.5	1389.9	1390.2
142.5°	1423.4	1425.1	1426.8	1428.6	1430.4	1431.2	1431.1	1430.9	1430.8	1430.7	1430.3
145°	1480.2	1481.9	1483.6	1485.3	1487.1	1487.8	1487.5	1487.2	1486.9	1486.6	1486.6
147.5°	1526.9	1529.0	1531.1	1533.2	1535.3	1536.2	1535.8	1535.5	1535.1	1534.8	1534.4
150°	1557.2	1559.5	1561.9	1564.2	1566.5	1567.4	1566.8	1566.3	1565.7	1565.1	1564.5
152.5°	1585.5	1587.6	1589.7	1591.7	1593.9	1594.6	1594.1	1593.5	1592.9	1592.3	1591.7
155°	1622.7	1625.0	1627.3	1629.6	1631.9	1632.6	1631.7	1630.9	1630.0	1629.2	1628.6
157.5°	1653.8	1656.1	1658.4	1660.7	1663.0	1663.8	1662.8	1661.9	1660.9	1660.0	1660.0
160°	1673.6	1676.0	1678.3	1680.6	1682.9	1683.5	1682.3	1681.2	1680.0	1678.9	1678.6
162.5°	1691.4	1693.9	1696.5	1699.1	1701.6	1702.1	1700.5	1698.8	1697.2	1695.6	1695.3
165°	1715.5	1717.8	1720.1	1722.4	1724.7	1725.1	1723.3	1721.5	1719.8	1718.1	1717.8
167.5°	1732.2	1734.8	1737.5	1740.0	1742.6	1742.9	1740.8	1738.8	1736.7	1734.5	1734.2
170°	1741.6	1744.2	1746.9	1749.5	1752.1	1752.2	1749.9	1747.6	1745.2	1742.9	1742.6
172.5°	1747.9	1750.5	1753.1	1755.8	1758.4	1758.6	1756.6	1754.4	1752.3	1750.2	1749.7
175°	1756.0	1758.6	1761.2	1763.8	1766.5	1766.6	1764.2	1761.9	1759.6	1757.3	1757.1
177.5°	1760.7	1762.5	1764.4	1766.3	1768.2	1768.3	1766.7	1765.0	1763.4	1761.7	1761.5
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1706.2	1702.3	1695.3	1688.7	1680.5	1673.4	1668.6	1662.5	1655.0	1645.7	1638.0
5°	1781.7	1766.7	1747.0	1729.9	1708.1	1691.0	1673.3	1656.3	1639.2	1617.4	1598.3
7.5°	1865.4	1834.4	1804.3	1766.5	1732.1	1701.4	1671.9	1642.1	1613.0	1582.0	1552.2
10°	1916.6	1879.2	1837.6	1789.9	1746.3	1704.7	1666.5	1629.0	1589.5	1554.7	1517.2
12.5°	1964.7	1916.2	1868.7	1808.5	1756.1	1705.3	1656.7	1609.9	1567.7	1522.6	1482.4
15°	2008.0	1960.2	1907.1	1833.5	1760.6	1699.2	1641.9	1581.3	1528.8	1478.3	1433.4
17.5°	2024.8	1974.7	1913.0	1842.2	1762.5	1685.4	1611.5	1545.1	1483.3	1424.5	1373.9
20°	2018.2	1969.8	1906.4	1839.0	1753.7	1673.3	1593.6	1519.9	1451.2	1389.1	1335.2
22.5°	2002.4	1952.4	1891.2	1819.9	1739.0	1653.7	1568.5	1490.0	1417.9	1353.6	1294.9
25°	1978.7	1910.6	1847.9	1778.3	1701.3	1616.8	1528.8	1442.3	1365.2	1299.8	1235.8
27.5°	1954.0	1869.0	1789.2	1720.1	1638.7	1563.3	1478.5	1389.8	1308.8	1242.1	1176.4
30°	1931.7	1836.2	1748.3	1669.9	1592.9	1521.4	1440.9	1354.3	1271.2	1202.3	1135.6
32.5°	1903.8	1802.4	1705.8	1615.4	1541.1	1470.1	1397.2	1314.5	1233.6	1162.6	1094.7
35°	1869.0	1739.5	1634.5	1538.3	1455.9	1387.0	1321.6	1254.9	1173.8	1100.1	1034.0
37.5°	1823.1	1676.2	1554.7	1450.1	1363.0	1293.9	1242.2	1181.2	1107.2	1036.7	975.3
40°	1795.3	1630.4	1497.4	1393.9	1302.5	1229.6	1181.2	1129.4	1062.0	995.8	934.4
42.5°	1758.3	1588.4	1439.7	1331.7	1239.8	1169.6	1120.6	1075.4	1018.9	956.5	890.8
45°	1685.6	1507.0	1350.9	1235.1	1142.4	1073.5	1027.8	987.6	944.7	887.5	830.2
47.5°	1590.9	1422.1	1258.8	1132.3	1041.5	977.5	933.2	901.5	870.8	822.1	766.5
50°	1515.2	1352.3	1192.8	1070.2	973.3	912.6	871.1	845.9	817.9	773.7	727.3
52.5°	1425.7	1280.3	1124.1	998.7	907.4	850.5	810.5	785.4	762.3	726.2	682.0
55°	1284.9	1157.4	1014.2	900.4	816.6	759.3	721.1	697.3	683.7	653.0	618.2
57.5°	1122.2	1030.9	904.6	794.9	720.7	664.2	636.2	615.9	600.5	578.9	554.3
60°	1008.8	944.7	831.5	727.3	659.1	605.2	580.1	563.0	548.7	530.3	511.2
62.5°	893.7	847.1	748.7	659.1	596.4	551.3	527.7	512.3	495.8	483.4	464.8
65°	739.5	697.9	629.8	559.6	501.7	465.5	448.5	434.8	424.6	411.0	398.1
67.5°	575.3	558.4	511.3	462.9	421.3	389.2	374.5	365.0	352.6	344.5	335.6
70°	474.4	466.3	432.8	400.8	361.9	340.1	326.5	322.3	307.4	299.2	293.1
72.5°	385.0	381.1	361.9	339.7	312.4	293.3	280.6	276.1	266.5	259.9	256.0
75°	263.8	265.2	261.8	247.4	237.2	224.9	214.0	211.3	204.5	199.0	195.6
77.5°	166.8	173.8	174.1	173.4	169.4	161.8	157.3	155.3	148.6	146.5	145.7
80°	114.5	122.0	128.9	128.2	126.7	124.7	121.3	119.3	115.8	113.8	112.5
82.5°	76.3	83.3	89.0	92.7	92.4	90.4	88.1	87.2	86.4	84.9	84.6
85°	36.2	37.5	39.5	44.3	47.7	48.4	47.7	47.1	44.9	45.6	46.4
87.5°	16.0	15.6	15.7	15.2	14.2	16.5	17.7	17.7	17.1	16.5	15.9
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	17.3	15.6	13.7	13.6	15.2	16.9	18.5	20.1	18.5	16.9	15.2
95°	43.0	54.0	65.0	71.0	71.9	72.8	73.6	74.5	73.6	72.8	71.9
97.5°	108.1	129.9	151.7	161.9	160.3	158.8	157.1	155.6	157.1	158.8	160.3
100°	225.2	224.0	222.9	221.9	221.0	220.0	219.2	218.3	219.2	220.0	221.0
102.5°	288.9	288.2	287.5	286.6	285.5	284.4	283.3	282.2	283.3	284.4	285.5
105°	389.6	389.6	389.6	389.1	387.9	386.8	385.6	384.5	385.6	386.8	387.9
107.5°	492.0	491.5	490.9	490.6	490.6	490.6	490.6	490.6	490.6	490.6	490.6
110°	561.1	560.5	559.9	559.7	559.7	559.7	559.7	559.7	559.7	559.7	559.7



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	628.4	628.1	627.8	627.2	626.5	625.9	625.2	624.5	625.2	625.9	626.5
115°	729.0	728.7	728.4	727.6	726.1	724.7	723.2	721.8	723.2	724.7	726.1
117.5°	825.0	823.8	822.7	822.2	822.2	822.3	822.3	822.4	822.3	822.3	822.2
120°	886.1	885.1	884.3	884.0	884.3	884.6	884.9	885.1	884.9	884.6	884.3
122.5°	946.6	946.2	945.8	945.0	943.9	942.8	941.7	940.6	941.7	942.8	943.9
125°	1035.5	1035.5	1035.5	1034.5	1032.5	1030.5	1028.4	1026.4	1028.4	1030.5	1032.5
127.5°	1114.4	1114.5	1114.7	1114.1	1112.6	1111.2	1109.7	1108.2	1109.7	1111.2	1112.6
130°	1165.7	1165.5	1165.2	1164.3	1162.9	1161.3	1159.9	1158.4	1159.9	1161.3	1162.9
132.5°	1214.7	1215.3	1216.0	1215.4	1213.8	1212.0	1210.3	1208.7	1210.3	1212.0	1213.8
135°	1286.5	1287.1	1287.6	1287.1	1285.3	1283.5	1281.8	1280.1	1281.8	1283.5	1285.3
137.5°	1351.2	1351.7	1352.2	1351.7	1350.2	1348.7	1347.2	1345.7	1347.2	1348.7	1350.2
140°	1390.5	1390.8	1391.1	1390.9	1390.3	1389.8	1389.2	1388.6	1389.2	1389.8	1390.3
142.5°	1429.9	1429.5	1429.1	1428.7	1428.4	1427.9	1427.6	1427.2	1427.6	1427.9	1428.4
145°	1486.6	1486.6	1486.6	1486.3	1485.8	1485.2	1484.6	1484.0	1484.6	1485.2	1485.8
147.5°	1534.1	1533.7	1533.4	1533.3	1533.4	1533.5	1533.6	1533.7	1533.6	1533.5	1533.4
150°	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1564.5	1564.0	1563.4
152.5°	1591.1	1590.5	1589.9	1590.3	1591.6	1592.9	1594.2	1595.4	1594.2	1592.9	1591.6
155°	1628.0	1627.4	1626.9	1627.4	1629.2	1630.9	1632.6	1634.4	1632.6	1630.9	1629.2
157.5°	1659.9	1659.8	1659.8	1660.3	1661.3	1662.3	1663.4	1664.5	1663.4	1662.3	1661.3
160°	1678.3	1678.0	1677.7	1678.4	1680.1	1681.9	1683.6	1685.4	1683.6	1681.9	1680.1
162.5°	1695.1	1694.8	1694.5	1695.2	1696.9	1698.6	1700.4	1702.1	1700.4	1698.6	1696.9
165°	1717.5	1717.2	1716.9	1717.7	1719.4	1721.1	1722.8	1724.6	1722.8	1721.1	1719.4
167.5°	1733.9	1733.6	1733.4	1734.1	1736.0	1737.8	1739.6	1741.3	1739.6	1737.8	1736.0
170°	1742.3	1742.0	1741.7	1742.6	1744.6	1746.7	1748.8	1750.8	1748.8	1746.7	1744.6
172.5°	1749.2	1748.7	1748.2	1748.9	1750.9	1753.0	1755.0	1757.1	1755.0	1753.0	1750.9
175°	1756.8	1756.5	1756.2	1756.9	1758.6	1760.4	1762.1	1763.8	1762.1	1760.4	1758.6
177.5°	1761.3	1761.1	1760.8	1761.4	1762.8	1764.2	1765.5	1767.0	1765.5	1764.2	1762.8
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1632.5	1625.0	1619.5	1608.6	1600.9	1597.7	1591.6	1590.0	1596.0	1591.6	1591.1
5°	1584.1	1564.3	1548.6	1532.9	1515.9	1505.0	1488.6	1485.9	1481.8	1475.6	1474.3
7.5°	1525.8	1500.1	1479.9	1454.0	1431.5	1413.4	1392.9	1383.2	1378.0	1370.0	1359.4
10°	1486.5	1455.9	1428.7	1402.7	1374.8	1352.3	1331.8	1316.2	1306.0	1296.4	1292.3
12.5°	1447.8	1416.6	1381.7	1350.4	1319.2	1293.9	1271.3	1261.1	1249.8	1238.6	1229.1
15°	1387.8	1346.2	1308.0	1271.8	1245.3	1218.0	1196.2	1181.2	1164.2	1159.4	1141.0
17.5°	1323.9	1283.1	1238.5	1200.4	1169.6	1139.6	1115.6	1098.6	1085.8	1068.2	1059.8
20°	1284.1	1235.8	1192.1	1157.4	1123.3	1087.8	1063.3	1048.9	1036.7	1022.4	1015.6
22.5°	1241.6	1194.3	1149.6	1108.8	1074.2	1039.4	1021.9	1007.0	993.1	979.9	970.9
25°	1179.1	1131.5	1084.4	1042.2	1006.0	980.8	960.4	943.3	935.8	922.9	913.3
27.5°	1117.4	1066.7	1017.9	975.7	947.5	922.5	905.7	892.2	878.7	867.4	859.1
30°	1077.6	1025.8	972.6	939.3	909.3	885.3	867.0	854.0	843.8	833.6	827.5
32.5°	1037.8	984.4	937.2	901.1	872.7	852.1	833.1	820.8	810.0	798.7	791.4
35°	974.0	919.5	881.3	845.9	817.9	798.8	785.9	768.2	759.3	751.1	743.7
37.5°	914.7	864.0	822.7	791.6	767.3	748.4	731.6	722.1	711.1	703.8	697.5
40°	871.1	824.8	787.3	754.6	736.8	715.7	700.0	687.7	679.5	670.0	663.2
42.5°	831.8	788.7	752.3	722.9	700.8	683.0	667.8	655.6	645.2	638.4	632.7
45°	776.4	733.4	697.9	670.7	650.3	633.2	617.5	611.4	597.7	589.6	586.8
47.5°	718.9	680.5	646.3	621.2	600.3	584.1	569.4	556.8	549.4	541.3	536.9
50°	680.2	643.4	611.4	586.8	566.4	548.7	535.0	526.8	516.6	509.2	503.7
52.5°	641.6	607.4	575.4	552.0	534.2	516.5	501.3	493.1	483.4	478.6	474.8
55°	586.2	550.1	522.8	499.6	481.2	464.8	450.5	442.3	436.3	431.4	430.1
57.5°	523.5	494.8	469.5	448.6	429.5	414.1	401.6	393.8	388.4	387.7	383.6
60°	482.6	456.7	433.5	411.0	394.7	380.3	369.4	360.5	355.1	354.5	353.0
62.5°	441.7	416.9	395.4	375.6	360.8	347.1	336.7	326.8	323.5	320.1	317.1
65°	381.0	358.5	340.8	325.1	309.4	297.8	287.6	281.6	274.0	269.9	262.5
67.5°	321.4	304.0	287.0	273.8	261.5	250.4	242.0	232.9	227.8	224.5	219.0
70°	282.2	268.5	251.6	237.2	227.6	218.8	212.0	201.8	198.3	195.6	192.9
72.5°	245.1	233.1	218.8	207.2	197.6	189.3	181.5	176.6	173.3	170.6	169.0
75°	192.9	181.3	169.1	160.9	154.0	147.2	143.1	139.8	138.4	137.6	134.9
77.5°	141.7	135.5	125.7	119.2	114.6	111.9	108.3	106.4	106.3	103.3	102.4
80°	108.4	104.9	96.7	94.0	90.7	88.0	85.8	82.5	79.1	77.7	75.6
82.5°	80.6	77.2	73.9	69.5	66.7	65.0	63.0	61.7	62.2	60.3	59.3
85°	42.9	39.5	38.2	37.5	36.2	37.5	36.8	36.2	35.4	34.7	35.4
87.5°	15.8	16.2	16.1	17.6	16.4	17.3	17.6	17.3	17.6	17.9	17.6
90°	10.6	12.8	14.8	16.9	18.9	20.9	22.4	23.8	25.2	26.8	27.9
92.5°	13.6	13.7	15.6	17.3	19.1	20.9	22.4	23.8	25.2	26.8	27.7
95°	71.0	65.0	54.0	43.0	31.9	20.9	22.4	23.8	25.2	26.8	27.5
97.5°	161.9	151.7	129.9	108.1	86.1	64.3	56.1	48.0	39.8	31.5	27.5
100°	221.9	222.9	224.0	225.2	226.3	227.5	184.2	140.9	97.7	54.3	32.1
102.5°	286.6	287.5	288.2	288.9	289.5	290.2	282.1	273.9	265.7	257.5	243.5
105°	389.1	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.5
107.5°	490.6	490.9	491.5	492.0	492.6	493.2	493.2	493.3	493.4	493.4	493.0
110°	559.7	559.9	560.5	561.1	561.7	562.2	561.4	560.5	559.7	558.8	558.5



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	627.2	627.8	628.1	628.4	628.8	629.1	628.0	626.9	625.9	624.8	624.0
115°	727.6	728.4	728.7	729.0	729.3	729.6	728.4	727.3	726.1	725.0	723.5
117.5°	822.2	822.7	823.8	825.0	826.1	827.2	825.7	824.2	822.6	821.1	819.9
120°	884.0	884.3	885.1	886.1	887.0	887.8	887.3	886.7	886.1	885.4	884.4
122.5°	945.0	945.8	946.2	946.6	947.1	947.5	946.8	946.2	945.6	945.1	943.9
125°	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4	1033.2	1032.1	1030.9	1029.9
127.5°	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4	1112.8	1112.1	1111.5	1110.0
130°	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5	1164.6	1163.7	1162.9	1161.6
132.5°	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3	1213.0	1212.8	1212.6	1211.8
135°	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8	1284.1	1283.5	1282.9	1281.8
137.5°	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3	1350.4	1350.5	1350.6	1349.9
140°	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5	1391.1	1391.6	1392.2	1391.6
142.5°	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8	1430.9	1431.1	1431.2	1430.4
145°	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9	1487.2	1487.5	1487.8	1487.1
147.5°	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1	1535.5	1535.8	1536.2	1535.3
150°	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7	1566.3	1566.8	1567.4	1566.5
152.5°	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9	1593.5	1594.1	1594.6	1593.9
155°	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0	1630.9	1631.7	1632.6	1631.9
157.5°	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9	1661.9	1662.8	1663.8	1663.0
160°	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0	1681.2	1682.3	1683.5	1682.9
162.5°	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2	1698.8	1700.5	1702.1	1701.6
165°	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8	1721.5	1723.3	1725.1	1724.7
167.5°	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7	1738.8	1740.8	1742.9	1742.6
170°	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2	1747.6	1749.9	1752.2	1752.1
172.5°	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3	1754.4	1756.6	1758.6	1758.4
175°	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6	1761.9	1764.2	1766.6	1766.5
177.5°	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4	1765.0	1766.7	1768.3	1768.2
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1590.5	1584.6	1583.0	1585.1	1583.0	1584.6	1590.5	1591.1	1591.6	1596.0	1590.0
5°	1467.5	1460.7	1464.1	1462.7	1464.1	1460.7	1467.5	1474.3	1475.6	1481.8	1485.9
7.5°	1359.3	1350.8	1341.8	1344.6	1341.8	1350.8	1359.3	1359.4	1370.0	1378.0	1383.2
10°	1283.4	1276.7	1272.5	1276.0	1272.5	1276.7	1283.4	1292.3	1296.4	1306.0	1316.2
12.5°	1219.6	1215.6	1212.0	1210.5	1212.0	1215.6	1219.6	1229.1	1238.6	1249.8	1261.1
15°	1132.9	1124.7	1121.3	1112.4	1121.3	1124.7	1132.9	1141.0	1159.4	1164.2	1181.2
17.5°	1052.8	1050.1	1041.2	1037.4	1041.2	1050.1	1052.8	1059.8	1068.2	1085.8	1098.6
20°	1005.3	1002.6	993.8	999.3	993.8	1002.6	1005.3	1015.6	1022.4	1036.7	1048.9
22.5°	966.1	960.1	957.3	955.6	957.3	960.1	966.1	970.9	979.9	993.1	1007.0
25°	910.6	901.7	898.4	894.2	898.4	901.7	910.6	913.3	922.9	935.8	943.3
27.5°	855.3	850.5	846.0	845.0	846.0	850.5	855.3	859.1	867.4	878.7	892.2
30°	819.3	814.6	811.1	811.1	811.1	814.6	819.3	827.5	833.6	843.8	854.0
32.5°	787.1	783.5	780.0	779.5	780.0	783.5	787.1	791.4	798.7	810.0	820.8
35°	740.2	734.8	733.4	729.3	733.4	734.8	740.2	743.7	751.1	759.3	768.2
37.5°	691.6	687.0	686.9	686.5	686.9	687.0	691.6	697.5	703.8	711.1	722.1
40°	660.5	657.0	656.4	651.6	656.4	657.0	660.5	663.2	670.0	679.5	687.7
42.5°	627.2	625.4	623.1	621.1	623.1	625.4	627.2	632.7	638.4	645.2	655.6
45°	582.1	577.3	577.3	573.9	577.3	577.3	582.1	586.8	589.6	597.7	611.4
47.5°	535.4	531.8	532.2	528.7	532.2	531.8	535.4	536.9	541.3	549.4	556.8
50°	504.4	502.3	501.7	500.3	501.7	502.3	504.4	503.7	509.2	516.6	526.8
52.5°	473.3	472.3	474.9	471.9	474.9	472.3	473.3	474.8	478.6	483.4	493.1
55°	431.4	429.4	433.5	429.4	433.5	429.4	431.4	430.1	431.4	436.3	442.3
57.5°	383.3	381.4	385.1	383.0	385.1	381.4	383.3	383.6	387.7	388.4	393.8
60°	351.7	347.6	349.6	350.3	349.6	347.6	351.7	353.0	354.5	355.1	360.5
62.5°	314.1	311.6	313.2	310.0	313.2	311.6	314.1	317.1	320.1	323.5	326.8
65°	261.1	259.0	256.3	254.9	256.3	259.0	261.1	262.5	269.9	274.0	281.6
67.5°	219.3	214.4	214.3	215.4	214.3	214.4	219.3	219.0	224.5	227.8	232.9
70°	188.8	188.8	188.1	188.1	188.1	188.8	188.8	192.9	195.6	198.3	201.8
72.5°	167.5	167.0	165.7	165.2	165.7	167.0	167.5	169.0	170.6	173.3	176.6
75°	134.9	135.6	134.3	133.6	134.3	135.6	134.9	134.9	137.6	138.4	139.8
77.5°	99.7	96.7	98.3	96.7	98.3	96.7	99.7	102.4	103.3	106.3	106.4
80°	75.6	74.9	77.1	74.9	77.1	74.9	75.6	75.6	77.7	79.1	82.5
82.5°	59.9	59.2	60.1	58.6	60.1	59.2	59.9	59.3	60.3	62.2	61.7
85°	36.2	35.4	34.7	35.4	34.7	35.4	36.2	35.4	34.7	35.4	36.2
87.5°	18.3	17.9	18.1	18.3	18.1	17.9	18.3	17.6	17.9	17.6	17.3
90°	28.8	29.6	30.5	31.4	30.5	29.6	28.8	27.9	26.8	25.2	23.8
92.5°	28.1	28.5	28.9	29.3	28.9	28.5	28.1	27.7	26.8	25.2	23.8
95°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	26.8	25.2	23.8
97.5°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	31.5	39.8	48.0
100°	30.9	29.8	28.6	27.5	28.6	29.8	30.9	32.1	54.3	97.7	140.9
102.5°	223.8	204.0	184.2	164.5	184.2	204.0	223.8	243.5	257.5	265.7	273.9
105°	389.2	388.9	388.6	388.3	388.6	388.9	389.2	389.5	389.6	389.6	389.6
107.5°	492.1	491.3	490.4	489.6	490.4	491.3	492.1	493.0	493.4	493.4	493.3
110°	558.8	559.1	559.4	559.7	559.4	559.1	558.8	558.5	558.8	559.7	560.5



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	623.6	623.2	622.8	622.4	622.8	623.2	623.6	624.0	624.8	625.9	626.9
115°	721.8	720.0	718.2	716.5	718.2	720.0	721.8	723.5	725.0	726.1	727.3
117.5°	819.2	818.5	817.7	817.0	817.7	818.5	819.2	819.9	821.1	822.6	824.2
120°	883.0	881.5	880.1	878.7	880.1	881.5	883.0	884.4	885.4	886.1	886.7
122.5°	942.3	940.6	938.9	937.3	938.9	940.6	942.3	943.9	945.1	945.6	946.2
125°	1029.1	1028.1	1027.2	1026.4	1027.2	1028.1	1029.1	1029.9	1030.9	1032.1	1033.2
127.5°	1107.9	1105.8	1103.6	1101.5	1103.6	1105.8	1107.9	1110.0	1111.5	1112.1	1112.8
130°	1160.2	1158.7	1157.3	1155.9	1157.3	1158.7	1160.2	1161.6	1162.9	1163.7	1164.6
132.5°	1210.4	1209.0	1207.5	1206.1	1207.5	1209.0	1210.4	1211.8	1212.6	1212.8	1213.0
135°	1280.1	1278.3	1276.6	1274.9	1276.6	1278.3	1280.1	1281.8	1282.9	1283.5	1284.1
137.5°	1348.4	1346.9	1345.3	1343.8	1345.3	1346.9	1348.4	1349.9	1350.6	1350.5	1350.4
140°	1389.9	1388.2	1386.4	1384.6	1386.4	1388.2	1389.9	1391.6	1392.2	1391.6	1391.1
142.5°	1428.6	1426.8	1425.1	1423.4	1425.1	1426.8	1428.6	1430.4	1431.2	1431.1	1430.9
145°	1485.3	1483.6	1481.9	1480.2	1481.9	1483.6	1485.3	1487.1	1487.8	1487.5	1487.2
147.5°	1533.2	1531.1	1529.0	1526.9	1529.0	1531.1	1533.2	1535.3	1536.2	1535.8	1535.5
150°	1564.2	1561.9	1559.5	1557.2	1559.5	1561.9	1564.2	1566.5	1567.4	1566.8	1566.3
152.5°	1591.7	1589.7	1587.6	1585.5	1587.6	1589.7	1591.7	1593.9	1594.6	1594.1	1593.5
155°	1629.6	1627.3	1625.0	1622.7	1625.0	1627.3	1629.6	1631.9	1632.6	1631.7	1630.9
157.5°	1660.7	1658.4	1656.1	1653.8	1656.1	1658.4	1660.7	1663.0	1663.8	1662.8	1661.9
160°	1680.6	1678.3	1676.0	1673.6	1676.0	1678.3	1680.6	1682.9	1683.5	1682.3	1681.2
162.5°	1699.1	1696.5	1693.9	1691.4	1693.9	1696.5	1699.1	1701.6	1702.1	1700.5	1698.8
165°	1722.4	1720.1	1717.8	1715.5	1717.8	1720.1	1722.4	1724.7	1725.1	1723.3	1721.5
167.5°	1740.0	1737.5	1734.8	1732.2	1734.8	1737.5	1740.0	1742.6	1742.9	1740.8	1738.8
170°	1749.5	1746.9	1744.2	1741.6	1744.2	1746.9	1749.5	1752.1	1752.2	1749.9	1747.6
172.5°	1755.8	1753.1	1750.5	1747.9	1750.5	1753.1	1755.8	1758.4	1758.6	1756.6	1754.4
175°	1763.8	1761.2	1758.6	1756.0	1758.6	1761.2	1763.8	1766.5	1766.6	1764.2	1761.9
177.5°	1766.3	1764.4	1762.5	1760.7	1762.5	1764.4	1766.3	1768.2	1768.3	1766.7	1765.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1591.6	1597.7	1600.9	1608.6	1619.5	1625.0	1632.5	1638.0	1645.7	1655.0	1662.5
5°	1488.6	1505.0	1515.9	1532.9	1548.6	1564.3	1584.1	1598.3	1617.4	1639.2	1656.3
7.5°	1392.9	1413.4	1431.5	1454.0	1479.9	1500.1	1525.8	1552.2	1582.0	1613.0	1642.1
10°	1331.8	1352.3	1374.8	1402.7	1428.7	1455.9	1486.5	1517.2	1554.7	1589.5	1629.0
12.5°	1271.3	1293.9	1319.2	1350.4	1381.7	1416.6	1447.8	1482.4	1522.6	1567.7	1609.9
15°	1196.2	1218.0	1245.3	1271.8	1308.0	1346.2	1387.8	1433.4	1478.3	1528.8	1581.3
17.5°	1115.6	1139.6	1169.6	1200.4	1238.5	1283.1	1323.9	1373.9	1424.5	1483.3	1545.1
20°	1063.3	1087.8	1123.3	1157.4	1192.1	1235.8	1284.1	1335.2	1389.1	1451.2	1519.9
22.5°	1021.9	1039.4	1074.2	1108.8	1149.6	1194.3	1241.6	1294.9	1353.6	1417.9	1490.0
25°	960.4	980.8	1006.0	1042.2	1084.4	1131.5	1179.1	1235.8	1299.8	1365.2	1442.3
27.5°	905.7	922.5	947.5	975.7	1017.9	1066.7	1117.4	1176.4	1242.1	1308.8	1389.8
30°	867.0	885.3	909.3	939.3	972.6	1025.8	1077.6	1135.6	1202.3	1271.2	1354.3
32.5°	833.1	852.1	872.7	901.1	937.2	984.4	1037.8	1094.7	1162.6	1233.6	1314.5
35°	785.9	798.8	817.9	845.9	881.3	919.5	974.0	1034.0	1100.1	1173.8	1254.9
37.5°	731.6	748.4	767.3	791.6	822.7	864.0	914.7	975.3	1036.7	1107.2	1181.2
40°	700.0	715.7	736.8	754.6	787.3	824.8	871.1	934.4	995.8	1062.0	1129.4
42.5°	667.8	683.0	700.8	722.9	752.3	788.7	831.8	890.8	956.5	1018.9	1075.4
45°	617.5	633.2	650.3	670.7	697.9	733.4	776.4	830.2	887.5	944.7	987.6
47.5°	569.4	584.1	600.3	621.2	646.3	680.5	718.9	766.5	822.1	870.8	901.5
50°	535.0	548.7	566.4	586.8	611.4	643.4	680.2	727.3	773.7	817.9	845.9
52.5°	501.3	516.5	534.2	552.0	575.4	607.4	641.6	682.0	726.2	762.3	785.4
55°	450.5	464.8	481.2	499.6	522.8	550.1	586.2	618.2	653.0	683.7	697.3
57.5°	401.6	414.1	429.5	448.6	469.5	494.8	523.5	554.3	578.9	600.5	615.9
60°	369.4	380.3	394.7	411.0	433.5	456.7	482.6	511.2	530.3	548.7	563.0
62.5°	336.7	347.1	360.8	375.6	395.4	416.9	441.7	464.8	483.4	495.8	512.3
65°	287.6	297.8	309.4	325.1	340.8	358.5	381.0	398.1	411.0	424.6	434.8
67.5°	242.0	250.4	261.5	273.8	287.0	304.0	321.4	335.6	344.5	352.6	365.0
70°	212.0	218.8	227.6	237.2	251.6	268.5	282.2	293.1	299.2	307.4	322.3
72.5°	181.5	189.3	197.6	207.2	218.8	233.1	245.1	256.0	259.9	266.5	276.1
75°	143.1	147.2	154.0	160.9	169.1	181.3	192.9	195.6	199.0	204.5	211.3
77.5°	108.3	111.9	114.6	119.2	125.7	135.5	141.7	145.7	146.5	148.6	155.3
80°	85.8	88.0	90.7	94.0	96.7	104.9	108.4	112.5	113.8	115.8	119.3
82.5°	63.0	65.0	66.7	69.5	73.9	77.2	80.6	84.6	84.9	86.4	87.2
85°	36.8	37.5	36.2	37.5	38.2	39.5	42.9	46.4	45.6	44.9	47.1
87.5°	17.6	17.3	16.4	17.6	16.1	16.2	15.8	15.9	16.5	17.1	17.7
90°	22.4	20.9	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	22.4	20.9	19.1	17.3	15.6	13.7	13.6	15.2	16.9	18.5	20.1
95°	22.4	20.9	31.9	43.0	54.0	65.0	71.0	71.9	72.8	73.6	74.5
97.5°	56.1	64.3	86.1	108.1	129.9	151.7	161.9	160.3	158.8	157.1	155.6
100°	184.2	227.5	226.3	225.2	224.0	222.9	221.9	221.0	220.0	219.2	218.3
102.5°	282.1	290.2	289.5	288.9	288.2	287.5	286.6	285.5	284.4	283.3	282.2
105°	389.6	389.6	389.6	389.6	389.6	389.6	389.1	387.9	386.8	385.6	384.5
107.5°	493.2	493.2	492.6	492.0	491.5	490.9	490.6	490.6	490.6	490.6	490.6
110°	561.4	562.2	561.7	561.1	560.5	559.9	559.7	559.7	559.7	559.7	559.7



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	628.0	629.1	628.8	628.4	628.1	627.8	627.2	626.5	625.9	625.2	624.5
115°	728.4	729.6	729.3	729.0	728.7	728.4	727.6	726.1	724.7	723.2	721.8
117.5°	825.7	827.2	826.1	825.0	823.8	822.7	822.2	822.2	822.3	822.3	822.4
120°	887.3	887.8	887.0	886.1	885.1	884.3	884.0	884.3	884.6	884.9	885.1
122.5°	946.8	947.5	947.1	946.6	946.2	945.8	945.0	943.9	942.8	941.7	940.6
125°	1034.4	1035.5	1035.5	1035.5	1035.5	1035.5	1034.5	1032.5	1030.5	1028.4	1026.4
127.5°	1113.4	1114.0	1114.2	1114.4	1114.5	1114.7	1114.1	1112.6	1111.2	1109.7	1108.2
130°	1165.5	1166.3	1166.0	1165.7	1165.5	1165.2	1164.3	1162.9	1161.3	1159.9	1158.4
132.5°	1213.3	1213.4	1214.1	1214.7	1215.3	1216.0	1215.4	1213.8	1212.0	1210.3	1208.7
135°	1284.8	1285.3	1285.9	1286.5	1287.1	1287.6	1287.1	1285.3	1283.5	1281.8	1280.1
137.5°	1350.3	1350.2	1350.7	1351.2	1351.7	1352.2	1351.7	1350.2	1348.7	1347.2	1345.7
140°	1390.5	1389.9	1390.2	1390.5	1390.8	1391.1	1390.9	1390.3	1389.8	1389.2	1388.6
142.5°	1430.8	1430.7	1430.3	1429.9	1429.5	1429.1	1428.7	1428.4	1427.9	1427.6	1427.2
145°	1486.9	1486.6	1486.6	1486.6	1486.6	1486.6	1486.3	1485.8	1485.2	1484.6	1484.0
147.5°	1535.1	1534.8	1534.4	1534.1	1533.7	1533.4	1533.3	1533.4	1533.5	1533.6	1533.7
150°	1565.7	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1
152.5°	1592.9	1592.3	1591.7	1591.1	1590.5	1589.9	1590.3	1591.6	1592.9	1594.2	1595.4
155°	1630.0	1629.2	1628.6	1628.0	1627.4	1626.9	1627.4	1629.2	1630.9	1632.6	1634.4
157.5°	1660.9	1660.0	1660.0	1659.9	1659.8	1659.8	1660.3	1661.3	1662.3	1663.4	1664.5
160°	1680.0	1678.9	1678.6	1678.3	1678.0	1677.7	1678.4	1680.1	1681.9	1683.6	1685.4
162.5°	1697.2	1695.6	1695.3	1695.1	1694.8	1694.5	1695.2	1696.9	1698.6	1700.4	1702.1
165°	1719.8	1718.1	1717.8	1717.5	1717.2	1716.9	1717.7	1719.4	1721.1	1722.8	1724.6
167.5°	1736.7	1734.5	1734.2	1733.9	1733.6	1733.4	1734.1	1736.0	1737.8	1739.6	1741.3
170°	1745.2	1742.9	1742.6	1742.3	1742.0	1741.7	1742.6	1744.6	1746.7	1748.8	1750.8
172.5°	1752.3	1750.2	1749.7	1749.2	1748.7	1748.2	1748.9	1750.9	1753.0	1755.0	1757.1
175°	1759.6	1757.3	1757.1	1756.8	1756.5	1756.2	1756.9	1758.6	1760.4	1762.1	1763.8
177.5°	1763.4	1761.7	1761.5	1761.3	1761.1	1760.8	1761.4	1762.8	1764.2	1765.5	1767.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1668.6	1673.4	1680.5	1688.7	1695.3	1702.3	1706.2	1706.2	1709.5	1716.6	1725.9
5°	1673.3	1691.0	1708.1	1729.9	1747.0	1766.7	1781.7	1796.0	1809.0	1825.3	1842.4
7.5°	1671.9	1701.4	1732.1	1766.5	1804.3	1834.4	1865.4	1889.7	1913.7	1945.0	1969.6
10°	1666.5	1704.7	1746.3	1789.9	1837.6	1879.2	1916.6	1950.8	1983.5	2017.5	2048.2
12.5°	1656.7	1705.3	1756.1	1808.5	1868.7	1916.2	1964.7	2000.9	2039.1	2076.4	2114.2
15°	1641.9	1699.2	1760.6	1833.5	1907.1	1960.2	2008.0	2055.1	2090.4	2132.7	2168.9
17.5°	1611.5	1685.4	1762.5	1842.2	1913.0	1974.7	2024.8	2069.5	2107.3	2153.7	2202.8
20°	1593.6	1673.3	1753.7	1839.0	1906.4	1969.8	2018.2	2064.6	2111.6	2172.2	2232.2
22.5°	1568.5	1653.7	1739.0	1819.9	1891.2	1952.4	2002.4	2059.1	2120.8	2189.7	2262.2
25°	1528.8	1616.8	1701.3	1778.3	1847.9	1910.6	1978.7	2055.1	2130.0	2220.7	2324.9
27.5°	1478.5	1563.3	1638.7	1720.1	1789.2	1869.0	1954.0	2036.8	2144.9	2269.6	2399.7
30°	1440.9	1521.4	1592.9	1669.9	1748.3	1836.2	1931.7	2029.1	2158.0	2304.5	2459.2
32.5°	1397.2	1470.1	1541.1	1615.4	1705.8	1802.4	1903.8	2023.2	2177.1	2343.8	2504.0
35°	1321.6	1387.0	1455.9	1538.3	1634.5	1739.5	1869.0	2014.2	2200.2	2379.4	2523.2
37.5°	1242.2	1293.9	1363.0	1450.1	1554.7	1676.2	1823.1	1999.5	2190.7	2351.5	2412.8
40°	1181.2	1229.6	1302.5	1393.9	1497.4	1630.4	1795.3	1976.6	2168.9	2280.7	2275.8
42.5°	1120.6	1169.6	1239.8	1331.7	1439.7	1588.4	1758.3	1946.6	2108.9	2151.4	2062.6
45°	1027.8	1073.5	1142.4	1235.1	1350.9	1507.0	1685.6	1866.2	1969.8	1901.0	1725.2
47.5°	933.2	977.5	1041.5	1132.3	1258.8	1422.1	1590.9	1739.2	1753.7	1605.9	1394.9
50°	871.1	912.6	973.3	1070.2	1192.8	1352.3	1515.2	1631.7	1595.6	1415.0	1197.6
52.5°	810.5	850.5	907.4	998.7	1124.1	1280.3	1425.7	1517.2	1433.7	1241.6	1046.0
55°	721.1	759.3	816.6	900.4	1014.2	1157.4	1284.9	1318.2	1195.5	1002.0	843.8
57.5°	636.2	664.2	720.7	794.9	904.6	1030.9	1122.2	1116.2	980.8	806.5	693.1
60°	580.1	605.2	659.1	727.3	831.5	944.7	1008.8	981.5	844.6	700.6	591.6
62.5°	527.7	551.3	596.4	659.1	748.7	847.1	893.7	856.1	726.7	600.4	513.6
65°	448.5	465.5	501.7	559.6	629.8	697.9	739.5	684.3	569.9	474.4	409.0
67.5°	374.5	389.2	421.3	462.9	511.3	558.4	575.3	523.5	434.4	370.1	324.1
70°	326.5	340.1	361.9	400.8	432.8	466.3	474.4	428.1	353.8	304.7	276.1
72.5°	280.6	293.3	312.4	339.7	361.9	381.1	385.0	341.9	285.1	251.3	229.1
75°	214.0	224.9	237.2	247.4	261.8	265.2	263.8	230.4	199.8	177.2	164.9
77.5°	157.3	161.8	169.4	173.4	174.1	173.8	166.8	145.7	129.9	120.7	115.6
80°	121.3	124.7	126.7	128.2	128.9	122.0	114.5	101.6	96.1	90.7	84.5
82.5°	88.1	90.4	92.4	92.7	89.0	83.3	76.3	69.9	66.1	63.4	61.1
85°	47.7	48.4	47.7	44.3	39.5	37.5	36.2	34.7	34.0	33.4	33.4
87.5°	17.7	16.5	14.2	15.2	15.7	15.6	16.0	15.8	15.7	16.0	16.3
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4	23.8
92.5°	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4	23.8
95°	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4	23.8
97.5°	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1	48.0
100°	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2	140.9
102.5°	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1	273.9
105°	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2	493.3
110°	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4	560.5



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0	626.9
115°	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4	727.3
117.5°	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7	824.2
120°	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3	886.7
122.5°	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8	946.2
125°	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4	1033.2
127.5°	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4	1112.8
130°	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5	1164.6
132.5°	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3	1213.0
135°	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8	1284.1
137.5°	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3	1350.4
140°	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5	1391.1
142.5°	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8	1430.9
145°	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9	1487.2
147.5°	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1	1535.5
150°	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7	1566.3
152.5°	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9	1593.5
155°	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0	1630.9
157.5°	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9	1661.9
160°	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0	1681.2
162.5°	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2	1698.8
165°	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8	1721.5
167.5°	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7	1738.8
170°	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2	1747.6
172.5°	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3	1754.4
175°	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6	1761.9
177.5°	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4	1765.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1732.9	1732.9	1742.2	1741.6	1747.7	1745.5	1746.6
5°	1862.8	1874.4	1884.6	1891.5	1901.7	1904.4	1903.0
7.5°	1997.5	2023.3	2035.8	2053.0	2056.1	2065.1	2064.2
10°	2080.9	2106.2	2125.3	2140.2	2147.7	2157.3	2158.0
12.5°	2146.4	2167.8	2184.6	2198.6	2207.7	2210.7	2212.5
15°	2197.5	2221.3	2241.1	2260.9	2272.5	2281.3	2286.1
17.5°	2249.0	2285.8	2320.7	2347.5	2363.7	2377.3	2377.1
20°	2288.9	2331.1	2374.7	2405.4	2436.7	2450.3	2452.4
22.5°	2331.4	2396.0	2452.2	2499.7	2540.8	2555.1	2560.4
25°	2419.6	2504.2	2590.8	2657.6	2705.2	2733.2	2737.3
27.5°	2526.4	2640.8	2731.9	2793.5	2833.2	2853.9	2858.3
30°	2601.7	2707.3	2789.1	2835.5	2853.9	2856.6	2846.4
32.5°	2635.4	2714.4	2747.1	2744.4	2708.3	2684.3	2675.1
35°	2594.1	2577.8	2498.1	2402.7	2329.8	2283.4	2271.1
37.5°	2360.8	2219.7	2073.1	1928.8	1852.1	1813.0	1746.0
40°	2130.7	1929.7	1777.0	1655.6	1569.0	1499.5	1483.2
42.5°	1871.2	1663.6	1510.9	1406.9	1337.9	1290.1	1269.4
45°	1503.6	1325.0	1198.9	1119.2	1066.0	1031.3	1015.6
47.5°	1202.6	1064.4	972.5	913.5	873.0	842.7	834.2
50°	1037.4	927.0	849.3	799.5	768.8	745.7	736.1
52.5°	901.1	811.9	752.2	711.1	682.2	667.7	659.7
55°	743.7	666.6	623.7	591.0	574.6	563.0	557.5
57.5°	608.1	552.5	521.2	498.6	483.4	476.1	473.3
60°	532.3	488.7	460.1	442.3	432.1	422.6	419.9
62.5°	465.2	430.9	408.8	393.2	383.0	379.0	377.3
65°	374.9	352.3	336.0	326.5	318.3	316.9	316.3
67.5°	298.0	284.8	276.2	266.2	263.4	258.6	257.6
70°	254.9	246.1	235.8	232.5	229.0	224.3	224.9
72.5°	216.2	207.3	200.4	195.9	194.7	192.6	194.4
75°	158.1	155.4	152.7	149.3	147.9	147.9	147.2
77.5°	112.9	110.6	107.6	105.5	105.1	102.2	103.3
80°	81.8	78.4	77.1	77.7	75.6	74.9	74.9
82.5°	60.5	59.3	58.0	58.1	57.7	57.0	57.6
85°	33.4	32.7	32.7	32.0	32.0	31.3	31.3
87.5°	17.1	17.9	17.1	16.7	16.9	17.6	18.3
90°	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	559.7	558.8	558.5	558.8	559.1	559.4	559.7



TEST NUMBER: P333712-840

CATALOG NUMBER: S125RDIW-S1090D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)