

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333713

Luminaire Tested: **S125RDIW-S1090D1340U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333713
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8914.6 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48														
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	48	47	47	41	41	41	41	41	41	41														
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35	35	35	35	35	35	35														
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30														
4	75	64	57	51	69	60	53	48	51	46	41	42	39	36	35	32	30	26	26	26	26	26	26	26														
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23														
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20														
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18	18	18	18	18	18	18														
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16	16	16	16														
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14	14	14	14	14	14	14														
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13	13	13	13	13	13	13														

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.8
10°-20°	462.1	5.2
20°-30°	732.6	8.2
30°-40°	883.5	9.9
40°-50°	789.0	8.9
50°-60°	605.0	6.8
60°-70°	393.2	4.4
70°-80°	191.2	2.1
80°-90°	49.3	0.6
90°-100°	111.6	1.3
100°-110°	329.7	3.7
110°-120°	558.4	6.3
120°-130°	734.9	8.2
130°-140°	823.5	9.2
140°-150°	807.1	9.1
150°-160°	677.9	7.6
160°-170°	450.6	5.1
170°-180°	157.7	1.8
0°-30°	1352.3	15.2
0°-40°	2235.8	25.1
0°-60°	3629.8	40.7
0°-90°	4263.4	47.8
90°-120°	999.7	11.2
90°-150°	3365.1	37.7
90°-180°	4651.0	52.2
0°-180°	8914.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	31	1	31	1	31	19
95°	112	84	112	84	112	114
105°	322	296	322	296	322	341
115°	564	559	564	559	564	558
125°	821	816	821	816	821	733
135°	1065	1061	1065	1061	1065	822
145°	1291	1286	1291	1286	1291	806
155°	1471	1471	1471	1471	1471	677
165°	1596	1599	1596	1599	1596	450
175°	1656	1663	1656	1663	1656	157
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	18.1	17.4	16.7	16.5	16.9	17.7	16.9	16.1	15.8	15.5	15.6
90°	31.1	30.3	29.4	28.5	27.7	26.5	25.1	23.6	22.2	20.8	18.7
92.5°	61.2	60.6	60.0	59.3	58.7	57.4	55.5	53.6	51.7	49.8	47.3
95°	111.6	111.0	110.4	109.8	109.2	108.0	105.9	103.9	101.9	99.9	97.0
97.5°	169.2	168.8	168.5	168.1	167.8	166.6	164.7	162.8	160.9	159.0	155.1
100°	212.7	212.2	211.6	211.0	210.4	208.8	206.2	203.7	201.1	198.5	194.7
102.5°	256.3	255.5	254.7	253.9	253.1	251.3	248.4	245.6	242.8	240.0	238.1
105°	321.7	320.8	320.0	319.1	318.2	316.9	315.2	313.5	311.8	310.0	308.3
107.5°	388.6	388.7	388.7	388.8	388.9	388.5	387.6	386.7	385.9	385.0	383.7
110°	438.4	438.7	439.0	439.3	439.6	439.3	438.4	437.6	436.7	435.8	435.0



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	487.7	488.3	488.8	489.3	489.3	488.9	488.5	488.1	487.7	486.6
115°	564.3	564.6	564.8	565.1	565.4	565.7	566.0	566.3	566.6	566.9	566.3
117.5°	639.5	640.7	641.8	643.0	644.1	644.6	644.3	644.1	643.9	643.7	643.1
120°	691.4	692.5	693.7	694.8	696.0	696.6	696.6	696.6	696.6	696.6	696.3
122.5°	743.3	744.2	745.1	746.0	747.0	747.5	747.8	748.0	748.2	748.5	747.7
125°	821.1	821.4	821.7	822.0	822.3	822.7	823.3	823.8	824.4	825.0	824.7
127.5°	895.8	896.4	897.0	897.6	898.1	898.6	898.8	899.1	899.4	899.7	899.4
130°	945.6	946.2	946.8	947.4	947.9	948.4	948.7	948.9	949.2	949.5	948.9
132.5°	992.3	993.1	993.9	994.8	995.6	996.1	996.4	996.7	997.0	997.3	997.4
135°	1065.0	1066.1	1067.3	1068.4	1069.6	1070.2	1070.2	1070.2	1070.2	1070.2	1069.9
137.5°	1136.1	1137.5	1138.9	1140.4	1141.8	1142.4	1142.0	1141.7	1141.3	1141.0	1140.4
140°	1181.7	1183.2	1184.6	1186.0	1187.5	1187.9	1187.3	1186.8	1186.2	1185.6	1184.7
142.5°	1225.3	1226.7	1228.2	1229.6	1231.1	1231.6	1231.3	1230.9	1230.6	1230.2	1229.1
145°	1290.7	1291.5	1292.4	1293.3	1294.1	1294.6	1294.6	1294.6	1294.6	1294.6	1293.7
147.5°	1346.5	1348.4	1350.4	1352.3	1354.3	1354.9	1354.2	1353.5	1352.9	1352.2	1351.5
150°	1388.0	1388.5	1389.1	1389.7	1390.3	1390.6	1390.6	1390.6	1390.6	1390.6	1389.4
152.5°	1422.2	1423.2	1424.3	1425.3	1426.4	1426.5	1425.8	1425.1	1424.5	1423.8	1423.3
155°	1471.0	1472.4	1473.9	1475.3	1476.7	1476.9	1475.7	1474.6	1473.4	1472.3	1472.0
157.5°	1511.7	1513.6	1515.5	1517.4	1519.3	1519.7	1518.5	1517.4	1516.2	1515.1	1514.8
160°	1539.7	1541.2	1542.6	1544.1	1545.5	1545.6	1544.5	1543.3	1542.2	1541.0	1540.7
162.5°	1563.6	1565.3	1566.9	1568.6	1570.3	1570.4	1569.0	1567.7	1566.3	1564.9	1564.8
165°	1595.5	1597.2	1599.0	1600.7	1602.4	1602.7	1601.6	1600.4	1599.3	1598.1	1597.8
167.5°	1620.9	1622.7	1624.5	1626.3	1628.1	1628.1	1626.4	1624.7	1622.9	1621.2	1621.2
170°	1634.4	1636.4	1638.5	1640.5	1642.5	1642.6	1640.9	1639.2	1637.5	1635.7	1635.7
172.5°	1645.8	1647.6	1649.4	1651.2	1653.0	1653.0	1651.3	1649.6	1647.8	1646.1	1646.1
175°	1656.5	1658.5	1660.5	1662.5	1664.5	1664.7	1663.0	1661.2	1659.5	1657.8	1657.8
177.5°	1662.7	1664.3	1665.9	1667.5	1669.2	1669.3	1667.9	1666.5	1665.1	1663.7	1664.0
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	15.8	15.4	15.5	15.1	14.1	16.3	17.5	17.5	16.9	16.3	15.7
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	44.9	42.4	39.9	37.8	36.2	34.6	33.0	31.4	33.0	34.6	36.2
95°	94.1	91.2	88.4	86.6	86.0	85.5	84.9	84.3	84.9	85.5	86.0
97.5°	151.1	147.1	143.1	141.0	140.8	140.6	140.3	140.1	140.3	140.6	140.8
100°	191.0	187.2	183.5	181.6	181.6	181.6	181.6	181.6	181.6	181.6	181.6
102.5°	236.2	234.3	232.4	230.8	229.7	228.5	227.4	226.2	227.4	228.5	229.7
105°	306.6	304.8	303.1	301.5	300.1	298.6	297.2	295.8	297.2	298.6	300.1
107.5°	382.3	381.0	379.7	378.3	376.9	375.4	374.0	372.5	374.0	375.4	376.9
110°	434.1	433.3	432.4	431.2	429.8	428.4	426.9	425.5	426.9	428.4	429.8



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	485.5	484.4	483.4	482.4	481.7	480.9	480.2	479.4	480.2	480.9	481.7
115°	565.7	565.1	564.6	563.7	562.5	561.4	560.2	559.1	560.2	561.4	562.5
117.5°	642.6	642.1	641.6	641.1	640.5	640.0	639.5	639.0	639.5	640.0	640.5
120°	696.0	695.7	695.4	694.6	693.1	691.7	690.2	688.8	690.2	691.7	693.1
122.5°	747.0	746.2	745.5	744.8	744.3	743.8	743.3	742.8	743.3	743.8	744.3
125°	824.4	824.1	823.8	822.8	821.1	819.4	817.6	815.9	817.6	819.4	821.1
127.5°	899.0	898.7	898.3	897.7	896.7	895.7	894.7	893.7	894.7	895.7	896.7
130°	948.4	947.8	947.2	946.2	944.8	943.3	941.9	940.4	941.9	943.3	944.8
132.5°	997.5	997.6	997.7	996.6	994.2	991.9	989.5	987.1	989.5	991.9	994.2
135°	1069.6	1069.3	1069.0	1068.0	1066.3	1064.5	1062.8	1061.1	1062.8	1064.5	1066.3
137.5°	1139.7	1139.1	1138.4	1137.3	1135.6	1134.0	1132.3	1130.6	1132.3	1134.0	1135.6
140°	1183.9	1183.0	1182.1	1181.0	1179.6	1178.1	1176.7	1175.2	1176.7	1178.1	1179.6
142.5°	1228.0	1226.9	1225.8	1224.7	1223.5	1222.3	1221.1	1219.9	1221.1	1222.3	1223.5
145°	1292.8	1292.0	1291.1	1290.1	1288.9	1287.8	1286.6	1285.5	1286.6	1287.8	1288.9
147.5°	1350.8	1350.1	1349.4	1348.7	1348.1	1347.5	1346.8	1346.2	1346.8	1347.5	1348.1
150°	1388.3	1387.1	1385.9	1385.5	1385.8	1386.1	1386.4	1386.7	1386.4	1386.1	1385.8
152.5°	1422.8	1422.4	1421.9	1421.5	1421.1	1420.7	1420.3	1419.9	1420.3	1420.7	1421.1
155°	1471.7	1471.4	1471.1	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0
157.5°	1514.5	1514.2	1513.9	1514.1	1514.7	1515.4	1516.0	1516.6	1516.0	1515.4	1514.7
160°	1540.5	1540.2	1539.9	1540.2	1541.0	1541.9	1542.8	1543.6	1542.8	1541.9	1541.0
162.5°	1564.8	1564.7	1564.7	1565.0	1565.6	1566.2	1566.9	1567.5	1566.9	1566.2	1565.6
165°	1597.5	1597.2	1597.0	1597.1	1597.7	1598.2	1598.8	1599.4	1598.8	1598.2	1597.7
167.5°	1621.2	1621.2	1621.2	1621.8	1622.9	1624.1	1625.2	1626.4	1625.2	1624.1	1622.9
170°	1635.7	1635.7	1635.7	1636.3	1637.5	1638.6	1639.8	1640.9	1639.8	1638.6	1637.5
172.5°	1646.1	1646.1	1646.1	1646.7	1647.8	1649.0	1650.1	1651.3	1650.1	1649.0	1647.8
175°	1657.8	1657.8	1657.8	1658.4	1659.5	1660.7	1661.8	1663.0	1661.8	1660.7	1659.5
177.5°	1664.2	1664.4	1664.7	1665.2	1666.2	1667.1	1668.0	1668.9	1668.0	1667.1	1666.2
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	15.6	16.0	15.9	17.4	16.2	17.1	17.4	17.1	17.4	17.7	17.4
90°	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6	25.1	26.5	27.7
92.5°	37.8	39.9	42.4	44.9	47.3	49.8	51.7	53.6	55.5	57.4	58.7
95°	86.6	88.4	91.2	94.1	97.0	99.9	101.9	103.9	105.9	108.0	109.2
97.5°	141.0	143.1	147.1	151.1	155.1	159.0	160.9	162.8	164.7	166.6	167.8
100°	181.6	183.5	187.2	191.0	194.7	198.5	201.1	203.7	206.2	208.8	210.4
102.5°	230.8	232.4	234.3	236.2	238.1	240.0	242.8	245.6	248.4	251.3	253.1
105°	301.5	303.1	304.8	306.6	308.3	310.0	311.8	313.5	315.2	316.9	318.2
107.5°	378.3	379.7	381.0	382.3	383.7	385.0	385.9	386.7	387.6	388.5	388.9
110°	431.2	432.4	433.3	434.1	435.0	435.8	436.7	437.6	438.4	439.3	439.6



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	482.4	483.4	484.4	485.5	486.6	487.7	488.1	488.5	488.9	489.3	489.3
115°	563.7	564.6	565.1	565.7	566.3	566.9	566.6	566.3	566.0	565.7	565.4
117.5°	641.1	641.6	642.1	642.6	643.1	643.7	643.9	644.1	644.3	644.6	644.1
120°	694.6	695.4	695.7	696.0	696.3	696.6	696.6	696.6	696.6	696.6	696.0
122.5°	744.8	745.5	746.2	747.0	747.7	748.5	748.2	748.0	747.8	747.5	747.0
125°	822.8	823.8	824.1	824.4	824.7	825.0	824.4	823.8	823.3	822.7	822.3
127.5°	897.7	898.3	898.7	899.0	899.4	899.7	899.4	899.1	898.8	898.6	898.1
130°	946.2	947.2	947.8	948.4	948.9	949.5	949.2	948.9	948.7	948.4	947.9
132.5°	996.6	997.7	997.6	997.5	997.4	997.3	997.0	996.7	996.4	996.1	995.6
135°	1068.0	1069.0	1069.3	1069.6	1069.9	1070.2	1070.2	1070.2	1070.2	1070.2	1069.6
137.5°	1137.3	1138.4	1139.1	1139.7	1140.4	1141.0	1141.3	1141.7	1142.0	1142.4	1141.8
140°	1181.0	1182.1	1183.0	1183.9	1184.7	1185.6	1186.2	1186.8	1187.3	1187.9	1187.5
142.5°	1224.7	1225.8	1226.9	1228.0	1229.1	1230.2	1230.6	1230.9	1231.3	1231.6	1231.1
145°	1290.1	1291.1	1292.0	1292.8	1293.7	1294.6	1294.6	1294.6	1294.6	1294.6	1294.1
147.5°	1348.7	1349.4	1350.1	1350.8	1351.5	1352.2	1352.9	1353.5	1354.2	1354.9	1354.3
150°	1385.5	1385.9	1387.1	1388.3	1389.4	1390.6	1390.6	1390.6	1390.6	1390.6	1390.3
152.5°	1421.5	1421.9	1422.4	1422.8	1423.3	1423.8	1424.5	1425.1	1425.8	1426.5	1426.4
155°	1471.0	1471.1	1471.4	1471.7	1472.0	1472.3	1473.4	1474.6	1475.7	1476.9	1476.7
157.5°	1514.1	1513.9	1514.2	1514.5	1514.8	1515.1	1516.2	1517.4	1518.5	1519.7	1519.3
160°	1540.2	1539.9	1540.2	1540.5	1540.7	1541.0	1542.2	1543.3	1544.5	1545.6	1545.5
162.5°	1565.0	1564.7	1564.7	1564.8	1564.8	1564.9	1566.3	1567.7	1569.0	1570.4	1570.3
165°	1597.1	1597.0	1597.2	1597.5	1597.8	1598.1	1599.3	1600.4	1601.6	1602.7	1602.4
167.5°	1621.8	1621.2	1621.2	1621.2	1621.2	1621.2	1622.9	1624.7	1626.4	1628.1	1628.1
170°	1636.3	1635.7	1635.7	1635.7	1635.7	1635.7	1637.5	1639.2	1640.9	1642.6	1642.5
172.5°	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.8	1649.6	1651.3	1653.0	1653.0
175°	1658.4	1657.8	1657.8	1657.8	1657.8	1657.8	1659.5	1661.2	1663.0	1664.7	1664.5
177.5°	1665.2	1664.7	1664.4	1664.2	1664.0	1663.7	1665.1	1666.5	1667.9	1669.3	1669.2
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	18.1	17.8	17.9	18.1	17.9	17.8	18.1	17.4	17.7	17.4	17.1
90°	28.5	29.4	30.3	31.1	30.3	29.4	28.5	27.7	26.5	25.1	23.6
92.5°	59.3	60.0	60.6	61.2	60.6	60.0	59.3	58.7	57.4	55.5	53.6
95°	109.8	110.4	111.0	111.6	111.0	110.4	109.8	109.2	108.0	105.9	103.9
97.5°	168.1	168.5	168.8	169.2	168.8	168.5	168.1	167.8	166.6	164.7	162.8
100°	211.0	211.6	212.2	212.7	212.2	211.6	211.0	210.4	208.8	206.2	203.7
102.5°	253.9	254.7	255.5	256.3	255.5	254.7	253.9	253.1	251.3	248.4	245.6
105°	319.1	320.0	320.8	321.7	320.8	320.0	319.1	318.2	316.9	315.2	313.5
107.5°	388.8	388.7	388.7	388.6	388.7	388.7	388.8	388.9	388.5	387.6	386.7
110°	439.3	439.0	438.7	438.4	438.7	439.0	439.3	439.6	439.3	438.4	437.6



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	488.8	488.3	487.7	487.2	487.7	488.3	488.8	489.3	489.3	488.9	488.5
115°	565.1	564.8	564.6	564.3	564.6	564.8	565.1	565.4	565.7	566.0	566.3
117.5°	643.0	641.8	640.7	639.5	640.7	641.8	643.0	644.1	644.6	644.3	644.1
120°	694.8	693.7	692.5	691.4	692.5	693.7	694.8	696.0	696.6	696.6	696.6
122.5°	746.0	745.1	744.2	743.3	744.2	745.1	746.0	747.0	747.5	747.8	748.0
125°	822.0	821.7	821.4	821.1	821.4	821.7	822.0	822.3	822.7	823.3	823.8
127.5°	897.6	897.0	896.4	895.8	896.4	897.0	897.6	898.1	898.6	898.8	899.1
130°	947.4	946.8	946.2	945.6	946.2	946.8	947.4	947.9	948.4	948.7	948.9
132.5°	994.8	993.9	993.1	992.3	993.1	993.9	994.8	995.6	996.1	996.4	996.7
135°	1068.4	1067.3	1066.1	1065.0	1066.1	1067.3	1068.4	1069.6	1070.2	1070.2	1070.2
137.5°	1140.4	1138.9	1137.5	1136.1	1137.5	1138.9	1140.4	1141.8	1142.4	1142.0	1141.7
140°	1186.0	1184.6	1183.2	1181.7	1183.2	1184.6	1186.0	1187.5	1187.9	1187.3	1186.8
142.5°	1229.6	1228.2	1226.7	1225.3	1226.7	1228.2	1229.6	1231.1	1231.6	1231.3	1230.9
145°	1293.3	1292.4	1291.5	1290.7	1291.5	1292.4	1293.3	1294.1	1294.6	1294.6	1294.6
147.5°	1352.3	1350.4	1348.4	1346.5	1348.4	1350.4	1352.3	1354.3	1354.9	1354.2	1353.5
150°	1389.7	1389.1	1388.5	1388.0	1388.5	1389.1	1389.7	1390.3	1390.6	1390.6	1390.6
152.5°	1425.3	1424.3	1423.2	1422.2	1423.2	1424.3	1425.3	1426.4	1426.5	1425.8	1425.1
155°	1475.3	1473.9	1472.4	1471.0	1472.4	1473.9	1475.3	1476.7	1476.9	1475.7	1474.6
157.5°	1517.4	1515.5	1513.6	1511.7	1513.6	1515.5	1517.4	1519.3	1519.7	1518.5	1517.4
160°	1544.1	1542.6	1541.2	1539.7	1541.2	1542.6	1544.1	1545.5	1545.6	1544.5	1543.3
162.5°	1568.6	1566.9	1565.3	1563.6	1565.3	1566.9	1568.6	1570.3	1570.4	1569.0	1567.7
165°	1600.7	1599.0	1597.2	1595.5	1597.2	1599.0	1600.7	1602.4	1602.7	1601.6	1600.4
167.5°	1626.3	1624.5	1622.7	1620.9	1622.7	1624.5	1626.3	1628.1	1628.1	1626.4	1624.7
170°	1640.5	1638.5	1636.4	1634.4	1636.4	1638.5	1640.5	1642.5	1642.6	1640.9	1639.2
172.5°	1651.2	1649.4	1647.6	1645.8	1647.6	1649.4	1651.2	1653.0	1653.0	1651.3	1649.6
175°	1662.5	1660.5	1658.5	1656.5	1658.5	1660.5	1662.5	1664.5	1664.7	1663.0	1661.2
177.5°	1667.5	1665.9	1664.3	1662.7	1664.3	1665.9	1667.5	1669.2	1669.3	1667.9	1666.5
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	17.4	17.1	16.2	17.4	15.9	16.0	15.6	15.7	16.3	16.9	17.5
90°	22.2	20.8	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	51.7	49.8	47.3	44.9	42.4	39.9	37.8	36.2	34.6	33.0	31.4
95°	101.9	99.9	97.0	94.1	91.2	88.4	86.6	86.0	85.5	84.9	84.3
97.5°	160.9	159.0	155.1	151.1	147.1	143.1	141.0	140.8	140.6	140.3	140.1
100°	201.1	198.5	194.7	191.0	187.2	183.5	181.6	181.6	181.6	181.6	181.6
102.5°	242.8	240.0	238.1	236.2	234.3	232.4	230.8	229.7	228.5	227.4	226.2
105°	311.8	310.0	308.3	306.6	304.8	303.1	301.5	300.1	298.6	297.2	295.8
107.5°	385.9	385.0	383.7	382.3	381.0	379.7	378.3	376.9	375.4	374.0	372.5
110°	436.7	435.8	435.0	434.1	433.3	432.4	431.2	429.8	428.4	426.9	425.5



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	488.1	487.7	486.6	485.5	484.4	483.4	482.4	481.7	480.9	480.2	479.4
115°	566.6	566.9	566.3	565.7	565.1	564.6	563.7	562.5	561.4	560.2	559.1
117.5°	643.9	643.7	643.1	642.6	642.1	641.6	641.1	640.5	640.0	639.5	639.0
120°	696.6	696.6	696.3	696.0	695.7	695.4	694.6	693.1	691.7	690.2	688.8
122.5°	748.2	748.5	747.7	747.0	746.2	745.5	744.8	744.3	743.8	743.3	742.8
125°	824.4	825.0	824.7	824.4	824.1	823.8	822.8	821.1	819.4	817.6	815.9
127.5°	899.4	899.7	899.4	899.0	898.7	898.3	897.7	896.7	895.7	894.7	893.7
130°	949.2	949.5	948.9	948.4	947.8	947.2	946.2	944.8	943.3	941.9	940.4
132.5°	997.0	997.3	997.4	997.5	997.6	997.7	996.6	994.2	991.9	989.5	987.1
135°	1070.2	1070.2	1069.9	1069.6	1069.3	1069.0	1068.0	1066.3	1064.5	1062.8	1061.1
137.5°	1141.3	1141.0	1140.4	1139.7	1139.1	1138.4	1137.3	1135.6	1134.0	1132.3	1130.6
140°	1186.2	1185.6	1184.7	1183.9	1183.0	1182.1	1181.0	1179.6	1178.1	1176.7	1175.2
142.5°	1230.6	1230.2	1229.1	1228.0	1226.9	1225.8	1224.7	1223.5	1222.3	1221.1	1219.9
145°	1294.6	1294.6	1293.7	1292.8	1292.0	1291.1	1290.1	1288.9	1287.8	1286.6	1285.5
147.5°	1352.9	1352.2	1351.5	1350.8	1350.1	1349.4	1348.7	1348.1	1347.5	1346.8	1346.2
150°	1390.6	1390.6	1389.4	1388.3	1387.1	1385.9	1385.5	1385.8	1386.1	1386.4	1386.7
152.5°	1424.5	1423.8	1423.3	1422.8	1422.4	1421.9	1421.5	1421.1	1420.7	1420.3	1419.9
155°	1473.4	1472.3	1472.0	1471.7	1471.4	1471.1	1471.0	1471.0	1471.0	1471.0	1471.0
157.5°	1516.2	1515.1	1514.8	1514.5	1514.2	1513.9	1514.1	1514.7	1515.4	1516.0	1516.6
160°	1542.2	1541.0	1540.7	1540.5	1540.2	1539.9	1540.2	1541.0	1541.9	1542.8	1543.6
162.5°	1566.3	1564.9	1564.8	1564.8	1564.7	1564.7	1565.0	1565.6	1566.2	1566.9	1567.5
165°	1599.3	1598.1	1597.8	1597.5	1597.2	1597.0	1597.1	1597.7	1598.2	1598.8	1599.4
167.5°	1622.9	1621.2	1621.2	1621.2	1621.2	1621.2	1621.8	1622.9	1624.1	1625.2	1626.4
170°	1637.5	1635.7	1635.7	1635.7	1635.7	1635.7	1636.3	1637.5	1638.6	1639.8	1640.9
172.5°	1647.8	1646.1	1646.1	1646.1	1646.1	1646.1	1646.7	1647.8	1649.0	1650.1	1651.3
175°	1659.5	1657.8	1657.8	1657.8	1657.8	1657.8	1658.4	1659.5	1660.7	1661.8	1663.0
177.5°	1665.1	1663.7	1664.0	1664.2	1664.4	1664.7	1665.2	1666.2	1667.1	1668.0	1668.9
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.5	16.3	14.1	15.1	15.5	15.4	15.8	15.6	15.5	15.8	16.1
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6
92.5°	33.0	34.6	36.2	37.8	39.9	42.4	44.9	47.3	49.8	51.7	53.6
95°	84.9	85.5	86.0	86.6	88.4	91.2	94.1	97.0	99.9	101.9	103.9
97.5°	140.3	140.6	140.8	141.0	143.1	147.1	151.1	155.1	159.0	160.9	162.8
100°	181.6	181.6	181.6	181.6	183.5	187.2	191.0	194.7	198.5	201.1	203.7
102.5°	227.4	228.5	229.7	230.8	232.4	234.3	236.2	238.1	240.0	242.8	245.6
105°	297.2	298.6	300.1	301.5	303.1	304.8	306.6	308.3	310.0	311.8	313.5
107.5°	374.0	375.4	376.9	378.3	379.7	381.0	382.3	383.7	385.0	385.9	386.7
110°	426.9	428.4	429.8	431.2	432.4	433.3	434.1	435.0	435.8	436.7	437.6



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.2	480.9	481.7	482.4	483.4	484.4	485.5	486.6	487.7	488.1	488.5
115°	560.2	561.4	562.5	563.7	564.6	565.1	565.7	566.3	566.9	566.6	566.3
117.5°	639.5	640.0	640.5	641.1	641.6	642.1	642.6	643.1	643.7	643.9	644.1
120°	690.2	691.7	693.1	694.6	695.4	695.7	696.0	696.3	696.6	696.6	696.6
122.5°	743.3	743.8	744.3	744.8	745.5	746.2	747.0	747.7	748.5	748.2	748.0
125°	817.6	819.4	821.1	822.8	823.8	824.1	824.4	824.7	825.0	824.4	823.8
127.5°	894.7	895.7	896.7	897.7	898.3	898.7	899.0	899.4	899.7	899.4	899.1
130°	941.9	943.3	944.8	946.2	947.2	947.8	948.4	948.9	949.5	949.2	948.9
132.5°	989.5	991.9	994.2	996.6	997.7	997.6	997.5	997.4	997.3	997.0	996.7
135°	1062.8	1064.5	1066.3	1068.0	1069.0	1069.3	1069.6	1069.9	1070.2	1070.2	1070.2
137.5°	1132.3	1134.0	1135.6	1137.3	1138.4	1139.1	1139.7	1140.4	1141.0	1141.3	1141.7
140°	1176.7	1178.1	1179.6	1181.0	1182.1	1183.0	1183.9	1184.7	1185.6	1186.2	1186.8
142.5°	1221.1	1222.3	1223.5	1224.7	1225.8	1226.9	1228.0	1229.1	1230.2	1230.6	1230.9
145°	1286.6	1287.8	1288.9	1290.1	1291.1	1292.0	1292.8	1293.7	1294.6	1294.6	1294.6
147.5°	1346.8	1347.5	1348.1	1348.7	1349.4	1350.1	1350.8	1351.5	1352.2	1352.9	1353.5
150°	1386.4	1386.1	1385.8	1385.5	1385.9	1387.1	1388.3	1389.4	1390.6	1390.6	1390.6
152.5°	1420.3	1420.7	1421.1	1421.5	1421.9	1422.4	1422.8	1423.3	1423.8	1424.5	1425.1
155°	1471.0	1471.0	1471.0	1471.0	1471.1	1471.4	1471.7	1472.0	1472.3	1473.4	1474.6
157.5°	1516.0	1515.4	1514.7	1514.1	1513.9	1514.2	1514.5	1514.8	1515.1	1516.2	1517.4
160°	1542.8	1541.9	1541.0	1540.2	1539.9	1540.2	1540.5	1540.7	1541.0	1542.2	1543.3
162.5°	1566.9	1566.2	1565.6	1565.0	1564.7	1564.7	1564.8	1564.8	1564.9	1566.3	1567.7
165°	1598.8	1598.2	1597.7	1597.1	1597.0	1597.2	1597.5	1597.8	1598.1	1599.3	1600.4
167.5°	1625.2	1624.1	1622.9	1621.8	1621.2	1621.2	1621.2	1621.2	1621.2	1622.9	1624.7
170°	1639.8	1638.6	1637.5	1636.3	1635.7	1635.7	1635.7	1635.7	1635.7	1637.5	1639.2
172.5°	1650.1	1649.0	1647.8	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.8	1649.6
175°	1661.8	1660.7	1659.5	1658.4	1657.8	1657.8	1657.8	1657.8	1657.8	1659.5	1661.2
177.5°	1668.0	1667.1	1666.2	1665.2	1664.7	1664.4	1664.2	1664.0	1663.7	1665.1	1666.5
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	16.9	17.7	16.9	16.5	16.7	17.4	18.1
90°	25.1	26.5	27.7	28.5	29.4	30.3	31.1
92.5°	55.5	57.4	58.7	59.3	60.0	60.6	61.2
95°	105.9	108.0	109.2	109.8	110.4	111.0	111.6
97.5°	164.7	166.6	167.8	168.1	168.5	168.8	169.2
100°	206.2	208.8	210.4	211.0	211.6	212.2	212.7
102.5°	248.4	251.3	253.1	253.9	254.7	255.5	256.3
105°	315.2	316.9	318.2	319.1	320.0	320.8	321.7
107.5°	387.6	388.5	388.9	388.8	388.7	388.7	388.6
110°	438.4	439.3	439.6	439.3	439.0	438.7	438.4



TEST NUMBER: P333713

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	488.9	489.3	489.3	488.8	488.3	487.7	487.2
115°	566.0	565.7	565.4	565.1	564.8	564.6	564.3
117.5°	644.3	644.6	644.1	643.0	641.8	640.7	639.5
120°	696.6	696.6	696.0	694.8	693.7	692.5	691.4
122.5°	747.8	747.5	747.0	746.0	745.1	744.2	743.3
125°	823.3	822.7	822.3	822.0	821.7	821.4	821.1
127.5°	898.8	898.6	898.1	897.6	897.0	896.4	895.8
130°	948.7	948.4	947.9	947.4	946.8	946.2	945.6
132.5°	996.4	996.1	995.6	994.8	993.9	993.1	992.3
135°	1070.2	1070.2	1069.6	1068.4	1067.3	1066.1	1065.0
137.5°	1142.0	1142.4	1141.8	1140.4	1138.9	1137.5	1136.1
140°	1187.3	1187.9	1187.5	1186.0	1184.6	1183.2	1181.7
142.5°	1231.3	1231.6	1231.1	1229.6	1228.2	1226.7	1225.3
145°	1294.6	1294.6	1294.1	1293.3	1292.4	1291.5	1290.7
147.5°	1354.2	1354.9	1354.3	1352.3	1350.4	1348.4	1346.5
150°	1390.6	1390.6	1390.3	1389.7	1389.1	1388.5	1388.0
152.5°	1425.8	1426.5	1426.4	1425.3	1424.3	1423.2	1422.2
155°	1475.7	1476.9	1476.7	1475.3	1473.9	1472.4	1471.0
157.5°	1518.5	1519.7	1519.3	1517.4	1515.5	1513.6	1511.7
160°	1544.5	1545.6	1545.5	1544.1	1542.6	1541.2	1539.7
162.5°	1569.0	1570.4	1570.3	1568.6	1566.9	1565.3	1563.6
165°	1601.6	1602.7	1602.4	1600.7	1599.0	1597.2	1595.5
167.5°	1626.4	1628.1	1628.1	1626.3	1624.5	1622.7	1620.9
170°	1640.9	1642.6	1642.5	1640.5	1638.5	1636.4	1634.4
172.5°	1651.3	1653.0	1653.0	1651.2	1649.4	1647.6	1645.8
175°	1663.0	1664.7	1664.5	1662.5	1660.5	1658.5	1656.5
177.5°	1667.9	1669.3	1669.2	1667.5	1665.9	1664.3	1662.7
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9

(END OF REPORT)